

Space, Avionics & Defense

Capacitors



KEMET makes it possible.

Electronic Components
KEMET
CHARGED.®

Tantalum Defense and Aerospace Parts

QPL (Qualified Product Listing)	Style	MIL-PRF/DLA/ KEMET Specification	KEMET Series	Space Qualified	Thermal Shock	Surge Current	Capacitance/DF	DC Leakage	ESR	3 Sigma Screening	Seal Test	Voltage Aging	Weibull Grading	X-Ray	Reflow Conditioning	DPA	Lead Pull Strength	Visual/Mechanical	Surge Voltage	PDA	Temperature Stability	Solderability	F-Tech	Stimulated Breakdown Screening (SBDS)	Step Stress Surge Test (SSST)	Polymer Reliability Assessment Method	Group C	Group B
N/A	N/A	GR500	T210/T220/T240	★	●	●	●	●	●		●		●	2														
QPL 39003	CSS13/33	MIL-PRF-39003/10	T216/T256	★	●	●	●	●	●		●		●	2														
QPL 39003	CSR13	MIL-PRF-39003/01	T212/T215		●	○	●	●	●		●		●	1														
QPL 39003	CSR09	MIL-PRF-39003/02	T222/T225		●	○	●	●	●		●		●	1														
QPL 39003	CSR23	MIL-PRF-39003/03	T242/T245		●	○	●	●	●		●		●	1														
QPL 39003	CSR91	MIL-PRF-39003/04	T213		●	○	●	●	●		●		●	1														
QPL 39003	CSR33	MIL-PRF-39003/06	T252/T255		●	●	●	●	●		●		●	1														
QPL 39003	CSR21	MIL-PRF-39003/09	T262		●	●	●	●	●		●		●	1					●		●	●						
QPL 49137	CX01, CX05	MIL-PRF-49137/1/5	T323		●														●		●	●						
QPL 49137	CX02, CX12	MIL-PRF-49137/2	T363, T369		●														●		●	●						
QPL 49137	CX06	MIL-PRF-49137/6	T378		●																●	●						
N/A	N/A	DLA 13030	T550			○	●	●	●		●	●		1				●				●	●			○		
N/A	N/A	Polymer Hermetic Seal 125°C	T551			○	●	●	●		●	●		1				●				●	●			○		
N/A	N/A	Polymer Hermetic Seal Modules	M550/M551*				●	●	●		●	●		1				●				●	●			○		
QPL 55365	CWR11	MIL-PRF-55365/8	T492		●	○	●	●	●				●	1	●			●				●	●					
QPL 55365	CWR09/19/29	MIL-PRF-55365/4/11	T409/T419/T429		●	○	●	●	●				●		●			●				●	●					
QPL 55365 ^T	CWR09/11/19/29	MIL-PRF-55365/4/8/11	T492/T409/T419/T429	★	●	●	●	●	●	●			●	1	●	●		●		●	●	●	●				●	
N/A	N/A	DLA 04051	T540		○	○	●	●	●	●		●		1	●			●		●	●	●	○	○		○	○	
N/A	N/A	DLA 04052	T541		○	○	●	●	●	●		●		1	●			●		●	●	●	○	○		○	○	
N/A	N/A	KO-CAP (Polymer) COTS	T543			○	●	●	●						●			●										
N/A	N/A	KO-CAP (Polymer) Fused COTS	T546		○	○	●	●	●	○		●	○		●	○	○	●	○	○	○	○		○	○			
N/A	N/A	DLA 04053	T496		○	○	●	●	●	○		●	●		●			●		●	○	○	○	○			○	
N/A	N/A	DLA 95158	T495		○	○	●	●	●	○		●	●		●			●		●	○	○	○	○			○	
N/A	N/A	DLA 07016	T493		○	○	●	●	●	○			●		●			●		●	○	○	○	○			○	
N/A	N/A	MnO ₂ COTS	T493/T497/T513/T496		●	○	●	●	●	○			●		●			●		●	○	○	○	○	○		○	
N/A	N/A	Ta MnO ₂ Stacks	TSM			◆	◇	◇	◇			◆					●											
N/A	N/A	KO (Polymer) Stacks	TSP			◆	◇	◇	◇			◆																
N/A	N/A	KEMET Space Grade	T493/T496/T497/T510	★	●	○	●	●	●	○		●	●	○	●	●		●		●	●	○	○				●	●
N/A	N/A	HVE	T428		●	○	●	●	●			●			●			●										

KEY

- Standard
- Optional
- 1 1 Plane
- 2 2 Plane
- ◆ Indicated per PIN
- ◇ Sample on PIN, Stacks 100%
- T Weibull / Level "T"
- ★ Space Qualified
- * Applies to discrete components; modules receive 100% Cap/DF/ESR/Lkg

Terminology Guide

- **C-SAM:** C-Mode Scanning Acoustic Microscopy (ceramic only)
- **DPA:** Destructive Physical Analysis
- **DWV:** Dielectric Withstanding Voltage (ceramic only)
- **ESR:** Equivalent Series Resistance (ESR) is the preferred high-frequency statement of the resistance unavoidably appearing in these capacitors. ESR is not a pure resistance, and it decreases with increasing frequency.
- **F-Tech:** KEMET's optional manufacturing process to eliminate hidden defects in the tantalum dielectric (tantalum only). For more information, please see page 7.
- **PDA:** Percent Defective Allowed
- **Polymer Reliability Assessment Method:** Sample test under accelerated conditions to demonstrate long-term device reliability (polymer only). Please contact KEMET for details.
- **SBDS:** KEMET's patented nondestructive testing technique which simulates the breakdown voltage of a capacitor without damage to its dielectric (tantalum only). For more information, please see page 7.
- **Thermal Shock:** Parts are temperature cycled.
- **Voltage Conditioning:** Parts receive a voltage conditioning at X rated voltage and X°C for a minimum and maximum amount of hours (ceramic only).

Ceramic Defense and Aerospace Parts

QPL (Qualified Product Listing)	Style	MIL-PRF/DLA/ KEMET Specification	KEMET Series	Space Qualified	CSAM	In-Process - 100% Visual Inspection	In-Process DPA	In-Process Lead Pull Strength	Thermal Shock	Voltage Conditioning	Hot IR (+125°C)	PDA	Visual/Mechanical	X-Ray	Solderability (each lot)	Group B (each lot)	Periodic Group B	Group C Lot Test per MIL-PRF-55681	Periodic Group C	Data Pack (standard w/ order)	Pb (lead) Content C of C	Humidity Steady State Low Voltage (LVH)	Final DPA	X-Ray Fluorescence (XRF) Analysis	Additional Thermal Shock Cycles (applies to Group A only)	100% Final Visual Inspection	Hot IR @ +125°C (X7R, C0G), @ +85°C (X5R)
N/A	N/A	GR900	B Spec Through-Hole	★	○	●	●	●	●	●	●	●	●	●		○				●	○	○	●			○	
N/A	N/A	GR900	A Spec SMD	★	○	●	●	●	●	●	●	●	●	●		○				●	○	○	●	○		○	
N/A	N/A	MIL-PRF-123, In-Process, Group A Tested	Q Spec Through-Hole	★	●	●	●	●	●	●	●	●	●	●		○				●	○	○	●			○	
N/A	N/A	MIL-PRF-123, In-Process, Group A Tested	Q Spec SMD	★	●	●	●	●	●	●	●	●	●	●		○				●	○	○	●	○		○	
QPL M123/1, /2, /3	CKS05, CKS06, CKS07	MIL-PRF-123/1, /2, /3 *	C052Z, C062Z, C512Z	★	●	●	●	●	●	●	●	●	●	●		●			●	●	○		●			○	
QPL M123/10, /11, /12, /13, /21, /22, /23	CKS51, CKS52, CKS53, CKS54	MIL-PRF-123/10, /11, /12, /13 *	C0805Z, C1210Z, C1808Z, C2225Z	★	●	●	●	●	●	●	●	●	●	●		●			●	●	○		●	○		○	
QPL M123/21, /22, /23	CKS55, CKS56, CKS57	MIL-PRF-123/21, /22, /23 *	C1206Z, C1812Z, C1825Z	★	●	●	●	●	●	●	●	●	●	●		●			●	●	○		●	○		○	
QPL 49470/1	PS01	MIL-PRF-49470/1 T Level	L1XN, L1RN, L1QN	★	●	●	●		●	●	●	●	●	●		●	●			●	○		●	○		○	
	PS02	MIL-PRF-49470/1 B Level	L1XN, L1RN, L1QN			●			●	●	●	●	●	●		●	●			●	○			○		○	
QPL 49470/2	PS02	MIL-PRF-49470/2 B Level	L1XN, L1RN, L1QN			●			●	●	●	●	●	●		●	●			●	○			○		○	
QPL 55681/1	CDR01, 02, 03, 04	MIL-PRF-55681/1	C0805P, C1805P, C1808P, C1812P				○		●	●	●	●	●	●		●			●	○			○	○		○	
QPL 55681/2	CDR05	MIL-PRF-55681/2	C1825P				○		●	●	●	●	●	●		●			●	○		○	○	○	○	○	
QPL 55681/3	CDR06	MIL-PRF-55681/3	C2225P				○		●	●	●	●	●	●		●			●	○		○	○	○	○	○	
QPL 55681/7, 8, 9, 10, 11	CDR31, 32, 33, 34, 35	MIL-PRF-55681/7, 8, 9, 10, 11	C0805N, C1206N, C1210N, C1812N, C1825N				○		●	●	●	●	●	●		●			●	○		○	○	○	○	○	
QPL 20/27, 28, 29, 30, 31	CCR/75, 76, 77, 78, 79	MIL-PRF-20/27, 28, 29, 30, 31	C114G, C124G, C192G, C202G, C222G					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/27, 28, 29, 30, 32	CC/75, 76, 77, 78, 80	MIL-PRF-20/27, 28, 29, 30, 32	C114G, C124G, C192G, C202G, C222G (no FR)					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/35	CCR05	MIL-PRF-20/35	C052G, C056G					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/36	CC05	MIL-PRF-20/36	C052G, C056G (no FR)					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/36	CCR06	MIL-PRF-20/36	C062G, C065G, C066G					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/36	CC06	MIL-PRF-20/36	C062G, C065G, C066G (no FR)					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/37, 28	CCR/07, 08	MIL-PRF-20/37, 38	C512G, C522G					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 20/37, 38	CC/07, 08	MIL-PRF-20/37, 38	C512G, C522G (no FR)					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 39014/1	CKR05	MIL-PRF-39014/1	C052T, C056T					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 39014/2	CKR06	MIL-PRF-39014/2	C062T, C066T					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
QPL 39014/5	CKR11, 12, 14, 15, 16	MIL-PRF-39014/5	C114T, C124T, C192T, C202T, C222T					○	●	●	●	●	●	■		●	●			●	○		○	○	○	○	
N/A	N/A	DLA 03028, 03029, 05006, 05007	D Spec 0603, 0805, 0402, 1206			●	○			●	●	●	●	●				○	○								
N/A	N/A	DLA 91019	E Spec 2220			●	○			●	●	●	●	●				○	○								
N/A	N/A	N/A	T Spec 0402, 0603, 0805, 1206 ***							●	●	●	●	●							○	○	○			○	○
N/A	N/A	N/A	T Spec 1210, 1812, 1825, 2220, 2225 ***							●	●	●	●	●							○	○	○			○	○
QPL 11015/18, /19, /20	CK05, CK06	MIL-PRF-11015/18, /19, /20	C052K, C062K, C114K, C124K, C192K, C202K, C222K					○					●		●												

Note: All series are tested for capacitance, dielectric withstanding voltage, insulation resistance at room temperature, and dissipation factor.

KEY


- Standard
- Optional - with fee
- JAN Branding will be affected
- S Failure Rate
- ★ Space Qualified

Optional tests performed on military specification parts will affect JAN branding.

* Non-stocking Item

*** MIL-PRF-55681 Group A Tested.
BME Dielectric, PME also available on select part numbers.

High Reliability Ceramic Capacitors




COTS MLCCS

DLA 05006/7, 03028/9 & 91019

Benefit from advances in commercial grade with tests and screening designed to identify suitable parts for High Reliability Applications

High Reliability Tantalum Capacitors



POLYMER HERMETIC SEAL T550/1

DLA Drawing 13030, T-Level Reliability

High capacitance, low ESR, lightweight alternative to wet tantalum axial capacitors
Based on polymer cathode technology

Ceramic COTS Test Levels

Test Level A

Voltage Conditioning
DWV
IR @ 25°C
CAP
DF

PDA 8%

C of C

Test Level B

Voltage Conditioning
DWV
IR @ 25°C
CAP
DF

PDA 8%

DPA

C of C

Test Level C

Voltage Conditioning
DWV
IR @ 25°C
CAP
DF

PDA 8%

DPA

85/85

C of C

F-Tech Advantage


KEMET's optional F-Tech eliminates hidden defects in the tantalum dielectric. This unique manufacturing process minimizes oxygen and carbon content in the anode, provides a stronger mechanical connection between anode and lead wire and significantly enhances capacitor robustness.

F-Tech is available on select KEMET tantalum capacitor families and can be combined with SBDS.

Simulated Breakdown Screening (SBDS)

Breakdown voltage (BDV) is the ultimate test of a capacitor's robustness but is a destructive test. To simulate the results of a breakdown screening, KEMET developed a patented Simulated Breakdown Screening (SBDS). This nondestructive testing technique simulates the BDV of a capacitor without damage to its dielectric. This 100% population screening identifies hidden defects in the dielectric, providing the highest level of dielectric testing.

SBDS is available on select KEMET tantalum capacitor families and can be combined with F-Tech.





SPACE GRADE MLCCS

MIL-PRF-123

Intensive screening and testing protocols with numerous termination options

KPS MIL STACKED CAPACITORS

MIL-PRF-49470, T-Level Reliability Available
Higher capacitance in the same footprint
Robust termination system



T540 & T541 POLYMER COTS


DLA Drawing 04051/2

Only polymer electrolytic capacitors available today with Reliability Assessment testing criteria

MIL-PRF-55365 MnO₂


MIL & Space Grade

Numerous custom testing/screening options and termination finishes available



Product Grades

KEMET is the undisputed global leader in delivering high performance ceramic and tantalum capacitors. Our Defense and Space Grade products comply with the most stringent reliability requirements in the industry.



www.kemet.com/product-grades

KSIM

Capacitor Simulation Tool

ksim.kemet.com



Made for Engineers by Engineers

engineeringcenter.com



Catalogs and Technical Data

Download on the App Store

ANDROID APP ON Google Play



3D Models, Specifications, and Search