




EH TQG PANEL MOUNT CONNECTORS

NEW PRODUCT BULLETIN 605

FEATURES & BENEFITS

- Same high quality connectors as our popular TQG Series, except both male and female versions utilize the same size panel cut-out, simplifying installation and modification.
- Rugged metal construction.
- Available in nickel or black finish.
- Available with 3, 4, 5, 6 or 7 contacts for male, plated in silver or gold and 3, 4 and 5 contacts for female.
- RoHS Compliant.
- The perfect match for our QGPK Series of I/O panels and our WP Series of wall-plates. More info available on our website.

APPLICATIONS

- Communications equipment
- Wall plates
- Custom I/O panels
- Pro audio equipment



SWITCHCRAFT®

A HEICO COMPANY




5555 N Elston Ave | Chicago, IL 60630 | P: 773.792.2700 | F: 773.792.2129 | www.switchcraft.com | Made in USA.

EH TQG PANEL MOUNT CONNECTORS

NEW PRODUCT BULLETIN 605

MALE EH TQG PANEL CONNECTORS




3 PIN



4 PIN



5 PIN




6 PIN



7 PIN




8 PIN




NOTES:

1. MATERIALS:
 - PLATE - ZINC ALLOY, PLATED
 - SHELL - COPPER ALLOY, NICKEL PLATED
 - INSERT - THERMOPLASTIC, BROWN
 - CONTACT PINS - COPPER ALLOY, PLATED
 - WASHER - COPPER ALLOY, NICKEL PLATED
 - NUT - COPPER ALLOY, NICKEL PLATED
2. THIS PART IS RoHS COMPLIANT.



FEMALE EH TQG PANEL CONNECTORS




3 PIN



4 PIN




5 PIN



NOTES:

1. MATERIALS:
 - HOUSING - ZINC ALLOY, PLATED
 - INNER HOUSING - COPPER ALLOY, NICKEL PLATED
 - FRONT AND REAR INSERTS - THERMOPLASTIC, BROWN
 - CONTACT PINS - COPPER ALLOY, PLATED
 - SOLDER TERMINAL - COPPER ALLOY, TIN PLATED
 - LATCH - COPPER ALLOY, NICKEL PLATED
 - RELEASE LEVER - STEEL, NICKEL PLATED
 - LEVER RETURN SPRING, STAINLESS STEEL
2. THIS PART IS RoHS COMPLIANT.



Please visit www.switchcraft.com for the most up-to-date product specifications. Made in USA.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[EH4FBAU](#) [EH5FB](#) [EH5MBAU](#) [EH4FPKG](#) [EH4MPKG](#) [EH3FAU](#) [EH3MBPKG](#) [EH8MPKG](#) [EH6MBPKG](#)
[EH5FPKG](#) [EH7M](#) [EH6MB](#) [EH5MAUPKG](#) [EH7MAUPKG](#) [EH8M](#) [EH5FBAUPKG](#) [EH3MB](#) [EH3MBAU](#)
[EH7MBAUPKG](#) [EH4FAU](#) [EH3MPKG](#) [EH5MBPKG](#) [EH3FAUPKG](#) [EH5MAU](#) [EH4FB](#) [EH4FBPKG](#) [EH4M](#)
[EH3MAU](#) [EH7MBPKG](#) [EH4F](#) [EH5MBAUPKG](#) [EH5FBPKG](#) [EH5MB](#) [EH3MBAUPKG](#) [EH6M](#)
[EH3FBAUPKG](#) [EH5MPKG](#) [EH5FBAU](#) [EH3FBPKG](#) [EH7MPKG](#) [EH3FB](#) [EH3M](#) [EH7MAU](#) [EH4FAUPKG](#)
[EH6MPKG](#) [EH7MBAU](#) [EH4MB](#) [EH4FBAUPKG](#) [EH5M](#) [EH3F](#) [EH4MBPKG](#) [EH3FBAU](#) [EH5FAU](#)
[EH3MAUPKG](#) [EH7MB](#) [EH5FAUPKG](#) [EH3FPKG](#) [EH5F](#)