


Surface-Mount PAR[®] Transient Voltage Suppressors

High Temperature Stability and High Reliability Conditions

eSMP[®] Series



Top View

Bottom View

SlimSMA (DO-221AC)



LINKS TO ADDITIONAL RESOURCES



3D Models



Related Documents



Packages



Marking

PRIMARY CHARACTERISTICS

V_{BR}	12 V to 100 V
V_{WM}	10.2 V to 85.5 V
P_{PPM} (10 x 1000 μ s)	600 W
P_D at $T_M = 65^\circ\text{C}$	8 W
T_J max.	185 $^\circ\text{C}$
Polarity	Bidirectional
Package	SlimSMA (DO-221AC)

FEATURES

- Very low profile - typical height of 0.95 mm
- Junction passivation optimized design passivated anisotropic rectifier technology
- $T_J = 185^\circ\text{C}$ capability suitable for high reliability and automotive requirement
- Ideal for automated placement
- Bidirectional
- Excellent clamping capability
- Peak pulse power: 600 W (10/1000 μ s)
- AEC-Q101 qualified
- IEC 61000-4-2 ESD capability:
 - 30 kV (air)
 - 30 kV (contact)
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 $^\circ\text{C}$
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

AUTOMOTIVE GRADE



RoHS
COMPLIANT
HALOGEN
FREE

TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lightning on ICs, MOSFET, signal lines of sensor units for automotive.

MECHANICAL DATA

Case: SlimSMA (DO-221AC)

Molding compound meets UL 94 V-0 flammability rating

Base P/NHM3 - halogen-free, RoHS-compliant and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD22-B102

HM3 suffix meets JESD 201 class 2 whisker test

Polarity: no cathode band for bidirectional types

MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$, unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with a 10/1000 μ s waveform	$P_{PPM}^{(1)}$	600	W
Peak pulse current with a 10/1000 μ s waveform	$I_{PPM}^{(1)}$	See next table	A
Power dissipation	$T_M = 65^\circ\text{C}$	$P_D^{(2)}$	W
	$T_A = 25^\circ\text{C}$	$P_D^{(3)}$	
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +185	$^\circ\text{C}$

Notes

(1) Non-repetitive current pulse, per fig. 3 and derated above $T_A = 25^\circ\text{C}$ per fig. 2.

(2) Power dissipation mounted on infinite heat sink

(3) Power dissipation mounted on minimum recommended pad layout

**ELECTRICAL CHARACTERISTICS** ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

DEVICE TYPE	DEVICE MARKING CODE	BREAKDOWN VOLTAGE $V_{BR}^{(1)}$ AT I_T (V)			TEST CURRENT I_T (mA)	STAND-OFF VOLTAGE V_{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V_{WM} I_R (μA)	$T_J = 150\text{ }^{\circ}\text{C}$ MAXIMUM REVERSE LEAKAGE AT V_{WM} I_R (μA)	MAXIMUM PEAK PULSE SURGE CURRENT I_{PPM} (A)	MAXIMUM CLAMPING VOLTAGE AT I_{PPM} V_C (V)	TYPICAL TEMP. COEFFICIENT OF $V_{BR}^{(2)}$ α_T ($\%/^{\circ}\text{C}$)
		MIN.	NOM.	MAX.							
TA6F12CA	ATP	11.4	12.0	12.6	1.0	10.2	2.0	6.0	35.9	16.7	0.070
TA6F13CA	AVP	12.4	13.0	13.7	1.0	11.1	2.0	5.0	33.0	18.2	0.072
TA6F15CA	AXP	14.3	15.0	15.8	1.0	12.8	1.0	5.0	28.3	21.2	0.076
TA6F16CA	AZP	15.2	16.0	16.8	1.0	13.6	1.0	5.0	26.7	22.5	0.078
TA6F18CA	BEP	17.1	18.0	18.9	1.0	15.3	1.0	5.0	23.8	25.2	0.080
TA6F20CA	BGP	19.0	20.0	21.0	1.0	17.1	1.0	5.0	21.7	27.7	0.082
TA6F22CA	BKP	20.9	22.0	23.1	1.0	18.8	1.0	5.0	19.6	30.6	0.084
TA6F24CA	BMP	22.8	24.0	25.2	1.0	20.5	1.0	5.0	18.1	33.2	0.085
TA6F27CA	BPP	25.7	27.0	28.4	1.0	23.1	1.0	5.0	16.0	37.5	0.087
TA6F30CA	BRP	28.5	30.0	31.5	1.0	25.6	1.0	5.0	14.5	41.4	0.088
TA6F33CA	BTP	31.4	33.0	34.7	1.0	28.2	1.0	5.0	13.1	45.7	0.089
TA6F36CA	BVP	34.2	36.0	37.8	1.0	30.8	1.0	5.0	12.0	49.9	0.090
TA6F39CA	BXP	37.1	39.0	41.0	1.0	33.3	1.0	5.0	11.1	53.9	0.091
TA6F43CA	BZP	40.9	43.0	45.2	1.0	36.8	1.0	5.0	10.1	59.3	0.092
TA6F47CA	CEP	44.7	47.0	49.4	1.0	40.2	1.0	10.0	9.3	64.8	0.092
TA6F51CA	CGP	48.5	51.0	53.6	1.0	43.6	1.0	10.0	8.6	70.1	0.093
TA6F56CA	CKP	53.2	56.0	58.8	1.0	47.8	1.0	10.0	7.8	77.0	0.093
TA6F62CA	CMP	58.9	62.0	65.1	1.0	53.0	1.0	10.0	7.1	85.0	0.094
TA6F68CA	CPP	64.6	68.0	71.4	1.0	58.1	1.0	10.0	6.5	92.0	0.095
TA6F75CA	CRP	71.3	75.0	78.8	1.0	64.1	1.0	10.0	5.8	104	0.095
TA6F82CA	CTP	77.9	82.0	86.1	1.0	70.1	1.0	10.0	5.3	113	0.095
TA6F91CA	CVP	86.5	91.0	95.5	1.0	77.8	1.0	10.0	4.8	125	0.096
TA6F100CA	CXP	95.0	100	105	1.0	85.5	1.0	10.0	4.4	137	0.096

Notes

- (1) Pulse test: $t_p \leq 50\text{ ms}$
 (2) To calculate V_{BR} vs. junction temperature, use the following formula: V_{BR} at $T_J = V_{BR}$ at $25\text{ }^{\circ}\text{C} \times (1 + \alpha_T \times (T_J - 25))$
 (3) All terms and symbols are consistent with ANSI / IEEE C62.35

THERMAL CHARACTERISTICS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Thermal resistance	$R_{\theta JA}^{(1)}$	120	150	$^{\circ}\text{C/W}$
	$R_{\theta JM}^{(2)}$	12	15	$^{\circ}\text{C/W}$

Notes

- (1) Thermal resistance junction-to-ambient to follow JEDEC[®] 51-2A, device mounted on FR4 PCB, 2 oz. standard footprint
 (2) Thermal resistance junction-to-mount to follow JEDEC[®] 51-14, using TDIM (transient dual interface test method)

IMMUNITY TO STATIC ELECTRICAL DISCHARGE TO THE FOLLOWING STANDARDS($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)

STANDARD	TEST TYPE	TEST CONDITIONS	SYMBOL	VALUE
IEC 61000-4-2	Contact discharge	$C = 150\text{ pF}$, $R = 330\text{ }\Omega$	ESD	30 kV
	Air discharge			30 kV



ORDERING INFORMATION TABLE

Device code	T	A	6	F	xxx	CA	H	M3
	1	2	3	4	5	6	7	8
	1	-	Vishay PAR [®] TVS product					
	2	-	Automotive TVS designator					
	3	-	Peak pulse power rating (6 = 600 W)					
	4	-	Package type (F = flat package)					
	5	-	Nominal breakdown voltage					
	6	-	Breakdown voltage tolerance and polarity (CA $\pm$ 5 %, bidirectional)					
	7	-	Quality grade (H = AEC-Q101 qualified, - = industry grade)					
	8	-	Material / environment category (M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free)					

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
TA6F12CAHM3/H ⁽¹⁾	0.032	H	3500	7" diameter plastic tape and reel
TA6F12CAHM3/I ⁽¹⁾	0.032	I	14 000	13" diameter plastic tape and reel

Note

⁽¹⁾ AEC-Q101 qualified


RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted)


Fig. 1 - Peak Pulse Power Rating Curve




Fig. 4 - Typical Junction Capacitance




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 5 - Power Dissipation Derating Curve




Fig. 3 - Pulse Waveform




Fig. 6 - Typical Transient Thermal Impedance



Note

- Fig. 1, power calculations is based on IPPM times defined maximum clamping voltage by pulse width





PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SlimSMA (DO-221AC)



Mounting Pad Layout





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.