

MAACPAK PressFit Power Module Full Bridge Inverter Silicon Carbide MOSFET, 38 mΩ



MAACPAK
(package example)



RoHS
COMPLIANT
HALOGEN
FREE

FEATURES

- Silicon carbide power MOSFET
- High blocking voltage with low on-resistance
- High speed switching with low capacitance
- Fast intrinsic diode with low reverse recovery (Q_{rr})
- Maximum 175 °C junction temperature
- PressFit pins locking technology
- UL pending
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

TYPICAL APPLICATIONS

- EV chargers
- Server and telecom PSU
- UPS
- Solar inverters
- SMPS
- DC/DC converters

PRIMARY CHARACTERISTICS

V_{DSS}	1200 V
$R_{DS(on)}$ at $I_D = 40$ A	33 mΩ
I_D at $T_{sink} = 80$ °C	35 A
Type	Modules - SiC MOSFET
Package	MAACPAK
Circuit configuration	Full bridge inverter

DESCRIPTION

This is an high performance silicon carbide MOSFET. The high blocking voltage with low on-resistance, high speed switching with low capacitance make this MOSFET ideal for high frequency switching application including solar inverters and EV chargers.

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
MOSFET				
Drain to source voltage	V_{DSS}		1200	V
Continuous drain current, V_{GS} at 15 V	I_D	$T_{sink} = 25$ °C	43	A
		$T_{sink} = 80$ °C	35	
Pulsed drain current	$I_{DM}^{(1)}$		180	
Power dissipation	P_D	$T_{sink} = 80$ °C	93	W
Gate to source voltage	V_{GS}		-8 / +19	V
MODULE				
Maximum junction temperature range	T_J max.	Instantaneous event	-55 to +175	°C
Operating junction temperature range	T_{JOP}	Continuous operation under switching	-40 to +150	°C
Operating storage temperature range	T_{Stg}		-40 to +150	
Insulation voltage (RMS)	V_{ISOL}	Any terminal to case, $t = 1$ min	3500	V

Note

⁽¹⁾ Limited at max. junction temperature

RECOMMENDED OPERATING CONDITIONS

PARAMETER	SYMBOL	RATING	UNITS
Recommended operating gate - source voltage	$V_{GS(op)}$	-4 / +15	V



ELECTRICAL CHARACTERISTICS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Drain to source breakdown voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}$, $I_D = 200\text{ }\mu\text{A}$	1200	-	-	V
Static drain to source on-resistance	$R_{DS(on)}$	$V_{GS} = 15\text{ V}$, $I_D = 40\text{ A}$	-	33	49.8	$\text{m}\Omega$
		$V_{GS} = 15\text{ V}$, $I_D = 40\text{ A}$, $T_J = 175\text{ }^{\circ}\text{C}$	-	63	-	
Gate threshold voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 10\text{ mA}$	1.6	2.7	3.8	V
		$V_{DS} = V_{GS}$, $I_D = 10\text{ mA}$, $T_J = 175\text{ }^{\circ}\text{C}$	-	2.08	-	
Temperature coefficient of threshold voltage	$\Delta V_{GS(th)}/\Delta T_J$	$V_{DS} = V_{GS}$, $I_D = 10\text{ mA}$ ($25\text{ }^{\circ}\text{C}$ to $125\text{ }^{\circ}\text{C}$)	-	-5.9	-	$\text{mV}/^{\circ}\text{C}$
Forward transconductance	g_{fs}	$V_{DS} = 20\text{ V}$, $I_D = 40\text{ A}$	-	27.3	-	S
Drain to source leakage current	I_{DSS}	$V_{DS} = 1200\text{ V}$, $V_{GS} = 0\text{ V}$	-	0.01	120	μA
		$V_{DS} = 1200\text{ V}$, $V_{GS} = 0\text{ V}$, $T_J = 150\text{ }^{\circ}\text{C}$	-	0.25	-	
Gate to source leakage	I_{GSS}	$V_{GS} = \pm 15\text{ V}$	-	-	± 250	nA
Total gate charge	Q_g	$V_{DD} = 800\text{ V}$, $I_D = 40\text{ A}$, $V_{GS} = -4\text{ V} / +15\text{ V}$	-	100	-	nC
Gate to source charge	Q_{gs}		-	33	-	
Gate to drain ("Miller") charge	Q_{gd}		-	27	-	
Turn-on switching energy	E_{on}	$V_{DD} = 800\text{ V}$, $I_D = 40\text{ A}$, $R_g = 1.0\text{ }\Omega$, $V_{GS} = -4\text{ V} / +15\text{ V}$	-	0.379	-	mJ
Turn-off switching energy	E_{off}		-	0.152	-	
Turn-on delay time	$t_{d(on)}$		-	15	-	ns
Rise time	t_r		-	13	-	
Turn-off delay time	$t_{d(off)}$		-	40	-	
Fall time	t_f	$V_{DD} = 800\text{ V}$, $I_D = 40\text{ A}$, $R_g = 1.0\text{ }\Omega$, $V_{GS} = -4\text{ V} / +15\text{ V}$, $T_J = 125\text{ }^{\circ}\text{C}$	-	10	-	mJ
Turn-on switching energy	E_{on}		-	0.508	-	
Turn-off switching energy	E_{off}		-	0.141	-	ns
Turn-on delay time	$t_{d(on)}$		-	15	-	
Rise time	t_r		-	14	-	
Turn-off delay time	$t_{d(off)}$	$V_{GS} = 0\text{ V}$, $V_{DS} = 1000\text{ V}$, $f = 100\text{ kHz}$	-	44	-	pF
Fall time	t_f		-	11	-	
Input capacitance	C_{iss}		-	2979	-	
Output capacitance	C_{oss}		-	91	-	
Reverse transfer capacitance	C_{rss}		-	8.9	-	

SOURCE-DRAIN RATINGS AND CHARACTERISTICS ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Pulsed source current (body diode)	I_{SM}	$T_C = 25\text{ }^{\circ}\text{C}$, $V_{GS} = 0\text{ V}$, $T_p = 6\text{ ms}$	-	-	189	A
Diode forward voltage	V_{SD}	$I_S = 40\text{ A}$, $V_{GS} = -4\text{ V}$	-	5.96	-	V
Reverse recovery time	t_{rr}	$T_J = 25\text{ }^{\circ}\text{C}$, $I_F = I_S = 40\text{ A}$, $di/dt = 5100\text{ A}/\mu\text{s}$, $V_R = 800\text{ V}$	-	15	-	ns
Reverse recovery charge	Q_{rr}		-	346	-	nC
Reverse recovery current	I_{RRM}		-	38.3	-	A

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER		SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Thermal resistance junction to sink each ⁽¹⁾	MOSFET	R_{thJS}		-	0.9	-	°C/W
Thermal resistance case to sink ⁽¹⁾	Module	R_{thCS}	Flat, greased surface	-	0.1	-	
Mounting torque (M3)				0.7	1.2	1.7	Nm
Weight				-	16	-	g
Case style				MAACPAK			

Note

⁽¹⁾ Mounting surface flat, smooth, and greased $\lambda_{grease} = 2.9 \text{ W/mK}$

INTERNAL NTC - THERMISTOR SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUE	UNITS
Resistance	R_{25}	$T_J = 25 \text{ °C}$	10 000	Ω
B constant	$B_{25/85}$	$R_2 = R_{25} \exp. (B_{25/85} (1/T_1 - 1/(298.15 \text{ K})))$	$3430 \pm 3 \%$	K
Operating temperature range at zero power			-40 to +150	°C
Dissipation factor	D		3.5	mW/K
Thermal time constant	τ		≈ 10	s




Fig. 1 - Max. Continuous Drain Current vs. Sink Temperature




Fig. 2 - Typical Drain to Source Current Output Characteristics at $T_J = 25 \text{ °C}$




Fig. 3 - Typical Drain to Source Current Output Characteristics at $T_J = 150\text{ }^{\circ}\text{C}$




Fig. 6 - Typical Transfer Characteristics




Fig. 4 - Normalized Drain-to-Source On-Resistance vs. Temperature




Fig. 7 - Typical Gate Threshold Voltage Characteristics




Fig. 5 - Typical Drain-to-Source On-Resistance vs. Gate to Source Voltage




Fig. 8 - Typical Zero Gate Voltage Drain Current









Fig. 9 - Typical Gate Charge vs. Gate to Source Voltage


Fig. 12 - Typical Turn-Off Energy Loss vs. I_D

Fig. 10 - Typical Turn-On Energy Loss vs. I_D

Fig. 13 - Typical Turn-Off Energy Loss vs. R_g

Fig. 11 - Typical Turn-On Energy Loss vs. R_g

Fig. 14 - Typical Turn-On Switching Time vs. I_D




Fig. 15 - Typical Turn-On Switching Time vs. R_g




Fig. 18 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 16 - Typical Turn-Off Switching Time vs. I_D




Fig. 19 - Typical Body Diode Source-to-Drain Current Characteristics $T_J = 25\text{ }^{\circ}\text{C}$




Fig. 17 - Typical Turn-Off Switching Time vs. R_g




Fig. 20 - Typical Body Diode Source-to-Drain Current Characteristics $T_J = 125\text{ }^{\circ}\text{C}$




Fig. 21 - Typical Body Diode Source-to-Drain Current Characteristics $T_J = 150^\circ\text{C}$




Fig. 22 - Normalized Body Diode Source-to-Drain Voltage Drop vs. Temperature




Fig. 23 - Safe Operating Area




Fig. 24 - Typical Thermal Impedance Z_{thJS} Characteristics




ORDERING INFORMATION TABLE

Device code	VS-	MP	Y	038	P	120
	1	2	3	4	5	6

- | | |
|---|---|
| 1 | - Vishay Semiconductors product |
| 2 | - Package indicator (MP = MAACPAK) |
| 3 | - Circuit configuration (Y = full bridge inverter topology) |
| 4 | - $R_{DS(on)}$ in m Ω (038 = 38 m Ω) |
| 5 | - Die technology (P = SiC MOSFET) |
| 6 | - Voltage rating (120 = 1200 V) |

CIRCUIT CONFIGURATION		
CIRCUIT	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Full bridge inverter	Y	


PACKAGE

LINKS TO RELATED DOCUMENTS

Dimensions

www.vishay.com/doc?97293

MAACPAK PressFit

DIMENSIONS in inches (millimeters)



Notes

- Tolerances (unless otherwise stated):
 - $x = \pm 0.3$
 - $x.x = \pm 0.1$
 - $x.xx = \pm 0.03$



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.