

WireLess Position Data Transfer Module


RoHS
COMPLIANT

FEATURES

- Autonomous (2 years battery life)
- Two independent channels for analog sensors data transfer
- Long range bi-directional communication (2 km)
- 2.4 GHz unlicensed friendly-usage frequency band (private network)
- Custom settable configurations
- Compact and robust for outdoor usage (IP67 sealed and UV resistant)
- Battery levels monitoring
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

LINKS TO ADDITIONAL RESOURCES



| QUICK REFERENCE DATA | |
|----------------------|--|
| Sensor type | MtM ⁽¹⁾ wireless position data transfer |
| Output type | Digital output - M8 sealed connectors (analog input) |
| Market appliance | Industrial |
| Dimensions | 89 mm x 55.5 mm x 21.6 mm |

Note

⁽¹⁾ MtM: Machine to Machine

LINKS TO SUITABLE POSITION SENSORS

[Analog linear / analog contacting](#)

[Analog linear / analog non-contacting](#)



MAIN FUNCTION

The WLMO wireless node powers, remotely acquires, and wirelessly transmits data from up to two analog position sensors to users' receivers / gateways for further processing within the host system for enhanced operational visibility and informed decision making. Both potentiometric and contactless sensors technologies are supported.

The WLMO operates worldwide in the 2.4 GHz ISM band, using a proprietary protocol layer over LoRa modulation, on private LoRa network, needless of license, maintaining a very good distance of broadcasting and low power consumption capabilities.

A sealed mechanical switch provides secure activation and pairing during commissioning, while parameterization queries can also be sent wirelessly for tuning the WLMO.

ORDERING INFORMATION / DESCRIPTION

| WLMO | 1 | L | D | ZXXX |
|-------|---|-----------|----------------------------|---|
| MODEL | NUMBER OF CONNECTED SENSORS | PROTOCOLE | ANTENNA | SPECIAL REQUEST |
| | 1: one sensor connected 2: two sensors connected | L: LoRa | D: internal X: external | ZXXX: special number for customized configuration |

SAP PART NUMBERING GUIDELINES

| WLMO | 2 | L | D | ZXXX |
|-------|-----------------------------|-----------|--------------|-----------------|
| MODEL | NUMBER OF CONNECTED SENSORS | PROTOCOLE | ANTENNA TYPE | SPECIAL REQUEST |
| | Two sensors connected | LoRa | Internal | |

ACCESSORIES (upon request)

- Connectors / wires harnesses
- Sensors already equipped with connectors / wires harnesses



| MAIN CHARACTERISTICS | |
|---|---|
| Number of input / sensor type | Up to two analog sensors (contacting and / or non-contacting) |
| Initial activation and pairing | By actuation of the sealed mechanical switch (incl. status colored LED) |
| Application layer / protocol of communication | LoRa 2.4 GHz (to be processed by the host system), no-license private network |
| Transmission / reception channels, five frequency bands (settable), bandwidth: ± 200 kHz each | CH0 at 2.402 GHz CH1 at 2.426 GHz CH2 at 2.450 GHz CH3 at 2.465 GHz CH4 at 2.480 GHz |
| Number of measures (NoM) during DFPC (settable) | 1 to 10 000 values per sensors |
| Data frame transmission cycle period (DFCP) (settable) | One frame ⁽¹⁾ per sensor is sent periodically at a configured value within the 20 s to 10 000 000 s range (1 s increment) |
| Power emission | 7.08 mW (8.5 dBm) |
| Spreading factor (SF) (settable) | SF7 to SF12 |
| Receiving sensitivity | -140 dBm |
| Signal range | 2 km (SF12 - open field - no obstacle - perfect orientation of the module / gateway), please refer to technical note www.vishay.com/doc?50094 |
| Stand-by mode | Request over the air (OTA) |
| Data encryption | AES128, please refer to technical note www.vishay.com/doc?50094 |
| Output data resolution (ADC) | 12 bits on 5 V → <u>theoretical electrical angular or linear travel</u> 4096 |
| Data storage (2 sensors) | Five last values of NoM |

Note

⁽¹⁾ The voltage value sent is the average value of the NoM (please refer to technical note www.vishay.com/doc?50094)

| INITIAL FACTORY SET UP | |
|---|--------|
| Transmission / reception channel | CH0 |
| Spreading factor (SF) | SF7 |
| Number of measures (NoM) during DFPC | 60 |
| Data frame transmission cycle period (DFCP) | 3600 s |

| CONNECTION / SUPPLY SPECIFICATIONS | |
|------------------------------------|---|
| Maximum voltage supply to sensors | 5 V _{DC} per sensor |
| Interface (to connect sensors) | Two threaded M8x1 sealed connectors - 3 male pins, TE connectivity: T4030014031-000 |
| Recommended cable (max. length) | 2 m cables - 3 wires AWG 20 per sensor |
| Recommended connectors | Matching with TE connectivity: T4030014031-000 |
| Power supply | 2 x AAAA 1.5 V - 625 mAh battery (included) |
| Battery level Information | Available in payload message (data 5) |
| Battery life (typical) | 2 years SF7 - 1 measure/15 minutes - 1 transmission/hour recommended storage conditions |

| MECHANICAL SPECIFICATIONS | |
|--|---|
| Recommended fixing hardware (not supplied) | 2 x (stainless steel M4 x 12 mm + washer) |
| Recommended screws tightening torque | 30 cNm max. |
| Weight | 60 g |
| Actuation stroke (activation button) | 0.65 mm ± 0.2 mm |
| Actuation force (activation button) | 3.5 N ± 1 N |

| ENVIRONMENTAL SPECIFICATIONS | |
|--|--|
| Sealing | IP67 |
| Operating temperature range | -18 °C to +55 °C |
| Storage temperature range | -18 °C to +55 °C |
| Shocks (dropping vertical impact) | 3 times / 3 axis / 1 m height on hard surface (ISO 2248) |
| Damp heat | 93 % RH - 40 °C - 96 h (NF EN 600 68-2-30) |
| UV protection | UV resistant materials according to ISO 4892-2 |
| Electrostatic discharges | Contact discharges: ± 4 kV, air discharges: ± 8 kV, EN 61000-4-2 |
| Immunity to power frequency magnetic field | 1 A/m, 50 Hz, EN 61000-4-8 |
| Immunity to radiated RF field | 3 V/m, 80 MHz to 1 GHz, EN6100-4-3 |

| MATERIALS | |
|------------------------------|---|
| RoHS directive (2011/65/UE) | Compliant |
| REACH regulation (1907/2006) | Compliant |
| Housing | PC and ABS (UL94HB) |
| Actuation button | Silicone |
| Connectors (contacts) | Nickel plated copper alloy (gold plated copper alloy) |
| Label | Metalized PE film |


| IDENTIFICATION LABEL | |
|--|--|
| <p>Hardware revision</p> <p>Part number</p> <p>Model</p> <p>EU certification</p> <p>ID of the node</p> <p>Date code</p> <p>US (FCC) / Canada (IC) certification ID's</p> <p>Link to instructions of use / technical note</p> | |

| CERTIFICATIONS | |
|--------------------------|---|
| CE conformity | EN 300440: SRD - 1 GHz to 40 GHz harmonized standard CISPR 32: EMC multimedia equip.- emission requirements CISPR 35: EMC multimedia equip.- immunity requirements EN 301489-3: EMC - SRD (9 kHz and 246 GHz) EN 301489-1: EMC common technical requirements CEI 62311: human exposure EMF 0 Hz to 300 GHz |
| FCC ID (USA) | FCCID: 2BKGFWLMO2LD |
| IC ID (Canada) | IC: 33601-WLMO2LD |
| USA and Canada standards | RSS-102 - RF all frequency bands KDB 447498 mobile and portable dev. RF exposure KDB 996369 D04 CEI 62368-1: 2014 audio / video safety requirements CEI 62368-1: 2018 CEI 60950-22 outdoor equipment safety requirements |


Note

- Nothing stated herein shall be construed as a guarantee of quality or durability

DIMENSIONS in millimeters (general tolerance ± 0.5 mm)




PAIRING



Please refer to technical note www.vishay.com/doc?50094

SENSORS CONNECTION / WIRING





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.