

SPRING-LOADED CONNECTORS

SERIES 319, 419 • .100" GRID CONCAVE FACE TARGET CONNECTORS FOR SPRING-LOADED ASSEMBLIES • SINGLE AND DOUBLE ROW STRIPS




FIG. 1






FIG. 2



Coplanarity .005". For Pin counts >20 positions, consult Technical Support.

FIG. 3

- Series 319 and 419 Spring Target Connectors, supplied in single and double row strips
- These target connectors have a concave face providing greater surface area for mating with our standard .042" diameter plungers. Target connectors provide an excellent gold-plated conductive path back to the board-mounted spring pin connector
- Target connectors use MM #1947 and #1948 pins. See page 223.1 for details
- Insulators are high temperature thermoplastic



ORDERING INFORMATION

FIG. 1	Series 319...006	Standard Solder Tails
	319-10-1	-00-006000 Specify number of pins 01-64
FIG. 2	Series 419...006	Standard Solder Tails
	419-10-2	-00-006000 Specify number of pins 04-64
FIG. 3	Series 419...007	Surface Mount
	419-10-2	-30-007000 Specify number of pins 04-64
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264		
SPECIFY PLATING CODE XX=		
Pin Plating	10 10 μ" Au	

