

OMRON

Switch Mode Power Supplies

S8VK-X

A New Standard in Preventative Maintenance

The Connected Power Supply



Production Site Innovation inspired by IoT

OMRON aims to create the production site of the future where the health of critical components is accessible from anywhere.

- Machine health is visible 24/7
- Information is displayed by individual machine and production site location
- Historical data is available for analytics

Facility conditions will be accessible through IoT connectivity all over the world. The data collected will help optimize each facility's operating rates and drastically change preventative maintenance activities.





Innovative Facility Maintenance through Power

Retrieving and centrally monitoring the status of power supplies enables you to plan equipment maintenance activity more effectively. This eliminates unexpected downtime and premature power supply replacement, thus reducing overall maintenance costs.

Currently



Maintenance personnel must respond quickly to any machine experiencing an issue.

Equipment status is not accessible. Maintenance personnel must physically inspect each machine to identify defective equipment.

Existing preventative maintenance programs replace equipment far before the service life of the component, increasing their maintenance costs.

Supply Monitoring

From now on

Centralized monitoring of equipment

Each machine and facility site can monitor the voltage, current, and expected life of their power supplies from a central location.



Improved Maintenance Planning

Historical data analysis can help plan schedule machine maintenance activity more strategically.

Enhanced facility uptime and reduced maintenance costs

Improved maintenance activity planning prevents unexpected downtime and reduces premature component replacement, thus lowering maintenance costs.

The first step in scheduled maintenance: knowing when to replace your power supply.

S8VK-X calculates the deterioration of the internal electrolytic capacitor based on its component's temperature. It is indicated on the display as well as via the communications system.




Do you know?

A power supply has a service life.


In general, aged deterioration of the internal electrolytic capacitor degrades the original performance (service life) of a power supply and ceases to function in the end. Using a power supply close to its service life may cause a disruption of output voltage even at power-on state and unexpected shutdown of equipment.

Relationship between service life of a electrolytic capacitor and temperature



S8VK-X power supplies help promote an innovative style of facility maintenance.

S8VS 240-W models



World's smallest class^{*1} of power supplies with a communication function

The space-saving design enables you to mount side-by-side and replace conventional power supplies in a control panel smoothly.

*1. According to OMRON investigation in October 2017.

Switch Mode Power Supplies

S8VK-X

*2. Two units of S8VK-X 240 W and W4S1-03B Switching Hub

Excellent environmental resistance contributes to stable equipment operation.

Temperature



-40 to 70 °C

Vibration and shock



Vibration: 5 G
Shock: 15 G

Humidity and gases



Coated PCBs

Altitude



3,000 m




Our shared Value Design for Panel (herein after referred to as Value Design) concept for the specifications of products used in control panels will create new value to IEI our customer's control panels. Combining multiple products that share the Value Design concept will further increase the value provided to control panels.

Compatible with multiple communication methods covering a wide range of applications globally.

Compatible with **EtherNet/IP™** / **Modbus**


System configuration example



I want to start right away.

Quick start

You can start easily using a dedicated Power Supply Monitoring Tool.




FUTURE RELEASE

What you can do with Power Supply Monitoring Tool

- Default setting of Power Supply (IP address etc.)
- Collective display of data, saving data, and the alarm display

Voltage	24.1 V	24.2 V	12.1 V
Current	1.3 A	2.0 A	0.5 A
Replacement time	4 years	3 years	1.5 years

- Verification of current operating environment & replacement simulation



Simulation can be performed to see how much margin will be created when you replace the current product with bigger capacity one.

etc.

Convenient local indicator displays current power supply status.



Easy-to-read Local Indicator

Advantages during design and measurement


You can easily check the expected output voltage and the designed current (steady-state and maximum) without using measuring equipment.

Display example



Advantages during operation

You can check the output voltage and current of the power supplies on site without using measuring equipment. Furthermore, you can check the maximum current value recorded.



Advantages during malfunction and maintenance


You can diagnose issues, while checking the output voltage and current, by using the local indicator without using measuring equipment.

What is the maximum current?



Contact person at the manufacturer or design division

Job site



Also you can check the number of years before replacement.



Communications and display items

Item	Monitor display	Communication		
		Ethernet/IP		Modbus TCP
		CIP message	Tag data link	
Output voltage	✓	Read	Read	Read
Output current	✓	Read	Read	Read
Output peak hold current	✓	Read and write*	Read	Read and write*
Years until replacement Percentage until replacement	✓	Read	Read	Read
Total run time	✓	Read	Read	Read
Continuous run time	✓	Read	Read	Read
Self-diagnostics	Overheating alarm	✓	Read	Read
	Measured value error	✓	Read	Read
	Memory error	✓	Read	Read
Product model	—	Read	Read	Read
Serial number	—	Read	Read	Read
Firmware version	—	Read	Read	Read
IP address Subnet mask Default gateway	—	Read and write	Read	Read and write
MAC address	—	Read	Read	Read

NOTES

EtherNet/IP™ is the trademarks of ODVA.

Mod bus is a registered trademark of Schneider Electric.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

OMRON AUTOMATION AMERICAS HEADQUARTERS • Chicago, IL USA • 847.843.7900 • 800.556.6766 • www.omron247.com

OMRON CANADA, INC. • HEAD OFFICE

Toronto, ON, Canada • 416.286.6465 • 866.986.6766 • www.omron247.com

OMRON ELECTRONICS DE MEXICO • HEAD OFFICE

México DF • 52.55.59.01.43.00 • 01-800-226-6766 • mela@omron.com

OMRON ELECTRONICS DE MEXICO • SALES OFFICE

Apodaca, N.L. • 52.81.11.56.99.20 • 01-800-226-6766 • mela@omron.com

OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE

São Paulo, SP, Brasil • 55.11.2101.6300 • www.omron.com.br

OMRON ARGENTINA • SALES OFFICE

Cono Sur • 54.11.4783.5300

OTHER OMRON LATIN AMERICA SALES

54.11.4783.5300

Authorized Distributor:

Controllers & I/O

- Machine Automation Controllers (MAC) • Motion Controllers
- Programmable Logic Controllers (PLC) • Temperature Controllers • Remote I/O

Robotics

- Industrial Robots • Mobile Robots

Operator Interfaces

- Human Machine Interface (HMI)

Motion & Drives

- Machine Automation Controllers (MAC) • Motion Controllers • Servo Systems
- Frequency Inverters

Vision, Measurement & Identification

- Vision Sensors & Systems • Measurement Sensors • Auto Identification Systems

Sensing

- Photoelectric Sensors • Fiber-Optic Sensors • Proximity Sensors
- Rotary Encoders • Ultrasonic Sensors

Safety

- Safety Light Curtains • Safety Laser Scanners • Programmable Safety Systems
- Safety Mats and Edges • Safety Door Switches • Emergency Stop Devices
- Safety Switches & Operator Controls • Safety Monitoring/Force-guided Relays

Control Components

- Power Supplies • Timers • Counters • Programmable Relays
- Digital Panel Meters • Monitoring Products

Switches & Relays

- Limit Switches • Pushbutton Switches • Electromechanical Relays
- Solid State Relays

Software

- Programming & Configuration • Runtime