




ZONE	MARK	DESCRIPTION	DATE	SIGN
------	------	-------------	------	------

ADVANTECH 研華股份有限公司		APPROVED				DESCRIPTION/PART NAME																																																												
		DRAWER		James Chen		2012/6/27		MIO-COMPACT-DIM																																																										
		DESIGNER				2012/6/27																																																												
		CHECKED				2012/6/27		MODEL NAME		INTERIOR PART APPEARANCE PART																																																								
<table><tr><td>DIMENSIONAL TOLERANCES ±</td><td>M1</td><td>M2</td><td>S1</td><td>S2</td><td>P1</td><td>P2</td><td>D</td><td rowspan="7">MATERIAL</td></tr><tr><td>0~5.99</td><td>0.05</td><td>0.10</td><td>0.15</td><td>0.20</td><td>0.05</td><td>0.10</td><td>0.20</td></tr><tr><td>6~29.99</td><td>0.10</td><td>0.20</td><td>0.15</td><td>0.25</td><td>0.10</td><td>0.15</td><td>0.25</td></tr><tr><td>30~79.99</td><td>0.15</td><td>0.25</td><td>0.20</td><td>0.30</td><td>0.20</td><td>0.40</td><td>0.30</td></tr><tr><td>80~179.99</td><td>0.15</td><td>0.30</td><td>0.25</td><td>0.45</td><td>0.40</td><td>0.50</td><td>0.40</td></tr><tr><td>180~314.99</td><td>0.20</td><td>0.50</td><td>0.35</td><td>0.60</td><td>0.40</td><td>0.60</td><td>0.50</td></tr><tr><td>315~800</td><td>0.30</td><td>0.80</td><td>0.50</td><td>1.10</td><td>0.70</td><td>1.00</td><td>0.60</td></tr></table>		DIMENSIONAL TOLERANCES ±	M1	M2	S1	S2	P1	P2	D	MATERIAL	0~5.99	0.05	0.10	0.15	0.20	0.05	0.10	0.20	6~29.99	0.10	0.20	0.15	0.25	0.10	0.15	0.25	30~79.99	0.15	0.25	0.20	0.30	0.20	0.40	0.30	80~179.99	0.15	0.30	0.25	0.45	0.40	0.50	0.40	180~314.99	0.20	0.50	0.35	0.60	0.40	0.60	0.50	315~800	0.30	0.80	0.50	1.10	0.70	1.00	0.60	FINISHING		PART NO.		P/N ADDED CODE			
		DIMENSIONAL TOLERANCES ±	M1	M2	S1	S2	P1	P2	D		MATERIAL																																																							
		0~5.99	0.05	0.10	0.15	0.20	0.05	0.10	0.20																																																									
		6~29.99	0.10	0.20	0.15	0.25	0.10	0.15	0.25																																																									
		30~79.99	0.15	0.25	0.20	0.30	0.20	0.40	0.30																																																									
		80~179.99	0.15	0.30	0.25	0.45	0.40	0.50	0.40																																																									
		180~314.99	0.20	0.50	0.35	0.60	0.40	0.60	0.50																																																									
315~800	0.30	0.80	0.50	1.10	0.70	1.00	0.60																																																											
FILE NAME		REV.																																																																
ANGLE TOLERANCES		90° ± 1.0° Other 1.5°		D				THIRD ANGLE PROJECTION				SCALE 1:1		UNITS mm		SHEET 1 of 1		SIZE A3																																																