

Features

- „Easy to Clean“ design based on standard ISO 14 159 und DIN EN 1672-2
- Applications:
 - Machines for food industry
 - Bottling plants
 - Packaging machines
- Application areas:
 - Interface inside the splash zone
 - Connections with chemical resistance and high cleaning cycles
- Materials and resistance:
 - Housing material with FDA 21 approval
 - Ecolab® tested:
 - P3-topax 52
 - P3-topax 19
 - P3-topax 66
 - P3-topax 99
 - P3-topax 56
 - P3-topax 200
 - Acigel, Supergel, Tego 2000

Technical characteristics

Hood

Material hood	PP
Material seal outside	EPDM/TPE
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 locked	IP67 / IP69K
Locking	screw locking

Inserts

Number of contacts	4/4 + PE
Electrical data acc. to EN 61 984	

Power range **16 A 400 V 6 kV 3**

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3





Control range **10 A 250 V 4 kV 3**






Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω

Material	PC
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	
- mating cycles	≥ 500






Connector for food industry

Identification	Part number	Drawing	Dimensions in mm
Panel mounted housing straight with through holes for fixing screws 	09 15 503 0301		
Panel mounted housing angled with through holes for fixing screws 	09 15 503 0901		
Cover panel mounted housing 	09 15 503 5401		
Cover hood 	09 15 503 5411		

Identification	Part number	Cable entry metric	Drawing	Dimensions in mm
Hood 	19 15 503 1401	M25		
Hoods cable to cable 	19 15 503 1701	M25		
Cable gland black 9 - 16 mm black 13 - 18 mm 	19 00 000 5191 19 00 000 5193	M25 M25		
Lock cover  	09 15 500 9911 09 15 500 9912		 	

Number of contacts

4 / 4 + 

Identification	Part number		Drawing	Dimensions in mm
Male insert (M)		Female insert (F)		
Insulator 4 contacts 16 A + PE 4 contacts 10 A 	09 15 508 3001	09 15 508 3101		
Identification	Part number		Drawing	Dimensions in mm
Coding pin delivery content 20 pieces per bloc 	09 12 000 9924			
Contacts Han® D and Han® E contacts see catalogue "HARTING Industrial Connectors Han®" chapters 2 and 3				
Han® 3 A adapter for male and female insert series on following page 	09 15 503 9911			

Summary Han® 3 A for Han® F+B



Series	Han® 3 A	Han® 3 A Quick Lock	Han® 3 A Quick Lock	Han® 4 A
Number of contacts	3 + ⊕	3 + ⊕	3 + ⊕	4 + ⊕
Termination	Screw terminal	Quick Lock terminal	Quick Lock terminal	Screw terminal
				
Rated current	10 A	10 A	10 A	10 A
Rated voltage	230 / 400 V	230 / 400 V	230 / 400 V	230 / 400 V
Wire gauge	1 ... 2.5 mm²	0.5 ... 2.5 mm²	0.25 ... 1.5 mm²	1 ... 2.5 mm²
Male insert (M)	09 20 003 2611	09 20 003 2633	09 20 003 2634	09 20 004 2611
Female insert (F)	09 20 003 2711	09 20 003 2733	09 20 003 2734	09 20 004 2711

Series	Han® 4 A Quick Lock	Han® 4 A Quick Lock	Han® 7 D	Han® 7 D Quick Lock
Number of contacts	4 + ⊕	4 + ⊕	7 + ⊕	7 + ⊕
Termination	Quick Lock terminal	Quick Lock terminal	Crimp terminal	Quick Lock terminal
				
Rated current	10 A	10 A	10 A	10 A
Rated voltage	230 / 400 V	230 / 400 V	250 V	250 V
Wire gauge	0.5 ... 2.5 mm²	0.25 ... 1.5 mm²	0.14 ... 2.5 mm²	0.14 ... 2.5 mm²
Male insert (M)	09 20 004 2633	09 20 004 2634	09 21 007 3031	09 21 007 2632
Female insert (F)	09 20 004 2733	09 20 004 2734	09 21 007 3131	09 21 007 2732

Series	Han® 8 D	Han® 8 D Quick Lock	Han® Q 2/0	Han® Q 2/0
Number of contacts	8	8	2 + ⊕	2 + ⊕
Termination	Crimp terminal	Quick Lock terminal	Axial screw terminal	Axial screw terminal
				
Rated current	10 A	10 A	40 A	40 A
Rated voltage	~ 50 V / – 120 V	~ 50 V / – 120 V	400 V	400 V
Wire gauge	0.14 ... 2.5 mm²	0.25 ... 1.5 mm²	2.5 ... 6 mm²	4 ... 10 mm²
Male insert (M)	09 36 008 3001	09 36 008 2632	09 12 002 2653	09 12 002 2651
Female insert (F)	09 36 008 3101	09 36 008 2732	09 12 002 2753	09 12 002 2751

Summary Han® 3 A for Han® F+B



Series	Han® Q 2/0	Han® Q 2/0	Han® Q 2/0	Han® Q 2/0
Number of contacts	2 + ⊕	2 + ⊕	2 + ⊕	2 + ⊕
Termination	Crimp terminal 	Axial screw terminal 	Axial screw terminal 	Crimp terminal 
Rated current	40 A	40 A	40 A	40 A
Rated voltage	400 V	830 V	830 V	830 V
Wire gauge	1.5 ... 10 mm²	2.5 ... 6 mm²	4 ... 10 mm²	1.5 ... 10 mm²
Male insert (M)	09 12 002 3051	09 12 002 2654	09 12 002 2652	09 12 002 3052
Female insert (F)	09 12 002 3151	09 12 002 2754	09 12 002 2752	09 12 002 3152
Series	Han® Q 3/0	Han® Q 4/0	Han® Q 5/0	Han® Q 5/0 Quick Lock
Number of contacts	3 + ⊕	4	5 + ⊕	5 + ⊕
Termination	Crimp terminal 	Crimp terminal 	Crimp terminal 	Quick Lock terminal 
Rated current	40 A	40 A	16 A	16 A
Rated voltage	400 V	830 V	230 / 400 V	230 / 400 V
Wire gauge	1.5 ... 10 mm²	1.5 ... 10 mm²	0.14 ... 2.5 mm²	0.5 ... 2.5 mm²
Male insert (M)	09 12 003 3051	09 12 004 3051	09 12 005 3001	09 12 005 2633
Female insert (F)	09 12 003 3151	09 12 004 3151	09 12 005 3101	09 12 005 2733
Series	Han® Q 7/0	Han® Q 12/0	Han® High Density	
Number of contacts	7 + ⊕	12 + ⊕	21	
Termination	Crimp terminal 	Crimp terminal/ Quick Lock terminal 	Crimp terminal 	
Rated current	10 A	10 A	6.5 A	
Rated voltage	400 V	400 V	~ 50 V / – 120 V	
Wire gauge	0.14 ... 2.5 mm²	0.14 ... 2.5 mm²	0.09 ... 0.56 mm²	
Male insert (M)	09 12 007 3001	09 12 012 3001	09 12 021 3001	
Female insert (F)	09 12 007 3101	09 12 012 3101	09 12 021 3101	

Summary Han® 3 A for Han® F+B



Series	Han-Brid® RJ45 C	Han-Brid® RJ45 C		
Number of contacts	2 / 8	2 / 8		
Termination	Crimp terminal / RJ45 	Crimp terminal / RJ45 		
Rated current	10 A	10 A		
Rated voltage	24 V	24 V		
Wire gauge	0.14 ... 2.5 mm²	0.14 ... 2.5 mm²		
Male insert (M)	09 12 003 3021	09 12 003 3031		
Female insert (F)				