


LSP05 Module Series



Agency Approvals

Agency	Standard	Agency File Number
	UL1449 3rd Edition	E320116

Notes:

1. These parts are in compliance with IEC61643-11 Class II (Low Voltage System) and EN61643-11 Type 2 (Low Voltage System).
2. Tested for temporary overvoltage from low-voltage system faults per IEC 61643-11

Description

The Littelfuse LSP05 thermally protected Surge Protective Device is a self-protected device which is specially designed to be used in outdoor and commercial LED lighting fixtures for transient overvoltage protection. It is constructed with Littelfuse thermally protected varistor technology. Its built-in thermal disconnect function provides additional protection to prevent catastrophic failure and fire hazard even under the extreme circumstances of varistor end-of-life or sustaining over voltage conditions. The LSP05 SPD facilitates customer's product compliance to IEEE C62.41.2 Location Category C Low and US Dept of Energy MSSLC Model Spec.

Features

- Maximum Discharge Current, 10kA, 8/20us
- Meets ANSI C136.2/ IEEE C62.41.2 Location Category C Low Exposure
- Parallel connected SPD device
- Thermally protected Varistor technology
- IP66 Water-proof and Dust-proof
- Indication wire lead options for Parallel connected modules
- UL1449 Type 4 Component Assembly Recognition
- IEC61643-11 Class II/ EN61643-11 Type 2 Compliance
- Compact form factor (48x48x30mm) with mounting tabs

Applications

- Outdoor and Commercial LED Lighting
- Wash wall lighting
- Parking garage/lot lighting
- Flood lighting
- Tunnel lighting
- Digital signage
- Street lighting

Absolute Maximum Ratings

- For ratings of individual members of a series, see Device Ratings and Specifications chart

	LSP05 Series	Units
Continuous:		
Steady State Applied Voltage:		
Max AC Voltage Range ($V_{M_{AC}IRMS}$)	150 to 510	V
Transient:		
Maximum Discharge Current 8/20 μ s Waveform (I_{max})	10,000	A
Nominal Discharge Current 8/20 μ s Waveform (I_n)	5,000	A
Operating Ambient Temperature Range (T_A)	-45 to +85	°C
Storage Temperature Range (T_{STG})	-45 to +125	°C
Isolation Voltage Capability (When the thermal disconnect opens)	600	V
Insulation Resistance	>1,000	MΩ

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

LSP05 Series Device Ratings & Specifications



Part Number	Operating Voltage (VAC)	MCOV (VAC)	Maximum Discharge Current (Imax)(A) ²	Nominal Discharge Current (In)(A) ¹	MLV (V) ³	Up (V) ⁴
LSP05120X	120	150	10,000	5,000	L-N:680 L-G:680 N-G:630	800
LSP05240X	240	275	10,000	5,000	L-N:1100 L-G:1100 N-G:1100	1200
LSP05277X	277	320	10,000	5,000	L-N:1270 L-G:1270 N-G:1220	1400
LSP05347X	347	420	10,000	5,000	L-N:1600 L-G:1600 N-G:1580	1700
LSP05480X	480	510	10,000	5,000	L-N:1780 L-G:1780 N-G:1730	1900
LSP05240LLX	L-L:240	L-L:275	10,000	5,000	L-L:1100	L-L:1200
	L-N/G:120	L-N/G:150			L-N/G:680	L-N/G:800
LSP05480LLX	L-L:480	L-L:510	10,000	5,000	L-L:1780	L-L:1900
	L-N/G:277	L-N/G:320			L-N/G:1270	L-N/G:1400

Notes:

1. Nominal Discharge Current (In)(A): The nominal discharge current is a measure of the SPDs endurance capability; 15 impulses of discharge current uses the 8/20us current waveform.
2. Maximum Discharge Current (Imax)(A): The maximum discharge current is a measure of the SPDs maximum capability; single impulse of discharge current uses the 8/20us current waveform.
3. MLV – Measured limiting voltage; the highest value of residual voltage measurements during the application of impulses of 8/20us nominal discharge current (In); an average voltage value of 15 impulses
4. Up – Voltage protection level; the highest value of residual voltage measurements during the application of impulses of 8/20us nominal discharge current (In); a rounding voltage value of maximum measurement.

Dimensions




Typical Dimensions (mm)



Notes:

1. Black: Line; White: Neutral; Green: Ground
2. Black: R1; Red: R2; Blue: R3
3. Wire Gauge: AWG14 wire Line in, AWG22 Wire for indication.

Application/Installation Schematic



Note: LED indicator and associated circuitry are not included in the module.

Part Numbering System

LSP 05 480LL X

Device Family _____

Littelfuse Surge Protection Module

Nominal Discharge Current _____

Current

Operating Voltage _____

(LL: for L,L,N/G mode)

P or PM _____

(P: parallel connection; PM: parallel connection and with monitor indication wire)

Note: X3316: without GND wire connection option