



## **SIOV metal oxide varistors**

Leaded varistors, SNF high operating temperature  
varistors, SNF AdvanceD series

**Series/Type:** B722\*

**Date:** January 2018

© EPCOS AG 2018. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.

## Construction

- Round varistor element, leaded
- Coating: silicon resin, flame-retardant to UL 94 V-0
- Terminals: tinned wire

## Features

- High-energy AdvanceD series E2
- High surge current ratings up to 10 kA
- High energy ratings up to 400 J
- Wide operating voltage range 130 ... 625 V<sub>RMS</sub>
- Enhanced resistance against heat and humidity 85 °C, 85% r.h., 0.85 · V<sub>V</sub> (1 mA), 1000 h for use in harsh environments
- PSpice models

## Approvals

- UL
- CSA
- VDE
- CQC SNF07 (K130 ... K320), SNF10/SNF14 (K130 ... K625), SNF20 (K130 ... K625)
- IEC

## Options

- Types qualified to AEC-Q200 available in SNF automotive series or upon request
- Special insulation types upon request

## Delivery mode

- Bulk (standard)

## General technical data

Climatic category	to IEC 60068-1	40/125/56	
Operating temperature	to IEC 61051	–40 ... +125	°C
Storage temperature		–40 ... +150	°C
Electric strength	to IEC 61051	≥ 2.5	kV <sub>RMS</sub>
Insulation resistance	to IEC 61051	≥ 100	MΩ



## Leaded varistors, SNF high operating temperature

B722\*

SNF AdvanceD series

## Electrical specifications and ordering codes

Maximum ratings ( $T_A = 125^\circ\text{C}$ )

Ordering code	Type (untaped) SIOV-	$V_{\text{RMS}}$ V	$V_{\text{DC}}$ V	$I_{\text{max}}$ (8/20 $\mu\text{s}$ ) 1 time A	$I_{\text{n}^{-1}}$ (8/20 $\mu\text{s}$ ) 15 times A	$W_{\text{max}}$ (2 ms) J	$P_{\text{max}}$ W
<b><math>V_{\text{RMS}} = 130 \text{ V}</math></b>							
B72205U2131K501	SNF05K130E2S5	130	170	800	150	6.0	0.10
B72207U2131K501	SNF07K130E2S5	130	170	1750	500	12.5	0.25
B72210U2131K501	SNF10K130E2S5	130	170	3500	1500	25.0	0.40
B72214U2131K501	SNF14K130E2S5	130	170	6000	3000	50.0	0.60
B72220U2131K501	SNF20K130E2S5	130	170	10000	3000	100.0	1.00
<b><math>V_{\text{RMS}} = 140 \text{ V}</math></b>							
B72205U2141K501	SNF05K140E2S5	140	180	800	150	6.5	0.10
B72207U2141K501	SNF07K140E2S5	140	180	1750	500	13.5	0.25
B72210U2141K501	SNF10K140E2S5	140	180	3500	1500	27.5	0.40
B72214U2141K501	SNF14K140E2S5	140	180	6000	3000	55.0	0.60
B72220U2141K501	SNF20K140E2S5	140	180	10000	3000	110.0	1.00
<b><math>V_{\text{RMS}} = 150 \text{ V}</math></b>							
B72205U2151K501	SNF05K150E2S5	150	200	800	150	7.5	0.10
B72207U2151K501	SNF07K150E2S5	150	200	1750	500	15.0	0.25
B72210U2151K501	SNF10K150E2S5	150	200	3500	1500	30.0	0.40
B72214U2151K501	SNF14K150E2S5	150	200	6000	3000	60.0	0.60
B72220U2151K501	SNF20K150E2S5	150	200	10000	3000	120.0	1.00
<b><math>V_{\text{RMS}} = 175 \text{ V}</math></b>							
B72205U2171K501	SNF05K175E2S5	175	225	800	150	8.0	0.10
B72207U2171K501	SNF07K175E2S5	175	225	1750	500	17.0	0.25
B72210U2171K501	SNF10K175E2S5	175	225	3500	1500	35.0	0.40
B72214U2171K501	SNF14K175E2S5	175	225	6000	3000	70.0	0.60
B72220U2171K501	SNF20K175E2S5	175	225	10000	3000	135.0	1.00
<b><math>V_{\text{RMS}} = 210 \text{ V}</math></b>							
B72205U2211K501	SNF05K210E2S5	210	270	800	150	9.5	0.10
B72207U2211K501	SNF07K210E2S5	210	270	1750	500	20.0	0.25
B72210U2211K501	SNF10K210E2S5	210	270	3500	1500	42.0	0.40
B72214U2211K501	SNF14K210E2S5	210	270	6000	3000	80.0	0.60
B72220U2211K501	SNF20K210E2S5	210	270	10000	3000	160.0	1.00
<b><math>V_{\text{RMS}} = 230 \text{ V}</math></b>							
B72205U2231K501	SNF05K230E2S5	230	300	800	150	11.0	0.10
B72207U2231K501	SNF07K230E2S5	230	300	1750	500	23.0	0.25
B72210U2231K501	SNF10K230E2S5	230	300	3500	1500	45.0	0.40
B72214U2231K501	SNF14K230E2S5	230	300	6000	3000	90.0	0.60
B72220U2231K501	SNF20K230E2S5	230	300	10000	3000	180.0	1.00

<sup>1)</sup> Note: Nominal discharge current  $I_n$  according to UL 1449, 4<sup>th</sup> edition.

Characteristics ( $T_A = 25^\circ\text{C}$ )

Ordering code	$V_v$ (1 mA) V	$\Delta V_v$ (1 mA) %	$V_{c,max}$ ( $i_c$ ) V	$i_c$ A	$C_{typ}$ (1 kHz) pF
<b><math>V_{RMS} = 130\text{ V}</math></b>					
B72205U2131K501	205	$\pm 10$	340	5.0	135
B72207U2131K501	205	$\pm 10$	340	10.0	245
B72210U2131K501	205	$\pm 10$	340	25.0	500
B72214U2131K501	205	$\pm 10$	340	50.0	880
B72220U2131K501	205	$\pm 10$	340	100.0	1850
<b><math>V_{RMS} = 140\text{ V}</math></b>					
B72205U2141K501	220	$\pm 10$	360	5.0	125
B72207U2141K501	220	$\pm 10$	360	10.0	230
B72210U2141K501	220	$\pm 10$	360	25.0	470
B72214U2141K501	220	$\pm 10$	360	50.0	820
B72220U2141K501	220	$\pm 10$	360	100.0	1700
<b><math>V_{RMS} = 150\text{ V}</math></b>					
B72205U2151K501	240	$\pm 10$	395	5.0	115
B72207U2151K501	240	$\pm 10$	395	10.0	210
B72210U2151K501	240	$\pm 10$	395	25.0	430
B72214U2151K501	240	$\pm 10$	395	50.0	750
B72220U2151K501	240	$\pm 10$	395	100.0	1550
<b><math>V_{RMS} = 175\text{ V}</math></b>					
B72205U2171K501	270	$\pm 10$	455	5.0	100
B72207U2171K501	270	$\pm 10$	455	10.0	190
B72210U2171K501	270	$\pm 10$	455	25.0	380
B72214U2171K501	270	$\pm 10$	455	50.0	670
B72220U2171K501	270	$\pm 10$	455	100.0	1350
<b><math>V_{RMS} = 210\text{ V}</math></b>					
B72205U2211K501	330	$\pm 10$	545	5.0	75
B72207U2211K501	330	$\pm 10$	545	10.0	140
B72210U2211K501	330	$\pm 10$	545	25.0	290
B72214U2211K501	330	$\pm 10$	545	50.0	580
B72220U2211K501	330	$\pm 10$	545	100.0	1100
<b><math>V_{RMS} = 230\text{ V}</math></b>					
B72205U2231K501	360	$\pm 10$	595	5.0	70
B72207U2231K501	360	$\pm 10$	595	10.0	130
B72210U2231K501	360	$\pm 10$	595	25.0	265
B72214U2231K501	360	$\pm 10$	595	50.0	530
B72220U2231K501	360	$\pm 10$	595	100.0	1000



## Leaded varistors, SNF high operating temperature

B722\*

SNF AdvanceD series

## Electrical specifications and ordering codes

Maximum ratings ( $T_A = 125^\circ\text{C}$ )

Ordering code	Type (untaped) SIOV-	$V_{\text{RMS}}$ V	$V_{\text{DC}}$ V	$I_{\text{max}}$ (8/20 $\mu\text{s}$ ) 1 time A	$I_n$ <sup>1)</sup> (8/20 $\mu\text{s}$ ) 15 times A	$W_{\text{max}}$ (2 ms) J	$P_{\text{max}}$ W
<b><math>V_{\text{RMS}} = 250\text{ V}</math></b>							
B72205U2251K501	SNF05K250E2S5	250	320	800	150	12.0	0.10
B72207U2251K501	SNF07K250E2S5	250	320	1750	500	25.0	0.25
B72210U2251K501	SNF10K250E2S5	250	320	3500	1500	50.0	0.40
B72214U2251K501	SNF14K250E2S5	250	320	6000	3000	100.0	0.60
B72220U2251K501	SNF20K250E2S5	250	320	10000	3000	195.0	1.00
<b><math>V_{\text{RMS}} = 275\text{ V}</math></b>							
B72205U2271K501	SNF05K275E2S5	275	350	800	150	13.5	0.10
B72207U2271K501	SNF07K275E2S5	275	350	1750	500	27.5	0.25
B72210U2271K501	SNF10K275E2S5	275	350	3500	1500	55.0	0.40
B72214U2271K501	SNF14K275E2S5	275	350	6000	3000	110.0	0.60
B72220U2271K501	SNF20K275E2S5	275	350	10000	3000	215.0	1.00
<b><math>V_{\text{RMS}} = 300\text{ V}</math></b>							
B72205U2301K501	SNF05K300E2S5	300	385	800	150	15.0	0.10
B72207U2301K501	SNF07K300E2S5	300	385	1750	500	30.0	0.25
B72210U2301K501	SNF10K300E2S5	300	385	3500	1500	60.0	0.40
B72214U2301K501	SNF14K300E2S5	300	385	6000	3000	125.0	0.60
B72220U2301K501	SNF20K300E2S5	300	385	10000	3000	250.0	1.00
<b><math>V_{\text{RMS}} = 320\text{ V}</math></b>							
B72207U2321K501	SNF07K320E2S5	320	420	1750	500	32.0	0.25
B72210U2321K501	SNF10K320E2S5	320	420	3500	1500	67.0	0.40
B72214U2321K501	SNF14K320E2S5	320	420	6000	3000	136.0	0.60
B72220U2321K501	SNF20K320E2S5	320	420	10000	3000	273.0	1.00
<b><math>V_{\text{RMS}} = 350\text{ V}</math></b>							
B72210U2351K501	SNF10K350E2S5	350	460	3500	1500	67.0	0.40
B72214U2351K501	SNF14K350E2S5	350	460	5000	3000	136.0	0.60
B72220U2351K501	SNF20K350E2S5	350	460	10000	3000	273.0	1.00
<b><math>V_{\text{RMS}} = 385\text{ V}</math></b>							
B72210U2381K501	SNF10K385E2S5	385	505	3500	1500	67.0	0.40
B72214U2381K501	SNF14K385E2S5	385	505	5000	3000	136.0	0.60
B72220U2381K501	SNF20K385E2S5	385	505	10000	3000	273.0	1.00

<sup>1)</sup> Note: Nominal discharge current  $I_n$  according to UL 1449, 4<sup>th</sup> edition.

Characteristics ( $T_A = 25^\circ\text{C}$ )

Ordering code	$V_v$ (1 mA) V	$\Delta V_v$ (1 mA) %	$V_{c,max}$ ( $i_c$ ) V	$i_c$ A	$C_{typ}$ (1 kHz) pF
<b><math>V_{RMS} = 250\text{ V}</math></b>					
B72205U2251K501	390	$\pm 10$	650	5.0	65
B72207U2251K501	390	$\pm 10$	650	10.0	120
B72210U2251K501	390	$\pm 10$	650	25.0	245
B72214U2251K501	390	$\pm 10$	650	50.0	490
B72220U2251K501	390	$\pm 10$	650	100.0	940
<b><math>V_{RMS} = 275\text{ V}</math></b>					
B72205U2271K501	430	$\pm 10$	710	5.0	60
B72207U2271K501	430	$\pm 10$	710	10.0	110
B72210U2271K501	430	$\pm 10$	710	25.0	220
B72214U2271K501	430	$\pm 10$	710	50.0	440
B72220U2271K501	430	$\pm 10$	710	100.0	850
<b><math>V_{RMS} = 300\text{ V}</math></b>					
B72205U2301K501	470	$\pm 10$	775	5.0	55
B72207U2301K501	470	$\pm 10$	775	10.0	100
B72210U2301K501	470	$\pm 10$	775	25.0	200
B72214U2301K501	470	$\pm 10$	775	50.0	400
B72220U2301K501	470	$\pm 10$	775	100.0	780
<b><math>V_{RMS} = 320\text{ V}</math></b>					
B72207U2321K501	510	$\pm 10$	840	10.0	90
B72210U2321K501	510	$\pm 10$	840	25.0	185
B72214U2321K501	510	$\pm 10$	840	50.0	370
B72220U2321K501	510	$\pm 10$	840	100.0	720
<b><math>V_{RMS} = 350\text{ V}</math></b>					
B72210U2351K501	560	$\pm 10$	910	25.0	160
B72214U2351K501	560	$\pm 10$	910	50.0	350
B72220U2351K501	560	$\pm 10$	910	100.0	660
<b><math>V_{RMS} = 385\text{ V}</math></b>					
B72210U2381K501	620	$\pm 10$	1025	25.0	175
B72214U2381K501	620	$\pm 10$	1025	50.0	315
B72220U2381K501	620	$\pm 10$	1025	100.0	600

## Leaded varistors, SNF high operating temperature

B722\*

SNF AdvanceD series



## Electrical specifications and ordering codes

Maximum ratings ( $T_A = 125^\circ\text{C}$ )

Ordering code	Type (untaped) SIOV-	$V_{\text{RMS}}$ V	$V_{\text{DC}}$ V	$I_{\text{max}}$ (8/20 $\mu\text{s}$ ) 1 time A	$I_{\text{n}}^{(1)}$ (8/20 $\mu\text{s}$ ) 15 times A	$W_{\text{max}}$ (2 ms) J	$P_{\text{max}}$ W
$V_{\text{RMS}} = 420 \text{ V}$							
B72210U2421K501	SNF10K420E2S5	420	560	3500	1500	67.0	0.40
B72214U2421K501	SNF14K420E2S5	420	560	5000	3000	136.0	0.60
B72220U2421K501	SNF20K420E2S5	420	560	10000	3000	273.0	1.00
$V_{\text{RMS}} = 460 \text{ V}$							
B72210U2461K501	SNF10K460E2S5	460	615	3500	1500	70.0	0.40
B72214U2461K501	SNF14K460E2S5	460	615	5000	3000	150.0	0.60
B72220U2461K501	SNF20K460E2S5	460	615	10000	3000	300.0	1.00
$V_{\text{RMS}} = 510 \text{ V}$							
B72210U2511K501	SNF10K510E2S5	510	670	3500	1500	80.0	0.40
B72214U2511K501	SNF14K510E2S5	510	670	5000	3000	165.0	0.60
B72220U2511K501	SNF20K510E2S5	510	670	10000	3000	325.0	1.00
$V_{\text{RMS}} = 550 \text{ V}$							
B72210U2551K501	SNF10K550E2S5	550	745	3500	1500	90.0	0.40
B72214U2551K501	SNF14K550E2S5	550	745	5000	3000	180.0	0.60
B72220U2551K501	SNF20K550E2S5	550	745	10000	3000	360.0	1.00
$V_{\text{RMS}} = 625 \text{ V}$							
B72210U2621K501	SNF10K625E2S5	625	825	3500	1500	100.0	0.40
B72214U2621K501	SNF14K625E2S5	625	825	5000	3000	200.0	0.60
B72220U2621K501	SNF20K625E2S5	625	825	10000	3000	400.0	1.00

<sup>1)</sup> Note: Nominal discharge current  $I_n$  according to UL 1449, 4<sup>th</sup> edition.

Characteristics ( $T_A = 25^\circ\text{C}$ )

Ordering code	$V_v$ (1 mA) V	$\Delta V_v$ (1 mA) %	$V_{c,max}$ ( $i_c$ ) V	$i_c$ A	$C_{typ}$ (1 kHz) pF
<b><math>V_{RMS} = 420 \text{ V}</math></b>					
B72210U2421K501	680	$\pm 10$	1120	25.0	165
B72214U2421K501	680	$\pm 10$	1120	50.0	290
B72220U2421K501	680	$\pm 10$	1120	100.0	550
<b><math>V_{RMS} = 460 \text{ V}</math></b>					
B72210U2461K501	750	$\pm 10$	1240	25.0	150
B72214U2461K501	750	$\pm 10$	1240	50.0	260
B72220U2461K501	750	$\pm 10$	1240	100.0	500
<b><math>V_{RMS} = 510 \text{ V}</math></b>					
B72210U2511K501	820	$\pm 10$	1355	25.0	140
B72214U2511K501	820	$\pm 10$	1355	50.0	240
B72220U2511K501	820	$\pm 10$	1355	100.0	460
<b><math>V_{RMS} = 550 \text{ V}</math></b>					
B72210U2551K501	910	$\pm 10$	1500	25.0	120
B72214U2551K501	910	$\pm 10$	1500	50.0	215
B72220U2551K501	910	$\pm 10$	1500	100.0	410
<b><math>V_{RMS} = 625 \text{ V}</math></b>					
B72210U2621K501	1000	$\pm 10$	1650	25.0	110
B72214U2621K501	1000	$\pm 10$	1650	50.0	200
B72220U2621K501	1000	$\pm 10$	1650	100.0	380


## Leaded varistors, SNF high operating temperature

B722\*

SNF AdvanceD series



## Dimensional drawings



1) Seating plane to IEC 60717

VAR0727-N-E

## Weight

Nominal diameter mm	$V_{RMS}$ V	Weight g
7	130 ... 320	0.6 ... 1.0
10	130 ... 625	1.6 ... 3.0
14	130 ... 625	2.8 ... 4.4
20	130 ... 625	6.0 ... 9.4

The weight of varistors in between these voltage classes can be interpolated.

**Please note:** Paint legs may have cracks or chips due to the mechanical forces acting on the wires, but this does not affect the performance of the component.

## Dimensions

Ordering code	$[e] \pm 1$ mm	a (typical) mm	$w_{max}$ mm	$th_{max}$ mm	$h_{max}$ mm	$l_{min}$ mm	$d \pm 0.05$ mm
$V_{RMS} = 130$ V							
B72205U2131K501	5.0	1.6	9.0	6.9	13.0	25.0	0.6
B72207U2131K501	5.0	1.6	11.0	6.9	15.5	25.0	0.6
B72210U2131K501	7.5	1.8	14.0	7.5	19.0	25.0	0.8
B72214U2131K501	7.5	1.9	17.5	7.6	23.0	25.0	0.8
B72220U2131K501	10.0	2.0	23.5	8.0	30.0	25.0	1.0
$V_{RMS} = 140$ V							
B72205U2141K501	5.0	1.7	9.0	7.0	13.0	25.0	0.6
B72207U2141K501	5.0	1.7	11.0	7.0	15.5	25.0	0.6
B72210U2141K501	7.5	1.9	14.0	7.6	19.0	25.0	0.8
B72214U2141K501	7.5	2.0	17.5	7.7	23.0	25.0	0.8
B72220U2141K501	10.0	2.1	23.5	8.1	30.0	25.0	1.0
$V_{RMS} = 150$ V							
B72205U2151K501	5.0	1.8	9.0	7.1	13.0	25.0	0.6
B72207U2151K501	5.0	1.8	11.0	7.1	15.5	25.0	0.6
B72210U2151K501	7.5	2.0	14.0	7.7	19.0	25.0	0.8
B72214U2151K501	7.5	2.1	17.5	7.8	23.0	25.0	0.8
B72220U2151K501	10.0	2.2	23.5	8.2	30.0	25.0	1.0



Ordering code	[e] $\pm 1$ mm	a (typical) mm	w <sub>max</sub> mm	th <sub>max</sub> mm	h <sub>max</sub> mm	l <sub>min</sub> mm	d $\pm 0.05$ mm
<b>V<sub>RMS</sub> = 175 V</b>							
B72205U2171K501	5.0	2.0	9.0	7.3	13.0	25.0	0.6
B72207U2171K501	5.0	2.0	11.0	7.3	15.5	25.0	0.6
B72210U2171K501	7.5	2.2	14.0	7.9	19.0	25.0	0.8
B72214U2171K501	7.5	2.2	17.5	7.9	23.0	25.0	0.8
B72220U2171K501	10.0	2.3	23.5	8.3	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 210 V</b>							
B72205U2211K501	5.0	1.7	9.0	7.2	13.0	25.0	0.6
B72207U2211K501	5.0	1.7	11.0	7.2	15.5	25.0	0.6
B72210U2211K501	7.5	1.9	14.0	8.0	19.0	25.0	0.8
B72214U2211K501	7.5	1.9	17.5	8.0	23.0	25.0	0.8
B72220U2211K501	10.0	2.2	23.5	8.4	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 230 V</b>							
B72205U2231K501	5.0	1.5	9.0	7.4	13.0	25.0	0.6
B72207U2231K501	5.0	1.5	11.0	7.4	15.5	25.0	0.6
B72210U2231K501	7.5	1.7	14.0	8.0	19.0	25.0	0.8
B72214U2231K501	7.5	1.7	17.5	8.1	23.0	25.0	0.8
B72220U2231K501	10.0	1.8	23.5	8.5	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 250 V</b>							
B72205U2251K501	5.0	1.5	9.0	7.5	13.0	25.0	0.6
B72207U2251K501	5.0	1.5	11.0	7.5	15.5	25.0	0.6
B72210U2251K501	7.5	1.7	14.0	8.2	19.0	25.0	0.8
B72214U2251K501	7.5	1.7	17.5	8.2	23.0	25.0	0.8
B72220U2251K501	10.0	1.9	23.5	8.7	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 275 V</b>							
B72205U2271K501	5.0	1.6	9.0	7.6	13.0	25.0	0.6
B72207U2271K501	5.0	1.6	11.0	7.6	15.5	25.0	0.6
B72210U2271K501	7.5	1.8	14.0	8.4	19.0	25.0	0.8
B72214U2271K501	7.5	1.8	17.5	8.4	23.0	25.0	0.8
B72220U2271K501	10.0	2.0	23.5	8.8	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 300 V</b>							
B72205U2301K501	5.0	1.7	9.0	7.7	13.0	25.0	0.6
B72207U2301K501	5.0	1.7	11.0	7.7	15.5	25.0	0.6
B72210U2301K501	7.5	1.9	14.0	8.6	19.0	25.0	0.8
B72214U2301K501	7.5	1.9	17.5	8.6	23.0	25.0	0.8
B72220U2301K501	10.0	2.1	23.5	9.1	30.0	25.0	1.0



## Leaded varistors, SNF high operating temperature

B722\*

SNF AdvanceD series

Ordering code	[e] $\pm 1$ mm	a (typical) mm	w <sub>max</sub> mm	th <sub>max</sub> mm	h <sub>max</sub> mm	l <sub>min</sub> mm	d $\pm 0.05$ mm
<b>V<sub>RMS</sub> = 320 V</b>							
B72207U2321K501	5.0	1.9	11.0	7.6	15.5	25.0	0.6
B72210U2321K501	7.5	2.1	14.0	8.8	19.5	25.0	0.8
B72214U2321K501	7.5	2.1	17.5	8.8	23.5	25.0	0.8
B72220U2321K501	10.0	2.3	23.5	9.2	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 350 V</b>							
B72210U2351K501	7.5	2.2	14.0	9.5	19.5	25.0	0.8
B72214U2351K501	7.5	2.2	17.5	9.5	23.5	25.0	0.8
B72220U2351K501	10.0	2.4	23.5	10.0	30.0	25.0	1.0
<b>V<sub>RMS</sub> = 385 V</b>							
B72210U2381K501	7.5	2.4	14.0	10.1	19.5	25.0	0.8
B72214U2381K501	7.5	2.4	17.5	10.1	23.5	25.0	0.8
B72220U2381K501	10.0	2.5	23.5	10.6	30.5	25.0	1.0
<b>V<sub>RMS</sub> = 420 V</b>							
B72210U2421K501	7.5	2.6	14.0	10.4	19.5	25.0	0.8
B72214U2421K501	7.5	2.6	17.5	10.5	23.5	25.0	0.8
B72220U2421K501	10.0	2.7	23.5	10.9	30.5	25.0	1.0
<b>V<sub>RMS</sub> = 460 V</b>							
B72210U2461K501	7.5	2.8	14.0	10.7	19.5	25.0	0.8
B72214U2461K501	7.5	2.8	17.5	10.8	23.5	25.0	0.8
B72220U2461K501	10.0	3.0	23.5	11.2	30.5	25.0	1.0
<b>V<sub>RMS</sub> = 510 V</b>							
B72210U2511K501	7.5	3.1	14.0	11.0	19.5	25.0	0.8
B72214U2511K501	7.5	3.1	17.5	11.1	23.5	25.0	0.8
B72220U2511K501	10.0	3.2	23.5	11.6	30.5	25.0	1.0
<b>V<sub>RMS</sub> = 550 V</b>							
B72210U2551K501	7.5	3.4	14.0	114	19.5	25.0	0.8
B72214U2551K501	7.5	3.4	17.5	11.5	23.5	25.0	0.8
B72220U2551K501	10.0	3.6	3	12.0	30.5	25.0	1.0
<b>V<sub>RMS</sub> = 625 V</b>							
B72210U2621K501	7.5	3.7	14.0	11.8	19.5	25.0	0.8
B72214U2621K501	7.5	3.7	17.5	11.9	23.5	25.0	0.8
B72220U2621K501	10.0	3.9	23.5	12.4	30.5	25.0	1.0



## Reliability data

Test	Test methods/ conditions	Requirement
Varistor voltage	The voltage between two terminals with the specified measuring current applied is called $V_V$ (1 mA <sub>DC</sub> @ 0.2 ... 2 s).	To meet the specified value
Clamping voltage	The maximum voltage between two terminals with the specified standard impulse current (8/20 µs) applied.	To meet the specified value
Endurance at upper category temperature	1000 h at UCT After having continuously applied the maximum allowable AC voltage at UCT $\pm 2$ °C for 1000 h, the specimen shall be stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of $V_V$ shall be measured.	$ \Delta V/V (1 \text{ mA})  \leq 10\%$
Surge current derating, 8/20 µs	10 surge currents (8/20 µs), unipolar, interval 30 s, amplitude corresponding to derating curve for 10 impulses at 20 µs	$ \Delta V/V (1 \text{ mA})  \leq 10\%$ (measured in direction of surge current) No visible damage
Surge current derating, 2 ms	10 surge currents (2 ms), unipolar, interval 120 s, amplitude corresponding to derating curve for 10 impulses at 2 ms	$ \Delta V/V (1 \text{ mA})  \leq 10\%$ (measured in direction of surge current) No visible damage
Electric strength	IEC 61051-1, test 4.9.2 Metal balls method, 2500 V <sub>RMS</sub> , 60 s The varistor is placed in a container holding 1.6 $\pm 0.2$ mm diameter metal balls such that only the terminations of the varistor are protruding. The specified voltage shall be applied between both terminals of the specimen connected together and the electrode inserted between the metal balls.	No breakdown



## Leaded varistors, SNF high operating temperature

B722\*

## SNF AdvanceD series

Test	Test methods/ conditions	Requirement
Climatic sequence	<p>The specimen shall be subjected to:</p> <ul style="list-style-type: none"> <li>a) dry heat at UCT, 16 h, IEC 60068-2-2, test Ba</li> <li>b) damp heat, 1st cycle: 55 °C, 93% r. H., 24 h, IEC 60068-2-30, test Db</li> <li>c) cold, LCT, 2 h, IEC 60068-2-1, test Aa</li> <li>d) damp heat, additional 5 cycles: 55 °C/25 °C, 93% r. H., 24 h/cycle, IEC 60068-2-30, test Db.</li> </ul> <p>Then the specimen shall be stored at room temperature and normal humidity for 1 to 2 h.</p> <p>Thereafter, the change of <math>V_y</math> shall be measured. Thereafter, insulation resistance <math>R_{ins}</math> shall be measured at <math>V = 500</math> V.</p>	$ \Delta V/V (1 \text{ mA})  \leq 10\%$ $R_{ins} \geq 100 \text{ M}\Omega$
Rapid change of temperature	IEC 60068-2-14, test Na, LCT/UCT, dwell time 10 min, 1000 cycles	$ \Delta V/V (1 \text{ mA})  \leq 5\%$ No visible damage
Damp heat	IEC 60068-2-78, test Cy 85 °C, 85% r. H., 0.85 * $V_y$ (1 mA), 1000 h	$ \Delta V/V (1 \text{ mA})  \leq 10\%$ No visible damage
Solderability	<p>IEC 60068-2-20, test Ta, method 1 with modified conditions for lead-free solder alloys: 245 °C, 3 s:</p> <p>After dipping the terminals to a depth of approximately 3 mm from the body in a soldering bath of 245 °C for 3 s, the terminals shall be visually examined.</p>	The inspection shall be carried out under adequate light with normal eyesight or with the assistance of a magnifier capable of giving a magnification of 4 to 10 times. The dipped surface shall be covered with a smooth and bright solder coating with no more than small amounts of scattered imperfections such as pinholes or un-wetted or de-wetted areas. These imperfections shall not be concentrated in one area.



Test	Test methods/ conditions	Requirement
Resistance to soldering heat	<p>IEC 60068-2-20, test Tb, method 1A, 260 °C, 10 s:</p> <p>Each lead shall be dipped into a solder bath having a temperature of <math>260 \pm 5</math> °C to a point 2.0 to 2.5 mm from the body of the specimen, be held there for <math>10 \pm 1</math> s and then be stored at room temperature and normal humidity for 1 to 2 h.</p> <p>The change of <math>V_v</math> shall be measured and the specimen shall be visually examined.</p>	$ \Delta V/V (1 \text{ mA})  \leq 5\%$ No visible damage
Tensile strength	<p>IEC 60068-2-21, test Ua1</p> <p>After gradually applying the force specified below and keeping the unit fixed for 10 s, the terminal shall be visually examined for any damage.</p> <p>Force for wire diameter:</p> <ul style="list-style-type: none"> <li>0.6 mm = 10 N</li> <li>0.8 mm = 10 N</li> <li>1.0 mm = 20 N</li> </ul>	$ \Delta V/V (1 \text{ mA})  \leq 5\%$ No break of solder joint, no wire break
Vibration	<p>IEC 60068-2-6, test Fc, method B4</p> <p>Frequency range: 10 ... 55 Hz</p> <p>Amplitude: 0.75 mm or 98 m/s<sup>2</sup></p> <p>Duration: 6 h (3 · 2 h)</p> <p>Pulse: sine wave</p> <p>After repeatedly applying a single harmonic vibration according to the table above.</p> <p>The change of <math>V_v</math> shall be measured and the specimen shall be visually examined.</p>	$ \Delta V/V (1 \text{ mA})  \leq 5\%$ No visible damage
Bump	<p>IEC 60068-2-29, test Eb</p> <p>Pulse duration: 6 ms</p> <p>Max. acceleration: 400 m/s<sup>2</sup></p> <p>Number of bumps: 4000</p> <p>Pulse: half sine</p>	$ \Delta V/V (1 \text{ mA})  \leq 5\%$ No visible damage
Fire hazard	<p>IEC 60695-11-5 (needle flame test)</p> <p>Severity: vertical 10 s</p>	5 s max.

**Note:**

UCT = Upper category temperature

LCT = Lower category temperature

 $R_{ins}$  = Insulation resistance



## Leaded varistors, SNF high operating temperature


B722\*

SNF AdvanceD series


## v/i characteristics

 $v = f(i)$  - for explanation of the characteristics refer to "General technical information", 1.6.3

A = Leakage current, B = Protection level } for worst-case varistor tolerances



SIOV-SNF05 ...





SIOV-SNF07 ...

**v/i characteristics**

$v = f(i)$  - for explanation of the characteristics refer to "General technical information", 1.6.3

A = Leakage current, B = Protection level } for worst-case varistor tolerances


**SIOV-SNF10 ...****SIOV-SNF14 ...**



## v/i characteristics

$v = f(i)$  - for explanation of the characteristics refer to "General technical information", 1.6.3

A = Leakage current, B = Protection level } for worst-case varistor tolerances




## SIOV-SNF20 ...




## Derating curves

Maximum surge current  $i_{\max} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", section 1.8.1



## SIOV-SNF05 ...




## SIOV-SNF07 ...




### Derating curves

Maximum surge current  $i_{\max} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", section 1.8.1



**SIOV-SNF10K130 ... K320E2S5K1**




**SIOV-SNF10K350 ... K625E2S5K1**




## Derating curves

Maximum surge current  $i_{\max} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", section 1.8.1



**SIOV-SNF14K130 ... K320E2S5K1**




**SIOV-SNF14K350 ... K625E2S5K1**




### Derating curves

Maximum surge current  $i_{\max} = f(t_r, \text{pulse train})$

For explanation of the derating curves refer to "General technical information", section 1.8.1



SIOV-SNF20K130 ... K320E2S5K1




SIOV-SNF20K350 ... K625E2S5K1



## Taping, packaging and lead configuration

### 1 EPCOS ordering code system

#### For leaded varistors







## 2 Taping and packaging of leaded varistors

Tape packaging for lead spacing  $\bar{e} = 5$  fully conforms to IEC 60286-2, while for lead spacings  $\bar{e} = 7.5$  and 10 the taping mode is based on this standard.

### 2.1 Taping in accordance with IEC 60286-2 for lead spacing 5.0 mm



### 2.2 Taping based on IEC 60286-2 for lead spacing 7.5 and 10 mm





## 2.3 Tape dimensions (in mm)

Symbol	$e = 5.0$	Tolerance	$e = 7.5$	Tolerance	$e = 10.0$	Tolerance	Remarks	
w		max.		max.		max.	see tables in each series under "Dimensions"	
th		max.		max.		max.		
d	0.6	$\pm 0.05$	0.8	$\pm 0.05$	1.0	$\pm 0.05$		
$P_0$	12.7	$\pm 0.3$	12.7 <sup>1)</sup>	$\pm 0.3$	12.7	$\pm 0.3$	$\pm 1$ mm/20 sprocket holes	
$P_1$	3.85	$\pm 0.7$	8.95	$\pm 0.8$	7.7	$\pm 0.8$		
F	5.0	$+0.6/-0.1$	7.5	$\pm 0.8$	10.0	$\pm 0.8$	measured at top of component body	
$\Delta h_0$	$\pm 2.0$	depends on s	0	$\pm 2.0$	0	$\pm 2.0$		
$\Delta p_0$	$\pm 1.3$							
W	18.0	$\pm 0.5$	18.0	$\pm 0.5$	18.0	$\pm 0.5$	Peel-off force $\geq 5$ N	
$W_0$	5.5	min.	11.0	min.	11.0	min.		
$W_1$	9.0	$\pm 0.5$	9.0	$+0.75/-0.5$	9.0	$+0.75/-0.5$		
$W_2$	3.0	max.	3.0	max.	3.0	max.		
H	18.0	$+2.0/-0$	18.0	$+2.0/-0$	18.0	$+2.0/-0$	<sup>2)</sup>	
$H_0$	16.0	$\pm 0.5$	16.0	$\pm 0.5$	16.0	$\pm 0.5$		
$(H_0)$	(18.0)		(18.0)					
$H_1$	32.2	max.	45.0	max.	45.0	max.		
$D_0$	4.0	$\pm 0.2$	4.0	$\pm 0.2$	4.0	$\pm 0.2$	without lead	
t	0.9	max.	0.9	max.	0.9	max.		
L	11.0	max.	11.0	max.	11.0	max.		
$L_1$	0.5	max.						

1) Taping with  $P_0 = 15.0$  mm upon request

2) Applies only to uncrimped types

3) Applies only to crimped types ( $H_0 = 18$  upon request)



## 2.4 Taping mode

Example: B72210S0271K1 **5** 1


Digit 14

Digit 14	Taping mode	Reel type	Seating plane height $H_0$ for crimped types mm	Seating plane height $H$ for uncrimped types mm	Pitch distance $P_0$ mm
0	–	Bulk	–	–	–
1	G	I	16	18	12.7
2	G2	I	18	–	12.7
3	G3	II	16	18	12.7
4	G4	II	18	–	12.7
5	G5	III	16	18	12.7
6	GA	Ammo pack	16	18	12.7
7	G2A	Ammo pack	18	–	12.7


Internal coding for special taping

G6	III	18	–	12.7
G10	II	16	18	15.0
G11	II	18	–	15.0
G10A	Ammo pack	16	18	15.0
G11A	Ammo pack	18	–	15.0

## 2.5 Reel dimension



VAR0304-Q



VAR0078-8-E


### Dimensions (in mm)

Reel type	d	f	n	w
I	360 max.	31 ±1	approx. 45	54 max.
II	360 max.	31 ±1	approx. 55	64 max.
III	500 max.	23 ±1	approx. 59	72 max.

If reel type III is not compatible with insertion equipment because of its large diameter, nominal disk diameter 10 mm and 14 mm can be supplied on reel II upon request (taping mode G3).



## 2.6 Ammo pack dimensions



VAR0402-G

## 3 Lead configuration

Straight leads are standard for disk varistors. Other lead configurations as crimp style or customer-specific lead wire length according to 3.1, 3.2, 3.3 and 3.4 are optional. Crimped leads (non-standard) are differently crimped for technical reasons; the individual crimp styles are denoted by consecutive numbers (S, S2 through S5) as shown in the dimensional drawings below.

The crimp styles of the individual types can be seen from the type designation in the ordering tables.

### 3.1 Crimp style mode

Example: B72210S0271K **5** 01  
Digit 13


Digit 13 of ordering code	Crimp style	Figure
1	Standard, straight leads	1
2	S2	2
3	S3	3
5	S5	4
Available upon request		
Internal coding	—	5



### 3.2 Standard leads and non-standard crimp styles


The basic dimensions in figure 1 to 5 are valid for types with either round or square (EnergetiQ series) component head.

**Standard, straight leads**




1) Seating plane to IEC 717  
VAR0586-W-E

**Non-standard, crimp style S2**



1) Seating plane to IEC 60717  
VAR0411-F-E

**Non-standard, crimp style S3**




1) Seating plane to IEC 60717  
VAR0396-R-E

**Figure 1**

**Figure 2**

**Figure 3**

**Non-standard, crimp style S5**



1) Seating plane to IEC 60717  
VAR0726-M-E

**Figure 4**



### 3.3 Trimmed leads (non-standard)


Varistors with cut leads available upon request.

Lead length tolerances:

Straight leads  $+/-0.8$  mm

Crimped leads  $+/-0.5$  mm

Minimum lead length 3.0 mm



1) Seating plane to IEC 60717

\*) For round component head

\*\*) For EnergetiQ series, square component head

VAR0642-U-E

**Figure 5**



## Cautions and warnings

### General

1. EPCOS metal oxide varistors are designed for specific applications and should not be used for purposes not identified in our specifications, application notes and data books unless otherwise agreed with EPCOS during the design-in-phase.
2. Ensure suitability of SIOVs through reliability testing during the design-in phase. SIOVs should be evaluated taking into consideration worst-case conditions.
3. For applications of SIOVs in line-to-ground circuits based on various international and local standards there are restrictions existing or additional safety measures required.

### Storage

1. Store SIOVs only in original packaging. Do not open the package prior to processing.
2. Recommended storage conditions in original packaging:  
Storage temperature:  $-25^{\circ}\text{C} \dots +45^{\circ}\text{C}$ ,  
Relative humidity:  $<75\%$  annual average,  
 $<95\%$  on maximum 30 days a year.  
Dew precipitation: is to be avoided.
3. Avoid contamination of an SIOV's during storage, handling and processing.
4. Avoid storage of SIOVs in harmful environments that can affect the function during long-term operation (examples given under operation precautions).
5. The SIOV type series should be soldered after shipment from EPCOS within the time specified:  
SIOV-S, -Q, -LS, -B, -SNF      24 months  
ETFV/ T series, -CU              12 months.

### Handling

1. SIOVs must not be dropped.
2. Components must not be touched with bare hands. Gloves are recommended.
3. Avoid contamination of the surface of SIOV electrodes during handling, be careful of the sharp edge of SIOV electrodes.

### Soldering (where applicable)

1. Use rosin-type flux or non-activated flux.
2. Insufficient preheating may cause ceramic cracks.
3. Rapid cooling by dipping in solvent is not recommended.
4. Complete removal of flux is recommended.
5. Temperatures of all preheat stages and the solder bath must be strictly controlled especially for T series (T14 and T20).



Leaded varistors, SNF high operating temperature

B722\*

SNF AdvanceD series

## Mounting

1. Potting, sealing or adhesive compounds can produce chemical reactions in the SIOV ceramic that will degrade the component's electrical characteristics.
2. Overloading SIOVs may result in ruptured packages and expulsion of hot materials. For this reason SIOVs should be physically shielded from adjacent components.

## Operation

1. Use SIOVs only within the specified temperature operating range.
2. Use SIOVs only within the specified voltage and current ranges.
3. Environmental conditions must not harm SIOVs. Use SIOVs only in normal atmospheric conditions. Avoid use in deoxidizing gases (chlorine gas, hydrogen sulfide gas, ammonia gas, sulfuric acid gas etc), corrosive agents, humid or salty conditions. Contact with any liquids and solvents should be prevented.

## Display of ordering codes for EPCOS products

The ordering code for one and the same EPCOS product can be represented differently in data sheets, data books, other publications, on the EPCOS website, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under [www.epcos.com/orderingcodes](http://www.epcos.com/orderingcodes)



## Symbols and terms

Symbol	Term
C	Capacitance
$C_{typ}$	Typical capacitance
i	Current
$i_c$	Current at which $V_{c, max}$ is measured
$I_{leak}$	Leakage current
$i_{max}$	Maximum surge current (also termed peak current)
$I_{max}$	Maximum discharge current
$I_h$	Nominal discharge current to UL 1449
LCT	Lower category temperature
$L_{typ}$	Typical inductance
$P_{max}$	Maximum average power dissipation
$R_{ins}$	Insulation resistance
$R_{min}$	Minimum resistance
$T_A$	Ambient temperature
$t_r$	Duration of equivalent rectangular wave
UCT	Upper category temperature
v	Voltage
$V_{clamp}$	Clamping voltage
$V_{c, max}$	Maximum clamping voltage at specified current $i_c$
$V_{DC}$	DC operating voltage
$V_{jump}$	Maximum jump start voltage
$V_{max}$	Maximum voltage
$V_{op}$	Operating voltage
$V_{RMS}$	AC operating voltage, root-mean-square value
$V_{RMS, op, max}$	Root-mean-square value of max. DC operating voltage incl. ripple current
$V_{surge}$	Super imposed surge voltage
$V_V$	Varistor voltage
$\Delta V_V$	Tolerance of varistor voltage
$W_{LD}$	Maximum load dump
$W_{max}$	Maximum energy absorption
$e$	Lead spacing

All dimensions are given in mm.

The commas used in numerical values denote decimal points.

## Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding **statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.tdk-electronics.tdk.com/material](http://www.tdk-electronics.tdk.com/material)). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard.** The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

## Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.tdk-electronics.tdk.com/trademarks](http://www.tdk-electronics.tdk.com/trademarks).

Release 2018-10

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## EPCOS / TDK:

[B72214U2511K501](#) [B72220U2321K501](#) [B72210U2151K501](#) [B72214U2271K501](#) [B72214U2151K501](#)  
[B72220U2511K501](#) [B72207U2271K501](#) [B72210U2511K501](#) [B72210U2271K501](#) [B72220U2151K501](#)  
[B72205U2151K501](#) [B72205U2271K501](#) [B72207U2151K501](#) [B72214U2321K501](#) [B72220U2271K501](#)  
[B72220U2551K502](#) [B72207U2321K502](#) [B72210U0500K502](#) [B72210U2171K903](#) [B72210U2231K303](#)  
[B72210U2301K903](#) [B72210U2351K501](#) [B72214U2621K103](#) [B72214U2621K502](#) [B72214U2301K505](#)  
[B72214U2321K502](#) [B72214U2351K102](#) [B72214U2381K102](#) [B72214U2381K502](#) [B72214U2421K502](#)  
[B72210U2381K303](#) [B72210U2381K502](#) [B72210U2381K903](#) [B72214U2171K504](#) [B72214U2271K302](#)  
[B72214U2301K502](#)