


### Product Overview

The Qorvo QPD1016 is a 500 W ( $P_{3dB}$ ) pre-matched discrete GaN on SiC HEMT which operates from DC to 1.7 GHz and 50 V supply. The device is in an industry standard air cavity package and is ideally suited for IFF, avionics, military and civilian radar, and test instrumentation. The device can support pulsed and linear operations.


ROHS compliant.

Evaluation boards are available upon request.



NI-780 Package

### Functional Block Diagram



### Key Features

- Frequency: DC to 1.7 GHz
- Linear Gain<sup>1</sup>: 18 dB
- Output Power ( $P_{3dB}$ )<sup>1</sup>: 537 W
- Drain Efficiency( $P_{3dB}$ )<sup>1</sup>: 67%
- Operating Voltage: 50 V
- CW and Pulse capable

Note 1: @ Typical EVB Performance at 1.3 GHz

### Applications

- IFF
- Avionics
- Military and civilian radar
- Test instrumentation

| Part No.     | Description                                |
|--------------|--------------------------------------------|
| QPD1016      | DC – 1.7 GHz, 500W, 50V, GaN RF Transistor |
| QPD1016EVB01 | 1.2 – 1.4 GHz EVB                          |

### Absolute Maximum Ratings<sup>1</sup>

| Parameter                                          | Rating           | Units      |
|----------------------------------------------------|------------------|------------|
| Breakdown Voltage, $BV_{DG}$                       | +145             | V          |
| Gate Voltage Range, $V_G$                          | -7 to +2         | V          |
| Drain Current, $I_{D_{MAX}}$                       | 70               | A          |
| Gate Current Range, $I_G$                          | See page 17.     | mA         |
| Power Dissipation, $P_{DISS}$                      | 714 <sup>2</sup> | W          |
| RF Input Power, Pulse, 1.3 GHz, $T = 25^\circ C^2$ | +45.5            | dBm        |
| Mounting Temperature (30 Seconds)                  | 320              | $^\circ C$ |
| Storage Temperature                                | -65 to +150      | $^\circ C$ |

#### Notes:

1. Operation of this device outside the parameter ranges given above may cause permanent damage.
2. Pulsed 300uS PW, 10% DC

### Recommended Operating Conditions<sup>1</sup>

| Parameter                                    | Min | Typ  | Max | Units      |
|----------------------------------------------|-----|------|-----|------------|
| Operating Temp. Range                        | -40 | +25  | +85 | $^\circ C$ |
| Drain Voltage Range, $V_D$                   | +32 | +50  | +55 | V          |
| Drain Bias Current, $I_{DQ}$                 |     | 1000 |     | mA         |
| Drain Current, $I_D^4$                       | –   | 16   | –   | A          |
| Gate Voltage, $V_G^3$                        | –   | -2.8 | –   | V          |
| Power Dissipation ( $P_D$ ) <sup>2,4</sup>   | –   | –    | 441 | W          |
| Power Dissipation ( $P_D$ ), CW <sup>2</sup> | –   | –    | 269 | W          |

#### Notes:

1. Electrical performance is measured under conditions noted in the electrical specifications table. Specifications are not guaranteed over all recommended operating conditions.
2. Package base at 85  $^\circ C$
3. To be adjusted to desired  $I_{DQ}$
4. Pulsed, 300uS PW, 10% DC

### Measured Load Pull Performance – Power Tuned<sup>1</sup>

| Parameter                                              | Typical Values |      |      |      |      |      | Units |
|--------------------------------------------------------|----------------|------|------|------|------|------|-------|
| Frequency, F                                           | 1.1            | 1.2  | 1.3  | 1.4  | 1.5  | 1.7  | GHz   |
| Drain Voltage, $V_D$                                   | 50             | 50   | 50   | 50   | 50   | 50   | V     |
| Drain Bias Current, $I_{DQ}$                           | 1000           | 1000 | 1000 | 1000 | 1000 | 1000 | mA    |
| Output Power at 3dB compression, $P_{3dB}$             | 58.8           | 58.6 | 58.3 | 58   | 57.6 | 58   | dBm   |
| Power Added Efficiency at 3dB compression, $PAE_{3dB}$ | 71.7           | 69.2 | 72.2 | 76.1 | 69.9 | 71.2 | %     |
| Gain at 3dB compression, $G_{3dB}$                     | 21             | 20.6 | 20.9 | 21.7 | 21.0 | 20.6 | dB    |

#### Notes:

1. Pulsed, 300 uS Pulse Width, 10% Duty Cycle
2. Characteristic Impedance,  $Z_0 = 3 \Omega$ .

### Measured Load Pull Performance – Efficiency Tuned<sup>1</sup>

| Parameter                                              | Typical Values |      |      |      |      |      | Units |
|--------------------------------------------------------|----------------|------|------|------|------|------|-------|
| Frequency, F                                           | 1.1            | 1.2  | 1.3  | 1.4  | 1.5  | 1.7  | GHz   |
| Drain Voltage, $V_D$                                   | 50             | 50   | 50   | 50   | 50   | 50   | V     |
| Drain Bias Current, $I_{DQ}$                           | 1000           | 1000 | 1000 | 1000 | 1000 | 1000 | mA    |
| Output Power at 3dB compression, $P_{3dB}$             | 57.6           | 57.1 | 56.4 | 57.3 | 56.1 | 56.7 | dBm   |
| Power Added Efficiency at 3dB compression, $PAE_{3dB}$ | 79.2           | 78.3 | 77.4 | 77.8 | 71.2 | 73.5 | %     |
| Gain at 3dB compression, $G_{3dB}$                     | 22.2           | 22.1 | 22.2 | 22.3 | 21.7 | 21.7 | dB    |

#### Notes:

1. Pulsed, 300 uS Pulse Width, 10% Duty Cycle
2. Characteristic Impedance,  $Z_0 = 3 \Omega$ .

### 1.2 – 1.4 GHz EVB at 1.3 GHz Performance<sup>1</sup>

| Parameter                                          | Min | Typ  | Max | Units |
|----------------------------------------------------|-----|------|-----|-------|
| Linear Gain, $G_{LIN}$                             | –   | 18.0 | –   | dB    |
| Output Power at 3dB compression point, P3dB        | –   | 57.3 | –   | dBm   |
| Drain Efficiency at 3dB compression point, DEFF3dB | –   | 67.3 | –   | %     |
| Gain at 3dB compression point, G3dB                | –   | 15.0 | –   | dB    |

Notes:

1.  $V_D = +50$  V,  $I_{DQ} = 1000$  mA, Temp = +25 °C, Pulse Width = 300 uS, Duty Cycle = 10%

### RF Characterization – Mismatch Ruggedness at 1.3 GHz<sup>1,2</sup>

| Symbol | Parameter                     | dB Compression | Typical |
|--------|-------------------------------|----------------|---------|
| VSWR   | Impedance Mismatch Ruggedness | 3              | 10:1    |

Notes:


1. Test conditions unless otherwise noted: TA = 25 °C, VD = 50 V, IDQ = 1000 mA
2. Input drive power is determined at pulsed 3dB compression under matched condition at EVB output connector.

## Measured Load-Pull Smith Charts<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ S Pulse Width, 10% Duty Cycle
2. See page 18 for load pull reference planes where the performance was measured.

### 1.1GHz, Load-pull




## Measured Load-Pull Smith Charts<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300 uS Pulse Width, 10% Duty Cycle
2. See page 18 for load pull reference planes where the performance was measured.

### 1.2GHz, Load-pull




## Measured Load-Pull Smith Charts<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ S Pulse Width, 10% Duty Cycle
2. See page 18 for load pull reference planes where the performance was measured.

### 1.3GHz, Load-pull




## Measured Load-Pull Smith Charts<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ S Pulse Width, 10% Duty Cycle
2. See page 18 for load pull reference planes where the performance was measured.

### 1.4GHz, Load-pull




## Measured Load-Pull Smith Charts<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ s Pulse Width, 10% Duty Cycle
2. See page 18 for load pull reference planes where the performance was measured.

### 1.5GHz, Load-pull




## Measured Load-Pull Smith Charts<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ s Pulse Width, 10% Duty Cycle
2. See page 18 for load pull reference planes where the performance was measured.





### 1.7GHz, Load-pull



## Typical Measured Performance – Load-Pull Drive-up<sup>1, 2</sup>

Notes:





1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ s Pulse Width, 10% Duty Cycle
2. See page 18 for load-pull and source-pull reference planes where the performance was measured.



## Typical Measured Performance – Load-Pull Drive-up<sup>1, 2</sup>

Notes:





1. C Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ S Pulse Width, 10% Duty Cycle
2. See page 18 for load-pull and source-pull reference planes where the performance was measured.



## Typical Measured Performance – Load-Pull Drive-up<sup>1, 2</sup>

Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ s Pulse Width, 10% Duty Cycle
2. See page 18 for load-pull and source-pull reference planes where the performance was measured.




### Power Driveup Performance Over Temperatures Of 1.2 – 1.4 GHz EVB <sup>1</sup>


Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ S Pulse Width, 10% Duty Cycle


**P3dB Over Temperatures**




**DEFF3dB Over Temperatures**



**G3dB Over Temperatures**



**Pdiss3dB Over Temperatures**




### Power Driveup Performance At 25°C Of 1.2 – 1.4 GHz EVB <sup>1</sup>


Notes:

1. Test Conditions:  $V_D = 50$  V,  $I_{DQ} = 1000$  mA, 300  $\mu$ S Pulse Width, 10% Duty Cycle


**P3dB At 25 °C**




**DEFF3dB At 25 °C**



**G3dB At 25 °C**




**Pdiss3dB At 25 °C**



## Thermal and Reliability Information – Pulsed <sup>1</sup>

Peak IR Surface Temperature vs. PW vs. Pulsed Dissipation Power  
Base Temperature at 85 °C




| Parameter <sup>1</sup>                    | Conditions                     | Values | Units |
|-------------------------------------------|--------------------------------|--------|-------|
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case                     | 0.22   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 284 W Pdiss, 300 uS PW, 10% DC | 148    | °C    |
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case                     | 0.23   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 378 W Pdiss, 300 uS PW, 10% DC | 172    | °C    |
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case                     | 0.24   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 473 W Pdiss, 300 uS PW, 10% DC | 198    | °C    |
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case                     | 0.25   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 567 W Pdiss, 300 uS PW, 10% DC | 228    | °C    |

Notes:

1. Refer to the following document [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)

Thermal and Reliability Information – CW <sup>1</sup>

Peak IR Surface Temperature vs. CW Power  
Base Temperature at 85 °C




| Parameter <sup>1</sup>                    | Conditions       | Values | Units |
|-------------------------------------------|------------------|--------|-------|
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case       | 0.34   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 94.5 W Pdiss, CW | 117    | °C    |
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case       | 0.37   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 189 W Pdiss, CW  | 154    | °C    |
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case       | 0.39   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 284 W Pdiss, CW  | 196    | °C    |
| Thermal Resistance, IR ( $\theta_{JC}$ )  | 85 °C Case       | 0.42   | °C/W  |
| Peak Channel Temperature, IR ( $T_{CH}$ ) | 378 W Pdiss, CW  | 242    | °C    |

Notes:

1. Refer to the following document [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)


## Maximum Gate Current

Maximum Gate Current Vs. Peak IR Surface Temperature



## Pin Configuration and Description<sup>1</sup>

Note 1: The QPD1016 will be marked with the “QPD1016” designator and a lot code marked below the part designator. The “YY” represents the last two digits of the calendar year the part was manufactured, the “WW” is the work week of the assembly lot start, the MXXX” is the production lot number, and the “ZZZ” is an auto-generated serial number.




| Pin | Symbol         | Description                        |
|-----|----------------|------------------------------------|
| 1   | RF IN / $V_G$  | Gate                               |
| 2   | RF OUT / $V_D$ | Drain                              |
| 3   | Source         | Source / Ground / Backside of part |


### Mechanical Drawing<sup>1</sup>

<sup>1</sup>Notes:

1. Dimension tolerances are  $\pm 0.005$  inches for lengths and  $0.5^\circ$  for angles.
2. Material:
  - Package base: Ceramic/Metal
  - Package lid: Ceramic
3. Package exposed metallization is gold plated.
4. Part is epoxy sealed.
5. Part meets industry NI780 footprint.
6. Body dimensions do not include lid shift or epoxy run out which can be up to 20 mils per side.



## 1.2 – 1.4 GHz Application Circuit - Schematic



## Bias-up Procedure


1. Set  $V_G$  to -4 V.
2. Set  $I_D$  current limit to 1100 mA.
3. Apply 50 V  $V_D$ .
4. Slowly adjust  $V_G$  until  $I_D$  is set to 1000 mA.
5. Set  $I_D$  current limit to 7 A (Pulsed operation)
6. Apply RF.

## Bias-down Procedure

1. Turn off RF signal.
2. Turn off  $V_D$
3. Wait 2 seconds to allow drain capacitor to discharge
4. Turn off  $V_G$

## 1.2 – 1.4 GHz Application Circuit - Layout


Board material is RO4350B 0.020" thickness with 2oz copper cladding. Overall EVB size is 3.98" x 3.98".



### 1.2 – 1.4 GHz Application Circuit - Bill Of material

| Description                               | Ref. Des. | Manufacturer | Part Number        |
|-------------------------------------------|-----------|--------------|--------------------|
| Capacitor 27 pF, 250V, 0805               | C1, C2    | Kyocera AVX  | 600F270FT250XT     |
| Capacitor 2.7 pF, 250V, 0805              | C3, C4    | Kyocera AVX  | 600F2R7BT250XT     |
| Capacitor 10 pF, 250V, 0805               | C9, C10   | Kyocera AVX  | 600F100FT250XT     |
| Capacitor 3.3 pF, 250V, 0805              | C11, C12  | Kyocera AVX  | 600F3R3BT250XT     |
| Capacitor 4.7 pF, 250V, 0805              | C13, C14  | Kyocera AVX  | 600F4R7BT250XT     |
| Capacitor 1.2 pF, 2%, 500V, 1111          | C15       | Kyocera AVX  | 800B1R2CT500X      |
| Capacitor 1.5 pF, 2%, 500V, 1111          | C16       | Kyocera AVX  | 800B1R5CT500X      |
| Capacitor 56 pF, 2%, 500V, 1111           | C17       | Kyocera AVX  | 800B560JT500X      |
| Capacitor 47 pF, 5%, 250V, 0805           | C18, C22  | Kyocera AVX  | 600F470JT250XT     |
| Capacitor 100 pF, 250V, 0805              | C20, C23  | Kyocera AVX  | 600F101JT250XT     |
| Capacitor, 0.1 uF, 10%, 100V X7R, 1206    | C19, C24  | Kyocera AVX  | 12061C104K4T2A     |
| Capacitor, 1 uF, 20%, 100V X7R, 1206      | C21, C25  | Murata       | GRM32ER72A105MA01L |
| Capacitor 220 uF, 20%, 100V, Electrolytic | C27, C28  | Nichicon     | UUJ2A221MNQ1MS     |
| Capacitor 220 uF, 20%, 50V, Electrolytic  | C26       | Panasonic    | EMVY500ADA221MJA0G |
| Resistor, 390 Ohm, 1%, 1/10W, 0805        | R1        | Vishay       | CRCW0805390RFKEAHP |
| Resistor, 10 Ohm, 1%, 1/10W, 0805         | R2        | Panasonic    | ERJ-6ENF10R0V      |
| Resistor, 6.04 Ohm, 1%, 1/10W, 0805       | R3        | Yageo        | RC0805FR-076R04L   |

## Recommended Solder Temperature Profile



### Handling Precautions

| Parameter                        | Rating           | Standard              |
|----------------------------------|------------------|-----------------------|
| ESD – Human Body Model (HBM)     | Class 1B (500V)  | ANSI/ESD/JEDEC JS-001 |
| ESD – Charged Device Model (CDM) | Class C3 (1000V) | ANSI/ESD/JEDEC JS-002 |
| MSL – Moisture Sensitivity Level | MSL3             | IPC/JEDEC J-STD-020   |



Caution!  
ESD-Sensitive Device

### Solderability

Compatible with both lead-free (260°C max. reflow temp.) and tin/lead (245°C max. reflow temp.) soldering processes.

Solder profiles available upon request.

Package lead plating is NiAu. Au thickness is 60 microinches minimum.

### RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- PFOS Free
- SVHC Free
- Lead Free



### Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: [www.qorvo.com](http://www.qorvo.com)

Tel: +1.844.890.8163

Email: [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

For technical questions and application information:

Email: [info-products@qorvo.com](mailto:info-products@qorvo.com)

### Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2025 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.