

Product data sheet

Specifications



speed control relay, Harmony Control Relays, 5A, 1CO, 24...240V AC DC

RM35S0MW

Product availability: Stock - Normally stocked in distribution facility

Main

Range of Product	Harmony Control Relays
Relay Type	Speed control relays
Product or Component Type	Speed control relay
Relay name	RM35S
Relay monitored parameters	Overspeed Underspeed
Time delay range	0.6...60 s adjustable on energisation 0...10 % of the full scale value)
Switching capacity in VA	1250 VA
Minimum switching current	10 mA 5 V DC
Maximum power consumption in VA	5 VA AC
Measurement range	0.05...0.5 s 0.5...5 min 1...10 min 1...10 s 0.5...5 s 0.1...1 s 0.1...1 min
Utilisation category	AC-12 IEC 60947-5-1 AC-13 IEC 60947-5-1 AC-14 IEC 60947-5-1 AC-15 IEC 60947-5-1 DC-12 IEC 60947-5-1 DC-13 IEC 60947-5-1 DC-14 IEC 60947-5-1
Measurement range	0.05...600 s
time delay	Adjustable 0.6...60 s Ti- inhibition time delay upon startup

Complementary

rest time in memory mode	50 ms contact S2 in memory mode on time delay 1 s supply Un in memory mode on time delay
Maximum switching voltage	250 V AC/DC
[Un] rated nominal voltage	24...240 V AC/DC 50/60 Hz, non self-powered
Supply voltage limits	20.4...264 V AC/DC
Maximum power consumption in W	3 W DC
Width	1.4 in (35 mm)
Output contacts	1 C/O
Contacts material	Cadmium free
nominal output current	5 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

delay at power up	0.05 s
Hysteresis	5 % threshold
Measurement accuracy	+/- 10 % of the full scale value
Repeat accuracy	+/- 0.5 % input and measurement circuit +/- 0.5 % time delay
Measurement error	+/- 0.1 %/°C with temperature variation < +/- 1 % over the whole range with voltage variation
Input frequency	0.0017...20 Hz
Response time	15 ms max (on crossing the threshold)
Polarity	Reversible polarity on DC supply
Threshold setting	10...100 %
supply voltage for sensor	11.5...12.5 V
Maximum supply current for sensors	40 mA < 24 V AC 77 °F (25 °C) 40 mA < 24 V DC 77 °F (25 °C) 50 mA 24...240 V AC 50 mA 24...240 V DC
Impulse duration	>= 5 ms high state >= 5 ms low state
Input compatibility	3-wire sensor (E1) PNP or NPN, 12 V, 50 mA NAMUR sensor (E2), 12 V, 1.5 kOhm Voltage input (E1), 0...30 V, 9.5 kOhm >= 4.5 V <= 1 V Volt-free contact input (E1), 12 V, 9.5 kOhm
Marking	CE : EMC 89/336/EEC CE : 73/23/EEC
Overvoltage category	III conforming to IEC 60664-1
Insulation resistance	> 500 MOhm 500 V DC between supply and relay output IEC 60255-5 > 500 MOhm 500 V DC between measurement and relay output IEC 60664-1 > 1 MOhm 500 V DC between supply and measurement IEC 60255-5 > 500 MOhm 500 V DC between supply and relay output IEC 60664-1 > 500 MOhm 500 V DC between measurement and relay output IEC 60255-5 > 1 MOhm 500 V DC between supply and measurement IEC 60664-1
[Ui] rated insulation voltage	250 V IEC 60664-1
operating voltage tolerance	- 15 % + 10 % Un
Supply frequency	50/60 Hz +/- 10 %
Operating position	Any position without derating
Connections - terminals	Screw terminals, 1 x 0.5...1 x 4 mm ² AWG 20...AWG 11) solid without cable end Screw terminals, 2 x 0.5...2 x 2.5 mm ² AWG 20...AWG 14) solid without cable end Screw terminals, 1 x 0.2...1 x 2.5 mm ² AWG 24...AWG 12) flexible with cable end Screw terminals, 2 x 0.2...2 x 1.5 mm ² AWG 24...AWG 16) flexible with cable end
Tightening torque	5.3...8.9 lbf.in (0.6...1 N.m) IEC 60947-1
Housing material	Self-extinguishing plastic
Status LED	1 LED Green power ON 1 LED Yellow inhibit 1 LED Yellow relay (R)
Mounting support	35 mm symmetrical DIN rail conforming to IEC 60715
Electrical durability	100000 cycles
Mechanical durability	30000000 cycles
Operating rate	<= 360 operations/hour full load
Control Type	Without test button

Environment

Immunity to microbreaks	50 ms
Electromagnetic compatibility	Emission standard for industrial environments IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments IEC 61000-6-3 Immunity for industrial environments NF EN/IEC 61000-6-2
Standards	NF EN 60255-6 IEC 60255-6
Product Certifications	C-tick GOST UL GL CSA
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative humidity	95 % 131 °F (55 °C) IEC 60068-2-30
Vibration resistance	0.35 mm (f= 5...57.6 Hz) conforming to IEC 60068-2-6/IEC 60255-21-1 1 gn (f= 57.6...150 Hz) conforming to IEC 60068-2-6/IEC 60255-21-1
Shock resistance	15 gn 11 ms IEC 60255-21-1
IP degree of protection	IP20 IEC 60529 terminals) IP30 IEC 60529 casing)
Pollution degree	3 IEC 60664-1
Dielectric test voltage	2 kV AC 50 Hz
Non-dissipating shock wave	4 kV

Ordering and shipping details

Category	US10CP222380
Discount Schedule	0CP2
GTIN	3389119405256
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	1.73 in (4.4 cm)
Package 1 Width	2.91 in (7.4 cm)
Package 1 Length	3.70 in (9.4 cm)
Package weight(Lbs)	4.6 oz (130.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	48
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	15.831 lb(US) (7.181 kg)

Contractual warranty

Warranty

18 months



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO₂ eq, Total Life cycle) **59**

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard **Yes**

Packaging without single use plastic **Yes**

[EU RoHS Directive](#) **Pro-active compliance (Product out of EU RoHS legal scope)**

SCIP Number **5e3fdf99-611b-4d07-ad17-6eba84ab488b**

California proposition 65 **WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](#)**

Use Again

Repack and remanufacture


Circularity Profile [End of Life Information](#)

Take-back **No**

Dimensions Drawings

Speed Control Relays

Dimensions and Mounting




Connections and Schema

Speed Control Relays

Wiring Diagrams


Contact input



(2) A quick-blow fuse or circuit-breaker.

S2 Inhibit - Reset


Namur proximity sensor input



(2) A quick-blow fuse or circuit-breaker.

S2 Inhibit - Reset


NPN/PNP sensor input



(2) A quick-blow fuse or circuit-breaker.

S2 Inhibit - Reset

0-30 V voltage input




(2) A quick-blow fuse or circuit-breaker.

S2 Inhibit - Reset


Technical Description

Function Diagrams**Underspeed Control**


Without memory ("No Memory" mode)




With memory ("Memory" mode)




With inhibition by S2 ("Inhib./S2" mode)

**Overspeed Control**

Without memory ("No Memory" mode)



With memory ("Memory" mode)


**Legend**

Ti Starting inhibition time delay

U_n Supply voltage
V Monitored speed
H Hysteresis
V_s Overspeed threshold
S2 Inhibition external contact
In LED indicating the inhibition status
(1) Power break to reset the output relay
(2) S2 contact closure to make the output relay return to normal state
11-12/11-14 Output relay connections
Relay status: black color = energized.


NOTE: In "Memory" mode, the relay opens after the time delay and stays in that position when crossing of the threshold is detected. The power supply voltage must be switched off to reset the product.

With inhibition by S2 ("Inhib./S2" mode)



Technical Illustration

Dimensions




Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony Control Relay



Offer Marketing Illustration

Product benefits / Features

Features

Harmony Control Relay



Wide monitoring parameters (phase, current, voltage, liquid level, frequency, speed, temperature, and pump control) to meet your application needs.

True RMS measurement that minimizes the possibility of unexpected trips from highly polluted networks (except RM17TG and RM22TG)

Experience unprecedented accuracy, predictive maintenance, and superior security.

Green Premium labelled products, promising compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ product

Compatible with a wide range of applications, such as hoisting, packaging, lifts, textile, pumping, and water.

Image of product / Alternate images

Alternative





