

# Product data sheet

Specifications



logic controller, Modicon M221, 16 IO, 9 DI, 7 DO, transistor, PNP, Ethernet

TM221CE16T

## Main

|                           |   |
|---------------------------|---|
| Range of product          | Modicon M221  |
| Product or component type | Logic controller  |
| [Us] rated supply voltage | 24 V DC   |
| Discrete input number     | 9, discrete input 4 fast input conforming to IEC 61131-2 Type 1 |
| Analogue input number     | 2 at 0...10 V   |
| Discrete output type      | Transistor  |
| Discrete output number    | 7 transistor 2 fast output                                      |
| Discrete output voltage   | 24 V DC   |
| Discrete output current   | 0.5 A   |

## Complementary

|  |  |
|--|--|
| Discrete I/O number                    | 16   |
| Maximum number of I/O expansion module | 4 (local I/O-Architecture)<br>11 (remote I/O-Architecture)   |
| Supply voltage limits                  | 20.4...28.8 V  |
| Inrush current                         | 35 A   |
| Maximum power consumption in W         | 11 W at 24 V (with max number of I/O expansion module)<br>4.6 W at 24 V (without I/O expansion module) |
| Power supply output current            | 0.325 A 5 V for expansion bus<br>0.15 A 24 V for expansion bus   |
| Discrete input logic                   | Sink or source (positive/negative)   |
| Discrete input voltage                 | 24 V   |
| Discrete input voltage type            | DC   |
| Analogue input resolution              | 10 bits  |
| LSB value                              | 10 mV  |
| Conversion time                        | 1 ms per channel + 1 controller cycle time for analogue input analog input                             |
| Permitted overload on inputs           | +/- 30 V DC for 5 min (maximum) for analog input<br>+/- 13 V DC (permanent) for analog input           |
| Voltage state 1 guaranteed             | >= 15 V for input  |
| Voltage state 0 guaranteed             | <= 5 V for input   |
| Discrete input current                 | 7 mA for discrete input<br>5 mA for fast input   |
| Input impedance                        | 3.4 kOhm for discrete input<br>100 kOhm for analog input<br>4.9 kOhm for fast input                    |

|  |   |
|--|---|
| <b>Response time</b>                     | 35 µs turn-off, I2...I5 terminal(s) for input<br>5 µs turn-on, I0, I1, I6, I7 terminal(s) for fast input<br>35 µs turn-on, other terminals terminal(s) for input<br>5 µs turn-off, I0, I1, I6, I7 terminal(s) for fast input<br>100 µs turn-off, other terminals terminal(s) for input<br>5 µs turn-on, turn-off, Q0...Q1 terminal(s) for output<br>50 µs turn-on, turn-off, Q2...Q3 terminal(s) for output<br>300 µs turn-on, turn-off, other terminals terminal(s) for output |
| <b>Configurable filtering time</b>       | 0 ms for input<br>3 ms for input<br>12 ms for input   |
| <b>Discrete output logic</b>             | Positive logic (source)   |
| <b>Maximum current per output common</b> | 3.5 A   |
| <b>Output frequency</b>                  | 100 kHz for fast output (PWM/PLS mode) at Q0...Q1<br>5 kHz for output at Q2...Q3<br>0.1 kHz for output at Q4...Q6   |
| <b>Absolute accuracy error</b>           | +/- 1 % of full scale for analog input  |
| <b>Maximum leakage current</b>           | 0.1 mA for transistor output  |
| <b>Maximum voltage drop</b>              | <1 V  |
| <b>Mechanical durability</b>             | 20000000 cycles for transistor output   |
| <b>Maximum tungsten load</b>             | <12 W for output and fast output  |
| <b>Protection type</b>                   | Overload and short-circuit protection at 1 A  |
| <b>Reset time</b>                        | 1 s automatic reset   |
| <b>Memory capacity</b>                   | 256 kB for user application and data RAM with 10000 instructions<br>256 kB for internal variables RAM   |
| <b>Data backed up</b>                    | 256 kB built-in flash memory for backup of application and data   |
| <b>Data storage equipment</b>            | 2 GB SD card (optional)   |
| <b>Battery type</b>                      | BR2032 or CR2032X lithium non-rechargeable  |
| <b>Backup time</b>                       | 1 year at 25 °C (by interruption of power supply)   |
| <b>Execution time for 1 KInstruction</b> | 0.3 ms for event and periodic task  |
| <b>Execution time per instruction</b>    | 0.2 µs Boolean  |
| <b>Exct time for event task</b>          | 60 µs response time   |
| <b>Maximum size of object areas</b>      | 512 %M memory bits<br>255 %C counters<br>512 %KW constant words<br>255 %TM timers<br>8000 %MW memory words  |
| <b>Realtime clock</b>                    | With  |
| <b>Clock drift</b>                       | <= 30 s/month at 25 °C  |
| <b>Regulation loop</b>                   | Adjustable PID regulator up to 14 simultaneous loops  |
| <b>Positioning functions</b>             | Position PTO 2 axe(s)pulse/direction mode (100 kHz)<br>Position PTO 1 axe(s)CW/CCW mode (100 kHz)   |
| <b>Function available</b>                | PWM<br>Frequency generator<br>PLS   |
| <b>Counting input number</b>             | 4 fast input (HSC mode) at 100 kHz 32 bits  |
| <b>counter function</b>                  | Single phase<br>A/B<br>Pulse/direction  |
| <b>Integrated connection type</b>        | USB port with mini B USB 2.0 connector<br>Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface<br>Ethernet with RJ45 connector   |

|   |   |
|---|---|
| <b>Supply</b>                                 | (serial)serial link supply: 5 V, <200 mA  |
| <b>Transmission rate</b>                      | 1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485<br>1.2...115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232<br>480 Mbit/s for USB   |
| <b>Communication port protocol</b>            | USB port: USB - SoMachine-Network<br>Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network<br>Ethernet   |
| <b>Port Ethernet</b>                          | 10BASE-T/100BASE-TX 1 port with 100 m copper cable  |
| <b>Communication service</b>                  | Modbus TCP client<br>DHCP client<br>Modbus TCP slave device<br>Modbus TCP server<br>Ethernet/IP adapter   |
| <b>Local signalling</b>                       | 1 LED (green) for PWR<br>1 LED (green) for RUN<br>1 LED (red) for module error (ERR)<br>1 LED (green) for SD card access (SD)<br>1 LED (red) for BAT<br>1 LED per channel (green) for I/O state<br>1 LED (green) for SL<br>Ethernet network activity (green) for ACT<br>Ethernet network link (yellow) for Link (Link Status) |
| <b>Electrical connection</b>                  | removable screw terminal block for inputs<br>removable screw terminal block for outputs<br>terminal block, 3 terminal(s) for connecting the 24 V DC power supply connector, 4 terminal(s) for analogue inputs<br>Mini B USB 2.0 connector for a programming terminal  |
| <b>Maximum cable distance between devices</b> | Shielded cable: <10 m for fast input<br>Unshielded cable: <30 m for output<br>Unshielded cable: <30 m for digital input<br>Unshielded cable: <1 m for analog input<br>Shielded cable: <3 m for fast output  |
| <b>Insulation</b>                             | Between input and internal logic at 500 V AC<br>Between fast input and internal logic at 500 V AC<br>Non-insulated between inputs<br>Between output and internal logic at 500 V AC<br>Non-insulated between analogue input and internal logic<br>Non-insulated between analogue inputs  |
| <b>Marking</b>                                | CE  |
| <b>Mounting support</b>                       | Top hat type TH35-15 rail conforming to IEC 60715<br>Top hat type TH35-7.5 rail conforming to IEC 60715<br>plate or panel with fixing kit   |
| <b>Height</b>                                 | 90 mm   |
| <b>Depth</b>                                  | 70 mm   |
| <b>Width</b>                                  | 95 mm   |
| <b>Product weight</b>                         | 0.346 kg  |

## Environment

|                               |   |
|-------------------------------|---|
| <b>Standards</b>              | IEC 61131-2<br>UL 508<br>CAN/CSA C22.2 No. 213<br>IACS E10<br>ANSI/ISA 12-12-01 |
| <b>Product certifications</b> | EAC<br>DNV-GL<br>RCM<br>ABS<br>cULus<br>LR<br>CE<br>UKCA<br>cULus HazLoc        |

|  |   |
|--|---|
| <b>Environmental characteristic</b>          | Ordinary and hazardous location   |
| <b>Resistance to electrostatic discharge</b> | 8 kV in air conforming to IEC 61000-4-2<br>4 kV on contact conforming to IEC 61000-4-2  |
| <b>Resistance to electromagnetic fields</b>  | 10 V/m 80 MHz...1 GHz conforming to IEC 61000-4-3<br>3 V/m 1.4 GHz...2 GHz conforming to IEC 61000-4-3<br>1 V/m 2...2.7 GHz conforming to IEC 61000-4-3   |
| <b>Resistance to magnetic fields</b>         | 30 A/m 50/60 Hz conforming to IEC 61000-4-8   |
| <b>Resistance to fast transients</b>         | 2 kV (power lines) conforming to IEC 61000-4-4<br>2 kV (relay output) conforming to IEC 61000-4-4<br>1 kV (I/O) conforming to IEC 61000-4-4<br>1 kV (Ethernet line) conforming to IEC 61000-4-4<br>1 kV (serial link) conforming to IEC 61000-4-4   |
| <b>Surge withstand</b>                       | 2 kV power lines (AC) common mode conforming to IEC 61000-4-5<br>2 kV relay output common mode conforming to IEC 61000-4-5<br>1 kV I/O common mode conforming to IEC 61000-4-5<br>1 kV shielded cable common mode conforming to IEC 61000-4-5<br>0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5<br>1 kV power lines (AC) differential mode conforming to IEC 61000-4-5<br>1 kV relay output differential mode conforming to IEC 61000-4-5<br>0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5   |
| <b>Resistance to conducted disturbances</b>  | 10 V 0.15...80 MHz conforming to IEC 61000-4-6<br>3 V 0.1...80 MHz conforming to Marine specification (LR, ABS, DNV, GL)<br>10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)   |
| <b>Electromagnetic emission</b>              | Conducted emissions - test level: 79 dB $\mu$ V/m QP/66 dB $\mu$ V/m AV ( power lines (AC)) at 0.15...0.5 MHz conforming to IEC 55011<br>Conducted emissions - test level: 73 dB $\mu$ V/m QP/60 dB $\mu$ V/m AV ( power lines (AC)) at 0.5...300 MHz conforming to IEC 55011<br>Conducted emissions - test level: 120...69 dB $\mu$ V/m QP ( power lines) at 10...150 kHz conforming to IEC 55011<br>Conducted emissions - test level: 63 dB $\mu$ V/m QP ( power lines) at 1.5...30 MHz conforming to IEC 55011<br>Radiated emissions - test level: 40 dB $\mu$ V/m QP class A ( 10 m) at 30...230 MHz conforming to IEC 55011<br>Conducted emissions - test level: 79...63 dB $\mu$ V/m QP ( power lines) at 150...1500 kHz conforming to IEC 55011<br>Radiated emissions - test level: 47 dB $\mu$ V/m QP class A ( 10 m) at 200...1000 MHz conforming to IEC 55011 |
| <b>Immunity to microbreaks</b>               | 10 ms   |
| <b>Ambient air temperature for operation</b> | -10...55 °C (horizontal installation)<br>-10...35 °C (vertical installation)  |
| <b>Ambient air temperature for storage</b>   | -25...70 °C   |
| <b>Relative humidity</b>                     | 10...95 %, without condensation (in operation)<br>10...95 %, without condensation (in storage)  |
| <b>IP degree of protection</b>               | IP20 with protective cover in place   |
| <b>Pollution degree</b>                      | <= 2  |
| <b>Operating altitude</b>                    | 0...2000 m  |
| <b>Storage altitude</b>                      | 0...3000 m  |
| <b>Vibration resistance</b>                  | 3.5 mm at 5...8.4 Hz on symmetrical rail<br>3.5 mm at 5...8.4 Hz on panel mounting<br>1 gn at 8.4...150 Hz on symmetrical rail<br>1 gn at 8.4...150 Hz on panel mounting  |
| <b>Shock resistance</b>                      | 147 m/s <sup>2</sup> for 11 ms  |

## Packing Units

|                                     |         |
|-------------------------------------|---------|
| <b>Unit Type of Package 1</b>       | PCE     |
| <b>Number of Units in Package 1</b> | 1       |
| <b>Package 1 Height</b>             | 10.6 cm |

|                              |          |
|------------------------------|----------|
| Package 1 Width              | 14.0 cm  |
| Package 1 Length             | 13.9 cm  |
| Package 1 Weight             | 300.0 g  |
| Unit Type of Package 2       | S04      |
| Number of Units in Package 2 | 20       |
| Package 2 Height             | 30 cm    |
| Package 2 Width              | 40 cm    |
| Package 2 Length             | 60 cm    |
| Package 2 Weight             | 6.983 kg |
| Unit Type of Package 3       | P12      |
| Number of Units in Package 3 | 240      |
| Package 3 Height             | 105.0 cm |
| Package 3 Width              | 120.0 cm |
| Package 3 Length             | 80.0 cm  |
| Package 3 Weight             | 156 kg   |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

## Environmental footprint

|                                  |   |
|----------------------------------|---|
| Total lifecycle Carbon footprint | 107   |
| Environmental Disclosure         | <a href="#">Product Environmental Profile</a> |

## Use Better

### Materials and Substances

|  |  |
|--|--|
| Packaging made with recycled cardboard | Yes  |
| Packaging without single use plastic   | Yes  |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)   |
| SCIP Number                            | C9e48184-76ce-4d1a-abc2-18108c652781   |
| REACH Regulation                       | <a href="#">REACH Declaration</a>  |
| California proposition 65              | <b>WARNING:</b> This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="#">www.P65Warnings.ca.gov</a> |
| PVC free                               | Yes  |


## Use Again

### Repack and remanufacture


|                                 |   |
|---------------------------------|---|
| End of life manual availability | <a href="#">End of Life Information</a>   |
| Take-back                       | No  |
| WEEE Label                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |


## Dimensions Drawings

## Dimensions




## Mounting and Clearance




Mounting on a Rail


**Direct Mounting on a Panel Surface**

(1) Install a mounting strip


**Mounting Hole Layout**

---

**Mounting****Correct Mounting Position****Acceptable Mounting Position****Incorrect Mounting Position**


**Clearance**

## Connections and Schema

Digital Inputs

- (\*) Type T fuse
- (A) Sink wiring (positive logic).
- (B) Source wiring (negative logic).


## Connection of the Fast Inputs




I0, I1, I6, I7

**Transistor Outputs**



---



(\*) Type T fuse


**Connection of the Fast Outputs**

Q0, Q1


Analog Inputs

The (-) poles are connected internally.

| Pin | Wire Color |
|-----|------------|
| 0 V | Black      |
| AN1 | Red        |
| 0 V | Black      |
| AN0 | Red        |


**Ethernet Connection**


| Pin N° | Signal |
|--------|--------|
| 1      | TD+    |
| 2      | TD-    |
| 3      | RD+    |
| 4      | -      |
| 5      | -      |
| 6      | RD-    |
| 7      | -      |
| 8      | -      |



**USB Mini-B Connection**

---




**SL1 Connection**

SL1

| N ° | RS 232 | RS 485 |
|-----|--------|--------|
| 1   | RxD    | N.C.   |
| 2   | TxD    | N.C.   |
| 3   | RTS    | N.C.   |
| 4   | N.C.   | D1     |
| 5   | N.C.   | D0     |
| 6   | CTS    | N.C.   |
| 7   | N.C.*  | 5 Vdc  |
| 8   | Common | Common |

N.C.: not connected


\* : 5 Vdc delivered by the controller. Do not connect.



## Performance Curves

Derating Curves


## Embedded Digital Inputs (No Cartridge)



X : Ambient temperature


Y : Input simultaneous ON ratio

## Embedded Digital Inputs (with Cartridge)




X : Ambient temperature

Y : Input simultaneous ON ratio

**Derating Curves****Embedded Digital Outputs (No Cartridge)**

X : Ambient temperature

Y : Output simultaneous ON ratio

**Embedded Digital Outputs (with Cartridge)**

X : Ambient temperature

Y : Output simultaneous ON ratio