


## 20V 7A<sub>RMS</sub> VBUS Over-Voltage Protection Load Switch

### Features

- 3V to 24V Operating Voltage Range
- 29V Abs. Max. Rating at VBUS and VSYS
- 7A Continuous Current Rating
  - ▶ 18A Pulse Current Rating (duration  $P_D$  limited)
- 14mΩ typ. On-Resistance from VBUS to VSYS
- Soft-Start (SS) Limits Inrush Current
- Over-Voltage Protection (OVP) at VBUS
  - ▶ 24V Internally Fixed
  - ▶ 4V to 24V External Resistor Programmable
- “Ideal Diode” Reverse Current Protection (RCP) for KTS1655A/B only
  - ▶ 15mV Forward Voltage and 15µs Fast Recovery
- Bi-directional Mode when enabled for KTS1655C/D only
- Over-Current Protection (OCP) at VBUS & VSYS
- Short-Circuit Protection (SCP)
- Over-Temperature Protection (OTP)
- Auto-Retry after All Faults
- EN or  $\overline{EN}$  Enable Logic Input Versions
- Support 1.2V GPIO Voltage
- ACOK Open-Drain Power Good Flag
- -40°C to 85°C Operating Temperature Range
- 20-bump WLCSP 2.485 x 2.228mm (0.5mm pitch)

### Typical Application



### Brief Description

KTS1655 is a low-resistance, high-current load switch with soft-start, over-voltage protection, reverse-current blocking, over-current protection, short-circuit protection, and over-temperature protection. It is optimized to protect systems with USB Type-C PD ports and barrel connectors that sink up to 140W at 20V and must withstand up to 29V on VBUS.

KTS1655A/B has automatic reverse-current blocking feature which acts as an “ideal diode” and isolates VBUS when charging or powering the system via another port. KTS1655C/D supports bi-directional mode during operation. Soft-start limits inrush current when turning on with large capacitors at the output. An ACOK flag indicates when power is good.

KTS1655 is packaged in advanced, fully “green” compliant, 2.485 x 2.228mm, 20-bump Wafer-Level Chip-Scale Package (WLCSP).

### Applications


- Desktop, Notebooks, Netbooks, Ultra-Books, Tablets
- Docking Stations, Monitors, Accessories

## Ordering Information

Part Number	Marking <sup>1</sup>	Enable Polarity	Switch Mode	Package
KTS1655AEIAE-TA <sup>2</sup>	__YWZNAABB	EN	Uni-directional with RCP	WLCSP-20
KTS1655BEIAE-TA	VMYWZNAABB	EN	Uni-directional with RCP	WLCSP-20
KTS1655CEIAE-TA <sup>2</sup>	__YWZNAABB	EN	Bi-directional without RCP	WLCSP-20
KTS1655DEIAE-TA <sup>2</sup>	VNYWZNAABB	EN	Bi-directional without RCP	WLCSP-20

## Pinout Diagram

WLCSP54-20



20-bump 2.485mm x 2.228mm x 0.555mm  
WLCSP Package, 0.5mm pitch

### Top Mark

XX = Device Code, YW = Date Code, Z = Serial Number, N = Wafer ID  
AABB = Axis Coordinates

## Pin Descriptions

Pin #	Name	Function
A1 to B4	VSYS	Power Switch System-Side Connection – connect to system internal power rail.
C1 to D4	VBUS	Power Switch Port-Side Connection – connect to VBUS on USB power port.
E1	EN	Enable – active-low logic input (KTS1655A/C)
	EN	Enable – active-high logic input (KTS1655B/D)
E2	OVLO	External OVLO Adjustment – connect to GND to use the internally fixed OVLO threshold. Connect an external resistive voltage divider from VBUS to OVLO to GND to set an adjustable the OVLO threshold.
E3	ACOK	Power Good Flag – active-low, open-drain logic output. Connect to GND or leave floating if unused.
E4	GND	Ground

1. VM or VN = Device Code, YW = Date Code, Z = Serial Number, N = Wafer ID, AABB = Axis Coordinates.  
2. Consult Kinetic Technologies authorized representative for availability.

## Absolute Maximum Ratings<sup>3</sup>

Symbol	Description	Value	Units
$V_{BUS}$	VBUS to GND (continuous)	-0.3 to 29	V
	VBUS to GND (during IEC61000-4-5 surge event with external TVS)	-5 to 36	
$V_{SYS}$	VSYS to GND	-0.3 to 29	V
$V_{BUS-SYS}$	VBUS to VSYS	-29 to 29	V
$V_{EN}, V_{\bar{EN}}$	EN, $\bar{EN}$ to GND	-0.3 to 29	V
$V_{OVLO}$	OVLO to GND	-0.3 to $V_{VBUS}$	V
$V_{ACOK}$	ACOK to GND	-0.3 to 6	V
$I_{SW}$	Maximum Switch Current (continuous)	7	A
	Peak Switch Current (duration is $P_D$ limited)	18	
$T_J$	Operating Temperature Range	-40 to 150	°C
$T_S$	Storage Temperature Range	-55 to 150	°C
$T_{LEAD}$	Maximum Soldering Temperature (at leads, 10 sec)	260	°C

## ESD Ratings<sup>4</sup>

Symbol	Description	Value	Units
$V_{ESD\_HBM}$	JEDEC JS-001-2017 Human Body Model (all pins)	±2	kV

## Thermal Capabilities<sup>5</sup>

Symbol	Description	Value	Units
$\Theta_{JA}$	Thermal Resistance – Junction to Ambient	40.6	°C/W
$P_D$	Maximum Power Dissipation at $T_A \leq 25^\circ\text{C}$ ( $T_J = 125^\circ\text{C}$ )	2.46	W
$\Delta P_D/\Delta T$	Derating Factor Above $T_A = 25^\circ\text{C}$	-24.6	mW/°C

---

3. Stresses above those listed in Absolute Maximum Ratings may cause permanent damage to the device. Functional operation at conditions other than the operating conditions specified is not implied. Only one Absolute Maximum rating should be applied at any one time.
4. ESD Ratings conform to JEDEC and IEC industry standards. Some pins may actually have higher performance.
5. Junction to Ambient thermal resistance is highly dependent on PCB layout. Values are based on thermal properties of the device when soldered to an EV board.

## Recommended Operating Conditions<sup>6</sup>

Symbol	Description	Value	Units
$V_{BUS}$	Supply Voltage Operating Range	3 to 24	V
$V_{SYS}$	Output Voltage Range	0 to 24	V
$V_{ACOK}$	Power Good Flag Output Voltage	0 to 5.5	V
$V_{OVLO}$	OVLO Adjust Input Bias Voltage		V
$V_{EN}, V_{\bar{EN}}$	Enable Logic Input Voltage	0 to 24	V
$C_{BUS}$	Input Capacitance	1 to 10	$\mu$ F
		35	V
$C_{SYS}$	Output Capacitance	10 to 1000	$\mu$ F
		25	V
$T_A$	Ambient Operating Temperature Range	-40 to 85	°C
$T_J$	Die Junction Operating Temperature Range	-40 to 125	°C

## Electrical Characteristics<sup>7</sup>

Unless otherwise noted, the *Min* and *Max* specs are applied over the full operation temperature range of  $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  and  $V_{BUS} = 3\text{V}$  to  $24\text{V}$  or  $V_{SYS} = 3\text{V}$  to  $24\text{V}$ . Typical values are specified at  $T_A = +25^{\circ}\text{C}$  with  $V_{BUS} = 5\text{V}$  or  $V_{SYS} = 5\text{V}$ .

### Supply Specifications

Symbol	Description	Conditions	Min	Typ	Max	Units
$V_{BUS}$	Input Voltage Operating Range		3		24	V
$V_{SYS}$	Output Voltage Operating Range		3		24	V
$V_{UVLO}$	Under-Voltage Lockout	$V_{BUS}$ rising threshold		2.7	2.95	V
		$V_{SYS}$ rising threshold (KTS1655C/D)		2.7	2.95	V
		Hysteresis	200			mV
$I_Q$	No-Load Supply Current (Enabled)	$V_{BUS} = 5\text{V}, V_{SYS} = \text{open}$	190			$\mu\text{A}$
		$V_{BUS} = 20\text{V}, V_{SYS} = \text{open}$	240			$\mu\text{A}$
	No-Load Supply Current (Enabled, KTS1655C/D in $I_{\text{SOURCE}}$ Mode)	$V_{SYS} = 5\text{V}, V_{BUS} = \text{open}$	190			$\mu\text{A}$
		$V_{SYS} = 20\text{V}, V_{BUS} = \text{open}$	240			$\mu\text{A}$
$I_{SHDN}$	Shutdown Supply Current	$V_{BUS} = 5\text{V}, V_{SYS} = \text{open}$	1			$\mu\text{A}$
		$V_{BUS} = 20\text{V}, V_{SYS} = \text{open}$	2.6			$\mu\text{A}$
	Shutdown Supply Current (KTS1655C/D in $I_{\text{SOURCE}}$ Mode)	$V_{SYS} = 5\text{V}, V_{BUS} = \text{open}$	1			$\mu\text{A}$
		$V_{SYS} = 20\text{V}, V_{BUS} = \text{open}$	2.6			$\mu\text{A}$
$I_{SYS\_RCP}$	Output Supply Current in RCP	Enabled, $V_{BUS} = 0\text{V}, V_{SYS} = 5\text{V}$ (KTS1655A/B)	90			$\mu\text{A}$

(continued next page)

6. The recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Kinetic does not recommend exceeding them or designing to Absolute Maximum Rating.
7. Device is guaranteed to meet performance specifications over the  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$  operating temperature range by design, characterization, and correlation with statistical process controls.

## Electrical Characteristics (continued)<sup>8</sup>

Unless otherwise noted, the *Min* and *Max* specs are applied over the full operation temperature range of  $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  and  $V_{\text{BUS}} = 3\text{V}$  to  $24\text{V}$  or  $V_{\text{SYS}} = 3\text{V}$  to  $24\text{V}$ . Typical values are specified at  $T_A = +25^{\circ}\text{C}$  with  $V_{\text{BUS}} = 5\text{V}$  or  $V_{\text{SYS}} = 5\text{V}$ .

### Logic Pin Specifications (EN, $\overline{\text{EN}}$ , $\overline{\text{ACOK}}$ )

Symbol	Description	Conditions	Min	Typ	Max	Units
$V_{\text{IH}}$	Input Logic High (EN, $\overline{\text{EN}}$ )		0.8			V
$V_{\text{IL}}$	Input Logic Low (EN, $\overline{\text{EN}}$ )				0.3	V
$R_{\text{I\_PD}}$	Input Logic Pull-Down (EN)			1		$\text{M}\Omega$
$I_{\text{I\_LK}}$	Input Logic Leakage (EN)	$V_I = 5\text{V}$	-1		1	$\mu\text{A}$
		$V_I = 20\text{V}$	-1		1	$\mu\text{A}$
$V_{\text{OL}}$	Output Logic Low ( $\overline{\text{ACOK}}$ )	$I_{\text{O\_SINK}} = 1\text{mA}$		0.01	0.2	V
$I_{\text{O\_LK}}$	Output Logic High-Z Leakage ( $\overline{\text{ACOK}}$ )	$V_O = 5\text{V}$	-1		1	$\mu\text{A}$

### Switch Specifications

Symbol	Description	Conditions	Min	Typ	Max	Units
$R_{\text{ON}}$	Switch On-Resistance	$T_A = +25^{\circ}\text{C}$	$V_{\text{BUS}} = 5\text{V}$		14	18
			$V_{\text{BUS}} = 20\text{V}$		14	18
	Switch On-Resistance (KTS1655C/D in $I_{\text{SOURCE}}$ Mode)	$T_A = +25^{\circ}\text{C}$	$V_{\text{SYS}} = 5\text{V}$		14	18
			$V_{\text{SYS}} = 20\text{V}$		14	18
$I_{\text{BUS\_OFF}}$	Switch Off-Leakage at $V_{\text{BUS}}$	Shutdown, $V_{\text{BUS}} = 5\text{V}$ , $V_{\text{SYS}} = 0\text{V}$		1		$\mu\text{A}$
		Shutdown, $V_{\text{BUS}} = 20\text{V}$ , $V_{\text{SYS}} = 0\text{V}$		2.6		
$I_{\text{SYS\_OFF}}$	Switch Off-Leakage at $V_{\text{SYS}}$	Shutdown, $V_{\text{BUS}} = 0\text{V}$ , $V_{\text{SYS}} = 5\text{V}$		1		$\mu\text{A}$
		Shutdown, $V_{\text{BUS}} = 0\text{V}$ , $V_{\text{SYS}} = 20\text{V}$		2.6		

(continued next page)

8. Device is guaranteed to meet performance specifications over the  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$  operating temperature range by design, characterization, and correlation with statistical process controls.

## Electrical Characteristics (continued)<sup>9</sup>

Unless otherwise noted, the *Min* and *Max* specs are applied over the full operation temperature range of  $T_J = -40^{\circ}\text{C}$  to  $+125^{\circ}\text{C}$  and  $V_{\text{BUS}} = 3\text{V}$  to  $24\text{V}$  or  $V_{\text{SYS}} = 3\text{V}$  to  $24\text{V}$ . Typical values are specified at  $T_A = +25^{\circ}\text{C}$  with  $V_{\text{BUS}} = 5\text{V}$  or  $V_{\text{SYS}} = 5\text{V}$ .

### Soft-Start (SS) Specifications (see Figure 1)

Symbol	Description	Conditions	Min	Typ	Max	Units
$t_{\text{DEB}}$	Soft-Start Debounce Time <sup>10</sup>	$R_L = 100\Omega$ , $C_{\text{VSY}} = 300\mu\text{F}$ , $V_{\text{BUS}} = 5\text{V}$		18		ms
		$R_L = 100 \Omega$ , $C_{\text{VBU}} = 10\mu\text{F}$ , $V_{\text{SYS}} = 5\text{V}$ (KTS1655C/D in $I_{\text{SOURCE}}$ Mode)		18		
$t_R$	Soft-Start $V_{\text{SYS}}$ Rising Slew-Rate Ramp Time <sup>11</sup>	$R_L = 10\Omega$ , $C_{\text{VSY}} = 300\mu\text{F}$ , $V_{\text{BUS}} = 5\text{V}$		3.2		ms
		$R_L = 100\Omega$ , $C_{\text{VSY}} = 300\mu\text{F}$ , $V_{\text{BUS}} = 20\text{V}$		3.1		
		$R_L = 100 \Omega$ , $C_{\text{VBU}} = 10\mu\text{F}$ , $V_{\text{SYS}} = 5\text{V}$ (KTS1655C/D in $I_{\text{SOURCE}}$ Mode)		2.3		
$I_{\text{LIM\_SS}}$	Soft-Start Current Limit	$V_{\text{BUS}} = 5\text{V}$ to $20\text{V}$		3.4		A
		$V_{\text{SYS}} = 5\text{V}$ to $20\text{V}$ (KTS1655C/D in $I_{\text{SOURCE}}$ Mode)		3.4		
$t_{\text{LIM\_SS}}$	Soft-Start Current Limit Done Time <sup>12</sup>	$V_{\text{BUS}} = 5\text{V}$ to $20\text{V}$		8		ms
		$V_{\text{SYS}} = 5\text{V}$ to $20\text{V}$ (KTS1655C/D in $I_{\text{SOURCE}}$ Mode)		8		
$t_{\text{ACOK}}$	Power Good Flag Delay after $t_{\text{LIM\_SS}}$ <sup>12</sup>	$V_{\text{BUS}}$ or $V_{\text{SYS}} = 5\text{V}$ to $20\text{V}$		3		ms
$t_{\text{DOFF}}$	Turn-Off Delay Time <sup>12</sup>		0		10	$\mu\text{s}$

9. Device is guaranteed to meet performance specifications over the  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$  operating temperature range by design, characterization, and correlation with statistical process controls.

10.  $t_{\text{DEB}}$  is time from  $\text{EN} = \text{H}$  and  $V_{\text{UVLO}} < V_{\text{BUS}} < V_{\text{OVP}}$  until  $V_{\text{OUT}} = 10\% * V_{\text{BUS}}$ .

11.  $t_R$  is time from  $V_{\text{SYS}} = 10\% * V_{\text{BUS}}$  until  $V_{\text{SYS}} = 90\% * V_{\text{BUS}}$ .

12. Guaranteed by design, characterization and statistical process control methods; not production tested.

## Electrical Characteristics (continued)<sup>13</sup>

Unless otherwise noted, the *Min* and *Max* specs are applied over the full operation temperature range of  $T_J = -40^\circ\text{C}$  to  $+125^\circ\text{C}$  and  $V_{\text{BUS}} = 3\text{V}$  to  $24\text{V}$  or  $V_{\text{SYS}} = 3\text{V}$  to  $24\text{V}$ . Typical values are specified at  $T_A = +25^\circ\text{C}$  with  $V_{\text{BUS}} = 5\text{V}$  or  $V_{\text{SYS}} = 5\text{V}$ .

### Over-Voltage Protection (OVP) Specifications

Symbol	Description	Conditions	Min	Typ	Max	Units
$V_{\text{OVP}}$	Internally Fixed Over-Voltage Protection	$V_{\text{BUS}}$ rising OVP threshold	23	24	25	V
		Hysteresis, $V_{\text{OVLO}} = 0\text{V}$		800		mV
$t_{\text{OVP}}$	OVP Response Time <sup>12, 14</sup>	$R_L = 100\Omega$ , $C_{\text{SYS}} = 0\mu\text{F}$ , $V_{\text{BUS}} > V_{\text{OVP}}$ , $V_{\text{OVLO}} = 0\text{V}$		90		ns
$t_{\text{OVP\_REC}}$	OVP Recovery Time <sup>12, 15</sup>			$t_{\text{DEB}} + t_R$		ms
$V_{\text{OVLO}}$	Externally Adjustable Over-Voltage Lockout	$V_{\text{OVLO}}$ enable threshold	0.15	0.25	0.35	V
		$V_{\text{OVLO}}$ rising OVP threshold	1.15	1.22	1.29	V
		Hysteresis		25		mV
$t_{\text{OVLO}}$	OVLO Response Time <sup>12, 16</sup>	$R_L = 100\Omega$ , $C_{\text{SYS}} = 0\mu\text{F}$		300		ns
$t_{\text{OVLO\_REC}}$	OVLO Recovery Time <sup>12</sup>			$t_{\text{DEB}} + t_R$		ms

### Reverse-Current Protection (RCP) Specifications (KTS1655A/B only)

Symbol	Description	Conditions	Min	Typ	Max	Units
$V_{\text{RCP}}$	RCP Droop Regulation Voltage	$V_{\text{RCP}} = V_{\text{BUS}} - V_{\text{SYS}}$ , $I_{\text{SYS}} = 100\text{mA}$	8	15	22	mV
$t_{\text{RCP\_REC}}$	RCP Fast Recovery Time <sup>12, 17</sup>			15		μs

### Over-Current Protection (OCP) Specifications

Symbol	Description	Conditions	Min	Typ	Max	Units
$I_{\text{OCP}}$	Over-Current Threshold <sup>12</sup>		21	28		A
$t_{\text{OCP}}$	OCP Response Time <sup>12, 18</sup>			100		ns
$t_{\text{OCP\_REC}}$	OCP Recovery Time <sup>12</sup>			$t_{\text{DEB}} + t_R$		ms

### Over-Temperature Protection (OTP) Specifications

Symbol	Description	Conditions	Min	Typ	Max	Units
$t_{\text{OTP}}$	IC Junction Over-Temperature Protection <sup>12</sup>	$T_J$ rising threshold		145		°C
		Hysteresis		15		°C
$t_{\text{OTP\_REC}}$	OTP Recovery Time <sup>12</sup>			$t_{\text{DEB}} + t_R$		ms

13. Device is guaranteed to meet performance specifications over the  $-40^\circ\text{C}$  to  $+85^\circ\text{C}$  operating temperature range by design, characterization and correlation with statistical process controls.

14.  $t_{\text{OVP}}$  is time from when the input voltage  $> V_{\text{OVP}}$  until the output voltage stops rising.


15.  $t_{\text{OVP\_REC}}$  is time from when the input voltage  $< V_{\text{OVP}}$  until the output voltage reaches 90% of input voltage.

16.  $t_{\text{OVLO}}$  is time from  $V_{\text{OVLO}}$  rises above its OVP threshold until  $V_{\text{SYS}}$  stops rising.


17.  $t_{\text{RCP\_REC}}$  is time from  $V_{\text{BUS}} = V_{\text{SYS}} - V_{\text{RCP}}$  until switch turns back on. Before measuring, first raise  $V_{\text{SYS}}$  higher than  $V_{\text{BUS}} + 300\text{mV}$ .

18.  $t_{\text{OCP}}$  is time from when the switch current  $> I_{\text{OCP}}$  until switch turns off.


## Timing Diagrams




**Figure 1. UVLO, Soft-Start and Turn-Off Timing Diagram**




**Figure 2. OVP Timing Diagram**




**Figure 3. "Ideal Diode" RCP Timing Diagram with Fast Recovery (KTS1655A/B only)**



**Figure 4. OTP Timing Diagram**









**Figure 5. OCP and SCP Timing Diagram**



**Figure 6. UVLO, Soft-Start and Turn-Off Timing Diagram in  $I_{SOURCE}$  Mode (KTS1655C/D Only)**

## Typical Characteristics







$C_{IN} = 10\mu F$ ,  $C_{OUT} = 20\mu F$ , and  $T_A = +25^\circ C$  unless otherwise noted.



(continued next page)

## Typical Characteristics (continued)

$C_{IN} = 10\mu F$ ,  $C_{OUT} = 20\mu F$ , and  $T_A = +25^\circ C$  unless otherwise noted.



(continued next page)


## Typical Characteristics (continued)

$C_{IN} = 10\mu F$ ,  $C_{OUT} = 20\mu F$ , and  $T_A = +25^\circ C$  unless otherwise noted.

### RCP Response

#### KTS1655A/B Uni-directional with RCP


(VBUS = 5.1V,  $R_{cable} = 200m\Omega$ , Load =  $5\Omega$ , VSYS = 5V  $\rightarrow$  9V)



### RCP Fast Recovery


#### KTS1655A/B Uni-directional with RCP

(VBUS = 5.1V,  $R_{cable} = 200m\Omega$ , Load =  $5\Omega$ , VSYS = 9V  $\rightarrow$  5V)




### OCP Response

(VBUS = 20V, VSYS = 20V  $\rightarrow$  Short Circuit)




### SCP Response with Auto - Retry

(VBUS = 20V, VSYS = 20V  $\rightarrow$  Short Circuit)




### Surge Transient Response

(VBUS = 20V + 200V Surge with KTS1287-25)



### Surge Transient Response

(VBUS = 20V + 200V Surge with KTS1287-25)



## Functional Block Diagram




Figure 7. Functional Block Diagram

## Functional Description

The KTS1655 is a slew-rate controlled,  $14\text{m}\Omega$  (typ) low resistance MOSFET switch intended to be inserted between a power source and a load to isolate and protect against abnormal voltage and current conditions. Featuring slew-rate controlled soft-start and soft-start current limit to prevent excessive large inrush current, the KTS1655 also features several additional protection functions. These include input over-voltage protection, “ideal diode” reverse-current protection with fast recovery (KTS1655A/B only), output short-circuit protection, over-current protection, and over-temperature protection.

Operating from a wide input voltage range of 3V to 24V, the KTS1655A/B is optimized for USB Type-C Power Delivery (PD) current-sink applications that require essential protection and enhanced system reliability. While in the OFF state, the KTS1655 blocks voltages of up to 29V on the VBUS and VSYS pins and prevents current flow. While in the ON state, the KTS1655A/B withstands voltages of up to 29V on the VBUS and VSYS pins, passes valid input voltages and current from VBUS to VSYS, and blocks reverse current from VSYS to VBUS. Due to the ideal-diode behavior, two or more KTS1655A/B parts connected in “diode-OR” configuration can be used in parallel to support systems that may be charged or powered from multiple ports. Compared with KTS1655A/B, KTS1655C/D supports bi-directional mode when enabled so it is optimized for USB Type-C Power Delivery (PD) current-sink and or current-source applications.

### Enable Input

The KTS1655A/C has  $\overline{\text{EN}}$  active-low input logic with internal  $1\text{M}\Omega$  pull-down. The KTS1655B/D has EN active-high input logic. When disabled, the power switch is off and the IC is placed into low-power shutdown mode. When enabled, the protection circuits and the power switch are on. An 18ms de-bounce timer deploys before device turn-on and the soft-start ramp.

## Under-Voltage Lockout (UVLO)

When  $V_{BUS} < V_{UVLO}$  or  $V_{SYS} < V_{UVLO}$  (KTS1655C/D in  $I_{SOURCE}$  mode), the power switch is disabled. Once  $V_{BUS}$  or  $V_{SYS}$ , respectively, exceeds  $V_{UVLO}$ , the power switch is controlled by the enable pin and fault detection circuits.

## Soft-Start (SS)

The internal soft-start function allows the KTS1655 to charge a total output capacitance of over  $1000\mu F$  to 5V without excessive in-rush current. Soft-start controls the output voltage slew-rate ramp time. Use the below formula to calculate the current required to charge a combination of load current and output capacitance:

$$I_{IN\_SS} = I_{LOAD} + C_{OUT} \left( \frac{V_{IN}}{t_R} \right)$$

where  $t_R = 2.6ms$ . In either case, the soft-start time is somewhat fast to reduce power dissipation in the KTS1655 during soft-start.

Note that in addition to the soft-start voltage ramp, the soft-start current limit is 3.4A (typ.) to prevent excessive heat when starting into an output short-circuit condition or a large total output capacitance. This current limit is turned off after 8ms. After an additional 3ms delay, if  $V_{SYS}$  is near  $V_{BUS}$ , the  $\overline{ACOK}$  flag indicates a power good condition.

## Over-Voltage Protection (OVP)

When logically enabled, the switch is normally on. However, if  $V_{BUS} > V_{OVP}$ , the power switch is disabled due to an OVP fault. Once  $V_{BUS}$  drops below  $V_{OVP}$ , no other fault is detected, and the enable logic is still valid, the power switch is re-enabled via the soft-start debounce and ramp time.


The OVLO pin is used to adjust the over-voltage threshold externally. The default internal over-voltage threshold is 24V when the OVLO pin is tied to GND. Biasing the OVLO pin with a resistive voltage divider adjusts the over voltage threshold from 4V to 24V as in the below formula:

$$V_{OVP} = V_{OVLO} \left( 1 + \frac{R1}{R2} \right)$$

where  $V_{OVLO} = 1.22V$ . Connect R1 from  $V_{BUS}$  to OVLO. Connect R2 from OVLO to ground.

## “Ideal Diode” Reverse-Current Protection (RCP, KTS1655A/B only)

The KTS1655A/B offers reverse-current protection regardless of the enable logic level. When disabled, all current flow is blocked. When enabled, the RCP acts as a voltage droop regulator. Whenever the voltage on  $V_{SYS}$  is higher than  $V_{BUS}$  minus 15mV, the RCP circuit reduces the MOSFET gate drive to try and maintain the regulated 15mV droop, thereby acting as an “ideal diode” with  $V_f = 15mV$ . See Figure 8. This control method blocks all reverse current. The RCP circuit makes it possible to connect two or more USB charging ports to a single battery charger IC input in a “diode-OR” configuration with autonomous reverse-current blocking. The KTS1655A/B includes a  $15\mu s$  “fast recovery” when  $V_{SYS}$  falls back down below the “ideal diode” droop regulation point.



**Figure 8. "Ideal Diode" Reverse-Current Protection V-I Curve (KTS1655A/B only)**

### Over-Current Protection (OCP)

The KTS1655 includes output over-current protection (OCP) at 28A that protects the IC from damage when an over-current or short-circuit event suddenly appears. The OCP circuit quickly disables the power switch, so the current becomes zero. After an OCP event, if no other fault is detected, and the enable logic is still valid, the power switch is re-enabled via the soft-start debounce and ramp time.

### Short-Circuit Protection (SCP)

The KTS1655 includes output short-circuit protection (SCP). If an SCP event occurs while the KTS1655 is already enabled and working, OCP is the first line of defense and responds very quickly. In this case, the current from  $C_{IN}$  through the switch to  $C_{OUT}$  increases very rapidly. For SCP events that do not reach OCP, if the output voltage drops significantly below the input voltage, it is also detected as a soft-short event. In case of auto-retry or simply starting into a pre-existing SCP condition, the KTS1655 furthermore includes hard and soft SCP detection during soft-start if the output voltage is not ramping up. The KTS1655 remains undamaged during continuous SCP events.

### Over-Temperature Protection (OTP)

When device junction temperature exceeds 145°C, the OTP circuit disables the power switch. Once the device junction temperature decreases below 130°C, if no other fault is detected, and the enable logic is still valid, the power switch is re-enabled via the soft-start debounce and ramp time.

### Auto-Retry

For all fault conditions that cause the switch to open, the KTS1655 will auto-retry via the soft-start debounce and ramp time. If any fault or the same fault is detected again, the switch will open again, and auto-retry will repeat. This continues until the fault is removed (normal operation), or the device is logically disabled via the  $\overline{EN}$  or  $EN$  pin, or the input voltage is removed (UVLO).

### ACOK Output Flag

The  $\overline{ACOK}$  output is an open-drain output that requires an external pull-up resistor with recommended value in the 10kΩ to 200kΩ range. Connect  $\overline{ACOK}$  to GND or leave floating if unused. The  $\overline{ACOK}$  pin indicates the fault status. When there is no fault (UVLO, OVP, OCP, SCP, and OTP are not triggered) and the power switch is ON, then the  $\overline{ACOK}$  flag is pulled low to indicate the power is good. Otherwise, the  $\overline{ACOK}$  flag is high impedance. RCP is not classified as a fault condition.

## Applications Information

### Input Capacitor $C_{VBUS}$ Section

For most applications, connect a  $1\mu\text{F}$  to  $10\mu\text{F}$  ceramic capacitor as close as possible to the device from VBUS to GND to minimize the effect of parasitic trace inductance. 35V or 50V rated capacitors with X5R or better dielectric are recommended. For optimal surge and ESD performance,  $10\mu\text{F}$  is preferred.

### Output Capacitor $C_{VSYS}$ Section

For most applications, connect from  $10\mu\text{F}$  to  $1000\mu\text{F}$  total capacitance to the output. Typical applications use  $30\mu\text{F}$  to  $100\mu\text{F}$  as needed for system load-transients. At minimum, connect a  $10\mu\text{F}$  ceramic capacitor as close as possible to the device from VSYS to GND to minimize the effect of parasitic trace inductance. 25V rated capacitors with X5R or better dielectric are recommended. Lower voltage ratings are acceptable when using the OVLO pin to set a lower over-voltage protection threshold.


### TVS Selection

In order to prevent any unexpected ESD/Surge event damaging the OVP chip, a suitable uni-directional TVS diode must be carefully selected and used between VBUS pin (VBUS) and GND pin. First of all, the TVS diode working voltage should be determined. A TVS with  $V_{RWM} \geq 24\text{V}$  can be selected for 20V charging port. Secondly, it is necessary to meet the requirement of surge protection capability. According to IEC61000-4-5 8/20 $\mu\text{s}$  surge standard, if selecting a TVS with the surge voltage rating of 100V, the TVS should meet the requirement of  $I_{PP} \geq (100\text{V} - 30\text{V}) / 2\Omega = 35\text{A}$ . When selecting the TVS model, the TVS maximum clamping voltage at desired  $I_{PP}$  should be below **34V**. KTS1287 is an active flat-clamp TVS which can meet this requirement perfectly (See Surge Transient Response waveform in page 15). Too high TVS clamping voltage may cause damage to the OVP chip.

### Recommended PCB Layout

Good PCB thermal design is required to support heavy load currents. The KTS1655 EVB is designed to extend the fill area for the VBUS, VSYS, and GND copper planes to about 4 square inches total area for increased thermal performance. Due to the number of bumps on VBUS and VSYS, these two planes are especially important and should not be ignored. Adding back-side and/or buried-layer fill area with thermal vias also helps significantly.


Other than thermal concerns, the PCB layout for the KTS1655 is quite simple. Place the TVS, input and output capacitors near the IC. Connect the TVS, capacitor ground terminals together and to the GND pins using the top-side copper layer. Route the control signals on buried layers. For internally set 24V OVP, directly connect the OVLO pin to the adjacent GND pins.




**Figure 9. Recommended PCB Layout**

### Safe Operating Area (SOA)

See Figure 10 and Figure 11 for the SOA of the KTS1655. SOA curves are normally associated with discrete MOSFETs (which are sometimes co-package with a controller IC). In these competing systems, precautions are necessary to stay within the SOA area. However, the KTS1655 is a monolithic IC with all the integrated protection features to automatically keep its operation within the SOA area. For example, it includes over-voltage protection (OVP) and over-current protection (OCP) with very fast response times. It also includes over-temperature protection (OTP) that is measured on the same monolithic die as the integrated power MOSFETs. Additionally, soft-start is controlled with a voltage ramp and current limit protection (Soft-Start CLP) to safely soft-start even in systems with very high capacitance at the output. Furthermore, the integrated control circuit and back-to-back MOSFET switch are optimized to work together as a system, including their tolerances over temperature and process corners.




**Figure 10. Safe Operating Area (SOA) for  $T_c = 25^\circ\text{C}$**



**Figure 11. Safe Operating Area (SOA) for T<sub>c</sub> = 80°C**


## Packaging Information

WLCSP54-20 (2.485mm x 2.228mm x 0.555mm)




Dimension	mm		
	Min.	Typ.	Max.
A	0.517	0.555	0.593
A1	0.204	0.224	0.244
A2	0.294	0.306	0.319
A3	0.020	0.025	0.030
b	0.248	0.268	0.288
D	2.460	2.485	2.510
D1	2.000 REF.		
D2	0.242 REF.		
E	2.203	2.228	2.253
E1	1.5 REF.		
E2	0.364 REF.		
e	0.5 REF.		
S1	—	0.20	—
S2	—	0.30	—

## Recommended Footprint




## Packing Material Information

### Reel Dimensions




### Carrier Tape Dimensions



Dimension	mm		
	Min.	Typ.	Max.
A	176	178	180
C	12.8	13.0	13.5
W1	8.4	8.4	9.9
W2	—	—	14.4

DSR-0207-01

### Cover Tape Dimensions



Dimension	mm		
	Min.	Typ.	Max.
A0	2.37	2.42	2.47
B0	2.63	2.68	2.73
K0	0.65	0.70	0.75
P0	3.90	4.00	4.10
P1	3.90	4.00	4.10
P2	1.95	2.00	2.05
D0	1.50	1.55	1.60
D1	1.00	—	—
E	1.65	1.75	1.85
F	3.45	3.50	3.55
10P0	39.8	40.0	40.2
W	7.90	8.00	8.30
T	0.15	0.20	0.25
θ	0°		5°
θ2	0°		5°

DWG-0307-01

Dimensions	Dimension	mm		
		Min.	Typ.	Max.
	Tape Thickness	0.045	0.05	0.055
8mm	Tape Width	5.4	5.5	5.6

DWG-0306-01

Kinetic Technologies cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Kinetic Technologies product. No intellectual property or circuit patent licenses are implied. Kinetic Technologies reserves the right to change the circuitry and specifications without notice at any time.