

Three-Phase Bridge, Brake, Soft Start, and Solenoid Power Module



MSCGLQ50X065CTYZBNMG

Product Overview

The MSCGLQ50X065CTYZBNMG device is a three-phase bridge, brake, soft start, and solenoid power module. The following figures show the electrical diagram and pinout location of the device.

Figure 1. Electrical Diagram






Figure 2. Pinout Location



Note: All ratings are at $T_j = 25^\circ\text{C}$, unless otherwise specified.



These devices are sensitive to electrostatic discharge. Proper handling procedures must be followed.

Features

The MSCGLQ50X065CTYZBNMG device has the following key features:

- Silicon Carbide (SiC) schottky diode
- IGBT4
- Low stray inductance
- Lead frames for power connections
- Si₃N₄ substrate for improved thermal performance
- AlSiC base plate for extended reliability and reduced weight
- Extended storage temperature range
- Internal thermistor for temperature monitoring

Benefits

The MSCGLQ50X065CTYZBNMG device has the following benefits:

- Stable temperature behavior
- Very rugged
- Solderable terminals for easy PCB mounting
- Direct mounting to heatsink (isolated package)
- Low junction-to-case thermal resistance
- RoHS Compliant

Application

The MSCGLQ50X065CTYZBNMG device has the following applications:

- Hybrid Power Device (HPD) for Electro-Mechanical Actuator (EMA) and Electro-Hydrostatic Actuator (EHA) systems
- High reliability Power Core Module (PCM)
- Modular power module for Power Drive Electronic (PDE)

1. Electrical Specification

The following sections describe the electrical specifications of the MSCGLQ50X065CTYZBNMG device.

1.1 Q1 to Q6 and Q8 IGBTs (Per IGBT): Three-Phase Bridge and Brake

The following table lists the absolute maximum ratings (per IGBT) of the Q1 to Q6 and Q8 IGBTs.

Table 1-1. Absolute Maximum Ratings: Q1 to Q6 and Q8 IGBTs

Symbol	Parameter	Maximum Ratings	Unit
V_{CES}	Collector-emitter voltage	650	V
I_C	Continuous collector current	$T_C = 25\text{ }^{\circ}\text{C}$ 70 ¹	A
		$T_C = 80\text{ }^{\circ}\text{C}$ 50 ¹	
I_{CM}	Pulsed collector current	$T_C = 25\text{ }^{\circ}\text{C}$ 150	
V_{GE}	Gate-emitter voltage	± 20	V
P_D	Power dissipation	210	W

Note:

1. Q1 to Q6 IGBT device specifications, but output current must be limited due to the shunt resistor. For more details, see [1.7. Electrical Shunt Characteristics](#).

The following table lists the electrical characteristics (per IGBT) of the Q1 to Q6 and Q8 IGBTs.

Table 1-2. Electrical Characteristics: Q1 to Q6 and Q8 IGBTs

Symbol	Characteristic	Test Conditions	Min.	Typ.	Max.	Unit
I_{CES}	Zero gate voltage collector current	$V_{GE} = 0V$ $V_{CE} = 650V$	—	—	50	μA
$V_{CE(sat)}$	Collector emitter saturation voltage	$V_{GE} = 15V$ $I_C = 50A$ $T_J = 25\text{ }^{\circ}\text{C}$	1.4	1.85	2.3	V
		$T_J = 150\text{ }^{\circ}\text{C}$	—	2.2	—	
$V_{GE(th)}$	Gate threshold voltage	$V_{GE} = V_{CE}$ $I_C = 0.8\text{ mA}$	4.2	5.1	5.6	
I_{GES}	Gate-emitter leakage current	$V_{GE} = 20V$ $V_{CE} = 0V$	—	—	150	nA

The following table lists the dynamic characteristics (per IGBT) of the Q1 to Q6 and Q8 IGBTs.

Table 1-3. Dynamic Characteristics: Q1 to Q6 and Q8 IGBTs

Symbol	Characteristic	Test Conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	$V_{GE} = 0V$	—	3100	—	pF
C_{oes}	Output capacitance	$V_{CE} = 25V$	—	116	—	
C_{res}	Reverse transfer capacitance	$f = 1\text{ MHz}$	—	90	—	
Q_g	Gate charge	$V_{GE} = 15V$ $V_{CE} = 480V$ $I_C = 50A$	—	315	—	nC
$T_{d(on)}$	Turn-on delay time	$V_{GE} = \pm 15V$	—	19	—	ns
T_r	Rise time	$V_{Bus} = 400V$	—	29	—	
$T_{d(off)}$	Turn-off delay time	$I_C = 50A$	—	227	—	
T_f	Fall time	$R_G = 7\Omega$	—	22	—	
E_{on}	Turn-on energy	$V_{GE} = \pm 15V$	—	0.74	—	mJ
E_{off}	Turn-off energy	$V_{Bus} = 400V$ $I_C = 50A$ $R_G = 7\Omega$	—	1	—	
I_{sc}	Short circuit data	$V_{GE} \leq 15V$ $V_{Bus} = 400V$ $t_p \leq 5\text{ }\mu s$	—	350	—	A
R_{thJC}	Junction-to-case thermal resistance		—	—	0.723	°C/W

1.2 CR1 to CR6 SiC Diodes (Per SiC Diode): Three-Phase Bridge

The following table lists the ratings and characteristics (per SiC diode) of the CR1 to CR6 SiC diodes.

Table 1-4. Ratings and Characteristics: CR1 to CR6 SiC Diodes

Symbol	Characteristic	Test Conditions	Min.	Typ.	Max.	Unit
V_{RRM}	Peak repetitive reverse voltage		—	—	700	V
I_{RM}	Reverse leakage current	$V_R = 700V$	—	10	400	μA
		$T_J = 175\text{ }^\circ C$	—	100	—	
I_F	DC forward current	$T_J = 175\text{ }^\circ C$	—	20	—	A
V_F	Diode forward voltage	$I_F = 20A$	—	1.5	1.8	V
		$T_J = 175\text{ }^\circ C$	—	1.9	—	
Q_C	Total capacitive charge	$V_R = 400V$	—	54	—	nC
C	Total capacitance	$f = 1\text{ MHz}, V_R = 200V$	—	98	—	pF
		$f = 1\text{ MHz}, V_R = 400V$	—	92	—	
R_{thJC}	Junction-to-case thermal resistance		—	—	2.48	°C/W

1.3 Q7 IGBT: Soft Start

The following table lists the absolute maximum ratings of the Q7 IGBT.

Table 1-5. Absolute Maximum Ratings: Q7 IGBT

Symbol	Parameter	Maximum Ratings	Unit
V_{CES}	Collector-emitter voltage	650	V
I_C	Continuous collector current	$T_C = 25\text{ }^{\circ}\text{C}$	A
		$T_C = 80\text{ }^{\circ}\text{C}$	
I_{CM}	Pulsed collector current	$T_C = 25\text{ }^{\circ}\text{C}$	200
V_{GE}	Gate-emitter voltage	± 20	V
P_D	Power dissipation	300	W

The following table lists the electrical characteristics of the Q7 IGBT.

Table 1-6. Electrical Characteristics: Q7 IGBT

Symbol	Characteristic	Test Conditions	Min.	Typ.	Max.	Unit
I_{CES}	Zero gate voltage collector current	$V_{GE} = 0\text{V}$ $V_{CE} = 650\text{V}$	—	—	100	μA
$V_{CE(sat)}$	Collector emitter saturation voltage	$V_{GE} = 15\text{V}$ $I_C = 75\text{A}$	—	1.85	2.3	V
		$T_J = 150\text{ }^{\circ}\text{C}$	—	2.2	—	
$V_{GE(th)}$	Gate threshold voltage	$V_{GE} = V_{CE}$ $I_C = 1.2\text{ mA}$	4.2	5.1	5.6	
I_{GES}	Gate-emitter leakage current	$V_{GE} = 20\text{V}$ $V_{CE} = 0\text{V}$	—	—	200	nA

The following table lists the dynamic characteristics of the Q7 IGBT.

Table 1-7. Dynamic Characteristics: Q7 IGBT

Symbol	Characteristic	Test Conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	$V_{GE} = 0\text{V}$	—	4620	—	pF
C_{oes}	Output capacitance	$V_{CE} = 25\text{V}$	—	160	—	
C_{res}	Reverse transfer capacitance	$f = 1\text{ MHz}$	—	137	—	
Q_G	Gate charge	$V_{GE} = 15\text{V}$ $V_{CE} = 480\text{V}$ $I_C = 75\text{A}$	—	440	—	nC
$T_{d(on)}$	Turn-on delay time	$V_{GE} = \pm 15\text{V}$	$T_J = 150\text{ }^{\circ}\text{C}$	19	—	ns
T_r	Rise time	$V_{BUS} = 400\text{V}$		29	—	
$T_{d(off)}$	Turn-off delay time	$I_C = 75\text{A}$		227	—	
T_f	Fall time	$R_G = 5\Omega$		22	—	
E_{on}	Turn-on switching energy	$V_{GE} = \pm 15\text{V}$ $V_{CE} = 400\text{V}$	$T_J = 150\text{ }^{\circ}\text{C}$	1.1	—	mJ
E_{off}	Turn-off switching energy	$I_C = 75\text{A}$ $R_G = 5\Omega$		1.5	—	
I_{sc}	Short circuit data	$V_{GE} \leq 15\text{V}$ $V_{BUS} = 400\text{V}$ $t_p \leq 5\text{ }\mu\text{s}$	$T_J = 150\text{ }^{\circ}\text{C}$	500	—	A
R_{thJC}	Junction-to-case thermal resistance		—	—	0.51	$^{\circ}\text{C/W}$

1.4 CR7 and CR8 SiC Diodes (Per SiC diode): Brake and Soft Start

The following table lists the ratings and characteristics (per SiC diode) of the CR7 and CR8 SiC diodes.

Table 1-8. Ratings and Characteristics: CR7 and CR8 SiC Diodes

Symbol	Characteristic	Test Conditions		Min.	Typ.	Max.	Unit
V_{RRM}	Peak repetitive reverse voltage			—	—	700	V
I_{RM}	Reverse leakage current	$V_R = 700V$	$T_J = 25\text{ }^{\circ}C$	—	15	200	μA
			$T_J = 175\text{ }^{\circ}C$	—	250	—	
I_F	DC forward current	$T_J = 175\text{ }^{\circ}C$	$T_C = 60\text{ }^{\circ}C$	—	30	—	A
V_F	Diode forward voltage	$I_F = 30A$	$T_J = 25\text{ }^{\circ}C$	—	1.5	1.8	V
			$T_J = 175\text{ }^{\circ}C$	—	1.9	—	
Q_C	Total capacitive charge	$V_R = 400V$		—	83	—	nC
C	Total capacitance	$f = 1\text{ MHz}, V_R = 200V$		—	150	—	pF
		$f = 1\text{ MHz}, V_R = 400V$		—	128	—	
R_{thJC}	Junction-to-case thermal resistance			—	—	1.75	$^{\circ}C/W$

1.5 Q9 and Q10 IGBTs (Per IGBT): Solenoid

The following table lists the absolute maximum ratings (per IGBT) of the Q9 and Q10 IGBTs.

Table 1-9. Absolute Maximum Ratings: Q9 and Q10 IGBTs

Symbol	Parameter		Maximum Ratings	Unit
V_{CES}	Collector-emitter voltage		1200	V
I_C	Continuous collector current	$T_C = 25\text{ }^{\circ}C$	27	A
		$T_C = 80\text{ }^{\circ}C$	15	
I_{CM}	Pulsed collector current	$T_C = 25\text{ }^{\circ}C$	30	
V_{GE}	Gate-emitter voltage		± 20	V
P_D	Power dissipation	$T_C = 25\text{ }^{\circ}C$	80	W

The following table lists the electrical characteristics (per IGBT) of the Q9 and Q10 IGBTs.

Table 1-10. Electrical Characteristics: Q9 and Q10 IGBTs

Symbol	Characteristic	Test Conditions		Min.	Typ.	Max.	Unit
I_{CES}	Zero gate voltage collector current	$V_{GE} = 0V$ $V_{CE} = 1200V$		—	—	100	μA
$V_{CE(sat)}$	Collector emitter saturation voltage	$V_{GE} = 15V$ $I_C = 8A$	$T_J = 25\text{ }^{\circ}C$	1.6	1.85	2.1	V
			$T_J = 150\text{ }^{\circ}C$	—	2.25	—	
$V_{GE(th)}$	Gate threshold voltage	$V_{GE} = V_{CE}$ $I_C = 0.3\text{ mA}$		5.3	5.8	6.3	
I_{GES}	Gate-emitter leakage current	$V_{GE} = 15V$ $V_{CE} = 0V$		—	—	150	nA
C_{ies}	Input capacitance	$V_{GE} = 0V$		—	490	—	pF
C_{res}	Reverse transfer capacitance	$V_{CE} = 25V$ $f = 1\text{ MHz}$		—	30	—	
R_{thJC}	Junction-to-case thermal resistance			—	—	1.85	$^{\circ}C/W$

1.6 CR9 and CR10 SiC Diodes (Per SiC diode): Solenoid

The following table lists the ratings and characteristics (per SiC diode) of the CR9 and CR10 SiC diodes.

Table 1-11. Ratings and Characteristics: CR9 and CR10 SiC Diodes

Symbol	Characteristic	Test Conditions		Min.	Typ.	Max.	Unit
V_{RRM}	Peak repetitive reverse voltage			—	—	700	V
I_{RM}	Reverse leakage current	$V_R = 700V$	$T_J = 25\text{ }^{\circ}C$	—	5	200	μA
			$T_J = 175\text{ }^{\circ}C$	—	50	—	
I_F	DC forward current	$T_J = 175\text{ }^{\circ}C$	$T_C = 60\text{ }^{\circ}C$	—	10	—	A
V_F	Diode forward voltage	$I_F = 10A$	$T_J = 25\text{ }^{\circ}C$	—	1.5	1.8	V
			$T_J = 175\text{ }^{\circ}C$	—	1.9	—	
Q_C	Total capacitive charge	$V_R = 400V$		—	27	—	nC
C	Total capacitance	$f = 1\text{ MHz}, V_R = 200V$		—	49	—	pF
		$f = 1\text{ MHz}, V_R = 400V$		—	46	—	
R_{thJC}	Junction-to-case thermal resistance			—	—	4.69	$^{\circ}C/W$

1.7 Electrical Shunt Characteristics

The following tables list the electrical shunt characteristics of the MSCGLQ50X065CTYZBNMG device.

Table 1-12. Shunt (R7 to R9)

Symbol	Characteristic		Min.	Typ.	Max.	Unit
R_i	Resistance value	$i = 7, 8, \text{ and } 9$	—	5	—	m Ω
T_{Ri}	Tolerance	TCR Max 50 ppm/ $^{\circ}C$ (from 20 $^{\circ}C$ to 60 $^{\circ}C$)	—	1	1.5	%
P_{Ri}	Load capacity		—	—	3	W
I_{Ri}	Current capacity		—	—	24	A

Table 1-13. Shunt (R10)

Symbol	Characteristic		Min.	Typ.	Max.	Unit
R_i	Resistance value	$i = 10$	—	0.5	—	m Ω
T_{Ri}	Tolerance	TCR Max 20 ppm/ $^{\circ}C$ (from 20 $^{\circ}C$ to 60 $^{\circ}C$)	—	1	1.5	%
P_{Ri}	Load capacity		—	—	5	W
I_{Ri}	Current capacity		—	—	100	A

Table 1-14. Shunt (R11)

Symbol	Characteristic		Min.	Typ.	Max.	Unit
R_i	Resistance value	$i = 11$	—	15	—	m Ω
$RSoli$	Resistance value with SOL+ connector ¹	TCR Max 50 ppm/ $^{\circ}C$ (from 20 $^{\circ}C$ to 60 $^{\circ}C$)	—	15.25	—	
T_{Ri}	Tolerance		—	1	1.5	%
P_{Ri}	Load capacity		—	—	3	W
I_{Ri}	Current capacity		—	—	14	A

Note:

- Value that integrates the resistivity of the SOL+ connector considering the user PCB mounted on the spacers and soldered on the power module in accordance with IPC A610, class 3.

1.8 Temperature Sensor PTC

The following table lists the temperature sensor PTC of the MSCGLQ50X065CTYZBNMG device.

Table 1-15. Temperature Sensor PTC

Symbol	Characteristic	Typ.	Unit
R_0	Resistance at 0 °C	1000	Ω
A	—	3.9083×10^{-3}	$^{\circ}\text{C}^{-1}$
B	—	-5.775×10^{-7}	$^{\circ}\text{C}^{-2}$
C	—	-4.183×10^{-12}	$^{\circ}\text{C}^{-4}$
ΔT	—	$\pm(0.3 + 0.005 \times T)$	$^{\circ}\text{C}$

For temperature range of 0 °C up to 175 °C, $R_T = R_0 (1 + A \times T + B \times T^2)$

For temperature range of -55 °C up to 0 °C, $R_T = R_0 (1 + A \times T + B \times T^2 + C (T - 100) T^3)$

Where:

T: Temperature in °C

R_T : Thermistor value at T

Note: For more information, see [APT0406—Using NTC Temperature Sensor Integrated into Power Module](#).

1.9 Thermal and Package Characteristics

The following table lists the thermal and package characteristics of the MSCGLQ50X065CTYZBNMG device.

Table 1-16. Thermal and Package Characteristics

Symbol	Characteristic			Min.	Max.	Unit
V_{ISOL}	RMS isolation voltage, any terminal to case, $t = 1$ min, at 1 bar			4000	—	V
$V_{ISOLPTC}$	RMS isolation voltage, PTC to any other electrical terminals, $t = 1$ min at 1 bar, 50/60 Hz			1500	—	
T_J	Operating junction temperature range			-55	175	$^{\circ}\text{C}$
T_{JOP}	Recommended junction temperature under switching conditions			-55	$T_{Jmax} - 25$	
T_{STG}	Storage temperature range			-60	125	
T_C	Operating case temperature			-55	125	
Torque	Mounting torque	Insert	M2.5	—	0.3	N.m
		To heatsink	M6	3	5	
Wt	Package weight			—	150	g

1.10 Typical IGBT Performance Curve (Q1 to Q6 and Q8)

The following figures show the performance curves of the Q1 to Q6 and Q8 IGBTs.

Figure 1-1. Maximum Thermal Impedance




Figure 1-2. Output Characteristics, $V_{GE} = 15V$




Figure 1-3. Output Characteristics, $T_J = 150\text{ }^{\circ}\text{C}$




Figure 1-4. Transfer Characteristics




Figure 1-5. Energy Losses vs. Collector Current




Figure 1-6. Switching Energy Losses vs. Gate Resistance





Figure 1-7. Operating Frequency vs. Collector Current



1.11 Typical SiC Diode Performance Curve (CR1 to CR6)

The following figures show the performance curves of the CR1 to CR6 SiC diodes.

Figure 1-8. Maximum Thermal Impedance




Figure 1-9. Forward Characteristics





Figure 1-10. Capacitance vs. Reverse Voltage



1.12 Typical IGBT Performance Curve (Q7)

The following figures show the performance curves of the Q7 IGBT.

Figure 1-11. Maximum Thermal Impedance




Figure 1-12. Output Characteristics, $V_{GE} = 15V$




Figure 1-13. Output Characteristics, $T_J = 150^\circ C$




Figure 1-14. Transfer Characteristics




Figure 1-15. Energy Losses vs. Collector Current




Figure 1-16. Switching Energy Losses vs. Gate Resistance





Figure 1-17. Operating Frequency vs. Collector Current



1.13 Typical SiC Diode Performance Curve (CR7 and CR8)

The following figures show the performance curves of the CR7 and CR8 SiC diodes.

Figure 1-18. Maximum Thermal Impedance




Figure 1-19. Forward Characteristics





Figure 1-20. Capacitance vs. Reverse Voltage



1.14 Typical IGBT Performance Curve (Q9 and Q10)

The following figures show the performance curves of the Q9 and Q10 IGBTs.

Figure 1-21. Maximum Thermal Impedance





Figure 1-22. Output Characteristics, $V_{GE} = 15V$



1.15 Typical SiC Diode Performance Curve (CR9 and CR10)

The following figures show the performance curves of the CR9 and CR10 SiC diodes.

Figure 1-23. Maximum Thermal Impedance




Figure 1-24. Forward Characteristics





Figure 1-25. Capacitance vs. Reverse Voltage




2. Package Specifications

The following section describes the package specification of the MSCGLQ50X065CTYZBNMG device.

2.1 Package Outline

The following figure shows the package outline drawing of the MSCGLQ50X065CTYZBNMG device. The dimensions in the following figure are in millimeters.

Figure 2-1. Package Outline Drawing



3. Revision History

The revision history describes the changes that were implemented in the document. The changes are listed by revision, starting with the most current publication.

Revision	Date	Description
A	04/2023	Initial revision

Microchip Information

The Microchip Website

Microchip provides online support via our website at www.microchip.com/. This website is used to make files and information easily available to customers. Some of the content available includes:

- **Product Support** – Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- **General Technical Support** – Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip design partner program member listing
- **Business of Microchip** – Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

Product Change Notification Service

Microchip's product change notification service helps keep customers current on Microchip products. Subscribers will receive email notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, go to www.microchip.com/pcn and follow the registration instructions.

Customer Support

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Embedded Solutions Engineer (ESE)
- Technical Support

Customers should contact their distributor, representative or ESE for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in this document.

Technical support is available through the website at: www.microchip.com/support

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.

Legal Notice

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure

that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at www.microchip.com/en-us/support/design-help/client-support-services.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimePictra, TimeProvider, TrueTime, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, GridTime, IdealBridge, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, KoD, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQL, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2023, Microchip Technology Incorporated and its subsidiaries. All Rights Reserved.

ISBN: 978-1-6683-2364-9

Quality Management System

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Worldwide Sales and Service

AMERICAS	ASIA/PACIFIC	ASIA/PACIFIC	EUROPE
Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: www.microchip.com/support Web Address: www.microchip.com	Australia - Sydney Tel: 61-2-9868-6733 China - Beijing Tel: 86-10-8569-7000 China - Chengdu Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588 China - Dongguan Tel: 86-769-8702-9880 China - Guangzhou Tel: 86-20-8755-8029 China - Hangzhou Tel: 86-571-8792-8115 China - Hong Kong SAR Tel: 852-2943-5100 China - Nanjing Tel: 86-25-8473-2460 China - Qingdao Tel: 86-532-8502-7355 China - Shanghai Tel: 86-21-3326-8000 China - Shenyang Tel: 86-24-2334-2829 China - Shenzhen Tel: 86-755-8864-2200 China - Suzhou Tel: 86-186-6233-1526 China - Wuhan Tel: 86-27-5980-5300 China - Xian Tel: 86-29-8833-7252 China - Xiamen Tel: 86-592-2388138 China - Zhuhai Tel: 86-756-3210040	India - Bangalore Tel: 91-80-3090-4444 India - New Delhi Tel: 91-11-4160-8631 India - Pune Tel: 91-20-4121-0141 Japan - Osaka Tel: 81-6-6152-7160 Japan - Tokyo Tel: 81-3-6880-3770 Korea - Daegu Tel: 82-53-744-4301 Korea - Seoul Tel: 82-2-554-7200 Malaysia - Kuala Lumpur Tel: 60-3-7651-7906 Malaysia - Penang Tel: 60-4-227-8870 Philippines - Manila Tel: 63-2-634-9065 Singapore Tel: 65-6334-8870 Taiwan - Hsin Chu Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830 Taiwan - Taipei Tel: 886-2-2508-8600 Thailand - Bangkok Tel: 66-2-694-1351 Vietnam - Ho Chi Minh Tel: 84-28-5448-2100	Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4485-5910 Fax: 45-4485-2829 Finland - Espoo Tel: 358-9-4520-820 France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79 Germany - Garching Tel: 49-8931-9700 Germany - Haan Tel: 49-2129-3766400 Germany - Heilbronn Tel: 49-7131-72400 Germany - Karlsruhe Tel: 49-721-625370 Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44 Germany - Rosenheim Tel: 49-8031-354-560 Israel - Ra'anana Tel: 972-9-744-7705 Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781 Italy - Padova Tel: 39-049-7625286 Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340 Norway - Trondheim Tel: 47-72884388 Poland - Warsaw Tel: 48-22-3325737 Romania - Bucharest Tel: 40-21-407-87-50 Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 Sweden - Gothenberg Tel: 46-31-704-60-40 Sweden - Stockholm Tel: 46-8-5090-4654 UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820