



MISSION-CRITICAL
INTERCONNECT
SOLUTIONS



Series 806 Mil-Aero Connectors

Next-Generation High-Density Connector Series for Rugged Air, Sea, Space,
and Ground Applications—Military and Commercial

SECOND EDITION • NOVEMBER 2021



Series 806 Mil-Aero Connectors

Advanced electrical, mechanical and environmental performance *plus reduced size and weight* compared to D38999

Series 806 offers significant size and weight savings while meeting key performance benchmarks for a broad range of applications such as commercial and military aerospace, industrial robotics, transportation systems and more. Designed for general use in harsh vibration, shock and environmental settings—as well as high-altitude, unpressurized aircraft zones with aggressive voltage ratings and altitude immersion standards—the Series 806 Mil-Aero features numerous mechanical design innovations including durable mechanical insert retention, radial seals and triple-ripple grommet seals. Its reduced thread pitch and re-engineered ratchet prevent decoupling problems, particularly in small shell sizes, solving one of the major problems of shell size 9 and 11 MIL-DTL-38999 Series III connectors.

SAVE SIZE AND WEIGHT WITH SERIES 806 VERSUS D38999

Series 806 Mil-Aero
Smallest Size
.500 In. Mating Threads
3 #20 Contacts
or 7 #22 contacts



MIL-DTL-38999
Smallest Size
.625 In. Mating Threads
3 #20 Contacts or 6 #22 contacts



- Next-generation small form factor aerospace-grade circular connector
- Designed for general use in harsh application environments such as aircraft, industrial robotics and more
- Upgraded environmental, electrical and mechanical performance
- Integrated anti-decoupling technology
- Higher density 20HD and 22HD contact arrangements
- Glass hermetic, lightweight aluminum hermetic, high-temperature, fiber optic, and filtered versions

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Table of Contents



SERIES 806 MIL-AERO GENERAL INFORMATION AND REFERENCE






Table of Contents and Product Features
Page 1



Contact Arrangements
Page 6




Performance Specification
Page 10



Space-Grade Information
Page 13



Recommended Torque Values
Page 217




Printed Circuit Board Layouts
Page 218

ENVIRONMENTAL SERIES 806 MIL-AERO CONNECTORS




Cable Plugs, Environmental
806-012
Page 15



Square Flange Receptacles
806-013
Page 17



In-Line Receptacles
806-019
Page 19




Jam-nut Receptacles
806-020
Page 21



Jam-nut PCB Receptacles
806-021
Page 23




Square Flange PCB Receptacles
806-022
Page 25




Jam-Nut Coax PCB Receptacles
806-058
Page 31


ENVIRONMENTAL SERIES 806 HIGH-SPEED / RF PCB RECEPTACLES




Jam-nut El Ochito Receptacle
806-039
Page 37



Square-Flange El Ochito Receptacle
806-040
Page 41




ThermaRex HT Plug
806-042
Page 47



ThermaRex HT Jam-Nut
806-053
Page 49



ThermaRex HT Square Flange
806-052
Page 51



ThermaRex HT PCB Jam-Nut
806-041
Page 53

FIBER OPTIC SERIES 806 MIL-AERO CONNECTORS AND ACCESSORIES



Cable Plug
806-012
Page 79



Sq-Flange Receptacle
806-013
Page 79




In-Line Receptacle
806-019
Page 80



Jam-Nut Receptacle
806-020
Page 80

HERMETIC GLASS-TO-METAL SEAL SERIES 806 MIL-AERO CONNECTORS



Hermetic Receptacles, PC Tail / Solder Cup
806-025
Page 89



Hermetic PCB Recept, Threaded Standoff
806-026
Page 92

CONNECTOR REFERENCE

MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors


Table of Contents




LIGHT-WEIGHT HERMETIC CODE RED SERIES 806 MIL-AERO CONNECTORS




PCB Jam-Nut Receptacle,
with Threaded Standoffs
CODE RED
806-028
Page 109



PCB Jam-Nut Receptacle,
High-Speed El Ochito®
CODE RED
806-043
Page 111



Filtered Solder Cup or PC Tail
Jam-Nut Receptacle,
240-806 (-07) or (-08)
Page 118



Filtered Solder Cup or PC Tail
Jam-Nut, Threaded Standoff
240-806-21
Page 120


SERIES 806 HIGH-SPEED CABLE ASSEMBLIES AND MIL-AERO CONTACTS



White, Blue and Red El Ochito Discrete and
Single or Double Ended Cable Assemblies
Page 123




Size 22 HD
Crimp Contacts
Page 146




Size 20HD
Crimp Contacts
Page 148



Size 16 Power,
and RF Contacts
Page 149



Size 12 Power,
and RF Contacts
Page 151



Size 8 Power,
and RF Contacts
Page 155

TOOLS, ACCESSORIES AND BACKSHELLS




Crimp Tools,
Ins/Ext Tools
Page 166




Filler Plugs
and DCSP
Page 172



Band-Master ATS®
Page 172



Holding Tools and
Spanner Wrench Skt
Page 173




Nut Plates
Page 174




Panel O-rings
and Gaskets
Page 175



Jam-Nuts, Hex and Low
Profile
Page 176 - 178



Protective
Covers
Page 179



Stowage Receptacles
Page 182



Backshell
Selection Guide
Page 183



Shrink
Boots
Page 214

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Product Features



About The Series 806

The Series 806 Mil-Aero is an aerospace-grade micro miniature circular connector with triple-start threaded coupling. The 806 connector is smaller and lighter than conventional aerospace connectors. Featuring size 22HD, 20HD contacts plus size 8 power and high speed El Ochito®, quadrax, and fiber optic options. The Series 806 offers up to twice the number of contacts with no reduction in performance than MIL-DTL-38999 Series III. In fact, independent laboratory testing has demonstrated that the Series 806 meets, and in many cases exceeds, the requirements of MIL-DTL-38999.

But there is more to the 806 than just size and weight reduction. This flight-proven high-performance

connector has many innovative features that meet the most aggressive requirements of the military/aerospace industry, including better resistance to vibration-induced decoupling. This is accomplished by re-engineering the ratchet mechanism and introducing a shallower mating thread ramp angle than is available in D38999.

Glenair pioneered integral shield banding platforms to allow direct attachment of cable shields, boots and overmolds. This innovation continues with the 806—Glenair's first connector to exclusively use the ultra lightweight Nano shield termination band for maximum size and weight reduction.




Another enhancement is a "top hat" insulator with raised bosses for foolproof alignment of insulator

cavities and retention clips as well as higher voltage ratings.

The Series 806 Mil-Aero connector features an O-ring radial interface sealing design instead of a flat gasket. This allows for easier metal-to-metal coupling, improved sealing, and better EMI performance. The MIL-DTL-38999 Series III and other legacy aerospace circular connectors have a flat gasket inside the receptacle shell. This peripheral seal must be compressed sufficiently to allow full metal-to-metal connector bottoming. In certain tolerance conditions this seal can make it difficult to fully mate the connectors "without the use of tools" as is required by MIL-DTL-38999.

Save Size and Weight with Series 806 Mil-Aero Connectors

The Next-Generation Higher-Density Connector for Demanding Aerospace and Defense Applications



Series 806 plug with 19 #22 contacts compared to MIL-DTL-38999 Series III with 6 #22 contacts. More than 3X the number of contacts, yet only .020 inches larger in diameter.

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Product Features




KEY FEATURES

- Next-generation high-performance micro miniature aerospace connector
- Reduced-pitch triple-start modified anti-decoupling stub ACME thread
- Higher density 20HD and 22HD contact arrangements
- +200° C operating temperature
- High-strength aluminum alloy plug barrel
- "Triple ripple" wire sealing grommet (75,000 ft. rated)
- Snap-in, rear-release crimp contacts
- Metal contact retention clips
- Integral Nano-Band shield termination platform
- EMI shielding effectiveness IAW MIL-DTL-38999M para. 4.5.28 (65 dB min. leakage attenuation @ 10GHz)
- 10,000 amp indirect lightning strike
- 300g. shock
- MIL-S-901 Grade A high-impact shock
- Aluminum and stainless steel versions
- Environmental crimp contact, glass-to-metal seal PC tail and solder cup hermetics, RF, fiber, and EMI filter versions
- RoHS compliant nickel, nickel-PTFE, black zinc and stainless steel plus mil-grade cadmium finish options
- Printed circuit board versions with threaded mounting holes

Plug Connector



Receptacle Connector



AVAILABLE LIGHTWEIGHT ALUMINUM "CODE RED" HERMETICS

CODE RED is a lightweight encapsulant sealing and application process with 50% package-weight savings compared to glass-to-metal seal Kovar/stainless steel solutions. Non-outgassing CODE RED (IAW NASA/ESA) provides durable hermetic sealing with better than 1×10^{-7} leak-rate performance. Gold-plated copper PCB contacts deliver outstanding low-resistance current carrying capacity. See 806-028.



MICRO MINIATURE CIRCULAR



Series 806

Mil-Aero Connectors

Product Features



SERIES 806 MIL-AERO FEATURES



Series 806 Mil-Aero, with its high-density size #8, #20HD and #22HD contact arrangements, is designed for universal mil-aero use. The many special design features shown above allow this micro miniature circular connector to meet and even exceed MIL-DTL-38999 performance even in high-altitude, unpressurized zones. In addition to high-density signal contacts, Series 806 also supports a broad range of high-speed shielded contacts including Glenair Signature El Ochito® (up to 40 GbE), as well as Size #8 Coax, and fiber optic termini.

CONNECTOR REFERENCE

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors




Contact Arrangements (Mating face of pin connector shown. Socket numbering is reversed.)

Contact Arrangements																							
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					14-20		20				14-3				3		18-59	55		4		
8-4	4					16-31		31				16-4				4		11-14	13			1	
8-7	7					18-41		41				16-7				7		12-14	12			2	
9-11	11					20-55		55				18-8				8		14-22	20			2	
10-15	15					22-69		69				20-11				11		12-14	12			2	
11-19	19					24-92		92				22-13				13		16-32	28			4	
12-26	26					8-1			1			24-19				19		16-42	40			2	
14-39	39					10-2			2			10-1					1	18-62	60			2	
16-60	60					11-4			4			16-2					2	14-20A	19				1
18-85	85					12-5			5			18-3					3	16-22	20				2
20-110	110					14-7			7			20-4					4	18-21	18				3
22-140	140					16-12			12			22-5					5	20-28	24				4
24-186	186					18-15			15			24-8					8	22-44	40				4
8-3		3				20-22			22			10-8A	6		2			24-97	93				4
9-5		5				22-24			24			11-13	11		2								
10-8		8				24-35			35			12-27	26		1								
11-10		10				9-1				1		14-21	17		4								
12-15		15				12-2				2		16-41	37		4								

Series 806 Size 22HD Contact Arrangements (1300 VAC, 5 A)

Mating face of pin connector. Socket numbering is reversed.


Symbol ▼ indicates master key location.



Arrangement No.	7-3	8-4	8-7	9-11	10-15	11-19	12-26	14-39
No. of Contacts	3	4	7	11	15	19	26	39

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.



Arrangement No.	16-60	18-85	20-110	22-140	24-186
No. of Contacts	60	85	110	140	186

See Appendix for PC board layouts

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors




Contact Arrangements (Mating face of pin connector shown. Socket numbering is reversed.)

Series 806 Size 20HD Contacts Arrangements (1800 VAC, 7.5 A)

Mating face of
pin connector.
Socket
numbering is
reversed.


Symbol ▼
indicates
master key
location.



Arrangement No.	8-3	9-5	10-8	11-10	12-15	14-20	16-31
No. of Contacts	3	5	8	10	15	20	31

Mating face of
pin connector.
Socket
numbering is
reversed.

Symbol ▼
indicates
master key
location.




Arrangement No.	18-41	20-55	22-69	24-92
No. of Contacts	41	55	69	92

Series 806 Size 16 Contact Arrangements (2300 VAC, 13 A)

Mating face of
pin connector.
Socket
numbering is
reversed.


Symbol ▼
indicates
master key
location.



Arrangement No.	8-1	10-2	11-4	12-5	14-7	16-12
No. of Contacts	1	2	4	5	7	12

Mating face of
pin connector.
Socket
numbering is
reversed.

Symbol ▼
indicates
master key
location.



Arrangement No.	18-15	20-22	22-24	24-35
No. of Contacts	15	22	24	35

See Appendix for PC board layouts

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors




Contact Arrangements (Mating face of pin connector shown. Socket numbering is reversed.)

Series 806 Size 12 Contact Arrangements (2300 VAC, 23 A)

Mating face of pin connector. Socket numbering is reversed.


Symbol ▼ indicates master key location.



Arrangement No.	9-1	12-2	14-3	16-4	16-7
No. of Contacts	1	2	3	4	7

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.




Arrangement No.	18-8	20-11	22-13	24-19
No. of Contacts	8	11	13	19

Series 806 Size 8 Contact Arrangements (1800 VAC, 46 A)

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.




Arrangement No.	10-1	16-2	18-3	20-4	22-5	24-8
No. of Contacts	1 - #8	2 - #8	3x #8	4x #8	5x #8	8x #8

Series 806 Size 22 and 16 Combo Contact Arrangements

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.



Arrangement No.	10-8A	11-13	12-27	14-21	16-41	18-59
No. of #22 Contacts	6	11	26	17	37	55
No. of #16 Contacts	2	2	1	4	4	4

CONNECTOR REFERENCE

See Appendix for PC board layouts

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors




Contact Arrangements (Mating face of pin connector shown. Socket numbering is reversed.)

Series 806 Size 22HD and 12 Combo Contact Arrangements

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.




Arrangement No.	11-14	12-14	14-22	16-32	16-42	18-62
No. of #22 Contacts	13	12	20	28	40	60
No. of #12 Contacts	1	2	2	4	2	2

Series 806 Size 22HD and 8 Combo Contact Arrangements

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.



Arrangement No.	14-20A	16-22	18-21	20-28	22-44	24-97
No. of #22 Contacts	19	20	18	24	40	93
No. of #8 Contacts	1	2	3	4	4	4


See Appendix for PC board layouts

Series 806 Mil-Aero combo insert arrangements support applications with both standard data signal requirements, plus high-speed datalink (multi-gigabit Ethernet, HDMI, etc.), as well as RF / microwave, and power. Glenair Signature El Ochito® octaxial contacts support 10GbE in a single shielded contact. Available size #8 differential Twinax and industry-standard Quadrax are also supported. A broad range of RF Coax contacts are also available in different frequency ranges. Size #8 power contacts support size 8 to size 12 AWG wire.


SERIES 806 MIL-AERO CONTACT SELECTION GUIDE



Fiber Termini
Page 81



El Ochito Contacts
Page 124




Crimp Contacts
Page 146



Power Contacts
Page 155



RF Coax Contacts
Page 157



Twinax / Quadrax
Page 158

CONNECTOR REFERENCE

Standard Materials and Finishes

DESCRIPTION	MATERIAL	FINISH
Pin Contact	Copper alloy	50 microinches gold over nickel
Socket Contact	Copper alloy, with stainless steel hood	50 microinches gold over nickel Contact hood: passivate
Insulators	High grade rigid dielectric	None
Seals	Fluorosilicone/silicone blend, blue	None
EMI Spring	Beryllium copper	Nickel
Shell, Coupling Nut, Jam-nut	Aluminum alloy or stainless steel	See how-to-order tables for finish options
Contact Retention Clip	Beryllium copper	None
Anti-Decoupling Ratchet Spring	Stainless steel	Passivate

Performance Specification

Performance Specification					
TEST DESCRIPTION	REQUIREMENT			PROCEDURE	
Dielectric withstanding voltage at sea level	Contact Size	Altitude	Voltage	MIL-DTL-38999M para. 4.5.11.1 EIA-364-20 Method A 2 mA maximum leakage current Unmated pairs	
	20HD	Sea level	1800		
	22HD	Sea level	1300		
Dielectric withstanding voltage at altitude	Contact Size	Altitude	Voltage	MIL-DTL-38999M para. 4.5.11.2 EIA-364-20 Method A 2 mA maximum leakage current Mated pairs	
	20HD	50,000 ft	1000		
		70,000 ft	1000		
		100,000 ft	1000		
	22HD	50,000 ft	800		
		70,000 ft	800		
		100,000 ft	800		
Insulation resistance at ambient temperature	5000 megohms minimum			MIL-DTL-38999M Para. 4.5.10.1 EIA-364-21	
Insulation resistance at elevated temperature	1000 megohms minimum			MIL-DTL-38999M Para. 4.5.10.2 EIA-364-21	
Contact resistance at 25°C, crimp contacts	Wire Size	Test Current Amperes	Maximum Voltage Drop (millivolts)		AS39029C Para. 4.7.5 EIA-364-06 Silver-plated wire
			Initial	After Conditioning	
	20	7.5	55	66	
	22	5	73	88	
	24	3	45	54	
	26	2	52	63	
	28	1.5	54	65	
	30	1	60	73	
	Contact resistance at 200° C, crimp contacts	Wire Size	Test Current Amperes	Maximum Voltage Drop (millivolts)	
20		7.5	94		
22		5	125		
24		3	77		
26		2	89		
28		1.5	92		
30		1	103		
Low level contact resistance, crimp contacts		Wire Size	Maximum Contact Resistance (milliohms)		AS39029C Para. 4.7.4 EIA-364-23 Silver plated wire
	Initial Values		After Conditioning		
	20	9	11		
	22	15	17		
	24	20	23		
	26	31	38		
	28	50	60		
	30	75	88		

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Performance Specification



Performance Specification							
TEST DESCRIPTION	REQUIREMENT				PROCEDURE		
Contact resistance, glass-sealed hermetic connectors	Contact Size, Wire Size	Test Current Amperes	Maximum Millivolt Drop		MIL-DTL-38999M Para. 3.18.2 EIA-364-06		
			Initial	After Conditioning			
	20	5	60	75			
	22	3	85	95			
Shell-to-shell conductivity	Finish Code	Shell Matl/Fin	Millivolt Drop (mV)		MIL-DTL-38999M Para. 4.5.25 EIA-364-83		
	NF	Al/OD Cad	2.5				
	MT	Al/Ni-PTFE	2.5				
	ME	Al/EN	1.0				
	ZR	Al/Zn-Ni	2.5				
	Z1	SST/pass.	10.0				
	ZL	SST/Ni	1.0				
	Backshell shield braid to shell conductivity	Finish Code	Shell Matl/Fin	Millivolt Drop (mV)		MIL-DTL-38999M Para. 4.5.25.1 EIA-364-83	
NF		Al/OD Cad	5.0				
MT		Al/Ni-PTFE	5.0				
ME		Al/EN	3.5				
ZR		Al/Zn-Ni	5.0				
Z1		SST/pass.	15.0				
ZL		SST/Ni	3.5				
Indirect lightning strike		No evidence of damage which could impair proper functioning. Connectors shall meet shell-to-shell conductivity, DWV and coupling torque.					MIL-DTL-38999M Para. 4.5.47 EIA-364-75 10,000 Amps peak current
EMI shielding	Freq. MHz	Leakage Attenuation, (dB) minimum		MIL-DTL-38999M Para. 4.5.28			
		Electroless Nickel Finish	Cadmium, Nickel-PTFE, Zinc-Nickel Finish				
	100	90	90				
	200	88	88				
	300	88	88				
	400	87	87				
	800	85	85				
	1,000	85	85				
	1,500	76	69				
	2,000	70	65				
	3,000	69	61				
	4,000	68	58				
	6,000	66	55				
	10,000	65	50				
	Durability	No evidence of damage which could impair proper functioning following 500 cycles of mating and unmating.				MIL-DTL-38999M Para. 4.5.8 EIA-364-09	
Coupling and uncoupling torque	Shell size	Maximum Engagement lbs.-inch.	Minimum Disengagement lbs.-inch.	MIL-DTL-38999M Para. 4.5.7 EIA-364-114			
	8	8	2				
	9	8	2				
	10	12	2				
	11	12	2				
	12	12	2				
	14	16	2				
	16	20	3				
	18	24	3				
	20	28	3				
	22	32	5				
	24	36	5				
	Insert retention	100 pounds per square inch, 25 pound minimum force				MIL-DTL-38999M Para. 4.5.12 EIA-364-35	
	External bend moment	Shell size	Pound inches		MIL-DTL-38999M Para. 4.5.16 EIA-364-43		
8		100					
9		100					
10		100					
11		200					
12		300					
14		400					
16		500					
18		600					
20		700					
22		800					
24	900						

CONNECTOR REFERENCE

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Performance Specification



CONNECTOR REFERENCE

Performance Specification			
TEST DESCRIPTION	REQUIREMENT		PROCEDURE
Contact retention	Contact size	Pounds $\pm$ 10 percent	MIL-DTL-38999M Para. 4.5.20.1 EIA-364-29
	22HD	10	
	20HD	10	
Magnetic permeability	2 μ maximum		MIL-DTL-38999M Para. 4.5.48 EIA-364-54
Contact engaging /separation force	Contact forces shall meet AS39029 Table 9 requirements		AS39029C Para. 4.7.6 EIA-364-37
Temperature cycling (thermal shock)	No evidence of damage detrimental to the function of the connector		MIL-DTL-38999M Para. 4.5.4 EIA-364-32 Mated connectors, -65° C to +200° C
Random vibration, elevated temperature, 43g rms	No discontinuities of 1 microsecond or longer No resonance at frequencies less than 300 Hz		MIL-DTL-38999M Para. 4.5.23.2.3 with Figure 24 accessory load EIA-364-28 +200° C
Random vibration, ambient temperature, 49g rms	No discontinuities of 1 microsecond or longer		MIL-DTL-38999M Para. 4.5.23.2.4 EIA-364-28 Test Condition V
Sine vibration, 60g	No discontinuities of 1 microsecond or longer		MIL-DTL-38999M Para. 4.5.23.2.1 with Figure 24 accessory load 12 hours in each of 3 axes 4 hours at ambient, 4 hours at -55° C, 4 hours at +200° C
Mechanical shock, 300g	No discontinuities of 1 microsecond or longer		MIL-DTL-38999M Para. 4.5.24.1 EIA-364-27
High impact shock (901)	No discontinuities of 1 microsecond or longer No evidence of damage which could impair proper functioning.		MIL-DTL-38999M Para. 4.5.24.2 MIL-S-901 Grade A
Humidity, cyclic	Meet DWV and IR test		MIL-DTL-38999M Para. 4.5.26 EIA-364-31 Method 4 10 cycles, 10 days, 25 – 65° C 80 – 100% RH
Ozone exposure	No evidence of damage detrimental to the function of the connector		MIL-DTL-38999M Para. 4.5.29 EIA-364-14
Fluid immersion	No damage to plastic, elastomeric and bonding materials detrimental to the function of the connector. Connector shall meet coupling torque and DWV requirements when tested within 3 hours of immersion.		MIL-DTL-38999M Para. 4.5.30 EIA-364-10
Altitude immersion	No evidence of moisture on connector interface or contacts. At the end of the third cycle, while still submersed, connectors shall meet dielectric withstanding voltage and 1,000 megohms insulation resistance.		MIL-DTL-38999M Para. 4.5.9 EIA-364-03 75,000 feet
Altitude- low temperature	Connectors shall meet insulation resistance requirement while at -65° C and 100,000 ft. Connectors shall meet DWV requirement when returned to ambient conditions.		MIL-DTL-38999M Para. 4.5.21 EIA-364-105 -65° C 100,000 ft.
Thermal vacuum outgassing	All nonmetallic materials shall not exceed 1.0% Total Mass Loss and 0.1% Total Volatile Condensable Materials. Applicable only to connectors that have been subjected to optional thermal vacuum outgassing.		MIL-DTL-38999M Para. 4.5.42 ASTM E595
Salt Spray (dynamic)	Finish Code	Matl/Fin	Hours
	NF	Al/OD Cad	500
	MT	Al/Ni-PTFE	500
	ME	Al/EN	48
	ZR	Al/Zn-Ni	500
	Z1	SST/passivate	1000
	ZL	SST/Ni	1000
			MIL-DTL-38999M Para. 4.5.13.2 EIA-364-26 500 mating cycles

MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors

NASA and D38999, Class G Space-Grade Guidelines



Series 806 Connectors for Space Flight

The Series 806 is an ideal interconnect choice for space flight equipment. The series 806 features materials, finishes, and performance specifications that meet the MIL-DTL-38999 Class G requirements for space-grade connectors, except with higher density and lower weight.

Outgassing

Space flight equipment requires low-outgassing components in order to prevent degradation to optics and other sensitive instruments. Series 806 connectors contain nonmetallic materials such as rubber, plastic, adhesives and potting compounds which can give off gasses when subjected to a vacuum or high heat. Unless the connector is specially processed, the TML and CVCM can exceed allowable limits. The space industry has adopted a standardized test procedure, ASTM E595, to evaluate outgassing properties. The MIL-DTL-38999 specification Class G also details specific TVM and CVCM values in addition to finish specifications. In Glenair's 186T process, for example, connectors and connector materials are heated to 175° C at a vacuum of 5×10^{-6} Torr for 48 hours. Items under test are then weighed to calculate the Total Mass Loss (TML), which may not exceed 1.0% of the total initial mass. A collector plate is used to determine the Collected Volatile Condensable Material (CVCM), which may not exceed 0.1% of the total original specimen mass for Class G rated connectors. Glenair is able to offer outgas processing which assures all materials comply with their respective standards.

Note on Connector Material and Finish Options

Some types of metals are prohibited for space flight. "Pure Tin, Cadmium and Zinc shall not be used as a final finish on EEE parts." (NASA EEE-INST-002 Instructions for EEE Parts Selection, Screening, Qualification, and Derating). NASA recommends electroless nickel or gold finish on connector shells and gold finish for contacts.

Specifying Appropriate NASA Screening

1 Choose a NASA EEE-INST-002 Table 2A screening level. This table contains three screening levels: **Level 1** for missions requiring the highest reliability and lowest level of risk, **Level 2** for low to moderate risk missions, and **Level 3** missions where enhanced screening and inspection is not invoked.

2 Choose outgassing process and/or NASA inspection requirements. Nine options are available for NASA outgassing, see Table I for details. Cross reference Table II for inspections completed by screening level as required by NASA standards.

3 Select the modification code from the Table I and add it to the Series 806 part number. Example: 806-012-ME8-7PMA-**429**.

Table I: Outgassing per NASA Screening Levels and D38999, Class G

Table 1: Outgassing per MIL-DTL-38999, Class G						
Screening Level	Screening Type	No Outgas Processing	100% 48 Hour Oven Bakeout at +175° C	100% Thermal Vacuum (10 ⁻⁶ Torr), 24 Hour at +125° C	100% Thermal Vacuum (10 ⁻⁶ Torr), 48 Hour at +175° C	Mod Code
3	Standard Reliability		●	●		429L 186
		●				429
2	High Reliability		●	●		429A 429K
1	Highest Reliability	●		●		429B 429C 429J
			●			
MIL-DTL-38999, Class G (No Inspection)					●	186T

Table II: NASA EEE-INST-02, Table 2A Screening Levels

Inspection	Level 1	Level 2	Level 3
Visual	100%	100%	100%
Mechanical	2	2	
Dielectric Withstanding Voltage	2	2	
Insulation Resistance	2	2	
Contact Engagement & Separation Force	2		
Hermeticity (Sealed Receptacles Only)	100%	100%	100%
Coupling Force	2		

Note: required inspection quantity shown. Zero acceptance of failures allowed for all quantities inspected. Inspection is not performed/required for MIL-DTL-38999, Class G

Outgassing Properties of Materials used in Series 806 Mil-Aero connectors BEFORE BAKE OUT				
Component	Material	TML %	CVCM %	Test Reference
Front and Rear Insulator	High grade rigid dielectric	0.37	0.01	Glenair test at Pacific Testing Laboratories
Rear Grommet Interfacial Seal Peripheral Seal	Fluorosilicone/silicone blend, blue	0.3	0.03	Glenair test at Pacific Testing Laboratories
Front-To-Rear Insulator Bonding Material	Eccobond 104 A/B	0.18	0.05	Glenair test at Pacific Testing Laboratories
Insulator-to-Rubber Bonding Material	DC3145 RTV, per MIL-A-46146	2.52*	0.58*	NASA Test GSC28621
White Epoxy Ink for Silk-screening	Markem 7224 White	0.60	0.01	NASA Test GSC19896
Black Ink for Part Number Identification	Videojet #16-5900Q	0.6	0.001	Mfg. Data Sheet
Red Ink for Paint Bands	Markem 7224 Red	0.41	0.04	NASA Test GSC15084
Blue Ink for Paint Bands	Markem 7224 Blue	0.43	0.07	NASA Test GSC15082
Potting Comp, Solder Cup and PC Tail Connectors	Glenair Proprietary Potting	0.16	0.08	Glenair test at Pacific Testing Laboratories
*Material requires Bake Out in order to meet <1% TML & <0.10% CVCM Outgassing per ASTM E595				

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-012 Plug Connector



Features

- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, and #8 arrangements and combo layouts
- Aerospace-grade materials, construction
- Snap-in crimp contacts

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
Size 20HD contacts: 1800 VAC
Size 22HD contacts: 1300 VAC
Size 16 contacts: varies; contact factory
Size 12 contacts: contact factory
Size 8 contacts: varies; contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Altitude immersion: EIA-364-03 75,000 feet altitude


Connector Construction

- Shell and coupling nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Wire grommet: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Ground spring: copper alloy, nickel plating
- Contact retention clips: copper alloy
- Ratchet springs: stainless steel, passivated
- Retainer rings: stainless steel, passivated

Micro miniature 806-012 cable plugs save space and weight compared to conventional aerospace-grade circular connectors. Rugged ratchet mechanism and unique triple-start mating thread provide improved de-coupling resistance under vibration. Series 806 connectors are intended for use in harsh application areas such as unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes. Available with integral Nano Band platform or metric accessory threads. Insert arrangements support size #22HD, #20HD, #16, #12, and #8 snap-in, rear-release contacts.

How To Order						
SAMPLE PART NUMBER						
Product	806-012	-ME	8-3	S	M	A
Shell Material and Finish	806-012 = Cable Plug ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated					
Arrangement Number	See Table 1 (Shell Size - Insert Arr.)					
Contact Type	P = Pin A = Pin connector, less contacts S = Socket B = Socket connector, less contacts For datalink contacts (including El Ochito) order connector without contacts and order datalink contacts separately					
Shell Style	M = Metric accessory threads B = Nano Band platform					
Polarization	A B C D E F					

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						


Series 806**Mil-Aero Connectors****806-012 Plug Connector**


806-012 Plug Dimensions				
Shell Size	øA Max	B Thread	C Mating Thread	øD
7	.606 (15.39)	M8x1.0-6g-0.100R	.4375-.067P-.2L-TS-2B	.267 (6.78)
8	.676 (17.17)	M10x1.0-6g-0.100R	.5000-.067P-.2L-TS-2B	.327 (8.31)
9	.771 (19.58)	M12x1.0-6g-0.100R	.5625-.067P-.2L-TS-2B	.406 (10.31)
10	.832 (21.13)	M14x1.0-6g-0.100R	.6250-.067P-.2L-TS-2B	.484 (12.29)
11	.890 (22.61)	M15x1.0-6g-0.100R	.6875-.067P-.2L-TS-2B	.524 (13.31)
12	.950 (24.13)	M17x1.0-6g-0.100R	.7500-.067P-.2L-TS-2B	.603 (15.32)
14	1.110 (28.19)	M19x1.0-6g-0.100R	.8750-.067P-.2L-TS-2B	.681 (17.30)
16	1.170 (29.72)	M22x1.0-6g-0.100R	1.0000-.067P-.2L-TS-2B	.782 (19.86)
18	1.350 (34.29)	M25x1.0-6g-0.100R	1.1250-.067P-.2L-TS-2B	.899 (22.83)
20	1.470 (37.34)	M28x1.0-6g-0.100R	1.2500-.067P-.2L-TS-2B	1.043 (26.49)
22	1.600 (40.64)	M31x1.0-6g-0.100R	1.3750-.067P-.2L-TS-2B	1.155 (29.34)
24	1.710 (43.43)	M34x1.0-6g-0.100R	1.5000-.067P-.2L-TS-2B	1.273 (32.33)

NOTES:

1. Boot groove for use with 809-060 Heat Shrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband

SERIES
806
MIL-AERO




**806-013 Receptacle Dimensions**

Shell Size	A Max	B Thread	C	D Mating Thread	øE	F Max	G Max	H
7	.750 (19.05)	M8x1.0-6g-0.100R	.469 (11.91)	.4375-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	.968 (24.59)	.265 (6.73)
8	.822 (20.88)	M10x1.0-6g-0.100R	.531 (13.49)	.5000-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.040 (26.42)	.327 (8.31)
9	.885 (22.48)	M12x1.0-6g-0.100R	.594 (15.09)	.5625-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.130 (28.70)	.406 (10.31)
10	.913 (23.19)	M14x1.0-6g-0.100R	.625 (15.88)	.6250-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.174 (29.82)	.484 (12.29)
11	.944 (23.98)	M15x1.0-6g-0.100R	.670 (17.02)	.6875-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.200 (30.48)	.524 (13.31)
12	1.040 (26.42)	M17x1.0-6g-0.100R	.765 (19.43)	.7500-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.354 (34.39)	.603 (15.32)
14	1.133 (28.78)	M19x1.0-6g-0.100R	.859 (21.82)	.8750-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.510 (38.35)	.681 (17.30)
16	1.227 (31.17)	M22x1.0-6g-0.100R	.938 (23.83)	1.0000-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.620 (41.15)	.782 (19.86)
18	1.320 (33.53)	M25x1.0-6g-0.100R	1.016 (25.81)	1.1250-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.784 (45.31)	.899 (22.83)
20	1.444 (36.68)	M28x1.0-6g-0.100R	1.109 (28.17)	1.2500-.067P-.2L-TS-2A	.154 (3.91)	.125 (3.18)	1.910 (48.51)	1.043 (26.49)
22	1.570 (39.88)	M31x1.0-6g-0.100R	1.203 (30.56)	1.3750-.067P-.2L-TS-2A	.154 (3.91)	.125 (3.18)	2.083 (52.91)	1.155 (29.34)
24	1.696 (43.08)	M34x1.0-6g-0.100R	1.312 (33.32)	1.5000-.067P-.2L-TS-2A	.154 (3.91)	.125 (3.18)	2.200 (55.88)	1.273 (32.33)

806-013 Panel Cutout Dimensions

Shell Size	A SQ	øB with Clinch Nut	øB without Clinch Nut	øC
7	.469 (11.91)	.128 (3.25)	.128 (3.25)	.443 (11.25)
8	.531 (13.49)	.128 (3.25)	.128 (3.25)	.505 (12.83)
9	.594 (15.09)	.128 (3.25)	.128 (3.25)	.572 (14.53)
10	.625 (15.88)	.128 (3.25)	.128 (3.25)	.640 (16.26)
11	.670 (17.02)	.128 (3.25)	.128 (3.25)	.707 (17.96)
12	.765 (19.43)	.128 (3.25)	.128 (3.25)	.762 (19.35)
14	.859 (21.82)	.128 (3.25)	.128 (3.25)	.885 (22.48)
16	.938 (23.83)	.128 (3.25)	.128 (3.25)	1.010 (25.65)
18	1.016 (25.81)	.128 (3.25)	.128 (3.25)	1.120 (28.45)
20	1.109 (28.17)	.128 (3.25)	.154 (3.91)	1.270 (32.26)
22	1.203 (30.56)	.128 (3.25)	.154 (3.91)	1.395 (35.43)
24	1.312 (33.32)	.128 (3.25)	.154 (3.91)	1.520 (38.61)




ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-019 In-Line Receptacle Connectors



Features

- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, and #8 arrangements and combo layouts
- Aerospace-grade materials, construction
- Snap-in crimp contacts

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#20HD contacts: 1800 VAC
#22HD contacts: 1300 VAC
#16 contacts: varies; contact factory
#12 contacts: varies; contact factory
#8 contacts: varies; contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude

Connector Construction


- Shell: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Wire grommet: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Peripheral seal: fluorosilicone
- Contact retention clips: copper alloy
- Retainer rings: stainless steel, passivated

806-019 Micro miniature Series 806 connectors save size and weight compared to conventional aerospace-grade circular connectors. These high performance connectors are suitable for harsh environmental areas such as unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes. Available with integral Nano Band platform or with metric accessory threads. Insert arrangements support size #22HD, #20HD, #16, #12, and #8 snap-in, rear-release contacts.

How To Order						
SAMPLE PART NUMBER		806-019	-NF	14-20	P	B A
Product	806-019 = In-Line Receptacle					
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated					
Arrangement Number (Shell Size - Insert Arr.)	See Table 1					
Contact Type	P = Pin S = Socket For datalink contacts (including El Ochito) order connector without contacts and order datalink contacts separately		A = Pin connector, less contacts B = Socket connector, less contacts			
Shell Style	M = Metric accessory threads B = Nano Band platform					
Polarization	A B C D E F					

Table 1: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						



806-019 Receptacle Dimensions						
Shell Size	A ±.010 (0.25) ±0.25 (6.35)	B Thread	C Mating Thread	D Max	øE	øF
7	.440 (11.18)	M8x1.0-6g-0.100R	.4375-.067P-.2L-TS-2A	.100 (2.54)	.572 (14.53)	.265 (6.73)
8	.545 (13.84)	M10x1.0-6g-0.100R	.5000-.067P-.2L-TS-2A	.100 (2.54)	.635 (16.13)	.327 (8.31)
9	.612 (15.54)	M12x1.0-6g-0.100R	.5625-.067P-.2L-TS-2A	.100 (2.54)	.702 (17.83)	.406 (10.31)
10	.680 (17.27)	M14x1.0-6g-0.100R	.6250-.067P-.2L-TS-2A	.100 (2.54)	.770 (19.56)	.484 (12.29)
11	.747 (18.97)	M15x1.0-6g-0.100R	.6875-.067P-.2L-TS-2A	.100 (2.54)	.837 (21.26)	.524 (13.31)
12	.803 (20.40)	M17x1.0-6g-0.100R	.7500-.067P-.2L-TS-2A	.100 (2.54)	.893 (22.68)	.603 (15.32)
14	.925 (23.50)	M19x1.0-6g-0.100R	.8750-.067P-.2L-TS-2A	.100 (2.54)	1.015 (25.78)	.681 (17.30)
16	1.050 (26.67)	M22x1.0-6g-0.100R	1.0000-.067P-.2L-TS-2A	.100 (2.54)	1.140 (28.96)	.782 (19.86)
18	1.160 (29.46)	M25x1.0-6g-0.100R	1.1250-.067P-.2L-TS-2A	.100 (2.54)	1.250 (31.75)	.899 (22.83)
20	1.310 (33.27)	M28x1.0-6g-0.100R	1.2500-.067P-.2L-TS-2A	.125 (3.18)	1.400 (35.56)	1.043 (26.49)
22	1.435 (36.45)	M31x1.0-6g-0.100R	1.3750-.067P-.2L-TS-2A	.125 (3.18)	1.525 (38.73)	1.155 (29.34)
24	1.560 (39.62)	M34x1.0-6g-0.100R	1.5000-.067P-.2L-TS-2A	.125 (3.18)	1.650 (41.91)	1.273 (32.33)

NOTES:


1. Boot groove for use with 809-060 Heat Shrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-020 Jam-nut Receptacle Connectors



Features

- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, and #8 arrangements and combo layouts
- Aerospace-grade materials, construction
- Snap-in crimp contacts

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#20HD contacts: 1800 VAC
#22HD contacts: 1300 VAC
#16 contacts: varies; contact factory
#12 contacts: varies; contact factory
#8 contacts: varies; contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude

Connector Construction

- Shell and jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Wire grommet: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone
- Contact retention clips: copper alloy
- Retainer rings: stainless steel, passivated

806-020 Micro miniature Series 806 connectors save size and weight compared to conventional aerospace-grade circular connectors. These high performance connectors are suitable for harsh environmental areas such as unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes. Integral Nano Band platform or metric accessory threads available. Insert arrangements support size #22HD, #20HD, #16, #12, and #8 snap-in, rear-release contacts.

How To Order						
SAMPLE PART NUMBER		806-020	-ME	10-15	S	M A
Product	806-020 = Jam-nut Receptacle					
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated					
Arrangement Number (Shell Size - Insert Arr.)	See Table 1					
Contact Type	P = Pin S = Socket For datalink contacts (including El Ochito) order connector without contacts and order datalink contacts separately		A = Pin connector, less contacts B = Socket connector, less contacts			
Shell Style	M = Metric accessory threads B = Nano band platform					
Polarization	A B C D E F					


Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

806-020 Jam-nut Receptacle Connectors



806-020 Receptacle Dimensions							
Shell Size	øA Max	B Thread	C Max	D Mating Thread	E Max	F Thread	øH
7	.918 (23.32)	M8x1.0-6g-0.100R	.858 (21.79)	.5000-.067P-.2L-TS-2A	.100 (2.54)	M13x1.0-6g-0.100R	.265 (6.73)
8	.980 (24.89)	M10x1.0-6g-0.100R	.920 (23.37)	.5000-.067P-.2L-TS-2A	.100 (2.54)	M15x1.0-6g-0.100R	.327 (8.31)
9	1.040 (26.42)	M12x1.0-6g-0.100R	.980 (24.89)	.5625-.067P-.2L-TS-2A	.100 (2.54)	M16x1.0-6g-0.100R	.406 (10.31)
10	1.110 (28.19)	M14x1.0-6g-0.100R	1.050 (26.67)	.6250-.067P-.2L-TS-2A	.100 (2.54)	M18x1.0-6g-0.100R	.484 (12.29)
11	1.160 (29.46)	M15x1.0-6g-0.100R	1.110 (28.19)	.6875-.067P-.2L-TS-2A	.100 (2.54)	M19x1.0-6g-0.100R	.524 (13.31)
12	1.230 (31.24)	M17x1.0-6g-0.100R	1.170 (29.72)	.7500-.067P-.2L-TS-2A	.100 (2.54)	M21x1.0-6g-0.100R	.603 (15.32)
14	1.360 (34.54)	M19x1.0-6g-0.100R	1.320 (33.53)	.8750-.067P-.2L-TS-2A	.100 (2.54)	M24x1.0-6g-0.100R	.681 (17.30)
16	1.515 (38.48)	M22x1.0-6g-0.100R	1.444 (36.68)	1.0000-.067P-.2L-TS-2A	.100 (2.54)	M27x1.0-6g-0.100R	.782 (19.86)
18	1.610 (40.89)	M25x1.0-6g-0.100R	1.570 (39.88)	1.1250-.067P-.2L-TS-2A	.100 (2.54)	M30x1.0-6g-0.100R	.899 (22.83)
20	1.850 (46.99)	M28x1.0-6g-0.100R	1.760 (44.70)	1.2500-.067P-.2L-TS-2A	.128 (3.25)	M34x1.0-6g-0.100R	1.043 (26.49)
22	2.010 (51.05)	M31x1.0-6g-0.100R	1.913 (48.59)	1.3750-.067P-.2L-TS-2A	.128 (3.25)	M37x1.0-6g-0.100R	1.155 (29.34)
24	2.195 (55.75)	M34x1.0-6g-0.100R	2.070 (52.58)	1.5000-.067P-.2L-TS-2A	.128 (3.25)	M41x1.0-6g-0.100R	1.273 (32.33)

Jam-Nut Cutout



806-020 Jam-nut D-Hole Dimensions		
Shell Size	øA +.005/-0.00 (+0.13/-0.00)	B +.005/-0.00 (+0.13/-0.00)
7	.522 (13.26)	.224 (5.69)
8	.601 (15.27)	.256 (6.50)
9	.640 (16.26)	.287 (7.29)
10	.719 (18.26)	.318 (8.08)
11	.759 (19.28)	.350 (8.89)
12	.837 (21.26)	.381 (9.68)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)

NOTES:

1. Boot groove for use with 809-463 Thermo-Rex Autoshrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband
3. High temperature crown ring pin and socket contacts required to meet higher operating temps

Series 806 Mil-Aero Connectors

806-021 Jam-nut Receptacle, PC Tail or Solder Cup Contacts



Features

- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight
- Aerospace-grade materials, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell and jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Potting compound: epoxy
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone

806-021 panel mount jam-nut receptacles feature potted-in-place printed circuit board terminals, integral standoffs and threaded holes for secure attachment to rigid or flex circuit boards. Gold-plated terminals are factory-installed, non-removeable and sealed with epoxy. Boss on shell flange guarantees correct connector orientation. These high performance connectors are suitable for harsh environmental areas such as unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes.

How To Order						
SAMPLE PART NUMBER		806-021	-ME	10-15	S	2 A
Product	806-021 = Jam-nut Receptacle with PC Tails					
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated					
Arrangement Number (Shell Size - Insert Arr.)	See Table 1					
Contact Type	P = Pin S = Socket E = Solder Cup, Pin F = Solder Cup, Socket Not Available with EI Ochito contacts see 806-039					
PC Tail Length	PC Tail Length Solder Cup 1 = .125" (3.18 mm.) Omit = Soldercup 2 = .250" (6.35 mm.)					
Polarization	A B C D E F					

Table I: Shell Size - Insert Arrangement


Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-021 Jam-nut Receptacle, PC Tail Contacts



806-021 Receptacle Dimensions

Shell Size	øA Max	B Thread	C Max	D	E Max	F Mating Thread	G Flat
7	.908 (23.06)	M8x1.0-6g-0.100R	.848 (21.54)	.489 (12.42)	.100 (2.54)	.4375-.067P-.2L-TS-2A	.463 (11.76)
8	.980 (24.89)	M15x1.0-6g-0.100R	.920 (23.37)	.534 (13.56)	.100 (2.54)	.5000-.067P-.2L-TS-2A	.534 (13.56)
9	1.040 (26.42)	M16x1.0-6g-0.100R	.980 (24.89)	.579 (14.71)	.100 (2.54)	.5625-.067P-.2L-TS-2A	.585 (14.86)
10	1.110 (28.19)	M18x1.0-6g-0.100R	1.050 (26.67)	.679 (17.25)	.100 (2.54)	.6250-.067P-.2L-TS-2A	.656 (16.66)
11	1.160 (29.46)	M19x1.0-6g-0.100R	1.110 (28.19)	.734 (18.64)	.100 (2.54)	.6875-.067P-.2L-TS-2A	.707 (17.96)
12	1.230 (31.24)	M21x1.0-6g-0.100R	1.170 (29.72)	.804 (20.42)	.100 (2.54)	.7500-.067P-.2L-TS-2A	.777 (19.74)
14	1.360 (34.54)	M24x1.0-6g-0.100R	1.320 (33.53)	.891 (22.63)	.100 (2.54)	.8750-.067P-.2L-TS-2A	.899 (22.83)
16	1.515 (38.48)	M27x1.0-6g-0.100R	1.444 (36.68)	1.049 (26.64)	.100 (2.54)	1.0000-.067P-.2L-TS-2A	1.020 (25.91)
18	1.610 (40.89)	M30x1.0-6g-0.100R	1.570 (39.88)	1.148 (29.16)	.100 (2.54)	1.1250-.067P-.2L-TS-2A	1.142 (29.01)
20	1.850 (46.99)	M34x1.0-6g-0.100R	1.760 (44.70)	1.252 (31.80)	.128 (3.25)	1.2500-.067P-.2L-TS-2A	1.283 (32.59)
22	2.010 (51.05)	M37x1.0-6g-0.100R	1.913 (48.59)	1.369 (34.77)	.128 (3.25)	1.3750-.067P-.2L-TS-2A	1.405 (35.69)
24	2.195 (55.75)	M41x1.0-6g-0.100R	2.070 (52.58)	1.509 (38.33)	.128 (3.25)	1.5000-.067P-.2L-TS-2A	1.546 (39.27)


806-021 Jam-nut D-Hole Dimensions

Shell Size	øA +.005/-0.00 (+0.13/-0.00)	B +.005/-0.00 (+0.13/-0.00)
7	.522 (13.26)	.224 (5.69)
8	.601 (15.27)	.256 (6.50)
9	.640 (16.26)	.287 (7.29)
10	.719 (18.26)	.318 (8.08)
11	.759 (19.28)	.350 (8.89)
12	.837 (21.26)	.381 (9.68)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)

PC Tail Diameter


Contact Size	Diameter
#22 HD	.020 (0.51)
#20 HD	.030 (0.76)
#16	.062 (1.57)
#12	.094 (2.39)
#8	.180 (4.57)

Jam-Nut Cutout



Series 806 Mil-Aero Connectors

806-022 Square Flange Receptacle, PC Tail or Solder Cup Contacts



Features

- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight
- Aerospace-grade materials, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#22HD: 1800 VAC
#20HD: 1300 VAC
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction


- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Potting compound: epoxy
- Interfacial seal and peripheral seal: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Clinch nuts: stainless steel, passivated

806-022 square flange receptacles feature potted-in-place printed circuit board terminals, integral standoffs and threaded holes for attachment to rigid or flex circuit boards. Series 806 connectors save size and weight. Suitable for harsh environmental areas such as unpressurized aircraft zones subject to extreme conditions.

How To Order							
SAMPLE PART NUMBER		806-022	-ME	11-19	P	1	C A
Product	806-022 = Square Flange Receptacle, PC Tails						
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated						
Arrangement Number	See Table 1 (Shell Size - Insert Arr.)						
Contact Type	P = Pin S = Socket E = Solder Cup, Pin F = Solder Cup, Socket Not Available with El Ochito contacts see 806-040						
Termination Type	PC Tail Length Solder Cup 1 = .125" (3.18 mm.) Omit = Soldercup 2 = .250" (6.35 mm.)						
Mounting Hole Style	T = Thru holes C = Clinch nut flange, #4-40, M45938/6-4C (rear panel mounting); consult factory for SST material						
Polarizing Position	A B C D E F; (See Page 7)						

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

**806-022 Receptacle Dimensions**


Shell Size	A Max	B	C Max	D	øE	F Max	G Mating Thread
7	.968 (24.59)	.469 (11.91)	.750 (19.05)	.489 (12.42)	.128 (3.25)	.100 (2.54)	.4375-.067P-.2L-TS-2A
8	1.040 (26.42)	.531 (13.49)	.822 (20.88)	.534 (13.56)	.128 (3.25)	.100 (2.54)	.5000-.067P-.2L-TS-2A
9	1.130 (28.70)	.594 (15.09)	.885 (22.48)	.579 (14.71)	.128 (3.25)	.100 (2.54)	.5625-.067P-.2L-TS-2A
10	1.174 (29.82)	.625 (15.88)	.913 (23.19)	.679 (17.25)	.128 (3.25)	.100 (2.54)	.6250-.067P-.2L-TS-2A
11	1.240 (31.50)	.670 (17.02)	.960 (24.38)	.734 (18.64)	.128 (3.25)	.100 (2.54)	.6875-.067P-.2L-TS-2A
12	1.354 (34.39)	.765 (19.43)	1.040 (26.42)	.804 (20.42)	.128 (3.25)	.100 (2.54)	.7500-.067P-.2L-TS-2A
14	1.510 (38.35)	.859 (21.82)	1.133 (28.78)	.891 (22.63)	.128 (3.25)	.100 (2.54)	.8750-.067P-.2L-TS-2A
16	1.620 (41.15)	.938 (23.83)	1.242 (31.55)	1.049 (26.64)	.128 (3.25)	.100 (2.54)	1.0000-.067P-.2L-TS-2A
18	1.784 (45.31)	1.016 (25.81)	1.343 (34.11)	1.148 (29.16)	.128 (3.25)	.100 (2.54)	1.1250-.067P-.2L-TS-2A
20	1.910 (48.51)	1.109 (28.17)	1.444 (36.68)	1.252 (31.80)	.154 (3.91)	.125 (3.18)	1.2500-.067P-.2L-TS-2A
22	2.083 (52.91)	1.203 (30.56)	1.570 (39.88)	1.369 (34.77)	.154 (3.91)	.125 (3.18)	1.3750-.067P-.2L-TS-2A
24	2.200 (55.88)	1.312 (33.32)	1.704 (43.28)	1.509 (38.33)	.154 (3.91)	.125 (3.18)	1.5000-.067P-.2L-TS-2A

806-022 Panel Cutout Dimensions

Shell Size	A Sq	øB with Clinch Nut	øB without Clinch Nut	øC
7	.469 (11.91)	.128 (3.25)	.128 (3.25)	.443 (11.25)
8	.531 (13.49)	.128 (3.25)	.128 (3.25)	.509 (12.93)
9	.594 (15.09)	.128 (3.25)	.128 (3.25)	.577 (14.66)
10	.625 (15.88)	.128 (3.25)	.128 (3.25)	.645 (16.38)
11	.670 (17.02)	.128 (3.25)	.128 (3.25)	.712 (18.08)
12	.765 (19.43)	.128 (3.25)	.128 (3.25)	.768 (19.51)
14	.859 (21.82)	.128 (3.25)	.128 (3.25)	.890 (22.61)
16	.938 (23.83)	.128 (3.25)	.128 (3.25)	1.015 (25.78)
18	1.016 (25.81)	.128 (3.25)	.128 (3.25)	1.125 (28.58)
20	1.109 (28.17)	.128 (3.25)	.154 (3.91)	1.275 (32.39)
22	1.203 (30.56)	.128 (3.25)	.154 (3.91)	1.400 (35.56)
24	1.312 (33.32)	.128 (3.25)	.154 (3.91)	1.525 (38.73)

PC Tail Diameter


Contact Size	Diameter
#22 HD	.020 (0.51)
#20 HD	.030 (0.76)
#16	.062 (1.57)
#12	.094 (2.39)
#8	.180 (4.57)

**NOTES**

1. Integral PCB Stand off 4x 4-40 UNC .156 (3.96) min thread and locating post

Series 806 Mil-Aero Connectors

806-029 Flange Receptacle, Bulkhead Feed-Thru



806-029 Bulkhead feed-thrus eliminate the need to permanently fix cable harnesses to panels — affording increased system flexibility, superior mechanical integrity, and greater serviceability. Environmental versions offer IP67 level sealing.

Features

- Power to a given contact on one end will result in power to contact directly opposite, regardless of identification letter.
- Electrical safety limits must be established by user. Peak voltage, switching surge, transient, ect. Should be used to determine to safe application.
- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, and #8 arrangements and combo layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#20HD contacts: 1800 VAC
#22HD contacts: 1300 VAC
#16 contacts: varies; contact factory
#12 contacts: varies; contact factory
#8 contacts: varies; contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude

Connector Construction


- Shell - AL alloy or CRES / see Table II.
- Insulators - High grade rigid dielectirc.
- Interfacial seal, grommet - fluorosilicone blend
- Contact - copper alloy / gold plate per mil-g-45204, Type II, Grade C, Class 5 (.000050 Inch) over a minimum of .000050 Inch nickel plating.

How To Order

SAMPLE PART NUMBER									
	806-029	-ME	8	-7	P	C	A	-01	
Product	806-029 = Square Mount Receptacle, Bulkhead Feed -Thru								
Finish Symbol	See Table III								
Shell Size	See Table II								
Insert Arrangement	See Table II; adjust table numbering as needed								
Contact Style	See Table IV								
Panel Mounting Hole Style	C = Clinch Nut, 4-40 THD M45938/6-4C (For Rear Panel Mounting Only) T = Thru Hole								
Alernate Keyway Polarization Code	A B C D E F								
Panel Accommodation	(See Table VI) -01 = .0625/.125 THK -02 = .0625/.250 THK -03 = .0625/.500 THK								

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						



CONTACT STYLE "P" SHOWN

Table II

Shell size	A Max	C	D Mating Thread	ø E Thru Hole	F Max	G Max
8	0.822 (20.88)	0.531 (13.49)	.5000-.067P-.2L-TS-2A	0.128 (3.25)	0.100 (2.54)	1.040 (26.42)
9	0.885 (22.48)	0.594 (15.09)	.5625-.067P-.2L-TS-2A			1.130 (28.70)
10	0.913 (23.19)	0.625 (15.88)	.6250-.067P-.2L-TS-2A			1.174 (29.82)
11	0.960 (24.38)	0.670 (17.02)	.6875-.067P-.2L-TS-2A			1.200 (30.48)
12	1.040 (26.42)	0.765 (19.43)	.7500-.067P-.2L-TS-2A			1.354 (34.39)
14	1.133 (28.78)	0.859 (21.82)	.8750-.067P-.2L-TS-2A			1.510 (38.35)
16	1.227 (31.17)	0.938 (23.83)	1.0000-.067P-.2L-TS-2A			1.620 (41.15)
18	1.320 (33.53)	1.016 (25.81)	1.1250-.067P-.2L-TS-2A			1.784 (45.31)
20	1.444 (36.68)	1.109 (28.17)	1.2500-.067P-.2L-TS-2A			1.910 (48.51)
22	1.570 (39.88)	1.203 (30.56)	1.3750-.067P-.2L-TS-2A	0.154 (3.91)	0.125 (3.18)	2.083 (52.91)
24	1.696 (43.08)	1.312 (33.32)	1.5000-.067P-.2L-TS-2A			2.200 (55.88)

PANEL MOUNT INFO




Table III

Code	Material	Finish
NF	Aluminum Alloy	Cad/Olive Drab Over Electroless Nickel
MT		Nickel-PTFE
ME		Electroless Nickel
ZR		Zinc Nickel, Black
Z1	Stainless Steel	Passivated
ZL		Electro-Deposited Nickel

Table IV

Contact Style	Description 6
P	Pin Contact On Panel Side (Socket Opposite)
S	Socket Contact On Panel Side (Pin Opposite)
PP	Pins On Both Sides
SS	Socket On Both Sides

Table V

Panel Accommodation	B Max
-01	1.29 (32.77)
-02	1.40 (35.56)
-03	1.65 (41.91)


Mount Info Table VI

Size	ø J	H	
		With Clinch Nut	Without Clinch Nut
8	.505 (12.83)	.128 (3.25)	.128 (3.25)
9	.572 (14.53)		
10	.640 (16.26)		
11	.707 (17.96)		
12	.762 (19.35)		
14	.885 (22.48)		
16	1.01 (25.65)		
18	1.12 (28.45)		
20	1.27 (32.26)		
22	1.395 (35.43)		.154 (3.91)
24	1.520 (38.61)		

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806-030 Jam Nut Receptacle, Bulkhead Feed-Thru



Features

- Power to a given contact on one end will result in power to contact directly opposite, regardless of identification letter.
- Electrical safety limits must be established by user. Peak voltage, switching surge, transient, ect. Should be used to determine to safe application.
- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, and #8 arrangements and combo layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#20HD contacts: 1800 VAC
#22HD contacts: 1300 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude

Connector Construction

- Shell - AL alloy or CRES / see Table II.
- Insulators - High grade rigid dielectirc.
- Interfacial seal, grommet - fluorosilicone blend
- Contact - copper alloy / gold plate per MIL-G-45204, Type II, Grade C, Class 5 (.000050 Inch) over a minimum of .000050 Inch nickel plating.

806-030 Bulkhead feed-thrus eliminate the need to permanently fix cable harnesses to panels — affording increased system flexibility, superior mechanical integrity, and greater serviceability. Environmental versions offer IP67 level sealing.

How To Order							
SAMPLE PART NUMBER		806-030	-ME	8	-7	P	A -01
Product	806-030 = Jam-Nut Receptacle, Bulkhead Feed -Thru						
Material/Finish	See Table III						
Shell Size	See Table II						
Insert Arrangement	See Table II; adjust table numbering as needed						
Contact Style	See Table IV						
Alernate Keyway Polarization Code	A B C D E F						
Panel Accommodation	(See Table VI) -01 = .0625/.125 THK -02 = .0625/.250 THK -03 = .0625/.500 THK						

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1		1				22-5					5
9-11	11					10-2		2				24-8					8
10-15	15					11-4		4				10-8A	6		2		
11-19	19					12-5		5				11-13	11		2		
12-26	26					14-7		7				12-27	26		1		
14-39	39					16-12		12				14-21	17		4		
16-60	60					18-15		15				16-41	37		4		
18-85	85					20-22		22				18-59	55		4		
20-110	110					22-24		24				11-14	13			1	
22-140	140					24-35		35				12-14	12			2	
24-186	186					9-1			1			14-22	20			2	
8-3		3				12-2			2			16-32	28			4	
9-5		5				14-3			3			16-42	40			2	
10-8		8				16-4			4			18-62	60			2	
11-10		10				16-7			7			14-20A	19				1
12-15		15				18-8			8			16-22	20				2
14-20		20				20-11			11			18-21	18				3
16-31		31				22-13			13			20-28	24				4
18-41		41				24-19			19			22-44	40				4
20-55		55				10-1				1		24-97	93				4
						16-2				2							

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors



806-030 Jam Nut Receptacle, Bulkhead Feed-Thru





Table II

Shell size	A Max	C Mating Thread	D Max	Ø E Max	F Thread
8	.920 (23.37)	.5000-.067P-.2L-TS-2A	.100 (2.54)	.980 (24.89)	M15 X 1-6g-.100R
9	.980 (24.89)	.5625-.067P-.2L-TS-2A		1.040 (26.42)	M16 X 1-6g-.100R
10	1.050 (26.67)	.6250-.067P-.2L-TS-2A		1.110 (28.19)	M18 X 1-6g-.100R
11	1.110 (28.19)	.6875-.067P-.2L-TS-2A		1.160 (29.46)	M19 X 1-6g-.100R
12	1.170 (29.72)	.7500-.067P-.2L-TS-2A		1.230 (31.24)	M21 X 1-6g-.100R
14	1.320 (33.53)	.8750-.067P-.2L-TS-2A		1.360 (34.54)	M24 X 1-6g-.100R
16	1.444 (36.68)	1.0000-.067P-.2L-TS-2A		1.515 (38.48)	M27 X 1-6g-.100R
18	1.570 (39.88)	1.1250-.067P-.2L-TS-2A		1.610 (40.89)	M30 X 1-6g-.100R
20	1.760 (44.70)	1.2500-.067P-.2L-TS-2A	.125 (3.18)	1.850 (46.99)	M34 X 1-6g-.100R
22	1.913 (48.59)	1.3750-.067P-.2L-TS-2A		2.010 (51.05)	M37 X 1-6g-.100R
24	2.070 (52.58)	1.5000-.067P-.2L-TS-2A		2.195 (55.75)	M41 X 1-6g-.100R

RECOMMENDED MOUNTING HOLE DIMENSIONS



Mount Info Table VI

Size	G + .005 - .005	Ø H + .005 - .005
8	.256 (6.50)	.601 (15.27)
9	.287 (7.29)	.640 (16.26)
10	.318 (8.08)	.719 (18.26)
11	.350 (8.89)	.759 (19.28)
12	.381 (9.68)	.837 (21.26)
14	.443 (11.25)	.955 (24.26)
16	.505 (12.83)	1.073 (27.25)
18	.568 (14.43)	1.192 (30.28)
20	.630 (16.00)	1.349 (34.26)
22	.693 (17.60)	1.467 (37.26)
24	.755 (19.18)	1.624 (41.25)

Table III

Code	Material	Finish
NF	Aluminum Alloy	Cad/Olive Drab Over Electroless Nickel
MT		Nickel-PTFE
ME		Electroless Nickel (96 Hour Salt Spray)
ZR		Zinc Nickel, Black
Z1	Stainless Steel	Passivated
ZL		Electro-Deposited Nickel

Table IV


Contact Style	Description 6
P	Pin Contact On Panel Side (Socket Opposite)
S	Socket Contact On Panel Side (Pin Opposite)
PP	Pins On Both Sides
SS	Socket On Both Sides

Table V

Panel Accommodation	B Max
-01	1.27 (32.26)
-02	1.40 (35.56)
-03	1.65 (41.91)

Series 806 Mil-Aero Connectors

806-058 Receptacle Coax PC Tail Contacts for 50 / 75 ohm Cable



Features

- Triple-start stub ACME mating thread
- Size #16, 50 ohm or #12, 75 ohm contacts
- Aerospace-grade materials, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage
#16 coax contacts: 800 VAC, VSWR rating 1.5:1 maximum up to 700 MHz.
#12 coax contacts: varies, see contacts section
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell and jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Potting compound: epoxy
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone

806-058 Panel mount jam-nut receptacle is similar to our 806-022 but adds size 16 and 12 potted-in-place coaxial contacts for 50 or 75 ohm cable. Connector includes integral standoffs and threaded holes for secure attachment to rigid or flex circuit boards. Gold-plated terminals are factory-installed, non-removeable and sealed with epoxy. Boss on shell flange guarantees correct connector orientation. These high performance connectors are suitable for harsh environmental areas such as unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes.

How To Order					
SAMPLE PART NUMBER		806-058	-ME	12-5	P1
Product	806-058 = Jam-nut Receptacle with PC Tails				
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated				
Arrangement Number (Shell Size - Insert Arr.)	See Table 1				
Contact Type	See Coax Contacts Table				
Polarization	A B C D E F				

Table I: Shell Size - Insert Arrangement											
Contact Layout	Number of Contacts			Contact Layout	Number of Contacts			Contact Layout	Number of Contacts		
	22HD	16	12		22HD	16	12		22HD	16	12
8-1		1		9-1			1	11-13	11	2	
10-2		2		12-2			2	12-27	26	1	
11-4		4		14-3			3	14-21	17	4	
12-5		5		16-4			4	16-41	37	4	
14-7		7		16-7			7	18-59	55	4	
16-12		12		18-8			8	11-14	13		1
18-15		15		20-11			11	12-14	12		2
20-22		22		22-13			13	14-22	20		2
22-24		24		24-19			19	16-32	28		4
24-35		35		10-8A	6	2		16-42	40		2
								18-62	60		2



COAX PCB FOOTPRINT


Coax Contacts		
Contact Description		Contact Type
50 ohm Coax	Pin	P1
	Socket	S1
75 ohm Coax	Pin	P2
	Socket	S2

806-058 Receptacle Dimensions						
Shell Size	øA Max	B Thread	C Max	D	E Max	F Mating Thread
8	.980 (24.89)	M15x1.0-6g-0.100R	.920 (23.37)	.534 (13.56)	.100 (2.54)	.5000-.067P-2L-TS-2A
9	1.040 (26.42)	M16x1.0-6g-0.100R	.980 (24.89)	.579 (14.71)	.100 (2.54)	.5625-.067P-2L-TS-2A
10	1.110 (28.19)	M18x1.0-6g-0.100R	1.050 (26.67)	.679 (17.25)	.100 (2.54)	.6250-.067P-2L-TS-2A
11	1.160 (29.46)	M19x1.0-6g-0.100R	1.110 (28.19)	.734 (18.64)	.100 (2.54)	.6875-.067P-2L-TS-2A
12	1.230 (31.24)	M21x1.0-6g-0.100R	1.170 (29.72)	.804 (20.42)	.100 (2.54)	.7500-.067P-2L-TS-2A
14	1.360 (34.54)	M24x1.0-6g-0.100R	1.320 (33.53)	.891 (22.63)	.100 (2.54)	.8750-.067P-2L-TS-2A
16	1.515 (38.48)	M27x1.0-6g-0.100R	1.444 (36.68)	1.049 (26.64)	.100 (2.54)	1.0000-.067P-2L-TS-2A
18	1.610 (40.89)	M30x1.0-6g-0.100R	1.570 (39.88)	1.148 (29.16)	.100 (2.54)	1.1250-.067P-2L-TS-2A
20	1.850 (46.99)	M34x1.0-6g-0.100R	1.760 (44.70)	1.252 (31.80)	.128 (3.25)	1.2500-.067P-2L-TS-2A
22	2.010 (51.05)	M37x1.0-6g-0.100R	1.913 (48.59)	1.369 (34.77)	.128 (3.25)	1.3750-.067P-2L-TS-2A
24	2.195 (55.75)	M41x1.0-6g-0.100R	2.070 (52.58)	1.509 (38.33)	.128 (3.25)	1.5000-.067P-2L-TS-2A

806-021 Jam-nut D-Hole Dimensions		
Shell Size	øA +.005/-0.00 (+.013/-0.00)	B +.005/-0.00 (+.013/-0.00)
8	.256 (6.50)	.601 (15.27)
9	.287 (7.29)	.640 (16.26)
10	.719 (18.26)	.318 (8.08)
11	.350 (8.89)	.759 (19.28)
12	.381 (9.68)	.837 (21.26)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)

NOTES

- 75 ohm P2 S2 is available only on #12 arrangements



Series 806 Mil-Aero Connectors

806-037 Jam-Nut, Right-Angle PCB Receptacle Connectors



806-037 right angle panel mount jam-nut receptacles feature potted-in-place printed circuit board terminals and threaded holes for secure attachment to rigid or flex circuit boards. High temperature thermoplastic housing withstands soldering temperatures while reducing weight. Stainless steel threaded inserts simplify attachment to printed circuit boards. These high performance connectors are suitable for harsh environmental areas such as unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes.

Features

- Triple-start stub ACME mating thread
- 5 High density #22HD arrangements available for reduced size and weight
- Aerospace-grade materials, construction
- Threaded holes for secure attachment to rigid or flex circuits

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage #22HD contacts: 1300 VAC
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell and jam-nut: aluminum or stainless steel
- Contact - copper alloy / gold plating
- Potting compound: epoxy
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone

How To Order


SAMPLE PART NUMBER		806-037	-ME	11-19	P	A
Product	806-037 = Jam-nut, Right-Angle Receptacle					
Shell Material and Finish	NF = Aluminum, O.D. Cad Over Electroless Nickel MT = Aluminum, Ni/PTFE ME = Aluminum, Electroless Nickel ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated ZL = Stainless Steel, Electro-Deposited Nickel					
Arrangement Number (Shell Size - Insert Arr.)	See Table 1					
Contact Type	P = Pin S = Socket					
Polarization	A B C D E F					

Polarization Key Code

POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°


Table 1: Shell Size - Insert Arrangement

Shell Size - Contact Layout	Number of Contacts
22HD	
8-4	4
8-7	7
9-11	11
10-15	15
11-19	19



Recommend Mounting Hole Dimensions

Shell Size	K (+.005/-0.00) (+.013/-0.00)	ØL (+.005/-0.00) (+.013/-0.00)
8	.256 (6.50)	.601 (15.27)
9	.287 (7.29)	.640 (16.26)
10	.318 (8.08)	.719 (18.26)
11	.350 (8.89)	.759 (19.28)




ARRANGEMENT NO. 11-19
SHOWN FOR REFERENCE ONLY


Dimensions

Shell Size / Arrangement	Øa Max.	B Thread Flat	C Flat Max.	D Mating Thread	E Thread	F	G	H Basic	J	M	N
8 - 4	.980 (24.89)	.534 (13.56)	.920 (23.37)	.5000-.0667P-.2L-TS-2A	M15 x 1-6g-.100R	.440 (11.18)	.226 (5.74)	.385 (9.78)	.319 (8.10)	.589 (14.96)	.281 (7.14)
8 - 7	.980 (24.89)	.534 (13.56)	.920 (23.37)	.5000-.0667P-.2L-TS-2A	M15 x 1-6g-.100R	.440 (11.18)	.228 (5.79)	.408 (10.36)	.282 (7.16)	.589 (14.96)	.234 (5.94)
9 - 11	1.040 (26.42)	.585 (14.86)	.980 (24.89)	.5625-.0667P-.2L-TS-2A	M16 x 1-6g-.100R	.585 (14.86)	.321 (8.15)	.490 (12.45)	.325 (8.25)	.710 (18.03)	.241 (6.12)
10 - 15	1.110 (28.19)	.656 (16.66)	1.050 (26.67)	.6250-.0667P-.2L-TS-2A	M18 x 1-6g-.100R	.585 (14.86)	.360 (9.14)	.600 (15.24)	.437 (11.10)	.800 (20.32)	.243 (6.17)
11 - 19	1.160 (29.46)	.707 (17.96)	1.110 (28.19)	.6875-.0667P-.2L-TS-2A	M19 x 1-6g-.100R	.585 (14.86)	.357 (9.07)	.600 (15.24)	.437 (11.10)	.800 (20.32)	.246 (6.25)


Series 806 Mil-Aero Connectors

806-037 Jam-Nut, Right-Angle PCB Receptacle Connectors






ARRANGEMENT NO. 10-15
15 X #22HD CONTACTS
PIN FACE SHOWN
(SOCKET FACE OPPOSITE)



ARRANGEMENT NO. 11-19
19 X #22HD CONTACTS
PIN FACE SHOWN
(SOCKET FACE OPPOSITE)

Series 806 Mil-Aero Connectors

806-063 Jam Nut Mount, Flush Rear PCB Receptacle Connector



Features

- Triple-start stub ACME mating thread
- 5 High density #22HD arrangements available for reduced size and weight
- Aerospace-grade materials, construction
- Threaded holes for secure attachment to rigid or flex circuits

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage #22HD contacts: 1300 VAC
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell and hex nut - al alloy or cres / see How to Order table
- Insulators - high grade rigid dielectric / N.A.
- Interfacial seal, peripheral O-ring, and flange o-ring - fluorosilicone blend / N.A.
- Contact - copper alloy / gold plating

How To Order


SAMPLE PART NUMBER		806-063	-ME	11-19	S	1	A
Product	806-063 = Jam Nut Mount, Flush Rear PCB Receptacle						
Shell Material and Finish	NF = Aluminum, O.D. Cad Over Electroless Nickel MT = Aluminum, Ni/PTFE ME = Aluminum, Electroless Nickel ZR = Aluminum, Black Zinc-Nickel TZ = Aluminum, Tin-Zinc MN = Aluminum, Mega-Nickel Z1 = Stainless Steel, Passivated ZL = Stainless Steel, Electro-Deposited Nickel						
Arrangement Number (Shell Size - Insert Arr.)	See Pages 6 thru 9 for Contact Arrangements						
Contact Type	P = Pin, PC Tail S = Socket, PC Tail E = Pin, Solder Cup F = Socket, Solder Cup						
PC Tail Length	1 = .125" 2 = .250" *Omit For Solder Cup						
Polarization	A B C D E F						

Polarization Key Code

POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

PC Tail Diameter

Contact Size	PC Tail Diameter
#22HD	.020 (0.51)
#20HD	.030 (0.76)
#16	.060 (1.52)
#12	.092 (2.34)
#8	.180 (4.57)




Recommend Mounting Hole Dimensions

Shell Size	ØJ (+.005/-0.00) (+.013/-0.00)	K Flat (+.005/-0.00) (+.013/-0.00)
7	.522 (13.26)	.224 (5.69)
8	.601 (15.27)	.256 (6.50)
9	.640 (16.26)	.287 (7.29)
10	.719 (18.26)	.318 (8.08)
11	.759 (19.28)	.350 (8.89)
12	.837 (21.26)	.381 (9.68)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)

Series 806

Mil-Aero Connectors

806-063 Jam Nut Mount, Flush Rear PCB Receptacle Connector




Dimensions

Shell Size	ØA Max	B Thread	C Flats Max	D Mating Thread	E	G Thd Flat
7	.908 (23.06)	M8 X 1-6g	.848 (21.54)	.4375-.067P-.2L-TS-2A	.090 (2.29)	.463 (11.76)
8	.980 (24.89)	M15 X 1-6g	.920 (23.37)	.5000-.067P-.2L-TS-2A		.534 (13.56)
9	1.040 (26.42)	M16 X 1-6g	.980 (24.89)	.5625-.067P-.2L-TS-2A		.585 (14.86)
10	1.110 (28.19)	M18 X 1-6g	1.050 (26.67)	.6250-.067P-.2L-TS-2A		.656 (16.66)
11	1.160 (29.46)	M19 X 1-6g	1.110 (28.19)	.6875-.067P-.2L-TS-2A		.707 (17.96)
12	1.230 (31.24)	M21 X 1-6g	1.170 (29.72)	.7500-.067P-.2L-TS-2A		.777 (19.74)
14	1.360 (34.54)	M24 X 1-6g	1.320 (33.53)	.8750-.067P-.2L-TS-2A		.899 (22.83)
16	1.515 (38.48)	M27 X 1-6g	1.444 (36.68)	1.000-.067P-.2L-TS-2A		1.020 (25.91)
18	1.610 (40.89)	M30 X 1-6g	1.570 (39.88)	1.125-.067P-.2L-TS-2A		1.142 (29.01)
20	1.850 (46.99)	M34 X 1-6g	1.760 (44.70)	1.250-.067P-.2L-TS-2A		1.283 (32.59)
22	2.010 (51.05)	M37 X 1-6g	1.913 (48.59)	1.375-.067P-.2L-TS-2A		1.405 (35.69)
24	2.195 (55.75)	M41 X 1-6g	2.070 (52.58)	1.500-.067P-.2L-TS-2A		1.546 (39.27)

Series 806 Mil-Aero Connectors

806-064 Square Flange, Flush Rear PCB Receptacle Connector



Features

- Triple-start stub ACME mating thread
- 5 High density #22HD arrangements available for reduced size and weight
- Aerospace-grade materials, construction
- Threaded holes for secure attachment to rigid or flex circuits

Specifications

- Operating temperature:
Finishes ME, MT, Z1: -65°C to +200°C
Finishes NF, ZR: -65°C to +175°C
- Dielectric withstanding voltage #22HD contacts: 1300 VAC
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell - al alloy or cres / see How to Order table
- Insulators - high grade rigid dielectric / N.A.
- Interfacial seal and peripheral O-ring - fluorosilicone blend / N.A.
- Contact - copper alloy / gold plating


How To Order							
SAMPLE PART NUMBER		806-064	-ME	11-19	S	1	T A
Product	806-064 = Square Flange, Flush Rear PCB Receptacle						
Shell Material and Finish	NF = Aluminum, O.D. Cad Over Electroless Nickel MT = Aluminum, Ni/PTFE ME = Aluminum, Electroless Nickel ZR = Aluminum, Black Zinc-Nickel TZ = Aluminum, Tin-Zinc MN = Aluminum, Mega-Nickel Z1 = Stainless Steel, Passivated ZL = Stainless Steel, Electro-Deposited Nickel						
Arrangement Number (Shell Size - Insert Arr.)	See Pages 6 thru 9 for Contact Arrangements						
Contact Type	P = Pin, PC Tail S = Socket, PC Tail E = Pin, Solder Cup F = Socket, Solder Cup						
PC Tail Length	1 = .125" 2 = .250" *Omit For Solder Cup						
Panel Mount Hole Style	T = Thru Hole C = Clinch Nuts (Rear Panel Mounting Only), #4-40 (M45938/6-4C Type Equivalent)						
Polarization	A B C D E F						

Polarization Key Code				
POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

PC Tail Diameter	
Contact Size	PC Tail Diameter
#22HD	.020 (0.51)
#20HD	.030 (0.76)
#16	.060 (1.52)
#12	.092 (2.34)
#8	.180 (4.57)




Recommend Mounting Hole Dimensions			
Shell Size	ØJ	ØK	
		Clinch Nuts	Thru Holes
7	.443 (11.25)	.128 (3.25)	.128 (3.25)
8	.509 (12.93)		
9	.577 (14.66)		
10	.645 (16.38)		
11	.712 (18.08)		
12	.768 (19.51)		
14	.890 (22.61)		
16	1.015 (25.78)		
18	1.125 (28.58)		
20	1.275 (32.39)		
22	1.400 (35.56)		
24	1.525 (38.73)		
			.154 (3.91)

Series 806**Mil-Aero Connectors****806-064 Square Flange, Flush Rear PCB Receptacle Connector****Dimensions**

Shell Size	ØA Max	B Sq	C Flats Max	D Mating Thread	E	ØF Thru Hole
7	.968 (24.59)	.469 (11.91)	.750 (19.05)	.4375-.067P-.2L-TS-2A	.090 (2.29)	.128 (3.25)
8	1.040 (26.42)	.531 (13.49)	.822 (20.88)	.5000-.067P-.2L-TS-2A		
9	1.130 (28.70)	.594 (15.09)	.885 (22.48)	.5625-.067P-.2L-TS-2A		
10	1.174 (29.82)	.625 (15.88)	.913 (23.19)	.6250-.067P-.2L-TS-2A		
11	1.240 (31.50)	.670 (17.02)	.960 (24.38)	.6875-.067P-.2L-TS-2A		
12	1.354 (34.39)	.765 (19.43)	1.040 (26.42)	.7500-.067P-.2L-TS-2A		
14	1.510 (38.35)	.859 (21.82)	1.133 (28.78)	.8750-.067P-.2L-TS-2A		
16	1.620 (41.15)	.938 (23.83)	1.242 (31.55)	1.000-.067P-.2L-TS-2A		
18	1.784 (45.31)	1.016 (25.81)	1.343 (34.11)	1.125-.067P-.2L-TS-2A		
20	1.910 (48.51)	1.109 (28.17)	1.444 (36.68)	1.250-.067P-.2L-TS-2A		
22	2.083 (52.91)	1.203 (30.56)	1.570 (39.88)	1.375-.067P-.2L-TS-2A	.105 (2.67)	.154 (3.91)
24	2.200 (55.88)	1.312 (33.32)	1.704 (43.28)	1.500-.067P-.2L-TS-2A		

Series 806 Mil-Aero Connectors

806-039 Jam-Nut PCB Receptacle Connectors, High-Speed / RF



Features

- Triple-start stub ACME mating thread
- Size 8 El Ochito or RF standard arrangements or hybrid size 8 and 22 arrangements
- Aerospace-grade materials, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature: -65°C to +175°C
- Dielectric withstanding voltage #22HD contacts: 1300 VAC
- #8 contacts: varies; contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- compound: epoxy
- Interfacial seal and peripheral seal: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone

806-039 Jam-nut PCB receptacles with potted-in-place printed circuit board terminals, integral standoffs, and threaded holes for secure attachment to rigid or flex circuit boards. Series supports hybrid signal and high-speed / RF shielded contacts including Glenair Signature El Ochito (up to 40 GbE), Quadrax, 50 Ohm Coax, and differential Twinax for 10GbE, HDMI, USB 3.0, and RF applications. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade circular connectors. These hybrid insert arrangement connectors are suitable for high-speed digital and standard signal applications in unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes.

How To Order								
SAMPLE PART NUMBER	806-039	-ME	14	E3	-	20A	S	A
Product	806-039 = Jam-Nut, El Ochito PCB Receptacle							
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Cad Olive Drab ZI = Stainless Steel, Passivated							
Shell Size	See Table I							
Contact Type	See Table II							
Ground Option	G = Common Ground* Dash (-) = None *Available for 10-1, 16-2, 18-3, 20-4, 22-5, and 24-8 inserts							
Contact Layout	See Table I							
Contact Gender	P = Pin S = Socket; see Table III for El Ochito mating contacts							
Polarization	A B C D E F							

Table I: Shell Size - Insert Arrangement		
Shell Size - Contact Layout	Number of Contacts	
	22HD	8
10-1		1
16-2		2
18-3		3
20-4		4
22-5		5
24-8		8
14-20A	19	1
16-22	20	2
18-21	18	3
20-28	24	4
22-44	40	4
24-97	93	4

Table II: Contact Type	
Contact Symbol	Description
C	Coax, 50 ohm
D	Differential Twinax 100 ohm
E**	El Ochito
Q	Quadrax, 100 ohm

**See Table III for complete Protocol Code

Glennair®


Series 806 Mil-Aero Connectors

806-039 Jam-Nut PCB Receptacle Connectors, High-Speed / RF

EI Ochito Mating Contact		
PART NUMBER	PROTOCOLS	
WHITE - PIN	858-045 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-051 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
WHITE - SKT	858-046 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-052 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
BLUE - PIN	858-047	USB 3.0, OTHER 90 OHM SIGNALS
BLUE - SKT	858-048	USB 3.0, OTHER 90 OHM SIGNALS
RED - PIN	858-049	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS
RED - SKT	858-050	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS

EI Ochito Protocols		
		
WHITE	BLUE	RED
10GBASE-T	USB 3.0	HDMI, SATA, DisplayPort

The Ochito octaxial contact has a color-coded insulator signifying the data protocol. White is used for 10 Gb Ethernet, blue is used for USB 3.0, and red is used for multi gigabit 100 ohm protocols including HDMI, DisplayPort and SATA. The connector part number includes a protocol code from Table III. This code determines specific contact position for every combination of protocol.



Example
Code E7







Example
Code E5

Table III - Protocol Code for EI Ochito Contact Positions B = Blue, R = Red, W = White								
SYMBOL	Contact							
	A	B	C	D	E	F	G	H
E	W	W	W	W	W	W	W	W
E2	B	W	W	W	W	W	W	W
E3	R	W	W	W	W	W	W	W
E4	B	B	W	W	W	W	W	W
E5	R	B	W	W	W	W	W	W
E6	R	R	W	W	W	W	W	W
E7	B	B	B	W	W	W	W	W
E8	R	B	B	W	W	W	W	W
E9	R	R	B	W	W	W	W	W
E10	R	R	R	W	W	W	W	W
E11	B	B	B	B	W	W	W	W
E12	R	B	B	B	W	W	W	W
E13	R	R	B	B	W	W	W	W
E14	R	R	R	B	W	W	W	W
E15	R	R	R	R	W	W	W	W
E16	B	B	B	B	B	W	W	W
E17	R	B	B	B	B	W	W	W
E18	R	R	B	B	B	W	W	W
E19	R	R	R	B	B	W	W	W
E20	R	R	R	R	B	W	W	W
E21	R	R	R	R	R	W	W	W
E22	B	B	B	B	B	B	W	W
E23	R	B	B	B	B	B	W	W
E24	R	R	B	B	B	B	W	W
E25	R	R	R	B	B	B	W	W
E26	R	R	R	R	B	B	W	W
E27	R	R	R	R	R	B	W	W
E28	R	R	R	R	R	R	W	W
E29	B	B	B	B	B	B	B	W
E30	R	B	B	B	B	B	B	W
E31	R	R	B	B	B	B	B	W
E32	R	R	R	B	B	B	B	W
E33	R	R	R	R	B	B	B	W
E34	R	R	R	R	R	B	B	W
E35	R	R	R	R	R	R	B	W
E36	R	R	R	R	R	R	R	W
E37	B	B	B	B	B	B	B	B
E38	R	B	B	B	B	B	B	B
E39	R	R	B	B	B	B	B	B
E40	R	R	R	B	B	B	B	B
E41	R	R	R	R	B	B	B	B
E42	R	R	R	R	R	B	B	B
E43	R	R	R	R	R	R	B	B
E44	R	R	R	R	R	R	R	B
E45	R	R	R	R	R	R	R	R

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Size 8 PCB Footprints for Coax, Quadrx, Twinax and El Ochito

See Appendix A for complete PCB footprint details



PIN INTERFACE SHOWN
SOCKET INTERFACE OPPOSITE


ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors



806-040 Box Mount PCB Receptacle Connectors, High-Speed / RF



Features

- Triple-start stub ACME mating thread
- Size 8 El Ochito arrangements or hybrid size 8 and 22 arrangements
- Aerospace-grade materials, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature: -65°C to +175°C
- Dielectric withstanding voltage:
#22HD contacts: 1300 VAC
#8 contacts: contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Potting compound: epoxy
- Interfacial seal and peripheral seal: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Clinch nuts: stainless steel, passivated

806-040 Box-mount PCB receptacles with potted-in-place printed circuit board terminals, integral standoffs, and threaded holes for secure attachment to rigid or flex circuit boards. Series supports hybrid signal and high-speed / RF shielded contacts including Glenair Signature El Ochito (up to 40 Gbe), Quadrax, 50 Ohm Coax, and differential Twinax for 10GbE, HDMI, USB 3.0, and RF applications. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade circular connectors. These hybrid insert arrangement connectors are suitable for high-speed digital and standard signal applications in unpressurized aircraft zones subject to vibration, moisture, altitude, and temperature extremes.

How To Order									
SAMPLE PART NUMBER	806-040	-ME	14	E	-	20A	S	T	A
Product	806-040 = Box Mount, El Ochito PCB Receptacle								
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated								
Shell Size	See Table I								
Contact Type	See Table II								
Ground Option	G = Common Ground Dash (-) = None Available for 10-1, 16-2, 18-3, 20-4, 22-5, and 24-8 inserts								
Contact Layout	See Table I								
Contact Gender	P = Pin S = Socket; see Table VI for El Ochito mating contacts								
Mounting Hole Style	T = Thru holes C = Clinch nut flange, #4-40, M45938/6-4C (rear panel mounting); consult factory for SST material								
Polarization	A B C D E F								

Table I: Shell Size - Insert Arrangement		
Contact Layout	Number of Contacts	
	22HD	8
10-1		1
16-2		2
18-3		3
20-4		4
22-5		5
24-8		8
14-20A	19	1
16-22	20	2
18-21	18	3
20-28	24	4
22-44	40	4
24-97	93	4


Table II: Contact Type	
Contact Symbol	Description
C	Coax, 50 ohm
D	Differential Twinax 100 ohm
E**	El Ochito (see Table IV for symbol)
Q	Quadrax, 100 ohm

**See Table III for complete Protocol Code

Series 806 Mil-Aero Connectors



806-040 Box Mount PCB Receptacle Connectors, High-Speed / RF



Dimensions

Shell Size	A Max	B	C Max	D	E Mounting Hole	F Max Flange Thickness	G Mating Thread
10	1.174 (29.82)	0.625 (15.88)	0.913 (23.19)	0.679 (17.25)	0.128 (3.25)	0.100 (2.54)	.625-.067P-.2L-TS-2B
14	1.510 (38.35)	0.859 (21.82)	1.133 (28.78)	0.891 (22.63)			.875-.067P-.2L-TS-2B
16	1.620 (41.15)	0.938 (23.83)	1.242 (31.55)	1.049 (26.64)			1.000-.067P-.2L-TS-2B
18	1.784 (45.31)	1.016 (25.81)	1.343 (34.11)	1.148 (29.16)			1.125-.067P-.2L-TS-2B
20	1.910 (48.51)	1.109 (28.17)	1.444 (36.68)	1.252 (31.80)			1.250-.067P-.2L-TS-2B
22	2.083 (52.91)	1.203 (30.56)	1.570 (39.88)	1.369 (34.77)	0.154 (3.91)	0.125 (3.18)	1.375-.067P-.2L-TS-2B
24	2.200 (55.88)	1.312 (33.32)	1.704 (43.28)	1.509 (38.33)			1.500-.067P-.2L-TS-2B

PC Tail Diameter


CONTACT SIZE	PC TAIL
22	Ø.020 (0.51)
COAX	Ø.025 (0.64)
DIFF TWINAX	Ø.025 (0.64)
EL OCHITO	Ø.016 (0.41)
QUADRAX	Ø.025 (0.64)
SIZE 8 GROUND	.030 (0.76) SQ.

Recommended Mounting Hole

Shell Size	ØJ	With Clinch Nut	Without Clinch Nut
10	0.645 (16.38)	0.128 (3.25)	0.128 (3.25)
14	0.890 (22.61)		
16	1.015 (25.78)		
18	1.125 (28.58)		
20	1.275 (32.39)		
22	1.400 (35.56)	0.154 (3.91)	0.154 (3.91)
24	1.525 (38.73)		

NOTES

- See Glenair application note AN0002 for optimal El Ochito board layout and design
- Integral PCB Stand off 4x 4-40 UNC .156 min thread and locating post
- See Table V for different combinations of El Ochito types
- Connector meets all performance requirements of Glenair product specification 806-014 and applies to all finishes
- Receptacle connector mates with all quick coupling, Glenair 806 style, plug connectors with same polarization and opposite contact gender



ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors



806-040 Box Mount PCB Receptacle Connectors, High-Speed / RF

El Ochito Mating Contact		
PART NUMBER	PROTOCOLS	
WHITE - PIN	858-045 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-051 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
WHITE - SKT	858-046 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-052 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
BLUE - PIN	858-047	USB 3.0, OTHER 90 OHM SIGNALS
BLUE - SKT	858-048	USB 3.0, OTHER 90 OHM SIGNALS
RED - PIN	858-049	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS
RED - SKT	858-050	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS

El Ochito Protocols		
WHITE	BLUE	RED
10GBASE-T	USB 3.0	HDMI, SATA, DisplayPort

The Ochito octaxial contact has a color-coded insulator signifying the data protocol. White is used for 10 Gb Ethernet, blue is used for USB 3.0, and red is used for multi gigabit 100 ohm protocols including HDMI, DisplayPort and SATA. The connector part number includes a protocol code from Table III. This code determines specific contact position for every combination of protocol.



Example
Code E7




Example
Code E5


Table III: Protocol Code for El Ochito Contact Positions B = Blue, R = Red, W = White								
SYMBOL	Contact							
	A	B	C	D	E	F	G	H
E	W	W	W	W	W	W	W	W
E2	B	W	W	W	W	W	W	W
E3	R	W	W	W	W	W	W	W
E4	B	B	W	W	W	W	W	W
E5	R	B	W	W	W	W	W	W
E6	R	R	W	W	W	W	W	W
E7	B	B	B	W	W	W	W	W
E8	R	B	B	W	W	W	W	W
E9	R	R	B	W	W	W	W	W
E10	R	R	R	W	W	W	W	W
E11	B	B	B	B	W	W	W	W
E12	R	B	B	B	W	W	W	W
E13	R	R	B	B	W	W	W	W
E14	R	R	R	B	W	W	W	W
E15	R	R	R	R	W	W	W	W
E16	B	B	B	B	B	W	W	W
E17	R	B	B	B	B	W	W	W
E18	R	R	B	B	B	W	W	W
E19	R	R	R	B	B	W	W	W
E20	R	R	R	R	B	W	W	W
E21	R	R	R	R	R	W	W	W
E22	B	B	B	B	B	B	W	W
E23	R	B	B	B	B	B	W	W
E24	R	R	B	B	B	B	W	W
E25	R	R	R	B	B	B	W	W
E26	R	R	R	R	B	B	W	W
E27	R	R	R	R	R	B	W	W
E28	R	R	R	R	R	R	W	W
E29	B	B	B	B	B	B	B	W
E30	R	B	B	B	B	B	B	W
E31	R	R	B	B	B	B	B	W
E32	R	R	R	B	B	B	B	W
E33	R	R	R	R	B	B	B	W
E34	R	R	R	R	R	B	B	W
E35	R	R	R	R	R	R	B	W
E36	R	R	R	R	R	R	R	W
E37	B	B	B	B	B	B	B	B
E38	R	B	B	B	B	B	B	B
E39	R	R	B	B	B	B	B	B
E40	R	R	R	B	B	B	B	B
E41	R	R	R	R	B	B	B	B
E42	R	R	R	R	R	B	B	B
E43	R	R	R	R	R	R	B	B
E44	R	R	R	R	R	R	R	B
E45	R	R	R	R	R	R	R	R

Size 8 PCB Footprints for Coax, Quadrax, Twinax and El Ochito


See Appendix A for complete PCB footprint details




COAX




DIFFERENTIAL TWINAX



QUADRAx



TRIX/CONCENTRIC TWINAX



EL OCHITO

PIN INTERFACE SHOWN
SOCKET INTERFACE OPPOSITE




EXTREME TEMPERATURE ThermaRex Series 806 Connectors

High-temperature micro miniature connectors, cables, and wire protection accessories


Sensor devices in aerospace engine applications are increasingly exposed to higher temperature operating environments. Environmental sensors in nuclear power reactors—an extremely high temperature and radiation-rich environment—are also exposed to temperature extremes well beyond the capabilities of conventional interconnect devices. Series 806 micro miniature connectors with Glenair Signature ThermaRex high-temperature inserts are designed to survive and excel in high continuous operating temperature application environments up to 300°C. The Series 806 Mil-Aero ThermaRex product family includes connectors, cables, and accessory wire protection conduit systems.



Micro miniature Series 806
circulars with high-temperature
ThermaRex technology



ThermaRex™




- **HT Service rating up to 300°C**
- **Vibration-resistant threaded coupling**
- **High-temperature ceramic insulators and silicone seals**
- **Durable stainless steel construction**
- **Utilizes Glenair Signature Crown Ring contacts**
- **Contact and wire support in sizes #22HD, #20HD, #16, #12, and #8**

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
With ThermaRex HT Inserts and Seals • Accessories




GLENAIR SIGNATURE CROWN RING CONTACTS



- Crimp removable contacts, sizes #22HD, #20HD, #16, #12, and #8
- Optimized for use at 300°C or higher while maintaining low electrical resistance
- Stainless steel Crown Ring provides compression force on the socket
- Superior vibration resistance
- Higher current carrying capabilities, lower contact resistance

300°C THERMAREX WIRE



- Special nickel-coated copper alloy conductors
- 300°C continuous service
- 24 to 8 AWG, 10 colors of insulation
- Single-wires plus jacketed, shielded, twisted pair available

300°C THERMAREX POLYMER-CORE CONDUIT



- High-temperature-tolerant flexible polymer-core conduit
- All standard colors: black, clear, orange, blue, yellow
- Qualification test report GT-17-261 available
- 300°C continuous service
- Available with high-temperature braid shield and/or jacket

300°C THERMAREX METAL-CORE CONDUIT



- Flexible passivated stainless steel core conduit
- High-temperature-tolerant ThermaRex jacket
- .127" to .250" outer diameter sizes
- 300°C continuous service

ARMORLITE CF MICROFILAMENT EMI/RFI SHIELDING




- Stainless steel over copper microfilament EMI shield
- High temperature -80°C to 300°C
- Corrosion / harsh environment resistant
- 1000 hour salt spray testing completed
- 70% reduced weight vs. standard braid
- Superb electrical resistance and shielding performance

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-042 ThermoRex HT Plug



Features

- Operating temperature -65° to 300°C
- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid Crown Ring contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Operating temperature: Finish Z1: -65°C to +300°C
- Dielectric withstanding voltage
#22HD layouts: 1300 VAC
#20HD layouts: 1800 VAC
#16 layouts: varies, contact factory
#12 layouts: varies, contact factory
#8 layouts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Plug barrel, coupling nut: passivated CRES
- Pin contact: copper alloy, gold plate
- Skt contact: copper alloy, gold plate; skt hood: CRES; crown ring: spring grade CRES
- Ground spring: spring grade CRES/nickel plate
- Insulator: high grade ceramic dielectric
- Interfacial seal, grommet: high-temp silicone

High-temperature 806-042 ThermoRex cable plugs are rated to perform from -65° to 300°C. Intended for use in high-temperature harsh application areas such as engine aircraft zones subject to high heat, altitude, and temperature extremes while providing size and weight savings compared to conventional aerospace-grade circular connectors. Rugged ratchet mechanism and unique triple-start mating thread provide improved de-coupling resistance under vibration. Available with integral Nano Band platform or with metric accessory threads, these connectors feature snap-in, rear release Crown Ring contacts (shielded, high-speed, or RF contacts not supported).

How To Order

SAMPLE PART NUMBER		806-042	Z1	11-19	S	M	A
Series / Basic Part No.	806-042 High-temperature ThermoRex Series 806 plug						
Material/Finish	Z1 = Passivated CRES						
Shell Size/Insert Arr.	See Table I						
Contact Style	P = Pin S = Socket Crown Ring contacts mandatory.						
Shell Style	M = Metric accessory thread B = Banding platform						
Polarization	A, B, C, D, E, F						

Table I: Shell Size - Insert Arrangement


Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1		1				22-5					5
9-11	11					10-2		2				24-8					8
10-15	15					11-4		4				10-8A	6		2		
11-19	19					12-5		5				11-13	11		2		
12-26	26					14-7		7				12-27	26		1		
14-39	39					16-12		12				14-21	17		4		
16-60	60					18-15		15				16-41	37		4		
18-85	85					20-22		22				18-59	55		4		
20-110	110					22-24		24				11-14	13			1	
22-140	140					24-35		35				14-22	20			2	
24-186	186					9-1				1		12-14	12			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-042 ThermaRex HT Plug



806-042 Dimensions				
Shell Size	ØA Max	B Thread	Mating Thd Triple Start Modified 60 Stub Acme	ØD
7	0.606 (15.39)	M8 X 1.0-6g-.100R	0.4375-.067P-.2L-TS-2B	0.267 (6.78)
8	0.676 (17.17)	M10 X 1.0-6g-.100R	0.500-.067P-.2L-TS-2B	0.327 (8.31)
9	0.771 (19.58)	M12 X 1.0-6g-.100R	0.562-.067P-.2L-TS-2B	0.406 (10.31)
10	0.832 (21.13)	M14 X 1.0-6g-.100R	0.625-.067P-.2L-TS-2B	0.484 (12.29)
11	0.890 (22.61)	M15 X 1.0-6g-.100R	0.688-.067P-.2L-TS-2B	0.524 (13.31)
12	0.950 (24.13)	M17 X 1.0-6g-.100R	0.750-.067P-.2L-TS-2B	0.603 (15.32)
14	1.110 (28.19)	M19 X 1.0-6g-.100R	0.875-.067P-.2L-TS-2B	0.681 (17.30)
16	1.170 (29.72)	M22 X 1.0-6g-.100R	1.000-.067P-.2L-TS-2B	0.782 (19.86)
18	1.350 (34.29)	M25 X 1.0-6g-.100R	1.125-.067P-.2L-TS-2B	0.899 (22.83)
20	1.470 (37.34)	M28 X 1.0-6g-.100R	1.250-.067P-.2L-TS-2B	1.043 (26.49)
22	1.600 (40.64)	M31 X 1.0-6g-.100R	1.375-.067P-.2L-TS-2B	1.155 (29.34)
24	1.710 (43.43)	M34 X 1.0-6g-.100R	1.500-.067P-.2L-TS-2B	1.273 (32.33)

NOTES:


1. Boot groove for use with 809-463 Therma-Rex Autoshrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband
3. High temperature crown ring pin and socket contacts required to meet higher operating temps

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-053 ThermoRex HT Jam-Nut



Features

- Operating temperature -65° to 300°C
- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, #12, and #8 standard and hybrid Crown Ring contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Operating temperature: Finish Z1: -65°C to +300°C
- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell: passivated CRES
- Pin contact: copper alloy, gold plate
- Skt contact: copper alloy, gold plate; skt hood: CRES; crown ring: spring grade CRES
- Insulator: high grade ceramic dielectric
- Interfacial seal, grommet: high-temp silicone

High-temperature 806-053 ThermoRex jam-nut receptacles are rated to perform from -65° to 300°C while providing size and weight savings compared to conventional aerospace-grade circular connectors. Unique triple-start mating thread provide improved de-coupling resistance under vibration. Series 806 enhanced performance connectors are intended for use in high temperature harsh application areas such as engine aircraft zones subject to high heat, altitude, and temperature extremes. Connectors feature snap-in, rear release Crown Ring contacts (shielded, high-speed, or RF contacts not supported).


How To Order						
SAMPLE PART NUMBER		806-053	Z1	11-19	S	M A
Series / Basic Part No.	806-053 ThermoRex jam-nut receptacle					
Material/Finish	Z1 = Passivated CRES					
Shell Size/Insert Arr.	See Table I					
Contact Style	P = Pin A = Pin connector, less contacts S = Socket B = Socket connector, less contacts					
Shell Style	M = Metric accessory thread B = Banding platform					
Polarization	A, B, C, D, E, F					

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						



806-053 Receptacle Dimensions

Shell Size	øA Max	B Thread	C Max	D Mating Thread	E Max	F Thread	øH
7	.848 (21.54)	M8x1.0-6g-0.100R	.908 (23.06)	.4375-.067P-.2L-TS-2A	.100 (2.54)	M13x1.0-6g-0.100R	.265 (6.73)
8	.980 (24.89)	M10x1.0-6g-0.100R	.920 (23.37)	.5000-.067P-.2L-TS-2A	.100 (2.54)	M15x1.0-6g-0.100R	.327 (8.31)
9	1.040 (26.42)	M12x1.0-6g-0.100R	.980 (24.89)	.5625-.067P-.2L-TS-2A	.100 (2.54)	M16x1.0-6g-0.100R	.406 (10.31)
10	1.110 (28.19)	M14x1.0-6g-0.100R	1.050 (26.67)	.6250-.067P-.2L-TS-2A	.100 (2.54)	M18x1.0-6g-0.100R	.484 (12.29)
11	1.160 (29.46)	M15x1.0-6g-0.100R	1.110 (28.19)	.6875-.067P-.2L-TS-2A	.100 (2.54)	M19x1.0-6g-0.100R	.524 (13.31)
12	1.230 (31.24)	M17x1.0-6g-0.100R	1.170 (29.72)	.7500-.067P-.2L-TS-2A	.100 (2.54)	M21x1.0-6g-0.100R	.603 (15.32)
14	1.360 (34.54)	M19x1.0-6g-0.100R	1.320 (33.53)	.8750-.067P-.2L-TS-2A	.100 (2.54)	M24x1.0-6g-0.100R	.681 (17.30)
16	1.515 (38.48)	M22x1.0-6g-0.100R	1.444 (36.68)	1.0000-.067P-.2L-TS-2A	.100 (2.54)	M27x1.0-6g-0.100R	.782 (19.86)
18	1.610 (40.89)	M25x1.0-6g-0.100R	1.570 (39.88)	1.1250-.067P-.2L-TS-2A	.100 (2.54)	M30x1.0-6g-0.100R	.899 (22.83)
20	1.850 (46.99)	M28x1.0-6g-0.100R	1.760 (44.70)	1.2500-.067P-.2L-TS-2A	.128 (3.25)	M34x1.0-6g-0.100R	1.043 (26.49)
22	2.010 (51.05)	M31x1.0-6g-0.100R	1.913 (48.59)	1.3750-.067P-.2L-TS-2A	.128 (3.25)	M37x1.0-6g-0.100R	1.155 (29.34)
24	2.195 (55.75)	M34x1.0-6g-0.100R	2.070 (52.58)	1.5000-.067P-.2L-TS-2A	.128 (3.25)	M41x1.0-6g-0.100R	1.273 (32.33)



Recommended Mounting Hole

SHELL SIZE	M	N
	+0.005 (0.13) 0.000 (0.00)	+0.005 (0.13) 0.00 (0.00)
7	.224 (5.69)	.522 (13.26)
8	.256 (6.50)	.601 (15.27)
9	.287 (7.29)	.640 (16.26)
10	.318 (8.08)	.719 (18.26)
11	.350 (8.89)	.759 (19.28)
12	.381 (9.68)	.837 (21.26)
14	.443 (11.25)	.955 (24.26)
16	.505 (12.83)	1.073 (27.25)
18	.568 (14.43)	1.192 (30.28)
20	.630 (16.00)	1.349 (34.26)
22	.693 (17.60)	1.467 (37.26)
24	.755 (19.18)	1.624 (41.25)

NOTES:

1. Boot groove for use with 809-463 ThermaRex Autoshrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband
3. High temperature crown ring pin and socket contacts required to meet higher operating temps

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-052 ThermoRex HT Square Flange



Features

- Operating temperature -65° to 300°C
- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid Crown Ring contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Operating temperature: Finish Z1: -65°C to +300°C
- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: contact factory
#12 contacts: contact factory
#8 contacts: contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell: passivated CRES
- Pin contact: copper alloy, gold plate
- Skt contact: copper alloy, gold plate; skt hood: CRES; crown ring: spring grade CRES
- Insulator: high grade ceramic dielectric
- Interfacial seal, grommet: high-temp silicone

High-temperature 806-052 ThermoRex PCB square flange receptacles are rated to perform from -65° to 300°C. Intended for use in high temperature harsh applications, such as, engine aircraft zones subject to high heat, altitude, and temperature extremes while providing size and weight savings compared to conventional aerospace-grade circular connectors. Rugged ratchet mechanism and unique triple-start mating thread provide improved de-coupling resistance under vibration. Available with integral Nano Band platform or metric accessory threads and snap-in, rear release Crown Ring contacts (shielded, high-speed, or RF contacts not supported).

How To Order									
SAMPLE PART NUMBER		806-052	Z1	11-19	S	M	T	A	
Series / Basic Part No.	806-052 ThermoRex square-flange Rcptl.								
Material/Finish	Z1 = Passivated CRES								
Shell Size/Insert Arr.	See Table I								
Contact Style	P = Pin A = Pin connector, less contacts S = Socket B = Socket connector, less contacts								
Shell Style	M = Metric accessory thread B = Banding platform								
Panel Mounting	T = Thru-hole								
Polarization	A, B, C, D, E, F								


Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-052 ThermaRex HT Square Flange




806-052 Receptacle Dimensions

Shell Size	A Max	B Thread	C	D Mating Thread	ϕE	F Max	G Max	H Max
7	.750 (19.05)	M8x1.0-6g-0.100R	.469 (11.91)	.4375-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	.968 (24.59)	.265 (6.73)
8	.822 (20.88)	M10x1.0-6g-0.100R	.531 (13.49)	.5000-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.040 (26.42)	.327 (8.31)
9	.885 (22.48)	M12x1.0-6g-0.100R	.594 (15.09)	.5625-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.130 (28.70)	.406 (10.31)
10	.913 (23.19)	M14x1.0-6g-0.100R	.625 (15.88)	.6250-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.174 (29.82)	.484 (12.29)
11	.960 (24.38)	M15x1.0-6g-0.100R	.670 (17.02)	.6875-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.200 (30.48)	.524 (13.31)
12	1.040 (26.42)	M17x1.0-6g-0.100R	.765 (19.43)	.7500-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.354 (34.39)	.603 (15.32)
14	1.133 (28.78)	M19x1.0-6g-0.100R	.859 (21.82)	.8750-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.510 (38.35)	.681 (17.30)
16	1.227 (31.17)	M22x1.0-6g-0.100R	.938 (23.83)	1.0000-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.620 (41.15)	.782 (19.86)
18	1.320 (33.53)	M25x1.0-6g-0.100R	1.016 (25.81)	1.1250-.067P-.2L-TS-2A	.128 (3.25)	.100 (2.54)	1.784 (45.31)	.899 (22.83)
20	1.444 (36.68)	M28x1.0-6g-0.100R	1.109 (28.17)	1.2500-.067P-.2L-TS-2A	.154 (3.91)	.125 (3.18)	1.910 (48.51)	1.043 (26.49)
22	1.570 (39.88)	M31x1.0-6g-0.100R	1.203 (30.56)	1.3750-.067P-.2L-TS-2A	.154 (3.91)	.125 (3.18)	2.083 (52.91)	1.155 (29.34)
24	1.696 (43.08)	M34x1.0-6g-0.100R	1.312 (33.32)	1.5000-.067P-.2L-TS-2A	.154 (3.91)	.125 (3.18)	2.200 (55.88)	1.273 (32.33)

Panel Cut-Out Dimensions

Shell Size	J	K
7	.443 (11.25)	.128 (3.25)
8	.505 (12.83)	.128 (3.25)
9	.572 (14.53)	.128 (3.25)
10	.640 (16.26)	.128 (3.25)
11	.707 (17.96)	.128 (3.25)
12	.762 (19.35)	.128 (3.25)
14	.885 (22.48)	.128 (3.25)
16	1.010 (25.65)	.128 (3.25)
18	1.120 (28.45)	.128 (3.25)
20	1.270 (32.26)	.154 (3.91)
22	1.395 (35.43)	.154 (3.91)
24	1.520 (38.61)	.154 (3.91)

Square Flange Cutout




NOTES:

1. Boot groove for use with 809-463 ThermaRex Autoshrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband
3. High temperature crown ring pin and socket contacts required to meet higher operating temps

Series 806 Mil-Aero Connectors

806-041 ThermoRex HT PC Tail Jam-Nut Connector



Features

- Operating temperature -65° to 300°C
- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid Crown Ring contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Operating temperature: Finish Z1: -65°C to +300°C
- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell, jam-nut: passivated CRES
- Pin contact: copper alloy, gold plate
- Insulator: high grade ceramic dielectric
- Interfacial seal: high-temp silicone

High-temperature 806-041 ThermoRex PCB jam-nut receptacles are rated to perform from -65° to 300°C. Intended for use in high temperature harsh applications, such as, engine aircraft zones subject to high heat, altitude, and temperature extremes while providing size and weight savings compared to conventional aerospace-grade circular connectors. Rugged ratchet mechanism and unique triple-start mating thread provide improved de-coupling resistance under vibration. Threaded PCB standoffs allow for secure attachment to PCB board or flex applications. Contacts are potted in place with high-temperature elastomeric compound and non-removable. Parylene compatible.

How To Order						
SAMPLE PART NUMBER		806-041	Z1	11-19	P	1 N
Series / Basic Part No.	806-041 ThermoRex PCB jam-nut receptacle					
Material/Finish	Z1 = Passivated CRES					
Shell Size/Insert Arr.	See Table I					
Contact Style	P = Pin contacts only					
PC Tail Length	1 = .125" 2 = .250"					
Polarization	A, B, C, D, E, F					


Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						



806-041 Dimensions

Shell Size	Øa Max	B Thread	C Max	D	E Max	F Mating Thread
7	0.848 (21.54)	M8X 1-6g-.100R	0.908 (23.06)	0.489 (12.42)	0.100 (2.54)	.4375-.067P-.2L-TS-2A
8	0.980 (24.89)	M15 X 1-6g-.100R	0.920 (23.37)	0.534 (13.56)		.5000-.067P-.2L-TS-2A
9	1.040 (26.42)	M16 X 1-6g-.100R	0.980 (24.89)	0.579 (14.71)		.5625-.067P-.2L-TS-2A
10	1.110 (28.19)	M18 X 1-6g-.100R	1.050 (26.67)	0.679 (17.25)		.6250-.067P-.2L-TS-2A
11	1.160 (29.46)	M19 X 1-6g-.100R	1.110 (28.19)	0.734 (18.64)		.6875-.067P-.2L-TS-2A
12	1.230 (31.24)	M21 X 1-6g-.100R	1.170 (29.72)	0.804 (20.42)		.7500-.067P-.2L-TS-2A
14	1.360 (34.54)	M24 X 1-6g-.100R	1.320 (33.53)	0.891 (22.63)		.8750-.067P-.2L-TS-2A
16	1.515 (38.48)	M27 X 1-6g-.100R	1.444 (36.68)	1.049 (26.64)		1.000-.067P-.2L-TS-2A
18	1.610 (40.89)	M30 X 1-6g-.100R	1.570 (39.88)	1.148 (29.16)	0.128 (3.25)	1.1250-.067P-.2L-TS-2A
20	1.850 (46.99)	M34 X 1-6g-.100R	1.760 (44.70)	1.252 (31.80)		1.250-.067P-.2L-TS-2A
22	2.010 (51.05)	M37 X 1-6g-.100R	1.913 (48.59)	1.369 (34.77)		1.3750-.067P-.2L-TS-2A
24	2.195 (55.75)	M41 X 1-6g-.100R	2.070 (52.58)	1.509 (38.33)		1.5000-.067P-.2L-TS-2A

Jam-Nut Cutout



Recommended Mounting Hole

Shell Size	M +.005 (0.13) 0.000 (0.00)	N +.005 (0.13) 0.00 (0.00)
7	.224 (5.69)	.522 (13.26)
8	.256 (6.50)	.601 (15.27)
9	.287 (7.29)	.640 (16.26)
10	.318 (8.08)	.719 (18.26)
11	.350 (8.89)	.759 (19.28)
12	.381 (9.68)	.837 (21.26)
14	.443 (11.25)	.955 (24.26)
16	.505 (12.83)	1.073 (27.25)
18	.568 (14.43)	1.192 (30.28)
20	.630 (16.00)	1.349 (34.26)
22	.693 (17.60)	1.467 (37.26)
24	.755 (19.18)	1.624 (41.25)


Table II: PC Tail Diameter

Contact Size	PC Tail Dia.
20	.030 (0.76)
22	.020 (0.51)


HERMITY, WIND, AND CIRCULAR

Series 806 Mil-Aero Connectors

620V*080 Strain Relief Cable Clamp Backshell, Straight, 45°, 90°



ThermaRex™



Stainless Steel Series 62 backshells for high temperature ThermaRex plug and receptacle connectors are rated to perform from -65° to 300°C. Anti-decoupling device for improved vibration resistance and detents to allow for axial positioning of backshell for improved cable routing.

Table II: Material and Finish

Symbol	Material	Finish Description
Z1	Stainless Steel	Passivate

How To Order					
SAMPLE PART NUMBER		620V	A	080	Z1 16
Series / Basic Part No.	620V ThermaRex strain relief cable clamp				
Angular Function	S = Straight A = 90° B = 45°				
Basic Number	080				
Finish Sym, Table II	Z1				
Shell Size, Table I	08, 09, 10, 11, 12, 14, 16, 18, 20, 22, 24				




Table I: Dimensions

Shell Size	A Thread ISO Metric	B Dia Max	C Max	D Max	E +0.031 (0.79)	F Min	G Max	H Max	J Max	L Max
07										
08	M10 x 1-6H	0.642 (16.31)	0.710 (18.03)	0.93 (23.62)	0.205 (5.21)	0.18 (4.57)	0.891 (22.63)	1.04 (26.42)	0.87 (22.10)	1.30 (33.02)
09	M12 x 1-6H	0.735 (18.67)	0.840 (21.34)	0.98 (24.89)	0.219 (5.56)	0.22 (5.59)	0.901 (22.89)	1.06 (26.92)	0.91 (23.11)	1.32 (33.53)
10	M14 x 1-6H	0.786 (19.96)	0.900 (22.86)	1.02 (25.91)	0.244 (6.20)	0.25 (6.35)	0.945 (24.00)	1.08 (27.43)	0.95 (24.13)	1.35 (34.29)
11	M15 x 1-6H	0.830 (21.08)	0.960 (24.38)	1.05 (26.67)	0.264 (6.71)	0.27 (6.86)	0.964 (24.49)	1.10 (27.94)	0.97 (24.64)	1.36 (34.54)
12	M17 x 1-6H	0.911 (23.14)	1.060 (26.92)	1.12 (28.45)	0.312 (7.92)	0.32 (8.13)	1.030 (26.16)	1.15 (29.21)	1.03 (26.16)	1.41 (35.81)
14	M19 x 1-6H	1.002 (25.45)	1.100 (27.94)	1.20 (30.48)	0.344 (8.74)	0.35 (8.89)	1.050 (26.67)	1.18 (29.97)	1.06 (26.92)	1.43 (36.32)
16	M22 x 1-6H	1.149 (29.18)	1.100 (27.94)	1.30 (33.02)	0.460 (11.68)	0.47 (11.94)	1.112 (28.24)	1.30 (33.02)	1.16 (29.46)	1.48 (37.59)
18	M25 x 1-6H	1.264 (32.11)	1.230 (31.24)	1.44 (36.58)	0.545 (13.84)	0.55 (13.97)	1.175 (29.85)	1.38 (35.05)	1.34 (34.04)	1.58 (40.13)
20	M28 x 1-6H	1.394 (35.41)	1.410 (35.81)	1.56 (39.62)	0.615 (15.62)	0.62 (15.75)	1.230 (31.24)	1.46 (37.08)	1.41 (35.81)	1.70 (43.18)
22	M31 x 1-6H	1.513 (38.43)	1.510 (38.35)	1.69 (42.93)	0.698 (17.73)	0.70 (17.78)	1.293 (32.84)	1.58 (40.13)	1.53 (38.86)	1.74 (44.20)
24	M34 x 1-6H	1.631 (41.43)	1.660 (42.16)	1.77 (44.96)	0.780 (19.81)	0.78 (19.81)	1.365 (34.67)	1.62 (41.15)	1.66 (42.16)	1.79 (45.47)

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

120-100 Helical Polymer-Core Convoluted Tubing



OUTSTANDING MECHANICAL WIRE PROTECTION AND LUBRICITY FOR NON-ENVIRONMENTAL AND NON-EMI/RFI APPLICATIONS, IAW SAE AS81914



How To Order							
SAMPLE PART NUMBER		120-100	-1	-1	-16	B	R L
Series / Basic Part No.	120-100 300°C ThemaRex polymer-core Conduit						
Class	1 = Standard Wall 2 = Thin Wall						
Convolution	1 = Standard 2 = Close						
Tubing Size	See table 1						
Color	B = Black C = Clear O = Orange BL = Blue Y = Yellow						
Material	R = High Temperature ThemaRex, 300°C						
Lanyard	L = Lanyard; omit for none						





Table 1: Tubing Size Order Number and Dimensions

Tubing Size	Fractional Size Ref	A Inside Dia Min	B Dia Max	Min Bend Radius
06	3/16	.181 (4.6)	.320 (8.1)	.50 (12.7)
09	9/32	.273 (6.9)	.414 (10.5)	.75 (19.1)
10	5/16	.306 (7.8)	.450 (11.4)	.75 (19.1)
12	3/8	.359 (9.1)	.510 (13.0)	.88 (22.4)
14	7/16	.427 (10.8)	.571 (14.5)	1.00 (25.4)
16	1/2	.480 (12.2)	.650 (16.5)	1.25 (31.8)
20	5/8	.603 (15.3)	.770 (19.6)	1.50 (38.1)
24	3/4	.725 (18.4)	.930 (23.6)	1.75 (44.5)
28	7/8	.860 (21.8)	1.073 (27.3)	1.88 (47.8)
32	1	.970 (24.6)	1.226 (31.1)	2.25 (57.2)
40	1 1/4	1.205 (30.6)	1.539 (39.1)	2.75 (69.9)
48	1 1/2	1.437 (36.5)	1.832 (46.5)	3.25 (82.6)
56	1 3/4	1.688 (42.9)	2.156 (54.8)	3.63 (92.2)
64	2	1.937 (49.2)	2.332 (59.2)	4.25 (108.0)

PACKAGING


- Long-length orders of 120-100 conduit are subject to carrier weight and box size restrictions. For example, UPS air shipments are currently limited to 50 lbs. per box. Unless otherwise specified, Glenair standard practice is to ship optimal lengths of product based on weight, size, and individual carrier specifications.
- Consult factory for thin-wall, close convolution combination and for PEEK™ and PTFE min/max dimensions.

Series 806 Mil-Aero Connectors


ThermaRex Metal-Core Conduit and Armorlite EMI Shield



750-216 300°C THERMAREX METAL-CORE CONDUIT



Clear Jacket Shown



How To Order						
SAMPLE PART NUMBER		750-216	047	C	R	P
Product Series / Basic No	750-216 = Flexible metal core with high-temperature jacketing					
Order No	See Table I					
Core Material	C = Stainless Steel					
Jacket	R = ThermaRex Jacket					
Jacket Color	B = Black P = Purple W = White; omit for natural					

TABLE I			
Order No.	A I.D. Ref	B O.D. Nom	Bend Radius
047	0.047 (1.19)	0.127 (3.23)	0.905 (22.99)
059	0.059 (1.50)	0.138 (3.51)	0.905 (22.99)
071	0.071 (1.80)	0.150 (3.81)	0.905 (22.99)
079	0.079 (2.01)	0.158 (4.01)	0.905 (22.99)
087	0.087 (2.21)	0.164 (4.17)	0.787 (19.99)
102	0.102 (2.59)	0.180 (4.57)	0.787 (19.99)
118	0.118 (3.00)	0.211 (5.36)	0.709 (18.01)
126	0.126 (3.20)	0.219 (5.56)	0.709 (18.01)
138	0.138 (3.51)	0.227 (5.77)	0.748 (19.00)
157	0.157 (3.99)	0.250 (6.35)	0.748 (19.00)

103-052 ARMORLITE™ CF LIGHTWEIGHT EMI/RFI MICROFILAMENT NICKEL COPPER / SST BRAID



How To Order					
SAMPLE PART NUMBER		103	-052	-024	-S
Product Code	Lightweight Braid Series				
ArmorLite™	-052 = 75% ArmorLite™ / 25% Nickel-Copper				
Braid Diameter Dash Number	See Table				
Silver Clad Option	-S = 75% ArmorLite / 25% silver-plated copper Omit for standard nickel clad				

Dash Number - Diameter, Wire Bundle and Weight			
Dash No.	Nominal I.D. (ref.)	Wire Bundle Range (ref.)	Approx. Grams/Foot
-002	.062 (1.6)	.040 (1.0) – .075 (1.9)	1.6
-004	.125 (3.2)	.093 (2.4) – .140 (3.5)	1.8
-008	.250 (6.4)	.125 (3.2) – .312 (7.9)	2.8
-012	.375 (9.5)	.250 (6.4) – .406 (10.3)	3.5
-016	.500 (12.7)	.375 (9.5) – .560 (14.2)	5.4
-020	.625 (15.9)	.375 (9.5) – .700 (17.8)	5.7
-024	.750 (19.1)	.500 (12.7) – .800 (20.3)	7.5
-032	1.000 (25.4)	.780 (19.8) – 1.100 (27.9)	13.1
-040	1.250 (31.8)	.938 (23.8) – 1.312 (33.3)	15.8
-048	1.500 (38.1)	1.187 (30.1) – 1.590 (40.4)	19.7
-064	2.000 (50.8)	1.312 (33.3) – 2.090 (53.1)	24.4

ARMORLITE™ CF

- 70+% weight savings over NiCu braid
- Outstanding EMI/RFI shielding and conductivity
- Broader temperature range: -80°C to +300°C
- Highly corrosion resistant
- Superior flexibility and "windowing" resistance

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors

961-047 300°C ThermaRex Wire



961-047 THERMAREX HIGH TEMPERATURE WIRE



How To Order				
SAMPLE PART NUMBER		961-047	-N	-A 2
Series / Basic Part No.	961-047 = 300°C ThermaRex Wire			
Material	N = nickel/copper (-40°C to 300°C)			
Wire Size	See Table I			
Jacket Color	See Table II			

NOTES

1. Bend Radius is 3X the O.D.
2. Based on NEC Table 310.19
3. Voltage rating is 1000 volts AC
4. Insulation material is 300°C high temperature thermoplastic




TABLE 1

Awg Code	Awg	Strand/Count/Awg	Cir Mil (Nom)	Weight Lbs/1000' (Nom)	Ø A	Ø B	Nickel Copper DC Res @ 20°C ohms/1000ft	Nickel Copper Ampacity (Amps) 40°C Ambient (See Note 2)	Jacket Wall Thickness (In)
A	24	19/36	475	3.45	0.044 (1.12)	0.024 (0.61)	38.4	TBD	0.010 (0.25)
B	22	19/34	754	4.58	0.050 (1.27)	0.030 (0.76)	24.1	TBD	0.010 (0.25)
C	20	19/32	1216	6.43	0.068 (1.73)	0.038 (0.97)	14.8	16	0.015 (0.38)
D	16	37/31	2931	13.1	0.090 (2.29)	0.060 (1.52)	6.33	40	0.015 (0.38)
E	14	7x7/30	4900	21.1	0.121 (3.07)	0.091 (2.31)	3.87	59	0.015 (0.38)
F	12	7x7/29	6257	25.9	0.132 (3.35)	0.102 (2.59)	3.03	78	0.015 (0.38)
G	10	7x19/31	10535	41.5	0.157 (3.99)	0.127 (3.23)	1.81	107	0.015 (0.38)
H	8	7x19/29	16983	63.9	0.191 (4.85)	0.161 (4.09)	1.12	142	0.015 (0.38)
J	6	7x19/27	27200	TBD	0.233 (5.92)	0.203 (5.16)	0.68	TBD	0.015 (0.38)

Table II: Jacket Color Option

Color Code	Color
0	Black
1	Brown
2	Red
3	Orange
4	Yellow
5	Kelly Green
6	Blue
7	Violet
8	Gray
9	White

CORRECTION FACTORS

For ambient temperatures other than 40°C (104°F), multiply the allowable ampacities by the appropriate factor shown below.

Ambient Temp. (°C)	Correction Factors	Ambient Temp. (°C)	Correction Factors
41-50	0.98	161-170	0.71
51-60	0.96	171-180	0.69
61-70	0.94	181-190	0.66
71-80	0.92	191-200	0.63
81-90	0.90	201-210	0.60
91-100	0.88	211-220	0.56
101-110	0.86	221-230	0.53
111-120	0.84	231-240	0.49
121-130	0.81	241-250	0.45
131-140	0.79	251-260	0.40
141-150	0.77	261-270	0.35
151-160	0.74	271-280	0.29

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

960-2731, ThermaRex 300 °C Cable



960-2371 THERMAREX HIGH TEMPERATURE WIRE

How To Order			
SAMPLE PART NUMBER		960-2371	-20 -3
Series / Basic Part No.	960-2371 = 300°C ThermaRex Wire		
Average Size	16 AWG to 24 AWG		
Number of Wires	Up to Four Wires		



NOTES

1. Jacket: white high temp thermoplastic (300°C), 0.015" wall
2. Shield Material: armorlite CF (103-126)
3. Wires: per 961-047 (wire color per Table 1)
4. Conductor Material: nickel/copper (-65°C to 300°C)
5. Insulation Material: high temp thermoplastic (300°C)
6. Voltage Rating: 1000 VAC


Table I				
Number of Wires	Wire Number with Respective Color			
	1	2	3	4
1	White			
2	White	Blue		
3	White	Blue	Orange	
4	White	Blue	Orange	Green

HERMETIC, HIGH-TEMPERATURE MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-066 ThermaRex High-Temp Hermetic Receptacles



Features

- High-temperature tolerant glass-to-metal seal
- Non-removable solder cup or PC tail contacts
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, #8 standard and hybrid arrangements
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -65°C to +300°C
- Leak Rate: 1×10^{-7} ccHe/sec at 1 ATM pressure differential
- Dielectric withstanding voltage
#23 contacts: 750 VAC
#20, #16, #12 contacts: 1800 VAC
Coax: 800VAC
- Shell-to-Shell Conductivity: 10 mV max.
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell and jam-nut: 316L CRES
- Shell (-13 only): 304L CRES
- Hermetic contacts: nickel-iron alloy, gold plated
- Insulator, hermetic: vitreous glass
- Seals, O-rings: ThermaRex HT high-temperature elastomer

Series 806 ThermaRex high-temperature hermetic receptacles feature stainless steel shells and glass-to-metal seals. Rated for -65°C to +300°C operating temperature. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade hermetic connectors. These high-temperature tolerant connectors are suitable for pressurized bulkhead applications subject to vibration, moisture, and temperature extremes. Equipped with low-profile, non-threaded standoff. Available pin-face receptacle shell styles are square flange, jam-nut, and weld mount.

How To Order						
SAMPLE PART NUMBER		806-066	-07	Z1	8-7	C A
Product	806-066 = Hermetic Receptacle					
Mounting Type	02 = Square Flange 07 = Jam-nut 13 = Weld Mount					
Shell Finish	Z1 = Passivated ZL = Nickel Plated					
Arrangement Number (Shell Size - Insert Arr.)	See Table 1					
Contact Type	C = Pin, PC Terminal P = Pin, Solder Cup (806-066 only available as a pin-face receptacle)					
Polarization	A B C D E F					


Table I: Shell Size - Insert Arrangement																		
Contact Layout	Number of Contacts						Contact Layout	Number of Contacts						Contact Layout	Number of Contacts			
	20HD	16	12	8				20HD	16	12	8				20HD	16	12	8
8-3	3					10-2		2				16-4			4			
9-5	5					11-4		4				16-7			7			
10-8	8					12-5		5				18-8			8			
11-10	10					14-7		7				20-11			11			
12-15	15					16-12		12				22-13			13			
14-20	20					18-15		15				24-19			19			
16-31	31					20-22		22				10-1				1		
18-41	41					22-24		24				16-2				2		
20-55	55					24-35		35				18-3				3		
22-69	69					9-1			1			20-4				4		
24-92	92					12-2			2			22-5				5		
8-1		1				14-3			3			24-8				8		

HERMETIC, HIGH-TEMPERATURE MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

806-066 ThermaRex High-Temp Hermetic Receptacles




ThermaRex™
HT Hermetic

806-066-02 Square Flange Receptacle Dimensions




Shell Size	A Mating Thread	ØB Max. Flange	C Max Flange Flats	D SQ BSC Mntg Holes	±0.010(0.25) ØE	F Max Flange	Ø M Thru Mntg Holes	Ø S Thru
7	.4375-.067P-.2L-TS-2A	.968 (24.59)	.750 (19.05)	.469 (11.91)	.306 (7.77)	.100 (2.54)	.128 (3.25)	.445 (11.30)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	.822 (20.88)	.531 (13.49)	.387 (9.83)	.100 (2.54)	.128 (3.25)	.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	.885 (22.48)	.594 (15.09)	.468 (11.89)	.100 (2.54)	.128 (3.25)	.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	.913 (23.19)	.625 (15.88)	.546 (13.87)	.100 (2.54)	.128 (3.25)	.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	.960 (24.38)	.670 (17.02)	.586 (14.88)	.100 (2.54)	.128 (3.25)	.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	.765 (19.43)	.663 (16.84)	.100 (2.54)	.128 (3.25)	.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	.859 (21.82)	.743 (18.87)	.100 (2.54)	.128 (3.25)	.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	.938 (23.83)	.842 (21.39)	.100 (2.54)	.128 (3.25)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	.959 (24.36)	.100 (2.54)	.128 (3.25)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	1.105 (28.07)	.125 (3.18)	.154 (3.91)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	1.215 (30.86)	.125 (3.18)	.154 (3.91)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	1.335 (33.91)	.125 (3.18)	.154 (3.91)	1.525 (38.73)


806-066-07 Jam-nut Receptacle Dimensions



Shell Size	A Mating Thread	ØE Mntg Boss	G Max Flange	H Max Flange Flats	J Max Flange	K Thread Mounting	Ø N Mntg Hole	P Mntg Flat
7	.4375-.067P-.2L-TS-2A	.306 (7.77)	.848 (21.54)	.908 (23.06)	.100 (2.54)	M13x1.0-6g-0.100R	.522 (13.26)	.224 (5.69)
8	.5000-.067P-.2L-TS-2A	.387 (9.83)	.980 (24.89)	.920 (23.37)	.100 (2.54)	M15x1.0-6g-0.100R	.601 (15.27)	.256 (6.50)
9	.5625-.067P-.2L-TS-2A	.468 (11.89)	1.040 (26.42)	.980 (24.89)	.100 (2.54)	M16x1.0-6g-0.100R	.640 (16.26)	.287 (7.29)
10	.6250-.067P-.2L-TS-2A	.546 (13.87)	1.110 (28.19)	1.050 (26.67)	.100 (2.54)	M18x1.0-6g-0.100R	.719 (18.26)	.318 (8.08)
11	.6875-.067P-.2L-TS-2A	.586 (14.88)	1.160 (29.46)	1.110 (28.19)	.100 (2.54)	M19x1.0-6g-0.100R	.759 (19.28)	.350 (8.89)
12	.7500-.067P-.2L-TS-2A	.663 (16.84)	1.230 (31.24)	1.170 (29.72)	.100 (2.54)	M21x1.0-6g-0.100R	.837 (21.26)	.381 (9.68)
14	.8750-.067P-.2L-TS-2A	.743 (18.87)	1.360 (34.54)	1.320 (33.53)	.100 (2.54)	M24x1.0-6g-0.100R	.955 (24.26)	.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	.842 (21.39)	1.515 (38.48)	1.444 (36.68)	.100 (2.54)	M27x1.0-6g-0.100R	1.073 (27.25)	.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	.959 (24.36)	1.610 (40.89)	1.570 (39.88)	.100 (2.54)	M30x1.0-6g-0.100R	1.192 (30.28)	.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	1.105 (28.07)	1.850 (46.99)	1.760 (44.70)	.128 (3.25)	M34x1.0-6g-0.100R	1.349 (34.26)	.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	1.215 (30.86)	2.010 (51.05)	1.913 (48.59)	.128 (3.25)	M37x1.0-6g-0.100R	1.467 (37.26)	.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	1.335 (33.91)	2.195 (55.75)	2.070 (52.58)	.128 (3.25)	M41x1.0-6g-0.100R	1.624 (41.25)	.755 (19.18)

806-066-13 Weld Mount Receptacle Dimensions

Shell Size	A Mating Thread	ϕE	L $\pm .002 (0.05)$	$\phi R \pm .002 (0.05)$	ϕS
7	.4375-.067P-2L-TS-2A	.306 (7.77)	.725 (18.42)	.730 (18.54)	.445 (11.30)
8	.5000-.067P-2L-TS-2A	.387 (9.83)	.788 (20.02)	.793 (20.14)	.509 (12.93)
9	.5625-.067P-2L-TS-2A	.468 (11.89)	.912 (23.16)	.917 (23.29)	.577 (14.66)
10	.6250-.067P-2L-TS-2A	.546 (13.87)	.975 (24.76)	.980 (24.89)	.645 (16.38)
11	.6875-.067P-2L-TS-2A	.586 (14.88)	1.038 (26.37)	1.043 (26.49)	.712 (18.08)
12	.7500-.067P-2L-TS-2A	.663 (16.84)	1.100 (27.94)	1.105 (28.07)	.768 (19.51)
14	.8750-.067P-2L-TS-2A	.743 (18.87)	1.225 (31.12)	1.230 (31.24)	.890 (22.61)
16	1.0000-.067P-2L-TS-2A	.842 (21.39)	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-2L-TS-2A	.959 (24.36)	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-2L-TS-2A	1.105 (28.07)	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-2L-TS-2A	1.215 (30.86)	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-2L-TS-2A	1.335 (33.91)	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)

Series 806**Mil-Aero Connectors****806-060 ThermaRex Cryogenic Plug**

Extreme low-temperature 806-060 ThermaRex Cryo plug connectors are rated to perform in temperatures as low as -195° C. Intended for use in sub-zero harsh applications such as space vehicles or aircraft zones subject to high altitude, while providing size and weight savings compared to conventional aerospace-grade circular connectors. Rugged ratchet mechanism and unique triple-start mating thread provide improved de-coupling resistance under vibration. Shell styles include integrated metric accessory thread or band platform.

Features

- Operating temperature -195°C to +200°C
- Special low-temperature 300G shock and aerospace vibration testing while submerged in liquid nitrogen
- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell: passivated CRES or Aluminum Alloy
- Contacts: copper alloy, gold plate
- Insulator: high grade rigid dielectric
- Interfacial seal, grommet: Duralectric K low-temp silicone

How To Order ThermaRex Series 806 Mil-Aero Plug						
SAMPLE PART NUMBER		806-060	-Z1	11-19	S	M A
Series / Basic Part No.	806-060 ThermaRex Cryogenic Plug					
Material/Finish	ME = Aluminum Alloy / Electroless Nickel Z1 = Stainless Steel / Passivated					
Shell Size/Insert Arr.	See Table I					
Contact Style	A = Pin connector less contacts P = Pin B = Socket connector Less contacts S = Socket					
Shell Style	M = Metric (Accessory Thread) B = Band (platform for attaching cable shield).					
Polarization	A, B, C, D, E, F					


Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

CRYOGENIC, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

806-060 ThermaRex Cryogenic Plug



BAND PLATFORM

METRIC ACCESSORY THREAD

806-060 Dimensions				
SHELL SIZE	ØA MAX	B THREAD	C MATING THREAD	Ø D
7	.606 (15.39)	M8X 1-6g-.100R	.4375-.067P-.2L-TS-2B	.267 (6.78)
8	.676 (17.17)	M10 X 1-6g-.100R	.500-.067P-.2L-TS-2B	.327 (8.31)
9	.774 (19.66)	M12 X 1-6g-.100R	.562-.067P-.2L-TS-2B	.406 (10.31)
10	.832 (21.13)	M14 X 1-6g-.100R	.625-.067P-.2L-TS-2B	.484 (12.29)
11	.890 (22.61)	M15 X 1-6g-.100R	.688-.067P-.2L-TS-2B	.524 (13.31)
12	.950 (24.13)	M17 X 1-6g-.100R	.750-.067P-.2L-TS-2B	.603 (15.32)
14	1.110 (28.19)	M19 X 1-6g-.100R	.875-.067P-.2L-TS-2B	.681 (17.30)
16	1.170 (29.72)	M22 X 1-6g-.100R	1.000-.067P-.2L-TS-2B	.782 (19.86)
18	1.350 (34.29)	M25 X 1-6g-.100R	1.1250-.067P-.2L-TS-2B	.899 (22.83)
20	1.470 (37.34)	M28 X 1-6g-.100R	1.250-.067P-.2L-TS-2B	1.043 (26.49)
22	1.600 (40.64)	M31 X 1-6g-.100R	1.375-.067P-.2L-TS-2B	1.155 (29.34)
24	1.710 (43.43)	M34 X 1-6g-.100R	1.500-.067P-.2L-TS-2B	1.273 (32.33)

NOTES:

1. Boot groove for use with overmolded strain relief or 809-060 heat shrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband



Extreme low-temperature 806-061 ThermaRex receptacle connectors are rated to perform in temperatures as low as -195° C. Intended for use in sub-zero harsh applications such as space vehicles or aircraft zones subject to high altitude, while providing size and weight savings compared to conventional aerospace-grade circular connectors. Unique triple-start mating thread provides improved de-coupling resistance under vibration. Jam nut receptacle styles include integrated metric accessory thread or band platform.

How To Order ThermaRex Series 806 Mil-Aero Jam-nut Receptacle

SAMPLE PART NUMBER		806-061	-Z1	11-19	S	M	A
Series / Basic Part No.	806-061 ThermaRex Cryogenic Jam Nut Receptacle						
Material/Finish	ME = Aluminum Alloy / Electroless Nickel Z1 = Stainless Steel / Passivated						
Shell Size/Insert Arr.	See Table I						
Contact Style	A = Pin connector less contacts B = Socket connector Less contacts		P = Pin S = Socket				
Shell Style	M = Metric (Accessory Thread) B = Band (platform for attaching cable shield).						
Polarization	A, B, C, D, E, F						

Features

- Operating temperature -195°C to +200°C
- Special low-temperature 300G shock and aerospace vibration testing while submerged in liquid nitrogen
- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications


- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction


- Shell, hex nut: passivated CRES or Aluminum Alloy
- Contacts: copper alloy, gold plate
- Insulator: high grade rigid dielectric
- Interfacial seal, grommet: Duralectric K low-temp silicone

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		12-14	12			2	
9-5		5				14-3				3		16-32	28			4	
10-8		8				16-4				4		16-42	40			2	
11-10		10				16-7				7		18-62	60			2	
12-15		15				18-8				8		14-20A	19				1
14-20		20				20-11				11		16-22	20				2
16-31		31				22-13				13		18-21	18				3
18-41		41				24-19				19		20-28	24				4
20-55		55				10-1					1	22-44	40				4
						16-2					2	24-97	93				4




**ThermaRex™
CRYO**



SHELL STYLE M
METRIC ACCESSORY THREAD

SHELL STYLE B
NANO BAND PLATFORM


Dimensions							
Shell Size	ØA Max	B Thread	C Max	D Mating Thread	E Max	F Thread	ØH
7	.848 (21.54)	M8X 1-6g-.100R	.908 (23.06)	.4375-.067P-.2L-TS-2A	0.100 (2.54)	M13 X 1-6g-.100R	.265 (6.73)
8	.980 (24.89)	M10 X 1-6g-.100R	.920 (23.37)	.5000-.067P-.2L-TS-2A		M15 X 1-6g-.100R	.327 (8.31)
9	1.040 (26.42)	M12 X 1-6g-.100R	.980 (24.89)	.5625-.067P-.2L-TS-2A		M16 X 1-6g-.100R	.406 (10.31)
10	1.110 (28.19)	M14 X 1-6g-.100R	1.050 (26.67)	.6250-.067P-.2L-TS-2A		M18 X 1-6g-.100R	.484 (12.29)
11	1.160 (29.46)	M15 X 1-6g-.100R	1.110 (28.19)	.6875-.067P-.2L-TS-2A		M19 X 1-6g-.100R	.524 (13.31)
12	1.230 (31.24)	M17 X 1-6g-.100R	1.170 (29.72)	.7500-.067P-.2L-TS-2A		M21 X 1-6g-.100R	.603 (15.32)
14	1.360 (34.54)	M19 X 1-6g-.100R	1.320 (33.53)	.8750-.067P-.2L-TS-2A		M24 X 1-6g-.100R	.681 (17.30)
16	1.515 (38.48)	M22 X 1-6g-.100R	1.444 (36.68)	1.000-.067P-.2L-TS-2A		M27 X 1-6g-.100R	.782 (19.86)
18	1.610 (40.89)	M25 X 1-6g-.100R	1.570 (39.88)	1.1250-.067P-.2L-TS-2A		M30 X 1-6g-.100R	.899 (22.83)
20	1.850 (46.99)	M28 X 1-6g-.100R	1.760 (44.70)	1.250-.067P-.2L-TS-2A		M34 X 1-6g-.100R	1.043 (26.49)
22	2.010 (51.05)	M31 X 1-6g-.100R	1.913 (48.59)	1.3750-.067P-.2L-TS-2A	0.128 (3.25)	M37 X 1-6g-.100R	1.155 (29.34)
24	2.195 (55.75)	M34 X 1-6g-.100R	2.070 (52.58)	1.500-.067P-.2L-TS-2A		M41 X 1-6g-.100R	1.273 (32.33)



Recommended Mounting Hole		
SHELL SIZE	K +.005 (0.13) 0.000 (0.00)	J +.005 (0.13) 0.00 (0.00)
7	.224 (5.69)	.522 (13.26)
8	.256 (6.50)	.601 (15.27)
9	.287 (7.29)	.640 (16.26)
10	.318 (8.08)	.719 (18.26)
11	.350 (8.89)	.759 (19.28)
12	.381 (9.68)	.837 (21.26)
14	.443 (11.25)	.955 (24.26)
16	.505 (12.83)	1.073 (27.25)
18	.568 (14.43)	1.192 (30.28)
20	.630 (16.00)	1.349 (34.26)
22	.693 (17.60)	1.467 (37.26)
24	.755 (19.18)	1.624 (41.25)

NOTES:

1. Boot groove for use with overmold strain relief or 809-060 heat shrink boots
2. Terminate shield with Glenair Band-Master ATS tool 601-108 and Glenair Nanoband



Features

- Operating temperature -195°C to +200°C
- Special low-temperature 300G shock and aerospace vibration testing while submerged in liquid nitrogen
- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak



Connector Construction

- Shell, hex nut: passivated CRES or Aluminum Alloy
- Contacts: copper alloy, gold plate
- Insulator: high grade rigid dielectric
- Interfacial seal, grommet: Duraelectric K low-temp silicone


Extreme low-temperature 806-085 ThermaRex receptacle connectors are rated to perform in temperatures as low as -195° C. Intended for use in sub-zero harsh applications such as space vehicles or aircraft zones subject to high altitude, while providing size and weight savings compared to conventional aerospace-grade circular connectors. Unique triple-start mating thread provides improved de-coupling resistance under vibration. Pin or socket PC tails or solder cup contacts. Integral PCB stand off with standard 4-40 UNC threads and locatin post.

How To Order ThermaRex Series 806 Mil-Aero Jam-nut Receptacle						
SAMPLE PART NUMBER		806-085	-Z1	11-19	S	M A
Series / Basic Part No.	806-085 ThermaRex Cryogenic Jam Nut PCB Standoff Receptacle					
Material/Finish	ME = Aluminum Alloy / Electroless Nickel Z1 = Stainless Steel / Passivated					
Shell Size/Insert Arr.	See Table I					
Contact Style	P = Pin E = Solder cup, pin S = Socket F = Solder cup, SKT					
PC Tail Length	1 = .125±.025 Solder Cup = Omit					
Polarization	A, B, C, D, E, F					

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		12-14	12			2	
9-5		5				14-3				3		16-32	28			4	
10-8		8				16-4				4		16-42	40			2	
11-10		10				16-7				7		18-62	60			2	
12-15		15				18-8				8		14-20A	19				1
14-20		20				20-11				11		16-22	20				2
16-31		31				22-13				13		18-21	18				3
18-41		41				24-19				19		20-28	24				4
20-55		55				10-1					1	22-44	40				4
						16-2					2	24-97	93				4



RECOMMENDED MOUNTING HOLE DIMENSIONS

**PC Tail Dimensions**

CONTACT SIZE	PC TAIL DIA
8	.180 (4.57)
12	.094 (2.39)
16	.062 (1.57)
20	.030 (0.76)
22	.020 (0.51)

Polarization Keyway Code


POS	A	B	C	D
A	105	140	215	265
B	102	170	248	305
C	80	150	230	295
D	68	140	205	275
E	64	155	234	304
F	72	120	200	298

Dimensions

SHELL SIZE	A MAX	B THREAD	C MAX	D	E MAX	F MATING THREAD	G FLAT
7	0.848 (21.54)	M8X 1-6g-.100R	0.908 (23.06)	0.489 (12.42)	0.100 (2.54)	.4375-.067P-.2L-TS-2A	0.463 (11.76)
8	0.980 (24.89)	M15 X 1-6g-.100R	0.920 (23.37)	0.534 (13.56)	0.100 (2.54)	.5000-.067P-.2L-TS-2A	0.534 (13.56)
9	1.040 (26.42)	M16 X 1-6g-.100R	0.980 (24.89)	0.579 (14.71)	0.100 (2.54)	.5625-.067P-.2L-TS-2A	0.585 (14.86)
10	1.110 (28.19)	M18 X 1-6g-.100R	1.050 (26.67)	0.679 (17.25)	0.100 (2.54)	.6250-.067P-.2L-TS-2A	0.656 (16.66)
11	1.160 (29.46)	M19 X 1-6g-.100R	1.110 (28.19)	0.734 (18.64)	0.100 (2.54)	.6875-.067P-.2L-TS-2A	0.707 (17.96)
12	1.230 (31.24)	M21 X 1-6g-.100R	1.170 (29.72)	0.804 (20.42)	0.100 (2.54)	.7500-.067P-.2L-TS-2A	0.777 (19.74)
14	1.360 (34.54)	M24 X 1-6g-.100R	1.320 (33.53)	0.891 (22.63)	0.100 (2.54)	.8750-.067P-.2L-TS-2A	0.899 (22.83)
16	1.515 (38.48)	M27 X 1-6g-.100R	1.444 (36.68)	1.049 (26.64)	0.100 (2.54)	1.000-.067P-.2L-TS-2A	1.020 (25.91)
18	1.610 (40.89)	M30 X 1-6g-.100R	1.570 (39.88)	1.148 (29.16)	0.100 (2.54)	1.1250-.067P-.2L-TS-2A	1.142 (29.01)
20	1.850 (46.99)	M34 X 1-6g-.100R	1.760 (44.70)	1.252 (31.80)	0.128 (3.25)	1.250-.067P-.2L-TS-2A	1.283 (32.59)
22	2.010 (51.05)	M37 X 1-6g-.100R	1.913 (48.59)	1.369 (34.77)	0.128 (3.25)	1.3750-.067P-.2L-TS-2A	1.405 (35.69)
24	2.195 (55.75)	M41 X 1-6g-.100R	2.070 (52.58)	1.509 (38.33)	0.128 (3.25)	1.5000-.067P-.2L-TS-2A	1.546 (39.27)

Panel Cutout Dimensions

SHELL SIZE	M +.005 0.000 (0.00)	N +.005 0.00 (0.00)
7	0.224 (5.69)	0.522 (13.26)
8	0.256 (6.50)	0.601 (15.27)
9	0.287 (7.29)	0.640 (16.26)
10	0.318 (8.08)	0.719 (18.26)
11	0.350 (8.89)	0.759 (19.28)
12	0.381 (9.68)	0.837 (21.26)
14	0.443 (11.25)	0.955 (24.26)
16	0.505 (12.83)	1.073 (27.25)
18	0.568 (14.43)	1.192 (30.28)
20	0.630 (16.00)	1.349 (34.26)
22	0.693 (17.60)	1.467 (37.26)
24	0.755 (19.18)	1.624 (41.25)

**Features**

- Operating temperature -195°C to +200°C
- Special low-temperature 300G shock and aerospace vibration testing while submerged in liquid nitrogen
- Triple-start stub ACME mating thread
- High density #22HD and #20HD arrangements for reduced size and weight plus #16, #12 and #8 standard and hybrid contact layouts
- Aerospace-grade materials, construction
- Band platform or accessory threads

Specifications

- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: varies, contact factory
#12 contacts: varies, contact factory
#8 contacts: varies, contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell, hex nut: passivated CRES or Aluminum Alloy
- Contacts: copper alloy, gold plate
- Insulator: high grade rigid dielectric
- Interfacial seal, grommet: Duraelectric K low-temp silicone




Extreme low-temperature 806-086 ThermaRex receptacle connectors are rated to perform in temperatures as low as -195° C. Intended for use in sub-zero harsh applications such as space vehicles or aircraft zones subject to high altitude, while providing size and weight savings compared to conventional aerospace-grade circular connectors. Unique triple-start mating thread provides improved de-coupling resistance under vibration. Pin or socket PC tails or solder cup contacts. Integral PCB stand off with standard 4-40 UNC threads and locatin post.

How To Order ThermaRex Series 806 Mil-Aero Jam-nut Receptacle

SAMPLE PART NUMBER		806-086	-Z1	11-19	S	M	A
Series / Basic Part No.	806-086 ThermaRex Cryogenic Square Flange PCB Standoff Receptacle						
Material/Finish	ME = Aluminum Alloy / Electroless Nickel Z1 = Stainless Steel / Passivated						
Shell Size/Insert Arr.	See Table I						
Contact Style	P = Pin E = Solder cup, pin S = Socket F = Solder cup, SKT						
PC Tail Length	1 = .125±.025 Solder Cup = Omit						
Polarization	A, B, C, D, E, F						

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		12-14	12			2	
9-5		5				14-3				3		16-32	28			4	
10-8		8				16-4				4		16-42	40			2	
11-10		10				16-7				7		18-62	60			2	
12-15		15				18-8				8		14-20A	19				1
14-20		20				20-11				11		16-22	20				2
16-31		31				22-13				13		18-21	18				3
18-41		41				24-19				19		20-28	24				4
20-55		55				10-1					1	22-44	40				4
						16-2					2	24-97	93				4

**Polarization Keyway Code**


POS	A	B	C	D
A	105	140	215	265
B	102	170	248	305
C	80	150	230	295
D	68	140	205	275
E	64	155	234	304
F	72	120	200	298

Dimensions

SHELL SIZE	A MAX	B	C MAX	D	E MOUNTNG HOLE	F FLANGE THICKNESS	G MATING THREAD
7	0.968 (24.59)	0.469 (11.91)	0.750 (19.05)	0.489 (12.42)	0.128 (3.25)	0.100 (2.54)	.4375-.067P-.2L-TS-2A
8	1.04 (26.42)	0.531 (13.49)	0.822 (20.88)	0.534 (13.56)	0.128 (3.25)	0.100 (2.54)	.5000-.067P-.2L-TS-2A
9	1.13 (28.70)	0.594 (15.09)	0.885 (22.48)	0.579 (14.71)	0.128 (3.25)	0.100 (2.54)	.5625-.067P-.2L-TS-2A
10	1.174 (29.82)	0.625 (15.88)	0.913 (23.19)	0.679 (17.25)	0.128 (3.25)	0.100 (2.54)	.6250-.067P-.2L-TS-2A
11	1.240 (31.50)	0.670 (17.02)	0.960 (24.38)	0.734 (18.64)	0.128 (3.25)	0.100 (2.54)	.6875-.067P-.2L-TS-2A
12	1.354 (34.39)	0.765 (19.43)	1.040 (26.42)	0.804 (20.42)	0.128 (3.25)	0.100 (2.54)	.7500-.067P-.2L-TS-2A
14	1.51 (38.35)	0.859 (21.82)	1.133 (28.78)	0.891 (22.63)	0.128 (3.25)	0.100 (2.54)	.8750-.067P-.2L-TS-2A
16	1.620 (41.15)	0.938 (23.83)	1.242 (31.55)	1.049 (26.64)	0.128 (3.25)	0.100 (2.54)	1.000-.067P-.2L-TS-2A
18	1.784 (45.31)	1.016 (25.81)	1.343 (34.11)	1.148 (29.16)	0.128 (3.25)	0.100 (2.54)	1.1250-.067P-.2L-TS-2A
20	1.910 (48.51)	1.109 (28.17)	1.444 (36.68)	1.252 (31.80)	0.154 (3.91)	0.125 (3.18)	1.250-.067P-.2L-TS-2A
22	2.083 (52.91)	1.203 (30.56)	1.570 (39.88)	1.369 (34.77)	0.154 (3.91)	0.125 (3.18)	1.3750-.067P-.2L-TS-2A
24	2.200 (55.88)	1.312 (33.32)	1.704 (43.28)	1.509 (38.33)	0.154 (3.91)	0.125 (3.18)	1.5000-.067P-.2L-TS-2A

Panel Cutout Dimensions

SHELL SIZE	J	H WITH CLINCH NUT	H WITHOUT CLINCH NUT
7	0.443 (11.25)	0.128 (3.25)	0.128 (3.25)
8	0.509 (12.93)	0.128 (3.25)	0.128 (3.25)
9	0.577 (14.66)	0.128 (3.25)	0.128 (3.25)
10	0.645 (16.38)	0.128 (3.25)	0.128 (3.25)
11	0.712 (18.08)	0.128 (3.25)	0.128 (3.25)
12	0.768 (19.51)	0.128 (3.25)	0.128 (3.25)
14	0.890 (22.61)	0.128 (3.25)	0.128 (3.25)
16	1.015 (25.78)	0.128 (3.25)	0.128 (3.25)
18	1.125 (28.58)	0.128 (3.25)	0.128 (3.25)
20	1.275 (32.39)	0.128 (3.25)	0.154 (3.91)
22	1.400 (35.56)	0.128 (3.25)	0.154 (3.91)
24	1.525 (38.74)	0.128 (3.25)	0.154 (3.91)




Material/Finish

- Shell & jam-nut: 304L CRES/PER P/N DEV
- Contacts, hermetic: Nickel-iron alloy/gold plate
- Contacts, sockets: Copper alloy/gold plate
- Hoods, sockets: 305 CRES/passivate
- Insulator, hermetic: Vitreous glass
- Insulator, Socket: Peek
- Seals & O-Rings: Duraelectric™ K

Test Criteria

- Leak rate: <1 X 10⁻⁷ ccHe/sec @ 1 ATM. delta pressure
- DWV: 1300 VAC (#22 Contacts)
1800 VAC (#20, 16, 12, and 8 Contacts)
- I.R.: 5000 MEGOHMS MIN @ 500 VDC
- Current capacity: 3 A (#22), 5 A (#20), 10 A (#16), 17 AMPS (#12), 33 A (#8)

Polarization Key Code



POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

PC Tail Diameter

Cont. Size	"Ø W" ±.002 PC Tail
22	.020 (0.51)
20	.030 (0.76)
16	.063 (1.60)
12	.094 (2.39)
8	.180 (4.57)

Series 806 cryogenic capable hermetic receptacles feature stainless steel shells and glass-to-metal seals. Rated for -195°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade hermetic connectors. These high performance, parylene compatible connectors are suitable for pressurized bulkhead applications subject to vibration, moisture, and temperature extremes.

How To Order						
SAMPLE PART NUMBER		806-088	S	-07	Z1	8-7 C A
Series / Basic Part No.	806-088 Solder Cup/PC Tail Termination Hermetic Receptacle					
Rear Configuration	B = Banding Porch S = Standard Rear T = Accessory Threads					
Mounting Type	02 = Box Mount 03 = Solder Mount 07 = Jam-Nut Mount 13 = Weld Mount					
Finish	Z1 = Passivated ZL = Nickel Plated					
Shell Size - Insert Arr.	See Table I					
Contact Style	C = PC Term., Pin (only available for standoff rear configuration style) D = PC Term., Skt (only available for standoff rear configuration style) P = Solder Cup, Pin S = Solder Cup, Socket					
Polarization	A, B, C, D					

Table I: Shell Size - Insert Arrangement


Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

Series 806 Mil-Aero Connectors

806-088 Solder Cup/PC Tail Termination Hermetic Receptacle



806-088-02 Box Mount Receptacle Dimensions





S = Standard

B = Banding Porch



T = Accessory Thread

Shell Size	"A" Thread Mating -2L-TS-2A	"Ø B" Max Flange	"C" Square Max Flange Flats	"D" Square BSC Mounting Holes	"Ø E" ±.010 Mounting Boss	"F" Max Flange	"Ø M" Thru MTG Holes	"Ø S" Thru	"Ø T"	"V" Rear Accessory Thread
7	.4375-.067P	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	0.306 (7.77)	0.100 (2.54)	0.128 (3.25)	0.445 (11.30)	.265 (6.73)	M8 X 1 6g .100R
8	.5000-.067P	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)	0.387 (9.83)			0.509 (12.93)	.327 (8.31)	M10 X 1 6g .100R
9	.5625-.067P	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)	0.468 (11.89)			0.577 (14.66)	.406 (10.31)	M12 X 1 6g .100R
10	.6250-.067P	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	0.546 (13.87)			0.645 (16.38)	.484 (12.29)	M14 X 1 6g .100R
11	.6875-.067P	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)	0.586 (14.88)			0.712 (18.08)	.524 (13.31)	M15 X 1 6g .100R
12	.7500-.067P	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)	0.663 (16.84)			0.768 (19.51)	.603 (15.32)	M17 X 1 6g .100R
14	.8750-.067P	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)	0.743 (18.87)			0.890 (22.61)	.681 (17.30)	M19 X 1 6g .100R
16	1.0000-.067P	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	0.842 (21.39)			1.015 (25.78)	.782 (19.86)	M22 X 1 6g .100R
18	1.1250-.067P	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	0.959 (24.36)	0.125 (3.18)	0.154 (3.91)	1.125 (28.58)	.899 (22.83)	M25 X 1 6g .100R
20	1.2500-.067P	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	1.105 (28.07)			1.275 (32.39)	1.043 (26.49)	M28 X 1 6g .100R
22	1.3750-.067P	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	1.215 (30.86)			1.400 (35.56)	1.155 (29.34)	M31 X 1 6g .100R
24	1.5000-.067P	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	1.335 (33.91)			1.525 (38.73)	1.273 (32.33)	M34 X 1 6g .100R





806-088-03 Solder Mount Receptacle Dimensions

Shell Size	"A" Thread Mating	"Ø E" ±.010 Mounting Boss	"Ø LL" Flange	"Ø T"	"V" Rear Accessory Thread
7	.4375-.067P-.2L-TS-2A	0.306 (7.77)	0.520 (13.21)	.265 (6.73)	M8 X 1 6g .100R
8	.5000-.067P-.2L-TS-2A	0.387 (9.83)	0.581 (14.76)	.327 (8.31)	M10 X 1 6g .100R
9	.5625-.067P-.2L-TS-2A	0.468 (11.89)	0.649 (16.48)	.406 (10.31)	M12 X 1 6g .100R
10	.6250-.067P-.2L-TS-2A	0.546 (13.87)	0.717 (18.21)	.484 (12.29)	M14 X 1 6g .100R
11	.6875-.067P-.2L-TS-2A	0.586 (14.88)	0.784 (19.91)	.524 (13.31)	M15 X 1 6g .100R
12	.7500-.067P-.2L-TS-2A	0.663 (16.84)	0.841 (21.36)	.603 (15.32)	M17 X 1 6g .100R
14	.8750-.067P-.2L-TS-2A	0.743 (18.87)	0.962 (24.43)	.681 (17.30)	M19 X 1 6g .100R
16	1.0000-.067P-.2L-TS-2A	0.842 (21.39)	1.087 (27.61)	.782 (19.86)	M22 X 1 6g .100R
18	1.1250-.067P-.2L-TS-2A	0.959 (24.36)	1.197 (30.40)	.899 (22.83)	M25 X 1 6g .100R
20	1.2500-.067P-.2L-TS-2A	1.105 (28.07)	1.347 (34.21)	1.043 (26.49)	M28 X 1 6g .100R
22	1.3750-.067P-.2L-TS-2A	1.215 (30.86)	1.472 (37.39)	1.155 (29.34)	M31 X 1 6g .100R
24	1.5000-.067P-.2L-TS-2A	1.335 (33.91)	1.597 (40.56)	1.273 (32.33)	M34 X 1 6g .100R


**806-088-07 Jam-Nut Mount Receptacle Dimensions**

Shell Size	"A" Thread Mating -2L-TS-2A	"Ø E" ±.010 Mounting Boss	"Ø G" Max Flange	"H" Square Max Flange Flats	"J" Max Flange	"K" Thread Mounting	"Ø N" +.005/- .000 Mounting Hole	"P" +.005/- .000 Mounting Flat	"Ø T"	"V" Rear Accessory Thread
7	.4375-.067P	0.306 (7.77)	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	M13 X 1-6g .100R	0.522 (13.26)	0.224 (5.69)	.265 (6.73)	M8 X 1 6g .100R
8	.5000-.067P	0.387 (9.83)	0.980 (24.89)	0.920 (23.37)		M15 X 1-6g .100R	0.601 (15.27)	0.256 (6.50)	.327 (8.31)	M10 X 1 6g .100R
9	.5625-.067P	0.468 (11.89)	1.040 (26.42)	0.980 (24.89)		M16 X 1-6g .100R	0.640 (16.26)	0.287 (7.29)	.406 (10.31)	M12 X 1 6g .100R
10	.6250-.067P	0.546 (13.87)	1.110 (28.19)	1.050 (26.67)		M18 X 1-6g .100R	0.719 (18.26)	0.318 (8.08)	.484 (12.29)	M14 X 1 6g .100R
11	.6875-.067P	0.586 (14.88)	1.160 (29.46)	1.110 (28.19)		M19 X 1-6g .100R	0.759 (19.28)	0.350 (8.89)	.524 (13.31)	M15 X 1 6g .100R
12	.7500-.067P	0.663 (16.84)	1.230 (31.24)	1.170 (29.72)		M21 X 1-6g .100R	0.837 (21.26)	0.381 (9.68)	.603 (15.32)	M17 X 1 6g .100R
14	.8750-.067P	0.743 (18.87)	1.360 (34.54)	1.320 (33.53)		M24 X 1-6g .100R	0.955 (24.26)	0.443 (11.25)	.681 (17.30)	M19 X 1 6g .100R
16	1.0000-.067P	0.842 (21.39)	1.515 (38.48)	1.444 (36.68)		M27 X 1-6g .100R	1.073 (27.25)	0.505 (12.83)	.782 (19.86)	M22 X 1 6g .100R
18	1.1250-.067P	0.959 (24.36)	1.610 (40.89)	1.570 (39.88)	0.128 (3.25)	M30 X 1-6g .100R	1.192 (30.28)	0.568 (14.43)	.899 (22.83)	M25 X 1 6g .100R
20	1.2500-.067P	1.105 (28.07)	1.850 (46.99)	1.760 (44.70)		M34 X 1-6g .100R	1.349 (34.26)	0.630 (16.00)	1.043 (26.49)	M28 X 1 6g .100R
22	1.3750-.067P	1.215 (30.86)	2.010 (51.05)	1.913 (48.59)		M37 X 1-6g .100R	1.467 (37.26)	0.693 (17.60)	1.155 (29.34)	M31 X 1 6g .100R
24	1.5000-.067P	1.335 (33.91)	2.195 (55.75)	2.070 (52.58)		M41 X 1-6g .100R	1.624 (41.25)	0.755 (19.18)	1.273 (32.33)	M34 X 1 6g .100R




806-088-13 Weld Mount Receptacle Dimensions

Shell Size	"A" Thread Mating	"Ø E" ±.005 Banding Porch	"Ø L" ±.002 Flange	"Ø R" ±.002 MTG Hole	"Ø S" Thru	"Ø T"	"V" Rear Accessory Thread
7	.4375-.067P-.2L-TS-2A	0.265 (6.73)	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)	.265 (6.73)	M8 X 1 6g .100R
8	.5000-.067P-.2L-TS-2A	0.327 (8.31)	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)	.327 (8.31)	M10 X 1 6g .100R
9	.5625-.067P-.2L-TS-2A	0.406 (10.31)	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)	.406 (10.31)	M12 X 1 6g .100R
10	.6250-.067P-.2L-TS-2A	0.484 (12.29)	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)	.484 (12.29)	M14 X 1 6g .100R
11	.6875-.067P-.2L-TS-2A	0.524 (13.31)	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)	.524 (13.31)	M15 X 1 6g .100R
12	.7500-.067P-.2L-TS-2A	0.603 (15.32)	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)	.603 (15.32)	M17 X 1 6g .100R
14	.8750-.067P-.2L-TS-2A	0.681 (17.30)	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)	.681 (17.30)	M19 X 1 6g .100R
16	1.0000-.067P-.2L-TS-2A	0.782 (19.86)	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)	.782 (19.86)	M22 X 1 6g .100R
18	1.1250-.067P-.2L-TS-2A	0.899 (22.83)	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)	.899 (22.83)	M25 X 1 6g .100R
20	1.2500-.067P-.2L-TS-2A	1.043 (26.49)	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)	1.043 (26.49)	M28 X 1 6g .100R
22	1.3750-.067P-.2L-TS-2A	1.155 (29.34)	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)	1.155 (29.34)	M31 X 1 6g .100R
24	1.5000-.067P-.2L-TS-2A	1.273 (32.33)	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)	1.273 (32.33)	M34 X 1 6g .100R



Series 806 Mil-Aero Connectors

806-089 Hermetic Bulkhead Feedthrough



ThermaRex™
CRYO

Series 806 cryogenic capable hermetic feedthroughs feature stainless steel shells and glass-to-metal seals. Rated for -195°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade hermetic connectors. These high performance connectors are suitable for pressurized bulkhead applications subject to vibration, moisture, and temperature extremes.


Material/Finish

- Shell & jam-nut: SS304L CRES / per p/n dev
- Contacts, hermetic: Nickel-iron alloy / gold plate
- Contacts, sockets: Copper alloy / gold plate
- Hoods, sockets: 305 CRES / passivate
- Insulator, hermetic: Vitreous glass
- Insulator, socket: High grade dielectric
- Seals & O-rings: Duralectric™ K

Test Criteria

- Leak rate: $<1 \times 10^{-7}$ ccHe/sec @ 1 ATM. delta pressure
- DWV: 1300 VAC (#22 contacts)
1800 VAC (#20, #16, #12 contacts)
1000 VAC (#8 contacts)
- I.R. - 5000 MEGOHMS MIN @ 500 VDC

Polarization Key Code



POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

Panel Thickness


Code	"T" Max	"U" Max
-01	1.275 (32.39)	.750 (19.05)
-02	1.400 (35.56)	.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

How To Order ThermaRex Series 806 Mil-Aero Feedthrough


SAMPLE PART NUMBER		806-089	-07	Z1	8-7	P	A	-01
Series / Basic Part No.	806-089 Bulkhead Feedthrough							
Mounting Type	02 = Box Mount 07 = Jam-Nut Mount 13 = Weld Mount							
Finish	Z1 = Passivated ZL = Nickel Plated							
Shell Size - Insert Arr.	See Table I							
Contact Style	P = Pin On Panel Side, Socket Opposite S = Socket On Panel Side, Pin Opposite PP = Pin-Pin Feedthrough SS = Socket-Socket Feedthrough							
Polarization	A, B, C, D							
Panel Thickness	-01 = .125 -02 = .250 -03 = .500							

Table I: Shell Size - Insert Arrangement


Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

806-089-02 Box Mount Dimensions

Shell Size	"A" Thread Mating	"Ø B" Max Flange	"C" Square Max Flange Flats	"D" Square BSC Mounting Holes	"Ø S" Thru	"F" Max Flange	"Ø M" Thru MTG Holes
7	.4375-.067P-.2L-TS-2A	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	0.445 (11.30)	0.100 (2.54)	0.128 (3.25)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)	0.509 (12.93)		
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)	0.577 (14.66)		
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	0.645 (16.38)		
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)	0.712 (18.08)		
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)	0.768 (19.51)		
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)	0.890 (22.61)		
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	1.015 (25.78)	0.125 (3.18)	0.154 (3.91)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	1.125 (28.58)		
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	1.275 (32.39)		
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	1.400 (35.56)		
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	1.525 (38.73)		

806-089-07 Jam-Nut Mount Dimensions

Shell Size	"A" Thread Mating	"ø G" MAX Flange	"H" Square Max Flange Flats	"J" Max Flange	"K" Thread Mounting	"ø N" +.005/- .000 Mounting Hole	"P" +.005/- .000 Mounting Flat
7	.4375-.067P-.2L-TS-2A	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	M13 X 1-6g-.100R	0.522 (13.26)	0.224 (5.69)
8	.5000-.067P-.2L-TS-2A	0.980 (24.89)	0.920 (23.37)		M15 X 1-6g .100R	0.601 (15.27)	0.256 (6.50)
9	.5625-.067P-.2L-TS-2A	1.040 (26.42)	0.980 (24.89)		M16 X 1-6g .100R	0.640 (16.26)	0.287 (7.29)
10	.6250-.067P-.2L-TS-2A	1.110 (28.19)	1.050 (26.67)		M18 X 1-6g .100R	0.719 (18.26)	0.318 (8.08)
11	.6875-.067P-.2L-TS-2A	1.160 (29.46)	1.110 (28.19)		M19 X 1-6g .100R	0.759 (19.28)	0.350 (8.89)
12	.7500-.067P-.2L-TS-2A	1.230 (31.24)	1.170 (29.72)		M21 X 1-6g .100R	0.837 (21.26)	0.381 (9.68)
14	.8750-.067P-.2L-TS-2A	1.360 (34.54)	1.320 (33.53)		M24 X 1-6g .100R	0.955 (24.26)	0.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	1.515 (38.48)	1.444 (36.68)		M27 X 1-6g .100R	1.073 (27.25)	0.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	1.610 (40.89)	1.570 (39.88)		M30 X 1-6g .100R	1.192 (30.28)	0.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	1.850 (46.99)	1.760 (44.70)		M34 X 1-6g .100R	1.349 (34.26)	0.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	2.010 (51.05)	1.913 (48.59)	0.128 (3.25)	M37 X 1-6g .100R	1.467 (37.26)	0.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	2.195 (55.75)	2.070 (52.58)		M41 X 1-6g .100R	1.624 (41.25)	0.755 (19.18)

806-089-13 Weld Mount Dimensions

Shell Size	"A" Thread Mating	"Ø L" ±.002 Flange	"Ø R" ±.002 MTG Hole	"Ø S" Thru
7	.4375-.067P-.2L-TS-2A	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)



Series 806 Mil-Aero Fiber Optics

High data rate, reduced size and weight
micro miniature F/O connector series


Glenair's innovative fiber optic / electrical connector design meets key performance benchmarks for harsh vibration, shock, and environmental settings in rigid conformance with MIL-DTL-38999 Series III—but at nearly half the size and weight. The rugged fiber optic connection system delivers typical insertion loss 0.5 dB and supports 50/125, 62.5/125, and 9/125 size fiber in singlemode (1310 and 1550 nm) and multimode (850 and 1300 nm) wavelengths. Glenair Signature #20HD fiber optic termini offer the same high data rate performance as larger size #16 D38999 series connectors with more fiber lines and reduced shell size in every insert arrangement.

SAVE SIZE AND WEIGHT WITH SERIES 806 CONNECTORS

Series 806 Mil-Aero
smallest shell (size 8)
.500 in. mating threads
3 #20 electrical or optical
contacts / termini



MIL-DTL-38999
smallest shell (size 11)
.750 in. mating threads
2 #16 electrical or optical
contacts / termini




- Next-generation small form factor aerospace-grade circular connector
- Designed for harsh application environments such as military and commercial aircraft
- Outstanding environmental, electrical, optical, and mechanical performance
- Integrated anti-decoupling technology
- High density 20HD fiber termini arrangements
- Low dB loss

Series 806 Arrangements compatible with #20HD Fiber Optic Termini

Mating face of pin connector. Socket numbering is reversed.

Symbol ▼ indicates master key location.



Arrangement No.	8-3	9-5	10-8	11-10	12-15	14-20	16-31
No. of Termini	3	5	8	10	15	20	31

CONNECTOR PLUG AND RECEPTACLE SHELL STYLES FOR #20HD FIBER OPTIC TERMINI



Cable Plug



Square-Flange Receptacle



Jam-nut Receptacle



In-Line Receptacle

#20HD FIBER OPTIC TERMINI FOR SERIES 806 MIL-AERO CONNECTORS


Single or multimode. Ceramic ferrule. 0.5 dB loss. Size 20HD fiber optic termini are compatible with Series 806 connectors with size 20HD contact arrangements. These snap-in, rear release termini feature precision ceramic ferrules and alignment sleeves for accurate fiber alignment. Typical insertion loss 0.5 dB. Fits 50/125 and 62.5/125 multimode and 9/125 singlemode fiber.

MATERIAL/FINISH

- Ferrule, alignment sleeve: zirconia ceramic
- Body, shroud: copper/nickel/zinc alloy
- Spring (socket, not shown): SST/passivated
- Protective cover (socket): BeCu alloy/nickel plated

How-To-Order #20HD Fiber Optic Termini for Series 806 Connectors

Termini Type	Optical Fiber Type	Part Number	ØA Ferrule Hole	Fiber Size Core/Cladding
Pin	Singlemode	181-134-1255	125.5 microns	9/125
Pin	Multimode	181-134-126	126.0 microns	50/125, 62.5/125
Socket	Singlemode	181-135-1255	125.5 microns	9/125
Socket	Multimode	181-135-126	126.0 microns	50/125, 62.5/125

FACTORY-TERMINATED SERIES 806 FIBER OPTIC CABLE ASSEMBLIES



Glenair is able to supply turnkey fiber optic cable assemblies for both environmental applications as well as non-jacketed harnesses for use inside the box. Rugged Series 806 Mil-Aero with size #20 HD fiber optic termini are a significant size and weight savings compared to conventional D38999 or other standards. Please consult the factory for design assistance and quoting.

FIBER OPTIC, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Fiber Optic Connectors




806-012 CABLE PLUG WITH #20HD FIBER OPTIC TERMINI



How To Order						
SAMPLE PART NUMBER	806-012	-ME	10-8	B	M	A
Product	806-012 = Cable Plug					
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated					
Arrangement Number (Shell Size - Insert Arr.)	8-3, 9-5, 10-8, 11-10, 12-15, 14-20, 16-31 (see table on previous page)					
Contact Type	Connector supplied without termini A = Pin B = Socket order fiber optic termini separately					
Shell Style	M = Metric accessory threads B = Nano Band platform					
Polarizing Position	A B C D E F					

806-013 SQUARE FLANGE RECEPTACLE WITH FIBER OPTIC TERMINI



How To Order								
SAMPLE PART NUMBER	806-013	-ME	10-8	A	B	T	A	
Product	806-013 = Panel Receptacle, Square Flange							
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated							
Arrangement Number (Shell Size - Insert Arr.)	8-3, 9-5, 10-8, 11-10, 12-15, 14-20, 16-31 (see table on previous page)							
Contact Type	Connector supplied without termini A = Pin B = Socket order fiber optic termini separately							
Shell Style	M = Metric accessory threads B = Nano Band platform							
Mounting Hole Style	T = Thru holes C = Clinch nut, #4-40 (rear panel mounting)							
Polarizing Position	A B C D E F							

SPECIFICATIONS


- Operating temperature: connector capable of -55°C to +200°C. Temperature rating for fiber applications limited by cable an epoxy used.
- Termination method: epoxy/polish
- Mating durability: 500 cycles
- Random vibration: 49.5 Grms, EIA-364-28 Test Condition V. Maximum optical discontinuity 0.5 dB, 50 microseconds.
- Mechanical shock: 300 G, TIA-455-14 Test Condition D. Maximum optical discontinuity 0.5 dB, 50 microseconds.

Series 806 Mil-Aero Connectors

Fiber Optic Connectors




806-019 IN-LINE RECEPTACLE WITH FIBER OPTIC TERMINI



		How To Order					
SAMPLE PART NUMBER		806-019	-ME	10-8	A	M	A
Product	806-019 = In-Line Receptacle						
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated						
Arrangement Number (Shell Size - Insert Arr.)	8-3, 9-5, 10-8, 11-10, 12-15, 14-20, 16-31 (see table on previous page)						
Contact Type	Connector supplied without termini A = Pin B = Socket order fiber optic termini separately						
Shell Style	M = Metric accessory threads B = Nano Band platform						
Polarizing Position	A B C D E F						

806-020 JAM-NUT RECEPTACLE WITH FIBER OPTIC TERMINI



		How To Order					
SAMPLE PART NUMBER		806-020	-ME	10-8	A	M	A
Product	806-020 = Jam-nut Receptacle						
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated						
Arrangement Number (Shell Size - Insert Arr.)	8-3, 9-5, 10-8, 11-10, 12-15, 14-20, 16-31 (see table on previous page)						
Contact Type	Connector supplied without termini A = Pin B = Socket order fiber optic termini separately						
Shell Style	M = Metric accessory threads B = Nano Band platform						
Polarizing Position	A B C D E F						

SPECIFICATIONS



- Operating temperature: connector capable of -55°C to +200°C. Temperature rating for fiber limited by cable an epoxy used.
- Termination method: epoxy/polish
- Mating durability: 500 cycles
- Random vibration: 49.5 Grms, EIA-364-28 Test Condition V. Maximum optical discontinuity 0.5 dB, 50 microseconds.
- Mechanical shock: 300 G, TIA-455-14 Test Condition D. Maximum optical discontinuity 0.5 dB, 50 microseconds.

FIBER OPTIC, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size #20HD Fiber Optic Termini



Single or multi mode. Ceramic ferrule. 0.5 dB loss. Size 20HD fiber optic termini are compatible with Series 806 connectors with size 20HD contact arrangements. These snap-in, rear release termini feature precision ceramic ferrules for accurate fiber alignment. Typical insertion loss 0.5 dB. Fits 50/125 and 62.5/125 multi mode and 9/125 single mode fiber.

#20HD Fiber Optic Termini for Series 806 Connectors

Termini Type	Optical Fiber Type	Part Number	ØA Ferrule Hole	Fiber Size Core/Cladding
Pin	Single Mode	181-134-1255	125.5 microns	9/125
Pin	Multi Mode	181-134-126	126.0 microns	50/125, 62.5/125
Socket	Single Mode	181-135-1255	125.5 microns	9/125
Socket	Multi Mode	181-135-126	126.0 microns	50/125, 62.5/125

Specifications

- Operating temperature: -55°C to +125°C
Temperature rating depends on the cable and epoxy used.
- Termination method: epoxy/polish
- Mating durability: 500 cycles
- Random vibration: 49.5 Grms, EIA-364-28 Test Condition V. Maximum optical discontinuity 0.5 dB, 50 microseconds.
- Mechanical shock: 300 G, TIA-455-14 Test Condition D. Maximum optical discontinuity 0.5 dB, 50 microseconds.

Construction

- Ferrule, alignment sleeve: zirconia ceramic
- Body, shroud: copper/nickel/zinc alloy
- Spring (socket, not shown): stainless steel, passivated
- Protective cover (socket): copper alloy, nickel plated

Termination Tools


- Polishing pucks

Puck Style	Type	Tool PN
Pin	dry polish	182-056P
	wet polish	182-056PW
Socket	dry polish	182-056S
	wet polish	182-056SW


Assembly Tools


- Plastic insertion/extraction tool: 809-203D
- Metal insertion/extraction tool: 809-203

#20HD Pin Terminus 181-134



#20HD Socket Terminus 181-135





Series 44 environmental backshells with swept 45° and 90° profiles are ideal for combo copper /fiber insert arrangements where EMI/RFI shielding and environmental sealing are needed. Anti-decoupling device for improved vibration resistance and detents to allow for axial positioning of backshell for improved cable routing.


How To Order										
SAMPLE PART NUMBER	440V	S	213	MT	20	12	-8	B	P	T
Product	440V = Series 806 Backshell									
Angular Function	S = Straight N = 90° M = 45°									
Basic No.	213									
Finish Code	ME = Aluminum Alloy; Electroless Nickel NF = Aluminum Alloy; Cadmium/O.D. over Electroless Nickel (500 hr salt spray) MT = Aluminum Alloy; Electroless Nickel-PTFE ZR = Aluminum Alloy; Zinc Nickel, Black over Electroless Nickel Z1 = Stainless Steel; Passivate									
Shell Size	See									
Dash Number	See Table III									
Length	Length in 1/8 Inch Increments (8 = 1 inch); See Note 3									
Band Option	B = Band K = Precoiled; omit if not required									
Shield Termination Finish	P = Polysulfide Plating Shield; See Note 4. Omit if not required.									
Shrink Boot Material Options	See Table II; See Note 5. Omit for none.									

Table II: Shrink Boot Options

Code	Description
T	Standard Fluid Resistant Elastomer With Adhesive Pre-Applied
TU	Standard Fluid Resistant Elastomer
N	Radiation Resistant Polyolefin, -50°C To 150°C (No Adhesive Option)
S	Low Outgassing Fluoropolymer; Use 779-001 As Adhesive Option (Not Included)
SU	Low-Outgassing Fluoropolymer

TABLE III

Dash No	X Dia	Y Dia	Z Dia	Shrink Boot T Or H Ref	Shrink Boot w/Adhesive
02	0.125 (3.18)	0.165 (4.19)	0.266 (6.76)	809S060-1*U	809S060-1*
03	0.188 (4.78)	0.228 (5.79)	0.329 (8.36)	809S060-1*U	809S060-1*
04	0.250 (6.35)	0.290 (7.37)	0.391 (9.93)	809S060-2*U	809S060-2*
05	0.312 (7.92)	0.353 (8.97)	0.453 (11.51)	809S060-2*U	809S060-2*
06	0.375 (9.52)	0.415 (10.54)	0.516 (13.11)	809S060-2*U	809S060-2*
07	0.438 (11.13)	0.478 (12.14)	0.579 (14.71)	809S060-2*U	809S060-2*
08	0.500 (12.70)	0.540 (13.72)	0.641 (16.28)	809S060-3*U	809S060-3*
09	0.562 (14.27)	0.603 (15.32)	0.703 (17.86)	809S060-3*U	809S060-3*
10	0.625 (15.88)	0.665 (16.89)	0.766 (19.46)	809S060-3*U	809S060-3*
11	0.688 (17.48)	0.728 (18.49)	0.829 (21.06)	809S060-4*U	809S060-4*
12	0.750 (19.05)	0.800 (20.32)	0.891 (22.63)	809S060-4*U	809S060-4*
13	0.812 (20.62)	0.863 (21.92)	0.953 (24.21)	809S060-4*U	809S060-4*
14	0.875 (22.23)	0.925 (23.50)	1.016 (25.81)	809S060-5*U	809S060-5*
15	0.938 (23.83)	0.988 (25.10)	1.079 (27.41)	809S060-5*U	809S060-5*
16	1.000 (25.40)	1.050 (26.67)	1.141 (28.98)	809S060-5*U	809S060-5*
17	1.062 (26.97)	1.113 (28.27)	1.203 (30.56)	809S060-6*U	809S060-6*
18	1.125 (28.58)	1.175 (29.85)	1.266 (32.16)	809S060-6*U	809S060-6*
20	1.250 (31.75)	1.310 (33.27)	1.391 (35.33)	809S060-6*U	809S060-6*

**TABLE I**

Shell Size	A Thread	Ø C Max	K Max	L Max	M Max	N Max	Max Dash No.
07	M8 x 1-6H	.640 (16.26)	.790 (20.07)	.905 (22.99)	.910 (23.11)	1.055 (26.80)	03
08	M10 x 1-6H	.710 (18.03)	.790(20.07)	.965(24.51)	.940(23.88)	1.125(28.58)	04
09	M12 x 1-6H	.780 (19.81)	.790(20.07)	.965(24.51)	.940(23.88)	1.125(28.58)	05
10	M14 x 1-6H	.880 (22.35)	.790(20.07)	1.035(26.29)	.970(24.64)	1.225(31.12)	06
11	M15 x 1-6H	.920 (23.37)	.790(20.07)	1.035(26.29)	.970(24.64)	1.225(31.12)	07
12	M17 x 1-6H	1.000 (25.40)	.830(21.08)	1.115(28.32)	1.040(26.42)	1.325(33.66)	08
14	M19 x 1-6H	1.090 (27.69)	.830(21.08)	1.115(28.32)	1.040(26.42)	1.325(33.66)	09
16	M22 x 1-6H	1.210 (30.73)	.840(21.34)	1.185(30.10)	1.080(27.43)	1.425(36.20)	12
18	M25 x 1-6H	1.330 (33.78)	.890(22.61)	1.265(32.13)	1.140(28.96)	1.515(38.48)	13
20	M28 x 1-6H	1.450 (36.83)	.920(23.37)	1.335(33.91)	1.210(30.73)	1.615(41.02)	15
22	M31 x 1-6H	1.570 (39.88)	.950(24.13)	1.395(35.43)	1.280(32.51)	1.715(43.56)	17
24	M34 x 1-6H	1.700 (43.18)	.970(24.64)	1.455(36.96)	1.330(33.78)	1.815(46.10)	18

NOTES

- For effective grounding connector with conductive finish should be used
- When Cable entry exceeds max. in Table I, Style II will be supplied. Dimensions F, G, H, J, K, L, M & N will not apply
- Standard minimum length for style I is 0.75, for style II is 1.5 inches, for shorter length, consult factory, applies to SYM S, straight only
- When polysulfide barrier is selected for plating shield termination surface shall be free of cadmium.
- See 809-060 for additional shrink boot options
- Material / Finish:
 - Adapters, elbows, coupling nut; see How-to-Order table
 - Anti-decoupling device: corrosion resistant material
 - O-rings: silicone/N.A.
 - Shrink boot: see individual drawings
 - Band: CRES/passivated



Series 37 Fiber-Con environmental composite backshells with swept 45° and 90° profiles are ideal for fiber media routing. Backshells offer a full range of connector-to-conduit adapters. Anti-decoupling device for improved vibration resistance, and detents to allow for axial positioning of backshell for improved cable routing. Special wire grommet ensures axial alignment of fiber media. Optional purple color readily identifies fiber runs (purple conduit also available).

How To Order								
SAMPLE PART NUMBER	377V	S	014	XM	11-10	06	4	T
Product	377V = Series 806 Backshell							
Angular Function	S = Straight							
	W = 90° Solid Elbow							
	T = 45° Solid Elbow							
Basic No.	014							
Finish Code	See Table I							
Shell Size - Insert Arrangement	11-10, 16-31, 18-41, 20-55, 22-69, 24-92							
Optional Entry Size	See Table II; omit for standard. Table I not applicable to SYM G							
Length	Length in 1/2 inch increments (e.g. 4 = 2 inches)							
Adapter Options	Sym G = Gland nut							
	Sym T = Tubing adapter, Glenair Types E, F, P & T							
	Sym K = Tubing adapter with nut, Glenair peek							
	Sym TB = Tubing adapter supplied with band, Glenair Types E, F, P & T Sym							
	TN = Tubing adapter with nut, Glenair Types E, F, P & T							
	Omit for standard shrink boot adapter							

NOTES

- Glenair 600 Series backshell assembly tools are recommended for assembly and installation
- Standard Min. Order Length 1.5 inch, consult factory for shorter lengths
- For sealing plugs see Glenair drawing 687-142
- Material:
 - Adapters, elbows, ferules, coupling nut, nut: high-grade engineering thermoplastic/see Table I
 - Grommet, O-ring: fluorosilicone/N/A.
 - anti-decoupling device: corrosion resistant material/N.A.

Table I		
SYM	FINISH DESCRIPTION	COMPONENTS
-	Dash (-) for no plating	Adapter, coupling nut & RFI nut
XB	No plating - black color	Adapter, coupling nut & RFI nut
XM	1000 Hour corrosion resistant electroless nickel	Adapter & RFI nut
	No plating - amber color	Coupling nut & rear components
XW	1000 Hour corrosion resistant Cad/O.D. Over electroless nickel	Backshell
	No plating - amber color	Coupling nut & rear components
XMT	Copper flash - gps52-xmt (JCP-3)	
XV	No plating - black or purple color (Mfg option)	Body & rear adapter
	No plating - purple color	Coupling nut & rear nut

337V*014 Fiber Optic Composite Fiber-Con™ Connector Backshells

Series 806

Mil-Aero Connectors

337V*014 Fiber Optic Composite Fiber-Con™ Connector Backshells

Dimensions																
SHELL SIZE	A THD ISO METRIC	B MAX	STD CONDUIT SIZE REF.	D MAX	E	F MAX	G MAX	H APPROX	J APPROX REF	K	L FLATS	M REF	N MAX	P REF	NO. OF HOLES	MAX ALT STD ENTRY
11-10	M15 X 1 - 6H	1.00 (25.40)	3/8	1.78 (45.21)	1.93 (49.02)	1.33 (33.78)	1.56 (39.62)	2.23 (56.64)	2.09 (53.09)	1.20 (30.48)	0.938 (23.83)	0.32 (8.13)	1.38 (35.05)	0.53 (13.46)	10	08
16-31	M22 X 1 - 6H	1.25 (31.75)	1/2	1.90 (48.26)	2.08 (52.83)	1.45 (36.83)	1.68 (42.67)	2.45 (62.23)	2.33 (59.18)	1.32 (33.53)	0.938 (23.83)	0.54 (13.72)	1.38 (35.05)	0.53 (13.46)	31	08
18-41	M25 X 1 - 6H	1.38 (35.05)	5/8	1.97 (50.04)	2.14 (54.36)	1.51 (38.35)	1.74 (44.20)	2.47 (62.74)	2.44 (61.98)	1.38 (35.05)	1.250 (31.75)	0.76 (19.30)	1.56 (39.62)	0.77 (19.56)	41	11
20-55	M28 X 1 - 6H	1.50 (38.10)	3/4	2.11 (53.59)	2.18 (55.37)	1.54 (39.12)	1.77 (44.96)	2.54 (64.52)	2.50 (63.50)	1.43 (36.32)	1.250 (31.75)	0.76 (19.30)	1.56 (39.62)	0.77 (19.56)	55	11
22-69	M31 X 1 - 6H	1.62 (41.15)	7/8	2.07 (52.58)	2.25 (57.15)	1.61 (40.89)	1.84 (46.74)	2.64 (67.06)	2.64 (67.06)	1.49 (37.85)	1.500 (38.10)	1.00 (25.40)	1.81 (45.97)	1.00 (25.40)	69	15
24-92	M34 X 1 - 6H	1.75 (44.45)	1	2.14 (54.36)	2.31 (58.67)	1.67 (42.42)	1.89 (48.01)	2.76 (70.10)	2.75 (69.85)	1.55 (39.37)	1.500 (38.10)	1.00 (25.40)	1.81 (45.97)	1.00 (25.40)	92	15

Table II

Entry Size	C Ref Sym T & TN	C Ref Sym K	Optional Conduit Size Ref.	M Ref Std
03	0.188 (4.78)	0.188 (4.78)	9/32	0.19 (4.83)
04	0.236 (5.99)	-	5/16	0.25 (6.35)
05	0.250 (6.35)	0.265 (6.73)	3/8	0.32 (8.13)
06	0.338 (8.59)	0.330 (8.38)	7/16	0.38 (9.65)
07	0.398 (10.11)	0.390 (9.91)	1/2	0.44 (11.18)
08	0.523 (13.28)	0.515 (13.08)	5/8	0.54 (13.72)
10	0.648 (16.46)	0.640 (16.26)	3/4	0.63 (16.00)
11	0.648 (16.46)	0.640 (16.26)	3/4	0.76 (19.30)
13	0.778 (19.76)	0.765 (19.43)	7/8	0.88 (22.35)
15	0.875 (22.23)	0.890 (22.61)	1	1.00 (25.40)
17	1.078 (27.38)	1.125 (28.58)	1 1/4	1.13 (28.70)



HIGH-RELIABILITY Glass-sealed Hermetic Connectors

Resolve gas, moisture and particle ingress problems with advanced-performance glass-sealed hermetic connectors

Helium Leak Testing

All Series 806 hermetic connectors are 100% tested prior to shipment. A helium leak test is performed to certify the hermetic seal. This test is conducted by inducing 1 ATM of vacuum on one side of the connector. Helium gas is released on the other side, and a mass spectrometer “counts” the number of helium molecules that penetrate the connector seal. Helium leak testing takes advantage of the small size of a helium molecule compared to air or water vapor. Helium is inert, rare in our atmosphere, and is easy to detect with a mass spectrometer. Series 806 hermetic connectors are designed specifically for commercial and military aircraft zones such as engine compartments. These areas are typically exposed to fuel, oil and changes in elevation. Such conditions present the need to protect sensitive electronic equipment from the effects of caustic chemicals and moisture ingress through standard environmental connectors where high pressure leads to sealing failure. Other aircraft locations such as the fuselage require hermetic connectors to maintain passenger cabin pressure while allowing for data transmission through separated compartments of the aircraft.



VITREOUS GLASS TECHNOLOGY ADVANTAGES

- Superior pressure resistance to 32,000+ PSI
- Higher resistance to extreme operating temperatures to 260°+ C
- Superior mechanical strength
- No material breakdown or aging over time
- Helium leak rate $<1 \times 10^{-7}$ cc/sec to 1×10^{-10}

Std cc/sec Approximate	Approximate Bubble Equivalent
1 x 10 ⁻¹	1 cc/10 sec
1 x 10 ⁻²	1 cc/100 sec
1 x 10 ⁻³	1 cc/hour
1 x 10 ⁻⁴	1 cc/3 hours
1 x 10 ⁻⁵	1 cc/24 hours
1 x 10 ⁻⁶	1 cc/2 weeks
1 x 10 ⁻⁷	3 cc/year
1 x 10 ⁻⁸	1 cc/3 year
1 x 10 ⁻⁹	1 cc/30 years
1 x 10 ⁻¹¹	1 cc/3000 years

HERMETIC, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Various Glass-to-Metal Hermetic Connector Solutions



GEOPHYSICAL AND OFFSHORE CONFIGURATIONS



GeoMarine® double-start hermetic connector



Hermetic power connector



Single-way tool joint hermetic connector




Hermetic probe connector



Hermetic bulkhead penetrator

HIGH-SPEED/SHIELDED DESIGNS



Triax hermetic




Hybrid coax/signal hermetic



Quadrax hermetic




MT ribbon fiber optic hermetic




Hybrid coax/signal hermetic


RECTANGULAR PACKAGES




MIL-DTL-24308 QPL hermetic



Series 79 Micro-Crimp hermetic




MIL-DTL-83513 type micro-D hermetics




Sealed panel-mount micro-D hermetic


MIL-DTL-38999 QPL PIN AND SOCKET HERMETICS



Series I Scoop-proof 3 Point Bayonet Coupling



Series II Low-profile 3 Point Bayonet Coupling



Series III Scoop-proof Triple Start, Self-Locking



Series IV Scoop-proof Breech Lock

Series 806 Mil-Aero Connectors

806-025 Glass-to-Metal Hermetic Receptacles, Solder Cup/PC Tail



Features

- Glass-to-metal seal
- Non-removable solder cup or PC tail contacts
- High density #20HD and #22HD arrangements for reduced size and weight plus #16, #12, #8 standard and hybrid arrangements
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -65°C to +200°C
- Leak Rate: 1E-7 cm³/s at 1 ATM pressure differential
- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: contact factory
#12 contacts: contact factory
#8 contacts: contact factory
- Shell-to-Shell Conductivity: 10 mV max.
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell and jam-nut: 304L CRES
- Hermetic contacts: nickel-iron alloy, gold plated
- Socket contacts: copper alloy, gold plated
- Insulator, hermetic: vitreous glass
- Interfacial seal, peripheral seal, O-ring: fluorosilicone
- Insulator, socket: high grade rigid dielectric


Series 806 hermetic receptacles feature stainless steel shells and glass-to-metal seals. Rated for -65°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade hermetic connectors. These high performance, parylene compatible connectors are suitable for pressurized bulkhead applications subject to vibration, moisture, and temperature extremes. Equipped with low-profile, non-threaded standoff. Available receptacle shell styles include square flange, jam-nut, solder mount, and weld mount.

How To Order						
SAMPLE PART NUMBER		806-025	-07	Z1	8-3	C A
Product	806-025 = Hermetic Receptacle					
Mounting Type	02 = Box Mount 03 = Solder Mount 07 = Jam-nut Mount 13 = Weld Mount					
Shell Finish	Z1 = Passivated ZL = Nickel Plated					
Arrangement Number (Shell Size - Insert Arr.)	See Table 1					
Contact Type	C = Pin, PC Terminal P = Pin, Solder Cup D = Socket, PC Terminal S = Socket, Solder Cup					
Polarization	A B C D					

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

806-025-02 Square Flange Receptacle Dimensions

Shell Size	A Mating Thread	ØB Max. Flange	C Max Flange Flats	D SQ BSC Mntg Holes	±0.010 (0.25) øE	F Max Flange	Ø M Thru Mntg Holes	Ø S Thru
7	.4375-.067P-.2L-TS-2A	.968 (24.59)	.750 (19.05)	.469 (11.91)	.306 (7.77)	.100 (2.54)	.128 (3.25)	.445 (11.30)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	.822 (20.88)	.531 (13.49)	.387 (9.83)	.100 (2.54)	.128 (3.25)	.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	.885 (22.48)	.594 (15.09)	.468 (11.89)	.100 (2.54)	.128 (3.25)	.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	.913 (23.19)	.625 (15.88)	.546 (13.87)	.100 (2.54)	.128 (3.25)	.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	.960 (24.38)	.670 (17.02)	.586 (14.88)	.100 (2.54)	.128 (3.25)	.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	.765 (19.43)	.663 (16.84)	.100 (2.54)	.128 (3.25)	.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	.859 (21.82)	.743 (18.87)	.100 (2.54)	.128 (3.25)	.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	.938 (23.83)	.842 (21.39)	.100 (2.54)	.128 (3.25)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	.959 (24.36)	.100 (2.54)	.128 (3.25)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	1.105 (28.07)	.125 (3.18)	.154 (3.91)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	1.215 (30.86)	.125 (3.18)	.154 (3.91)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	1.335 (33.91)	.125 (3.18)	.154 (3.91)	1.525 (38.73)

806-025-07 Jam-nut Receptacle Dimensions


Shell Size	A Mating Thread	øE Mntg Boss	G Max Flange	H Max Flange Flats	J Max Flange	K Thread Mounting	Ø N Mntg Hole	P Mntg Flat
7	.4375-.067P-.2L-TS-2A	.306 (7.77)	.848 (21.54)	.908 (23.06)	.100 (2.54)	M13x1.0-6g-0.100R	.522 (13.26)	.224 (5.69)
8	.5000-.067P-.2L-TS-2A	.387 (9.83)	.980 (24.89)	.920 (23.37)	.100 (2.54)	M15x1.0-6g-0.100R	.601 (15.27)	.256 (6.50)
9	.5625-.067P-.2L-TS-2A	.468 (11.89)	1.040 (26.42)	.980 (24.89)	.100 (2.54)	M16x1.0-6g-0.100R	.640 (16.26)	.287 (7.29)
10	.6250-.067P-.2L-TS-2A	.546 (13.87)	1.110 (28.19)	1.050 (26.67)	.100 (2.54)	M18x1.0-6g-0.100R	.719 (18.26)	.318 (8.08)
11	.6875-.067P-.2L-TS-2A	.586 (14.88)	1.160 (29.46)	1.110 (28.19)	.100 (2.54)	M19x1.0-6g-0.100R	.759 (19.28)	.350 (8.89)
12	.7500-.067P-.2L-TS-2A	.663 (16.84)	1.230 (31.24)	1.170 (29.72)	.100 (2.54)	M21x1.0-6g-0.100R	.837 (21.26)	.381 (9.68)
14	.8750-.067P-.2L-TS-2A	.743 (18.87)	1.360 (34.54)	1.320 (33.53)	.100 (2.54)	M24x1.0-6g-0.100R	.955 (24.26)	.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	.842 (21.39)	1.515 (38.48)	1.444 (36.68)	.100 (2.54)	M27x1.0-6g-0.100R	1.073 (27.25)	.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	.959 (24.36)	1.610 (40.89)	1.570 (39.88)	.100 (2.54)	M30x1.0-6g-0.100R	1.192 (30.28)	.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	1.105 (28.07)	1.850 (46.99)	1.760 (44.70)	.128 (3.25)	M34x1.0-6g-0.100R	1.349 (34.26)	.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	1.215 (30.86)	2.010 (51.05)	1.913 (48.59)	.128 (3.25)	M37x1.0-6g-0.100R	1.467 (37.26)	.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	1.335 (33.91)	2.195 (55.75)	2.070 (52.58)	.128 (3.25)	M41x1.0-6g-0.100R	1.624 (41.25)	.755 (19.18)

Series 806 Mil-Aero Connectors

806-025 Glass-to-Metal Hermetic Receptacles, Solder Cup/PC Tail




806-025-13 Weld Mount Receptacle Dimensions




See pages 160-202 for recommended PC board layouts
(omit mounting holes and orientation hole)

PC Tail Dia.	±.002 (0.05)
#22	.020 (0.51)
#20	.030 (0.76)
#16	.063 (1.60)
#12	.094 (2.39)
#8	.180 (4.57)



Shell Size	A Mating Thread	Ø E ±.010 Mounting Boss	L ±.002 (0.05)	Ø R ±.002 (0.05)	Ø S ±.005
7	.4375-.067P-.2L-TS-2A	.306 (7.77)	.725 (18.42)	.730 (18.54)	.445 (11.30)
8	.5000-.067P-.2L-TS-2A	.387 (9.83)	.788 (20.02)	.793 (20.14)	.509 (12.93)
9	.5625-.067P-.2L-TS-2A	.468 (11.89)	.912 (23.16)	.917 (23.29)	.577 (14.66)
10	.6250-.067P-.2L-TS-2A	.546 (13.87)	.975 (24.76)	.980 (24.89)	.645 (16.38)
11	.6875-.067P-.2L-TS-2A	.586 (14.88)	1.038 (26.37)	1.043 (26.49)	.712 (18.08)
12	.7500-.067P-.2L-TS-2A	.663 (16.84)	1.100 (27.94)	1.105 (28.07)	.768 (19.51)
14	.8750-.067P-.2L-TS-2A	.743 (18.87)	1.225 (31.12)	1.230 (31.24)	.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	.842 (21.39)	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	.959 (24.36)	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.105 (28.07)	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	1.215 (30.86)	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	1.335 (33.91)	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)


806-025-03 Solder Mount Receptacle Dimensions



See pages 160-202 for recommended
PC board layouts (omit mounting
holes and orientation hole)

PC Tail Dia.	±.002 (0.05)
#22	.020 (0.51)
#20	.030 (0.76)
#16	.063 (1.60)
#12	.094 (2.39)
#8	.180 (4.57)

Shell Size	A Mating Thread	Ø E ±.010 Mounting Boss	Ø LL Flange
7	.4375-.067P-.2L-TS-2A	.306 (7.77)	.520 (13.21)
8	.5000-.067P-.2L-TS-2A	.387 (9.83)	.581 (14.76)
9	.5625-.067P-.2L-TS-2A	.468 (11.89)	.649 (16.48)
10	.6250-.067P-.2L-TS-2A	.546 (13.87)	.717 (18.21)
11	.6875-.067P-.2L-TS-2A	.586 (14.88)	.784 (19.91)
12	.7500-.067P-.2L-TS-2A	.663 (16.84)	.841 (21.36)
14	.8750-.067P-.2L-TS-2A	.743 (18.87)	.962 (24.43)
16	1.0000-.067P-.2L-TS-2A	.842 (21.39)	1.087 (27.61)
18	1.1250-.067P-.2L-TS-2A	.959 (24.36)	1.197 (30.40)
20	1.2500-.067P-.2L-TS-2A	1.105 (28.07)	1.347 (34.21)
22	1.3750-.067P-.2L-TS-2A	1.215 (30.86)	1.472 (37.39)
24	1.5000-.067P-.2L-TS-2A	1.335 (33.91)	1.597 (40.56)



Features

- Glass-to-metal seal
- Non-removable PC tail contacts
- Threaded holes for attaching to printed circuit boards
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, 12, and #8 standard and hybrid layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -65°C to +200°C
- Leak Rate: 1E-7 cm³/s at 1 ATM pressure differential
- Dielectric withstanding voltage
#22HD contacts: 1300 VAC
#20HD contacts: 1800 VAC
#16 contacts: contact factory
#12 contacts: contact factory
#8 contacts: contact factory
- Shell-to-Shell Conductivity: 10 mV max.
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell and jam-nut: 316L CRES
- Hermetic contacts: nickel-iron alloy, gold plated
- Socket contacts: copper alloy, gold plated
- Insulator, hermetic: vitreous glass
- Interfacial seal, peripheral seal, O-ring: fluorosilicone
- Insulator, socket: high grade rigid dielectric

Series 806 hermetic receptacles feature stainless steel shells and glass-to-metal seals. Rated for -65°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade circular hermetic connectors. These high performance, parylene compatible connectors are suitable for use on pressurized bulkheads and vacuum chamber applications subject to vibration, moisture, and temperature extremes. Equipped with low-profile, threaded standoff with gold-plated PC tail contacts.

How To Order							
SAMPLE PART NUMBER		806-026	-02	Z1	8-3	C	1 A
Product	806-026 = Hermetic Receptacle, PC Tails, Threaded Standoff						
Mounting Type	02 = Square Flange 07 = Jam-nut						
Shell Finish	Z1 = Passivated ZL = Nickel Plated						
Shell Size - Insert Arr.	See Table 1						
Contact Type	C = Pin, PC Terminal D = Socket, PC Terminal						
PC Tail Length	1 = .125" (3.18 mm.) 2 = .250" (6.35 mm.)						
Polarizing Position	A B C D E F; (See Page 7)						


Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6				
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

Series 806 Mil-Aero Connectors

806-026 Hermetic Receptacles, PC Tails, Threaded Standoff




806-026-02 Square Flange Receptacle Dimensions




Shell Size	A Mating Thread	ϕB Max. Flange	C Max Flange Flts	D SQ BSC Mntg Holes	F Max Flange	L Board Mntg	ϕM Thru Mntg Holes	ϕR $\pm .015$ (.38)	ϕS Thru
7	.4375-.067P-.2L-TS-2A	.968 (24.59)	.750 (19.05)	.469 (11.91)	.100 (2.54)	.489 (12.42)	.128 (3.25)	.259 (6.58)	.450 (11.43)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	.822 (20.88)	.531 (13.49)	.100 (2.54)	.534 (13.56)	.128 (3.25)	.325 (8.25)	.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	.885 (22.48)	.594 (15.09)	.100 (2.54)	.579 (14.71)	.128 (3.25)	.405 (10.29)	.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	.913 (23.19)	.625 (15.88)	.100 (2.54)	.679 (17.25)	.128 (3.25)	.465 (11.81)	.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	.960 (24.38)	.670 (17.02)	.100 (2.54)	.734 (18.64)	.128 (3.25)	.525 (13.34)	.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	.765 (19.43)	.100 (2.54)	.804 (20.42)	.128 (3.25)	.595 (15.11)	.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	.859 (21.82)	.100 (2.54)	.891 (22.63)	.128 (3.25)	.650 (16.51)	.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.242 (31.55)	.938 (23.83)	.100 (2.54)	1.049 (26.64)	.128 (3.25)	.795 (20.19)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.343 (34.11)	1.016 (25.81)	.100 (2.54)	1.148 (29.16)	.128 (3.25)	.920 (23.37)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	.125 (3.18)	1.252 (31.80)	.154 (3.91)	1.030 (26.16)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	.125 (3.18)	1.369 (34.77)	.154 (3.91)	1.130 (28.70)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	.125 (3.18)	1.509 (38.33)	.154 (3.91)	1.275 (32.39)	1.525 (38.73)


PC Tail Dimensions





Contact Size	ϕT $\pm .002$ (0.05)
#22	.020 (0.51)
#20	.030 (0.76)
#16	.063 (1.60)
#12	.094 (2.39)
#8	.180 (4.57)

Recommended Panel Cutout



806-026-07 Jam-nut Receptacle Dimensions


Shell Size	A Mating Thread	G Max Flange	H Max Flange Flats	J Max Flange	K Thread Mntg	L Board Mntg	ϕN Mntg Hole	P +.005/-.000 (0.13/0.00) Mntng Flat	ϕR $\pm .015$ (0.38)
7	.4375-.067P-.2L-TS-2A	.848 (21.54)	.908 (23.06)	.100 (2.54)	M13x1.0-6g-0.100R	.489 (12.42)	.522 (13.26)	.224 (5.69)	.259 (6.58)
8	.5000-.067P-.2L-TS-2A	.980 (24.89)	.920 (23.37)	.100 (2.54)	M15x1.0-6g-0.100R	.534 (13.56)	.601 (15.27)	.256 (6.50)	.325 (8.25)
9	.5625-.067P-.2L-TS-2A	1.040 (26.42)	.980 (24.89)	.100 (2.54)	M16x1.0-6g-0.100R	.579 (14.71)	.640 (16.26)	.287 (7.29)	.405 (10.29)
10	.6250-.067P-.2L-TS-2A	1.110 (28.19)	1.050 (26.67)	.100 (2.54)	M18x1.0-6g-0.100R	.679 (17.25)	.719 (18.26)	.318 (8.08)	.465 (11.81)
11	.6875-.067P-.2L-TS-2A	1.160 (29.46)	1.110 (28.19)	.100 (2.54)	M19x1.0-6g-0.100R	.734 (18.64)	.759 (19.28)	.350 (8.89)	.525 (13.34)
12	.7500-.067P-.2L-TS-2A	1.230 (31.24)	1.170 (29.72)	.100 (2.54)	M21x1.0-6g-0.100R	.804 (20.42)	.837 (21.26)	.381 (9.68)	.595 (15.11)
14	.8750-.067P-.2L-TS-2A	1.360 (34.54)	1.320 (33.53)	.100 (2.54)	M24x1.0-6g-0.100R	.891 (22.63)	.955 (24.26)	.443 (11.25)	.650 (16.51)
16	1.0000-.067P-.2L-TS-2A	1.515 (38.48)	1.444 (36.68)	.100 (2.54)	M27x1.0-6g-0.100R	1.049 (26.64)	1.073 (27.25)	.505 (12.83)	.795 (20.19)
18	1.1250-.067P-.2L-TS-2A	1.610 (40.89)	1.570 (39.88)	.100 (2.54)	M30x1.0-6g-0.100R	1.148 (29.16)	1.192 (30.28)	.568 (14.43)	.920 (23.37)
20	1.2500-.067P-.2L-TS-2A	1.850 (46.99)	1.760 (44.70)	.128 (3.25)	M34x1.0-6g-0.100R	1.252 (31.80)	1.349 (34.26)	.630 (16.00)	1.030 (26.16)
22	1.3750-.067P-.2L-TS-2A	2.010 (51.05)	1.913 (48.59)	.128 (3.25)	M37x1.0-6g-0.100R	1.369 (34.77)	1.467 (37.26)	.693 (17.60)	1.130 (28.70)
24	1.5000-.067P-.2L-TS-2A	2.195 (55.75)	2.070 (52.58)	.128 (3.25)	M41x1.0-6g-0.100R	1.509 (38.33)	1.624 (41.25)	.755 (19.18)	1.275 (32.39)

PC Tail Dimensions**Recommended Panel Cutout**

Contact Size	ϕT $\pm .002 (0.05)$ In.
#22	.020 (0.51)
#20	.030 (0.76)
#16	.063 (1.60)
#12	.094 (2.39)
#8	.180 (4.57)

Series 806 Mil-Aero Connectors

806-087 Crimp Removable Hermetic Receptacle



Material/Finish

- Shell & jam-nut: 304L CRES/PER P/N DEV
- Contacts, hermetic: Nickel-iron alloy/gold plate
- Contacts, sockets: Copper alloy/gold plate
- Hoods, sockets: 305 CRES/passivate
- Insulator, hermetic: Vitreous glass
- Insulator, socket: High grade dielectric
- Seals & O-rings: Fluorosilicone

Test Criteria

- Leak rate: $<1 \times 10^{-7}$ ccHe/sec @ 1 ATM. delta pressure
- DWV: Per Table II
- I.R.: 5000 MEGOHMS min @ 500 VDC


Series 806 hermetic receptacles feature stainless steel shells and glass-to-metal seals. Rated for -65°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade hermetic connectors. These high performance, parylene compatible connectors are suitable for pressurized bulkhead applications subject to vibration, moisture, and temperature extremes. The 806-087 receptacles are equipped with a crimp-removable termination system for vastly improved ease of use.

How To Order ThermoRex Series 806 Mil-Aero Jam-nut Receptacle								
SAMPLE PART NUMBER		806-087	-07	Z1	8-7	P	-B	A
Series / Basic Part No.	806-087 Crimp Removable Hermetic Receptacle							
Mounting Type	02 = Box Mount 03 = Solder Mount 07 = Jam-Nut Mount 13 = Weld Mount							
Finish	Z1 = Passivated ZL = Nickel Plated							
Shell Size - Insert Arr.	See Table I							
Contact Type	P = Pin S = Socket							
Rear Attachment Style	B = Banding Porch T = Accessory Threads							
Polarization	A, B, C, D							

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						


Polarization Key Code




POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

Table II: DWV Voltage

Cont. Size	Volts RMS
22	1300
20	1800
16	1800
12	1800
8	1000

806-087-02 Box Mount Receptacle Dimensions

Shell Size	"A" Thread Mating	"Ø B" Max Flange	"C" Square Max Flange Flats	"D" Square BSC Mounting Holes	"F" Max Flange	"Ø M" Thru MTG Holes	"ø S" Thru	
7	.4375-.067P-.2L-TS-2A	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	0.100 (2.54)	0.128 (3.25)	0.445 (11.30)	
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)			0.509 (12.93)	
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)			0.577 (14.66)	
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)			0.645 (16.38)	
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)			0.712 (18.08)	
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)			0.768 (19.51)	
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)			0.890 (22.61)	
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)			1.015 (25.78)	
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	0.100 (2.54)	0.154 (3.91)	1.125 (28.58)	
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	0.125 (3.18)		1.275 (32.39)	
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)			1.400 (35.56)	
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)			1.525 (38.73)	

806-087-03 Solder Mount Receptacle Dimensions

Shell Size	"A" Thread Mating	"Ø LL" Flange
7	.4375-.067P-.2L-TS-2A	0.520 (13.21)
8	.5000-.067P-.2L-TS-2A	0.581 (14.76)
9	.5625-.067P-.2L-TS-2A	0.649 (16.48)
10	.6250-.067P-.2L-TS-2A	0.717 (18.21)
11	.6875-.067P-.2L-TS-2A	0.784 (19.91)
12	.7500-.067P-.2L-TS-2A	0.841 (21.36)
14	.8750-.067P-.2L-TS-2A	0.962 (24.43)
16	1.0000-.067P-.2L-TS-2A	1.087 (27.61)
18	1.1250-.067P-.2L-TS-2A	1.197 (30.40)
20	1.2500-.067P-.2L-TS-2A	1.347 (34.21)
22	1.3750-.067P-.2L-TS-2A	1.472 (37.39)
24	1.5000-.067P-.2L-TS-2A	1.597 (40.56)

HERMETIC, MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors


806-087 Crimp Removable Hermetic Receptacle



806-087-07 Jam-Nut Mount Receptacle Dimensions




Shell Size	"A" Thread Mating	" $\varnothing G$ " Max Flange	"H" Square Max Flange Flats	"J" Max Flange	"K" Thread Mounting	" $\varnothing N$ " +.005/- .000 Mounting Hole	"P" +.005/- .000 Mounting Flat	"V" Rear Accessory Thread
7	.4375-.067P-.2L-TS-2A	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	M13 X 1-6g .100R	0.522 (13.26)	0.224 (5.69)	M8 X 1 6g .100R
8	.5000-.067P-.2L-TS-2A	0.980 (24.89)	0.920 (23.37)		M15 X 1-6g .100R	0.601 (15.27)	0.256 (6.50)	M10 X 1 6g .100R
9	.5625-.067P-.2L-TS-2A	1.040 (26.42)	0.980 (24.89)		M16 X 1-6g .100R	0.640 (16.26)	0.287 (7.29)	M12 X 1 6g .100R
10	.6250-.067P-.2L-TS-2A	1.110 (28.19)	1.050 (26.67)		M18 X 1-6g .100R	0.719 (18.26)	0.318 (8.08)	M14 X 1 6g .100R
11	.6875-.067P-.2L-TS-2A	1.160 (29.46)	1.110 (28.19)		M19 X 1-6g .100R	0.759 (19.28)	0.350 (8.89)	M15 X 1 6g .100R
12	.7500-.067P-.2L-TS-2A	1.230 (31.24)	1.170 (29.72)		M21 X 1-6g .100R	0.837 (21.26)	0.381 (9.68)	M17 X 1 6g .100R
14	.8750-.067P-.2L-TS-2A	1.360 (34.54)	1.320 (33.53)		M24 X 1-6g .100R	0.955 (24.26)	0.443 (11.25)	M19 X 1 6g .100R
16	1.0000-.067P-.2L-TS-2A	1.515 (38.48)	1.444 (36.68)		M27 X 1-6g .100R	1.073 (27.25)	0.505 (12.83)	M22 X 1 6g .100R
18	1.1250-.067P-.2L-TS-2A	1.610 (40.89)	1.570 (39.88)	0.128 (3.25)	M30 X 1-6g .100R	1.192 (30.28)	0.568 (14.43)	M25 X 1 6g .100R
20	1.2500-.067P-.2L-TS-2A	1.850 (46.99)	1.760 (44.70)		M34 X 1-6g .100R	1.349 (34.26)	0.630 (16.00)	M28 X 1 6g .100R
22	1.3750-.067P-.2L-TS-2A	2.010 (51.05)	1.913 (48.59)		M37 X 1-6g .100R	1.467 (37.26)	0.693 (17.60)	M31 X 1 6g .100R
24	1.5000-.067P-.2L-TS-2A	2.195 (55.75)	2.070 (52.58)		M41 X 1-6g .100R	1.624 (41.25)	0.755 (19.18)	M34 X 1 6g .100R

806-087-13 Weld Mount Receptacle Dimensions

Shell Size	"A" Thread Mating	"Ø E" ±.005 Banding Porch	"Ø L" ±.002 Flange	"Ø R" ±.002 MTG Hole	"Ø S" Thru
7	.4375-.067P-.2L-TS-2A	0.265 (6.73)	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	0.327 (8.31)	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	0.406 (10.31)	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	0.484 (12.29)	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	0.524 (13.31)	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	0.603 (15.32)	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	0.681 (17.30)	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	0.782 (19.86)	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	0.899 (22.83)	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.043 (26.49)	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	1.155 (29.34)	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	1.273 (32.33)	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)

Series 806 Mil-Aero Connectors

806-081 Hermetic Bulkhead Feedthrough



Features

- Glass-to-metal seal
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, 12, and #8 standard and hybrid layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -65°C to +200°C
- Leak Rate: 1E-7 cm³/s at 1 ATM pressure differential
- Dielectric withstanding voltage
 - #22HD contacts: 1300 VAC
 - #20HD contacts: 1800 VAC
 - #16 contacts: 1800 VAC
 - #12 contacts: 1800 VAC
 - #8 contacts: 1000 VAC
- I.R.: 5000 megOhms min at 500 VDC
- Shell-to-Shell Conductivity: 10 mV max.
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell and jam-nut: 300 series CRES
- Hermetic contacts: nickel-iron alloy, gold plated
- Socket contacts: copper alloy, gold plated
- Socket Hood: 300 series CRES
- Insulator, hermetic: vitreous glass
- Interfacial seal, peripheral seal, O-ring: fluorosilicone
- Insulator, socket: high grade rigid dielectric
- Seals and O-rings: Fluorosilicone

Series 806 hermetic bulkhead feedthroughs feature stainless steel shells and glass-to-metal seals. Rated for -65°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade circular hermetic connectors. These high performance connectors are suitable for use on pressurized bulkheads and vacuum chamber applications subject to vibration, moisture, and temperature extremes.

How To Order							
SAMPLE PART NUMBER		806-081	-07	Z1	9-1	P	A -01
Product	806-081 = Hermetic Bulkhead Feedthrough Connector						
Mounting Type	02 = Box Mount 13 = Weld Mount 07 = Jam-nut Mount						
Shell Finish	Z1 = Passivated ZL = Nickel Plated						
Shell Size-Insert Arrangement	See Table 1						
Contact Style	P = Pin on Panel Side, Socket Opposite S = Socket on Panel Side, Pin Opposite PP = Pin-Pin Feedthrough SS = Socket-Socket Feedthrough; -01 length increases by .25"						
Keyway Polarization	Per Detail						
Panel Thickness	-01 = .125 -02 = .250 -03 = .500						


Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

806-081-02 Box Mount Dimensions


SHELL SIZES	A THREAD MATING	Ø B MAX FLANGE	C SQ MAX FLANGE FLATS	D SQUARE BSC MOUNTING HOLES	F MAX FLANGE	Ø M THRU MOUNTING HOLES	Ø S THRU
7	.4375-.067P-.2L-TS-2A	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	0.100 (2.54)	0.128 (3.25)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)	0.100 (2.54)	0.128 (3.25)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)	0.100 (2.54)	0.128 (3.25)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	0.100 (2.54)	0.128 (3.25)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)	0.100 (2.54)	0.128 (3.25)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)	0.100 (2.54)	0.128 (3.25)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)	0.100 (2.54)	0.128 (3.25)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	0.100 (2.54)	0.128 (3.25)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	0.100 (2.54)	0.128 (3.25)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	0.125 (3.18)	0.154 (3.91)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	0.125 (3.18)	0.154 (3.91)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	0.125 (3.18)	0.154 (3.91)	1.525 (38.73)

Dimensions Based on Panel Thickness Option

DASH NO	T MAX	U MAX
-01	1.275 (32.39)	0.750 (19.05)
-02	1.400 (35.56)	0.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

Polarization Key Code


POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

806-081-07 Jam-Nut Mount Dimensions


SHELL SIZES	A THREAD MATING	Ø G MAX FLANGE	H SQUARE MAX FLANGE FLATS	J MAX FLANGE	Ø N +.005/- .000 (+0.13/- .000) MTG HOLE	P +.005/- .000 (+0.13/- .000) MNTG FLAT
7	.4375-.067P-.2L-TS-2A	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	0.522 (13.26)	0.224 (5.69)
8	.5000-.067P-.2L-TS-2A	0.980 (24.89)	0.920 (23.37)	0.100 (2.54)	0.601 (15.27)	0.256 (6.50)
9	.5625-.067P-.2L-TS-2A	1.040 (26.42)	0.980 (24.89)	0.100 (2.54)	0.640 (16.26)	0.287 (7.29)
10	.6250-.067P-.2L-TS-2A	1.110 (28.19)	1.050 (26.67)	0.100 (2.54)	0.719 (18.26)	0.318 (8.08)
11	.6875-.067P-.2L-TS-2A	1.160 (29.46)	1.110 (28.19)	0.100 (2.54)	0.759 (19.28)	0.350 (8.89)
12	.7500-.067P-.2L-TS-2A	1.230 (31.24)	1.170 (29.72)	0.100 (2.54)	0.837 (21.26)	0.381 (9.68)
14	.8750-.067P-.2L-TS-2A	1.360 (34.54)	1.320 (33.53)	0.100 (2.54)	0.955 (24.26)	0.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	1.515 (38.48)	1.444 (36.68)	0.100 (2.54)	1.073 (27.25)	0.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	1.610 (40.89)	1.570 (39.88)	0.100 (2.54)	1.192 (30.28)	0.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	1.850 (46.99)	1.760 (44.70)	0.128 (3.25)	1.349 (34.26)	0.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	2.010 (51.05)	1.913 (48.59)	0.128 (3.25)	1.467 (37.26)	0.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	2.195 (55.75)	2.070 (52.58)	0.128 (3.25)	1.624 (41.25)	0.755 (19.18)

Dimensions Based on Panel Thickness Option

DASH NO	T MAX	U MAX
-01	1.275 (32.39)	0.750 (19.05)
-02	1.400 (35.56)	0.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

Polarization Key Code


POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

806-081-13 Weld Mount Dimensions

SHELL SIZES	A THREAD MATING	ϕL $\pm .002 (0.05)$ FLANGE	ϕR $\pm .002 (0.05)$ MTG HOLE	ϕS THRU
7	.4375-.067P-.2L-TS-2A	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)

Dimensions Based on Panel Thickness Option


DASH NO	T MAX	U MAX
-01	1.275 (32.39)	0.750 (19.05)
-02	1.400 (35.56)	0.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

Polarization Key Code

POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

Series 806 Mil-Aero Connectors

806-083 Hermetic Bulkhead Feedthrough with RF Contacts



Features

- Glass-to-metal seal
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, 12, and #8 standard and hybrid layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -65°C to +200°C
- Leak rate: 1E-7 cm³/s at 1 ATM pressure differential
- Dielectric withstanding voltage
 - #22HD contacts: 1300 VAC
 - #20HD contacts: 1800 VAC
 - #16 contacts: 1800 VAC
 - #12 contacts: 1800 VAC
 - #8 contacts: 1000 VAC
- R/F Contacts - Per As39029 or Glenair Spec
- I.R.: 5000 megOhms min at 500 VDC
- Shell-to-shell conductivity: 10 mV max.
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High impact shock: MIL-S-901 Grade A
- Indirect lightning strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell and jam-nut: 300 Series
- Hermetic contacts: nickel-iron alloy, gold plate
- Socket contacts: copper alloy, gold plated
- Socket hood: 300 Series
- Hermetic insulator: vitreous glass
- Socket insulator: high grade rigid dielectric
- Seals and O-rings: fluorosilicone


Series 806 hermetic bulkhead feedthroughs feature RF contacts and stainless steel shells and glass-to-metal seals. Rated for -65°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight. Series 806 connectors are ideal for pressurized bulkheads subject to vibration, moisture, and temperature extremes.

How To Order

SAMPLE PART NUMBER		806-083	-07	Z1	9-1	C	P	A	-01	-75
Product	806-083 = Hermetic Bulkhead Feedthrough with RF Contacts									
Mounting Type	02 = Square Flange 13 = Weld Mount 07 = Jam-nut									
Shell Finish	Z1 = Passivated ZL = Nickel Plated									
Shell Size - Insert Arr.	See Table 1									
RF Contact	C = Co-Ax D = Differential Twin-Ax* Q = Quadrax* T = Concentric Twin-Ax* *Size 8 contacts; for signal/power, see 806-081									
Contact Style	P = Pin on Panel Side, Socket Opposite S = Socket on Panel Side, Pin Opposite									
Keyway Polarization	Per Polarization Key Code									
Panel Thickness	-01 = .125 -02 = .250 -03 = .500									
Nominal Impedance	#12 & #8 Quadrax -75 = 75 ohm; omit for std (50 ohm) -150 = 150 ohm; omit for std (100 ohm)									

Table I: Shell Size - Insert Arrangement


Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69	69					18-3					3
8-4	4					24-92	92					20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

806-083-02 Square Flange Dimensions

SHELL SIZES	A THREAD MATING	ø B MAX FLANGE	C SQ MAX FLANGE FLATS	D SQUARE BSC MOUNTING HOLES	F MAX FLANGE	ø M THRU MOUNTING HOLES	ø S THRU
7	.4375-.067P-.2L-TS-2A	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	0.100 (2.54)	0.128 (3.25)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)	0.100 (2.54)	0.128 (3.25)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)	0.100 (2.54)	0.128 (3.25)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	0.100 (2.54)	0.128 (3.25)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)	0.100 (2.54)	0.128 (3.25)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)	0.100 (2.54)	0.128 (3.25)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)	0.100 (2.54)	0.128 (3.25)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	0.100 (2.54)	0.128 (3.25)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	0.100 (2.54)	0.128 (3.25)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	0.125 (3.18)	0.154 (3.91)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	0.125 (3.18)	0.154 (3.91)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	0.125 (3.18)	0.154 (3.91)	1.525 (38.73)

Dimensions Based on Panel Thickness Option

DASH NO	T MAX	U MAX
-01	1.275 (32.39)	0.750 (19.05)
-02	1.400 (35.56)	0.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

Polarization Key Code


POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

Series 806 Mil-Aero Connectors

806-083 Hermetic Bulkhead Feedthrough with RF Contacts



806-083-07 Jam-Nut




SHELL SIZES	A THREAD MATING	ø G MAX FLANGE	H SQUARE MAX FLANGE FLATS	J MAX FLANGE	ø N +.005/- .000 (+0.13/- .000) MTG HOLE	P +.005/- .000 (+0.13/- .000) MNTG FLAT
7	.4375-.067P-.2L-TS-2A	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	0.522 (13.26)	0.224 (5.69)
8	.5000-.067P-.2L-TS-2A	0.980 (24.89)	0.920 (23.37)	0.100 (2.54)	0.601 (15.27)	0.256 (6.50)
9	.5625-.067P-.2L-TS-2A	1.040 (26.42)	0.980 (24.89)	0.100 (2.54)	0.640 (16.26)	0.287 (7.29)
10	.6250-.067P-.2L-TS-2A	1.110 (28.19)	1.050 (26.67)	0.100 (2.54)	0.719 (18.26)	0.318 (8.08)
11	.6875-.067P-.2L-TS-2A	1.160 (29.46)	1.110 (28.19)	0.100 (2.54)	0.759 (19.28)	0.350 (8.89)
12	.7500-.067P-.2L-TS-2A	1.230 (31.24)	1.170 (29.72)	0.100 (2.54)	0.837 (21.26)	0.381 (9.68)
14	.8750-.067P-.2L-TS-2A	1.360 (34.54)	1.320 (33.53)	0.100 (2.54)	0.955 (24.26)	0.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	1.515 (38.48)	1.444 (36.68)	0.100 (2.54)	1.073 (27.25)	0.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	1.610 (40.89)	1.570 (39.88)	0.100 (2.54)	1.192 (30.28)	0.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	1.850 (46.99)	1.760 (44.70)	0.128 (3.25)	1.349 (34.26)	0.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	2.010 (51.05)	1.913 (48.59)	0.128 (3.25)	1.467 (37.26)	0.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	2.195 (55.75)	2.070 (52.58)	0.128 (3.25)	1.624 (41.25)	0.755 (19.18)


Dimensions Based on Panel Thickness Option

DASH NO	T MAX	U MAX
-01	1.275 (32.39)	0.750 (19.05)
-02	1.400 (35.56)	0.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

Polarization Key Code




POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

806-083-13 Weld Mount

SHELL SIZES	A THREAD MATING	Ø L ±.002 (0.05) FLANGE	Ø R ±.002 (0.05) MTG HOLE	Ø S THRU
7	.4375-.067P-.2L-TS-2A	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)

Dimensions Based on Panel Thickness Option

DASH NO	T MAX	U MAX
-01	1.275 (32.39)	0.750 (19.05)
-02	1.400 (35.56)	0.875 (22.23)
-03	1.650 (41.91)	1.125 (28.58)

Polarization Key Code

POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

A technician wearing a flight helmet, goggles, and gloves is working on the underside of an aircraft. He is holding a screwdriver in his right hand and reaching up with his left hand to adjust a component. The background is a clear blue sky.

LIGHTWEIGHT, LOW RESISTANCE


CODE RED

“Mission-Critical” hermetic sealing with 1×10^{-7} leak-rate performance

Hermetically-sealed interconnects used in vacuum or high-altitude applications prevent moisture and other contaminants from damaging sensitive electronic equipment. Glass-to-metal hermetic sealing has been the gold standard in the aerospace and petrochemical industries for decades due to the strength and long-term durability of the materials used. But glass-to-metal seal hermetics come with a big price tag in both weight and electrical resistance.

CODE RED is an innovative sealing encapsulant and application process—invented by Glenair—that provides durable hermetic sealing in a lightweight aluminum package. CODE RED allows for the use of conventional gold-plated copper alloy contacts, significantly improving electrical performance. CODE RED hermetic connectors are available now in Glenair SuperNine® (D38999 Series III type metal and composite), Series 80 Mighty Mouse, and M24308 D-Sub; and deliver reliable, life-of-system 1×10^{-7} max leak-rate hermetic sealing. Special non-magnetic (zero residual magnetism) versions are also available, consult factory.

- Full hermetic sealing, 1×10^{-7} in a lightweight aluminum shell with low electrical resistance gold-plated copper contacts
- Passed full D38999/23 qualification testing
- Meets NASA outgassing requirements, as well as aerospace temperature and corrosion resistance standards
- Operating temperature -65°C to $+200^{\circ}\text{C}$
- Available today in Mighty Mouse 806 Mil-Aero, M24308/9 D-Sub and D38999/23
- Significant weight savings—up to +50%
- Order-of-magnitude improvement in current carrying capacity and electrical resistance compared to Kovar/Inconel solutions

CODE RED LIGHTWEIGHT HERMETIC CONNECTOR TESTING AND VALIDATION

Connectors utilizing CODE RED hermetic encapsulant sealing went through a grueling qualification test and validation process to prove material durability and hermeticity. Validation testing including 100 cycles of thermal shock IAW EIA-364-32 Test Condition A -65°C to +200°C while maintaining hermeticity followed by 1000 hours of thermal aging at 200°C. Additional tests included:

- DWV, DWV at altitude
- IR, IR at temperature
- Highly Accelerated Life Testing (HALT)
- Insert and contact retention
- Mating durability
- Random vibration at temperature IAW MIL-DTL-38999
- Hermetic seal at 30 psi

The entire qualification test cycle was repeated successfully a second time with new parts to validate complete reliability.


CODE RED USES PROVEN-PERFORMANCE CONNECTOR AND CONTACT MATERIALS

CODE RED Materials / Finish	
Sealing Adhesive	Proprietary Glenair compound
Contacts*	Gold-plated beryllium copper alloy per ASTM B 197 or equivalent
Insulator	Rigid plastic
Seals	Blended fluorosilicone/silicone elastomer
Receptacle Shell and Jam Nut*	Aluminum alloy 6061-T6 per ASTM B 221
Finish*	Electroless nickel per ASTM B 733

*zero residual magnetism materials also available

Percentage Weight Savings CODE RED vs. Glass-to-Metal MIL-DTL-38999 Sr. III	
Shell Size/Insert Arr.	Weight Reduction
9-35	52%
11-98	47%
13-35	47%
15-97	42%
19-32	40%
21-11	32%
23-21	28%
25-08	43%

Graph illustrates Current Carrying Capacity of CODE RED copper alloy contacts compared to the Inconel, Kovar, and nickel iron contacts used in conventional glass-to-metal seal hermetics.




APPLICATION NOTES: CODE RED is a viable drop-in solution for conventional glass-to-metal seal hermetic connectors with the following exceptions:

- 1. Fuel Cells:** Although CODE RED exhibits outstanding resistance to caustic chemicals and fuels, its use in fuel tanks/fuel cell applications is not recommended.
- 2. Cryogenics:** CODE RED has been tested and qualified to -65°C IAW MIL-DTL-38999
- 3. Sustained High-Operating Temperatures:** CODE RED has been tested and qualified to +200°C IAW MIL-DTL-38999
- 4. High Radiation:** Exposure to no more than 6 Megarads of radiation
- 5. Deep Subsea:** CODE RED is ideally suited for aerospace and downhole applications that do not exceed 2 BAR (30 psi) atmospheric pressure differential.
- 6. Space Life Support Systems:** Requires additional qualification testing not yet performed by Glenair.

SERIES 806 Mil-Aero Hermetic Receptacles



806-067 Hermetic Receptacles with Accessory Thread or Banding Porch




Series 806 hermetic receptacles feature stainless steel shells and glass-to-metal seals. Rated for -65°C to +200°C temperature range. Micro miniature Series 806 connectors save size and weight compared to legacy aerospace-grade hermetic connectors. These high performance, parylene compatible connectors are suitable for pressurized bulkhead applications subject to vibration, moisture, and temperature extremes.

How To Order

Sample Part Number	806-067	-07	Z1	8-7	P	-B	A
Series	806-067 Hermetic Receptacle						
Mounting Type	02 = Box Mount 13 = Weld Mount 07 = Jam-Nut Mount						
Finish	Z1 = Passivated ZL = Nickel Plated						
Shell Size - Insert Arr.	See Insert Arrangement table						
Contact Type	P = Pin S = Socket						
Rear Attachment Style	B = Banding Porch (Terminate Shield With Glenair Nano Band) T = Accessory Threads						
Polarization	A, B, C, D, E, F						

Polarization Key Code



POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

Shell Size - Insert Arrangement

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				16-2					2
8-4	4					24-92		92				18-3					3
8-7	7					8-1			1			20-4					4
9-11	11					10-2			2			22-5					5
10-15	15					11-4			4			24-8					8
11-19	19					12-5			5			10-8A	6		2		
12-26	26					14-7			7			11-13	11		2		
14-39	39					16-12			12			12-27	26		1		
16-60	60					18-15			15			14-21	17		4		
18-85	85					20-22			22			16-41	37		4		
20-110	110					22-24			24			18-59	55		4		
22-140	140					24-35			35			11-14	13			1	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		12-14	12			2	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4

NOTES


- DWV
 - #22 cont: 1300 VAC
 - #20 cont: 1800 VAC
 - #16, 12, & 8: Varies; consult factory
- I.R. - 5000 MEGOHMS min @ 500 VDC
- Assembly to be identified with Glenair name and/or cage code, part number, and date code (space permitting).
- 806-067 Receptacles mate with Glenair 806-style plug connectors with same size, arrangement, polarization, and opposite contact gender.
- Material / finish:
 - Shells & jam-nut: 304L cres / per p/n dev
 - Contacts, hermetic: Nickel-iron alloy / gold plate
 - Contacts, sockets: Copper alloy / gold plate
 - Insulator, hermetic: Vitreous glass
 - Insulator, socket: Rigid dielectric / none
 - Seals & o-rings: Fluorosilicone / N.A.

SERIES 806 Mil-Aero Hermetic Receptacles



806-067 Hermetic Receptacles with Accessory Thread or Banding Porch

806-067-02 BOX MOUNT HERMETIC RECEPTACLE



Dimensions									
Shell Sizes	"A" Thread Mating	"Ø B" Max Flange	"C" Square Max Flange Flats	"D" Square Bsc Mounting Holes	"Ø ET" Accessory Thread -0.100R	"Ø EB" ±.005 Banding Porch	"F" Max Flange	"Ø M" Thru Mtg Holes	"Ø S" Thru
7	.4375-.067P-.2L-TS-2A	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	M8 x 1.0-6g	0.265 (6.73)	0.100 (2.54)	0.128 (3.25)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)	M10 x 1.0-6g	0.327 (8.31)	0.100 (2.54)	0.128 (3.25)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)	M12 x 1.0-6g	0.406 (10.31)	0.100 (2.54)	0.128 (3.25)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	M14 x 1.0-6g	0.484 (12.29)	0.100 (2.54)	0.128 (3.25)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)	M15 x 1.0-6g	0.524 (13.31)	0.100 (2.54)	0.128 (3.25)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)	M17 x 1.0-6g	0.603 (15.32)	0.100 (2.54)	0.128 (3.25)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)	M19 x 1.0-6g	0.681 (17.30)	0.100 (2.54)	0.128 (3.25)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	M22 x 1.0-6g	0.782 (19.86)	0.100 (2.54)	0.128 (3.25)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	M25 x 1.0-6g	0.899 (22.83)	0.100 (2.54)	0.128 (3.25)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	M28 x 1.0-6g	1.043 (26.49)	0.125 (3.18)	0.154 (3.91)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	M31 x 1.0-6g	1.155 (29.34)	0.125 (3.18)	0.154 (3.91)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	M34 x 1.0-6g	1.273 (32.33)	0.125 (3.18)	0.154 (3.91)	1.525 (38.73)


SERIES 806 GLASS-TO-METAL SEAL CONNECTORS

SERIES 806
Mil-Aero Hermetic Receptacles



806-067 Hermetic Receptacles with Accessory Thread or Banding Porch

806-067-07 JAM-NUT MOUNT HERMETIC RECEPTACLE



Dimensions									
Shell Sizes	"A" Thread Mating	"ET" Accessory Threads -.100R	"Ø EB" ±.005 Banding Porch	"Ø G" Max Flange	"H" Square Max Flange Flats	"J" Max Flange	"K" Thread Mounting	"Ø N" +.005/- .000 Mounting Hole	"P" +.005/- .000 Mounting Flat
7	.4375-.067P-.2L-TS-2A	M8 X 1.0-6g	.265 (6.73)	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	M13 X 1-6g .100R	0.522 (13.26)	0.224 (5.69)
8	.5000-.067P-.2L-TS-2A	M10 X 1.0-6g	.327 (8.31)	0.980 (24.89)	0.920 (23.37)		M15 X 1-6g .100R	0.601 (15.27)	0.256 (6.50)
9	.5625-.067P-.2L-TS-2A	M12 x 1.0-6g	.406 (10.31)	1.040 (26.42)	0.980 (24.89)		M16 X 1-6g .100R	0.640 (16.26)	0.287 (7.29)
10	.6250-.067P-.2L-TS-2A	M14 X 1.0-6g	.484 (12.29)	1.110 (28.19)	1.050 (26.67)		M18 X 1-6g .100R	0.719 (18.26)	0.318 (8.08)
11	.6875-.067P-.2L-TS-2A	M15 X 1.0-6g	.524 (13.31)	1.160 (29.46)	1.110 (28.19)		M19 X 1-6g .100R	0.759 (19.28)	0.350 (8.89)
12	.7500-.067P-.2L-TS-2A	M17 X 1.0-6g	.603 (15.32)	1.230 (31.24)	1.170 (29.72)		M21 X 1-6g .100R	0.837 (21.26)	0.381 (9.68)
14	.8750-.067P-.2L-TS-2A	M19 X 1.0-6g	.681 (17.30)	1.360 (34.54)	1.320 (33.53)		M24 X 1-6g .100R	0.955 (24.26)	0.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	M22 X 1.0-6g	.782 (19.86)	1.515 (38.48)	1.444 (36.68)		M27 X 1-6g .100R	1.073 (27.25)	0.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	M25 X 1.0-6g	.899 (22.83)	1.610 (40.89)	1.570 (39.88)	0.128 (3.25)	M30 X 1-6g .100R	1.192 (30.28)	0.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	M28 X 1.0-6g	1.043 (26.49)	1.850 (46.99)	1.760 (44.70)		M34 X 1-6g .100R	1.349 (34.26)	0.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	M31 X 1.0-6g	1.155 (29.34)	2.010 (51.05)	1.913 (48.59)		M37 X 1-6g .100R	1.467 (37.26)	0.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	M34 X 1.0-6g	1.273 (32.33)	2.195 (55.75)	2.070 (52.58)		M41 X 1-6g .100R	1.624 (41.25)	0.755 (19.18)

SERIES 806 GLASS-TO-METAL SEAL CONNECTORS

Glennair®


806-067-13 WELD MOUNT HERMETIC RECEPTACLE



Dimensions						
Shell Sizes	"A" Thread Mating	"ET" Accessory Threads -0.100R	"Ø EB" ±.005 Banding Porch	"ø L" ±.002 Flange	"ø R" ±.002 MTG Hole	"ø S" Thru
7	.4375-.067P-.2L-TS-2A	M8 X 1.0-6g	.265 (6.73)	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	M10 X 1.0-6g	.327 (8.31)	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	M12 x 1.0-6g	.406 (10.31)	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	M14 X 1.0-6g	.484 (12.29)	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	M15 X 1.0-6g	.524 (13.31)	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	M17 X 1.0-6g	.603 (15.32)	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	M19 X 1.0-6g	.681 (17.30)	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	M22 X 1.0-6g	.782 (19.86)	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	M25 X 1.0-6g	.899 (22.83)	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	M28 X 1.0-6g	1.043 (26.49)	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	M31 X 1.0-6g	1.155 (29.34)	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	M34 X 1.0-6g	1.273 (32.33)	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)

Series 806 Mil-Aero Connectors

806-028 Lightweight Aluminum Hermetic Receptacles, PC Tail


CODE RED


Features

- Triple-start stub ACME mating thread
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, #12, #8 standard and hybrid layouts
- Aerospace-grade material options, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature: -65°C to +200°C
- Leak Rate: 1E-7 cm³/s at 1 ATM pressure differential
- Dielectric withstanding voltage
#22HD layouts: 1300 VAC
#20HD layouts: 1800 VAC
#16 layouts: contact factory
#12 layouts: contact factory
#8 layouts: contact factory
- Mating durability: 500 cycles
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random): EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Salt spray (dynamic): EIA-364-26, 96 hours
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak


Connector Construction

- Shell and jam-nut: see Table II
- Contacts: copper alloy, gold plating
- Sealing compound: proprietary Glenair formulation
- Dielectric inserts: high grade rigid dielectric
- Interfacial seal, peripheral seal, O-ring: fluorosilicone


Lightweight aluminum Hermetic. Higher current rating. 806-028 aluminum hermetic receptacles are lighter than stainless steel glass-to-metal hermetic connectors. A signature sealing process delivers reliable hermetic performance at extreme temperatures. Copper alloy contacts have lower resistance and higher current rating than iron alloy contacts used in standard hermetics. Hermeticity is 1E⁻⁷ cm³/sec at 1 ATM pressure differential. Series supports hybrid signal and high-speed / RF shielded contacts including Glenair Signature El Ochito (up to 40 GbE), Quadrax, 50 Ohm Coax, and differential Twinax for 10GbE, HDMI, USB 3.0, and RF applications. Integral standoffs and threaded mounting holes offer secure attachment to rigid or flex circuits and parylene compatible.

How To Order						
SAMPLE PART NUMBER		806-028	-ME	8-7	P	1 A
Product	806-028 = Jam-nut Receptacle with PC Tails					
Shell Material and Finish	See Table II					
Arrangement Number (Shell Size - Insert Arr.)	See Table I					
Contact Type	P = Pin S = Socket					
PC Tail Length	1 = .125" (3.18 mm.) 2 = .250" (6.35 mm.)					
Polarization	A B C D E F					

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

806-028 Lightweight Aluminum Hermetic Receptacles, PC Tail**806-028 Receptacle Dimensions**

Shell Size	ØA Max	B Thread	C Max	D	E Max	F Mating Thread
7	.848 (21.54)	M8x1.0-6g-0.100R	.908 (23.06)	.489 (12.42)	.100 (2.54)	.4375-.067P-.2L-TS-2A
8	.980 (24.89)	M15x1.0-6g-0.100R	.920 (23.37)	.534 (13.56)	.100 (2.54)	.5000-.067P-.2L-TS-2A
9	1.040 (26.42)	M16x1.0-6g-0.100R	.980 (24.89)	.579 (14.71)	.100 (2.54)	.5625-.067P-.2L-TS-2A
10	1.110 (28.19)	M18x1.0-6g-0.100R	1.050 (26.67)	.679 (17.25)	.100 (2.54)	.6250-.067P-.2L-TS-2A
11	1.160 (29.46)	M19x1.0-6g-0.100R	1.110 (28.19)	.734 (18.64)	.100 (2.54)	.6875-.067P-.2L-TS-2A
12	1.230 (31.24)	M21x1.0-6g-0.100R	1.170 (29.72)	.804 (20.42)	.100 (2.54)	.7500-.067P-.2L-TS-2A
14	1.360 (34.54)	M24x1.0-6g-0.100R	1.320 (33.53)	.891 (22.63)	.100 (2.54)	.8750-.067P-.2L-TS-2A
16	1.515 (38.48)	M27x1.0-6g-0.100R	1.444 (36.68)	1.049 (26.64)	.100 (2.54)	1.0000-.067P-.2L-TS-2A
18	1.610 (40.89)	M30x1.0-6g-0.100R	1.570 (39.88)	1.148 (29.16)	.100 (2.54)	1.1250-.067P-.2L-TS-2A
20	1.850 (46.99)	M34x1.0-6g-0.100R	1.760 (44.70)	1.252 (31.80)	.128 (3.25)	1.2500-.067P-.2L-TS-2A
22	2.010 (51.05)	M37x1.0-6g-0.100R	1.913 (48.59)	1.369 (34.77)	.128 (3.25)	1.3750-.067P-.2L-TS-2A
24	2.195 (55.75)	M41x1.0-6g-0.100R	2.070 (52.58)	1.509 (38.33)	.128 (3.25)	1.5000-.067P-.2L-TS-2A

806-028 Jam-nut D-Hole Dims.

Shell Size	ØA +.005/-0.00 (+.013/-0.00)	B +.005/-0.00 (+.013/-0.00)
7	.552 (14.02)	.224 (5.69)
8	.601 (15.27)	.256 (6.50)
9	.640 (16.26)	.287 (7.29)
10	.719 (18.26)	.318 (8.08)
11	.759 (19.28)	.350 (8.89)
12	.837 (21.26)	.381 (9.68)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)

Table II: Material and Finish

Sym	Material	Finish	Temp. Range
AB	Marine Bronze	None (Clean Only)	-65° to +200°C
M	Aluminum Alloy	Electroless Nickel,	
MA		Electroless Nickel, Matte Finish	
ME		Electroless Nickel	
NF		Cad/O.D. over electroless nickel	-65° to +175°C
ZN		Zinc Ni, Olive Drab	
ZR		Zinc Ni, Black (Tri-Valent CR)	

Series 806 Mil-Aero Connectors



806-043 Lightweight Hermetic PCB Receptacle with El Ochito Contacts

CODE RED


Features

- Triple-start stub ACME mating thread
- High density #22HD / El Ochito arrangements for reduced size and weight
- Aerospace-grade materials, construction
- Integral PC board standoffs
- Threaded holes for secure attachment to rigid or flex circuits
- Alignment post

Specifications

- Operating temperature: -65°C to +175°C
- Dielectric withstanding voltage #22HD layouts: 1300 VAC
- Mating durability: 500 cycles (El Ochito)
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction


- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Potting compound: epoxy
- Interfacial seal and peripheral seal: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone

Lightweight aluminum hermetic. Higher current rating. 806-043 aluminum hermetic receptacles with high-speed El Ochito contacts are lighter than stainless steel glass-to-metal hermetic connectors. A signature sealing process delivers reliable hermetic performance. Copper alloy contacts have lower resistance and higher current rating than iron alloy contacts used in conventional hermetics. Hermeticity is $1E^{-7}$ cm³/sec at 1 ATM pressure differential. Integral standoffs and threaded mounting holes provide secure attachment to rigid or flex circuits. Series 806 connectors are parylene compatible, and ideal for high-speed aerospace data link applications.


How To Order									
SAMPLE PART NUMBER		806-043	-ME	14	E	-	20A	S	A
Product	806-043 = Jam-Nut, El Ochito PCB Recept								
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated								
Shell Size	See Table I or Dimensions Table								
Protocol Code	See Table II								
Ground Option	G = Common Ground for arrangements 10-1, 16-2, 18-3, 20-4, 22-5, and 24-8 only Dash (-) = None								
Contact Layout	See Table I								
Contact Gender	P = Pin S = Socket								
Polarization	A B C D E F								

Table I: Shell Size - Insert Arrangement

Contact Layout	Number of Contacts	
	22HD	8
10-1		1
16-2		2
18-3		3
20-4		4
22-5		5
24-8		8
14-20A	19	1
16-22	20	2
18-21	18	3
20-28	24	4
22-44	40	4
24-97	93	4

806-043 Lightweight Hermetic PCB Receptacle with El Ochito Contacts**Dimensions**

Shell Size	ØA Max	B Thread	C Max	D	E Max	F Mating Thread
10	1.110	M18 X 1-6g-.100R	1.050 (26.67)	0.679 (17.25)	0.100 (2.54)	.6250-.067P-.2L-TS-2A
14	1.360	M24 X 1-6g-.100R	1.320 (33.53)	0.891 (22.63)	0.100 (2.54)	.8750-.067P-.2L-TS-2A
16	1.515	M27 X 1-6g-.100R	1.444 (36.68)	1.049 (26.64)	0.100 (2.54)	1.000-.067P-.2L-TS-2A
18	1.610	M30 X 1-6g-.100R	1.570 (39.88)	1.148 (29.16)	0.100 (2.54)	1.1250-.067P-.2L-TS-2A
20	1.850	M34 X 1-6g-.100R	1.760 (44.70)	1.252 (31.80)	0.128 (3.25)	1.250-.067P-.2L-TS-2A
22	2.010	M37 X 1-6g-.100R	1.913 (48.59)	1.369 (34.77)	0.128 (3.25)	1.3750-.067P-.2L-TS-2A
24	2.195	M41 X 1-6g-.100R	2.070 (52.58)	1.509 (38.33)	0.128 (3.25)	1.5000-.067P-.2L-TS-2A

**Recommended Mounting Hole**

Shell Size	M +.005 (0.13) 0.000 (0.00)	N +.005 (0.13) 0.00 (0.00)
10	0.318 (8.08)	0.719 (18.26)
14	0.443 (11.25)	0.955 (24.26)
16	0.505 (12.83)	1.073 (27.25)
18	0.568 (14.43)	1.192 (30.28)
20	0.630 (16.00)	1.349 (34.26)
22	0.693 (17.60)	1.467 (37.26)
24	0.755 (19.18)	1.624 (41.25)

PC Tail Diameter

CONTACT SIZE	PC Tail
22	Ø .020
El Ochito Signal	Ø .016
El Ochito Ground	.030 Sq.

Series 806 Mil-Aero Connectors




806-043 Lightweight Hermetic PCB Receptacle with El Ochito Contacts

El Ochito Mating Contact		
PART NUMBER	PROTOCOLS	
WHITE - PIN	858-045 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-051 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
WHITE - SKT	858-046 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-052 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
BLUE - PIN	858-047	USB 3.0, OTHER 90 OHM SIGNALS
BLUE - SKT	858-048	USB 3.0, OTHER 90 OHM SIGNALS
RED - PIN	858-049	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS
RED - SKT	858-050	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS

El Ochito Protocols		
WHITE	BLUE	RED
10GBASE-T	USB 3.0	HDMI, SATA, DisplayPort

The Ochito octaxial contact has a color-coded insulator signifying the data protocol. White is used for 10 Gb Ethernet, blue is used for USB 3.0, and red is used for multi gigabit 100 ohm protocols including HDMI, DisplayPort and SATA. The connector part number includes a protocol code from Table III. This code determines specific contact position for every combination of protocol.



Example
Code E7



Example
Code E5


Table III: Protocol Code for El Ochito Contact Positions B = Blue, R = Red, W = White								
SYMBOL	Contact							
	A	B	C	D	E	F	G	H
E	W	W	W	W	W	W	W	W
E2	B	W	W	W	W	W	W	W
E3	R	W	W	W	W	W	W	W
E4	B	B	W	W	W	W	W	W
E5	R	B	W	W	W	W	W	W
E6	R	R	W	W	W	W	W	W
E7	B	B	B	W	W	W	W	W
E8	R	B	B	W	W	W	W	W
E9	R	R	B	W	W	W	W	W
E10	R	R	R	W	W	W	W	W
E11	B	B	B	B	W	W	W	W
E12	R	B	B	B	W	W	W	W
E13	R	R	B	B	W	W	W	W
E14	R	R	R	B	W	W	W	W
E15	R	R	R	R	W	W	W	W
E16	B	B	B	B	B	W	W	W
E17	R	B	B	B	B	W	W	W
E18	R	R	B	B	B	W	W	W
E19	R	R	R	B	B	W	W	W
E20	R	R	R	R	B	W	W	W
E21	R	R	R	R	R	W	W	W
E22	B	B	B	B	B	B	W	W
E23	R	B	B	B	B	B	W	W
E24	R	R	B	B	B	B	W	W
E25	R	R	R	B	B	B	W	W
E26	R	R	R	R	B	B	W	W
E27	R	R	R	R	R	B	W	W
E28	R	R	R	R	R	R	W	W
E29	B	B	B	B	B	B	B	W
E30	R	B	B	B	B	B	B	W
E31	R	R	B	B	B	B	B	W
E32	R	R	R	B	B	B	B	W
E33	R	R	R	R	B	B	B	W
E34	R	R	R	R	R	B	B	W
E35	R	R	R	R	R	R	B	W
E36	R	R	R	R	R	R	R	W
E37	B	B	B	B	B	B	B	B
E38	R	B	B	B	B	B	B	B
E39	R	R	B	B	B	B	B	B
E40	R	R	R	B	B	B	B	B
E41	R	R	R	R	B	B	B	B
E42	R	R	R	R	R	B	B	B
E43	R	R	R	R	R	R	B	B
E44	R	R	R	R	R	R	R	B
E45	R	R	R	R	R	R	R	R

HERMETIC CODE RED, MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806-077 Lightweight Hermetic Feed-Through

CODE RED



Features

- Triple-start stub ACME mating thread
- High density #22HD / El Ochito arrangements for reduced size and weight
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -65°C to +175°C
- Dielectric withstanding voltage
#22HD: 1300 VAC
#20HD, #16HD, #12HD: 1800 VAC
#8HD: 1000 VAC
- Mating durability: 500 cycles (El Ochito)
- Mechanical shock: EIA-364-27, 300g.
- Vibration (sine): MIL-DTL-38999M, 60g.
- Vibration (random) EIA-364-28 Condition VI, Letter J, 43.92 Grms, +200°C
- High Impact shock: MIL-S-901 Grade A
- Humidity: EIA-364-31 Method 4
- Salt spray (dynamic): EIA-364-26, 500 hours (96 hours for nickel-plated versions)
- Fluid immersion: EIA-364-10
- Altitude immersion: EIA-364-03 75,000 feet altitude
- Indirect Lightning Strike: EIA-364-75 Type B Level 2 10kA Peak

Connector Construction

- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plating
- Potting compound: Code Red
- Interfacial seal and peripheral seal: fluorosilicone
- Dielectric inserts: high grade rigid dielectric
- Panel O-ring: fluorosilicone

Lightweight aluminum hermetic. 806-077 aluminum hermetic receptacles with high-speed El Ochito contacts are lighter than stainless steel glass-to-metal hermetic connectors. A signature sealing process delivers reliable hermetic performance. Copper alloy contacts have lower resistance and higher current rating than iron alloy contacts used in conventional hermetics. Hermeticity is $1\text{E}^{-7} \text{ cm}^3/\text{sec}$ at 1 ATM pressure differential. Series 806 connectors are ideal for high-speed aerospace data link applications.

How To Order								
SAMPLE PART NUMBER		806-077	-07	Z1	10	E	-1	P A
Product	806-077 = El Ochito Feed-Through							
Mounting Type	02 = Box Mount 07 = Jam-Nut Mount 13 = Weld Mount							
Finish	See Table II							
Shell Size	10, 11, 12, 14, 16, 18, 20, 22, 24							
El Ochito Type	See Table IV							
Contact Arrangement	See Pages 6 thru 9 for Contact Arrangements							
Contact Style	P = Pin on Panel Side, Socket Opposite S = Socket on Panel Side, Pin Opposite							
Polarization	A B C D E F							

Table II - Material/Finish


SYM	Material	Finish
AB	Marine Bronze	None (Clean Only)
MA	Aluminum Alloy	Electroless Nickel, Matte Finish
ME		Electroless Nickel
MT		Teflon Nickel
NF		Cad/O.d. Over Electroless Nickel
ZN		Zinc Ni, Olive Drab
ZR		Zinc Ni, Black (Tri-Valent Cr)
Z1	Stainless Steel	Passivated
ZL		Electrolytic Nickel

Table III - Panel Mounting Cut-Outs

Shell Sizes	"Ø N" +.005/- .000 Mounting Hole	"P" +.005/- .000 Mounting Flat	"Ø R" ±.002 Mtg Hole	"Ø S" Thru
10	0.719 (18.26)	0.318 (8.08)	0.980 (24.89)	0.645 (16.38)
11	0.759 (19.28)	0.350 (8.89)	1.043 (26.49)	0.712 (18.08)
12	0.837 (21.26)	0.381 (9.68)	1.105 (28.07)	0.768 (19.51)
14	0.955 (24.26)	0.443 (11.25)	1.230 (31.24)	0.890 (22.61)
16	1.073 (27.25)	0.505 (12.83)	1.355 (34.42)	1.015 (25.78)
18	1.192 (30.28)	0.568 (14.43)	1.480 (37.59)	1.125 (28.58)
20	1.349 (34.26)	0.630 (16.00)	1.605 (40.77)	1.275 (32.39)
22	1.467 (37.26)	0.693 (17.60)	1.730 (43.94)	1.400 (35.56)
24	1.624 (41.25)	0.755 (19.18)	1.855 (47.12)	1.525 (38.74)

Series 806 Mil-Aero Connectors

806-077 Lightweight Hermetic Feed-Through


Table I - Connector Dimensions


Shell Sizes	"A" Thread Mating	"Ø B" Max Flange	"C" Square Max Flange Flats	"D" Square Bsc Mounting Holes	"F" Max Flange	"Ø G" Max Flange	"H" Square Max Flange Flats	"J" Max Flange	"K" Thread Mounting	"Ø L" ±.002 Flange	"Ø M" Thru Mtg Holes
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	0.100 (2.54)	1.110 (28.19)	1.050 (26.67)	0.100 (2.54)	M18 X 1-6g, 100R	0.975 (24.77)	0.128 (3.25)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)		1.160 (29.46)	1.110 (28.19)		M19 X 1-6g, 100R	1.038 (26.37)	
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)		1.230 (31.24)	1.170 (29.72)		M21 X 1-6g, 100R	1.100 (27.94)	
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)		1.360 (34.54)	1.320 (33.53)		M24 X 1-6g, 100R	1.225 (31.12)	
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	0.125 (3.18)	1.515 (38.48)	1.444 (36.68)	0.128 (3.25)	M27 X 1-6g, 100R	1.350 (34.29)	0.154 (3.91)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)		1.610 (40.89)	1.570 (39.88)		M30 X 1-6g, 100R	1.475 (37.47)	
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)		1.850 (46.99)	1.760 (44.70)		M34 X 1-6g, 100R	1.600 (40.64)	
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)		2.010 (51.05)	1.913 (48.59)		M37 X 1-6g, 100R	1.725 (43.82)	
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)		2.195 (55.75)	2.070 (52.58)		M41 X 1-6g, 100R	1.850 (46.99)	

Series 806**Mil-Aero Connectors****806-077 Lightweight Hermetic Feed-Through Receptacle**

El Ocho Mating Contact		
PART NUMBER	PROTOCOLS	
WHITE - PIN	858-045 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-051 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
WHITE - SKT	858-046 Type I	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
	858-052 Type II	10GBASE-T ETHERNET, CAT 6A 40GBASE-T ETHERNET, CAT 8
BLUE - PIN	858-047	USB 3.0, OTHER 90 OHM SIGNALS
BLUE - SKT	858-048	USB 3.0, OTHER 90 OHM SIGNALS
RED - PIN	858-049	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS
RED - SKT	858-050	HDMI, DISPLAYPORT, SATA, OTHER 100 OHM SIGNALS

El Ocho Protocols		
WHITE	BLUE	RED
10GBASE-T	USB 3.0	HDMI, SATA, DisplayPort

The Ocho octaxial contact has a color-coded insulator signifying the data protocol. White is used for 10 Gb Ethernet, blue is used for USB 3.0, and red is used for multi gigabit 100 ohm protocols including HDMI, DisplayPort and SATA. The connector part number includes a protocol code from Table III. This code determines specific contact position for every combination of protocol.



Example
Code E7



Example
Code E5

Table IV: Protocol Code for El Ocho Contact Positions B = Blue, R = Red, W = White								
SYMBOL	Contact							
	A	B	C	D	E	F	G	H
E	W	W	W	W	W	W	W	W
E2	B	W	W	W	W	W	W	W
E3	R	W	W	W	W	W	W	W
E4	B	B	W	W	W	W	W	W
E5	R	B	W	W	W	W	W	W
E6	R	R	W	W	W	W	W	W
E7	B	B	B	W	W	W	W	W
E8	R	B	B	W	W	W	W	W
E9	R	R	B	W	W	W	W	W
E10	R	R	R	W	W	W	W	W
E11	B	B	B	B	W	W	W	W
E12	R	B	B	B	W	W	W	W
E13	R	R	B	B	W	W	W	W
E14	R	R	R	B	W	W	W	W
E15	R	R	R	R	W	W	W	W
E16	B	B	B	B	B	W	W	W
E17	R	B	B	B	B	W	W	W
E18	R	R	B	B	B	W	W	W
E19	R	R	R	B	B	W	W	W
E20	R	R	R	R	B	W	W	W
E21	R	R	R	R	R	W	W	W
E22	B	B	B	B	B	B	W	W
E23	R	B	B	B	B	B	W	W
E24	R	R	B	B	B	B	W	W
E25	R	R	R	B	B	B	W	W
E26	R	R	R	R	B	B	W	W
E27	R	R	R	R	R	B	W	W
E28	R	R	R	R	R	R	W	W
E29	B	B	B	B	B	B	B	W
E30	R	B	B	B	B	B	B	W
E31	R	R	B	B	B	B	B	W
E32	R	R	R	B	B	B	B	W
E33	R	R	R	R	B	B	B	W
E34	R	R	R	R	R	B	B	W
E35	R	R	R	R	R	R	B	W
E36	R	R	R	R	R	R	R	W
E37	B	B	B	B	B	B	B	B
E38	R	B	B	B	B	B	B	B
E39	R	R	B	B	B	B	B	B
E40	R	R	R	B	B	B	B	B
E41	R	R	R	R	B	B	B	B
E42	R	R	R	R	R	B	B	B
E43	R	R	R	R	R	R	B	B
E44	R	R	R	R	R	R	R	B
E45	R	R	R	R	R	R	R	R



SERIES 240-806


EMI/EMP Filter Connectors



Glenair Series 806 filter connectors for use in EMC/EMP management of electronic systems and interconnect cabling. 806 filter connectors are designed in accordance with applicable connector specifications, and are designed to mate with plugs with the same insert configuration and opposite contact gender. Planar filter arrays and TVS diodes may be integrated into both standard catalog as well as build-to-order configurations. Glenair's state-of-the-art diode burn-in process tests leaded and surface mount diodes with leakage current monitored throughout the entire test procedure ensuring field reliability.


- Planar, multilayer ceramic capacitive filters, with and without transient voltage suppression diodes
- C and Pi electrical configurations
- PC tail or solder cup wire termination
- 35 – 240,000 pF capacitance
- Fast and reliable diode burn-in and test services
- Turnkey in-house manufacturing of all filter connector elements and processes

Filter Module Elements



Filter Types


- C** Single capacitor with low self inductance
- LC, CL** Single capacitor combined with an inductive element
- Pi** Dual capacitors with a single inductive element positioned between.



SERIES 806 CODE-RED™ Mil-Aero Lightweight Hermetic Receptacles



806-100 Solder Cup with Accessory Thread or Banding Porch Rear Attachment Receptacle



Lightweight aluminum Hermetic. with higher current rating. 806-100 aluminum hermetic receptacles are lighter than stainless steel glass-to-metal hermetic connectors. Copper alloy contacts have lower resistance and higher current rating than iron alloy contacts used in standard hermetics. A signature sealing process delivers reliable hermetic performance at extreme temperatures. Hermeticity is 1E-7 cm³/sec at 1 ATM pressure differential. Connector provides solder cup termination with accessory threads or banding porch. Ideal for harsh environment aerospace applications subject to severe wind, moisture and vibration.

How To Order							
Sample Part Number	806-100	-07	MA	8-7	P	B	A
Series	806-100 Code Red Receptacle with Accessory Thread or Banding Porch options with Solder Cup Termination						
Mounting Type	02 = Box Mount 13 = Weld Mount 07 = Jam-Nut Mount						
Material/Finish	See Material/Finish table						
Shell Size - Insert Arr.	See Insert Arrangement table						
Contact Type	P = Pin S = Socket						
Rear Attachment Style	B = Banding Porch (Terminate Shield With Glenair Nano Band) T = Accessory Threads						
Polarization	A, B, C, D, E or F						

Material/Finish		
Sym	Material/Finish	Temp. Range
AB	Marine Bronze, None (Clean Only)	-65°C to +200°C
MA	Aluminum Alloy, Electroless Nickel, Matte Finish	
ME	Aluminum Alloy, Electroless Nickel	
NF	Aluminum Alloy, Cad/O.D. Over Electroless Nickel	-65°C to +175°C
ZN	Aluminum Alloy, Zinc Ni, Olive Drab	
ZR	Aluminum Alloy, Zinc Ni, Black (Tri-Valent Cr)	

Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				16-2					2
8-4	4					24-92		92				18-3					3
8-7	7					8-1			1			20-4					4
9-11	11					10-2			2			22-5					5
10-15	15					11-4			4			24-8					8
11-19	19					12-5			5			10-8A	6		2		
12-26	26					14-7			7			11-13	11		2		
14-39	39					16-12			12			12-27	26		1		
16-60	60					18-15			15			14-21	17		4		
18-85	85					20-22			22			16-41	37		4		
20-110	110					22-24			24			18-59	55		4		
22-140	140					24-35			35			11-14	13			1	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		12-14	12			2	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4

NOTES


- Material / finish:
 - Shells & jam-nut: al alloy / per p/n dev
 - Insulator: high grade rigid dielectric / N.A.
 - O-ring & seals: fluorosilicone / N.A.
 - Contacts: copper alloy / gold plated
 - Sealing compound: polymer encapsulant
- Performances:
 - Operation temperature range: see Material/Finish table
 - Leak rate: 1 x 10⁻⁷ cc/s max helium, 1 atm.
 - I.R.: 5,000 megohms min at room temperature
 - DWV (contact size):
 - 22HD - 1300 VAC
 - 20HD - 1800 VAC
 - Others - consult factory
- Assembly to be identified with Glenair name and/or cage code, part number, and date code (space permitting).
- 806-100 Receptacles mate with Glenair 806 style plug connectors with same size, arrangement, polarization, and opposite contact gender.
- This connector meets all performance of Glenair product spec 806-014 and applies to all finishes.

SERIES 806 Mil-Aero Code Red Hermetic Connectors




806-100 Solder Cup with Accessory Thread or Banding Porch Rear Attachment Receptacle

806-100-02 CODE RED BOX MOUNT HERMETIC RECEPTACLE



Dimensions								
Shell Sizes	"A" Thread Mating	"Ø B" Max Flange	"C" Square Max Flange Flats	"D" Square Bsc Mounting Holes	"Ø Eb" ±.005 Banding Porch	"F" Max Flange	"Ø M" Thru Mtg Holes	"Ø S" Thru
7	.4375-.067P-.2L-TS-2A	0.968 (24.59)	0.750 (19.05)	0.469 (11.91)	0.265 (6.73)	0.100 (2.54)	0.128 (3.25)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	1.040 (26.42)	0.822 (20.88)	0.531 (13.49)	0.327 (8.31)			0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	1.130 (28.70)	0.885 (22.48)	0.594 (15.09)	0.406 (10.31)			0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	1.174 (29.82)	0.913 (23.19)	0.625 (15.88)	0.484 (12.29)			0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	1.240 (31.50)	0.960 (24.38)	0.670 (17.02)	0.524 (13.31)			0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	1.354 (34.39)	1.040 (26.42)	0.765 (19.43)	0.603 (15.32)			0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	1.510 (38.35)	1.133 (28.78)	0.859 (21.82)	0.681 (17.30)			0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	1.620 (41.15)	1.227 (31.17)	0.938 (23.83)	0.782 (19.86)			1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	1.784 (45.31)	1.320 (33.53)	1.016 (25.81)	0.899 (22.83)	0.125 (3.18)	0.154 (3.91)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	1.910 (48.51)	1.444 (36.68)	1.109 (28.17)	1.043 (26.49)			1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	2.083 (52.91)	1.570 (39.88)	1.203 (30.56)	1.155 (29.34)			1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	2.200 (55.88)	1.696 (43.08)	1.312 (33.32)	1.273 (32.33)			1.525 (38.73)

Polarization Key Code




POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°

SERIES 806
Mil-Aero Code Red Hermetic Connectors




806-100 Solder Cup with Accessory Thread or Banding Porch Rear Attachment Receptacle

806-100-07 CODE RED JAM-NUT MOUNT HERMETIC RECEPTACLE



Dimensions								
Shell Sizes	"A" Thread Mating	"ET" Accessory Threads -0.100R	"Ø G" Max Flange	"H" Square Max Flange Flats	"J" Max Flange	"K" Thread Mounting	"Ø N" +.005/- .000 Mounting Hole	"P" +.005/- .000 Mounting Flat
7	.4375-.067P-.2L-TS-2A	M8 X 1.0-6g	0.848 (21.54)	0.908 (23.06)	0.100 (2.54)	M13 X 1-6g-.100R	0.522 (13.26)	0.224 (5.69)
8	.5000-.067P-.2L-TS-2A	M10 X 1.0-6g	0.980 (24.89)	0.920 (23.37)		M15 X 1-6g .100R	0.601 (15.27)	0.256 (6.50)
9	.5625-.067P-.2L-TS-2A	M12 x 1.0-6g	1.040 (26.42)	0.980 (24.89)		M16 X 1-6g .100R	0.640 (16.26)	0.287 (7.29)
10	.6250-.067P-.2L-TS-2A	M14 X 1.0-6g	1.110 (28.19)	1.050 (26.67)		M18 X 1-6g .100R	0.719 (18.26)	0.318 (8.08)
11	.6875-.067P-.2L-TS-2A	M15 X 1.0-6g	1.160 (29.46)	1.110 (28.19)		M19 X 1-6g .100R	0.759 (19.28)	0.350 (8.89)
12	.7500-.067P-.2L-TS-2A	M17 X 1.0-6g	1.230 (31.24)	1.170 (29.72)		M21 X 1-6g .100R	0.837 (21.26)	0.381 (9.68)
14	.8750-.067P-.2L-TS-2A	M19 X 1.0-6g	1.360 (34.54)	1.320 (33.53)		M24 X 1-6g .100R	0.955 (24.26)	0.443 (11.25)
16	1.0000-.067P-.2L-TS-2A	M22 X 1.0-6g	1.515 (38.48)	1.444 (36.68)		M27 X 1-6g .100R	1.073 (27.25)	0.505 (12.83)
18	1.1250-.067P-.2L-TS-2A	M25 X 1.0-6g	1.610 (40.89)	1.570 (39.88)		M30 X 1-6g .100R	1.192 (30.28)	0.568 (14.43)
20	1.2500-.067P-.2L-TS-2A	M28 X 1.0-6g	1.850 (46.99)	1.760 (44.70)	0.128 (3.25)	M34 X 1-6g .100R	1.349 (34.26)	0.630 (16.00)
22	1.3750-.067P-.2L-TS-2A	M31 X 1.0-6g	2.010 (51.05)	1.913 (48.59)		M37 X 1-6g .100R	1.467 (37.26)	0.693 (17.60)
24	1.5000-.067P-.2L-TS-2A	M34 X 1.0-6g	2.195 (55.75)	2.070 (52.58)		M41 X 1-6g .100R	1.624 (41.25)	0.755 (19.18)

Polarization Key Code



POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°


SEREIS 806 CODE RED CONNECTORS

SERIES 806
Mil-Aero Code Red Hermetic Connectors



806-100 Solder Cup with Accessory Thread or Banding Porch Rear Attachment Receptacle

806-100-13 CODE RED WELD MOUNT HERMETIC RECEPTACLE




-13 PANEL CUT-OUT


* IF THICKER THAN .030 COUNTERBORE IS REQUIRED FOR BACKSHELL NUT

Dimensions					
Shell Sizes	"A" Thread Mating	"ET" Accessory Threads -0.100R	" ϕL " $\pm .002$ Flange	" ϕR " $\pm .002$ MTG Hole	" ϕS " Thru
7	.4375-.067P-.2L-TS-2A	M8 X 1.0-6g	0.725 (18.42)	0.730 (18.54)	0.445 (11.30)
8	.5000-.067P-.2L-TS-2A	M10 X 1.0-6g	0.788 (20.02)	0.793 (20.14)	0.509 (12.93)
9	.5625-.067P-.2L-TS-2A	M12 x 1.0-6g	0.912 (23.16)	0.917 (23.29)	0.577 (14.66)
10	.6250-.067P-.2L-TS-2A	M14 X 1.0-6g	0.975 (24.76)	0.980 (24.89)	0.645 (16.38)
11	.6875-.067P-.2L-TS-2A	M15 X 1.0-6g	1.038 (26.37)	1.043 (26.49)	0.712 (18.08)
12	.7500-.067P-.2L-TS-2A	M17 X 1.0-6g	1.100 (27.94)	1.105 (28.07)	0.768 (19.51)
14	.8750-.067P-.2L-TS-2A	M19 X 1.0-6g	1.225 (31.12)	1.230 (31.24)	0.890 (22.61)
16	1.0000-.067P-.2L-TS-2A	M22 X 1.0-6g	1.350 (34.29)	1.355 (34.42)	1.015 (25.78)
18	1.1250-.067P-.2L-TS-2A	M25 X 1.0-6g	1.475 (37.47)	1.480 (37.59)	1.125 (28.58)
20	1.2500-.067P-.2L-TS-2A	M28 X 1.0-6g	1.600 (40.64)	1.605 (40.77)	1.275 (32.39)
22	1.3750-.067P-.2L-TS-2A	M31 X 1.0-6g	1.725 (43.82)	1.730 (43.94)	1.400 (35.56)
24	1.5000-.067P-.2L-TS-2A	M34 X 1.0-6g	1.850 (46.99)	1.855 (47.12)	1.525 (38.73)

Polarization Key Code



POS	A°	B°	C°	D°
A	105°	140°	215°	265°
B	102°	170°	248°	305°
C	80°	150°	230°	295°
D	68°	140°	205°	275°
E	64°	155°	234°	304°
F	72°	120°	200°	298°



Features

- Ceramic planar filter array
- Solder cup or PC tail contacts
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, #12, #8 standard and hybrid layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -55°C to +125°C
- Dielectric withstanding voltage: 300 VDC
- Current rating
 - #20HD contacts: 5 A max.
 - #22HD contacts: 3 A max.
 - #16 contacts: contact factory
 - #12 contacts: contact factory
 - #8 contacts: contact factory
- Mating durability: 500 cycles

Connector Construction

- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plated
- Seals: fluorosilicone
- Insulator: high grade rigid dielectric

Table 2 Capacitance Class		
Capacitance Range (pF)		
Filter Type		
Class	P (Pi-Section)	C, L, M (C, L-C, C-L)
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300
J	70 - 120	35 - 60

Ceramic planar array C and Pi filters. PC tail or solder cup contacts. 240-806 filtered receptacles strip line signals of unwanted RF or HRF noise. Suitable for areas subject to high vibration, altitude, and moisture. Operating temperature of -55°C to +125°C.

How To Order									
SAMPLE PART NUMBER		240-806	-07	ME	8-7	PS	C	B	A
Product	240-806 = Filtered Receptacle								
Mounting Type	07 = Jam-nut with Solder Cup Contacts and NanoBand Platform 08 = Jam-nut with PC Tail Contacts*								
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium ZI = Stainless Steel, Passivated								
Arrangement Number	See Table 1 (Shell Size - Insert Arr.)								
Contact Type	PP = Pin, PC Tail (mounting type 08 only) PS = Pin, Solder Cup (mounting type 07 only) SP = Socket, PC Tail (mounting type 08 only) SS = Socket, Solder Cup (mounting type 07 only)								
Filter Type (Table 3)	P = Pi Filter C = C Filter L = L - C Filter M = C - L Filter								
Capacitance Class (Table 2)	A B C D E F G J								
Polarizing Position	A B C D E F								




* PC-tail contact versions are parylene-compatible

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

FILTER, MICRO MINIATURE CIRCULAR

Series 806 Mil-Aero Connectors

240-806-07, 240-806-08 Receptacles, Jam-nut, Solder Cup or PC Tail



Contact Size	øU	
	± .002 (0.05)	
	In.	mm.
#20	.026	0.66
#22	.020	0.51


SHELL STYLE 07
JAM NUT RECEPTACLE
NANOBAND PLATFORM, SOLDER CUP CONTACTS

SHELL STYLE 08
JAM NUT RECEPTACLE
PCB CONTACTS

240-806 Receptacle Dimensions

Shell Size	A Mating Thread	øB	øG Max	H Max	J Flat	K Thd x1.0-6g-0.100R
7	..4375-.067P-.2L-TS-2A	.365 (9.27)	.908 (23.06)	.848 (21.54)	.463 (11.76)	M13
8	.5000-.067P-.2L-TS-2A	.424 (10.77)	.980 (24.89)	.920 (23.37)	.536 (13.61)	M15
9	.5625-.067P-.2L-TS-2A	.464 (11.79)	1.040 (26.42)	.980 (24.89)	.587 (14.91)	M16
10	.6250-.067P-.2L-TS-2A	.584 (14.83)	1.110 (28.19)	1.050 (26.67)	.658 (16.71)	M18
11	.6875-.067P-.2L-TS-2A	.619 (15.72)	1.160 (29.46)	1.110 (28.19)	.709 (18.01)	M19
12	.7500-.067P-.2L-TS-2A	.699 (17.75)	1.230 (31.24)	1.170 (29.72)	.779 (19.79)	M21
14	.8750-.067P-.2L-TS-2A	.784 (19.91)	1.360 (34.54)	1.320 (33.53)	.900 (22.86)	M24
16	1.0000-.067P-.2L-TS-2A	.919 (23.34)	1.515 (38.48)	1.444 (36.68)	1.022 (25.96)	M27
18	1.1250-.067P-.2L-TS-2A	1.014 (25.76)	1.610 (40.89)	1.570 (39.88)	1.144 (29.06)	M30
20	1.2500-.067P-.2L-TS-2A	1.150 (29.21)	1.850 (46.99)	1.760 (44.70)	1.285 (32.64)	M34
22	1.3750-.067P-.2L-TS-2A	1.254 (31.85)	2.010 (51.05)	1.913 (48.59)	1.406 (35.71)	M37
24	1.5000-.067P-.2L-TS-2A	1.394 (35.41)	2.195 (55.75)	2.070 (52.58)	1.547 (39.29)	M41

240-806 Jam-nut D-Hole Dimensions




Shell Size	øA +.005/-0.00 (+0.13/-0.00)	B +.005/-0.00 (+0.13/-0.00)
7	.522 (13.26)	.224 (5.69)
8	.601 (15.27)	.256 (6.50)
9	.640 (16.26)	.287 (7.29)
10	.719 (18.26)	.318 (8.08)
11	.759 (19.28)	.350 (8.89)
12	.837 (21.26)	.381 (9.68)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)

Table 3 Filter Types

C
Single capacitor with low self inductance




Pi
Dual capacitors with a single inductive element positioned between




L-C
Single capacitor and an inductive element



C-L
Single capacitor and an inductive element





Features

- Ceramic planar filter array
- PC tail contacts
- High density #20HD and #22HD arrangements for reduced size and weight plus size #16, #12, #8 standard and hybrid layouts
- Aerospace-grade materials, construction

Specifications

- Operating temperature: -55°C to +125°C
- Dielectric withstanding voltage: 300 VDC
- Current rating
 - #20HD contacts: 5 A max.
 - #22HD contacts: 3 A max.
 - #16 contacts: contact factory
 - #12 contacts: contact factory
 - #8 contacts: contact factory
- Mating durability: 500 cycles

Connector Construction

- Shell, jam-nut: aluminum or stainless steel
- Contacts: copper alloy, gold plated
- Seals: fluorosilicone
- Insulator: high grade rigid dielectric

Table 2 Capacitance Class		
Class	Capacitance Range (pF)	
	Filter Type	
	P (Pi-Section)	C, L, M (C, L-C, C-L)
A	38,000 - 56,000	19,000 - 28,000
B	32,000 - 45,000	16,000 - 22,500
C	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300
J	70 - 120	35 - 60

Ceramic planar array C and Pi filters. Jam-nut panel mounting. PC tail with board mounting flange. 240-806-21 filtered receptacles save size and weight compared to legacy aerospace-grade EMI/RFI filter connectors. These high-performance connectors are suitable for areas subject to high vibration, altitude, and moisture as well as temperature ranges from -55°C to +125°C. Size 20HD and size 22HD contacts. Board mounting flange has threaded standoffs and orientation post.


How To Order							
SAMPLE PART NUMBER		240-806-21	ME	8-7	PP	P	C A
Product	240-806-21 = Filtered Receptacle, Board Mount						
Shell Material and Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated						
Arrangement Number (Shell Size - Insert Arr.)	See Table 1						
Contact Type	PP = Pin, PC Tail SP = Socket, PC Tail						
Filter Type (Table 3)	P = Pi Filter C = C Filter L = L - C Filter M = C - L Filter						
Capacitance Class (Table 2)	A B C D E F G J						
Polarizing Position	A B C D E F; (see reference section for polarizing table)						

Table I: Shell Size - Insert Arrangement																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					22-69		69				18-3					3
8-4	4					24-92		92				20-4					4
8-7	7					8-1			1			22-5					5
9-11	11					10-2			2			24-8					8
10-15	15					11-4			4			10-8A	6		2		
11-19	19					12-5			5			11-13	11		2		
12-26	26					14-7			7			12-27	26		1		
14-39	39					16-12			12			14-21	17		4		
16-60	60					18-15			15			16-41	37		4		
18-85	85					20-22			22			18-59	55		4		
20-110	110					22-24			24			11-14	13			1	
22-140	140					24-35			35			12-14	12			2	
24-186	186					9-1				1		14-22	20			2	
8-3		3				12-2				2		16-32	28			4	
9-5		5				14-3				3		16-42	40			2	
10-8		8				16-4				4		18-62	60			2	
11-10		10				16-7				7		14-20A	19				1
12-15		15				18-8				8		16-22	20				2
14-20		20				20-11				11		18-21	18				3
16-31		31				22-13				13		20-28	24				4
18-41		41				24-19				19		22-44	40				4
20-55		55				10-1					1	24-97	93				4
						16-2					2						

Series 806 Mil-Aero Connectors



240-806-21 Receptacles, Jam-nut, PC Tail, Threaded Standoff



240-806-21 Receptacle Dimensions

Shell Size	A Mating Thread	B	C Max	ØG Max	H Max	J Flat	K Thd x1.0-6g-0.100R
7	.4375-.067P-.2L-TS-2A	.489 (12.42)	.100 (2.54)	.908 (23.06)	.848 (21.54)	.463 (11.76)	M13
8	.5000-.067P-.2L-TS-2A	.534 (13.56)	.100 (2.54)	.980 (24.89)	.920 (23.37)	.536 (13.61)	M15
9	.5625-.067P-.2L-TS-2A	.579 (14.71)	.100 (2.54)	1.040 (26.42)	.980 (24.89)	.587 (14.91)	M16
10	.6250-.067P-.2L-TS-2A	.679 (17.25)	.100 (2.54)	1.110 (28.19)	1.050 (26.67)	.658 (16.71)	M18
11	.6875-.067P-.2L-TS-2A	.734 (18.64)	.100 (2.54)	1.160 (29.46)	1.110 (28.19)	.709 (18.01)	M19
12	.7500-.067P-.2L-TS-2A	.804 (20.42)	.100 (2.54)	1.230 (31.24)	1.170 (29.72)	.779 (19.79)	M21
14	.8750-.067P-.2L-TS-2A	.891 (22.63)	.100 (2.54)	1.360 (34.54)	1.320 (33.53)	.900 (22.86)	M24
16	1.0000-.067P-.2L-TS-2A	1.049 (26.64)	.100 (2.54)	1.515 (38.48)	1.444 (36.68)	1.022 (25.96)	M27
18	1.1250-.067P-.2L-TS-2A	1.148 (29.16)	.100 (2.54)	1.610 (40.89)	1.570 (39.88)	1.144 (29.06)	M30
20	1.2500-.067P-.2L-TS-2A	1.252 (31.80)	.128 (3.25)	1.850 (46.99)	1.760 (44.70)	1.285 (32.64)	M34
22	1.3750-.067P-.2L-TS-2A	1.369 (34.77)	.128 (3.25)	2.010 (51.05)	1.913 (48.59)	1.406 (35.71)	M37
24	1.5000-.067P-.2L-TS-2A	1.509 (38.33)	.128 (3.25)	2.195 (55.75)	2.070 (52.58)	1.547 (39.29)	M41

240-806-21 Jam-nut D-Hole Dimensions

Shell Size	ØA +.005/-0.00 (+0.13/-0.00)	B +.005/-0.00 (+0.13/-0.00)
7	.522 (13.26)	.224 (5.69)
8	.601 (15.27)	.256 (6.50)
9	.640 (16.26)	.287 (7.29)
10	.719 (18.26)	.318 (8.08)
11	.759 (19.28)	.350 (8.89)
12	.837 (21.26)	.381 (9.68)
14	.955 (24.26)	.443 (11.25)
16	1.073 (27.25)	.505 (12.83)
18	1.192 (30.28)	.568 (14.43)
20	1.349 (34.26)	.630 (16.00)
22	1.467 (37.26)	.693 (17.60)
24	1.624 (41.25)	.755 (19.18)




Table 3
Filter Types

C
Single capacitor with low self inductance



Pi
Dual capacitors with a single inductive element positioned between



L-C
Single capacitor and an inductive element




C-L
Single capacitor and an inductive element





HIGH-PERFORMANCE Contacts, Jumpers, and Pigtails for Series 806 Environmental Connectors



Glenair signature high-speed Octaxial El Ochito contact series may be specified as discrete contacts or factory-wired jumpers and pigtails

Glenair supplies a complete family of low-resistance, high-durability rear-release crimp contacts, jumpers, and pigtails for snap-in use in environmental versions of our Signature micro miniature Series 806 Mil-Aero. Our popular El Ochito octaxial contact family is available as discrete contacts or turnkey jumpers and pigtails Ethernet (up to 40GbE), SuperSpeed USB, SATA, HDMI, and other multi-gigabit data link protocols. We also supply and stock for immediate shipment all supported sizes of crimp signal contacts, power contacts, RF/Coaxial, differential Twinax, and Quadrax contacts. Environmental series 806 connectors may be specified with pin or socket contacts, or more commonly without included contacts for complete convenience in assembly of hybrid contact insert arrangements.

- **El Ochito® octaxial contacts, jumpers, and pigtail assemblies**
- **Standard crimp signal contacts in size #22HD, #20HD, #12, #16**
- **Crimp-removable size #8 power contacts**
- **50 and 75 ohm coax contacts**
- **High-frequency, spring-loaded microwave contacts**
- **Differential Twinax contacts for shielded twisted pair wiring**
- **Industry-standard Quadrax contacts**



See our Series 806 tool section for complete selection of crimp contact assembly tooling

Series 806 Mil-Aero Connectors

Contacts, Jumpers, and Pigtails Selection Guide

EL OCHITO SERIES AVAILABLE AS DISCRETE CONTACTS, SINGLE- AND DOUBLE-ENDED JUMPERS, AND COMMERCIAL CONNECTOR JUMPERS

El Ochito® White



1000BASE-T, 10GBASE-T, 40BASE-T

Up to 40 Gigabit Ethernet. El Ochito® "White" octaxial contacts provide an aerospace-grade solution for Ethernet signals up to 40GBASE-T.


El Ochito® Blue



SuperSpeed USB

90 ohms up to 5 Gbps. El Ochito® "Blue" octaxial contacts provide an aerospace-grade solution for SuperSpeed USB.


El Ochito® Red



HDMI, DisplayPort, SATA


100 ohms up to 10 Gbps per pair. El Ochito® "Red" octaxial contacts provide an aerospace-grade solution for multi-gigabit signals.

SIGNAL, POWER, COAX, RF, TWINAX, AND QUADRIX CONTACTS




850-094/-095

Size 22HD Crimp Contacts for #22–30 wire




809-442/-443

Size 22HD Crimp Contacts for #20–24 wire



809-204/-205

Size 20HD Crimp Contacts for #20–24 wire




809-110/-111

Size 16 Power Crimp Contacts for #16–20 wire




809-114/-115/-116/-117

Size 16 Coax Contacts for 50/75 Ohm Cable




809-112/-113

Size 12 Power Crimp Contacts for #12–14 wire



809-118/-119/-120/-121

Size 12 Coaxial Crimp Contacts for #12–14 wire




852-015/-016/-017/-018

Size 12 50 Ohm 3GHz Coax Contacts



852-103

Size 12 75 Ohm High-Frequency Coax Contacts




850-158/-159

Size 8 Crimp-Removable Power Contacts




850-148

Size 8 50 Ohm Matched-Impedance Coaxial RF Contacts




852-150/-151

Size 8 Coaxial RF 75 Ohm Matched-Impedance Contacts



853-075

Size 8 Differential Twinax Contacts



854-048

Size 8 Quadrix Contacts



850-144/-145


Size 22HD Thermocouple Contacts

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size 22HD Crimp Contacts for AWG #22 - 30 Wire



Military grade. Heavy gold plating. High-density size #22HD contacts accept #22 to #30 AWG wire. Compatible with Series 806 connectors with size 22HD contact cavities. Crimp termination. Contacts are bulk packaged.

Size 22HD Contacts for Series 806 Connectors

Contact Type	Wire Size AWG	Part Number	In.	mm.	Color Band
Pin	#22 – #28	850-094-1	.0335-.0355	0.851-0.902	(none)
Pin	#26 – #30	850-094-2	.0229-.0245	0.582-0.622	Blue
Socket	#22 – #28	850-095-1	.0335-.0355	0.851-0.902	(none)
Socket	#26 – #30	850-095-2	.0229-.0245	0.582-0.622	Blue

Specifications

- Operating temperature: -65°C to +200°C
- Current rating 5 A
- Crimp Tensile Strength:

Wire Size	Axial Load (lbs)
22	12
24	8
26	5
28	3
30	1.5

- Contact Resistance: silver-plated wire, 25°C (AS39029 Table 5)

Wire Size	Test Current Amperes	Max. mV Drop
22	5	73
24	3	45
26	2	52
28	1.5	54
30	1	60

- Meets performance requirements of SAE AS39029/121 and /122

Construction

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated


Termination Tools

Contact Part Number	Positioner	Crimp Tool
850-094-1	859-147	809-015
850-094-2	859-148	
850-095-1	809-005	
850-095-2	809-057	


Assembly Tools

- Insertion/Extraction Tool: 859-163


Size 22HD Socket Contact 850-095



Size 22HD Pin Contact 850-094




Wire Strip Length



RECOMMENDED WIRE STRIP LENGTH

Series 806 Mil-Aero Connectors

Size 22HD Crimp Contacts for AWG #20 - #24 Wire, Non-removable



Military grade. Heavy gold plating. High-density size #22HD contacts accept #20 AWG wire. Compatible with Series 806 connectors with size 22HD contact cavities. Crimp termination, non-removable. Contacts are bulk packaged.

Size 22HD for #20AWG Wire

Contact	Part Number
Pin	809-442
Socket	809-443

Specifications

- Maximum engagement force 8.0 oz. (MS33197-23Y1 Pin)
- Maximum separation force 0.5 oz (MS3197-23X1 pin)
- Current rating: 5 AMP max.
- Crimp tensile strength:

Wire Size	Axial Load (lbs)
20	20
22	12
24	8

- Contact millivolt drop: 70 millivolts max at 5 AMPs, 25°C

Construction

- Contact: copper alloy, 50 microinches gold over nickel underplating
- Socket hood: stainless steel, passivated


Termination Tools

Contact Part Number	Positioner	Crimp Tool
809-443	809-542	809-015
809-442		


Intended Use

- For use with Series 806 connectors
- Cannot be removed after installation
- Due to diameter of 20AWG wire, the arrangement may not be able to accept a full complement of 20AWG wire assemblies. It is recommended that 20AWG wire assemblies be utilized in alternate cavities.


Size 22HD Socket Contact 809-443




Size 22HD Pin Contact 809-442



Wire Strip Length






Military grade. Heavy gold plating. High-density size #20HD contacts accept #20 to #24 AWG wire. Compatible with Series 806 connectors with size 20HD contact cavities. Crimp termination. Bulk packaged.


Size 20HD Power Contacts

Contact Type	Wire Size AWG	Part Number	Crimp Tool	Positioner
Pin	#20 – #24	809-204	809-015 (M22520/2-01)	809-206
Socket	#20 – #24	809-205	809-015 (M22520/2-01)	809-206


Pin Contact 809-204



Socket Contact 809-205



Wire Strip Length



RECOMMENDED WIRE STRIP LENGTH

Specifications

- Operating temperature: -65°C to +200°C
- Wire accommodation: 20, 22, and 24
- Crimp Tensile Strength:

Wire Size	Axial Load lbs.
20	20
22	12
24	8

- Contact Resistance: silver-plated wire, 25°C (AS39029 Table 5)

Wire Size	Test Current Amperes	Max. mV Drop
20	7.5	55
22	5	73
24	3	45

- Meets performance requirements of SAE AS39029/121 and /122

Construction

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

Termination Tools


- Crimp Tool: 809-015 (M22520/2-01)
- Positioner: 809-206

Insertion/Extraction Tool

- Metal Tip Tool: 809-203
- Plastic Tip Tool: 809-203D

Series 806 Mil-Aero Connectors

Size 16 Power Crimp Contacts for AWG #16 to #20 Wire




Standard size #16 contacts accept #16 to #20 AWG wire. At rated test current of 13 amps, the maximum voltage drop is 49 millivolts. Contacts are gold-plated copper alloy. Socket contacts feature stainless steel hoods to protect against probe damage. Approved to SAE-AMS-39029. Contacts are bulk packaged. Terminate with M22520/1-01 crimper and M22520/1-04 positioner.

Size 16 HD Power Contacts

Contact Type	Wire Size	Part Number	Military Part Number	Color Band		
				1st	2nd	3rd
Pin	#16 – #20	809-110	AS39029/58-364	Orange	Blue	Yellow
Socket	#16 – #20	809-111	AS39029/57-358	Orange	Green	Gray

Pin Contact 809-110



Specifications

- Operating temperature: -65°C to +200°C
- Current rating: 13 A
- VAC: 2300
- Crimp Tensile Strength: silver tin-plated wire, (AS39029 Table X)

Wire Size	Axial Load lbs.	
	Init. Cond.	Therm. Cond.
16	50	45
20	20	14

- Contact Resistance: silver-plated wire, 25°C ±3, (AS39029 Table V)

Wire Size	Test Current Amperes	Max. mV Drop
16	13	49
20	7.5	55

- Meets performance requirements of SAE AS39029/58 and /57

Construction

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated


Termination Tools


- Hand Crimp Tool: 809-136 (M22520/1-01)
- Pin/Skt Positioner: 809-137 (M22520/1-04)

Insertion/Extraction Tool

- Tool: 809-131 (M81969/14-03)

Socket Contact 809-111





These #16 contacts accept 50 ohm and 75 ohm coaxial cable. Inner contact is rated at 1 amp, the outer contact 12 amps. DWV voltage rating is 800 VAC rms sea level, 250 VAC at 50,000 feet. Contacts are packaged individually and are unassembled with instruction sheet. One contact consists of outer contact, fluorocarbon dielectric, inner contact and shield crimp sleeve. Inner and outer contacts are gold-plated copper alloy. Approved to SAE AS39029. VSWR rating 1.5:1 maximum up to 700 MHz. 5000 megohm insulation resistance.

Size 16 Coax Contacts

Type	Cable Size	Part Number	Military Part Number	Color Band		
				1st	2nd	3rd
Pin	RG174, RG316, RG179	809-114	AS39029/76-424	Yellow	Red	Yellow
Pin	RG178	809-115	AS39029/76-425	Yellow	Red	Green
Socket	RG174, RG316, RG179	809-116	AS39029/78-432	Yellow	Orange	Red
Socket	RG178	809-117	AS39029/78-433	Yellow	Orange	Orange

Specifications

- Operating temperature: -65°C to +200°C
- Crimp Tensile Strength: silver tin-plated wire, (AS39029/76 & 78 Table 6)

Wire Size	Contact Tensile Load (lbs.)	
	Inner	Outer
RG174	15.0	15.0
RG316	10.0	15.0
RG179	3.5	15.0
RG178	3.5	10

- Low Signal Level Contact Resistance (inner contact only): AS39029/76 & 78 Table VI

Wire	Max. Contact Resist. (Mv)			
	Initial		After Cond. ¹	
	inner	Outer	Inner	Outer
RG174	55	85	66	102
RG316	55	75	66	90
RG179	120	70	144	84
RG178	120	110	144	132

1. After conditioning

- Meets performance requirements of SAE AS39029/76 and /78

Construction



- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

Termination Tools

- Inner Contact Crimp Tool: 809-015 (M22520/2-01)
- Inner Contact Positioner: 809-125 (M22520/2-35)
- Outer Contact Crimp Tool: 809-127 (M22520/4-01)
- Outer Contact Positioner: 809-126 (M22520/4-02)


Insertion/Extraction Tool

- Installation Tool: M81969//8-07
- Removal Tool: M81969//8-08

Pin Contact 809-114 and 115**Socket Contact 809-116 and 117**

Series 806 Mil-Aero Connectors

Size 12 Power Crimp Contacts for AWG #12 to #14 Wire




Standard size #12 contacts accept #12 to #14 AWG wire. At rated test current of 23 amps, the maximum voltage drop is 63 millivolts. Contacts are gold-plated copper alloy. Socket contacts feature stainless steel hoods to protect against probe damage. Approved to SAE AS39029. Contacts are bulk packaged. Terminate with M22520/1-01 crimper and M22520/1-04 positioner.


Size 12 Contacts

Contact Type	Wire Size	Part Number	Military Part Number	Color Band		
				1st	2nd	3rd
Pin	#12 – #14	809-112	AS39029/58-365	Orange	Blue	Green
Socket	#12 – #14	809-113	AS39029/57-359	Orange	Green	White

Pin Contact 809-112



Socket Contact 809-113



Specifications

- Operating temperature: -65°C to +200°C
- Current rating: 23 A
- Crimp Tensile Strength: silver tin-plated copper wire, (AS39029 Table X):

Wire Size	Axial Load lbs.	
	Init. Values	Therm. Values
16	50	45
20	20	14

- Contact Resistance: silver-plated wire, 25° ±3°, C (AS39029 Table V)

Wire Size	Test Current Amperes	Max. mV Drop
12	23	42
14	17	40

- Meets performance requirements of SAE AS39029/58 and /57

Construction

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

Termination Tools

- Crimp Tool: 809-136 (M22520/1-01)
- Positioner: 809-137 (M22520/1-04)

Insertion/Extraction Tool


- Pin and Socket Tool: 809-132 (M81969/14-04)

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size 12, 50 and 75 Ohm Coaxial Contacts



These #12 contacts accept 50 ohm and 75 ohm coaxial cable. Inner contact is rated at 1 amp, the outer contact 12 amps. DWV voltage rating is 1000 VAC rms sea level, 250 VAC at 50,000 feet. Contacts are packaged individually and shipped unassembled with instruction sheet. One contact consists of outer contact, fluorocarbon dielectric, inner contact and shield crimp sleeve. Inner and outer contacts are gold-plated copper alloy. Approved to SAE AS39029. VSWR rating 1.5:1 maximum up to 700 MHz. 5000 megohm insulation resistance.

Specifications

- Operating temperature: -65°C to +200°C
- Crimp Tensile Strength:
(AS39029/28 and 27 Table VII)

Wire Size	Tensile Load (lbs.)	
	Inner	Outer
RG174	15.0	15.0
RG316	10.0	15.0
RG179	3.5	15.0
RG180	3.5	20.0

- Contact Resistance at 25°C ±3°C in milliohms (AS39029/28 and 27 Table VII)

Wire	Max. Contact Resistance	
	Initial	After Cond. ¹
RG174	55	66
RG316	55	66
RG179	120	144
RG180	120	144

1. After conditioning
2. 85°C +3°, -0°

- Meets performance requirements of SAE AS39029/28 and /27

Construction

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

Termination Tools

- Inner Contact Crimp Tool:
809-015 (M22520/2-01)
- Inner Contact Positioner:
809-135 (M22520/2-34)
- Outer Contact Crimp Tool:
809-133 (M22520/31-01)
- Outer Contact Positioner:
809-134 (M22520/31-02)


Insertion/Extraction Tool

- Installation Tool: M81969/8-09
- Removal Tool: M81969/8-10


Size 12 Coaxial Contacts

Type	Cable Size	Part Number	Military Part Number	Color Band		
				1st	2nd	3rd
Pin	RG174, RG316, RG179	809-118	M39029/28-211	Red	Brown	Brown
Pin	RG180	809-119	M39029/28-409	Yellow	Black	White
Socket	RG174, RG316, RG179	809-120	M39029/27-210	Red	Brown	Black
Socket	RG180	809-121	M39029/27-402	Yellow	Black	Red

Pin Contact 809-118 and 809-119




Socket Contact 809-120 and 809-121



Series 806 Mil-Aero Connectors

Size 12, 50 ohm matched impedance 3 GHz Coax Contacts



These contacts offer improved frequency response compared to standard coaxial contacts. VSWR is 1.32:1 at 3GHz. Nominal impedance is 50 ohms. Insertion loss at 3GHz is 0.20 dB maximum. Inner contact is rated at 1 amp, the outer contact 12 amps. DWV voltage rating is 1000 VAC at sea level, 250 VAC at 50,000 feet. 5000 megohm insulation resistance. Contacts are packaged individually and shipped unassembled with instruction sheet. Inner and outer contacts are gold-plated copper alloy.

Specifications

- Operating temperature: -65°C to +200°C
- Crimp Tensile Strength:

Wire Size	Tensile Load (lbs.)	
	Inner	Outer
RG316	10.0	15.0
RG316DS	10.0	20.0
RG178	3.5	10.0
962-025-086	TBD	TBD

- Low Signal Level Contact Resistance: 25°C

Wire Size	Initial	After Cond.
RG316	55	66
RG316DS	55	66
RG178	120	144
962-025-086	TBD	TBD

Construction

- Copper alloy, 50 microinches gold over nickel plating
- Socket Hood: stainless steel, passivated

Size 12, 50 Ohm matched impedance 3 GHz Coax Contacts				
Contact Type	Cable Type	Part Number	Termination	Fig.
Pin	M17/113-RG316	852-016-01	Crimp	1
Pin	M17/152-00001(RG316DS)	852-016-02	Crimp	1
Pin	M17/93-RG178	852-016-03	Crimp	1
Pin	962-025-086	852-018	Solder	2
Socket	M17/113-RG316	852-015-01	Crimp	3
Socket	M17/152-00001(RG316DS)	852-015-02	Crimp	3
Socket	M17/93-RG178	852-015-03	Crimp	3
Socket	962-025-086	852-017	Solder	4




Figure 1




Figure 2




Figure 3




Figure 4

Contact Crimp and Removal Tools

Contact	Inner Contact		Outer Contact		Installation Tool	Removal Tool
	Crimp Tool	Positioner	Crimp Tool	Hex Die		
852-016-01, -02 852-015-01, -02	809-128	859-006	809-129 (M22520/5-01)	809-130 (M22520/5-03)	M81969 /8-07	M81969 /8-07
852-016-03 852-015-03	809-128	859-006	809-129 (M22520/5-01)	809-130 (M22520/5-03)	M81969 /8-07	M81969 /8-08

Series 806 Mil-Aero Connectors

Size 12, 75 Ohm High Frequency Matched-Impedance Coax Contacts



75 ohm coax contacts provide DC – 3 GHz frequency range. Crimp termination. Supplied as unassembled kit with contact body, center contact and outer ferrule. These snap-in, rear-release contacts fit Glenair Series 79 connectors. Gold-plated copper alloy, fluoroplastic insulator.

Size 12 75 Ohm High Frequency Matched-Impedance Coaxial Contacts

RG Cable	Pin Contact	Socket Contact
RG179 (M17/94-RG179)	852-103-02	852-104-02
V75268, V76261, V73263 (PIC™ Wire and Cable)	852-103-01	852-104-01


Specifications

- Operating temperature: -65 to +200°C
- Dielectric withstanding voltage: 500 VAC
- Insulation resistance: 5000 megohms min at 200 VDC
- Current rating: 1 ampere
- VSWR: 1.25:1 max. @ 3 GHz
- Impedance: 75 ohm
- Durability: 500 mating cycles
- Shock: EIA-364-27 condition D
- Vibration: EIA-364-28 condition VI, letter J


Construction

- Center contact, body, crimp sleeve: copper alloy, 50 microinches gold over nickel plating
- Insulator: fluoroplastic
- Hood: stainless steel, passivated

Socket Contact 852-104-01, -02



Pin Contact 852-103-01, -02



Crimp Tools, Installation/Removal Tool

Contact Part Number	Crimp Tools				Insertion/Removal Tool
	Inner Contact Crimper	Inner Contact Positioner	Shield Crimp Sleeve Crimper	Shield Crimp Sleeve Positioner	
852-103-01	809-128 (MH992)	859-006 (K1721)	809-133 (M22520/31-01)	859-128 (GP959)	809-132 (M81969/14-04)
852-103-02	809-128 (MH992)	859-006 (K1721)	809-129 (M22520/5-01)	809-130 (M22520/5-03)	809-132 (M81969/14-04)
852-104-01	809-128 (MH992)	859-006 (K1721)	809-133 (M22520/31-01)	859-128 (GP959)	809-132 (M81969/14-04)
852-104-02	809-128 (MH992)	859-006 (K1721)	809-129 (M22520/5-01)	809-130 (M22520/5-03)	809-132 (M81969/14-04)

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size 8 Crimp Removable Power Contacts



Military grade. Gold plating. size #8 contacts accept #8 AWG wire. Compatible with Series 806 connectors with size 8 contact cavities. Crimp termination. Bulk packaged.

#8 Power Contacts						
Contact Type	Wire Size AWG	Grommet Follower	Part Number	Crimp Tool	Die Assembly	Locator
Pin	#8	no	850-159	859-025 (M22520/23-01)	859-026 (M22520/23-02)	859-046 or 859-164 (recommended)
Pin	#8	yes	850-159F			
Socket	#8	no	850-158	859-025 (M22520/23-01)	809-026 (M22520/23-02)	
Socket	#8	yes	850-158F			

Specifications

- Operating temperature: -65°C to +200°C
- Current rating 46 A
- DWV:
- Accommodates size #8 AWG wire
- Meets performance requirements of SAE AS39029/45


Construction

- Copper alloy, 50 microinches gold over nickel plating


Termination Tools

- Crimp Tool: 859-025 (M22520/23-01)
- Die Assembly: 8569-026 (M22520/23-02)
- Locator: 859-046.
- Spring loaded locator recommended: 859-164

Pin Contact 850-159



Socket Contact 850-158





Coax Contacts. Compatible with Series 806 connectors with size 8 contact cavities. Crimp termination. 50 Ohm nominal impedance. DC - 6 GHz frequency range. Inner contact is solder type, shield termination is crimp type. Supplied as unassembled kit with contact body, center contact front and rear dielectric, retainer, clamp nut, crimp sleeve, sealing boot and instruction sheet. Contacts are snap-in, rear-release.

Table I: Part Number and Cable Accommodation

PART NUMBER		CABLES ACCOMMODATED	Max Freq.	"A" HEX
PIN	SOCKET			
852-149-01F	852-148-01F	M17/152-00001 (RG316DS)	6 GHz	0.128 (3.25)
852-149-02F	852-148-02F	M17/113-RG316	3 GHz	0.128 (3.25)
852-149-03F	852-148-03F	M17/060-RG142; M17/128-RG400		0.213 (5.41)
852-149-04F	852-148-04F	M17/28-RG58		0.213 (5.41)
852-149-05F	852-148-05F	LLSB-200; LMR-195	2.5 GHz	0.213 (5.41)

Grommet follower (F) optional; omit if not needed

Specifications

- Operating temperature: -65°C to +200°C
- Differential Impedance: 100 Ohms nominal
- Dielectric withstanding voltage: 500 VRMS
- Insulation resistance: 5000 megohms min at 200 VDC

Construction



- Contact Cady: Copper alloy / gold plated
- Inner Contact: Copper alloy / gold plated
- Crimp Ferrule: Brass or equivalent / gold plated
- Insulator: Teflon, Ultem Series 1000 or equivalent
- Grommet follower: see separate drawing

Termination Tools

- For Dash No. -1 thru -5:**
- For -01 and -02**
- Inner contact: solder
- Outer shield crimp tool: M22520/5-01
- Outer shield die sett: M22520/5-03
- For -03, 04, 05**
- Center contact: solder
- Outer contact crimp tool: M22520/5-01
- Outer contact Die-set: M22520/5-05

Assembly Instructions

- 852-148-01F: AI85164
- 852-149-01F: AI85165
- 852-148-02F: AI85171
- 852-149-02F: AI85171
- 852-148-03F: AI85172
- 852-149-03F: AI85172
- 852-148-04F: AI85173
- 852-149-04F: AI85173
- 852-148-05F: AI85166
- 852-149-05F: AI85166

Pin Contact 852-149**Socket Contact 852-148**

Series 806 Mil-Aero Connectors

Size 8 75 Ohm Matched-Impedance Coaxial RF Contacts



Pin Contact



Socket Contact

Size 8 coax contacts fit aerospace-grade digital video cable. 75 ohm nominal impedance. 0-4 GHz frequency range. Crimp termination. Supplied as unassembled kit with contact body, center contact, outer ferrule and sealing boot. These snap-in, rear-release contacts compatible with all Series 806 layouts with size 8 contact cavities. Gold-plated copper alloy, fluoroplastic insulators.

Size 8, 75 Ohm Matched-Impedance Coaxial Contacts

Cable	Pin Contact	Socket Contact	A Hex Crimp
V75268, V76261, V73263 (PIC™ Wire and Cable)	852-151-01F	852-150-01F	.218 (5.54)
RG179 (M17/94-RG179)	852-151-02F	852-150-02F	.128 (3.25)
V78209 (PIC™ Wire and Cable)	852-151-03F	852-150-03F	.231 (5.87)
LMR-240-75 (Times Microwave)	852-151-04F	852-150-04F	.231 (5.87)

Grommet follower (F) optional; omit if not needed

Specifications

- Operating temperature: -650C. to +2000C.
- Dielectric withstanding voltage: 500 VAC rms at sea level
- Current rating: 1 ampere
- VSWR: 1.25:1 max. @ 4 GHz
- 75 ohm nominal impedance
- Durability: 500 mating cycles
- Shock: EIA-364-27 condition D
- Vibration: EIA-364-28 condition VI, letter J

Construction

- Center contact, body, retainer, clamp nut, ferrule: copper alloy, 50 microinches gold over nickel plating
- Front and rear insulator: fluoropolymer
- Sealing boot: fluorosilicone rubber, glass-filled PEI


Termination Tools

- Inner contact crimp tool for -01 thru -04: 809-015 (M22520/2-01)
- Inner contact positioner for -01 thru -04: 809-240 (M22520/2-37)
- Outer contact crimp tool for -01 thru -04: 809-129 (M22520/5-01)
- Outer contact hex die P/N 859-047 (M22520/5-45) for contact P/N's: 852-151-01F, 852-150-01F, 852-151-03F, 852-151-04F, 852-150-03F, 852-150-04F
- Outer contact hex die P/N 809-130 (M22520/5-03) for contact P/N's: 852-151-02F, 852-150-02F


Removal Tool


- 859-049 (M81969/14-12) for contact part numbers 852-151 and 852-150

Pin Contact 852-151




Socket Contact 852-150





Pin Contact



Socket Contact

Specifications

- Operating temperature: -65°C to +200°C
- Differential Impedance: Designed to have the nominal impedance for cables listed in Table I
- Dielectric withstanding voltage:
Between inner contacts: 1000 VRMS
Between inner contacts and body: 500 VRMS
- Insulation resistance: 5000 megohms min at 200 VDC

Construction

- Contact Cody: Copper alloy / gold plated
- Inner Contact: Copper alloy / gold plated
- Crimp Ferrule: Brass or equivalent / gold plated
- Insulator: High grade rigid dielectric

Termination Tools



- Dash No. -1 thru -13:
Inner contact crimp tool: M22520/2-01
Inner contact positioner: M22520/2-37
Outer contact crimp tool: M22520/5-01
Outer contact die-set: M22520/5-45

Twinax Contacts. Shielded contacts protect against disruptive radio signals from unshielded sources including magnetic and electrostatic interference. Data rate exceeds 2 Gbps and provides DC – 3 GHz frequency range suitable for High-Speed applications such as Fibre Channel, Ethernet 100 Base-T, 1394b Firewire, and Gigabit Ethernet.

Part Number and Cable Accommodation

PART NUMBER		CABLES ACCOMMODATED	AWG	REF CABLE IMPEDANCE	ASSEMBLY INSTRUCTIONS
PIN	SOCKET				
853-076-01-F	853-075-01-F	GORE RCN 8945	24	100 OHMS	AI850007
853-076-02-F	853-075-02-F	GSC-03-83971-00	24	100 OHMS	AI850007
853-076-03-F	853-075-03-F	RAYCHEM 10612	24	77 OHMS	AI850007
853-076-04-F	853-075-04-F	RAYCHEM 0024A0024	24	100 OHMS	AI850007
853-076-04-F	853-075-04-F	TENSOLITE 24463/9P025X-2 (LD)S280W502-1	24	100 OHMS	AI850007
853-076-05-F	853-075-05-F	M17/176-00002	24	77 OHMS	AI850007
853-076-05-F	853-075-05-F	5M2022-003	24	75 OHMS	AI850007
853-076-06-F	853-075-06-F	BELDEN 1350SB	24	100 OHMS	AI85029
853-076-07-F	853-075-07-F	TE 2525B0524	24	125 OHMS	AI85050
853-076-08-F	853-075-08-F	CICOIL CLSPEC-1 OR EQUIV	28	100 OHMS	AI85079
853-076-09-F	853-075-09-F	GORE DXN2603 / TE 0028S2664	26/28	100 OHMS	AI85007
853-076-10-F	853-075-10-F	PIC E10222	22	100 OHMS	AI85138
853-076-11-F	853-075-11-F	963-102-30	30	100 OHMS	AI85142
853-076-12-F	853-075-12-F	GORE GSC-05-84308-00	26	100 OHMS	AI85143
853-076-13-F	853-075-13-F	GORE DXN2602	24	100 OHMS	AI85007

Grommet follower (F) optional; omit if not needed


Pin Contact 853-076**Socket Contact 853-075**

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors

Size 8 Quadrax Pin and Socket Contacts



Pin Contact




Socket Contact

Quadrax Contacts. Popular quadrax contacts are well suited for high speed solutions applications such as Gigabit Ethernet, IEEE 802.3Z, and IEEE 1394B FireWire-110 Ohm. Crimp termination.


Table I: Contact Part Numbers and Cables Accommodated

PART NUMBER		CABLES	REF CABLE	
PIN	SOCKET	ACCOMMODATED	OD	"A" HEX
854-047-01F	854-048-01F	TENSOLITE NF26Q100	.137 (3.48)	.218 (5.54)
854-047-02F	854-048-02F	TENSOLITE NF24Q100, PIC E51424	.163 (4.14)	.218 (5.54)
854-047-03F	854-048-03F	DRAKA FILECA F 4704-6	.153 (3.89)	.218 (5.54)
854-047-04F	854-048-04F	DRAKA FILECA F 4704-4	.175 (4.44)	.218 (5.54)
854-047-05F	854-048-05F	TENSOLITE NF22Q100	.190 (4.83)	.231 (5.87)

Pin Contact 854-047



Socket Contact 854-048



Specifications

- Operating temperature: -65°C to +200°C
- Differential Impedance: 100 Ohms nominal
- Dielectric withstanding voltage: 500 VRMS
- Insulation resistance: 5000 megohms min at 200 VDC

Construction

- Contact Cady: Copper alloy / gold plated
- Inner Contact: Copper alloy / gold plated
- Crimp Ferrule: Brass or equivalent / gold plated
- Insulator: Teflon, ultem series 1000 or equivalent
- Grommet follower: see separate drawing

Termination Tools

- Dash No. -1 thru -5:
Inner contact crimp tool: M22520/2-01
Inner contact positioner: M22520/2-37.
Outer contact crimp tool: M22520/5-01
Outer contact hex die: M22520/5-45

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size 22HD Thermocouple Pin and Socket Contacts



Thermocouple Contacts. Size 22 high density thermocouple contacts for use in harsh environment, temperature measuring applications. Contacts are crimp termination type.


Table I: Contact Part Numbers, Material Type and Color Band

PART NUMBER			COLOR BAND	
PIN	SOCKET	MATERIAL TYPE	1ST BAND	2ND BAND
850-144-1A	850-145-1A	IAW ASTM-E230, TYPE K (-)	RED	NONE
850-144-1C	850-145-1C	IAW ASTM-E230, TYPE K (+)	YELLOW	NONE
850-144-2A	850-145-2A	IAW ASTM-E230, TYPE K (-)	RED	BLUE
850-144-2C	850-145-2C	IAW ASTM-E230, TYPE K (+)	NONE	BLUE

Table I: Wire Accomodation Diameter

PART NUMBER		A DIA
PIN	SOCKET	
850-144-1A	850-145-1A	.0335 (0.851) - .0355 (0.902)
850-144-1C	850-145-1C	
850-144-2A	850-145-2A	.0229 (0.582) - .0245 (0.622)
850-144-2C	850-145-2C	

Pin Contact 850-144




Termination Tools

850-145:


- Crimp Tool: 809-015 (M22250/2-01)
- Positioner for 850-145-1: 809-005
- Positioner for 850-145-2: 809-057
- Insertion/Extraction Tool: 809-088

850-144:

- Crimp Tool: 809-015 (M22250/2-01)
- Positioner for 850-144-1: 859-147
- Positioner for 850-144-2: 859-148
- Insertion/Extraction Tool: 809-088




Socket Contact 850-145



Series 806 Mil-Aero Connectors

600-280 El Ochito® contact termination/installation kit


Assembly Tools										
Contact PN	Inner Contact Crimp		Cable Shield Hex Crimp		Cable Shield Round Crimp			Key Alignment Tool	Rear Ferrule Insertion Tool	Mating Tool
	Tool	Positioner	Tool	Hex Die	Tool	Positioner 1	Positioner 2			
858-045	809-015	809-101	809-129	859-007				600-274	600-274	600-267
858-046	809-015	809-101	809-129	859-007				600-235	600-274	600-264
858-047-01	809-015	809-101	809-129	859-007				600-274	600-274	600-267
858-047-02	809-015	809-101			809-134	859-184-2	859-184-3	600-274	600-274	600-267
858-048-01	809-015	809-101	809-129	859-007				600-235	600-274	600-264
858-048-02	809-015	809-101			809-134	859-184-2	859-184-3	600-235	600-274	600-264
858-049	809-015	809-101	809-129	859-007				600-274	600-274	600-267
858-050	809-015	809-101	809-129	859-007				600-235	600-274	600-267
858-051	809-015	809-101						600-274	600-274	600-264
858-052	809-015	809-101						600-235	600-274	600-267
858-067	809-015	809-101						600-274	600-274	600-264
858-068	809-015	809-101						600-235	600-274	600-267
858-073	809-015	809-101						600-274	600-274	600-264
858-074	809-015	809-101						600-235	600-274	600-267

Inner Contact Crimp Tools		Cable Shield Crimp Tools				Removal Tool
		Hex Crimp	Round Crimp			
						
809-015 (M22520/2-01)	859-101 (K1906)	809-129 (M22520/5-01)	859-007 (M22520/5-45)	859-134 (GS206)	859-184 (M22520/31-02)	859-049 (M81969/14-12)

Key Alignment Tools		Rear Ferrule Insertion Tool
		
600-235 600-243 Socket contact	600-236 600-244 Pin contact	600-242

Contact factory for available alignment inspection tools for use with existing assemblies.

Sealing Boot
An "F" suffix in the contact part number indicates the contact is supplied with a sealing boot. To order these contacts without sealing boots, delete the "F" suffix from the part number. Sealing boots are not supplied with 858-005, 858-006, 858-009, 858-010, 858-035, 858-037, 858-038 and 858-039 contacts.



687-754-8-8
FOR .220 (5.56) DIAMETER CABLES
687-754-8-9
FOR .236 (5.99) DIAMETER CABLES
687-754-8-4
FOR .177 (4.50) DIAMETER CABLES



600-280 tool kit combines all the tools necessary to terminate El Ochito red, blue, and white contacts. Great for customers looking to terminate el Ochito® contacts to cables. Unit includes portable protective case with cutout foam for ease of transportation. Order by kit level for simplified ordering. Customize tool kit contents to meet your specific requirements. Additional foam cutout cavities allow for easy to upgrade your kit as you increase your el Ochito tool collection.

Part Number Development			
Sample Part Number	600-280	-06	
Product	600-280 = El Ochito Installation Tool Kit		
Kit Number	-03 = Basic Assembly -06 = Basic Assembly + Crimp Dies, and Positioners -09 = Basic Assembly+ Crimp Dies, Positioners and Crimp Tools		
Modifier	Omit = None H = Hex Crimp Only (See Table I)		

Kit 03: Basic Kit	
-03	
Tool Description	P/N
Socket Ochito Alignment Tool	600-235
Pin El Ochito Alignment Tool	600-274
Ferrule Inserter	600-242

Table I: Items Removed By Modifier "H"

Tool Description	P/N
859-134 (GS206) Positioner 1	859-184-1
859-134 (GS206) Positioner 2	859-184-2
859-134 (GS206) Positioner 3	859-184-3
Circle Body Crimper (GS206)	859-134

Notes


Modifier "H" Removes all tools and dies associated with the circle body crimp. See Table II.
Not applicable to "-01".

Kit -06: Basic Kit + Crimp Dies & Positioners	
-06	
Tool Description	P/N
Socket El Ochito Alignment Tool	600-235
Pin El Ochito Alignment Tool	600-274
Ferrule Inserter	600-242
Contact Positioner (K1906)	859-101
Body Hex Crimp Die (M22520/5-45)	859-007
859-134 (GS206) Positioner 1	859-184-1
859-134 (GS206) Positioner 2	859-184-2
859-134 (GS206) Positioner 3	859-184-3
Removal Tool (M81969/14-12)	859-049

Kit -09: Basic Kit + Crimp Dies & Positioners, and Crimp Tools	
-09	
Tool Description	P/N
Socket El Ochito Alignment Tool	600-235
Pin El Ochito Alignment Tool	600-274
Ferrule Inserter	600-242
Contact Positioner (K1906)	859-101
Body Hex Crimp Die (M22520/5-45)	859-007
859-134 (GS206) Positioner 1	859-184-1
859-134 (GS206) Positioner 2	859-184-2
859-134 (GS206) Positioner 3	859-184-3
Removal Tool (M81969/14-12)	859-049
Contact Crimper (M22520/2-01)	809-015
Hex Body Crimper (M22520/5-01)	809-129
Circle Body Crimper (GS206)	859-134

Series 806 Mil-Aero Connectors


El Ochito® Heat Shrink Boots and Sealing Boots



Specifications

- 770-074 non-lipped, zero halogen heat shrink boot without eyelet. Shrink boot is adhesive lined for use with Type 2 El Ochito contacts. Provides environmental sealing and strain relief support. Pre-coated with W1 zero halogen/hot melt adhesive rated for use up to 125°C. Is be used in place of a grommet follower for the type 2.


How To Order					
SAMPLE PART NUMBER		770-074	S	1	01 W1
Product	770-074 = Non-Lipped Boot Without Eyelet				
Angular Function	S = Straight				
Material	Glenair high performance elastomer				
Boot Size	See Shrink Boot Dimensions table				
Adesive	W1 = 125° C Zero Halogen/Hot Melt				



770-074 Shrink Boot Dimensions									
Boot Size	Ae Dia Min	Ce Dia Min	Ar Dia Max	at ±30%	Cr Dia Max	ct ±20%	C0 Ref	P0 ±10%	R0 Ref
-01	.354 (8.99)	.354 (8.99)	.265 (6.73)	.023 (0.58)	.080 (2.03)	.023 (0.58)	.354 (8.99)	1.015 (25.78)	.401 (10.19)

Grommet Follower

- An "F" suffix in the contact part number indicates the contact is supplied with a grommet follower. To order these contacts without grommet follower, delete the "F" suffix from the part number. Grommet followers are not available for Type II Ochito contacts.



687-754-8-4

FOR .177 (4.5) DIAMETER CABLES

687-754-8-8

FOR .220 (5.56) DIAMETER CABLES

687-754-8-9

FOR .236 (6.0) DIAMETER CABLES

BAYONET-COUPLING MICRO MINIATURE CIRCULAR

Series 806 Mil-Aero Connectors



806B-012 Plug



MATERIAL/FINISH

- Plug Barrel, Coupling Nut - Al Alloy Or CRES
- Insulators - High Grade Rigid Dielectirc.
- Interfacial Seal, Grommet - Fluorosilicone Blend
- Contact - Copper Alloy / Gold Plated
- Ground Spring - Beryllium Copper / Nickel Plated (Silver Plated For ZR Finish)

NOTES

- Assembly to be identified with Glenair's name, part number and date code, space permitting.
- Blue Color Band Indicates Rear Release Retention System.
- See Series 80 catalog for contact termination tools.
- Insert arrangement shown for reference only, see 806-015 for additional contact arrangements.
- This plug connector mates with all bayonet-style receptacle, Glenair 806B style, connectors with same polarization and opposite contact gender.
- Connectors supplied with standard crimp contacts, for coax or other special consult factory for option. Connector can be ordered less contacts and contacts ordered separately.
- This connector meets all performance requirements of Glenair product spec 806-014.
- Terminate shield with Glenair BandMaster ATS® Tool 601-108 and Glenair Nano Band. Groove for use with overmolded strain relief or 809-060 heat shrink boots.
- Please consult Glenair for shell sizes 16 and up

HOW TO ORDER						
Sample Part Number	806B-012	-ME	11-19	S	M	A
Basic Part Number	806B-012 Plug					
Material and Finish	-NF = Aluminum Alloy, O.D. Cadmium over Electroless Nickel -MT = Aluminum Alloy, Nickel-PTFE -ME = Aluminum Alloy, Electroless Nickel -ZR = Aluminum Alloy, Black Zinc-Nickel -Z1 = Stainless Steel, Passivate -ZL = Stainless Steel, Electro-Deposited Nickel					
Insert Arrangement	See Table I. Consult Glenair for shell sizes 16 and up.					
Contact Type	A = Pin Connector, Less Contacts B = Socket Connector, Less Contacts P = Pin S = Socket					
Shell Style	M = Metric (Accessory Thread) B = Band (Platform for Attaching Cable Shield)					
Key Position	See Dimensions Table					

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					24-92		92				20-4					4
8-4	4					8-1			1			22-5					5
8-7	7					10-2			2			24-8					8
9-11	11					11-4			4			10-8A	6		2		
10-15	15					12-5			5			11-13	11		2		
11-19	19					14-7			7			12-27	26		1		
12-26	26					16-12			12			14-21	17		4		
14-39	39					18-15			15			16-41	37		4		
16-60	60					20-22			22			18-59	55		4		
18-85	85					22-24			24			11-14	13			1	
20-110	110					24-35			35			12-14	12			2	
22-140	140					9-1				1		14-22	20			2	
24-186	186					12-2				2		16-32	28			4	
8-3		3				14-3				3		16-42	40			2	
9-5		5				16-4				4		18-62	60			2	
10-8		8				16-7				7		14-20A	19				1
11-10		10				18-8				8		16-22	20				2
12-15		15				20-11				11		18-21	18				3
14-20		20				22-13				13		20-28	24				4
16-31		31				24-19				19		22-44	40				4
18-41		41				10-1					1	24-97	93				4
20-55		55				16-2					2						
22-69		69				18-3					3						

SERIES 806 BAYONET





Diagram illustrating the master key position and angles for a cylinder lock. The diagram shows a cross-section of the cylinder with the master key inserted. The master key is labeled "MASTER KEY". The angle between the master key position and the cylinder's vertical axis is labeled W° (MASTER KEY POSITION). The angle between the master key position and the cylinder's horizontal axis is labeled F° . The angle between the master key position and the cylinder's vertical axis is labeled Z° . The angle between the master key position and the cylinder's horizontal axis is labeled X° . The angle between the master key position and the cylinder's vertical axis is labeled Y° .

6

BAYONET-COUPLING MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806B-013 Square-Flange Receptacle



MATERIAL/FINISH

- Shell - Al Alloy or CRES
- Insulators - High Grade Rigid Dielectirc.
- Interfacial Seal, Grommet - Fluorosilicone Blend
- Contact - Copper Alloy / Gold Plated

NOTES

- Assembly to be identified with Glenair's name, part number and date code, space permitting.
- Blue color bayonet heads indicate rear release retention system.
- See Series 80 catalog for contact termination tools.
- Insert arrangement shown for reference only, see 806-015 for additional contact arrangements.
- This receptacle connector mates with all bayonet-style coupling, Glenair 806B style, plug connectors with same polarization and opposite contact gender.
- Plug connectors with same polarization and opposite contact gender. Contacts, consult factory for option. Connector can be ordered less contacts (contacts syle a or b) and contacts ordered separately.
- This connector meets all performance requirements of Glenair product spec 806-014.
- Terminate shield with Glenair BandMaster ATS® Tool 601-108 and Glenair Nano Band.
- Groove for use with overmolded strain relief or 809-060 heat shrink boots.
- Please consult Glenair for shell sizes 16 and up

HOW TO ORDER							
Sample Part Number	806B-013	-ME	11-19	S	M	T	A
Basic Part Number	806B-013 Square-Flange Receptacle						
Material and Finish	-NF = Aluminum Alloy, O.D. Cadmium over Electroless Nickel -MT = Aluminum Alloy, Nickel-PTFE -ME = Aluminum Alloy, Electroless Nickel -ZR = Aluminum Alloy, Black Zinc-Nickel -Z1 = Stainless Steel, Passivate -ZL = Stainless Steel, Electro-Deposited Nickel						
Insert Arrangement	See Table I. Consult Glenair for shell sizes 16 and up.						
Contact Type	A = Pin Connector, Less Contacts B = Socket Connector, Less Contacts P = Pin S = Socket						
Shell Style	M = Metric (Accessory Thread) B = Band (Platform for Attaching Cable Shield)						
Panel Mounting Hole Style	T = Thru hole C = Clinch Nut (Consult factory for SST with clinch nuts)						
Key Position	See Dimensions Table						

TABLE I: SHELL SIZE - INSERT ARRANGEMENT																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					24-92		92				20-4					
8-4	4					8-1			1			22-5					5
8-7	7					10-2			2			24-8					8
9-11	11					11-4			4			10-8A	6		2		
10-15	15					12-5			5			11-13	11		2		
11-19	19					14-7			7			12-27	26		1		
12-26	26					16-12			12			14-21	17		4		
14-39	39					18-15			15			16-41	37		4		
16-60	60					20-22			22			18-59	55		4		
18-85	85					22-24			24			11-14	13			1	
20-110	110					24-35			35			12-14	12			2	
22-140	140					9-1				1		14-22	20			2	
24-186	186					12-2				2		16-32	28			4	
8-3		3				14-3				3		16-42	40			2	
9-5		5				16-4				4		18-62	60			2	
10-8		8				16-7				7		14-20A	19				1
11-10		10				18-8				8		16-22	20				2
12-15		15				20-11				11		18-21	18				3
14-20		20				22-13				13		20-28	24				4
16-31		31				24-19				19		22-44	40				4
18-41		41				10-1					1	24-97	93				4
20-55		55				16-2					2						
22-69		69				18-3					3						

BAYONET-COUPLING MICRO MINIATURE CIRCULAR
Series 806 Mil-Aero Connectors



806B-013 Square-Flange Receptacle

SERIES 806 BAYONET

DIMENSIONS

The diagram illustrates the dimensions of the 806B-013 Square-Flange Receptacle. It includes three views: a front view showing the flange with mounting holes and keyways, a side view showing the profile with the master key and accessory teeth, and a detail view of the master key. Key dimensions are labeled in inches and millimeters. The front view shows the master keyway position (W°), master key (ØE), flange thickness (F°), and mounting hole positions (X°, Y°, Z°). The side view shows the master key (1.175 (29.85) MAX), master keyway position (.587 (14.91)), master keyway thickness (.150 (3.81) MAX), master key (F MAX), master key (B THREAD), master key (ACCESSORY TEETH), master key (A), master key (2X C), master key (ØD), master key (ØH), master key (.19 (4.83)), master key (.065 (1.65)).

METRIC ACCESSORY THREAD

BAND PLATFORM

Shell Size	A Max	B Thread	C	Ø D	Ø E Thru Hole	F Max	Ø G Max	Ø H	Master Keyway Codes (W°)					Minor Keyway Positions			
									N	A	B	C	D	F°	X°	Y°	Z°
7	0.780 (19.81)	M8 X 1-6g-.100R	0.513 (13.03)	0.390 (9.91)	0.128 (3.25)	0.100 (2.54)	0.993 (25.22)	0.265 (6.73)	104°					14°	45°	85°	38°
8	0.856 (21.74)	M10 X 1-6g-.100R	0.594 (15.09)	0.485 (12.32)			1.101 (27.97)	0.327 (8.31)									
9	0.895 (22.73)	M12 X 1-6g-.100R	0.625 (15.88)	0.563 (14.30)			1.144 (29.06)	0.406 (10.31)									
10	0.979 (24.87)	M14 X 1-6g-.100R	0.719 (18.26)	0.612 (15.54)			1.277 (32.44)	0.484 (12.29)									
11	1.035 (26.29)	M15 X 1-6g-.100R	0.765 (19.43)	0.695 (17.65)			1.342 (34.09)	0.524 (13.31)									
12	1.072 (27.23)	M17 X 1-6g-.100R	0.812 (20.62)	0.720 (18.29)			1.410 (35.81)	0.603 (15.32)									
14	1.166 (29.62)	M19 X 1-6g-.100R	0.906 (23.01)	0.845 (21.46)			1.542 (39.17)	0.681 (17.30)	95°	75°	63°	127°	115°	5°	45°	88°	27°
16	1.234 (31.34)	M22 X 1-6g-.100R	0.969 (24.61)	0.966 (24.54)			1.632 (41.45)	0.782 (19.86)									
18	1.328 (33.73)	M25 X 1-6g-.100R	1.062 (26.97)	1.086 (27.58)			1.778 (45.16)	0.899 (22.83)									
20	1.453 (36.91)	M28 X 1-6g-.100R	1.156 (29.36)	1.211 (30.76)			1.910 (48.51)	1.043 (26.49)									
22	1.578 (40.08)	M31 X 1-6g-.100R	1.250 (31.75)	1.325 (33.66)	0.154 (3.91)	0.125 (3.18)	2.083 (52.91)	1.155 (29.34)	95°	80°	69°	121°	110°	5°	45°	88°	27°
24	1.703 (43.26)	M34 X 1-6g-.100R	1.375 (34.93)	1.462 (37.13)			2.248 (57.10)	1.273 (32.33)									

MOUNT INFO						
PANEL MOUNT INFO		Size	J Min. Rear Panel Mnt	J Min. Front Panel Mnt	K	
					With Clinch Nut	Without Clinch Nut
		7	0.465 (11.81)	0.349 (8.86)	0.128 (3.25)	0.128 (3.25)
		8	0.557 (14.15)	0.411 (10.44)		
		9	0.634 (16.10)	0.490 (12.45)		
		10	0.682 (17.32)	0.568 (14.43)		
		11	0.774 (19.66)	0.618 (15.70)		
		12	0.799 (20.29)	0.697 (17.70)		
		14	0.923 (23.44)	0.775 (19.69)		
		16	1.043 (26.49)	0.876 (22.25)		
		18	1.193 (30.30)	0.993 (25.22)		
		20	1.317 (33.45)	1.137 (28.88)		
		22	1.431 (36.35)	1.249 (31.72)	0.154 (3.91)	0.154 (3.91)
		24	1.567 (39.80)	1.367 (34.72)		

BAYONET-COUPLING MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806B-019 In-Line Receptacle

SERIES 806 BAYONET

MATERIAL/FINISH

- Shell - Al Alloy or CRES
- Insulators - High Grade Rigid Dielectric.
- Interfacial Seal, Grommet - Fluorosilicone / Blend
- Contact - Copper Alloy / Gold Plate Per Mil-G-45204, Type II, Grade C, Class 5 (.000050 INCH) over a minimum of .000050 Inch nickel plating.

NOTES

- Assembly to be identified with Glenair's name, part number and date code, space permitting.
- Blue color bayonet heads indicate rear release retention system.
- See Series 80 catalog for contact termination tools.
- This receptacle connector mates with all bayonet-style coupling, Glenair 806B style, plug connectors with same polarization and opposite contact gender.
- Connectors supplied with standard crimp contacts, for coax or other special contacts, consult factory for option. Connector can be ordered less contacts (contacts style a or b) and contacts ordered separately.
- This connector meets all performance requirements of Glenair product spec 806-014.
- Terminate shield with Glenair BandMaster ATS® Tool 601-108 and Glenair Nano Band.
- Groove for use with overmolded strain relief or 809-060 heat shrink boots.
- Please consult Glenair for shell sizes 16 and up

HOW TO ORDER						
Sample Part Number	806B-019	-ME	11-19	S	M	A
Basic Part Number	806B-019 In-Line Receptacle					
Material and Finish	-NF = Aluminum Alloy, O.D. Cadmium over Electroless Nickel -MT = Aluminum Alloy, Nickel-PTFE -ME = Aluminum Alloy, Electroless Nickel -ZR = Aluminum Alloy, Black Zinc-Nickel -Z1 = Stainless Steel, Passivate -ZL = Stainless Steel, Electro-Deposited Nickel					
Insert Arrangement	See Table I. Consult Glenair for shell sizes 16 and up.					
Contact Type	A = Pin Connector, Less Contacts B = Socket Connector, Less Contacts P = Pin S = Socket					
Shell Style	M = Metric (Accessory Thread) B = Band (Platform for Attaching Cable Shield)					
Key Position	See Dimensions Table					

Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					24-92		92				20-4					4
8-4	4					8-1			1			22-5					5
8-7	7					10-2			2			24-8					8
9-11	11					11-4			4			10-8A	6		2		
10-15	15					12-5			5			11-13	11		2		
11-19	19					14-7			7			12-27	26		1		
12-26	26					16-12			12			14-21	17		4		
14-39	39					18-15			15			16-41	37		4		
16-60	60					20-22			22			18-59	55		4		
18-85	85					22-24			24			11-14	13			1	
20-110	110					24-35			35			12-14	12			2	
22-140	140					9-1				1		14-22	20			2	
24-186	186					12-2				2		16-32	28			4	
8-3		3				14-3				3		16-42	40			2	
9-5		5				16-4				4		18-62	60			2	
10-8		8				16-7				7		14-20A	19				1
11-10		10				18-8				8		16-22	20				2
12-15		15				20-11				11		18-21	18				3
14-20		20				22-13				13		20-28	24				4
16-31		31				24-19				19		22-44	40				4
18-41		41				10-1					1	24-97	93				4
20-55		55				16-2					2						
22-69		69				18-3					3						

BAYONET-COUPLING MICRO MINIATURE CIRCULAR
Series 806 Mil-Aero Connectors



806B-019 In-Line Receptacle

SERIES 806 BAYONET

DIMENSIONS

METRIC ACCESSORY THREAD

BAYONET-COUPLING MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806B-020 Jam-Nut Receptacle

SERIES 806 BAYONET

MATERIAL/FINISH

- Shell, Jam Nut - Al Alloy or CRES
- Insulators - High Grade Rigid Dielectirc.
- Interfacial Seal, Grommet, O-Rings - Fluorosilicone Blend
- Contact - Copper Alloy / Gold Plate

NOTES

- Assembly to be identified with Glenair's name, part number and date code, space permitting.
- Blue color band indicates rear release retention system.
- See Series 80 catalog for contact termination tools.
- Insert arrangement shown for reference only, see 806-015 for additional contact arrangements.
- This receptacle connector mates with all bayonet-coupling, Glenair 806B style, plug connectors with same polarization and opposite contact gender.
- Connectors supplied with standard crimp contacts; for coax or other special contacts, consult factory for option. Connector can be ordered less contacts (contacts style A or B) and contacts ordered separately.
- This connector meets all performance requirements of Glenair product spec 806-014.
- Terminate shield with Glenair BandMaster ATS® tool 601-108 and Glenair Nano Band. Groove for use with overmolded strain relief or 809-060 heat shrink boots.
- Please consult Glenair for shell sizes 16 and up

HOW TO ORDER						
Sample Part Number	806B-020	-ME	11-19	S	M	A
Basic Part Number	806B-020 Jam-Nut Receptacle					
Material and Finish	-NF = Aluminum Alloy, O.D. Cadmium over Electroless Nickel -MT = Aluminum Alloy, Nickel-PTFE -ME = Aluminum Alloy, Electroless Nickel -ZR = Aluminum Alloy, Black Zinc-Nickel -Z1 = Stainless Steel, Passivate -ZL = Stainless Steel, Electro-Deposited Nickel					
Insert Arrangement	See Table I. Consult Glenair for shell sizes 16 and up.					
Contact Type	A = Pin Connector, Less Contacts B = Socket Connector, Less Contacts P = Pin S = Socket					
Shell Style	M = Metric (Accessory Thread) B = Band (Platform for Attaching Cable Shield)					
Key Position	See Dimensions Table					


TABLE I: SHELL SIZE - INSERT ARRANGEMENT																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					24-92		92				20-4					4
8-4	4					8-1			1			22-5					5
8-7	7					10-2			2			24-8					8
9-11	11					11-4			4			10-8A	6		2		
10-15	15					12-5			5			11-13	11		2		
11-19	19					14-7			7			12-27	26		1		
12-26	26					16-12			12			14-21	17		4		
14-39	39					18-15			15			16-41	37		4		
16-60	60					20-22			22			18-59	55		4		
18-85	85					22-24			24			11-14	13			1	
20-110	110					24-35			35			12-14	12			2	
22-140	140					9-1				1		14-22	20			2	
24-186	186					12-2				2		16-32	28			4	
8-3		3				14-3				3		16-42	40			2	
9-5		5				16-4				4		18-62	60			2	
10-8		8				16-7				7		14-20A	19				1
11-10		10				18-8				8		16-22	20				2
12-15		15				20-11				11		18-21	18				3
14-20		20				22-13				13		20-28	24				4
16-31		31				24-19				19		22-44	40				4
18-41		41				10-1					1	24-97	93				4
20-55		55				16-2					2						
22-69		69				18-3					3						

BAYONET-COUPLING MICRO MINIATURE CIRCULAR
Series 806 Mil-Aero Connectors



806B-020 Jam-Nut Receptacle

SERIES 806 BAYONET



RECOMMENDED MOUNTING HOLE			
RECOMMENDED MOUNTING HOLE DIMENSIONS	Shell Size	K +.008 -.000	J +.008 -.000
	7	0.478 (12.14)	0.510 (12.95)
	8	0.553 (14.05)	0.572 (14.53)
	9	0.623 (15.82)	0.635 (16.13)
	10	0.683 (17.35)	0.697 (17.70)
	11	0.788 (20.02)	0.822 (20.88)
	12	0.820 (20.83)	0.885 (22.48)
	14	0.945 (24.00)	1.010 (25.65)
	16	1.075 (27.31)	1.135 (28.83)
	18	1.200 (30.48)	1.260 (32.00)
	20	1.325 (33.66)	1.385 (35.18)
	22	1.450 (36.83)	1.510 (38.35)
	24	1.575 (40.01)	1.635 (41.53)

BAYONET-COUPLING MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806B-021 Jam-Nut Receptacle with PCB standoff

SERIES 806 BAYONET

HOW TO ORDER						
Sample Part Number	806B-021	-ME	11-19	S	1	A
Basic Part Number	806B-021 Jam-Nut Receptacle with PCB standoff					
Material and Finish	-NF = Aluminum Alloy, O.D. Cadmium over Electroless Nickel -MT = Aluminum Alloy, Nickel-PTFE -ME = Aluminum Alloy, Electroless Nickel -ZR = Aluminum Alloy, Black Zinc-Nickel -Z1 = Stainless Steel, Passivate -ZL = Stainless Steel, Electro-Deposited Nickel					
Insert Arrangement	See Table I. Consult Glenair for shell sizes 16 and up.					
Contact Type	P = Pin S = Socket E = Solder Cup, Pin F = Solder Cup, Skt					
PC Tail Length	1 = .125" 2 = .250"					
Key Position	See Dimensions Table					

MATERIAL/FINISH

- Shell, Jam Nut - Al Alloy Or Cres / See Material and Finish Table
- Insulators - High Grade Rigid Dielectirc.
- Interfacial & Peripheral Seal, Flang O-Ring - Fluorosilicone Blend
Contact - Copper Alloy / Gold Plated

NOTES

- Assembly to be identified with Glenair's name, part number and date code, space permitting.
- See 806-023 for printed circuit board layouts.
- Insert arrangement shown for reference only, see 806-015 for additional contact arrangements.
- This receptacle connector mates with all bayonet-coupling, Glenair 806B style, plug connectors with same polarization and opposite contact gender.
- This connector meets all performance requirements of Glenair product spec 806-014.
- Backfill with epoxy. Consult manufacturer for hermetically sealed versions.
- Integral PCB stand off 4x 4-40 UNC .156 Min. thread and locating post.
- Please consult Glenair for shell sizes 16 and up


TABLE I: SHELL SIZE - INSERT ARRANGEMENT																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					24-92		92				20-4					4
8-4	4					8-1			1			22-5					5
8-7	7					10-2			2			24-8					8
9-11	11					11-4			4			10-8A	6		2		
10-15	15					12-5			5			11-13	11		2		
11-19	19					14-7			7			12-27	26		1		
12-26	26					16-12			12			14-21	17		4		
14-39	39					18-15			15			16-41	37		4		
16-60	60					20-22			22			18-59	55		4		
18-85	85					22-24			24			11-14	13			1	
20-110	110					24-35			35			12-14	12			2	
22-140	140					9-1				1		14-22	20			2	
24-186	186					12-2				2		16-32	28			4	
8-3		3				14-3				3		16-42	40			2	
9-5		5				16-4				4		18-62	60			2	
10-8		8				16-7				7		14-20A	19				1
11-10		10				18-8				8		16-22	20				2
12-15		15				20-11				11		18-21	18				3
14-20		20				22-13				13		20-28	24				4
16-31		31				24-19				19		22-44	40				4
18-41		41				10-1					1	24-97	93				4
20-55		55				16-2					2						
22-69		69				18-3					3						

BAYONET-COUPLING MICRO MINIATURE CIRCULAR
Series 806 Mil-Aero Connectors



806B-021 Jam-Nut Receptacle with PCB standoff

SERIES 806 BAYONET



Shell Size	Ø A Max	B Thread	C Max	Ø D	E Max	F Flat	G	Master Keyway Codes (W°)					Minor Keyway Positions			
								N	A	B	C	D	F°	X°	Y°	Z°
7	0.918 (23.32)	.5000-16 UN	0.858 (21.79)	0.390 (9.91)	0.100 (2.54)	0.460 (11.68)	0.489 (12.42)	104°					14°	45°	85°	38°
8	0.980 (24.89)	.5625-24 UNEF	0.920 (23.37)	0.485 (12.32)		0.535 (13.59)	0.534 (13.56)	95°	80°	110°			5°	45°	88°	27°
9	1.043 (26.49)	.6250-28 UN	0.983 (24.97)	0.563 (14.30)		0.605 (15.37)	0.579 (14.71)									
10	1.105 (28.07)	.6875-24 UNEF	1.045 (26.54)	0.612 (15.54)		0.665 (16.89)	0.679 (17.25)									
11	1.230 (31.24)	.8125-20 UNEF	1.170 (29.72)	0.695 (17.65)		0.770 (19.56)	0.734 (18.64)									
12	1.293 (32.84)	.8750-20 UNEF	1.233 (31.32)	0.720 (18.29)		0.805 (20.45)	0.804 (20.42)		75°	63°	127°	115°				
14	1.469 (37.31)	1.0000-20 UNEF	1.379 (35.03)	0.845 (21.46)		0.930 (23.62)	0.891 (22.63)		80°	69°	121°	110°				
16	1.594 (40.49)	1.1250-18 UNEF	1.504 (38.20)	0.966 (24.54)		1.056 (26.82)	1.049 (26.64)									
18	1.719 (43.66)	1.2500-18 UNEF	1.629 (41.38)	1.086 (27.58)		1.182 (30.02)	1.148 (29.16)									
20	1.842 (46.79)	1.3750-18 UNEF	1.752 (44.50)	1.211 (30.76)		1.307 (33.20)	1.252 (31.80)									
22	2.059 (52.30)	1.5000-18 UNEF	1.969 (50.01)	1.325 (33.66)	0.128 (3.25)	1.431 (36.35)	1.369 (34.77)									
24	2.184 (55.47)	1.6250-18 UNEF	2.094 (53.19)	1.462 (37.13)		1.555 (39.50)	1.509 (38.33)									

RECOMMENDED MOUNTING HOLE			
	Shell Size	$\varnothing J$ +.008 -.000	K +.008 -.000
RECOMMENDED MOUNTING HOLE DIMENSIONS	7	0.478 (12.14)	0.510 (12.95)
	8	0.553 (14.05)	0.572 (14.53)
	9	0.623 (15.82)	0.635 (16.13)
	10	0.683 (17.35)	0.697 (17.70)
	11	0.788 (20.02)	0.822 (20.88)
	12	0.820 (20.83)	0.885 (22.48)
	14	0.945 (24.00)	1.010 (25.65)
	16	1.075 (27.31)	1.135 (28.83)
	18	1.200 (30.48)	1.260 (32.00)
	20	1.325 (33.66)	1.385 (35.18)
	22	1.450 (36.83)	1.510 (38.35)
	24	1.575 (40.01)	1.635 (41.53)

TABLE IV	
Contact Style	Description
P	Pin
S	Socket
E	Solder Cup, Pin
F	Solder Cup, Skt

TABLE V	
Contact Size	PC Tail Dia
8	0.180 (4.57)
12	0.094 (2.39)
16	0.062 (1.57)
20	0.030 (0.76)
22	0.020 (0.51)

BAYONET-COUPLING MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors



806B-022 Square-Flange Receptacle with PCB standoff

SERIES 806 BAYONET

HOW TO ORDER							
Sample Part Number	806B-022	-ME	11-19	S	1	T	A
Basic Part Number	806B-022 Square-Flange Receptacle with PCB standoff						
Material and Finish	-NF = Aluminum Alloy, O.D. Cadmium over Electroless Nickel -MT = Aluminum Alloy, Nickel-PTFE -ME = Aluminum Alloy, Electroless Nickel -ZR = Aluminum Alloy, Black Zinc-Nickel -Z1 = Stainless Steel, Passivate -ZL = Stainless Steel, Electro-Deposited Nickel						
Insert Arrangement	See Table I. Consult Glenair for shell sizes 16 and up.						
Contact Type	P = Pin S = Socket E = Solder Cup, Pin F = Solder Cup, Skt						
PC Tail Length	1 = .125" 2 = .250" Soldercup = Omit						
Panel Mounting Hole Style	T = Thru Hole C = Clinch nuts for rear panel mounting, 4-40, M45938/6-4C (Consult factory for SST with clinch nuts)						
Key Position	See Dimensions Table						

MATERIAL/FINISH

- Shell - Al Alloy or Cres / See Material and Finish Table.
- Insulators - High Grade Rigid Dielectirc.
- Interfacial & Peripheral Seal - Fluorosilicone Blend
- Contact - Copper Alloy / Gold Plated

NOTES

- Assembly to be identified with Glenair's name, part number and date code, space permitting.
- See 806-023 for printed circuit board layouts.
- Insert arrangement shown for reference only, see 806-015 for additional contact arrangements.
- This receptacle connector mates with all bayonet-style coupling, Glenair 806 style, plug connectors with same polarization and opposite contact gender.
- This connector meets all performance requirements of Glenair product spec 806-014.
- Backfill with epoxy. Consult manufacturer for hermetically sealed versions.
- Integral PCB stand off 4x 4-40 UNC .156 Min. thread and locating post.
- Please consult Glenair for shell sizes 16 and up


TABLE I: SHELL SIZE - INSERT ARRANGEMENT																	
Contact Layout	Number of Contacts					Contact Layout	Number of Contacts					Contact Layout	Number of Contacts				
	22HD	20HD	16	12	8		22HD	20HD	16	12	8		22HD	20HD	16	12	8
7-3	3					24-92		92				20-4					4
8-4	4					8-1			1			22-5					5
8-7	7					10-2			2			24-8					8
9-11	11					11-4			4			10-8A	6		2		
10-15	15					12-5			5			11-13	11		2		
11-19	19					14-7			7			12-27	26		1		
12-26	26					16-12			12			14-21	17		4		
14-39	39					18-15			15			16-41	37		4		
16-60	60					20-22			22			18-59	55		4		
18-85	85					22-24			24			11-14	13			1	
20-110	110					24-35			35			12-14	12			2	
22-140	140					9-1				1		14-22	20			2	
24-186	186					12-2				2		16-32	28			4	
8-3		3				14-3				3		16-42	40			2	
9-5		5				16-4				4		18-62	60			2	
10-8		8				16-7				7		14-20A	19				1
11-10		10				18-8				8		16-22	20				2
12-15		15				20-11				11		18-21	18				3
14-20		20				22-13				13		20-28	24				4
16-31		31				24-19				19		22-44	40				4
18-41		41				10-1					1	24-97	93				4
20-55		55				16-2					2						
22-69		69				18-3					3						

BAYONET-COUPLING MICRO MINIATURE CIRCULAR
Series 806 Mil-Aero Connectors



806B-022 Square-Flange Receptacle with PCB standoff

SERIES 806 BAYONET



Shell Size	A Max	Ø B Max	C	Ø D	Ø E Thru Hole	F Max	G	Master Keyway Codes (W°)					Minor Keyway Positions			
								N	A	B	C	D	F°	X°	Y°	Z°
7	0.780 (19.81)	0.993 (25.22)	0.513 (13.03)	0.390 (9.91)	0.128 (3.25)	0.100 (2.54)	0.489 (12.42)	104°					14°	45°	85°	38°
8	0.856 (21.74)	1.101 (27.97)	0.594 (15.09)	0.485 (12.32)			0.534 (13.56)	80°	110°							
9	0.895 (22.73)	1.144 (29.06)	0.625 (15.88)	0.563 (14.30)			0.579 (14.71)									
10	0.979 (24.87)	1.277 (32.44)	0.719 (18.26)	0.612 (15.54)			0.679 (17.25)									
11	1.035 (26.29)	1.342 (34.09)	0.765 (19.43)	0.695 (17.65)			0.734 (18.64)	75°	63°	127°	115°					
12	1.072 (27.23)	1.410 (35.81)	0.812 (20.62)	0.760 (19.30)			0.804 (20.42)									
14	1.166 (29.62)	1.542 (39.17)	0.906 (23.01)	0.845 (21.46)			0.891 (22.63)	95°					5°	45°	88°	27°
16	1.234 (31.34)	1.632 (41.45)	0.969 (24.61)	0.966 (24.54)			1.049 (26.64)									
18	1.328 (33.73)	1.778 (45.16)	1.062 (26.97)	1.086 (27.58)			1.148 (29.16)									
20	1.453 (36.91)	1.910 (48.51)	1.156 (29.36)	1.211 (30.76)			1.252 (31.80)									
22	1.578 (40.08)	2.083 (52.91)	1.250 (31.75)	1.325 (33.66)	0.154 (3.91)	0.125 (3.18)	1.369 (34.77)	80°	69°	121°	110°					
24	1.703 (43.26)	2.248 (57.10)	1.375 (34.93)	1.462 (37.13)			1.509 (38.33)									

MOUNT INFO				
	Size	Ø J	K	
			With Clinch Nut	Without Clinch Nut
	7	0.465 (11.81)	0.128 (3.25)	0.128 (3.25)
	8	0.557 (14.15)		
	9	0.634 (16.10)		
	10	0.682 (17.32)		
	11	0.774 (19.66)		
	12	0.799 (20.29)		
	14	0.923 (23.44)		
	16	1.043 (26.49)		
	18	1.193 (30.30)		
	20	1.317 (33.45)		
	22	1.431 (36.35)		0.154 (3.91)
	24	1.567 (39.80)		

DIAMETER	
Contact Size	PC Tail Dia
8	0.180 (4.57)
12	0.094 (2.39)
16	0.062 (1.57)
20	0.030 (0.76)
22	0.020 (0.51)

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Series 806 Tools and Accessories Selection Guide



CRIMP TOOLS, POSITIONERS AND HEX DIES



809-015 Standard M22520/2-01 Crimper

Use with size #20HD and #22HD Series 806 contacts.

[Page 166](#)



Positioners

Bayonet-type positioners hold contacts at correct height for crimping with 809-015 (M22520/2-01) crimp tool.

[Page 166](#)



809-129 Standard M22520/5-01 Crimper

Use with size #8 twinax and quadrax Series 806 contacts.

[Page 167](#)



Hex-Dies for

Hex-die crimp affixes coax, twinax and quadrax connectors to end of cable.

[Page 167](#)



829-025 Standard M22520/23-01 Crimper

Use with size #8 Series 806 contacts.

[Page 168](#)



829-025 Standard M22520/23-02 Crimper

Indenter Die Assembly for Series 806 contacts.

[Page 168](#)



Locator

Aluminum locator holds contact at correct depth for crimping.

[Page 168](#)


INSERTION / EXTRACTION TOOLS, GROMMET SEALING PLUGS AND DUMMY CONTACT SEALING PLUGS



809-015


Insertion/Extraction tools
Use with size 20HD, 22HD, and 16 Series 806 contacts.

[Page 169](#)




Insertion/Extraction tools
For size 12 power and coax,

[Page 170](#)



Termination Instructions
For use with #22HD contacts used in Series 806 connectors

[Page 171](#)



Grommet Sealing Plug and Dummy Contact Sealing Plugs

[Page 172](#)

Series 806 Mil-Aero Connectors

Series 806 Tools and Accessories Selection Guide

SHIELD TERMINATION




601-108 Nano Band Installation Tool

Offers rapid termination of cable shield to band platform

[Page 172](#)

HOLDING TOOLS




600-221 Connector Holding Tool

Assist in installation of backshell by holding connector in place

[Page 173](#)

SQ FLANGE NUT PLATE




480-003 Nut Plate

Full perimeter nut plate for use with unwired connectors. Use 3/4 perimeter nut plate for wired connectors

[Page 174](#)

PANEL GASKET



930-017 Square Flange Panel Basket

Creates a seal between square flange and mounting panel

[Page 175](#)

O-RING SEALS



M25988/3 or 249-003 O-ring Seal

Fluorosilicone or Viton seals provide sealing between receptacle and the mounting panel

[Page 175](#)

SPANNER WRENCH



Jam-Nut Wrench

For use with low-profile jam-nuts (809-044)

[Page 176](#)

LOW PROFILE JAM-NUT



809-044

Ideally suited for panels with tightly spaced multiple connectors

[Page 176](#)

HEX JAM-NUT




806-035

Standard jam-nut

[Page 177](#)

PROTECTIVE COVER




667-441

Protective Cover

Protect unmated connectors with aluminum or SST covers

[Page 179](#)

DUMMY STOWAGE



667-441

Stowage Receptacle

Protect cabled plug connectors with aluminum or SST dummy stowage receptacles.

[Page 182](#)

Series 806 Mil-Aero Connectors



Crimp Tools, Positioners, Hex Dies and Insertion/Extraction Tools

CRIMP TOOL FOR #20HD, AND #22HD CONTACTS PLUS CENTER PIN #16, #12, AND #8 RF CONTACTS



809-015 (M22520/2-01) crimper for use with size #20HD and #22HD signal contacts and #8, #12, #16 co-axial and tri-axial Series 806 contacts. Requires positioner, sold separately. These crimp tools perform precision eight indent crimps for wire terminations and excellent tensile strength. Adjustment wheel has 8 settings. Ratchet mechanism prevents improper crimps. Use with bayonet-type positioners. Length is 6.75 inches, weight is approx. 10 oz.

Contact Type	Ref. Contact Part Number		Positioner	
	Pin	Socket	Pin	Socket
#22HD Contact	850-094-1	850-095-1	859-147	809-005
#22HD, Small Dia. Wire	850-094-2	850-095-2	859-148	809-057
#20HD Contact	809-204	809-205	809-206	809-206
#16 Coaxial Inner Contact*	809-114 and 809-115	809-116 and 809-117	809-125 (M22520/2-35)	
#8 Diff. Twinax Inner Contact*	853-076	853-075	M22520/2-37	
#8 Quadrax Inner Contact*	854-047	854-048	M22520/2-37	
#8 Twinax Inner Contact*	854-047	854-048	M22520/2-37	

* Requires outer contact crimp tooling as well, refer to tools below and on following page.

CRIMP TOOL FOR SIZE #12, 3 GHZ COAX CENTER PIN



809-128 special crimper with sharper indenter tips for use with size #12 Series 806, 3 GHz coax center pin. Requires positioner, sold separately. These crimp tools perform precision eight indent crimps for wire terminations and excellent tensile strength. Ratchet mechanism prevents improper crimps. Use with bayonet-type positioners. Length is 6.75 inches, weight is 10 oz.

Contact Description	Ref. Contact Part Number		Positioner
	Pin	Socket	
#12, 3GHz Coaxial Inner Contact	852-016-01, 02, 03	852-015-01, 02, 03	859-006

* Requires outer contact crimp tooling as well, refer to tools below and on following page.

CRIMP TOOL FOR SIZE #12, AND #16 POWER CONTACTS



809-136 (M22520/1-01) crimper for use with size #12, and #16 Series 806 contacts. Requires positioner, sold separately. These crimp tools perform precision eight indent crimps for wire terminations and excellent tensile strength. Adjustment wheel has 8 settings for wire being used. Ratchet mechanism prevents improper crimps. Use with bayonet-type positioners. Length is 9.75 inches, weight is 15 oz.

Contact Description	Ref. Contact Part Number		Positioner
	Pin	Socket	
#16 Contact	809-110	809-111	809-137 (M22520/1-04)
#12 Contact	809-112	809-113	809-137 (M22520/1-04)

Series 806 Mil-Aero Connectors

Crimp Tools, Positioners, Hex Dies and Insertion/Extraction Tools

CRIMP TOOL AND POSITIONER FOR SIZE #16 COAX SHIELD CRIMP SLEEVE



809-127 (M22520/4-01) crimper for use with size #16 coax Series 806 contacts. Requires positioner, ordered separately. These crimp tools perform precision eight indent crimps for wire terminations and excellent tensile strength. Ratchet mechanism prevents improper crimps. Use with bayonet-type positioners. Length is 9.75 inches, weight is 15 oz.

Contact Description	Ref. Contact Part Number		Positioner
	Pin	Socket	
#16 Coaxial Contact	809-114 and 809-115	809-116 and 809-117	809-126 (M22520/4-02)

CRIMP TOOL FOR SIZE #12 COAX SHIELD CRIMP SLEEVE



809-133 (M22520/31-01) crimper for use with size #12 Series 806 coax contacts. Requires positioner, ordered separately. These crimp tools perform precision eight indent crimps for wire terminations and excellent tensile strength. Adjustment wheel has 8 settings for wire being used. Ratchet mechanism prevents improper crimps. Use with bayonet-type positioners. Length is 9.75 inches, weight is 15 oz.

Contact Description	Ref. Contact Part Number		Die Set
	Pin	Socket	
#12 Coaxial Outer Contact	809-118 and 809-119	809-120 and 809-121	809-134 (M22520/31-02)

CRIMP TOOL FOR SIZE #8 TWINAX AND QUADRAX SHIELD CRIMP SLEEVE




Standard 809-129 (M22520/5-01) crimper. Use with size #8 twinax and quadrax Series 806 RF contacts. Requires hex-die, ordered separately. These crimp tools attach contact body to cable. Length is 11 inches, weight is approx. 1.476 lbs. For use with interchangeable coax hex-dies. Dies snap in frame of M22520/5-01 and are held in frame by internal spring clips.

Contact Description	Ref. Contact Part Number		Die Set
	Pin	Socket	
#12, 3GHz Coaxial, Outer Contact	852-016-01, -02	852-015-01, -02	809-130 (M22520/5-03) Hex Die
#12, 3GHz Coaxial, Outer Contact	852-016-03	822-015-03	809-130 (M22520/5-03) Hex Die
#8 Coaxial, Outer Contact	852-149-01, -02	852-148-01, -02	M22520/5-03 Hex Die
#8 Diff. Twinax	853-076	853-075	M22520/5-45
Quadrax	854-047	854-048	M22520/5-45

PNEUMATIC CRIMP TOOL FOR #8 POWER CONTACTS

The Daniels WA23 pneumatic crimp tool sets the standard for heavy duty crimping chores. This four-indent tool accommodates large power contacts ranging from size 8 through size 0000. Die plates and locators are purchased separately. Qualified to M22520/23, the WA23 tool is specified for use with SAE AS39029 closed barrel copper alloy contacts.

**PNEUMATIC CRIMP TOOL**

Bench mount heavy duty pneumatic indent crimp tool. Four-indent crimp termination. Use with closed barrel contact sizes 8 through 4/0. Attach to air supply with quick-disconnect fitting or install 1/4 NPT fitting into tapped port. 90-120 psi air supply. Requires die assembly and locator, sold separately. Hand actuate with push-button valve trigger on handle. Steel with black wrinkle enamel coating. 13 inches overall length, 9.2 inches tall, 17 pounds (7.7 Kg).

Description	Part Number	Military Part Number	Daniels Part Number
Pneumatic Crimper	859-025	M22520/23-01	WA23

DIE ASSEMBLY FOR SIZE #8 CONTACTS

Indenter Die Assembly. Precision four-indent die with hardened tool steel indenters, stainless steel housing, aluminum cap. Use with size #8 contacts. Go/ No Go calibration dimensions are stamped on face of tool. Approximately 3.3 inches (84mm.) diameter.

Description	Part Number	Military Part Number	Daniels Part Number
Die Assembly, Size #8	859-026	M22520/23-02	WA23-2

LOCATOR FOR SIZE #8 CONTACTS


Aluminum locator holds contact at correct depth for crimping.

Description	Part Number	Military Part Number	Daniels Part Number
Locator, #8, Special	859-046	(none)	WA23-395L
Locator, #8, Spring Loaded	859-164	(none)	WA23-395SSL

Series 806 Mil-Aero Connectors

Crimp Tools, Positioners, Hex Dies and Insertion/Extraction Tools

INSERTION/EXTRACTION TOOL FOR #20HD CONTACTS




Insertion/Extraction Tool for #20HD Contacts. This tool features molded plastic grips and sturdy stainless steel or thermoplastic tips.

Contact Size	Tip Material	Color	Insertion/Extraction Tool
#20HD	Stainless Steel	Green (Ins.)/White (Ext.)	809-203
#20HD	Thermoplastic	Green (Ins.)/Blue (Ext.)	809-203D*

* Append D for Delrin tip


INSERTION/EXTRACTION TOOLS FOR #22HD CONTACTS



Insertion/extraction tool for #22HD contacts. Features molded plastic grips and sturdy stainless steel tips. White/yellow molded handle.

Contact Size	Tip Material	Color	Insertion/Extraction Tool
#22HD	Stainless Steel	Yellow (Ins.)/White (Ext.)	859-163 (M81969/1-05)

INSERTION/EXTRACTION TOOLS FOR #16 POWER CONTACTS



Insertion/Extraction Tool for #16 contacts. For use with power contacts. Economical molded plastic. White extraction tip, blue insertion tip.


Contact Size	Material	Color	Insertion/Extraction Tool
#16	Delrin or Equivalent	Blue (Ins.)/White (Ext.)	809-131 (M81969/14-03)

INSERTION/EXTRACTION TOOLS FOR #16, COAX CONTACTS



Insertion/Extraction reverse tweezer for #16 shielded coax contacts. Metal construction.

Contact Size	Material	Color	Insertion/Extraction Tool
#16	Stainless Steel	Blue Tipped Handle	(M81969/8-08)

INSERTION/EXTRACTION TOOLS FOR #12, POWER CONTACTS

Insertion/Extraction tool for #12 power contacts.

Contact Size	Material	Color	Insertion / Extraction Tool
#12	Thermoplastic	Yellow (Ins.)/White (Ext.)	809-132 (M81969/14-04)

INSERTION/EXTRACTION TOOLS FOR #12, 50 AND 75 COAX CONTACTS


Insertion/Extraction reverse tweezer for #12 power contacts. Metal construction. Yellow tip handle

Contact Size	Material	Color	Insertion Tool	Extraction Tool
#12	Stainless Steel	Yellow Tipped Handle	(M81969/8-09)	(M81969/8-10)

INSERTION/EXTRACTION TOOLS FOR #12, 50 OHM MATCHED IMPEDANCE 3 GHZ COAX CONTACTS

Insertion/Extraction reverse tweezer for #12 power contacts. Metal construction. Blue tip handle

Contact Size	Material	Color	Insertion / Extraction Tool
#12	Stainless Steel	Blue (Ins.)/White (Ext.)	(M81969/8-07)

INSERTION/EXTRACTION TOOLS FOR #12, 75 OHM MATHCHED IMPEDANCE 3 GHZ COAX CONTACTS

Insertion/Extraction tool for #12 power contacts. Metal construction. Yellow tip handle

Contact Size	Material	Color	Insertion / Extraction Tool
#12	Thermoplastic	Yellow (Ins.)/White (Ext.)	809-132 (M81969/14-04)

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors



Crimp Tools, Positioners, Hex Dies and Insertion/Extraction Tools

HOW TO TERMINATE, INSTALL AND REMOVE SIZE #22 CONTACTS

1 Set Up Crimp Tool. Install proper positioner into crimp tool. The label on the positioner shows the proper tool setting for each wire size. Turn the adjustment wheel to the correct setting.


2 Strip Wire. Remove wire insulation, taking care to avoid nicking or cutting wire strands. Strip wire to length shown.

3 Insert wire into contact. The wire should be visible in the inspection hole.

4 Insert contact into crimp tool as shown. Make sure that the contact is fully inserted into the tool. Squeeze handle completely. The ratchet mechanism will not allow a partial crimp. Release handle and remove contact.


5 Inspect crimped contact. Wire should be fully inserted and the crimp should be uniform in appearance.

Insertion/Extraction Tool 859-163



6 Install contact into connector. Push the contact through the rear grommet until the contact locks into place. This can usually be done by hand without the need for a tool. If the wire gage is #26 or smaller, a tool is helpful. There are two techniques for installing contacts with a tool. One method is to push the contact in by hand, then use the tool to finish the insertion. The other method is to position the insertion tip against the contact shoulder, then insert the contact. Use insertion/extraction tool 859-163 to install contacts. Slide the wire into the groove on the yellow end of the tool. Slide the tool tip up the contact until it touches the contact shoulder. **USE CARE TO AVOID DAMAGING THE CONNECTOR.**

7 Contact Extraction. Use tool 859-163. The white end is used for contact extraction. First, push the wire into the groove of the metal tip. Slide the tip of the tool into the connector. Push the tool into the connector cavity until the tip bottoms in the connector. Avoid wiggling or rocking the tip. This may damage the cavity. A straight push is best. Pinch the wire between your finger and the white plastic grip and slide the tool and contact out of the connector. **Wire insulation diameter greater than 0.045 inches (1.14mm) is too large to work properly with the extraction tool. connector damage is possible.**




Series 806 Mil-Aero Connectors




Grommet Sealing Plugs, Dummy Contact Sealing Plugs, Band-Master ATS

GROMMET SEALING PLUGS



Reference
Dimension
Callouts for Figures
1 thru 4




Grommet sealing plugs are used to seal unwired contact cavities. After installing unwired contacts into unused cavities, insert knob end of sealing plug into grommet until it bottoms against the unwired contact. Size 8 sealing plug dimensions shown below chart.

Fig.	Cavity Size	Color	Part Number	Military Part Number	A Ref. in. mm.	B Ref. in. mm.	C Ref. in. mm.	D Ref. in. mm.
1	#22HD	Black	859-021	MS27488-22-2	.062 1.57	.125 3.18	.668 16.97 .618 15.70	.042 1.07
2	#20HD	Red	859-012	MS27488-20-2	.085 2.16	.125 3.18	.780 19.81	.053 1.35
3	#16	Green	859-013	MS27488-16-12	.074 1.88	.88 22.4	.125 3.18	.125 3.18
4	#12	Orange	859-014	MS27488-12-2	.120 3.05	.85 21.6	.165 4.19	.125 3.18

DUMMY CONTACT SEALING PLUGS

Size	Color	Pin Cavity P/N	Socket Cavity P/N
#22HD	Bone	680-116-22HD	680-116-22HDS
#20HD	Brown	680-116-20HD	680-116-20HDS
#16	Violet	680-116-16	680-116-16S
#12	Orange	680-116-12	680-116-12S
#8	Green	680-116-80B	

Dummy Contact Sealing Plugs (DCSP) are a weight-saving alternative to using grommet sealing plugs and unwired contacts. DCSP Plugs replace both contact and sealing plug in one piece.



NANO BAND-MASTER ATS® SHIELD TERMINATION SYSTEM




Contact Glenair or visit our website (glenair.com/bandmaster) to view our complete line of **Band-Master ATS®** products, including pneumatic tools for high volume production and calibration kits.

Fast, cost-effective shield termination. Attach cable shields to Series 806 connectors with low profile, lightweight Nano **Band-Master®** stainless steel straps. The **Band-Master®** system offers fast termination and the flexibility to handle a wide range of parts with just one band size. Approved for aerospace and defense, these straps have successfully passed rigorous shock, vibration and environmental testing.

1 Nano Band Installation Tool. Use with .075" (1.90 mm) wide nano bands. 6.75 inches (172 mm.) length, 1.2 pounds (0.6 Kg.). Tool is factory-calibrated at 50 ± 3 pounds (22.4 N ± 13.3). LED calibration counter.

Description	Part Number
Nano Band Installation Tool	601-108

2 Nano Band, .075" (1.90 mm) wide. Available in three lengths, flat or pre-coiled. 300 series stainless steel, passivated.



Length		Part Number		Accommodates Diameter	
in.	mm.	Flat	Pre-Coiled	in.	mm.
6.000	152.40	601-500	601-501	.60	15.24
9.000	228.60	601-504	601-505	.94	23.88
14.000	355.60	601-508	601-509	1.88	47.75

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

600-221 Connector Holding Tool




600-221 SERIES 806 CONNECTOR HOLDING TOOLS

Connector holding tools keep connectors stationary while tightening coupling nut of backshell onto connector. Nickel-plated alloy steel. Tool fits 1/4 inch square socket drive.




Receptacle holding tool




Plug holding tool

600-221	-11	P	A	K
Basic Part No	Shell Size	P = Plug R = Receptacle	Polarization A, B, C, D, E or F	Add "K" for full kit in designated polarization

Shell Size	Recommended Backshell Torque (In-Lbs)		
	Standard Min/Max	Composite Min/Max	High Vibration Min/Max
7	25/35	17/22	35/45
8	25/35	20/25	42/52
9	30/40	20/30	51/61
10	30/40	20/30	63/73
11	30/40	20/30	71/81
12	30/40	25/35	79/89
14	35/45	25/35	105/115
16	35/45	25/35	111/121
18	35/45	30/40	111/121
20	35/45	30/40	111/121
22	75/85	35/45	131/141
24	75/85	35/45	131/141



Plug Holder
Polarization Keyway



Receptacle Holder
Polarization Key

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors


480-003 Nut Plates



480-003 NUT PLATES




1 Full perimeter nut plate. Assemble over wires before connector termination. Shown with epoxy primer coating.



2 3/4 perimeter nut plate for installation on pre-wired assemblies. Shown with epoxy primer coating.

Nut plates speed up connector installation and eliminate dropped hardware in hard-to-reach locations. For use with Series 806 square flange panel mount connectors. Two styles: full perimeter and 3/4 perimeter. Install full perimeter plate over wires before terminating the connector. 3/4 perimeter version can be installed on wired connectors. Aluminum plate with self-locking stainless steel female clinch nuts. Plate is coated with chem film per MIL-DTL-5541 Class 1A, or, for maximum corrosion protection choose epoxy primer coating.

How To Order					
SAMPLE PART NUMBER		480-003	E	12	B
Product	480-003 = Nut Plate for Series 806 Receptacles				
Finish	E = Chem film EAP = Epoxy primer coating				
Shell Size	7 8 9 10 11 12 14 16 18 20 22 24				
Style	A = full perimeter (Fig. 1) B = 3/4 perimeter (Fig. 2)				
Clinch Nut Thread Size	Omit = standard UNC threads M = metric threads				



Construction

- Plate: aluminum alloy
- Code E finish: chemical conversion coating per MIL-DTL-5541 Class 1A
- Code EAP finish: epoxy primer per MIL-PRF-23377 Type 1
- Clinch nuts: stainless steel, passivated



Shell Size	A Typ		B		øC		D		E	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	UNC	Metric
7	.740	18.80	.469	11.91	.433	11.00	.201	5.11	4-40	M3 x 0.5
8	.812	20.62	.531	13.49	.494	12.54	.263	6.68	4-40	M3 x 0.5
9	.875	22.23	.594	15.09	.562	14.27	.326	8.28	4-40	M3 x 0.5
10	.903	22.94	.625	15.88	.630	16.00	.357	9.07	4-40	M3 x 0.5
11	.950	24.13	.670	17.02	.697	17.70	.402	10.21	4-40	M3 x 0.5
12	1.028	26.11	.765	19.43	.753	19.13	.497	12.62	4-40	M3 x 0.5
14	1.123	28.52	.859	21.82	.875	22.23	.591	15.01	4-40	M3 x 0.5
16	1.217	30.91	.938	23.83	1.000	25.40	.670	17.02	4-40	M3 x 0.5
18	1.308	33.22	1.016	25.81	1.110	28.19	.748	19.00	4-40	M3 x 0.5
20	1.434	36.42	1.109	28.17	1.260	32.00	.789	20.04	6-32	M4 x 0.7
22	1.560	39.62	1.203	30.56	1.385	35.18	.883	22.43	6-32	M4 x 0.7
24	1.686	42.82	1.312	33.32	1.510	38.35	.992	25.20	6-32	M4 x 0.7

Series 806 Mil-Aero Connectors

Panel Gaskets and Jam-Nut Receptacle Replacement O-rings

PANEL GASKETS FOR SERIES 806 SQUARE FLANGE RECEPTACLES


These flange gaskets provide sealing between square flange receptacles and the mounting panel. Choose fluorosilicone, Viton®, silver-plated aluminum-filled silicone (MIL-DTL-83528 Type B) or passivated silver-plated aluminum-filled fluorosilicone (MIL-DTL-83528 Type D).




Shell Size	Non-Conductive Elastomer		Conductive Elastomer		DIMENSIONS									
	Fluorosilicone	Viton®	Silicone MIL-DTL-83528 Type B	Fluorosilicone MIL-DTL-83528 Type D	A BSC		Ø B		C		D		E RAD	
					In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
7	930-017F-12	930-017V-12	930-017C-12	930-017X-12	.469	11.9	.453	11.5	.743	18.9	.131	3.33	.130	3.30
8	930-017F-1	930-017V-1	930-017C-1	930-017X-1	.531	13.49	.515	13.08	.815	20.70	.131	3.33	.130	3.30
9	930-017F-2	930-017V-2	930-017C-2	930-017X-2	.594	15.09	.582	14.78	.878	22.30	.131	3.33	.130	3.30
10	930-017F-3	930-017V-3	930-017C-3	930-017X-3	.625	15.88	.650	16.51	.906	23.01	.131	3.33	.130	3.30
11	930-017F-4	930-017V-4	930-017C-4	930-017X-4	.670	17.02	.717	18.21	.953	24.21	.131	3.33	.130	3.30
12	930-017F-5	930-017V-5	930-017C-5	930-017X-5	.765	19.43	.773	19.63	1.031	26.19	.131	3.33	.130	3.30
14	930-017F-6	930-017V-6	930-017C-6	930-017X-6	.859	21.82	.895	22.73	1.126	28.60	.131	3.33	.090	2.29
16	930-017F-7	930-017V-7	930-017C-7	930-017X-7	.938	23.83	1.020	25.91	1.220	30.99	.157	3.99	.130	3.30
18	930-017F-8	930-017V-8	930-017C-8	930-017X-8	1.016	25.81	1.130	28.70	1.311	33.30	.157	3.99	.090	2.29
20	930-017F-9	930-017V-9	930-017C-9	930-017X-9	1.109	28.17	1.280	32.51	1.437	36.50	.157	3.99	.130	3.30
22	930-017F-10	930-017V-10	930-017C-10	930-017X-10	1.203	30.56	1.405	35.69	1.563	39.70	.157	3.99	.130	3.30
24	930-017F-11	930-017V-11	930-017C-11	930-017X-11	1.312	33.32	1.530	38.86	1.689	42.90	.157	3.99	.180	4.57

O-RINGS FOR SERIES 806 JAM-NUT RECEPTACLES

Replace damaged O-rings with standard mil spec fluorosilicone O-rings or, for added EMI protection, select O-rings made of silver-plated aluminum-filled silicone (MIL-DTL-83528 Type B) or passivated silver-plated aluminum-filled fluorosilicone (MIL-DTL-83528 Type D).



Shell Size	Size (ID x W)	Fluorosilicone (Non-conductive)	MIL-DTL-83528 Type B Conductive Silicone	MIL-DTL-83528 Type D Conductive Fluorosilicone
7	.489 x .055	M25988/3-016	249-003-806-07-B	249-003-806-07-C
8	.676 x .070	M25988/3-017	249-003-806-08-B	249-003-806-08-C
9	.739 x .070	M25988/3-018	249-003-806-09-B	249-003-806-09-C
10	.801 x .070	M25988/3-019	249-003-806-10-B	249-003-806-10-C
11	.864 x .070	M25988/3-020	249-003-806-11-B	249-003-806-11-C
12	.926 x .070	M25988/3-021	249-003-806-12-B	249-003-806-12-C
14	1.051 x .070	M25988/3-023	249-003-806-14-B	249-003-806-14-C
16	1.176 x .070	M25988/3-025	249-003-806-16-B	249-003-806-16-C
18	1.301 x .070	M25988/3-027	249-003-806-18-B	249-003-806-18-C
20	1.424 x .103	M25988/3-127	249-003-806-20-B	249-003-806-20-C
22	1.549 x .103	M25988/3-129	249-003-806-22-B	249-003-806-22-C
24	1.737 x .103	M25988/3-132	249-003-806-24-B	249-003-806-24-C

SERIES 806 LOW PROFILE JAM-NUT

Replace standard hex-profile jam-nuts with special Series 806 low-profile jam-nuts. Ideal for use when multiple receptacles are mounted close together on a box interface.

809-444Product Series and
Basic Number**-ME**Material and Finish
See Table II**8**Dash Number,
See Table I**Table I**

Dash No.	Thread A	B ±.020 Dia.
7	M13 x 1.0-6H	.705 (17.91)
8	M15 x 1.0-6H	.766 (19.46)
9	M16 x 1.0-6H	.829 (21.06)
10	M18 x 1.0-6H	.891 (22.63)
11	M19 x 1.0-6H	.954 (24.23)
12	M21 x 1.0-6H	1.016 (25.81)
14	M24 x 1.0-6H	1.149 (29.18)
16	M27 x 1.0-6H	1.272 (32.31)
18	M30 x 1.0-6H	1.397 (35.48)
20	M34 x 1.0-6H	1.567 (39.80)
22	M37 x 1.0-6H	1.690 (42.93)
24	M41 x 1.0-6H	1.880 (47.75)

Table II

Class	Material	Finish Description
ME	Aluminum	Electroless nickel
MT		Nickel-PTFE
NF		Olive drab cadmium over electroless nickel finish
ZR		Zinc nickel black over electroless nickel. RoHS compliant
ZI	Stainless	Passivate
ZL	Steel	Electrodeposited nickel

600-246 SERIES 806 CONNECTOR LOW-PROFILE JAM-NUT SPANNER TOOL

Tool used to tighten Series 806 low-profile jam-nuts. Fits 3/8" torque wrench socket drive. Heat-treated steel, nickel plated.



Shell Size	Part Number	Jam-nut Torque In-Lbs.		Jam-nut Thread Size Reference
		Min.	Max.	
7	600-246-7	20	25	M13 x 1.0-6H
8	600-246-8	20	25	M15 x 1.0-6H
9	600-246-9	20	25	M16 x 1.0-6H
10	600-246-10	25	30	M18 x 1.0-6H
11	600-246-11	25	30	M19 x 1.0-6H
12	600-246-12	25	30	M21 x 1.0-6H
14	600-246-14	25	30	M24 x 1.0-6H
16	600-246-16	25	30	M27 x 1.0-6H
18	600-246-18	25	30	M30 x 1.0-6H
20	600-246-20	25	30	M34 x 1.0-6H
22	600-246-22	25	30	M37 x 1.0-6H
24	600-246-24	25	30	M41 x 1.0-6H
All Shell Sizes	600-246-KIT	25	30	All Listed Above

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806



Mil-Aero Connectors

Series 806 Hex Jam-Nut with Wire Holes



SERIES 806 HEX JAM-NUT

Replace lost or damaged hex jam-nuts with these standard replacement parts. Jam-nut fits all Series 80 jam-nut receptacles. Use with Glenair tool 600-146



How To Order				
SAMPLE PART NUMBER		806-035	ME	10 W
Product	806-035 = Jam-nut for Series 806 jam-nut receptacles			
Finish	See Table I for material and finish options			
Shell Size	7 8 9 10 11 12 14 16 18 20 22 24			
Wire Hole	W = Wire hole; omit for none			

Table I: Dimensions			
Shell Size	"A" Hex	B Thread	C
7	.76 (19.30)	M8 x 1.06h 0.100 R	.88 (22.35)
8	.82 (20.83)	M15 x 1.06h 0.100 R	.92 (23.37)
9	.86 (21.84)	M16 x 1.06h 0.100 R	.97 (24.64)
10	.94 (23.88)	M18 x 1.06h 0.100 R	1.06 (26.92)
11	.98 (24.89)	M19 x 1.06h 0.100 R	1.10 (27.94)
12	1.06 (26.92)	M21 x 1.06h 0.100 R	1.19 (30.23)
14	1.26 (32.00)	M24 x 1.06h 0.100 R	1.42 (36.07)
16	1.31 (33.27)	M27 x 1.06h 0.100 R	1.48 (37.59)
18	1.41 (35.81)	M30 x 1.06h 0.100 R	1.60 (40.64)
20	1.58 (40.13)	M34 x 1.06h 0.100 R	1.79 (45.47)
22	1.71 (43.43)	M37 x 1.06h 0.100 R	1.94 (49.28)
24	1.86 (47.24)	M41 x 1.06h 0.100 R	2.12 (53.85)

Table I: Dimensions		
Code	Material	Finish
NF	Aluminum Alloy	Cad/O.D. over Electroless Nickel
MT	Aluminum Alloy	Nickel-PTFE
ME	Aluminum Alloy	Electroless Nickel (96 hour salt spray)
ZR	Aluminum Alloy	Zinc Ni, Black (ti-valent cr)
Z1	Stainless Steel	Passivate
ZL	Stainless Steel	Electro-deposited nickel

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors

Series 806 Hex Jam-Nut with 6 Wire Holes



SERIES 806 HEX JAM-NUT



Replace lost or damaged hex jam-nut with this standard replacement part. Jam-nut used on 8070-3334 series receptacles. (Ref. Series 806 Special) Use with Glenair tool 600-146.

How To Order			
SAMPLE PART NUMBER	809-539	-ME	16
Product	809-539 = Jam-nut for Series 8070-3334 receptacles		
Finish	See Table I for material and finish options		
Shell Size	16		

Table I: Dimensions		
Code	Material	Finish
NF	Aluminum Alloy	Cad/O.D. over Electroless Nickel
MT	Aluminum Alloy	Nickel-PTFE
ME	Aluminum Alloy	Electroless Nickel (96 hour salt spray)
ZR	Aluminum Alloy	Zinc Ni, Black (ti-valent cr)
Z1	Stainless Steel	Passivate
ZL	Stainless Steel	Electro-deposited nickel

Series 806 Mil-Aero Connectors

Protective Covers 667-440, 667-441 and 667-443





Figure 1
667-440 Receptacle Cover




Figure 2
667-441 Plug Cover







Figure 3
667-443 Self-Locking
Receptacle Cover

Protect unmated Series 806 connectors with thread-on covers. IP68 ingress protection. Aluminum, stainless steel or composite material. Self-locking receptacle cover features anti-decoupling mechanism for resistance to loosening under vibration.

Construction

- Cover: aluminum alloy, high grade engineering thermoplastic or stainless steel. See ordering info for finish options
- O-ring, gasket: fluorosilicone
- Hardware: stainless steel, passivated
- Lanyard: see Table 1

Table 2 Ring Codes


Ring Type	Ring Code	Inside Diameter	
		In.	mm.
No Ring	00	—	—
	04	.126	3.20
	06	.145	3.68
	08	.188	4.78
	10	.197	5.00
	12	.423	10.74
	14	.481	12.22
	16	.560	14.22
	18	.600	15.24
	20	.635	16.13
	22	.695	17.65
	24	.715	18.16
	26	.766	19.46
	28	.845	21.46
	30	.885	22.48
	32	.950	24.13
	34	1.015	25.78
	36	1.070	27.18
	38	1.135	28.83
	40	1.210	30.73
	42	1.275	32.39
	44	1.380	35.05
	46	1.470	37.34
	48	1.625	41.28
	50	.432	10.97
	52	.492	12.50
	54	.648	16.46
	56	.757	19.23
	58	.898	22.81
	60	1.023	25.98
	64	1.137	28.88
	68	1.357	34.47

How To Order


SAMPLE PART NUMBER		667-441	ME	12	U	01	-6		
Product	667-440 = Receptacle cover (fig. 1) 667-441 = Plug cover (fig. 2) 667-443 = Receptacle cover, self-locking (fig. 3)								
Material/ Finish	Material	Finish	Code						
	Aluminum	Electroless Nickel	ME						
		Nickel-PTFE	MT						
		Olive Drab Cadmium	NF						
		Black Zinc-Nickel	ZR						
	Stainless Steel	Passivate	Z1						
	Composite	Electroless Nickel	XMD						
		Olive Drab Cadmium	XW						
		Black Unplated	XB						
Violet Unplated (Fiber)		XV							
Shell Size	7 8 9 10 11 12 14 16 18 20 22 24								
Attachment Lanyard (Table I)	N = No attachment G = Nylon rope SK = Nylon rope with slip knot U = SST rope with polyurethane coating H = SST rope with high temperature translucent FEP jacket S = Sash chain, #8, SST								
Attachment Ring Code (Table 2)	Omit for attachment types N and SK See Table 2 for ring styles and sizes								
Attachment Length	Omit for attachment type N Lanyard length in inches								

Table 1 Attachment Lanyards


 Nylon Rope (G) -55° to +100°C, black, very flexible, very good abrasion resistance, good resistance to fuels, .120" (3mm) diameter	 Sash Chain (S) Stainless steel, #8 chain, .240" (6mm)
 Polyurethane Coated Wire Rope (U) Black polyurethane over stainless steel rope, -55° to +125°C, very flexible, excellent abrasion resistance, excellent resistance to fuels, .080" (2mm) diameter	 Slip Knot (SK) 55° to +100°C, black, very flexible, very good abrasion resistance, good resistance to fuels, .120" (3mm) diameter. Length includes .5" (13mm) diameter loop.
 Teflon® Jacketed Wire Rope (H) Translucent FEP jacket over stainless steel, -55° to +200°C, fair flexibility, good abrasion resistance, .100" diameter	

667-440 Receptacle Cover

Shell Size	ØC Max		E Thread
	In.	mm.	
7	.600	15.2	.4375-.067P-.2L-TS-2B
8	.640	16.3	.5000-.067P-.2L-TS-2B
9	.703	17.8	.5625-.067P-.2L-TS-2B
10	.765	19.4	.6250-.067P-.2L-TS-2B
11	.828	21.0	.6875-.067P-.2L-TS-2B
12	.890	22.6	.7500-.067P-.2L-TS-2B
14	1.015	25.8	.8750-.067P-.2L-TS-2B
16	1.140	30.0	1.0000-.067P-.2L-TS-2B
18	1.265	32.1	1.1250-.067P-.2L-TS-2B
20	1.390	35.3	1.2500-.067P-.2L-TS-2B
22	1.515	38.5	1.3750-.067P-.2L-TS-2B
24	1.710	43.4	1.5000-.067P-.2L-TS-2B

667-441 Plug Cover

Shell Size	ØC Max		E Thread
	In.	mm.	
7	.606	15.4	.4375-.067P-.2L-TS-2A
78	.676	17.2	.5000-.067P-.2L-TS-2A
9	.771	19.6	.5625-.067P-.2L-TS-2A
10	.832	21.1	.6250-.067P-.2L-TS-2A
11	.890	22.6	.6875-.067P-.2L-TS-2A
12	.950	24.1	.7500-.067P-.2L-TS-2A
14	1.110	28.2	.8750-.067P-.2L-TS-2A
16	1.170	29.7	1.0000-.067P-.2L-TS-2A
18	1.350	34.3	1.1250-.067P-.2L-TS-2A
20	1.470	37.3	1.2500-.067P-.2L-TS-2A
22	1.600	40.6	1.3750-.067P-.2L-TS-2A
24	1.710	43.4	1.5000-.067P-.2L-TS-2A

667-443 Receptacle Cover With Anti-Decoupling Device

Shell Size	ØC Max		E Thread
	In.	mm.	
7	.606	15.4	.4375-.067P-.2L-TS-2B
8	.676	17.2	.5000-.067P-.2L-TS-2B
9	.771	19.6	.5625-.067P-.2L-TS-2B
10	.832	21.1	.6250-.067P-.2L-TS-2B
11	.890	22.6	.6875-.067P-.2L-TS-2B
12	.950	24.1	.7500-.067P-.2L-TS-2B
14	1.110	28.2	.8750-.067P-.2L-TS-2B
16	1.170	29.7	1.0000-.067P-.2L-TS-2B
18	1.350	34.3	1.1250-.067P-.2L-TS-2B
20	1.470	37.3	1.2500-.067P-.2L-TS-2B
22	1.600	40.6	1.3750-.067P-.2L-TS-2B
24	1.710	43.4	1.5000-.067P-.2L-TS-2B

Solid Attachment Ring Dimensions

Ring Code	Inside Diameter		Max. Outside Diameter	
	In.	mm.	In.	mm.
00	—	—	—	—
04	.126	3.20	.310	7.87
06	.145	3.68	.310	7.87
08	.188	4.78	.310	7.87
10	.197	5.00	.310	7.87
11	.326	8.28	.445	11.3
12	.423	10.74	.535	13.59
14	.481	12.22	.593	15.06
16	.560	14.22	.672	17.07
18	.600	15.24	.712	18.08
20	.635	16.13	.770	19.56

Ring Code	Inside Diameter		Max. Outside Diameter	
	In.	mm.	In.	mm.
22	.695	17.65	.830	21.08
24	.715	18.16	.830	21.08
26	.766	19.46	.895	22.73
28	.845	21.46	1.026	26.06
30	.885	22.48	1.026	26.06
32	.950	24.13	1.172	29.77
34	1.015	25.78	1.205	30.61
36	1.070	27.18	1.205	30.61
38	1.135	28.83	1.260	32.00
40	1.210	30.73	1.322	33.58
42	1.275	32.39	1.385	35.18


Ring Code	Inside Diameter		Max. Outside Diameter	
	In.	mm.	In.	mm.
44	1.380	35.05	1.485	37.72
46	1.470	37.34	1.672	42.47
48	1.625	41.28	1.797	45.64
50	.432	10.97	.570	14.48
52	.492	12.50	.630	16.00
54	.648	16.46	.790	20.07
56	.757	19.23	.890	22.61
58	.898	22.81	1.040	26.42
60	1.023	25.98	1.160	29.46
64	1.137	28.88	1.270	32.26
68	1.357	34.47	1.480	37.59

Series 806 Mil-Aero Connectors

Protective Covers 667-440, 667-441 and 667-443


Attachment Ring Application Guide

Attaching a Cover to a Cable-Mounted Connector with Solid Ring




Shell Size	Accessory Thread Size	Max. Thd. Dia.		Recommended Ring Code
		In.	mm.	
7	M8x1.0-6g-0.100R	.315	8	11
8	M10x1.0-6g-0.100R	.393	10	12
9	M12x1.0-6g-0.100R	.471	12	14
10	M14x1.0-6g-0.100R	.550	14	16
11	M15x1.0-6g-0.100R	.589	15	18
12	M17x1.0-6g-0.100R	.668	17	22
14	M19x1.0-6g-0.100R	.747	19	26
16	M22x1.0-6g-0.100R	.865	22	30
18	M25x1.0-6g-0.100R	.983	25	34
20	M28x1.0-6g-0.100R	1.101	28	38
22	M31x1.0-6g-0.100R	1.219	31	42
24	M34x1.0-6g-0.100R	1.338	34	44

Attaching a Receptacle Cover to a Jam-nut Receptacle with Solid Ring




Shell Size	Jam-nut Thread	Max. Thd. Dia.		Recommended Ring Code
		In.	mm.	
7	M13x1.0-6g-0.100R	.512	13	16
8	M15x1.0-6g-0.100R	.589	15	18
9	M16x1.0-6g-0.100R	.629	16	20
10	M18x1.0-6g-0.100R	.707	18	24
11	M19x1.0-6g-0.100R	.747	19	26
12	M21x1.0-6g-0.100R	.827	21	28
14	M24x1.0-6g-0.100R	.944	24	32
16	M27x1.0-6g-0.100R	1.062	27	36
18	M30x1.0-6g-0.100R	1.180	30	40
20	M34x1.0-6g-0.100R	1.338	34	44
22	M37x1.0-6g-0.100R	1.456	37	46
24	M41x1.0-6g-0.100R	1.613	41	48

Attaching a Cover to a Panel with Ring Terminal



Screw Size	Ring Code	Ring I.D.	
		In.	mm.
		±.005	±0.13
#4, M3	04	.126	3.20
#6	06	.145	3.68
#8, M4	08	.188	4.78
#10	10	.197	5.00

Attaching a Cover with Split Ring to a Cordset



Split Ring Code	Ring I.D.		Split Ring Code	Ring I.D.	
	In.	mm.		In.	mm.
50	.432	10.97	58	.898	22.81
52	.492	12.50	60	1.023	25.98
54	.648	16.46	64	1.137	28.88
56	.757	19.23	68	1.357	34.47

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Dummy Stowage Receptacle 650-088



DUMMY STOWAGE RECEPTACLES


Dummy stowage receptacles secure plug ends of cables during maintenance and storage. Mates with Series 806 plug connectors. Universal keying. O-ring provides environmental seal. Aluminum or stainless steel.



Construction

- Shell: aluminum alloy or stainless steel. See How to Order table for finish options
- O-ring: fluorosilicone

How To Order					
SAMPLE PART NUMBER		650-088		ME	12
Product	650-088 = Stowage receptacle for Series 806 plugs				
Finish	Material		Finish		Code
	Aluminum		Electroless Nickel		ME
			Nickel-PTFE		MT
			Olive Drab Cadmium		NF
			Black Zinc-Nickel		ZR
	Stainless Steel		Passivate		Z1
		Nickel		ZL	
Shell Size	7 8 9 10 11 12 14 16 18 20 22 24				



650-088 Dummy Receptacle Dimensions									
Shell Size	A Max		B		C Thread	ØD		E Max	
	In.	mm.	In.	mm.		In.	mm.	In.	mm.
7	.750	19	.469	11.9	.4375-.067P-.2L-TS-2A	.128	3.25	.100	2.54
8	.822	20.88	.531	13.49	.5000-.067P-.2L-TS-2A	.128	3.25	.100	2.54
9	.885	22.48	.594	15.09	.5625-.067P-.2L-TS-2A	.128	3.25	.100	2.54
10	.913	23.19	.625	15.88	.6250-.067P-.2L-TS-2A	.128	3.25	.100	2.54
11	.944	23.98	.670	17.02	.6875-.067P-.2L-TS-2A	.128	3.25	.100	2.54
12	1.040	26.42	.765	19.43	.7500-.067P-.2L-TS-2A	.128	3.25	.100	2.54
14	1.133	28.78	.859	21.82	.8750-.067P-.2L-TS-2A	.128	3.25	.100	2.54
16	1.227	31.17	.938	23.83	1.0000-.067P-.2L-TS-2A	.128	3.25	.100	2.54
18	1.320	33.53	1.016	25.81	1.1250-.067P-.2L-TS-2A	.128	3.25	.100	2.54
20	1.444	36.68	1.109	28.17	1.2500-.067P-.2L-TS-2A	.154	3.91	.125	3.18
22	1.570	39.88	1.203	30.56	1.3750-.067P-.2L-TS-2A	.154	3.91	.125	3.18
24	1.696	43.08	1.312	33.32	1.5000-.067P-.2L-TS-2A	.154	3.91	.125	3.18

Series 806 Mil-Aero Connectors

Series 806 Backshell, Adapter and Strain Relief Selection Guide

STRAIN RELIEF CLAMPS



871V004
Swing-Arm Flex Clamp
EMI Banding Adapter,
Composite
[Page 186](#)



871V006
Style II Composite
Swing-Arm Flex Clamp,
Banding Adapter
[Page 188](#)

SWING-ARM FLEX CLAMP



620V081
Composite Strain Relief
Clamp
Straight, 45° and 90°
[Page 190](#)



620V080
Strain Relief Clamp
Aluminum or SST,
self-locking
[Page 203](#)

EMI RFI BANDING ADAPTERS



440V202
Composite Band/Boot Adapters
These composite self-locking adapters
are lightweight and corrosion resistant
[Page 192](#)



317V111
Piggyback Boot Adapter
These composite, self-locking backshells
have a drop-in banding adapter and are
supplied with pre-attached shrink boot
[Page 196](#)



440V191
Band/Boot Adapters
Aluminum or stainless steel
[Page 204](#)

EMI BACKSHELLS



387V243
Composite EMI
Ground rings for shield termination
[Page 191](#)



380V143
EMI Backshell
These self-locking backshells are
available in aluminum or stainless steel
[Page 197](#)




390V091
EMI Environmental
Aluminum or SST. Environmental
[Page 199](#)

Series 806 Mil-Aero Connectors



Series 806 Backshell, Adapter and Strain Relief Selection Guide

"BAND-IN-A-CAN" BANDING ADAPTERS



4470V1061

Composite Band-in-a-Can

Use with Band-Master ATS® shield termination bands. Saddle clamps provide cable strain relief. Non-environmental.

[Page 185](#)




443V039

Aluminum or SST Band-in-a-Can

Use with Band-Master ATS® shield termination bands. Environmentally protected with O-rings.

[Page 201](#)


SIZE #8 CONTACT, EXTENDED LENGTH BACKSHELLS



320V030

Environmental Extended Adapter


[Page 206](#)



440V233

Environmental Banding Backshell

[Page 207](#)



620VS090

Strain Relief Cable Clamp Backshell

[Page 209](#)



440VS232

EMI/RFI Cable Clamp Backshell with Banding Platform

[Page 210](#)



443V042

EMI/RFI Cable Clamp Backshell and Band-in-a-Can Banding Platform

[Page 211](#)

COMPOSITE QWIK-TY



457V048

Composite Qwik-Ty with Drop-In EMI Adapter

Drop-in adapter terminates to cable braid shield.

[Page 185](#)

SHORTING CAP



340VS035

Shorting Backshell

[Page 213](#)

SHRINK BOOTS



809-060

Thin Lip Shrink Boots

[Page 214](#)

Series 806 Mil-Aero Connectors

457V*048 Composite EMI/RFI Qwik-Ty® Strain Relief



Specifications

- Operating temperature: -65° to +200°C (Finish code BN is +175°C)
- Salt spray (corrosion): 2000 hours


Construction

- Drop-in EMI adapter: brass, see ordering info for finish options
- Coupling nut, Qwik-Ty body: high grade engineering thermoplastic, no plating, black
- Anti-decoupling device: high grade engineering thermoplastic
- Shield termination strap: 300 series stainless steel, passivated (not supplied)
- Pad: green fluorosilicone

Low profile. Light weight. Band-Master ATS® shield termination. Self-locking.

Next-generation Qwik-Ty® features high-strength composite construction plus EMI shielding. Available in straight, 45° or 90° versions. Terminate cable shield to plated brass shield termination adapter using Band-Master ATS® strap and hand tool. Attach wire bundle to arm with MS3367-type nylon tie strap (not supplied). Optional rubber pad provides wire cushioning. Slots in shield adapter accept individual shields.

How To Order				
SAMPLE PART NUMBER		457VS048	BM	16
Product	457VS048 = Straight 457VB048 = 45° 457VA048 = 90°			
Finish	BM = Electroless nickel BMT = Nickel/PTFE BN = Olive drab cadmium BZR = Black zinc-nickel			
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24			
Optional Rubber Pad	<i>Omit for no rubber pad.</i> P = Supplied with rubber pad (687-038)			



Band Strap

Band strap is purchased separately.



Micro Band Strap Hand Tool

601-101

Micro Band Ordering Information


Length		Part Number	Max Diameter	
in.	mm.		in.	mm.
5.0	127	601-025	.50	12.7
8.0	203	601-061	.88	22.4
14.0	356	601-065	1.88	47.8

Dimensions


Shell Size	A ISO Metric Thread	ØB Max.	ØC Max.	D Hex	E Max.	G Max.	H Max.	J
09	M12 x 1.0-6H	.65 (16.51)	.86 (21.84)	.75 (19.05)	1.28 (32.51)	1.22 (30.99)	1.14 (28.96)	.178 (4.52)
10	M14 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	1.28 (32.51)	1.29 (32.77)	1.14 (28.96)	.295 (7.49)
11	M15 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	1.28 (32.51)	1.29 (32.77)	1.14 (28.96)	.305 (7.75)
12	M17 x 1.0-6H	.89 (22.61)	1.16 (29.46)	1.00 (25.40)	1.44 (36.58)	1.62 (41.15)	1.14 (28.96)	.394 (10.01)
14	M19 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	1.51 (38.35)	1.66 (42.16)	1.64 (41.66)	.472 (11.99)
16	M22 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	1.51 (38.35)	1.66 (42.16)	1.64 (41.66)	.565 (14.35)
18	M25 x 1.0-6H	1.15 (29.21)	1.41 (35.81)	1.25 (31.75)	1.51 (38.35)	1.72 (43.69)	1.64 (41.66)	.658 (16.71)
20	M28 x 1.0-6H	1.28 (32.51)	1.52 (38.61)	1.38 (35.05)	1.57 (39.88)	1.72 (43.69)	1.74 (44.20)	.777 (19.74)
22	M31 x 1.0-6H	1.41 (35.81)	1.64 (41.66)	1.50 (38.10)	1.71 (43.43)	1.79 (45.47)	1.74 (44.20)	.873 (22.17)
24	M34 x 1.0-6H	1.53 (38.86)	1.77 (44.96)	1.63 (41.40)	1.83 (46.48)	1.85 (46.99)	1.74 (44.20)	.997 (25.32)

Series 806 Mil-Aero Connectors

871V004 Swing-Arm Flex Clamp, EMI Banding Adapter, Composite

Self-Locking**Adapter Code V**

This accessory fits Glenair Series 806 Mil-Aero connectors

FIGURE 1**FINISH CODES NFS, BNS****FIGURE 2****BANDING ADAPTER SLOTS**

Route pigtail shield braid into optional "T" slots in banding adapter.

Shielded, self-locking, adjustable arms. 871V004 Swing-Arm Flex Clamp fits Glenair Series 806 Mil-Aero connectors. Adjustable arms pivot to 0°, 45° or 90° positions. Includes EMI banding adapter with optional "T" slots for pigtailed individual shields. Terminate shield braid to adapter with optional Band-Master ATS® pre-coiled banding strap. Coupling nut has anti-decoupling mechanism for audible detented coupling and prevents backoff under high vibration.



PART NUMBER**871V004****M****22****S****K****Base P/N 871V004****Banding Adapter Material/Finish**

ME Alum/Electroless Nickel
NF Alum/Olive Drab Cadmium
NFS Alum/O.D. Cadmium, selective (fig. 1)
MT Alum/Nickel-PTFE
TZ Alum/Tin-Zinc
BM Brass/Electroless Nickel
BN Brass/Olive Drab Cadmium
BNS Brass/O.D. Cadmium, selective (fig. 1)
BMT Brass/Nickel-PTFE

Shell Size 08 09 10 11 12 14 16 18 20 22 24

Banding Adapter Slots *Omit if not required. See Figure 2*
S "T" Slots in Banding Adapter for Shield Pigtails

Band *Omit if not required.*
K Pre-Coiled Micro Band included With Clamp
J Pre-Coiled Slim Micro Band included With Clamp

DETAIL A**BANDING ADAPTER WITH OPTIONAL T-SLOTS**

Shell Size	A Thread ISO Metric	ø B Min		ø C Max		D Flats		E Max		F Max		G Max		H Max		J Max		K Ref.			
		in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	Max	Min	in	mm
08	M10 x 1.0-6H	.178	4.5	.812	20.6	.750	19.1	1.79	45.5	1.57	39.9	.87	22.1	.96	24.4	1.12	28.4	.393	10.0	.098	2.5
09	M12 x 1.0-6H	.178	4.5	.812	20.6	.750	19.1	1.79	45.5	1.57	39.9	.87	22.1	.96	24.4	1.12	28.4	.393	10.0	.098	2.5
10	M14 x 1.0-6H	.305	7.7	.938	23.8	.875	22.2	1.80	45.7	1.57	39.9	.89	22.6	.96	24.4	1.15	29.2	.455	11.6	.121	3.1
11	M15 x 1.0-6H	.305	7.7	.938	23.8	.875	22.2	1.80	45.7	1.57	39.9	.89	22.6	.96	24.4	1.15	29.2	.455	11.6	.121	3.1
12	M17 x 1.0-6H	.404	10.3	1.125	28.6	1.000	25.4	2.08	52.8	1.88	47.8	1.10	27.9	1.05	26.7	1.44	36.6	.598	15.2	.157	4.0
14	M19 x 1.0-6H	.565	14.4	1.250	31.8	1.125	28.6	2.08	52.8	1.88	47.8	1.16	29.5	1.32	33.5	1.50	38.1	.710	18.0	.210	5.3
16	M22 x 1.0-6H	.565	14.4	1.250	31.8	1.125	28.6	2.08	52.8	1.88	47.8	1.16	29.5	1.32	33.5	1.50	38.1	.710	18.0	.210	5.3
18	M25 x 1.0-6H	.658	16.7	1.375	34.9	1.250	31.8	2.29	58.2	2.13	54.1	1.28	32.5	1.21	30.7	1.68	42.7	.839	21.3	.246	6.2
20	M28 x 1.0-6H	.777	19.7	1.500	38.1	1.375	34.9	2.28	57.9	2.13	54.1	1.35	34.3	1.21	30.7	1.81	46.0	.934	23.7	.277	7.0
22	M31 x 1.0-6H	.877	22.3	1.625	41.3	1.500	38.1	2.75	69.9	2.54	64.5	1.63	41.4	1.37	34.8	2.12	53.8	1.068	27.1	.313	8.0
24	M34 x 1.0-6H	.999	25.4	1.750	44.5	1.625	41.3	2.75	69.9	2.54	64.5	1.67	42.4	1.37	34.8	2.16	54.9	1.197	30.4	.349	8.9

Series 806 Mil-Aero Connectors



871V004 Swing-Arm Flex Clamp, EMI Banding Adapter, Composite

MATERIAL/FINISH

Coupling nut, body, arms, saddles:
polyetherimide (PEI)/ unplated black
Screws, washers, inserts: stainless steel/
passivated
Anti-decoupling springs: thermoplastic
Banding adapter: aluminum alloy or brass
Band (optional): stainless steel/ passivated
Clinch nuts: stainless steel/ silver plated

BAND INFORMATION

Terminate cable braid to band adapter with optional pre-coiled banding strap. Glenair's Band-Master ATS® banding system provides quick, easy, cost-effective and highly reliable termination. Band is passivated stainless steel.



Band



*Micro Band
Tool
601-101*



*Slim Micro
Band Tool
601-122*

Shell Size	Pre-Coiled Micro Band Part No.	Pre-Coiled Slim Micro Band Part No.	Length		Max Diameter	
			in	mm	in	mm
8 - 12	601-061	601-601	8.125	206	.88	22.4
14 - 24	601-065	601-603	14.25	362	1.88	47.8

Series 806 Mil-Aero Connectors

871V006 • Style II Composite Swing-Arm Flex Clamp, Banding Adapter

FOR SERIES 806 MIL-AERO CONNECTORS



Adapter Code **V**

This accessory fits Glenair Series 806 Mil-Aero connectors

TABLE II

DROP-IN BANDING ADAPTER,
THREAD BUSHING
MATERIAL/ FINISH

Aluminum

ME	Electroless Nickel
NF	Olive Drab Cadmium and Electroless Nickel
MT	Nickel-PTFE
TZ	Tin-Zinc
ZR	Black Zinc-Nickel

Brass

BM	Electroless Nickel Cadmium/Olive Drab Over
BNS	Electroless Nickel (See Detail A)
BMT	Nickel-PTFE
BZS	Black Zinc-Nickel (See Detail A)

871V006 Swing-Arm Flex Clamp fits Glenair Series 806 Mil-Aero connectors. Style II accommodates larger cable entry sizes than standard Swing-Arm clamps. Adjustable arms pivot to 0°, 45° or 90° positions. Includes EMI banding adapter with optional "T" slots for pigtailed individual shields. Terminate shield braid to adapter with optional Band-Master ATS® pre-coiled banding strap. Coupling nut has anti-decoupling mechanism for audible detented coupling and prevents backoff under high vibration.

PART NUMBER

	871V006	BM	16	S	J
Base P/N	871V006				
Finish Symbol	See Table II				
Dash Number	09 10 11 12 14 16 18 20 22 24				
Shield Termination Slot	Omit if not required S				
Precoiled Band Option	Omit if not required J Micro Slim band				

BANDING TOOLS AND BANDS

Terminate cable braid to band adapter with optional pre-coiled banding strap. Glenair's Band-Master ATS® banding system provides quick, easy, cost-effective and highly reliable termination. Band is passivated stainless steel.




Shell Size	Pre-Coiled Micro Slim Band Part No.	Length in	Length mm	Max Diameter in	Max Diameter mm
8 - 12	601-601	8.125	206	.88	22.4
14 - 25	601-603	14.25	362	1.88	47.8

Series 806

Mil-Aero Connectors

871V006 • Style II Composite Swing-Arm Flex Clamp, Banding Adapter



Shell Size	A Thread ISO Metric	ØB Min	C Flats		ØD Max	E Max	F Max	G Max	H Max	J Max	K Ref Recommended Cable Range	
			Max	Min							Max	Min
09	M12 x 1.0-6H	0.305 (7.75)	0.875 (22.23)	0.860 (21.84)	0.938 (23.83)	1.90 (48.26)	1.67 (42.42)	0.89 (22.61)	1.06 (26.92)	1.15 (29.21)	0.455 (11.56)	0.121 (3.07)
10	M14 x 1.0-6H	0.404 (10.26)	1.000 (25.40)	0.980 (24.89)	1.125 (28.58)	2.18 (55.37)	1.98 (50.29)	1.10 (27.94)	1.15 (29.21)	1.44 (36.58)	0.598 (15.19)	0.157 (3.99)
11	M15 x 1.0-6H	0.404 (10.26)	1.000 (25.40)	0.980 (24.89)	1.125 (28.58)	2.18 (55.37)	1.98 (50.29)	1.10 (27.94)	1.15 (29.21)	1.44 (36.58)	0.598 (15.19)	0.157 (3.99)
12	M17 x 1.0-6H	0.526 (13.36)	1.125 (28.58)	1.100 (27.94)	1.250 (31.75)	2.18 (55.37)	1.98 (50.29)	1.16 (29.46)	1.15 (29.21)	1.50 (38.10)	0.710 (18.03)	0.210 (5.33)
14	M19 x 1.0-6H	0.565 (14.35)	1.125 (28.58)	1.100 (27.94)	1.250 (31.75)	2.18 (55.37)	1.98 (50.29)	1.16 (29.46)	1.15 (29.21)	1.50 (38.10)	0.710 (18.03)	0.210 (5.33)
16	M22 x 1.0-6H	0.658 (16.71)	1.250 (31.75)	1.224 (31.09)	1.375 (34.93)	2.39 (60.71)	2.23 (56.64)	1.28 (32.51)	1.31 (33.27)	1.68 (42.67)	0.839 (21.31)	0.246 (6.25)
18	M25 x 1.0-6H	0.777 (19.74)	1.375 (34.93)	1.348 (34.24)	1.500 (38.10)	2.39 (60.71)	2.23 (56.64)	1.35 (34.29)	1.31 (33.27)	1.81 (45.97)	0.934 (23.72)	0.277 (7.04)
20	M28 x 1.0-6H	0.877 (22.28)	1.500 (38.10)	1.469 (37.31)	1.625 (41.28)	2.85 (72.39)	2.64 (67.06)	1.63 (41.40)	1.47 (37.34)	2.12 (53.85)	1.068 (27.13)	0.313 (7.95)
22	M31 x 1.0-6H	0.999 (25.37)	1.625 (41.28)	1.581 (40.16)	1.750 (44.45)	2.85 (72.39)	2.64 (67.06)	1.67 (42.42)	1.47 (37.34)	2.16 (54.86)	1.197 (30.40)	0.349 (8.86)
24	M34 x 1.0-6H	1.127 (28.63)	1.750 (44.45)	1.690 (42.93)	1.875 (47.63)	3.06 (77.72)	2.85 (72.39)	1.84 (46.74)	1.56 (39.62)	2.41 (61.21)	1.323 (33.60)	0.380 (9.65)

**Features**

- Corrosion resistant high strength engineering thermoplastic
- Self-locking spin coupling
- Non-environmental

Specifications

- Operating temperature:
codes XB, XM, XMT: -65°C to +200°C
codes XZN, XW: -65°C to +175°C
- Salt spray (corrosion): 2000 hours
- Vibration: SAE AS85049 Category 4C
- Shock: SAE AS85049 Category 4C

Construction


- Adapter: high grade engineering thermoplastic. See How to Order for finish options
- Coupling nut, saddle clamps: high grade engineering thermoplastic, no plating, black
- Hardware: stainless steel, passivated
- Anti-Rotation Device: high grade engineering thermoplastic

Notes

1. Cable entry measured with saddle clamps closed and bottomed on clamp ears.

Lightweight. Straight, 45° or 90°. Composite. Self-Locking. Spin coupling backshell with full radius cable clamp provides protection for open wire bundles or jacketed cable. Compatible with Glenair Series 806 micro miniature circular connectors.

How To Order			
SAMPLE PART NUMBER			
	620VS081	XM	12
Product	620VS081 = Cable Clamp, Straight 620VB081 = Cable Clamp, 45° 620VA081 = Cable Clamp, 90°		
Adapter Finish	XB = Unplated (black) XM = Electroless nickel XMT = Nickel/PTFE XW = Olive Drab Cadmium XZN = Zinc nickel (black) Coupling nut and saddle clamps are unplated black thermoplastic		
Shell Size	08 09 10 11 12 14 16 18 20 22 24		



Shell Size	A ISO Metric Thd	ØB Max.	ØC Max.	D Hex	E Ref.	F	G	H	J	K Max.	M
08	M10 x 1.0-6H	.65 (16.51)	.86 (21.84)	.75 (19.05)	.63 (16.00)	.86 (21.84)	.88 (22.35)	.88 (22.35)	.80 (20.32)	1.32 (33.53)	.218 (5.54)
09	M12 x 1.0-6H	.65 (16.51)	.86 (21.84)	.75 (19.05)	.63 (16.00)	.86 (21.84)	.88 (22.35)	.88 (22.35)	.80 (20.32)	1.32 (33.53)	.218 (5.54)
10	M14 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	.65 (16.51)	.91 (23.11)	.94 (23.88)	.94 (23.88)	.88 (22.35)	1.35 (34.29)	.264 (6.71)
11	M15 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	.65 (16.51)	.91 (23.11)	.94 (23.88)	.94 (23.88)	.88 (22.35)	1.35 (34.29)	.264 (6.71)
12	M17 x 1.0-6H	.89 (22.61)	1.16 (29.46)	1.00 (25.40)	.71 (18.03)	1.02 (25.91)	1.03 (26.16)	1.17 (29.72)	1.00 (25.40)	1.43 (36.32)	.345 (8.76)
14	M19 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	.76 (19.30)	1.13 (28.70)	1.13 (28.70)	1.28 (32.51)	1.00 (25.40)	1.48 (37.59)	.461 (11.71)
16	M22 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	.76 (19.30)	1.13 (28.70)	1.13 (28.70)	1.28 (32.51)	1.00 (25.40)	1.48 (37.59)	.461 (11.71)
18	M25 x 1.0-6H	1.15 (29.21)	1.41 (35.81)	1.25 (31.75)	.80 (20.32)	1.26 (32.00)	1.31 (33.27)	1.41 (35.81)	1.13 (28.70)	1.58 (40.13)	.544 (13.82)
20	M28 x 1.0-6H	1.28 (32.51)	1.52 (38.61)	1.38 (35.05)	.83 (21.08)	1.31 (33.27)	1.38 (35.05)	1.50 (38.10)	1.19 (30.23)	1.70 (43.18)	.614 (15.60)
22	M31 x 1.0-6H	1.41 (35.81)	1.64 (41.66)	1.50 (38.10)	.90 (22.86)	1.37 (34.80)	1.50 (38.10)	1.56 (39.62)	1.25 (31.75)	1.74 (44.20)	.697 (17.70)
24	M34 x 1.0-6H	1.53 (38.86)	1.77 (44.96)	1.63 (41.40)	.94 (23.88)	1.45 (36.83)	1.63 (41.40)	1.69 (42.93)	1.38 (35.05)	1.79 (45.47)	.780 (19.81)

Series 806 Mil-Aero Connectors

387V*243 Composite EMI/RFI Cable Clamp Backshell with Boot Groove



Features

- Corrosion resistant high strength engineering thermoplastic
- Self-locking spin coupling
- Non-environmental
- Three shield ferrules

Specifications

- Operating temperature: codes XM, XMT: -65°C to +200°C
codes XW: -65°C to +175°C
- Salt spray (corrosion): 2000 hours
- Vibration: SAE AS85049 Category 4C
- Shock: SAE AS85049 Category 4C

Construction

- Adapter: high grade engineering thermoplastic. See How to Order for finish options
- Coupling nut, saddle clamps, clamp body: high grade engineering thermoplastic, no plating, black
- Ferrules: aluminum alloy. See How to Order for finish options.
- Hardware: stainless steel, passivated
- Anti-decoupling device: high grade engineering thermoplastic

Notes

1. Cable entry is measured with the saddle clamps closed and bottomed on clamp ears.

Table 1 Cable Entry Code

Cable Entry Code	Cable Entry ± .039 (1.0)		G Max.	
	In.	mm.	In.	mm.
04	.312	7.9	1.125	28.6
06	.437	11.1	1.250	31.8
08	.500	12.7	1.312	33.3
10	.625	15.9	1.438	36.5
12	.750	19.1	1.625	41.3
14	.874	22.2	1.688	42.9
16	.937	23.8	1.750	44.5
17	1.094	27.8	1.906	48.5

Composite. Straight or 90°. Shielded. Self-Locking. Corrosion-resistant EMI backshell features high-strength thermoplastic construction. Aluminum alloy shield termination rings. Self-locking coupling ring and cable clamp screws. Nickel, cadmium, or nickel-PTFE finish.

How To Order

SAMPLE PART NUMBER	387VS243	XM	12	06	-4
Product	387VS243 = Straight Adapter 387VW243 = 90° Adapter				
Material/ Finish	XM = Electroless nickel XMT = Nickel/PTFE XW = Olive Drab Cadmium				
Shell Size	08 09 10 11 12 14 16 18 20 22 24				
Cable Entry Code	See Table 1 for cable entry sizes				
Adapter Length	Omit for 90° version. Applicable to 387VS243 only. Length in ¼ inch increments: 4 = 1 inch (min.) 5 = 1.25 inches 6 = 1.5 inches 8 = 2 inches				




Table 2 Dimensions

Shell Size	A ISO Metric Thread	øB Max.		øC Max.		D Hex		E ± .078 (2.0)		F ± .078 (2.0)		Max. Cable Entry
		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	
08	M10 x 1.0-6H	.65	16.5	.86	21.8	.75	19.1	.722	18.3	1.750	44.4	04
09	M12 x 1.0-6H	.65	16.5	.86	21.8	.75	19.1	.722	18.3	1.750	44.4	04
10	M14 x 1.0-6H	.77	19.5	.98	24.9	.88	22.2	.784	19.9	1.820	46.2	06
11	M15 x 1.0-6H	.77	19.5	.98	24.9	.88	22.2	.784	19.9	1.820	46.2	06
12	M17 x 1.0-6H	.89	22.6	1.16	29.5	1.00	25.4	.816	20.7	1.860	47.2	08
14	M19 x 1.0-6H	1.03	26.2	1.28	32.5	1.13	28.6	.878	22.3	1.880	47.8	10
16	M22 x 1.0-6H	1.03	26.2	1.28	32.5	1.13	28.6	.878	22.3	1.880	47.8	10
18	M25 x 1.0-6H	1.15	29.2	1.41	35.8	1.25	31.8	.942	23.9	1.942	49.3	12
20	M28 x 1.0-6H	1.28	32.5	1.52	38.6	1.38	34.9	1.003	25.5	2.000	50.8	14
22	M31 x 1.0-6H	1.41	35.8	1.64	41.7	1.50	38.1	1.037	26.3	2.062	52.4	16
24	M34 x 1.0-6H	1.53	38.9	1.77	45.0	1.63	41.3	1.116	28.3	2.194	55.7	17


Series 806 Mil-Aero Connectors



440V*202 Composite EMI/RFI Banding Adapter with Boot Groove



Lightweight. Corrosion-resistant composite. Band-Master ATS® shield termination. Self-locking. Integral Qwik-Ty. Spin coupling EMI/RFI adapter with anti-decoupling ratchet prevents loosening under vibration. Fits Series 806 connectors. Terminate cable shield to backshell with **Band-Master ATS®** stainless steel band. Compatible with Glenair Series 77 lipped heatshrink boots. Straight, 45° or 90° cable exit.



Features

- EMI/RFI
- Self-locking spin coupling
- Integral Qwik-Ty® strain relief

Specifications

- Operating temperature:
codes XM, XMT: -65°C to +200°C
codes XW: -65°C to +175°C
- Salt spray (corrosion): 2000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Adapter: high grade engineering thermoplastic with electroless nickel (code XM), nickel-PTFE (XMT) or olive drab cadmium (XW)
- Coupling nut: high grade engineering thermoplastic, no plating, black
- Anti-decoupling device: high grade engineering thermoplastic
- Shield termination strap: 300 series stainless steel, passivated

Notes

- If drain holes are supplied, the O-ring is deleted.

Shrink Boot Options

- Consult factory for shrink boot options.

How To Order						
SAMPLE PART NUMBER		440VS202	XM	14	09	
Product	440VS202 = Straight Adapter 440VT202 = 45° Adapter 440VA202 = 90° Adapter					
Finish	XM = Electroless nickel XMT = Nickel/PTFE XW = Olive Drab Cadmium					
Shell Size	08 09 10 11 12 14 16 18 20 22 24					
Entry Code	Shell Size	Entry Code	Diameter			
			In.	mm.		
	08, 09, 10, 11	04	.25	6.4		
	10, 11, 18	05	.31	7.9		
	12, 20	07	.44	11.2		
	14, 16, 22	09	.56	14.2		
	18, 24	11	.68	17.3		
	20	13	.81	20.6		
	22	15	.94	23.9		
	24	16	1.00	25.4		
Optional Drain Holes	Omit for no drain holes. D = Adapter supplied with coupling nut drain holes					
Optional Band Strap	Omit for no band strap. B = Adapter supplied with shield termination band					
Optional Shield Termination Slots	Omit for unslotted version. S = Adapter supplied with shield termination slots					

Series 806 Mil-Aero Connectors

440V*202 Composite EMI/RFI Banding Adapter






Table 1 Dimensions

Shell Size	Available Entry Codes	A ISO Metric Thread	ØB Max.		ØC Max.		D Hex		L ± .09 (2.3)		M ± .09 (2.3)		N Max.	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
08	04	M10 x 1.0-6H	.65	16.5	.86	21.8	.75	19.1	.69	17.5	.88	22.4	1.36	34.5
09	04	M12 x 1.0-6H	.65	16.5	.86	21.8	.75	19.1	.69	17.5	.88	22.4	1.36	34.5
10	04, 05	M14 x 1.0-6H	.77	19.5	.98	24.9	.88	22.2	.75	19.1	1.00	25.4	1.42	36.1
11	04, 05	M15 x 1.0-6H	.77	19.5	.98	24.9	.88	22.2	.75	19.1	1.00	25.4	1.42	36.1
12	07	M17 x 1.0-6H	.89	22.6	1.16	29.5	1.00	25.4	.81	20.6	1.13	28.7	1.48	37.6
14	09	M19 x 1.0-6H	1.03	26.2	1.28	32.5	1.13	28.6	.88	22.4	1.13	28.7	1.48	37.6
16	09	M22 x 1.0-6H	1.03	26.2	1.28	32.5	1.13	28.6	.88	22.4	1.31	33.3	1.55	39.4
18	05, 11	M25 x 1.0-6H	1.15	29.2	1.41	35.8	1.25	31.8	.94	23.9	1.38	35.1	1.61	40.9
20	07, 13	M28 x 1.0-6H	1.28	32.5	1.52	38.6	1.38	34.9	.97	24.6	1.44	36.6	1.64	41.7
22	09, 15	M31 x 1.0-6H	1.41	35.8	1.64	41.7	1.50	38.1	1.06	26.9	1.63	41.4	1.73	43.9
24	11, 15	M34 x 1.0-6H	1.53	38.9	1.77	45.0	1.63	41.3	1.13	28.7	1.75	44.5	1.80	45.7

Table 2 Entry Codes and Qwik-Ty Dimensions

Entry Code	ØE ± .03 (0.8)		F		G		H		J ± .06 (1.5)		K ± .09 (2.3)	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
04	.25	6.4	.187	4.74	.312	7.92	.512	13.0	.72	18.3	.87	22.1
05	.31	7.9	.187	4.74	.312	7.92	.512	13.0	.75	19.1	.93	23.6
07	.44	11.2	.187	4.74	.312	7.92	.512	13.0	.75	19.1	1.00	25.4
09	.56	14.2	.219	5.56	.375	9.53	.630	16.0	.76	19.3	1.03	26.2
11	.68	17.3	.219	5.56	.375	9.53	.630	16.0	.78	19.8	1.05	26.7
13	.81	20.6	.219	5.56	.375	9.53	.630	16.0	.79	20.1	1.06	26.9
15	.94	23.9	.219	5.56	.375	9.53	.630	16.0	.82	20.8	1.09	27.7
16	1.00	25.4	.219	5.56	.375	9.53	.630	16.0	.86	21.8	1.13	28.7



**Corrosion-resistant. Self-locking. Shielded. Saddle clamp. Band termination.**

EMI/RFI "band-in-a-can" backshell fits Series 806 connectors. Terminate cable shield to backshell with optional **Band-Master ATS®** stainless steel band. Coupling nut and cable clamp are black composite material, adapter is plated with conductive nickel, nickel-PTFE or olive drab cadmium. Non-environmental. Straight, 45° or 90°.

Specifications

- Operating temperature:
codes XM, XMT: -65°C to +200°C
code XW: -65°C to +175°C
- Salt spray (corrosion): 2000 hours

Construction

- Coupling nut, cable clamp, thread ring: high grade engineering thermoplastic, no plating, black
- Adapter body: high grade engineering thermoplastic, see ordering information for finish options.
- Hardware: 300 series stainless steel
- Anti-decoupling device: thermoplastic
- Band strap: stainless steel, passivated

How To Order

SAMPLE PART NUMBER		4470VS1061	XM	10	12	B	S
Product	4470VS1061	Straight Backshell					
	4470VT1061	45° Backshell					
	4470VW1061	90° Backshell					
Finish	XM = Electroless nickel XMT = Nickel/PTFE XW = Olive Drab Cadmium						
Shell Size	08 09 10 11 12 14 16 18 20 22 24						
Entry Code	See Table 1 for cable entry codes						
Band Option	Omit for none. B = Band (601-040) K = Pre-coiled band (601-041)						
Slot Option	Omit for none. S = slotted band platform for pigtail braid termination						

Band-Master Bands and Tool

Band strap can be ordered with backshell or purchased separately.

**Standard Band Ordering Information**


Length		Part Number		Max Dia.	
in.	mm.	Flat	Pre-Coiled	in.	mm.
9.0	229	601-005	601-006	1.0	25
14.0	356	601-040	601-041	1.8	48
18.0	457	601-049	601-050	2.5	64

Band Strap Hand Tool

601-100

**Table 1 Entry Code**


Entry Code	Shell Size	Entry Dia. ± .03 (0.8)	Clamp Closed ± .03 (0.8)	K ± .06 (1.5)
10	08 thru 24	.22 (5.59)	.26 (6.60)	.94 (23.88)
12	10 thru 24	.28 (7.11)	.34 (8.64)	1.17 (29.72)
14	12 thru 24	.34 (8.64)	.46 (11.68)	1.28 (32.51)
16	14 thru 24	.46 (11.68)	.55 (13.97)	1.41 (35.81)
18	18 thru 24	.55 (13.97)	.62 (15.75)	1.50 (38.10)
20	18 thru 24	.62 (15.75)	.70 (17.78)	1.56 (39.62)
22	22, 24	.70 (17.78)	.78 (19.81)	1.69 (42.93)
24	24	.78 (19.81)	.85 (21.59)	1.81 (45.97)




Series 806

Mil-Aero Connectors


4470V*1061 Composite EMI/RFI Band-in-a-Can Backshell



4470VS1061
STRAIGHT



4470VT1061
45°



4470VW1061
90°

Shell Size	Max Entry Code	A ISO Metric Thread	ØB Max.	ØC Max.	D Hex	E ± .06 (1.5)	F ± .09 (2.3)	G Max.	H ± .06 (1.5)	J ± .09 (2.3)
08	10	M10 x 1.0-6H	.65 (16.51)	.86 (21.84)	.75 (19.05)	.69 (17.53)	.88 (22.35)	1.31 (33.27)	.72 (18.29)	1.15 (29.21)
09	10	M12 x 1.0-6H	.65 (16.51)	.86 (21.84)	.75 (19.05)	.69 (17.53)	.88 (22.35)	1.31 (33.27)	.72 (18.29)	1.15 (29.21)
10	12	M14 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	.75 (19.05)	1.00 (25.40)	1.42 (36.07)	.75 (19.05)	1.27 (32.26)
11	12	M15 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	.75 (19.05)	1.00 (25.40)	1.42 (36.07)	.75 (19.05)	1.27 (32.26)
12	14	M17 x 1.0-6H	.89 (22.61)	1.16 (29.46)	1.00 (25.40)	.81 (20.57)	1.13 (28.70)	1.57 (39.88)	.75 (19.05)	1.33 (33.78)
14	16	M19 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	.88 (22.35)	1.31 (33.27)	1.57 (39.88)	.76 (19.30)	1.37 (34.80)
16	16	M22 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	.88 (22.35)	1.31 (33.27)	1.57 (39.88)	.76 (19.30)	1.37 (34.80)
18	20	M25 x 1.0-6H	1.15 (29.21)	1.41 (35.81)	1.25 (31.75)	.94 (23.88)	1.38 (35.05)	1.64 (41.66)	.78 (19.81)	1.39 (35.31)
20	20	M28 x 1.0-6H	1.28 (32.51)	1.52 (38.61)	1.38 (35.05)	.97 (24.64)	1.44 (36.58)	1.73 (43.94)	.79 (20.07)	1.41 (35.81)
22	22	M31 x 1.0-6H	1.41 (35.81)	1.64 (41.66)	1.50 (38.10)	1.06 (26.92)	1.63 (41.40)	1.82 (46.23)	.82 (20.83)	1.43 (36.32)
24	24	M34 x 1.0-6H	1.53 (38.86)	1.77 (44.96)	1.63 (41.40)	1.13 (28.70)	1.75 (44.45)	1.82 (46.23)	.86 (21.84)	1.47 (37.34)

**Specifications**




- Operating temperature: -55° to +125°C
- Salt spray (corrosion): 2000 hours

Construction

- Drop-in EMI adapter: brass, see ordering info for finish options
- Coupling nut, adapter: high grade engineering thermoplastic, no plating, black
- Anti-decoupling device: high grade engineering thermoplastic
- Shield termination strap: 300 series stainless steel, passivated
- O-ring: silicone
- Adhesive: W1 hot melt polyamide, 125°C max. operating temperature

Labor-saving. Environmental. Shielded. Self-locking. "Piggyback" boot adapters reduce installation time compared to conventional heatshrink boots. Supplied as shown with the boot already installed on adapter. Terminate cable shield to plated brass shield termination adapter using Band-Master ATS® strap and hand tool. Boot is pre-coated with "W1" hot melt adhesive. These adapters fit Glenair Series 806 micro miniature circular connectors.

How To Order						
SAMPLE PART NUMBER		317VS111	BM	12	-1	K
Product	317VS111 = Straight Adapter 317VB111 = 45° Adapter 317VA111 = 90° Adapter					
Finish	BM = Electroless nickel BMT = Nickel/PTFE BN = Olive drab cadmium BZR = Black zinc-nickel					
Shell Size	09 10 11 12 14 16 18 20 22 24					
Boot Material	1 = High performance elastomer 2 = Low smoke zero halogen polyolefin					
Optional Band Strap	Omit for no band strap. K = Adapter supplied with pre-coiled shield termination band					

45°
317VB11190°
317VA111**Band Strap**

Band strap can be ordered with backshell or purchased separately.

**Band Strap Hand Tool****601-101****Micro Band Ordering Information**

Length	Part Number	Max Diameter
5.0 (127.00)	601-025	.50 (12.70)
8.0 (203.20)	601-061	.88 (22.35)
14.0 (355.60)	601-065	1.88 (47.75)


Shell Size	A ISO Metric Thread	ØB Max.	ØC Max.	D Hex	ØG	M Min.	N Max.
09	M12 x 1.0-6H	.65 (16.51)	.86 (21.84)	.75 (19.05)	.178 (4.52)	.250 (6.35)	.197 (5.00)
10	M14 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	.295 (7.49)	.355 (9.02)	.197 (5.00)
11	M15 x 1.0-6H	.77 (19.56)	.98 (24.89)	.88 (22.35)	.305 (7.75)	.355 (9.02)	.197 (5.00)
12	M17 x 1.0-6H	.89 (22.61)	1.16 (29.46)	1.00 (25.40)	.394 (10.01)	.491 (12.47)	.236 (5.99)
14	M19 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	.472 (11.99)	.565 (14.35)	.236 (5.99)
16	M22 x 1.0-6H	1.03 (26.16)	1.28 (32.51)	1.13 (28.70)	.565 (14.35)	.565 (14.35)	.236 (5.99)
18	M25 x 1.0-6H	1.15 (29.21)	1.41 (35.81)	1.25 (31.75)	.658 (16.71)	.690 (17.53)	.276 (7.01)
20	M28 x 1.0-6H	1.28 (32.51)	1.52 (38.61)	1.38 (35.05)	.777 (19.74)	.769 (19.53)	.335 (8.51)
22	M31 x 1.0-6H	1.41 (35.81)	1.64 (41.66)	1.50 (38.10)	.873 (22.17)	.894 (22.71)	.394 (10.01)
24	M34 x 1.0-6H	1.53 (38.86)	1.77 (44.96)	1.63 (41.40)	.997 (25.32)	1.019 (25.88)	.394 (10.01)

Series 806 Mil-Aero Connectors

380V*143 Metal EMI/RFI Full Radius Profile Backshell



EMI shielding. Self-locking. Straight, 45° or 90°. Non-environmental. 380-143 backshells fit Glenair Series 806 connectors. These spin coupling backshells have ground rings for cable braid shield termination. Heavy duty-saddle clamp with stainless steel telescoping screws. Meets requirements of AS85049 Category 3C medium duty. Aluminum or stainless steel.



Features


- EMI/RFI protected
- Self-locking spin coupling
- Telescoping clamp screws
- Non-environmental

Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT, Z1: 1000 hours
- Vibration: SAE AS85049 Category 3C
- Shock: SAE AS85049 Category 3C

Construction

- Coupling nut, adapter, ferrules, clamps: see material/finish codes
- Anti-decoupling device: corrosion-resistant material
- Hardware: stainless steel, passivated



How To Order						
SAMPLE PART NUMBER		380VS143	ME	12	06	H 4
Product	380VS143 = EMI Backshell, Straight 380VM143 = EMI Backshell, 45° 380VN143 = EMI Backshell, 90°					
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium TZ = Alum/Tin-Zinc Z1 = Stainless Steel, Passivated					
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24					
Cable Clamp Size	See Table 1 for cable clamp sizes					
Strain Relief Clamp	H = Saddle bar clamp, heavy duty, with telescoping screws					
Backshell Length	Omit for 45° and 90° versions. Applicable to 380VS143 only. Length in ½ inch increments: 3 = 1½ inches (min. for Style 1 shown at right) 4 = 2 inches (min. for Style 2 shown on following page) 5 = 2½ inches 6 = 3 inches					






Table 1 Cable Clamp Size								
Clamp Size	Cable Range				T Max.		V Max.	
	Min.		Max.					
	In.	mm.	In.	mm.	In.	mm.	In.	mm.
03	.125	3.2	.250	6.4	.780	19.8	.957	24.3
04	.125	3.2	.312	7.9	.780	19.8	.957	24.3
06	.250	6.4	.437	11.1	.780	19.8	1.145	29.1
08	.312	7.9	.562	14.3	.780	19.8	1.332	33.8
10	.350	8.9	.625	15.9	.780	19.8	1.332	33.8
12	.500	12.7	.750	19.1	.811	20.6	1.551	39.4
16	.625	15.9	.937	23.8	.905	23.0	1.770	45.0
20	.875	22.2	1.250	31.8	1.092	27.7	2.113	53.7
24	1.000	25.4	1.375	34.9	1.124	28.5	2.363	60.0
28	1.250	31.8	1.625	41.3	1.399	35.5	2.770	70.4
32	1.437	36.5	1.875	47.6	1.399	35.5	3.020	76.7

380VS143


Straight Exit

**380VM143**

45° Exit

**380VN143**

90° Exit




Shell Size	A ISO Metric Thread	øD Max.	K Max. ⁽¹⁾	L Max.	M Max. ⁽¹⁾	N Max.	Max. Clamp Size ⁽¹⁾	Max. Cable Dia. ⁽¹⁾
07	M8 x 1.0-6H	.58 (0.02)	.790 (0.03)	1.070 (0.04)	.940 (0.04)	1.230 (0.05)	03 (0.12)	.250 (0.01)
08	M10 x 1.0-6H	.64 (0.03)	.790 (0.03)	1.070 (0.04)	.940 (0.04)	1.230 (0.05)	03 (0.12)	.250 (0.01)
09	M12 x 1.0-6H	.74 (0.03)	.790 (0.03)	1.070 (0.04)	.940 (0.04)	1.230 (0.05)	04 (0.16)	.312 (0.01)
10	M14 x 1.0-6H	.80 (0.03)	.790 (0.03)	1.130 (0.04)	.970 (0.04)	1.320 (0.05)	04 (0.16)	.312 (0.01)
11	M15 x 1.0-6H	.84 (0.03)	.790 (0.03)	1.130 (0.04)	.970 (0.04)	1.320 (0.05)	06 (0.24)	.437 (0.02)
12	M17 x 1.0-6H	.92 (0.04)	.830 (0.03)	1.210 (0.05)	1.040 (0.04)	1.420 (0.06)	06 (0.24)	.437 (0.02)
14	M19 x 1.0-6H	1.02 (0.04)	.830 (0.03)	1.210 (0.05)	1.040 (0.04)	1.420 (0.06)	08 (0.31)	.562 (0.02)
16	M22 x 1.0-6H	1.16 (0.05)	.840 (0.03)	1.280 (0.05)	1.080 (0.04)	1.520 (0.06)	10 (0.39)	.625 (0.02)
18	M25 x 1.0-6H	1.26 (0.05)	.890 (0.04)	1.360 (0.05)	1.140 (0.04)	1.620 (0.06)	12 (0.47)	.750 (0.03)
20	M28 x 1.0-6H	1.40 (0.06)	.920 (0.04)	1.430 (0.06)	1.210 (0.05)	1.710 (0.07)	16 (0.63)	.937 (0.04)
22	M31 x 1.0-6H	1.52 (0.06)	.950 (0.04)	1.490 (0.06)	1.280 (0.05)	1.810 (0.07)	16 (0.63)	.937 (0.04)
24	M34 x 1.0-6H	1.64 (0.06)	.980 (0.04)	1.550 (0.06)	1.330 (0.05)	1.910 (0.08)	16 (0.63)	.937 (0.04)

(1) If the maximum clamp size is exceeded, the backshell will be a "Style 2" with a transition adapter as shown below. The K and M dimensions will be increased by 1.00 inch (25.4 mm.) maximum.

Style 2 Backshells for Large Diameter Cables

If the cable clamp is larger than the maximum clamp size shown in the table above, the backshell will be supplied with a **transition adapter** and a second coupling nut. This type of backshell is called a **Style 2**. The large diameter of the Style 2 backshell allows it to slide over the cable until the connector is wired and ready for backshell installation. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.


**Style 2 Backshell**

Series 806 Mil-Aero Connectors

390V*091 Metal EMI/RFI Full Radius Environmental Backshell



EMI shielding. Environmental. Self-locking. Straight, 45° or 90°. For use with shielded, jacketed cable. Compatible with Series 806 micro miniature connectors. Terminate cable shield to inner and outer ground rings. Heavy duty cable clamps. Aluminum or stainless steel with silicone O-rings and gland. Stainless steel telescoping clamp screws. Meets environmental, electrical and mechanical requirements of AS85049 Category 1A Heavy Duty.



Features


- EMI/RFI protected
- Self-locking spin coupling
- Telescoping clamp screws
- Environmental

Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT, Z1: 1000 hours
- Vibration: SAE AS85049 Category 1A
- Shock: SAE AS85049 Category 1A
- Water pressure: SAE AS85049 Cat. 1A

Construction

- Coupling nut, adapters, ferrules, clamps, follower: see material/finish codes
- O-rings, grommet: silicone
- Anti-decoupling device: corrosion-resistant material
- Hardware: stainless steel, passivated



How To Order

SAMPLE PART NUMBER		390VS091	ME	12	06	H	4
Product	390VS091 = Straight Backshell 390VM091 = 45° Backshell 390VN091 = 90° EMI Backshell						
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium Z1 = Stainless Steel, Passivated						
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24						
Cable Clamp Size	See Table 1 for cable clamp sizes						
Strain Relief Clamp	H = Saddle bar clamp, heavy duty, with telescoping screws						
Backshell Length	Omit for 45° and 90° versions. Applicable to 390VS091 only. Length in 1/2 inch increments: 3 = 1 1/2 inches (min. for Style 1) 4 = 2 inches (min. for Style 2) 5 = 2 1/2 inches 6 = 3 inches						





Table 1: Cable Clamp Size

Clamp Size	Cable Range				A Thread Class 2B	B Max.		C Max.	
	Min. In.	Max. In.	Min. mm.	Max. mm.		In.	mm.	In.	mm.
04	.125	.312	3.2	7.9	.625-24UNEF	1.301	33.04	.957	24.3
06	.250	.437	6.4	11.1	.750-20UNEF	1.301	33.04	1.145	29.1
08	.312	.562	7.9	14.3	.875-20UNEF	1.301	33.04	1.332	33.8
10	.350	.625	8.9	15.9	1.000-20UNEF	1.301	33.04	1.332	33.8
12	.500	.750	12.7	19.1	1.1875-18UNEF	1.332	33.83	1.551	39.4
16	.625	.937	15.9	23.8	1.4375-18UNEF	1.426	36.22	1.770	45.0
20	.875	1.250	22.2	31.8	1.750-18UNS	1.613	40.97	2.113	53.7
24	1.000	1.375	25.4	34.9	2.000-18UNS	1.645	41.78	2.363	60.0




Shell Size	A ISO Metric Thread	ØC Max.	K Max. ⁽¹⁾	L Max.	M Max. ⁽¹⁾	N Max.	Clamp Dash Number ⁽¹⁾	Max. Cable Dia. ⁽¹⁾
07	M8 x 1.06H	.640 (16.26)	.790 (20.07)	1.070 (27.18)	.940 (23.88)	1.290 (32.77)	03	.250 (6.35)
08	M10 x 1.06H	.710 (18.03)	.790 (20.07)	1.070 (27.18)	.940 (23.88)	1.290 (32.77)	03	.250 (6.35)
09	M12 x 1.0-6H	.780 (19.81)	.790 (20.07)	1.070 (27.18)	.940 (23.88)	1.290 (32.77)	04	.312 (7.92)
10	M14 x 1.0-6H	.880 (22.35)	.790 (20.07)	1.130 (28.70)	.970 (24.64)	1.380 (35.05)	04	.312 (7.92)
11	M15 x 1.0-6H	.920 (23.37)	.790 (20.07)	1.130 (28.70)	.970 (24.64)	1.380 (35.05)	06	.437 (11.10)
12	M17 x 1.0-6H	1.000 (25.40)	.830 (21.08)	1.210 (30.73)	1.040 (26.42)	1.480 (37.59)	06	.437 (11.10)
14	M19 x 1.0-6H	1.080 (27.43)	.830 (21.08)	1.210 (30.73)	1.040 (26.42)	1.480 (37.59)	08	.562 (14.27)
16	M22 x 1.0-6H	1.200 (30.48)	.840 (21.34)	1.280 (32.51)	1.080 (27.43)	1.580 (40.13)	10	.625 (15.88)
18	M25 x 1.0-6H	1.320 (33.53)	.890 (22.61)	1.360 (34.54)	1.140 (28.96)	1.680 (42.67)	12	.750 (19.05)
20	M28 x 1.0-6H	1.440 (36.58)	.920 (23.37)	1.430 (36.32)	1.210 (30.73)	1.770 (44.96)	16	.937 (23.80)
22	M31 x 1.0-6H	1.560 (39.62)	.950 (24.13)	1.490 (37.85)	1.280 (32.51)	1.870 (47.50)	16	.937 (23.80)
24	M34 x 1.0-6H	1.700 (43.18)	.980 (24.89)	1.550 (39.37)	1.330 (33.78)	1.970 (50.04)	16	.937 (23.80)

(1) If the maximum clamp size is exceeded, the backshell will be a "Style 2" with a transition adapter as shown below. The K and M dimensions will be increased by 1.00 inch (25.4 mm.) maximum.

Style 2 Backshells for Large Diameter Cables

If the cable clamp is larger than the maximum clamp size shown in the table above, the backshell will be supplied with a **transition adapter** and a second coupling nut. This type of backshell is called a **Style 2**. The large diameter of the Style 2 backshell allows it to slide over the cable until the connector is wired and ready for backshell installation. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.



Series 806 Mil-Aero Connectors

443V*039 Metal EMI/RFI Band-in-a-Can Backshell Cable Clamp



EMI shielding. Band-Master ATS® shield termination. Self-locking. Environmental. Spin coupling EMI/RFI backshell with anti-decoupling ratchet prevents loosening under vibration. Fits Series 806 connectors. Terminate cable shield to backshell with **Band-Master ATS®** stainless steel band, supplied with backshell. Cable clamp grommet provides environmental seal to cable jacket. Straight, 45° or 90° cable exit. Aluminum or stainless steel.

Features



- EMI/RFI
- Self-locking spin coupling
- Supplied with MicroBand shield termination band
- Environmental


Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF, NFP: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME, NFP: 96 hours
Code NF, ZR, MT, Z1: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Coupling nut, adapter, saddle bars, cable clamp: aluminum alloy or 300 series stainless steel. See material/finish options in How to Order table for options.
- O-rings, grommet: silicone
- Hardware: 300 series stainless steel
- Anti-decoupling device: corrosion-resistant material
- Band strap: stainless steel, passivated



How To Order						
SAMPLE PART NUMBER		443VS039	MT	08	01	-2
Product	443VS039 = Straight Backshell 443VH039 = 45° Backshell 443VJ039 = 90° Backshell					
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium NFP = Aluminum, Olive Drab Cadmium, nickel-plated shield termination area , polysulfide barrier Z1 = Stainless Steel, Passivated					
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24					
Cable Entry Code	See Table 1 for cable entry sizes					
Adapter Length	Omit for 45° and 90° versions. Applicable to 443VS039 only. Length in ½ inch increments. 2 = 1 inch (min. for Style 1) 3 = 1½ inches 4 = 2 inches (min. for Style 2) 5 = 2½ inches 6 = 3 inches		LENGTH 			







Table 1: Cable Entry					
Cable Entry Code	Grommet Diameter		J Max.	W Closed	Ø X Min.
	Min.	Max.			
01	.125 (3.18)	.250 (6.35)	1.05 (26.67)	.264 (6.71)	.25 (6.35)
02	.188 (4.78)	.375 (9.52)	1.20 (30.48)	.344 (8.74)	.37 (9.40)
03	.312 (7.92)	.438 (11.13)	1.30 (33.02)	.460 (11.68)	.43 (10.92)
04	.343 (8.71)	.500 (12.70)	1.44 (36.58)	.545 (13.84)	.50 (12.70)
05	.438 (11.13)	.625 (15.88)	1.69 (42.93)	.698 (17.73)	.62 (15.75)
06	.562 (14.27)	.750 (19.05)	1.77 (44.96)	.780 (19.81)	.75 (19.05)
07	.688 (17.48)	.875 (22.23)	2.12 (53.85)	.950 (24.13)	.87 (22.10)
08	.812 (20.62)	1.000 (25.40)	2.50 (63.50)	1.015 (25.78)	1.00 (25.40)
09	.938 (23.83)	1.125 (28.58)	2.62 (66.55)	1.187 (30.15)	1.12 (28.45)
10	1.062 (26.97)	1.250 (31.75)	2.68 (68.07)	1.220 (30.99)	1.25 (31.75)
11	1.125 (28.58)	1.375 (34.92)	3.00 (76.20)	1.500 (38.10)	1.38 (35.05)
12	1.250 (31.75)	1.500 (38.10)	3.50 (88.90)	1.625 (41.28)	1.50 (38.10)




Shell Size	A ISO Metric Thread	Ø C Max.	F Max. ⁽¹⁾	G Max.	H Max. ⁽¹⁾	J Max.	Max. Cable Entry Code ⁽¹⁾
07	M8 x 1.0-6H	.640 (16.26)	.580 (14.73)	1.030 (26.16)	.830 (21.08)	1.180 (29.97)	01
08	M10 x 1.0-6H	.692 (17.58)	.630	1.030 (26.16)	.880 (22.35)	1.180 (29.97)	01
09	M12 x 1.0-6H	.786 (19.96)	.640 (16.26)	1.030 (26.16)	.880 (22.35)	1.210 (30.73)	01
10	M14 x 1.0-6H	.883 (22.43)	.670 (17.02)	1.060 (26.92)	.930 (23.62)	1.260 (32.00)	02
11	M15 x 1.0-6H	.911 (23.14)	.680 (17.27)	1.090 (27.69)	.980 (24.89)	1.290 (32.77)	03
12	M17 x 1.0-6H	1.002 (25.45)	.700 (17.78)	1.100 (27.94)	.990 (25.15)	1.320 (33.53)	04
14	M19 x 1.0-6H	1.066 (27.08)	.720 (18.29)	1.100 (27.94)	.990 (25.15)	1.350 (34.29)	04
16	M22 x 1.0-6H	1.196 (30.38)	.760 (19.30)	1.130 (28.70)	1.050 (26.67)	1.410 (35.81)	05
18	M25 x 1.0-6H	1.311 (33.30)	.790 (20.07)	1.170 (29.72)	1.120 (28.45)	1.470 (37.34)	06
20	M28 x 1.0-6H	1.430 (36.32)	.830 (21.08)	1.200 (30.48)	1.180 (29.97)	1.530 (38.86)	07
22	M31 x 1.0-6H	1.548 (39.32)	.860 (21.84)	1.240 (31.50)	1.240 (31.50)	1.590 (40.39)	08
24	M34 x 1.0-6H	1.696 (43.08)	.910 (23.11)	1.290 (32.77)	1.300 (33.02)	1.670 (42.42)	09

(1) If the maximum cable entry code is exceeded, the backshell will be a "Style 2" with a transition adapter as shown below. The F and H dimensions will be increased by 0.9 inch (22.9 mm.) maximum.


STYLE 2 ADAPTERS FOR LARGE DIAMETER CABLES

If the cable entry diameter exceeds the maximum cable entry code shown in the above table, the adapter will be supplied with a **transition adapter**. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 0.9 inch (22.9 mm) maximum to the backshell length.



APPLICATION NOTE: SELECTIVE PLATED CADMIUM WITH POLYSULFIDE BARRIER

Olive drab (OD) cadmium (Cd) over electroless nickel (EN) is available in two versions. The standard version, designated as Glenair code **NF**, is a uniform Cd/EN finish over the entire part. A second version, designated as Glenair code **NFP**, is selectively plated with electroless nickel in the knurled shield attachment area. A polysulfide barrier separates the electroless nickel area from the cadmium plated area. This selectively plated version prevents galvanic corrosion that could potentially occur if nickel-coated shield braid is attached to a cadmium plated surface.



Series 806 Mil-Aero Connectors

620V*080 Metal Strain Relief Cable Clamp



Strain relief clamp with anti-decoupling ratchet prevents loosening under vibration. Full radius saddle clamps prevent pinching of cables. Fits Series 806 connectors. Straight, 45° or 90° cable exit.

How To Order			
SAMPLE PART NUMBER	620VS080	MT	08
Product	620VS080 = Straight Strain Relief 620VB080 = 45° Strain Relief 620VA080 = 90° Strain Relief		
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium		
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24		

Features


- Straight, 45° and 90°
- Self-locking spin coupling
- Fits Series 806 micro miniature connectors
- Captive threaded inserts

Specifications

- Operating temperature:
codes ME and MT: -65°C to +200°C
codes ZR, NF, NFP: -65°C to +175°C
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT: 1000 hours
- Vibration, shock: SAE AS85049 Category 4C

Construction

- Clamp, body, saddles, coupling nut: aluminum alloy. See material/finish options in How to Order table for options.
- Hardware: 300 series stainless steel
- Anti-decoupling device: corrosion-resistant material



Shell Size	A ISO Metric Thd	øB Max.	C Max.	D Max.	E ±.031 (0.79)	F Min.	H Max.	J Max.	ØG Max.	K Max.	J ±.031	M Min.	N Max.	P Max.
07	M8 x 1.0-6H	.58 (14.73)	.780 (19.81)	.77 (19.56)	.209 (5.31)	.21 (5.33)	1.02 (25.91)	.83 (21.08)	-	-	-	-	-	-
08	M10 x 1.0-6H	.64 (16.26)	.780 (19.81)	.83 (21.08)	.269 (6.83)	.27 (6.86)	1.04 (26.42)	.87 (22.10)	.79 (20.07)	.89 (22.61)	.265 (6.73)	.27 (6.86)	.96 (24.38)	1.43 (36.32)
09	M12 x 1.0-6H	.74 (18.80)	.840 (21.34)	.91 (23.11)	.346 (8.79)	.35 (8.89)	1.06 (26.92)	.91 (23.11)	.79 (20.07)	.89 (22.61)	.265 (6.73)	.27 (6.86)	.96 (24.38)	1.43 (36.32)
10	M14 x 1.0-6H	.80 (20.32)	.900 (22.86)	.97 (24.64)	.410 (10.41)	.42 (10.67)	1.08 (27.43)	.95 (24.13)	.91 (23.11)	1.00 (25.40)	.310 (7.87)	.31 (7.87)	1.05 (26.67)	1.50 (38.10)
11	M15 x 1.0-6H	.84 (21.34)	.960 (24.38)	1.08 (27.43)	.430 (10.92)	.44 (11.18)	1.10 (27.94)	.97 (24.64)	.91 (23.11)	1.00 (25.40)	.310 (7.87)	.31 (7.87)	1.05 (26.67)	1.50 (38.10)
12	M17 x 1.0-6H	.92 (23.37)	1.060 (26.92)	1.14 (28.96)	.488 (12.40)	.49 (12.45)	1.15 (29.21)	1.03 (26.16)	1.02 (25.91)	1.27 (32.26)	.390 (9.91)	.39 (9.91)	1.11 (28.19)	1.55 (39.37)
14	M19 x 1.0-6H	1.02 (25.91)	1.100 (27.94)	1.20 (30.48)	.530 (13.46)	.54 (13.72)	1.18 (29.97)	1.06 (26.92)	1.02 (25.91)	1.27 (32.26)	.390 (9.91)	.39 (9.91)	1.11 (28.19)	1.55 (39.37)
16	M22 x 1.0-6H	1.16 (29.46)	1.100 (27.94)	1.29 (32.77)	.620 (15.75)	.63 (16.00)	1.30 (33.02)	1.16 (29.46)	1.18 (29.97)	1.38 (35.05)	.506 (12.85)	.51 (12.95)	1.18 (29.97)	1.65 (41.91)
18	M25 x 1.0-6H	1.26 (32.00)	1.230 (31.24)	1.41 (35.81)	.700 (17.78)	.71 (18.03)	1.38 (35.05)	1.34 (34.04)	1.31 (33.27)	1.48 (37.59)	.591 (15.01)	.59 (14.99)	1.23 (31.24)	1.77 (44.96)
20	M28 x 1.0-6H	1.40 (35.56)	1.410 (35.81)	1.59 (40.39)	.778 (19.76)	.78 (19.81)	1.46 (37.08)	1.41 (35.81)	1.42 (36.07)	1.58 (40.13)	.661 (16.79)	.66 (16.76)	1.29 (32.77)	1.81 (45.97)
22	M31 x 1.0-6H	1.52 (38.61)	1.510 (38.35)	1.66 (42.16)	.850 (21.59)	.86 (21.84)	1.58 (40.13)	1.53 (38.86)	1.54 (39.12)	1.68 (42.67)	.744 (18.90)	.74 (18.80)	1.37 (34.80)	1.86 (47.24)
24	M34 x 1.0-6H	1.64 (41.66)	1.660 (42.16)	1.77 (44.96)	.961 (24.41)	.97 (24.64)	1.62 (41.15)	1.66 (42.16)	1.65 (41.91)	1.80 (45.72)	.826 (20.98)	.83 (21.08)	1.42 (36.07)	1.90 (48.26)

**Features**

- EMI/RFI
- Self-locking spin coupling
- Band-Master shield termination

Specifications


- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF, NFP: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME, NFP: 96 hours
Code NF, ZR, MT, Z1: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Coupling nut, adapter: aluminum alloy or 300 series stainless steel. See material/finish options in How to Order table.
- O-ring: silicone
- Anti-decoupling device: corrosion-resistant material

Shrink Boot Options

- Consult factory for shrink boot options.



EMI shielding. Band-Master ATS® shield termination. Self-locking. Environmental. Spin coupling EMI/RFI adapter with anti-decoupling ratchet prevents loosening under vibration. Fits Series 806 connectors. Terminate cable shield to backshell with **Band-Master ATS®** stainless steel band. Compatible with Glenair Series 77 lipped heatshrink boots. Straight, 45° or 90° cable exit. Aluminum or Stainless Steel.

How To Order						
SAMPLE PART NUMBER	440VS191	ME	12	06	-4	K
Product	440VS191 = Straight Adapter 440VH191 = 45° Adapter 440VJ191 = 90° Adapter					
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium NFP = Aluminum, Olive Drab Cadmium, nickel-plated shield termination area, polysulfide barrier TZ = Aluminum, Tin-Zinc Z1 = Stainless Steel, Passivated					
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24					
Cable Entry Code	See Table 1 for cable entry sizes					
Adapter Length	Omit for 45° and 90° versions. Applicable to 440VS191 only. Length in ½ inch increments: 3 = 1½ inches (min. for Style 1 shown at right) 4 = 2 inches (min. for Style 2 shown on following page) 5 = 2½ inches 6 = 3 inches					
Optional Band Strap	Omit if bands will be purchased separately. K = Adapter supplied with pre-coiled band strap 601-041					





Table 1: Cable Entry							
Cable Entry Code	ø X Typ.	ø Y Typ.	ø Z Typ.	Cable Entry Code	ø X Typ.	ø Y Typ.	ø Z Typ.
02	.125 (3.18)	.250 (6.35)	.312 (7.92)	13	.812 (20.62)	.938 (23.83)	1.000 (25.40)
03	.188 (4.78)	.312 (7.92)	.374 (9.50)	14	.875 (22.23)	1.000 (25.40)	1.062 (26.97)
04	.250 (6.35)	.375 (9.52)	.437 (11.10)	15	.938 (23.83)	1.062 (26.97)	1.124 (28.55)
05	.312 (7.92)	.438 (11.13)	.500 (12.70)	16	1.000 (25.40)	1.125 (28.58)	1.187 (30.15)
06	.375 (9.52)	.500 (12.70)	.562 (14.27)	17	1.062 (26.97)	1.188 (30.18)	1.250 (31.75)
07	.438 (11.13)	.562 (14.27)	.624 (15.85)	18	1.125 (28.58)	1.250 (31.75)	1.312 (33.32)
08	.500 (12.70)	.625 (15.88)	.687 (17.45)	20	1.250 (31.75)	1.375 (34.92)	1.437 (36.50)
09	.562 (14.27)	.688 (17.48)	.750 (19.05)	22	1.375 (34.92)	1.500 (38.10)	1.562 (39.67)
10	.625 (15.88)	.750 (19.05)	.812 (20.62)	24	1.500 (38.10)	1.625 (41.28)	1.687 (42.85)
11	.688 (17.48)	.812 (20.62)	.874 (22.20)	26	1.625 (41.28)	1.750 (44.45)	1.812 (46.02)
12	.750 (19.05)	.875 (22.23)	.937 (23.80)	28	1.750 (44.45)	1.875 (47.63)	1.937 (49.20)

Series 806 Mil-Aero Connectors


440V*191 Metal EMI/RFI Boot and Band Adapter

440VS191


Straight Exit

**440VH191**

45° Exit

**440VJ191**

90° Exit




Shell Size	A ISO Metric Thd	ØC Max.	F Max. ⁽¹⁾	G Max.	H Max. ⁽¹⁾	J Max.	Max. Cable Entry Code ⁽¹⁾	Max. Cable Entry Dia. ⁽¹⁾
07	M8 x 1.0-6H	.640 (16.26)	.630 (16.00)	.880 (22.35)	.730 (18.54)	1.080 (27.43)	03	.188 (4.78)
08	M10 x 1.0-6H	.710 (18.03)	.640 (16.26)	.920 (23.37)	.760 (19.30)	1.130 (28.70)	04	.250 (6.35)
09	M12 x 1.0-6H	.780 (19.81)	.650 (16.51)	.960 (24.38)	.790 (20.07)	1.180 (29.97)	05	.312 (7.92)
10	M14 x 1.0-6H	.880 (22.35)	.680 (17.27)	.990 (25.15)	.840 (21.34)	1.230 (31.24)	06	.375 (9.52)
11	M15 x 1.0-6H	.920 (23.37)	.690 (17.53)	1.020 (25.91)	.850 (21.59)	1.240 (31.50)	07	.438 (11.13)
12	M17 x 1.0-6H	1.000 (25.40)	.720 (18.29)	1.050 (26.67)	.900 (22.86)	1.290 (32.77)	08	.500 (12.70)
14	M19 x 1.0-6H	1.090 (27.69)	.730 (18.54)	1.080 (27.43)	.930 (23.62)	1.320 (33.53)	09	.562 (14.27)
16	M22 x 1.0-6H	1.210 (30.73)	.770 (19.56)	1.150 (29.21)	1.000 (25.40)	1.400 (35.56)	12	.750 (19.1)
18	M25 x 1.0-6H	1.330 (33.78)	.800 (20.32)	1.210 (30.73)	1.050 (26.67)	1.490 (37.85)	13	.812 (20.62)
20	M28 x 1.0-6H	1.450 (36.83)	.840 (21.34)	1.270 (32.26)	1.110 (28.19)	1.580 (40.13)	15	.938 (23.83)
22	M31 x 1.0-6H	1.570 (39.88)	.870 (22.10)	1.320 (33.53)	1.170 (29.72)	1.660 (42.16)	17	1.062 (26.97)
24	M34 x 1.0-6H	1.700 (43.18)	.920 (23.37)	1.390 (35.31)	1.250 (31.75)	1.770 (44.96)	18	1.125 (28.58)

(1) If the maximum cable entry code is exceeded, the backshell will be a "Style 2" with a transition adapter as shown below. The F and H dimensions will be increased by 1.00 inch (25.4 mm.) maximum.


Style 2 Adapters for Large Diameter Cables

If the cable entry diameter exceeds the maximum cable entry code shown in the above table, the adapter will be supplied with a **transition adapter**. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.



Application Note: Selective Plated Cadmium with Polysulfide Barrier


Olive drab (OD) cadmium (Cd) over electroless nickel (EN) is available in two versions. The standard version, designated as Glenair code **NF**, is a uniform Cd/EN finish over the entire part. A second version, designated as Glenair code **NFP**, is selectively plated with electroless nickel in the knurled shield attachment area. A polysulfide barrier separates the electroless nickel area from the cadmium plated area. This selectively plated version prevents galvanic corrosion that could potentially occur if nickel-coated shield braid is attached to a cadmium plated surface.



Series 806 Mil-Aero Connectors



320V*030 Environmental Extended Adapter for Size #8 Contacts



Features

- Expanded clearance for El Ocho contacts
- EMI/RFI
- Self-locking spin coupling

Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF, TZ: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT, Z1, TZ: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B


Construction

- Coupling nut, adapter: aluminum alloy or 300 series stainless steel. See material/finish options in How to Order table.
- O-ring: silicone
- Anti-decoupling device: corrosion-resistant material

Self-locking, Straight, 45°, or 90°. Threaded coupling extended front end adapter with long radius angular function. Anti-decoupling ratchet prevents loosening under vibration. Accommodates Series 806 connectors with size #8 contacts. Straight, 45° or 90° cable exit. Aluminum or stainless steel.

How To Order				
SAMPLE PART NUMBER		320VS030	ME	16 -4
Product	320VS030 = Straight Backshell 320VM030 = 45° Backshell 320VN030 = 90° Backshell			
Material/ Finish	ME = Aluminum, Electroless Nickel, MT = Aluminum, Ni/PTFE NF = Aluminum, Olive Drab Cadmium TZ = Aluminum, Tin-Zinc ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated			
Shell Size	08 09 10 11 12 14 16 18 20 22 24			
Backshell Length	length given in .25 inch increments (eg. 8 = 2.0 inches). Applies to straight backshell only			


ANTI-DECOUPLING DEVICE - TYP



Shell Size	A Thread Iso Metric	B Max	C Max	D Max	E Max	F Max	G Max
08	M10 X 1	0.692 (17.58)	1.853 (47.07)	1.457 (37.01)	1.393 (35.38)	0.997 (25.32)	0.723 (18.36)
09	M12 X 1	0.786 (19.96)	1.853 (47.07)	1.457 (37.01)	1.393 (35.38)	0.997 (25.32)	0.723 (18.36)
10	M14 X 1	0.883 (22.43)	1.915 (48.64)	1.519 (38.58)	1.420 (36.07)	1.024 (26.01)	0.742 (18.85)
11	M15 X 1	0.911 (23.14)	1.915 (48.64)	1.519 (38.58)	1.420 (36.07)	1.024 (26.01)	0.742 (18.85)
12	M17 X 1	1.002 (25.45)	2.067 (52.50)	1.671 (42.44)	1.445 (36.70)	1.049 (26.64)	0.760 (19.30)
14	M19 X 1	1.066 (27.08)	2.067 (52.50)	1.671 (42.44)	1.445 (36.70)	1.049 (26.64)	0.760 (19.30)
16	M22 X 1	1.196 (30.38)	2.130 (54.10)	1.734 (44.04)	1.501 (38.13)	1.105 (28.07)	0.799 (20.29)
18	M25 X 1	1.311 (33.30)	2.235 (56.77)	1.839 (46.71)	1.540 (39.12)	1.144 (29.06)	0.827 (21.01)
20	M28 X 1	1.430 (36.32)	2.298 (58.37)	1.902 (48.31)	1.566 (39.78)	1.170 (29.72)	0.845 (21.46)
22	M31 X 1	1.548 (39.32)	2.359 (59.92)	1.963 (49.86)	1.548 (39.32)	1.152 (29.26)	0.833 (21.16)
24	M34 X 1	1.696 (43.08)	2.380 (60.45)	1.984 (50.39)	1.570 (39.88)	1.174 (29.82)	0.848 (21.54)

Series 806 Mil-Aero Connectors

440V*233 Metal EMI/RFI, Shield Termination Backshell



Features

- Expanded clearance for El Ochoito Contacts
- Self-locking spin coupling

Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF, TZ: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT, Z1, TZ: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Adapter, elbow, coupling nut, ferrule, clamp: see material/finish options in How to Order table.
- Anti-decoupling device: corrosion-resistant material or high grade engineering thermoplastic
- O-rings: silicone/N.A.
- Band/hardware: CRES/passivate






Application Notes

- Standard minimum length is 1.50 inches, applies to Symbol S, Straight only
- For effective grounding, connector with conductive finish should be used.

EMI/RFI, extended front end long radius angular function strain relief cable clamp backshell with integral banding platform. Threaded coupling backshell with anti-decoupling ratchet prevents loosening under vibration. Accommodates Series 806 connectors with size #8 contacts and cable sealing boots. Aluminum or stainless steel.

How To Order										
SAMPLE PART NUMBER		440VS233	ME	10	08	M	-8	K	P	T
Product	440VS233 = Straight Backshell 440VN233 = 90° Angle Backshell 440VM233 = 45° Angle Backshell									
Material/Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE NF = Aluminum, Olive Drab Cadmium TZ = Tin-Zinc ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated									
Shell Size	08 09 10 11 12 14 16 18 20 22 24									
Dash No	See Dash Number Table									
Band Platform Option	M = Micro Band Platform (omit for standard platform)									
Length	Designate in .25 inch increments (eg. -8 = 2.0 inches) <i>Applies to straight backshell only</i>									
Band Option	K = Precoiled Band (omit if not required)									
Plating Shield	P = Polysulfide (omit if not required); when polysulfide barrier is selected for plating, shield termination surface shall be electroless nickel plated only. Applies to "NF", "TZ", and "ZR"									
Shrink Boot	T = Standard Shrink Boot (* = 1) T1 = Standard with Pre-Coated W1 Hot Melt Adhesive (* = 1) H = Zero Halogen Shrink Boot (* = 2) H1 = Zero Halogen with pre-coated W1 Hot Melt Adhesive (* = 2) See Dash Number Table for complete shrink boot part number to order separately (Omit for none)									


Dash Number					
DASH NO	ØH TYP	ØJ TYP	ØK TYP	SHRINK BOOT T OR H REF	SHRINK BOOT WITH ADHESIVE
02	0.125 (3.18)	0.250 (6.35)	0.312 (7.92)	770-003S*11	770-003S*11W1
03	0.188 (4.78)	0.312 (7.92)	0.374 (9.50)	770-003S*11	770-003S*11W1
04	0.250 (6.35)	0.375 (9.52)	0.437 (11.10)	770-003S*12	770-003S*12W1
05	0.312 (7.92)	0.438 (11.13)	0.500 (12.70)	770-003S*12	770-003S*12W1
06	0.375 (9.52)	0.500 (12.70)	0.562 (14.27)	770-001S*03	770-001S*03W1
07	0.438 (11.13)	0.562 (14.27)	0.624 (15.85)	770-001S*04	770-001S*04W1
08	0.500 (12.70)	0.625 (15.88)	0.687 (17.45)	770-001S*04	770-001S*04W1
09	0.562 (14.27)	0.688 (17.48)	0.750 (19.05)	770-001S*04	770-001S*04W1
10	0.625 (15.88)	0.750 (19.05)	0.812 (20.62)	770-001S*04	770-001S*04W1
11	0.688 (17.48)	0.812 (20.62)	0.874 (22.20)	770-001S*04	770-001S*04W1
12	0.750 (19.05)	0.875 (22.23)	0.937 (23.80)	770-001S*05	770-001S*05W1
13	0.812 (20.62)	0.938 (23.83)	1.000 (25.40)	770-001S*05	770-001S*05W1
14	0.875 (22.23)	1.000 (25.40)	1.062 (26.97)	770-001S*05	770-001S*05W1
15	0.938 (23.83)	1.062 (26.97)	1.124 (28.55)	770-001S*05	770-001S*05W1
16	1.000 (25.40)	1.125 (28.58)	1.187 (30.15)	770-001S*06	770-001S*06W1
17	1.062 (26.97)	1.188 (30.18)	1.250 (31.75)	770-001S*06	770-001S*06W1
18	1.125 (28.58)	1.250 (31.75)	1.312 (33.32)	770-001S*07	770-001S*07W1



Shell Size	A Thread ISO Metric	ØC Max	D	E	F	G	Max Cable Entry	Max Entry
08	M10 X 1-6H	.692 (17.58)	.790 (20.07)	1.190 (30.23)	.940 (23.88)	1.350 (34.29)	.250 (6.35)	04
09	M12 X 1-6H	.786 (19.96)	.790 (20.07)	1.190 (30.23)	.940 (23.88)	1.350 (34.29)	.250 (6.35)	04
10	M14 X 1-6H	.883 (22.43)	.790 (20.07)	1.260 (32.00)	.970 (24.64)	1.450 (36.83)	.375 (9.52)	06
11	M15 X 1-6H	.911 (23.14)	.790 (20.07)	1.260 (32.00)	.970 (24.64)	1.450 (36.83)	.375 (9.52)	06
12	M17 X 1-6H	1.002 (25.45)	.830 (21.08)	1.340 (34.04)	1.040 (26.42)	1.550 (39.37)	.500 (12.70)	08
14	M19 X 1-6H	1.066 (27.08)	.830 (21.08)	1.340 (34.04)	1.040 (26.42)	1.550 (39.37)	.500 (12.70)	08
16	M22 X 1-6H	1.196 (30.38)	.840 (21.34)	1.410 (35.81)	1.080 (27.43)	1.650 (41.91)	.625 (15.88)	10
18	M25 X 1-6H	1.311 (33.30)	.890 (22.61)	1.490 (37.85)	1.40 (35.56)	1.740 (44.20)	.750 (19.05)	12
20	M28 X 1-6H	1.430 (36.32)	.920 (23.37)	1.560 (39.62)	1.210 (30.73)	1.840 (46.74)	.875 (22.23)	14
22	M31 X 1-6H	1.548 (39.32)	.950 (24.13)	1.620 (41.15)	1.280 (32.51)	1.940 (49.28)	1.000 (25.40)	16
24	M34 X 1-6H	1.696 (43.08)	.970 (24.64)	1.680 (42.67)	1.330 (33.78)	2.040 (51.82)	1.125 (28.58)	18

Series 806 Mil-Aero Connectors

620VS090 Strain Relief Cable Clamp Backshell, Size #8 Contacts



Extended shell strain relief cable clamp backshell. Self-locking. Threaded coupling adapter with anti-decoupling ratchet prevents loosening under vibration. Accommodates Series 806 connectors with size #8 contacts and cable sealing boots. Aluminum or stainless steel.

Features

- Expanded clearance for El Ocho contacts
- Self-locking spin coupling


Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF, TZ: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT, Z1, TZ: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Coupling nut, saddles, clamp body: aluminum alloy or 300 series stainless steel. See material/finish options in How to Order table.
- Hardware: CRES/passivate or Cad/O.D. over nickel
- Anti-decoupling device: corrosion-resistant material

How To Order			
SAMPLE PART NUMBER		620VS090	ME 16
Product	620VS090 = Series 806, Straight Backshell		
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE NF = Aluminum, Olive Drab Cadmium ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated		
Shell Size	10 11 12 14 16 18 20 22 24		



Shell Size	A Thread ISO Metric	B Dia Max	C	D Max	E ±.031(0.79)	F Min
10	M14 x 1-6H	.80 (20.32)	1.28 (32.51)	1.05 (26.67)	.264 (6.71)	.36 (9.14)
11	M15 x 1-6H	.84 (21.34)	1.35 (34.29)	1.05 (26.67)	.264 (6.71)	.36 (9.14)
12	M17 x 1-6H	.92 (23.37)	1.35 (34.29)	1.20 (30.48)	.344 (8.74)	.42 (10.67)
14	M19 x 1-6H	1.02 (25.91)	1.41 (35.81)	1.20 (30.48)	.344 (8.74)	.42 (10.67)
16	M22 x 1-6H	1.16 (29.46)	1.47 (37.34)	1.30 (33.02)	.460 (11.68)	.47 (11.94)
18	M25 x 1-6H	1.26 (32.00)	1.53 (38.86)	1.44 (36.58)	.545 (13.84)	.55 (13.97)
20	M28 x 1-6H	1.40 (35.56)	1.66 (42.16)	1.56 (39.62)	.615 (15.62)	.62 (15.75)
22	M31 x 1-6H	1.52 (38.61)	1.72 (43.69)	1.69 (42.93)	.698 (17.73)	.70 (17.78)
24	M34 x 1-6H	1.64 (41.66)	1.78 (45.21)	1.77 (44.96)	.780 (19.81)	.78 (19.81)

Series 806 Mil-Aero Connectors



440VS232 EMI/RFI Strain Relief Cable Clamp, Size #8 Contacts



Strain relief cable clamp adapter. Self-locking. Threaded coupling adapter with anti-decoupling ratchet prevents loosening under vibration. Accommodates Series 806 connectors with size #8 contacts and cable sealing boots. Aluminum or stainless steel.

Features

- Expanded clearance for El Ochito contacts
- EMI/RFI
- Band strap shield termination
- Shield termination slot option
- Self-locking spin coupling


Specifications

- Operating temperature:
codes ME, MT and Z1: -65°C to +200°C
codes ZR, NF, TZ: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT, Z1, TZ: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Coupling nut, saddles, clamp body:
aluminum alloy or 300 series stainless steel. See material/finish options in How to Order table.
- Hardware: CRES/passivate or Cad/O.D. over nickel
- Anti-decoupling device: corrosion-resistant material

How To Order						
SAMPLE PART NUMBER		440VS232	NF	16	S	K
Product	440VS232 = Series 806, Straight Backshell					
Material/ Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE NF = Aluminum, Olive Drab Cadmium ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated					
Shell Size	08 09 10 11 12 14 16 18 20 22 24					
Shield Termination Slot	S = Shield Termination Slot					
Precoiled Band	K = Percoiled Band (Omit for None)					



Shell Size	A Thread ISO Metric	B Dia Max	C	D Max	E +0.031 (0.79)	F Min
08	M10 x 1	0.642 (16.31)	1.23 (31.24)	0.93 (23.62)	0.205 (5.21)	0.18 (4.57)
09	M12 x 1	0.735 (18.67)	1.28 (32.51)	0.98 (24.89)	0.219 (5.56)	0.22 (5.59)
10	M14 x 1	0.786 (19.96)	1.28 (32.51)	1.02 (25.91)	0.244 (6.20)	0.25 (6.35)
11	M15 x 1	0.830 (21.08)	1.35 (34.29)	1.05 (26.67)	0.264 (6.71)	0.27 (6.86)
12	M17 x 1	0.911 (23.14)	1.35 (34.29)	1.12 (28.45)	0.312 (7.92)	0.32 (8.13)
14	M19 x 1	1.002 (25.45)	1.41 (35.81)	1.20 (30.48)	0.344 (8.74)	0.35 (8.89)
16	M22 x 1	1.149 (29.18)	1.47 (37.34)	1.30 (33.02)	0.460 (11.68)	0.47 (11.94)
18	M25 x 1	1.264 (32.11)	1.53 (38.86)	1.44 (36.58)	0.545 (13.84)	0.55 (13.97)
20	M28 x 1	1.394 (35.41)	1.66 (42.16)	1.56 (39.62)	0.615 (15.62)	0.62 (15.75)
22	M31 x 1	1.513 (38.43)	1.72 (43.69)	1.69 (42.93)	0.698 (17.73)	0.70 (17.78)
24	M34 x 1	1.631 (41.43)	1.78 (45.21)	1.77 (44.96)	0.780 (19.81)	0.78 (19.81)

Series 806 Mil-Aero Connectors

443V*042 EMI/RFI Environmental, Cable Clamp for Size #8 Contacts



Features

- Expanded clearance for El Ochito Contacts
- Self-locking spin coupling

Specifications

- Operating temperature:
codes ME, and Z1: -65°C to +200°C
codes ZR, MT, NF, TZ: -65°C to +175°C
- Shell conductivity:
aluminum versions: 2.5 milliohms max.
Stainless steel: 5 milliohms max.
- Salt spray (corrosion)
Code ME: 96 hours
Code ZR : 500 hours
Code NF, MT, Z1, TZ: 1000 hours
- Vibration: SAE AS85049 Category 3B
- Shock: SAE AS85049 Category 3B

Construction

- Adapter, elbow, coupling nut, ferrule, clamp: see material/finish options in How to Order table.
- Anti-decoupling device: corrosion-resistant material or high grade engineering thermoplastic
- O-rings: silicone/N.A.
- Band/hardware: CRES/passivate


Application Notes

- Standard minimum length is 1.50 inches, applies to Symbol S, Straight only
- For effective grounding, connector with conductive finish should be used.

EMI/RFI environmental, extended front end long radius angular function strain relief with cable clamp backshell with band in a can banding. Threaded coupling backshell with anti-decoupling ratchet prevents loosening under vibration. Accommodates Series 806 connectors with size #8 contacts and cable sealing boots. Aluminum or stainless steel.

How To Order							
SAMPLE PART NUMBER		443VS042	ME	12	04	-8	K P
Product	443VS042 = Series 806, Straight Backshell						
	443VN042 = Series 806, 90° Angle Backshell						
Material/Finish	443VM042 = Series 806, 45° Angle Backshell						
	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE NF = Aluminum, Olive Drab Cadmium TZ = Tin-Zinc ZR = Aluminum, Black Zinc-Nickel Z1 = Stainless Steel, Passivated						
Shell Size	08 09 10 11 12 14 16 18 20 22 24						
Dash No	See Dash Number Table						
Length	Designate in .25 inch increments (eg. 8 = 2.0 inches) Applies to straight backshell only						
Band	K = precoiled band (omit if not required)						
Plating Shield	P = Polysulfide (omit if not required); when polysulfide barrier is selected for plating, shield termination surface shall be electroless nickel plated only. Applies to "NF", "TZ", and "ZR"						

Dash Number					
DASH NO	J MAX	CABLE RANGE		W CLOSED	H MIN DIA
		MIN	MAX		
01	1.05 (26.67)	0.125 (3.18)	0.250 (6.35)	0.264 (6.71)	0.25 (6.35)
02	1.20 (30.48)	0.188 (4.78)	0.375 (9.52)	0.344 (8.74)	0.37 (9.40)
03	1.30 (33.02)	0.312 (7.92)	0.438 (11.13)	0.460 (11.68)	0.43 (10.92)
04	1.44 (36.58)	0.343 (8.71)	0.500 (12.70)	0.545 (13.84)	0.50 (12.70)
05	1.69 (42.93)	0.438 (11.13)	0.625 (15.88)	0.698 (17.73)	0.62 (15.75)
06	1.77 (44.96)	0.562 (14.27)	0.750 (19.05)	0.780 (19.81)	0.75 (19.05)
07	2.12 (53.85)	0.688 (17.48)	0.875 (22.23)	0.950 (24.13)	0.87 (22.10)
08	2.50 (63.50)	0.812 (20.62)	1.000 (25.40)	1.015 (25.78)	1.00 (25.40)
09	2.62 (66.55)	0.938 (23.83)	1.125 (28.58)	1.187 (30.15)	1.12 (28.45)



Shell Size	A Thd ISO Metric	ØB Max	ØC ±.005 (0.13)	D Max	B Max	F Max	G Max	Max Entry
08	M10 X 1	.710(18.0)	0.269 (6.80)	1.853(47.1)	1.903(48.3)	1.393(35.4)	1.443(36.7)	01
09	M12 X 1	.790(20.1)	0.346 (8.80)	1.853(47.1)	1.903(48.3)	1.393(35.4)	1.443(36.7)	01
10	M14 X 1	.890(22.6)	.410(10.4)	1.915(48.6)	1.965(49.9)	1.420(36.1)	1.470(37.3)	02
11	M15 X 1	.930(23.6)	.471(11.9)	1.915(48.6)	1.965(49.9)	1.420(36.1)	1.470(37.3)	02
12	M17 X 1	1.010(25.7)	.539(13.7)	2.067(52.5)	2.117(53.8)	1.445(36.7)	1.495(38.0)	04
14	M19 X 1	1.090(27.7)	.592(15.0)	2.067(52.5)	2.117(53.8)	1.445(36.7)	1.495(38.0)	04
16	M22 X 1	1.210(30.7)	.740(18.8)	2.130(54.1)	2.180(55.4)	1.501(38.1)	1.551(39.4)	05
18	M25 X 1	1.330(33.8)	.856(21.7)	2.235(56.8)	2.285(58.0)	1.540(39.1)	1.590(40.4)	06
20	M28 X 1	1.450(36.8)	.980(24.9)	2.298(58.4)	2.348(59.6)	1.566(39.8)	1.616(41.0)	07
22	M31 X 1	1.570(39.9)	1.070(27.2)	2.359(59.9)	2.409(61.2)	1.548(39.3)	1.598(40.6)	08
24	M34 X 1	1.710(43.4)	1.214(30.8)	2.380(60.5)	2.430(61.7)	1.570(39.9)	1.620(41.1)	09

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

340VS035 Shorting Cap



Features

- Spin coupling, environmental
- Wire rope, sash chain or braided nylon lanyards

Specifications

- Operating temperature:
codes ME, MT: -65°C to +200°C
codes ZR, NF: -65°C to +175°C
- Salt spray (corrosion)
Code ME: 96 hours
Code NF, ZR, MT: 1000 hours

Construction

- Coupling nut, shell: aluminum alloy.
- O-ring: silicone
- Attachment hardware: stainless steel, passivated

Table 1 Attachment Type



Nylon Rope (G)

-55° to +100°C, black, very flexible, very good abrasion resistance, good resistance to fuels, .120" (3mm) diameter



Polyurethane Coated Wire Rope (U)

Black polyurethane over stainless steel rope, -55° to +125°C, very flexible, excellent abrasion resistance, excellent resistance to fuels, .080" (2mm) diameter



Teflon® Jacketed Wire Rope (H)

Translucent FEP jacket over stainless steel, -55° to +200°C, fair flexibility, good abrasion resistance, .100" diameter




Sash Chain (S)

Stainless steel, #8 chain, .240" (6mm)

Spin coupling shorting cap fits Series 806 connectors with metric accessory thread. Available with lanyard attachments. Aluminum.

How To Order							
SAMPLE PART NUMBER	340VS035	ME	12	-3	S	12	-04
Product	340VS035 = Shorting Cap, straight, for Series 806 connectors						
Finish	ME = Aluminum, Electroless Nickel MT = Aluminum, Ni/PTFE ZR = Aluminum, Black Zinc-Nickel NF = Aluminum, Olive Drab Cadmium						
Shell Size	07 08 09 10 11 12 14 16 18 20 22 24						
Length	Length in ¼ inch increments. ¾ inch minimum. 3 = .75 inches (minimum) 8 = 2 inches 4 = 1 inch 9 = 2.25 inches 5 = 1.25 inches 10 = 2.5 inches 6 = 1.5 inches 12 = 3 inches 7 = 1.75 inches 16 = 4 inches						
Attachment Type (Table I)	N = No attachment G = Nylon rope U = SST rope with polyurethane coating H = SST rope with high temperature translucent FEP jacket S = Sash chain, #8, SST						
Attachment Length	Omit for attachment type N (no attachment) Lanyard length in ½ inch increments. e.g. 12 = 6 inches, 16 = 8 inches						
Attachment Ring Inside Diameter	Omit for attachment type N (no attachment) 04 = .126 (3.20) diameter 06 = .145 (3.68) diameter 08 = .188 (4.78) diameter 10 = .197 (5.00) diameter						

Shell Size	A ISO Metric Thread	øB Max.
07	M8 x 1.0-6H	.500 (12.70)
08	M10 x 1.0-6H	.570 (14.48)
09	M12 x 1.0-6H	.650 (16.51)
10	M14 x 1.0-6H	.750 (19.05)
11	M15 x 1.0-6H	.790 (20.07)
12	M17 x 1.0-6H	.870 (22.10)
14	M19 x 1.0-6H	.950 (24.13)
16	M22 x 1.0-6H	1.070 (27.18)
18	M25 x 1.0-6H	1.180 (29.97)
20	M28 x 1.0-6H	1.300 (33.02)
22	M31 x 1.0-6H	1.420 (36.07)
24	M34 x 1.0-6H	1.540 (39.12)




ENVIRONMENTAL, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

809*060 Thin Lip Environmental Shrink Boots




Protect Your Cable Harness with heat-shrinkable boots. These easy-to-use boots provide excellent electrical, mechanical and environmental protection. Heating the boot causes the boot to shrink onto the connector and cable. An adhesive lining bonds the boot to the connector and cable and fills small gaps for a complete seal. These lipped boots attach directly to Series 806 connectors with integral band platform.

Shrink boot installation guide and application instructions are available in the Series 77 Shrink Boot catalog or on the Glenair website.
(www.glenair.com/environmental_shrink_boots/index.htm)

Boot Size to Shell Size Reference	
Part Number	Shell Size
809*060-1	7/8
809*060-2	9
809*060-3	10/11
809*060-4	12/14/16
809*060-5	18
809*060-6	20/22/24

How To Order				
SAMPLE PART NUMBER		809S060	-3	HR
Product	809A060 = 90° boot 809B060 = 45° boot 809S060 = straight boot 809SL060 = straight boot, extended length			
	Boot Size (See Dimension Tables)	1 2 3 4 5 6 see boot size to shell size reference table.		
Material and Adhesive Code (material and adhesive information follows dimension tables)	Boot Material	No Adhesive	Pre-coated with Adhesive	
	Standard Type 1 Fluid-Resistant Elastomer	U	Hot Melt Polyamide (W1) (Omit)	High Performance Epoxy (R) R
	Low Smoke/Zero Halogen Type 2 Elastomer	HU	H	HR

809S060 Straight Boots




Boot Size	A Min.	B Min.	C Max.	D Ref.	E Max.	F Ref.	H Ref.	Cable Range	
								Maximum	Minimum
1	.390 (9.91)	.390 (9.91)	.260 (6.60)	1.370 (34.80)	.080 (2.03)	.030 (0.76)	.750 (19.05)	.230 (5.84)	.100 (2.54)
2	.669 (16.99)	.669 (16.99)	.300 (7.62)	1.500 (38.10)	.140 (3.56)	.032 (0.81)	.750 (19.05)	.500 (12.70)	.170 (4.32)
3	.945 (24.00)	.945 (24.00)	.390 (9.91)	1.500 (38.10)	.200 (5.08)	.035 (0.89)	.750 (19.05)	.800 (20.32)	.240 (6.10)
4	1.181 (30.00)	1.181 (30.00)	.550 (13.97)	2.170 (55.12)	.240 (6.10)	.039 (0.99)	1.180 (29.97)	1.020 (25.91)	.280 (7.11)
5	1.260 (32.00)	1.260 (32.00)	.710 (18.03)	2.640 (67.06)	.280 (7.11)	.039 (0.99)	1.300 (33.02)	1.120 (28.45)	.300 (7.62)
6	1.417 (35.99)	1.417 (35.99)	.900 (22.86)	3.150 (80.01)	.330 (8.38)	.047 (1.19)	1.570 (39.88)	1.200 (30.48)	.350 (8.89)

Series 806

Mil-Aero Connectors


809-060 Thin Lip Environmental Shrink Boots

809A060 90° Boots



Boot Size	A Min.	B Min.	C Max.	D Ref.	E Max.	F Ref.	G Ref.	Cable Range	
								Maximum	Minimum
1	.390 (9.91)	.390 (9.91)	.260 (6.60)	.790 (20.07)	.095 (2.41)	.032 (0.81)	.750 (19.05)	.230 (5.84)	.100 (2.54)
2	.669 (16.99)	.669 (16.99)	.310 (7.87)	.790 (20.07)	.140 (3.56)	.032 (0.81)	.790 (20.07)	.500 (12.70)	.170 (4.32)
3	.945 (24.00)	.945 (24.00)	.390 (9.91)	.980 (24.89)	.200 (5.08)	.040 (1.02)	.980 (24.89)	.800 (20.32)	.240 (6.10)
4	1.181 (30.00)	1.181 (30.00)	.530 (13.46)	1.060 (26.92)	.220 (5.59)	.046 (1.17)	1.260 (32.00)	1.020 (25.91)	.270 (6.86)
5	1.260 (32.00)	1.260 (32.00)	.710 (18.03)	1.260 (32.00)	.280 (7.11)	.052 (1.32)	1.540 (39.12)	1.120 (28.45)	.300 (7.62)
6	1.417 (35.99)	1.417 (35.99)	.900 (22.86)	1.500 (38.10)	.330 (8.38)	.052 (1.32)	1.930 (49.02)	1.200 (30.48)	.350 (8.89)

809B060 45° Boots



Boot Size	A Min.	B Min.	C Max.	D Ref.	E Max.	F Ref.	G Ref.	Cable Range	
								Maximum	Minimum
1	.390 (9.91)	.390 (9.91)	.260 (6.60)	.600 (15.24)	.080 (2.03)	.030 (0.76)	.560 (14.22)	.230 (5.84)	.100 (2.54)
2	.669 (16.99)	.669 (16.99)	.300 (7.62)	.640 (16.26)	.140 (3.56)	.035 (0.89)	.620 (15.75)	.500 (12.70)	.170 (4.32)
3	.945 (24.00)	.945 (24.00)	.390 (9.91)	.500 (12.70)	.160 (4.06)	.040 (1.02)	.750 (19.05)	.800 (20.32)	.240 (6.10)
4	1.181 (30.00)	1.181 (30.00)	.550 (13.97)	.748 (19.00)	.230 (5.84)	.043 (1.09)	1.180 (29.97)	1.020 (25.91)	.280 (7.11)
5	1.260 (32.00)	1.260 (32.00)	.710 (18.03)	.984 (24.99)	.280 (7.11)	.065 (1.65)	1.380 (35.05)	1.120 (28.45)	.300 (7.62)
6	1.417 (35.99)	1.417 (35.99)	.900 (22.86)	1.260 (32.00)	.330 (8.38)	.065 (1.65)	1.570 (39.88)	1.200 (30.48)	.350 (8.89)

ENVIRONMENTAL, MICRO MINIATURE CIRCULAR


Series 806

Mil-Aero Connectors

809-060 Thin Lip Environmental Shrink Boots



809SL060 Straight Long Tail Boots



Boot Size	A Min.	B Min.	C Max.	D Ref	E Max.	F Ref.	H Ref.	Cable Range	
								Maximum	Minimum
1	.390 (9.91)	.390 (9.91)	.280 (7.11)	2.500 (63.50)	.080 (2.03)	.045 (1.14)	.750 (19.05)	.230 (5.84)	.100 (2.54)
2	.669 (16.99)	.669 (16.99)	.310 (7.87)	2.500 (63.50)	.140 (3.56)	.045 (1.14)	.750 (19.05)	.500 (12.70)	.170 (4.32)
3	.945 (24.00)	.945 (24.00)	.390 (9.91)	2.500 (63.50)	.200 (5.08)	.045 (1.14)	.750 (19.05)	.800 (20.32)	.240 (6.10)
4	1.181 (30.00)	1.181 (30.00)	.550 (13.97)	3.000 (76.20)	.240 (6.10)	.045 (1.14)	1.180 (29.97)	1.020 (25.91)	.280 (7.11)

Boot Material Information

Type 1 High Performance Elastomer

Semi-rigid high performance boots combine excellent resistance to fuels, oils and solvents with superior performance at extreme temperatures. Material meets the requirements of VG95343 Type 6, BSG 198-5-DE, EN62329-102 and SAE AS5258 Type H. These boots are ideal for demanding applications such as military vehicles and petrochemical exploration.

Type 2 Zero halogen

Halogen-free polyolefin boots meet low smoke and toxicity requirements of shipboard, transit and aircraft systems. These Low Smoke/Zero Halogen (LSZH) boots meet the requirements of NAVSEA 5617649, VG95343 Part 29, BSG 198-5-DF, EN62329-101 and SAE AS5258 Type G. Resistance to oils, fuels and solvents.

Shrink Boot Typical Material Properties

Property	Type 1 High Performance Elastomer	Type 2 Zero Halogen Polyolefin
Flexibility	Semi-rigid	Semi-flexible
Operating Temperature Range	-75°C to +150°C	-40°C to +130°C
Shrink Temperature (min.)	135°C	135°C
Tensile Strength (psi)	1700	1100
Elongation (% min.)	400	250
Long Term Heat Aging	3000 hrs, 150°C	3000 hrs, 135°C
Heat Shock	4 hrs, 215°C	4 hrs, 215°C
Heat Aging	168 hrs, 160°C	168 hrs, 160°C
Dielectric Strength (V/mil)	300	380
Volume Resistivity (ohms-cm)	10 ¹³	10 ¹²
Water Absorption (%)	0.5	0.5
Flammability	Burn Time <15 sec	Burn Length <25mm
RoHS Compliant	Yes	Yes
Oxygen Index (% min.)	N/A	30
Temperature Index (0C)	N/A	250
Smoke Index (max.)	N/A	20
Toxicity Index (max.)	N/A	3
Lubricating Oil Resistance	Very Good	Good
Hydraulic Fluid Resistance	Very Good	Good
Aviation Fuel Resistance	Very Good	Good
Gasoline Resistance	Very Good	Fair
De-Icing Fluid Resistance	Excellent	Very Good
Automotive Diesel Resistance	Good	Fair

Pre-Coat Adhesive Properties

Attribute	W1 Standard Poly- amide Hot Melt Adhesive	R High Performance Epoxy Pre-coat
Continuous Operating Temp.	-55° to +125°C	-75° to +150°C
Resistance to Fuels, Oils & Fluids	Good	
Low Toxicity, Zero Halogen	Yes	
IEC 62329-2 Dynamic Shear, 23°C	300N	300N
IEC 62329-2 Dynamic Shear, 100°C	30N	110N
IEC 62329-2 Dynamic Shear, 150°C	(not rated)	30N
IEC 62329-2 Heat Shock, 4 hrs., 215°C	Peel adhesion > 60N/25mm Dynamic shear > 300N	
IEC 62329-2 Heat Aging, 168 hrs., 160°C	Peel adhesion > 60N/25mm Dynamic shear > 300N	
IEC 62329-2 Peel Adhesion	>60N/25mm	
IEC 62329-2 Fluid Resistance Lubricating Oil 0-156 Aircraft Grease G-354 Hydraulic Fluid H-520 Water Turbine Fuel F-34	24 hrs. immersion @ 70°C Dynamic shear > 150N	


MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
Torque Values




Series 806 Recommended Torque Values (in-lbs)														
Shell Size	Coupling				Jam Nut				Backshell					
	Standard		High Vibration		Hex Nut		Spanner Nut		Standard		Composite		High Vibration	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
7	7	11	12	16	26	30	20	25	25	35	17	22	35	45
8	7	11	12	16	26	30	20	25	25	35	20	25	42	52
9	7	11	12	16	32	36	20	25	30	40	20	30	51	61
10	10	14	20	24	38	42	25	30	30	40	20	30	63	73
11	10	14	20	24	43	48	25	30	30	40	20	30	71	81
12	10	14	20	24	49	54	25	30	30	40	25	35	79	89
14	10	14	28	32	60	66	25	30	35	45	25	35	105	115
16	12	16	36	40	72	78	25	30	35	45	25	35	111	121
18	14	18	44	48	83	90	25	30	35	45	30	40	111	121
20	17	21	52	56	94	102	25	30	35	45	30	40	111	121
22	35	39	60	64	106	114	25	30	75	85	35	45	131	141
24	40	44	68	72	117	126	25	30	75	85	35	45	131	141

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.


Size 8, 12, 16 PCB Footprints for Coax, Quadax, Twinax and El Ochito




#8 COAX




#8 DIFFERENTIAL TWINAX




#8 QUADAX




#8 TRIAX / CONCENTRIC TWINAX




#8 EL OCHITO



**50 / 75 OHM
#16 COAX**



**50 OHM
#12 COAX**



**75 OHM
#12 COAX**

PIN INTERFACE SHOWN
SOCKET INTERFACE OPPOSITE

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Size 22HD PC Board Layouts



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.


Arrangement No. 7-3

3x #22HD Contacts




Arrangement No. 8-4

4x #22HD Contacts




Arrangement No. 8-7

7x #22HD Contacts



Arrangement No. 9-11

11x #22HD Contacts



MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 22HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.


Arrangement No. 10-15
15x #22HD Contacts



Arrangement No. 11-19
19x #22HD Contacts



Arrangement No. 12-26
26x #22HD Contacts



MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Size 22HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 14-39
39x #22HD Contacts

Contact Position ID	Location		Contact Position ID	Location	
	X Axis	Y Axis		X Axis	Y Axis
1	.039	.232	21	.106	.119
2	.112	.207	22	.149	.057
3	.173	.160	23	.158	-.019
4	.216	.095	24	.131	-.091
5	.235	.019	25	.074	-.141
6	.228	-.058	26	.000	-.160
7	.197	-.129	27	-.074	-.141
8	.145	-.186	28	-.131	-.091
9	.077	-.223	29	-.158	-.019
10	.000	-.236	30	-.149	.057
11	-.077	-.223	31	-.106	.119
12	-.145	-.186	32	-.038	.155
13	-.197	-.129	33	.042	.072
14	-.228	-.058	34	.084	.000
15	-.235	.019	35	.042	-.072
16	-.216	.095	36	-.042	-.072
17	-.173	.160	37	-.084	.000
18	-.112	.207	38	-.042	.072
19	-.039	.232	39	.000	.000
20	.038	.155			



Arrangement No. 16-60
60x #22HD Contacts




Glenair

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 18-85

85x #22HD Contacts




MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 22HD PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 20-110

110x #22HD Contacts




MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 22HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 22-140
 140x #22HD Contacts



SERIES
806
MIL-AERO

186x #22HD Contacts



APPENDIX

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 20HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.


Arrangement No. 8-3
3x #20HD Contacts




Arrangement No. 9-5
5x #20HD Contacts



Arrangement No. 10-8
8x #20HD Contacts



Arrangement No. 11-10
10x #20HD Contacts



MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 20HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 12-15
15x #20HD Contacts



Arrangement No. 14-20
4x #20HD Contacts



Contact Position ID	Location	
	X Axis	Y Axis
1	.053	.215
2	.147	.166
3	.207	.079
4	.220	-.027
5	.182	-.126
6	.103	-.196
7	.000	-.222
8	-.103	-.196
9	-.182	-.126
10	-.220	-.027
11	-.207	.079
12	-.147	.166
13	-.053	.215
14	.058	.101
15	.117	.000
16	.058	-.101
17	-.058	-.101
18	-.117	.000
19	-.058	.101
20	.000	.000

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size 20HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 16-31

31x #20HD Contacts


Contact Position ID	Location		Contact Position ID	Location	
	X Axis	Y Axis		X Axis	Y Axis
1	.053	.283	17	-.053	.283
2	.152	.245	18	.057	.174
3	.230	.174	19	.148	.108
4	.277	.079	20	.183	.000
5	.287	-.027	21	.148	-.108
6	.258	-.128	22	.057	-.174
7	.194	-.213	23	-.057	-.174
8	.104	-.269	24	-.148	-.108
9	.000	-.288	25	-.183	.000
10	-.104	-.269	26	-.148	.108
11	-.194	-.213	27	-.057	.174
12	-.258	-.128	28	.000	.078
13	-.287	-.027	29	.078	.000
14	-.277	.079	30	.000	-.078
15	-.230	.174	31	-.078	.000
16	-.152	.245			



Arrangement No. 18-41

41x #20HD Contacts

Contact Position ID	Location		Contact Position ID	Location	
	X Axis	Y Axis		X Axis	Y Axis
1	.053	.336	22	.156	.176
2	.155	.303	23	.220	.083
3	.241	.241	24	.234	-.028
4	.303	.155	25	.194	-.134
5	.336	.053	26	.109	-.209
6	.336	-.053	27	.000	-.236
7	.303	-.155	28	-.109	-.209
8	.241	-.241	29	-.194	-.134
9	.155	-.303	30	-.234	-.028
10	.053	-.336	31	-.220	.083
11	-.053	-.336	32	-.156	.176
12	-.155	-.303	33	-.056	.229
13	-.241	-.241	34	.057	.118
14	-.303	-.155	35	.127	.029
15	-.336	-.053	36	.102	-.081
16	-.336	.053	37	.000	-.130
17	-.303	.155	38	-.102	-.081
18	-.241	.241	39	-.127	.029
19	-.155	.303	40	-.057	.118
20	-.053	.336	41	.000	.000
21	.056	.229			




MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 20HD PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 20-55

55x #20HD Contacts



Contact Pos. ID	Location		Contact Pos. ID	Location		Contact Pos. ID	Location	
	X Axis	Y Axis		X Axis	Y Axis		X Axis	Y Axis
1	.055	.400	20	-.330	.233	39	-.157	.254
2	.161	.370	21	-.255	.313	40	-.055	.293
3	.255	.313	22	-.161	.370	41	.055	.186
4	.330	.233	23	-.055	.400	42	.146	.127
5	.380	.135	24	.055	.293	43	.192	.028
6	.403	.028	25	.157	.254	44	.176	-.080
7	.395	-.082	26	.238	.180	45	.105	-.163
8	.358	-.186	27	.287	.082	46	.000	-.194
9	.295	-.275	28	.297	-.028	47	-.105	-.163
10	.210	-.345	29	.267	-.133	48	-.176	-.080
11	.109	-.389	30	.201	-.221	49	-.192	.028
12	.000	-.404	31	.108	-.278	50	-.146	.127
13	-.109	-.389	32	.000	-.299	51	-.055	.186
14	-.210	-.345	33	-.108	-.278	52	.000	.088
15	-.295	-.275	34	-.201	-.221	53	.088	.000
16	-.358	-.186	35	-.267	-.133	54	.000	-.088
17	-.395	-.082	36	-.297	-.028	55	-.088	.000
18	-.403	.028	37	-.287	.082			
19	-.380	.135	38	-.238	.180			

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 20HD PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 22-69
69x #20HD Contacts



Contact ID	Location		Contact Position ID	Location		Contact Position ID	Location		Contact Position ID	Location	
	X Axis	Y Axis		X Axis	Y Axis		X Axis	Y Axis		X Axis	Y Axis
1	.055	.451	19	-.441	-.109	37	-.055	-.345	55	-.152	-.191
2	.161	.425	20	-.454	.000	38	-.158	-.311	56	-.220	-.106
3	.258	.374	21	-.441	.109	39	-.247	-.247	57	-.244	.000
4	.340	.301	22	-.402	.211	40	-.311	-.158	58	-.220	.106
5	.402	.211	23	-.340	.301	41	-.345	-.055	59	-.152	.191
6	.441	.109	24	-.258	.374	42	-.345	.055	60	-.054	.238
7	.454	.000	25	-.161	.425	43	-.311	.158	61	.053	.128
8	.441	-.109	26	-.055	.451	44	-.247	.247	62	.128	.053
9	.402	-.211	27	.055	.345	45	-.158	.311	63	.128	-.053
10	.340	-.301	28	.158	.311	46	-.055	.345	64	.053	-.128
11	.258	-.374	29	.247	.247	47	.054	.238	65	-.053	-.128
12	.161	-.425	30	.311	.158	48	.152	.191	66	-.128	-.053
13	.055	-.451	31	.345	.055	49	.220	.106	67	-.128	.053
14	-.055	-.451	32	.345	-.055	50	.244	.000	68	-.053	.128
15	-.161	-.425	33	.311	-.158	51	.220	-.106	69	.000	.000
16	-.258	-.374	34	.247	-.247	52	.152	-.191			
17	-.340	-.301	35	.158	-.311	53	.054	-.238			
18	-.402	-.211	36	.055	-.345	54	-.054	-.238			

APPENDIX

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

Size 20HD PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

Arrangement No. 24-92

92x #20HD Contacts

Contact Position ID	Location		Contact Position ID	Location	
	X Axis	Y Axis		X Axis	Y Axis
1	.053	.523	47	-.334	-.256
2	.158	.502	48	-.389	-.161
3	.255	.460	49	-.417	-.055
4	.343	.399	50	-.417	.055
5	.416	.322	51	-.389	.161
6	.472	.232	52	-.334	.256
7	.509	.132	53	-.256	.334
8	.525	.027	54	-.161	.389
9	.520	-.080	55	-.055	.417
10	.493	-.183	56	.055	.311
11	.446	-.278	57	.158	.274
12	.381	-.362	58	.242	.203
13	.301	-.432	59	.297	.108
14	.207	-.483	60	.316	.000
15	.106	-.515	61	.297	-.108
16	.000	-.526	62	.242	-.203
17	-.106	-.515	63	.158	-.274
18	-.207	-.483	64	.055	-.311
19	-.301	-.432	65	-.055	-.311
20	-.381	-.362	66	-.158	-.274
21	-.446	-.278	67	-.242	-.203
22	-.493	-.183	68	-.297	-.108
23	-.520	-.080	69	-.316	.000
24	-.525	.027	70	-.297	.108
25	-.509	.132	71	-.242	.203
26	-.472	.232	72	-.158	.274
27	-.416	.322	73	-.055	.311
28	-.343	.399	74	.055	.204
29	-.255	.460	75	.149	.149
30	-.158	.502	76	.204	.055
31	-.053	.523	77	.204	-.055
32	.055	.417	78	.149	-.149
33	.161	.389	79	.055	-.204
34	.256	.334	80	-.055	-.204
35	.334	.256	81	-.149	-.149
36	.389	.161	82	-.204	-.055
37	.417	.055	83	-.204	.055
38	.417	-.055	84	-.149	.149
39	.389	-.161	85	-.055	.204
40	.334	-.256	86	.053	.092
41	.256	-.334	87	.106	.000
42	.161	-.389	88	.053	-.092
43	.055	-.417	89	-.053	-.092
44	-.055	-.417	90	-.106	.000
45	-.161	-.389	91	-.053	.092
46	-.256	-.334	92	.000	.000



MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 16 PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.


Arrangement No. 8-1
1x #16 Contacts




Arrangement No. 10-2
2x #16 Contacts



Arrangement No. 11-4
4x #16 Contacts



Arrangement No. 12-5
5x #16 Contacts



SERIES
806
MIL-AERO

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 16 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.

Arrangement No. 18-15
15x #16 Contacts



ID NO	LOCATION	
	X	Y
1	.099	.304
2	.259	.188
3	.320	.000
4	.259	-.188
5	.099	-.304
6	-.099	-.304
7	-.259	-.188
8	-.320	.000
9	-.259	.188
10	-.099	.304
11	.089	.122
12	.144	-.047
13	.000	-.151
14	-.144	-.047
15	-.089	.122

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 16 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.

Arrangement No. 20-22
22x #16 Contacts



ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	0.084	0.368	12	-0.340	0.164
2	0.235	0.295	13	-0.235	0.295
3	0.340	0.164	14	-0.084	0.368
4	0.378	0.0	15	0.0	0.210
5	0.340	-0.164	16	0.164	0.131
6	0.235	-0.295	17	0.204	-0.047
7	0.084	-0.368	18	0.091	-0.189
8	-0.084	-0.368	19	-0.091	-0.189
9	-0.235	-0.295	20	-0.204	-0.047
10	-0.340	-0.164	21	-0.164	0.131
11	-0.378	0.0	22	0.0	0.0

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 16 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.

Arrangement No. 22-24
24x #16 Contacts



ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	0.084	0.397	13	-0.352	0.203
2	0.239	0.329	14	-0.239	0.329
3	0.352	0.203	15	-0.084	0.397
4	0.404	0.042	16	0.0	0.238
5	0.386	-0.126	17	0.168	0.168
6	0.302	-0.272	18	0.238	0.0
7	0.165	-0.371	19	0.168	-0.168
8	0.0	-0.406	20	0.0	-0.238
9	-0.165	-0.371	21	-0.168	-0.168
10	-0.302	-0.272	22	-0.238	0.0
11	-0.386	-0.126	23	-0.168	0.168
12	-0.404	0.042	24	0.0	0.0

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Size 16 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.

Arrangement No. 24-35

35x #16 Contacts



ID NO	LOCATION X	LOCATION Y	ID NO	LOCATION X	LOCATION Y	ID NO	LOCATION X	LOCATION Y
1	0.087	0.490	13	-0.170	-0.468	25	-0.085	-0.319
2	0.249	0.431	14	-0.498	0.0	26	-0.233	-0.233
3	0.382	0.320	15	-0.468	0.170	27	-0.319	-0.085
4	0.468	0.170	16	-0.382	0.320	28	-0.319	0.085
5	0.498	0.0	17	-0.249	0.431	29	-0.233	0.233
6	0.468	-0.170	18	-0.087	0.490	30	-0.085	0.319
7	0.382	-0.320	19	0.085	0.319	31	0.0	0.162
8	0.249	-0.431	20	0.233	0.233	32	0.154	0.050
9	0.087	-0.490	21	0.319	0.085	33	0.095	-0.131
10	-0.087	-0.490	22	0.319	-0.085	34	-0.095	-0.131
11	-0.249	-0.431	23	0.233	-0.233	35	-0.154	0.050
12	-0.382	-0.320	24	0.085	-0.319	----	----	----

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 12 PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.


Arrangement No. 9-1
1x #12 Contact




Arrangement No. 12-2
2x #12 Contacts



Arrangement No. 14-3
3x #12 Contacts



Arrangement No. 16-4
4x #12 Contacts



MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Size 12 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.


Arrangement No. 16-7

7x #12 Contacts



Arrangement No. 18-8

8x #12 Contacts



MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Size 12 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 20-11

11x #12 Contacts



ID NO	LOCATION	
	X	Y
1	.114	.314
2	.290	.167
3	.329	-.058
4	.215	-.256
5	.000	-.335
6	-.215	-.256
7	-.329	-.058
8	-.290	.167
9	-.114	.314
10	.110	.000
11	-.110	.000

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors


Size 12 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 22-13

13x #12 Contacts



ID NO	LOCATION	
	X	Y
1	.112	.345
2	.294	.213
3	.363	.000
4	.294	-.213
5	.112	-.345
6	-.112	-.345
7	-.294	-.213
8	-.363	.000
9	-.294	.213
10	-.112	.345
11	.000	.143
12	.124	-.072
13	-.124	-.072

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 12 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 24-19
19x #12 Contacts




ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	.118	.440	11	-.322	.322
2	.322	.322	12	-.118	.440
3	.440	.118	13	.000	.235
4	.440	-.118	14	.204	.118
5	.322	-.322	15	.204	-.118
6	.118	-.440	16	.000	-.235
7	-.118	-.440	17	-.204	-.118
8	-.322	-.322	18	-.204	.118
9	-.440	-.118	19	.000	.000
10	-.440	.118			

MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 8 PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadax, and El Ochoito PC tail footprints.

Arrangement No. 10-1
 1x #8 Contacts



Arrangement No. 16-2
 2x #8 Contacts




MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 8 PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadax, and El Ochito PC tail footprints.

Arrangement No. 18-3
 3x #8 Contact



Arrangement No. 20-4
 4x #8 Contacts




MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 8 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadrax, and El Ocho PC tail footprints.

Arrangement No. 22-5
 5x #8 Contacts




MICRO MINIATURE CIRCULAR
Series 806
Mil-Aero Connectors
 Size 8 PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadrax, and EI Ochito PC tail footprints.

Arrangement No. 24-8
 8x #8 EI Ochito Contacts




Size 22 and 16 combination PCB footprints




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.

Arrangement No. 10-8A


2x #16 and 6x #22HD Contacts



Arrangement No. 11-13




Arrangement No. 12-27
1x #16 and 26x #22HD Contacts




ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	.040	.199	15	-.113	.169
2	.113	.169	16	-.040	.199
3	.169	.113	17	.040	.121
4	.199	.040	18	.103	.075
5	.199	-.040	19	.127	.000
6	.169	-.113	20	.103	-.075
7	.113	-.169	21	.040	-.121
8	.040	-.199	22	-.040	-.121
9	-.040	-.199	23	-.103	-.075
10	-.113	-.169	24	-.127	.000
11	-.169	-.113	25	-.103	.075
12	-.199	-.040	26	-.040	.121
13	-.199	.040	A	.000	.000
14	-.169	.113			

APPENDIX

Size 22 and 16 combination PCB footprints



4x #16 and 17x #22HD Contacts




Size 22 and 16 combination PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 16 coax PC tail footprints.


Arrangement No. 16-41

4x #16 and 37x #22HD Contacts




ID NO	LOCATION	Y	ID NO	LOCATION	Y	ID NO	LOCATION	Y
	X			X			X	
1	0.039	0.299	15	-0.184	-0.240	29	0.173	-0.145
2	0.116	0.279	16	-0.240	-0.184	30	0.113	-0.196
3	0.184	0.240	17	-0.279	-0.116	31	-0.113	-0.196
4	0.240	0.184	18	-0.299	-0.039	32	-0.173	-0.145
5	0.279	0.116	19	-0.299	0.039	33	-0.212	-0.077
6	0.299	0.039	20	-0.279	0.116	34	-0.212	0.077
7	0.299	-0.039	21	-0.240	0.184	35	-0.173	0.145
8	0.279	-0.116	22	-0.184	0.240	36	-0.113	0.196
9	0.240	-0.184	23	-0.116	0.279	37	0.0	0.0
10	0.184	-0.240	24	-0.039	0.299	A	0.0	0.120
11	0.116	-0.279	25	0.113	0.196	B	0.120	0.0
12	0.039	-0.299	26	0.173	0.145	C	0.0	-0.120
13	-0.039	-0.299	27	0.212	0.077	D	-0.120	0.0
14	-0.116	-0.279	28	0.212	-0.077	--	----	----

Size 22 and 16 combination PCB footprints



4x #16 and 55x #22HD Contacts



ID NO	LOCATION		ID NO	LOCATION		ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y		X	Y		X	Y
1	0.040	0.353	16	-0.117	-0.335	31	0.151	0.235	46	-0.276	0.040
2	0.117	0.335	17	-0.189	-0.301	32	0.211	0.183	47	-0.254	0.116
3	0.189	0.301	18	-0.251	-0.251	33	0.254	0.116	48	-0.211	0.183
4	0.251	0.251	19	-0.301	-0.183	34	0.276	0.040	49	-0.151	0.235
5	0.301	0.183	20	-0.335	-0.117	35	0.276	-0.040	50	-0.079	0.268
6	0.335	0.117	21	-0.353	-0.040	36	0.254	-0.116	51	0.144	0.144
7	0.353	0.040	22	-0.353	0.040	37	0.211	-0.183	52	0.144	-0.144
8	0.353	-0.040	23	-0.335	0.117	38	0.151	-0.235	53	-0.144	-0.144
9	0.335	-0.117	24	-0.301	0.183	39	0.079	-0.268	54	-0.144	0.144
10	0.301	-0.183	25	-0.251	0.251	40	0.000	-0.279	55	0.000	0.000
11	0.251	-0.251	26	-0.189	0.301	41	-0.079	-0.268	A	0.000	0.120
12	0.189	-0.301	27	-0.117	0.335	42	-0.151	-0.235	B	0.120	0.000
13	0.117	-0.335	28	-0.040	0.353	43	-0.211	-0.183	C	0.000	-0.120
14	0.040	-0.353	29	0.000	0.279	44	-0.254	-0.116	D	-0.120	0.000
15	-0.040	-0.353	30	0.079	0.268	45	-0.276	-0.040	--	----	----

MICRO MINIATURE CIRCULAR Series 806 Mil-Aero Connectors




Size 22 and 12 combination PCB footprints

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.


Arrangement No. 11-14

1x #12 and 13x #22HD Contacts



Arrangement No. 12-14

2x #12 and 12x #22HD Contacts



ID NO	LOCATION	
	X	Y
1	0.040	0.161
2	0.110	0.124
3	0.155	0.059
4	0.164	-0.020
5	0.136	-0.094
6	0.077	-0.147
7	0.000	-0.166
8	-0.077	-0.147
9	-0.136	-0.094
10	-0.164	-0.020
11	-0.155	0.059
12	-0.110	0.124
13	-0.040	0.161
A	0.000	0.000

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors

Size 22 and 12 combination PCB footprints



Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 14-22
2x #12 and 20x #22HD Contacts



ID NO	LOCATION	
	X	Y
1	.129	.197
2	.186	.145
3	.223	.077
4	.236	.000
5	.223	-.077
6	.186	-.145
7	.129	-.197
8	-.129	-.197
9	-.186	-.145
10	-.223	-.077
11	-.236	.000
12	-.223	.077
13	-.186	.145
14	-.129	.197
15	.141	.074
16	.160	.000
17	.141	-.074
18	-.141	-.074
19	-.160	.000
20	-.141	.074
A	.000	.110
B	.000	-.110

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors




Size 22 and 12 combination PCB footprints

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 16-32

4x #12 and 28x #22HD Contacts



ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	.039	.299	17	-.279	-.116
2	.116	.279	18	-.299	-.039
3	.184	.240	19	-.299	.039
4	.240	.184	20	-.279	.116
5	.279	.116	21	-.240	.184
6	.299	.039	22	-.184	.240
7	.299	-.039	23	-.116	.279
8	.279	-.116	24	-.039	.299
9	.240	-.184	25	.000	.223
10	.184	-.240	26	.233	.000
11	.116	-.279	27	.000	-.223
12	.039	-.299	28	-.233	.000
13	-.039	-.299	A	.109	.109
14	-.116	-.279	B	.109	-.109
15	-.184	-.240	C	-.109	-.109
16	-.240	-.184	D	-.109	.109

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors



Size 22 and 12 combination PCB footprints

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 16-42
2x #12 and 40x #22HD Contacts



ID NO	LOCATION X	LOCATION Y	ID NO	LOCATION X	LOCATION Y
1	0.039	0.299	22	-0.184	0.240
2	0.116	0.279	23	-0.116	0.279
3	0.184	0.240	24	-0.039	0.299
4	0.240	0.184	25	0.039	0.223
5	0.279	0.116	26	0.113	0.196
6	0.299	0.039	27	0.173	0.145
7	0.299	-0.039	28	0.173	-0.145
8	0.279	-0.116	29	0.113	-0.196
9	0.240	-0.184	30	0.039	-0.223
10	0.184	-0.240	31	-0.039	-0.223
11	0.116	-0.279	32	-0.113	-0.196
12	0.039	-0.299	33	-0.173	-0.145
13	-0.039	-0.299	34	-0.173	0.145
14	-0.116	-0.279	35	-0.113	0.196
15	-0.184	-0.240	36	-0.039	0.223
16	-0.240	-0.184	37	0.039	0.145
17	-0.279	-0.116	38	0.039	-0.145
18	-0.299	-0.039	39	-0.039	-0.145
19	-0.299	0.039	40	-0.039	0.145
20	-0.279	0.116	A	0.110	0.0
21	-0.240	0.184	B	-0.110	0.0

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors



Size 22 and 12 combination PCB footprints

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 12 coax PC tail footprints.

Arrangement No. 18-62
60x #22HD and 2x #12 Contacts




ID NO	LOCATION		ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y		X	Y
1	0.040	0.353	22	-0.353	0.040	43	-0.211	-0.183
2	0.117	0.335	23	-0.335	0.117	44	-0.254	-0.116
3	0.189	0.301	24	-0.301	0.189	45	-0.276	-0.040
4	0.251	0.251	25	-0.251	0.251	46	-0.276	0.040
5	0.301	0.189	26	-0.189	0.301	47	-0.254	0.116
6	0.335	0.117	27	-0.117	0.335	48	-0.211	0.183
7	0.353	0.040	28	-0.040	0.353	49	-0.151	0.235
8	0.353	-0.040	29	0.0	0.279	50	-0.079	0.268
9	0.335	-0.117	30	0.079	0.268	51	0.040	0.199
10	0.301	-0.189	31	0.151	0.235	52	0.113	0.169
11	0.251	-0.251	32	0.211	0.183	53	0.113	-0.169
12	0.189	-0.301	33	0.254	0.116	54	0.040	-0.199
13	0.117	-0.335	34	0.276	0.040	55	-0.040	-0.199
14	0.040	-0.353	35	0.276	-0.040	56	-0.113	-0.169
15	-0.040	-0.353	36	0.254	-0.116	57	-0.113	0.169
16	-0.117	-0.335	37	0.211	-0.183	58	-0.040	0.199
17	-0.189	-0.301	38	0.151	-0.235	59	0.0	0.127
18	-0.251	-0.251	39	0.079	-0.268	60	0.0	-0.127
19	-0.301	-0.189	40	0.0	-0.279	A	0.110	0.0
20	-0.335	-0.117	41	-0.079	-0.268	B	-0.110	0.0
21	-0.353	-0.040	42	-0.151	-0.235			

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadax, and El Ocho PC tail footprints.

Arrangement No. 14-20A

19x #22HD and 1x#8 Contacts




Size 22 and 8 combination PCB footprints

SERIES
806
MIL-AERO

Arrangement No. 16-22


20x #22HD and 2x#8 Contacts



Glenair®

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadrax, and EI Ocho PC tail footprints.

Arrangement No. 18-21



ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	-.113	.336	12	-.342	-.095
2	-.038	.353	13	-.038	.276
3	.038	.353	14	.038	.276
4	.113	.336	15	.258	-.105
5	.342	-.095	16	.220	-.171
6	.314	-.166	17	-.220	-.171
7	.271	-.230	18	-.258	-.105
8	.215	-.283	A	-.180	.104
9	-.215	-.283	B	.180	.104
10	-.271	-.230	C	.000	-.208
11	-.314	-.166			

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors




Size 22 and 8 combination PCB footprints

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadax, and El Ochito PC tail footprints.

Arrangement No. 20-28

24x #22HD and 4x #8 Contacts




ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	-.113	.397	16	-.397	.113
2	-.038	.411	17	.000	.337
3	.038	.411	18	.337	.000
4	.113	.397	19	.000	-.337
5	.397	.113	20	-.337	.000
6	.411	.038	21	.000	.056
7	.411	-.038	22	.056	.000
8	.397	-.113	23	.000	-.056
9	.113	-.397	24	-.056	.000
10	.038	-.411	A	-.180	.180
11	-.038	-.411	B	.180	.180
12	-.113	-.397	C	-.180	-.180
13	-.397	-.113	D	.180	-.180
14	-.411	-.038			
15	-.411	.038			

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed. See page 159 for size 8 coax, twinax, quadax, and El Ochito PC tail footprints.

Arrangement No. 22-44

40x #22HD and 4x #8 Contacts



dimensions provided on following page

MICRO MINIATURE CIRCULAR

Series 806


Mil-Aero Connectors




Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.

ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y
1	-.186	.400	23	-.426	.114
2	-.114	.426	24	-.400	.186
3	-.038	.439	25	-.038	.363
4	.038	.439	26	.038	.363
5	.114	.426	27	.363	.038
6	.186	.400	28	.363	-.038
7	.400	.186	29	.038	-.363
8	.426	.114	30	-.038	-.363
9	.439	.038	31	-.363	-.038
10	.439	-.038	32	-.363	.038
11	.426	-.114	33	.000	.293
12	.400	-.186	34	.293	.000
13	.186	-.400	35	.000	-.293
14	.114	-.426	36	-.293	.000
15	.038	-.439	37	.000	.054
16	-.038	-.439	38	.054	.000
17	-.114	-.426	39	.000	-.054
18	-.186	-.400	40	-.054	.000
19	-.400	-.186	A	-.180	.180
20	-.426	-.114	B	.180	.180
21	-.439	-.038	C	-.180	-.180
22	-.439	.038	D	.180	-.180

Size 22 and 8 combination PCB footprints



93 #22HD and 4 #8 Contacts



dimensions provided on following page

MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors



Size 22 and 8 combination PCB footprints

Recommended PCB Layouts are shown for the connector mounting side of PC board. Contact identification numbers are for pin connectors. Socket identification numbers are reversed.


ID NO	LOCATION		ID NO	LOCATION		ID NO	LOCATION	
	X	Y		X	Y		X	Y
1	0.038	0.532	34	-532	0.038	67	-0.408	-0.206
2	0.113	0.521	35	-0.521	0.113	68	-0.437	-0.134
3	0.186	0.499	36	-0.499	0.186	69	-0.453	-0.058
4	0.255	0.468	37	-0.468	0.255	70	-0.457	0.019
5	0.319	0.427	38	-0.427	0.319	71	-0.447	0.096
6	0.377	0.377	39	-0.377	0.377	72	-0.424	0.170
7	0.427	0.319	40	-0.319	0.427	73	-0.389	0.240
8	0.468	0.255	41	-0.255	0.468	74	-0.077	0.373
9	0.499	0.186	42	-0.186	0.499	75	0	0.381
10	0.521	0.113	43	-0.113	0.521	76	0.077	0.373
11	0.532	0.038	44	-0.038	0.532	77	0.373	0.077
12	0.532	-0.038	45	-0.223	0.399	78	0.381	0v
13	0.521	-0.113	46	-0.152	0.431	79	0.373	-0.077
14	0.499	-0.186	47	-0.077	0.450	80	0.077	-0.373
15	0.468	-0.255	48	0	0.457	81	0	-0.381
16	0.427	-0.319	49	0.077	0.450	82	-0.077	-0.373
17	0.377	-0.377	50	0.152	0.431	83	-0.373	-0.077
18	0.319	-0.427	51	0.223	0.399	84	-0.381	0
19	0.255	-0.468	52	0.389	0.240	85	-0.373	0.077
20	0.186	-0.499	53	0.424	0.170	86	0	0.305
21	0.113	-0.521	54	0.447	0.096	87	0.305	0
22	0.038	-0.532	55	0.457	0.019	88	0	-0.305
23	-0.038	-0.532	56	0.453	-0.058	89	-0.305	0
24	-0.113	-0.521	57	0.437	-0.134	90	0	0.054
25	-0.186	-0.499	58	0.408	-0.206	91	0.054	0
26	-0.255	-0.468	59	0.256	-0.379	92	0	-0.054
27	-0.319	-0.427	60	0.188	-0.416	93	-0.054	0
28	-0.377	-0.377	61	0.115	-0.442	A	-.180	.180
29	-0.427	-0.319	62	0.039	-0.455	B	.180	.180
30	-0.468	-0.255	63	-0.039	-0.455	C	-.180	-.180
31	-0.499	-0.186	64	-0.115	-0.442	D	.180	-.180
32	-0.521	-0.113	65	-0.188	-0.416			
33	-0.532	-0.038	66	-0.256	-0.379			



About Glenair, the Mission-Critical Interconnect Company

Commitment to Quality, Availability, and Customer Service

Glenair is proud of the quality, availability, and performance we build into our broad range of mission-critical interconnect solutions—from bulk wire and cable, to aerospace-grade connectors, wire-protection shielding and jacketing, complex cable assemblies, and more. Since our founding in 1956, Glenair has made an indelible mark on the high-reliability interconnect industry with its innovative technologies built exclusively in the United States, UK, Italy, and Germany. Glenair's Worldwide Quality System is ISO 9001 and AS9100 certified and registered. We also hold many discrete product and process certifications for specialty, high-performance markets including space, nuclear power, and rail. In addition to world-class quality, we are laser-focused on industry-leading fast turnaround on quotes and orders, and are universally recognized as being the easiest manufacturer in our industry to do business with. Here are some of the reasons why:



Lightning-fast turnarounds on quotes and special orders



ISO 9001 and AS9100 quality



Huge same-day shipment inventory



Full-spectrum, "no gap" product lines



Abundant engineering and technical support



No attitudinal constraints when it comes to customer convenience and service

No Dollar or Quantity Minimum Orders
NO MINS.

No MOQ on any product including wire and cable



Mil-qualified and Glenair signature technologies

SERIES
806
MIL-AERO



Made in America: From Design Engineering to Component Part Manufacture and Assembly


**Connector shells,
plating, inserts, contacts,
environmental seals, filter
arrays, assembly and test all
controlled in-house**




- Largest small form-factor connector engineering team in the industry
- Largest U.S. CNC metal turning operation in the high-rel interconnect industry
- Largest U.S. interconnect component part fabrication and assembly facility
- Massive same-day inventory of Mighty Mouse connectors and cables—bagged, tagged, and ready for immediate shipment

Other Signature Interconnect Technologies for Aircraft Electrical Wiring Interconnect Systems


ELECTRICAL CONTACTS / SEALING CONTACTS




Standard and high-density signal



Extended-duty signal (up to 1500 cycles)



High-speed, RF, and El Ochito® contacts



Lightweight sealing plugs and dummy sealing contacts


ULTRAMINIATURE CIRCULARS



Series 806 Mil-Aero: small form-factor equivalent for MIL-DTL-38999



Series 806 Mil-Aero glass-sealed hermetics



Series 806 Mil-Aero CODE RED-sealed hermetics

MIL-AERO CIRCULARS



QPL MIL-DTL-38999 Series III Suitable for Zones 1 and 2 only



SuperNine® MIL-DTL-38999 Series III + Better than QPL™ performance



SuperNine® MIL-DTL-38999 Series III + glass- and CODE RED-sealed hermetics

HIGH-SPEED DATALINK CONNECTORS



SuperSeal™ MIL-DTL-38999 RJ45



SuperSeal™ MIL-DTL-38999 USB 2.0



GateLink Pro high-speed data uplink


FIBER OPTICS



SuperNine® MIL-DTL-38999 Series III type tight-tolerance fiber optics



Series 806 Mil-Aero high-density fiber optics



Qualified fiber optic terminus

POWER CONNECTORS AND PRESSURE BOUNDARY FEEDTHRUS




PowerLoad™ power distribution connectors



PowerLoad™ bulkhead feedthru




Pressure boundary and firewall feedthrus




EMI/RFI BRAIDED SHIELDING AND PROTECTIVE COVERING



Band-Master ATS® advanced shield termination system



ArmorLite microfilament EMI/RFI shielding



Lightweight, flexible ground straps and HSTs



MasterWrap side-entry wraparound shielding

CONNECTOR BACKSHELLS AND ACCESSORIES



ProSeal spring-action protective covers



Environmental protective covers



Swing-Arm FLEX composite backsells




Swing-Arm standard and wide-mouth composite backsells

SPECIAL-PURPOSE EWIS TECHNOLOGIES




Advanced rectangular aviation backsells (ARINC 600 shown)



Receptacle / bulkhead connector nut plates



SpliceSaver time- and labor-saving wire splice replacement



Polymer- and metal-core conduit wire protection systems Suitable for Zones 5, 6, and 8



MISSION-CRITICAL INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497

Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com

www.glenair.com

Glenair East

20 Sterling Drive
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
Mansfield, Notts
NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 42
SE-169 27 Solna
Sweden

Telephone:
+46-8-50550000
sales@glenair.se

Glenair GmbH

Schaberweg 28
61348 Bad Homburg
Germany

Telephone:
06172 / 68 16 0
Facsimile:
06172 / 68 16 90
info@glenair.de

Glenair Iberica

C/ La Vega, 16
45612 Velada
Spain

Telephone:
+34-925-89-29-88
Facsimile:
+34-925-89-29-87
sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:
+39-051-782811
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

Glenair Korea

6-21Tapsil-ro 58beon-gil
Giheung-gu, Yongin-si
Gyeonggi-do
Republic of Korea

Telephone:
+82-07-5067-2437
Facsimile:
+82-504-375-4549
sales@glenair.kr