

SATA III 2280 M.2 SSD

MTS800

Datasheet

Products

TS1TMTS800
TS512GMTS800
TS256GMTS800
TS128GMTS800
TS64GMTS800
TS32GMTS800
TS16GMTS800

Product Description

M.2 2280 SSD, SATA3 B+M Key, MLC

Datasheet version

1.2



No.70, Xingzhong Rd., Neihu Dist., Taipei City 114, Taiwan, R.O.C.
Tel:+886-2-2792-8000 Fax:+886-2-2792-1614
www.transcend-info.com

Copyright© Transcend Information, Inc. All Rights Reserved.

 **Transcend**®

Revision History

| Revision No. | History | Released Date | Editor by |
|--------------|--|---------------|-----------|
| 1.0 | First version (WD 15nm) | 2019/12/26 | TSD |
| 1.1 | Vibration Format Updated Add 2.6 Recommended Measurement Point Revise 5.2.5 PS(Power shield) description Remove hardware purge (Optional) | 2020/05/25 | TSD |
| 1.2 | Update product image (UL LOGO) | 2021/05/20 | TSD |

Transcend MTS800 Features

| Part Name | Capacity |
|--------------|----------|
| TS1TMTS800 | 1TB |
| TS512GMTS800 | 512GB |
| TS256GMTS800 | 256GB |
| TS128GMTS800 | 128GB |
| TS64GMTS800 | 64GB |
| TS32GMTS800 | 32GB |
| TS16GMTS800 | 16GB |

FEATURES

- SATA 6Gbps
- 2D MLC NAND Flash
- M.2 SATA 2280 B+M Key
- DDR3 DRAM cache
- Global wear-leveling function
- Enhance Bad block management
- Power shield function
- BCH ECC function
- TRIM Command function
- Advanced Garbage Collection
- Supports S.M.A.R.T. function
- Supports DEVSLP mode
- Self-encrypting drives(SED) with AES-256 (Optional)

RELIABILITY¹⁾

- TBW
 - 1TB 2,360TB
 - 512GB 1,480TB
 - 256GB 740TB
 - 128GB 360TB
 - 64GB 180TB
 - 32GB 90 TB
 - 16GB 45 TB
- UBER 10^{-15}
- DWPD 2.6 DWPD
- MTBF 2,500,000 hours
- Data Retention 1 year
- Warranty 3 years

PERFORMANCE¹⁾

- Data Transfer Rate
 - Sequential Read Up to 530 MB/s
 - Sequential Write Up to 460 MB/s

ENVIRONMENTAL SPECIFICATIONS¹⁾

- Temperature
 - Operating 0°C to 70°C
 - Non-operating -40°C to 85°C
- Humidity(non-condensing) 5%~95%
- Shock 1500G, 0.5ms
- Vibration 20G, 7~2000Hz

POWER REQUIREMENTS¹⁾

- Supply voltage / Tolerance 3.3V±5%
- Active (max) 2.64W
- Idle (max) 0.41W

PHYSICAL DIMENSION

- Width 22.00±0.15mm
- Length 80.00±0.15mm
- Height(max) 3.58mm
- Weight Up to 9g

Note:

- 1) For detail information, please refer to document content.

Table of Content

| | |
|--|-----------|
| 1 Introduction | 6 |
| 1.1 General Feature Information..... | 6 |
| 1.2 Product List..... | 6 |
| 1.3 Ordering Information..... | 7 |
| 2 Product Specifications | 8 |
| 2.1 Interface and Compliance..... | 8 |
| 2.2 Drive Capacity..... | 8 |
| 2.3 System Performance..... | 8 |
| 2.4 Supply Voltage..... | 9 |
| 2.5 System Power Consumption..... | 9 |
| 2.6 Environment Specifications..... | 10 |
| 2.7 System Reliability..... | 11 |
| 3 Mechanical Specification | 12 |
| 4 Pin Assignments | 14 |
| 4.1 Pin Assignments..... | 14 |
| 5 Block Diagram and Function Explanations | 15 |
| 5.1 Block Diagram..... | 15 |
| 5.2 Function Explanations..... | 15 |
| 6 Technology Term Explanations | 17 |
| 6.1 TBW..... | 18 |
| 6.2 DWPD..... | 18 |
| 6.3 MTBF – Telcorida SR332..... | 18 |
| 7 Installation Requirements | 19 |
| 7.1 Card Insertion..... | 19 |
| 8 Command Descriptions | 20 |
| 8.1 Support ATA Commands..... | 20 |
| 8.2 SMART Data Structure..... | 22 |
| 8.3 SMART Attributes..... | 23 |
| 9 Contact Information | 24 |

1. Introduction

1.1 General Feature Information

Hardware Feature

- SATA 6Gbps
- Transcend Controller TS6500
- 2D MLC NAND Flash
- Temperature operation from 0°C to 70°C
- M.2 SATA 2280 B+M Key
- Embedded DDR3 DRAM cache
- Power shield function
- AES-256 function (Optional)

Firmware Feature

- Global wear-leveling function
- Enhance Bad block management function
- BCH ECC(Error Correction Code) function
- TRIM Command function
- Advanced Garbage Collection function
- StaticDataRefresh function
- S.M.A.R.T. function
- DEVSLP mode
- TCG-Opal function (Optional)

Software Feature

- Transcend SSD Scope Pro



TS1TMTS800

1.2 Product List

| Form Factor | Part Name | Capacity |
|-------------|--------------|----------|
| 2280-D2-B-M | TS1TMTS800 | 1TB |
| | TS512GMTS800 | 512GB |
| | TS256GMTS800 | 256GB |
| | TS128GMTS800 | 128GB |
| | TS64GMTS800 | 64GB |
| | TS32GMTS800 | 32GB |
| | TS16GMTS800 | 16GB |

1.3 Ordering Information

T S X X X G M T S 8 0 0

1 2 3 4 5

1 – Transcend

2 – SSD Density

3 – G: Gigabyte; T: Terabyte

4 – M.2 SATA device

5 – 2280 form factor

2. Product Specifications

2.1 Interface and Compliance

- SATA3, compatible to SATA2 and SATA1
- Compatible with ATA/ATAPI-7 Standard
- Native Command Queuing(NCQ) Command Set
- RoHS Compliance
- CE, FCC and BSMI Compliance

2.2 Drive Capacity

[Table 1] User Capacity and Addressable Sectors

| | 16GB | 32GB | 64GB | 128GB |
|---------------------------------|------------|------------|-------------|-------------|
| User-Addressable Sectors | 31,277,232 | 62,533,296 | 125,045,424 | 250,069,680 |
| Byte per Sector | 512 Byte | | | |

| | 256GB | 512GB | 1TB |
|---------------------------------|-------------|---------------|---------------|
| User-Addressable Sectors | 500,118,192 | 1,000,215,216 | 2,000,409,264 |
| Byte per Sector | 512 Byte | | |

2.3 System Performance

[Table 2] Sequential Read / Write Performance

| Read / Write | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|------------------|----------|----------|---------|---------|---------|---------|---------|
| Sequential Read | 140 MB/s | 280 MB/s | 520MB/s | 520MB/s | 520MB/s | 520MB/s | 530MB/s |
| Sequential Write | 30 MB/s | 50 MB/s | 100MB/s | 200MB/s | 400MB/s | 460MB/s | 460MB/s |

Note: Maximum transfer speed recorded

1) 25°C, test on GIGABYTE GA-Z87X-D3H, 4GB, Windows® 7 Professional with AHCI mode, benchmark utility CrystalDiskMark (version 3.0.1), copied file 1000MB.

2) The recorded performance is obtained while the SSD is not operated as an OS disk Physical Specification.

[Table 3] Random Read / Write Performance

| Read / Write | 16GB | 32GB | 64GB | 128GB |
|-------------------|------|------|------|-------|
| Random Read IOPS | 13K | 26K | 50K | 70K |
| Random Write IOPS | 6.5K | 13K | 26K | 50K |

| Read / Write | 256GB | 512GB | 1TB |
|-------------------|-------|-------|-----|
| Random Read IOPS | 70K | 70K | 75K |
| Random Write IOPS | 75K | 75K | 75K |

Note: Maximum transfer speed recorded

- 1) 25°C, test on GIGABYTE GA-Z87X-D3H, 4GB, Windows® 7 Professional with AHCI mode, benchmark utility IOmeter2006 with 4K file size and queue depth of 32, unit IOPS
- 2) The recorded performance is obtained while the SSD is not operated as an OS disk Physical Specification.

2.4 Supply Voltage

[Table 4] Supply Voltage

| Item | Requirements |
|--------------------------|--------------------|
| Allowable voltage | 3.3V±5% |
| Allowable noise / ripple | 100 mV p-p or less |

2.5 System Power Consumption

[Table 5] Power Consumption

| Read / Write | 16GB | 32GB | 64GB | 128GB |
|-----------------------------------|-------|-------|-------|-------|
| Active Write (Max.) ¹⁾ | 0.61W | 0.69W | 0.73W | 0.83W |
| Active Read (Max.) ¹⁾ | 0.59W | 0.64W | 0.64W | 0.66W |
| Idle | 0.28W | 0.28W | 0.28W | 0.26W |
| DEVSLP | | 5mW | | |

| Read / Write | 256GB | 512GB | 1TB |
|-----------------------------------|-------|-------|-------|
| Active Write (Max.) ¹⁾ | 1.80W | 2.51W | 2.64W |
| Active Read (Max.) ¹⁾ | 0.86W | 0.92W | 1.85W |
| Idle | 0.28W | 0.31W | 0.41W |
| DEVSLP | | 5mW | |

Note:

- 1) The power consumption is measured under SSD operation at maximum performance. The value is affected by system operation performance and workload.

2.6 Environment Specifications

[Table 6] Environment Specification


| Features | Operating ¹⁾ | Non-Operating ²⁾ |
|----------------------|---------------------------|--|
| Temperature | 0°C to +70°C | -40°C to 85°C |
| Temperature Gradient | 60°C/Hr | 60°C/Hr |
| Humidity | 5% to 95%, non-condensing | |
| Shock | | 1500G, duration 0.5 ms, 3 axis ³⁾ |
| Vibration | | 20G, 7~2000Hz, 3 axis ⁴⁾ |

Note:

- 1) The operating specification is regarded as Ambient Temperature. Standard grade (0°C to +70°C) and Industrial grade (-40°C to +85°C) indicate the temperature conditions for testing devices on programmable temperature and humidity chamber room.
- 2) The non-operating specification is regarded as storage specification.
- 3) Refer IEC 68-2-27 standard.
- 4) Refer IEC 68-2-6 standard.

Recommended Measurement Point

Recommended temperature measurement point is in the center of the connector inserted by the device. Sufficient airflow is recommended for proper operation on heavier workloads within the device operating temperature.



2.7 System Reliability

[Table 7] Telcordia SR332 issue 4 MTBF Specifications

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|-----------|-----------------|------|------|-------|-------|-------|-----|
| MTBF | 2,500,000 hours | | | | | | |

Note:

1) The calculation is based on 25°C.

[Table 8] UBER Specifications

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|-----------|------------|------|------|-------|-------|-------|-----|
| UBER | 10^{-15} | | | | | | |

Note:

1) Uncorrectable Bit Error Rate (UBER) is a metric for the rate of occurrence of data errors, equal to the number of data errors per bits read as specified in the JESD218 document of JEDEC standard. For the client application, JEDEC recommends that UBER shall be below 10^{-15} .

[Table 9] TBW (Terabytes Written) Specifications

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|-----------|-------|-------|--------|--------|--------|----------|----------|
| TBW | 45 TB | 90 TB | 180 TB | 360 TB | 740 TB | 1,480 TB | 2,360 TB |

Note:

1) TBW specification follows JESD219A Client workload.

[Table 10] Drive Write Per Day (DWPD) Specifications

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|--------------------|---------------|------|------|-------|-------|-------|-----|
| DWPD ¹⁾ | 2.6 (3 Years) | | | | | | |

Note:

1) DWPD is based on [Table 13] Warranty year to calculate.

[Table 11] Data Retention Specifications

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|----------------|--------|------|------|-------|-------|-------|-----|
| Data Retention | 1 year | | | | | | |

Note:

1) Data retention was measured by assuming that SSD reaches the maximum rated endurance at 30°C under power-off state.
2) The data retention is defined in JESD218 Requirements for standard classes of SSDs.

[Table 12] Power On to Ready

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|------------|-------|------|------|-------|-------|-------|-----|
| Setup time | 0.4 s | | | | | | |

[Table 13] Warranty

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|-----------|-----------------|------|------|-------|-------|-------|-----|
| Warranty | 3 years limited | | | | | | |


[Table 14] Regulations

| Parameter | 16GB | 32GB | 64GB | 128GB | 256GB | 512GB | 1TB |
|------------|------------------|------|------|-------|-------|-------|-----|
| Compliance | CE, FCC and BSMI | | | | | | |

3. Mechanical Specification

The figure below illustrates the Transcend M.2 Type 2280-D2-B-M Solid State Drive.
 [Table 15] Physical Dimensions and Weight

| Model | Height (mm) | Width (mm) | Length (mm) | Weight (gram) |
|--|-------------|------------|-------------|---------------|
| 16GB/32GB/64GB/128GB/ 256GB/512GB/1TB | Max 3.58 | 22.00±0.15 | 80.00±0.15 | Max 9g |



4. Pin Assignments

4.1 Pin Assignments

[Table 16] Pin Assignments


| Pin No. | Pin Name | Pin No. | Pin Name | Pin No. | Pin Name | Pin No. | Pin Name |
|---------|------------------------|---------|-----------------------|---------|------------------------|---------|--------------------|
| 01 | CONFIG_3 ¹⁾ | 02 | 3.3V | 39 | GND | 40 | NC |
| 03 | GND | 04 | 3.3V | 41 | TX+ | 42 | NC |
| 05 | NC | 06 | NC | 43 | TX- | 44 | NC |
| 07 | NC | 08 | NC | 45 | GND | 46 | NC |
| 09 | NC | 10 | DAS/DSS ²⁾ | 47 | RX- | 48 | NC |
| 11 | NC | 12 | NOTCH | 49 | RX+ | 50 | NC |
| 13 | NOTCH | 14 | NOTCH | 51 | GND | 52 | NC |
| 15 | NOTCH | 16 | NOTCH | 53 | NC | 54 | NC |
| 17 | NOTCH | 18 | NOTCH | 55 | NC | 56 | MFG1 ⁴⁾ |
| 19 | NOTCH | 20 | NC | 57 | GND | 58 | MFG2 ⁴⁾ |
| 21 | CONFIG_0 ¹⁾ | 22 | NC | 59 | NOTCH | 60 | NOTCH |
| 23 | NC | 24 | NC | 61 | NOTCH | 62 | NOTCH |
| 25 | NC | 26 | NC | 63 | NOTCH | 64 | NOTCH |
| 27 | GND | 28 | NC | 65 | NOTCH | 66 | NOTCH |
| 29 | NC | 30 | NC | 67 | NC | 68 | NC |
| 31 | NC | 32 | NC | 69 | CONFIG_1 ¹⁾ | 70 | 3.3V |
| 33 | GND | 34 | NC | 71 | GND | 72 | 3.3V |
| 35 | NC | 36 | NC | 73 | GND | 74 | 3.3V |
| 37 | NC | 38 | DEVSLP ³⁾ | 75 | CONFIG_2 ¹⁾ | | |

Note:

- 1) For SATA M.2 SSD, these pins are connected to GND internally.
- 2) Device Activity Signal / Disable Staggered Spin-up
- 3) Device Sleep is an input pin. If driven high, the host is informing the SSD to enter a low power state.
- 4) Manufacturing pins. Do not connect.

5. Block Diagram and Function Explanations

5.1 Block Diagram



5.2 Function Explanations

5.2.1 Global Wear Leveling Function

Global wear leveling ensures that every block has an even erase count. This helps to extend the life expectancy of an SSD.

There are three main processes in global wear leveling:

- (1) Record the block erase count and save this in the wear-leveling table.
- (2) Find the static-block and save this in the wear-leveling pointer.
- (3) Check the erase count when a block is pulled from the pool of spare blocks. If the block erase count is larger than WEARCNT, then swap the static-block and the over-count-block.

5.2.2 Bad Block Management Function

When the flash encounters ECC fail, program fail or erase fail, the controller will mark the block as a bad block. This will prevent the usage of bad blocks which may result in data loss in the future.

5.2.3 Enhanced S.M.A.R.T. function

Transcend SSD supports S.M.A.R.T. command (Self-Monitoring, Analysis, and Reporting Technology) that allows users to read the health information of the SSD. Transcend also define some innovated S.M.A.R.T. features which allows the user to evaluate the status of the SSD in a much more efficient way.

5.2.4 StaticDataRefresh Technology

Normally, ECC engine corrections are taken place without affecting the host normal operations. As time passes by, the number of error bits accumulated in the read transaction exceeds the correcting capability of the ECC engine, resulting in corrupted data being sent to the host. In order to prevent such occurrence, the controller monitors the error bit levels at each read operation; when it reaches the preset threshold value, the controller automatically performs data refresh to "restore" the correct charge levels in the cell. This implementation practically restores the data to its original, error-free state, and hence lengthening data life.

5.2.5 PS(Power shield) Function

Power Shield (PS) is a basic technology supported by all Transcend's embedded SSDs to prevent internal NAND flash data loss in event of a sudden power outage. The internal voltage detection circuit (VDT) of the controller monitors the external power supply. When the external voltage drops from 5V to 4V or from 3.3V to 2.7V, the VDT activates the PS detection mechanism. When a sudden power outage occurs, the internal power shield circuit would trigger the PS function so that the controller will stop accepting new write commands. The write operation is terminated to ensure that the firmware and the data in the NAND flash are undamaged.

When the external voltage drops to a certain level, the internal voltage detection circuit (VDT) of the controller activates the PS mechanism. The SSD controller then stops accepting new write commands from the host, ensuring the integrity of existing data for the NAND flash.

The PS function ensures the safety of the data which has already been written into the flash before sudden power outage.

5.2.6 DEVSLP Function

DevSlp or DevSleep (regarded as device sleep or SATA DEVSLP) is a feature in SATA SSD which allows them to go into a low power "device sleep" mode when sent the appropriate signal, which uses one or two orders of magnitude less power than a traditional idle (about 5 mW). This function can help save battery power in platform idle, so that the user can operate the platform for longer time.

5.2.7 AES-256 Function(Optional)

Defined by the National Institute of Standards and Technology (NIST) under the Federal Information Processing Standards Publication 197 (FIPS PUB 197), the Advanced Encryption Standard (AES) specifies a FIPS-approved cryptographic algorithm that can be used to protect electronic data.

Transcend Information's SSDs, equipped with hardware-based AES-256 encryption, offer superior data protection and performance compared to competing offerings that utilize software-based or firmware-based encryption. With hardware-based encryption, all data are encrypted before being stored in NAND Flash. After the encrypted data has been written into the flash, it becomes virtually impossible to decrypt the data without the original key. Performance is also improved as compared to software-based solutions, since hardware-based encryption does not require system resources to perform the encryption/decryption process.

5.2.8 TCG-Opal Function(Optional)

Opal is a comprehensive set of guidelines. The target audience includes manufacturers of storage devices, software vendors, system integrators, and academia. These specifications cover the manufacture of storage devices, system setup, management, and use; they allow for password protection and hierarchical storage management, while preventing data from being stolen or tampered with.

They are self-encrypting devices: Data encryption is performed on the device, without need to pass through the host. The encryption key is also stored on the device (commonly AES is utilized).

(1) Features boot authentication:

When the user starts the device, the shadow MBR will conduct a pre-boot identification; where the user is cleared, the normal boot process will begin and connections to the devices are to be made.

(2) Sector specific permissions:

The device manager may create a logical block address (LBA) range and assign different permissions for each LBA range. Only users with the correct key for a particular LBA range may perform permitted actions. Where drive locations are password-protected, only users with the correct key will be authorized entry.

5.2.9 Transcend SSD Scope Pro

Transcend's SSD Scope Pro is a convenient software package that helps users monitor and manage SSD status via an intuitive interface. It offers various useful features, including drive information and S.M.A.R.T. status monitoring, diagnostic scan, secure erase, health indication, system clone, and monitoring. For more information, please refer the website link. <https://us.transcend-info.com/Embedded/Essay-20>

5.2.10 Other Functions

Transcend SSD embedded a lot of cutting-edge technology. Should you have any technical request, please contact the local support team or send us an e-mail.

6. Technology Term Explanations

6.1 TBW

Terabytes Written (TBW) directly measures how much you can write cumulatively into the drive over its lifetime. Essentially, it just includes the multiplication conducted above in the measurement itself.

For example, if your drive is rated for 365 TBW, that means you can write 365 TB into it before a replacement is required.

If its warranty period is 5 years, that works out to $365 \text{ TB} \div (5 \text{ years} \times 365 \text{ days/year}) = 200 \text{ GB of writes per day}$. If your drive was 200 GB in size, that's equivalent to 1 DWPD. Correspondingly, if your drive was rated for 3.65 PBW = 3,650 TBW, that works out to 2 TB of writes per day, or 10 DWPD.

As you can see, if you know the drive's size and warranty period, you can always calculate TBW from DWPD and vice-versa with simple multiplications or divisions. The two measurements are very similar.

6.2 DWPD

Drive Writes Per Day (DWPD) measures how many times you could overwrite the drive's entire size each day of its life. For example, suppose your drive is 200 GB and its warranty period is 5 years. If its DWPD is 1, that means you can write 200 GB (its size, one time) into it every single day for the next five years.

If you multiply that out, that's $200 \text{ GB per day} \times 365 \text{ days/year} \times 5 \text{ years} = 365 \text{ TB of cumulative writes before you may need to replace it}$.

If the DWPD is 10 instead of 1, that means you can write $10 \times 200 \text{ GB} = 2 \text{ TB}$ (its size, ten times) into it every day. Correspondingly, that's $3,650 \text{ TB} = 3.65 \text{ PB}$ of cumulative writes over 5 years.

6.3 MTBF – Telcordia SR332

MTBF (mean time between failures) is a measure of how reliable a hardware product or component is. For most components, the measurement is typically in thousands or even tens of thousands of hours between failures. For example, a SSD may have a mean time between failures of 200,000 hours. A desired MTBF can be used as a quantifiable objective when designing a new product. The MTBF figure can be developed as the result of intensive testing, based on actual product experience, or predicted by analyzing known factors. The manufacturer may provide it as an index of a product's or component's reliability and, in some cases, to give customers an idea of how much service to plan for. In Transcend MTBF data, we use Telcordia SR-332 Issue 4 method to do estimated calculation.


7. Installation Requirements

7.1 Card Insertion

Angles insertion is allowable and preferred; the intention is to minimize the insertion/extraction force.

- Minimum of angle of insertion is 5°

Minimum two step insertion is desirable; the intention is to minimize the insertion/extraction force.



8. Command Descriptions

8.1 Support ATA Commands

This table and the following paragraphs summarize the ATA command set.

[Table 17] ATA Command Table

| Support ATA/ATAPI Command | Code | Protocol |
|-------------------------------------|------------|-------------------|
| General Feature Set | | |
| EXECUTE DIAGNOSTICS | 90h | Device diagnostic |
| FLUSH CACHE | E7h | Non-data |
| IDENTIFY DEVICE | ECh | PIO data-In |
| Initialize Drive Parameters | 91h | Non-data |
| READ DMA | C8h | DMA |
| READ LOG Ext | 2Fh | PIO data-In |
| READ MULTIPLE | C4h | PIO data-In |
| READ SECTOR(S) | 20h | PIO data-In |
| READ VERIFY SECTOR(S) | 40h or 41h | Non-data |
| SET FEATURES | EFh | Non-data |
| SET MULTIPLE MODE | C6h | Non-data |
| WRITE DMA | CAh | DMA |
| WRITE MULTIPLE | C5h | PIO data-out |
| WRITE SECTOR(S) | 30h | PIO data-out |
| NOP | 00h | Non-data |
| READ BUFFER | E4h | PIO data-out |
| WRITE BUFFER | E8h | PIO data-out |
| Power Management Feature Set | | |
| CHECK POWER MODE | E5h or 98h | Non-data |
| IDLE | E3h or 97h | Non-data |
| IDLE IMMEDIATE | E1h or 95h | Non-data |
| SLEEP | E6h or 99h | Non-data |
| STANDBY | E2h or 96h | Non-data |
| STANDBY IMMEDIATE | E0h or 94h | Non-data |
| Security Mode Feature Set | | |
| SECURITY SET PASSWORD | F1h | PIO data-out |
| SECURITY UNLOCK | F2h | PIO data-out |
| SECURITY ERASE PREPARE | F3h | Non-data |
| SECURITY ERASE UNIT | F4h | PIO data-out |
| SECURITY FREEZE LOCK | F5h | Non-data |
| SECURITY DISABLE PASSWORD | F6h | PIO data-out |
| SMART Feature Set | | |

| | | |
|--|-----|--------------|
| SMART Disable Operations | B0h | Non-data |
| SMART Enable/Disable Autosave | B0h | Non-data |
| SMART Enable Operations | B0h | Non-data |
| SMART Execute Off-Line Immediate | B0h | Non-data |
| SMART Read LOG | B0h | PIO data-In |
| SMART Read Data | B0h | PIO data-In |
| SMART Read THRESHOLD | B0h | PIO data-In |
| SMART Return Status | B0h | Non-data |
| SMART SAVE ATTRIBUTE VALUES | B0h | Non-data |
| SMART WRITE LOG | B0h | PIO data-out |
| Host Protected Area Feature Set | | |
| Read Native Max Address | F8h | Non-data |
| Set Max Address | F9h | Non-data |
| Set Max Set Password | F9h | PIO data-out |
| Set Max Lock | F9h | Non-data |
| Set Max Freeze Lock | F9h | Non-data |
| Set Max Unlock | F9h | PIO data-out |
| 48-bit Address Feature Set | | |
| Flush Cache Ext | Eah | Non-data |
| Read Sector(s) Ext | 24h | PIO data-in |
| Read DMA Ext | 25h | DMA |
| Read Multiple Ext | 29h | PIO data-in |
| Read Native Max Address Ext | 27h | Non-data |
| Read Verify Sector(s) Ext | 42h | Non-data |
| Set Max Address Ext | 37h | Non-data |
| Write DMA Ext | 35h | DMA |
| Write Multiple Ext | 39h | PIO data-out |
| Write Sector(s) Ext | 34h | PIO data-out |
| NCQ Feature Set | | |
| Read FPDMA Queued | 60h | DMA Queued |
| Write FPDMA Queued | 61h | DMA Queued |
| Other | | |
| Data Set Management | 06h | DMA |
| SEEK | 70h | Non-data |

8.2 SMART Data Structure

[Table 18] SMART Data Structure

| BYTE | F / V | Description |
|---------|-------|---|
| 0-1 | X | Revision code |
| 2-361 | X | Vendor specific |
| 362 | V | Off-line data collection status |
| 363 | X | Self-test execution status byte |
| 364-365 | V | Total time in seconds to complete off-line data collection activity |
| 366 | X | Vendor specific |
| 367 | F | Off-line data collection capability |
| 368-369 | F | SMART capability |
| 370 | F | Error logging capability |
| | | 7-1 Reserved |
| | | 0 1=Device error logging supported |
| 371 | X | Vendor specific |
| 372 | F | Short self-test routine recommended polling time (in minutes) |
| 373 | F | Extended self-test routine recommended polling time (in minutes) |
| 374 | F | Conveyance self-test routine recommended polling time (in minutes) |
| 375-385 | R | Reserved |
| 386-395 | F | Firmware Version/Date Code |
| 396-397 | F | Reserved |
| 398-399 | V | Reserved |
| 400-406 | V | TS6500 |
| 407-415 | X | Vendor specific |
| 416 | F | Reserved |
| 417 | F | Program/write the strong page only |
| 418-419 | V | Number of spare block |
| 420-423 | V | Average Erase Count |
| 424-510 | X | Vendor specific |
| 511 | V | Data structure checksum |

Note:

- 1) F = content (byte) is fixed and does not change.
- 2) V= content (byte) is variable and may change depending on the state of the device or the commands executed by the device.
- 3) X= content (byte) is vendor specific and may be fixed or variable.
- 4) R= content (byte) is reserved and shall be zero.

8.3 SMART Attributes

The following table shows the vendor specific data in byte 2 to 361 of 512-byte SMART data.

[Table 19] SMART Attributes

| Attribute ID (hex) | Raw Attribute Value | | | | | | | Attribute Name |
|--------------------|---------------------|-----|----|-----|----|----|-----|---|
| 01 | MSB | 00 | 00 | 00 | 00 | 00 | 00 | Read Error Rate |
| 05 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Reallocated sectors count |
| 09 | LSB | - | - | MSB | 00 | 00 | 00 | Power-on hours |
| 0C | LSB | - | - | MSB | 00 | 00 | 00 | Power Cycle Count |
| A0 | LSB | - | - | MSB | 00 | 00 | 00 | Uncorrectable sectors count when read/write |
| A1 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Number of valid spare blocks |
| A3 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Number of initial invalid blocks |
| A4 | LSB | - | - | MSB | 00 | 00 | 00 | Total erase count |
| A5 | LSB | - | - | MSB | 00 | 00 | 00 | Maximum erase count |
| A6 | LSB | - | - | MSB | 00 | 00 | 00 | Minimum erase count |
| A7 | LSB | - | - | MSB | 00 | 00 | 00 | Average erase count |
| A8 | LSB | - | - | MSB | 00 | 00 | 00 | Max erase count of spec |
| A9 | LSB | - | - | MSB | 00 | 00 | 00 | Remain Life (percentage) |
| AF | LSB | - | - | MSB | 00 | 00 | 00 | Program fail count in worst die |
| B0 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Erase fail count in worst die |
| B1 | LSB | - | - | MSB | 00 | 00 | 00 | Total wear level count |
| B2 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Runtime invalid block count |
| B5 | LSB | - | - | MSB | 00 | 00 | 00 | Total program fail count |
| B6 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Total erase fail count |
| C0 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Power-off retract Count |
| C2 | MSB | 00 | 00 | 00 | 00 | 00 | 00 | Controller temperature ¹⁾ |
| C3 | LSB | - | - | MSB | 00 | 00 | 00 | Hardware ECC recovered |
| C4 | LSB | - | - | MSB | 00 | 00 | 00 | Reallocation event count |
| C5 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Current Pending Sector Count |
| C6 | LSB | - | - | MSB | 00 | 00 | 00 | Uncorrectable error count off-line |
| C7 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Ultra DMA CRC Error Count |
| E8 | LSB | MSB | 00 | 00 | 00 | 00 | 00 | Available reserved space |
| F1 | LSB | - | - | - | - | - | MSB | Total LBA written (each write unit = 32MB) |
| F2 | LSB | - | - | - | - | - | MSB | Total LBA read (each read unit = 32MB) |
| F5 | LSB | - | - | - | - | - | MSB | Flash write sector count |

Note:

1) Controller temperature is only presented as a positive value.

9. Contact Information

TAIWAN

No.70, XingZhong Rd., NeiHu Dist., Taipei, Taiwan,
R.O.C
TEL +886-2-2792-8000
Fax +886-2-2793-2222
E-mail: sales-tw@transcend-info.com

Shanghai

E-mail: sales-cn@transcendchina.com
TEL: +86-21-6161-9388

Beijing

E-mail: sales-cn@transcendchina.com
TEL: +86-10-8265-9969

Shenzhen

E-mail: sales-cn@transcendchina.com
TEL: +86-755-2598-7200

Hong Kong

E-mail: sales-hk@transcend-info.com
TEL: +852-2331-8929

Los Angeles

E-mail: sales-us@transcend-info.com
TEL: +1-714-921-2000

Maryland

E-mail: sales-us@transcend-info.com
TEL: +1-410-689-4900

Silicon Valley

E-mail: sales-us@transcend-info.com
TEL: +1-408-785-5990

JAPAN

E-mail: sales-jp@transcend-info.com
TEL: +81-3-5820-6000

KOREA

E-mail: sales-kr@transcend-info.com
TEL: +82-2-782-8088

GERMANY

E-mail: sales-de@transcend-info.com
TEL: +49-40-538-907-0

NETHERLANDS

E-mail: sales-nl@transcend-info.com
TEL: +31-10-298-8500

United Kingdom

E-mail: sales-uk@transcend-info.com
TEL: +44-1442-202-880