

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Gigabit Ethernet extender, network extension with coaxial cable up to 1 kilometer and bandwidth up to 1 Gbps, Power over Link function (PoL) for the power supply of additional devices via the coaxial cable, Power over Ethernet function (PoE)

Your advantages

- Use of existing twisted pair cables or coaxial cables
- Flexible network configuration
- Easy startup, plug and play
- Network transparent (no IP configuration required)
- Protocol-transparent transmission of all standard Ethernet protocols

Commercial data

Item number	1319320
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN24
Product key	DNC361
GTIN	4063151604806
Weight per piece (including packing)	201.05 g
Weight per piece (excluding packing)	144 g
Customs tariff number	85176200
Country of origin	DE

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type	Ethernet extender
MTTF	293 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	134 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	55 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
Basic functions	Gigabit Ethernet extender in accordance with ITU G.9960

Insulation characteristics

Pollution degree	2
------------------	---

Functions

Basic functions	Gigabit Ethernet extender in accordance with ITU G.9960
Management	Plug and Play, diagnostics via LEDs, PoL switch on the device
Redundancy	Ring segment redundancy (All devices at a ring segment)

Security functions

Basic functions	Gigabit Ethernet extender in accordance with ITU G.9960
Encryption methods	AES path encryption, Advanced Encryption Standard

System properties

Functionality	
Basic functions	Gigabit Ethernet extender in accordance with ITU G.9960

Electrical properties

Electrical isolation	VCC (US+GND) // Ethernet (PoE) // G.hn (without PoL) // FE
Mains type	Permanent line
Test voltage data interface/power supply	1.5 kV AC (50 Hz, 1 min.)

Supply

Supply voltage range	18 V DC ... 57 V DC
Nominal supply voltage	24 V DC (Without PoL, without PoE)
	48 V DC (With PoL or with PoE)
Power consumption	≤ 7.5 W (Without PoL, without PoE)
	≤ 37.5 W (Without PoL, with PoE)
	≤ 37.5 W (With PoL, without PoE)
	≤ 82.5 W (With PoL, with PoE)

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Protective circuit	Overload protection, protection against polarity reversal; Internal device protection: 2x 5 AF, internal series diode
--------------------	---

Connection data

Supply

Connection method	Push-in spring connection
Conductor cross-section flexible, with ferrule without plastic sleeve	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.2 mm ² ... 2.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Single conductor/terminal point, rigid	0.2 mm ² ... 2.5 mm ² ≥ 0.5 mm ² (PoL cables in accordance with DIN VDE 0100, part 523)
Single-wire/terminal point, flexible	0.2 mm ² ... 2.5 mm ² ≥ 0.5 mm ² (PoL cables in accordance with DIN VDE 0100, part 523)
Conductor cross-section, flexible [AWG]	24 ... 16
Stripping length	10.00 mm

Interfaces

Signal	Ethernet
Basic functions	Gigabit Ethernet extender in accordance with ITU G.9960

Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

Serial transmission speed	10/100/1000 Mbps
Connection method	RJ45 jack, shielded
Note on the connection method	CAT6 Autonegotiation PoE port status: Always active Mode: Auto
No. of channels	1
Transmission length	< 100 m (shielded twisted pair)
Protocols supported	Protocol-transparent for TCP/IP, IPv4, and IPv6
Maximum output power	15 W (at ≤ 55°C) 30 W (at ≤ 50 °C)

Data: G.hn interface in accordance with ITU G.9960

Transmission speed	≤ 1000 Mbps (Depending on the quality of the data line)
Connection method	BNC female connector for coaxial cables, 75 Ω
Note on the connection method	Short-circuit-proof
Transmission length	≤ 1000 m (Depending on the quality of the data line)
Transmission method	QAM (quadrature amplitude modulation) carrier frequency method
Output power	≤ 91 W (With PoL)

Dimensions


EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Dimensional drawing



Width

23 mm

Height

101 mm

Depth

115 mm

Material specifications

Color (Housing)	gray (RAL 7042)
Material (Housing)	PA 6.6-FR
Flammability rating according to UL 94	V0

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	: 1g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	: 15g, 11 ms

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 60 °C (Free standing, without PoE)
	-40 °C ... 55 °C (Free standing, PoE up to 15 W)
	-40 °C ... 50 °C (Free standing, PoE up to 30 W)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Approvals

CE	
Certificate	CE-compliant
Corrosive gas test	
Identification	ISA-S71.04-1985 G3 Harsh Group A

EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 55035
Noise emission	
Standards/regulations	EN 61000-6-4, Class A, industrial area of application

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Contact discharge	± 6 kV
Discharge in air	± 8 kV
Indirect discharge	± 6 kV
Comments	Criterion B

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Frequency range	80 MHz ... 3 GHz (80% amplitude modulation with 1 kHz)
Field intensity	10 V/m
Frequency range	3 GHz ... 6 GHz (80% amplitude modulation with 1 kHz)
Field intensity	3 V/m
Comments	Criterion A

Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

Fast transients (burst)

Input	± 2.2 kV
Signal	± 2.2 kV (Ethernet, G.hn)

Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

Surge current load (surge)

Input	± 0.5 kV (Symmetrical, unshielded supply line)
Signal	± 1 kV (Asymmetrical, unshielded supply line)
	± 1 kV (Ethernet signal / asymmetrical: shielded Ethernet cable)
	± 4 kV (Ethernet signal / asymmetrical: cable to ground, unshielded G.hn cable)
	± 2 kV (Ethernet signal / symmetrical: cable to cable, unshielded G.hn cable)
	± 4 kV (Telecommunication lines, symmetrical, unshielded, with primary protection)
	± 1 kV (Telecommunication lines, symmetrical, unshielded, without primary protection)
Comments	Criterion B

Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

Conducted interference

Frequency range	0.15 MHz ... 80 MHz (80% amplitude modulation with 1 kHz)
Comments	Criterion A

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Voltage	10 V
---------	------

Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

Mounting

Mounting type	DIN rail mounting
Assembly note	To allow for air circulation, mount the device freestanding, with a clearance of at least one centimeter on all sides to other devices.
Mounting position	Vertical (horizontal DIN rail)

EXTENDER 2010 ETH COAX-G - Ethernet extender


1319320

<https://www.phoenixcontact.com/us/products/1319320>




Drawings

Dimensional drawing



Application drawing



PoE supply of a PoE end device


EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>




Application drawing




Separate supply with one power supply unit each

Application drawing




PoL supply of the remote extender

Application drawing



PoL supply of the remote extender and PoE supply of a PoE end device

Application drawing



PoL supply of the local extender


EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Application drawing



PoL supply of the local extender and PoE supply of a PoE end device


EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Schematic diagram



Front view


EXTENDER 2010 ETH COAX-G - Ethernet extender



1319320

<https://www.phoenixcontact.com/us/products/1319320>

Schematic diagram



Connection terminal blocks

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Classifications

ECLASS

ECLASS-13.0	19170407
ECLASS-15.0	19170407

ETIM

ETIM 9.0	EC000309
----------	----------

UNSPSC

UNSPSC 21.0	43223100
-------------	----------

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



Accessories

C-UB/E - Surge protection device

2763701

<https://www.phoenixcontact.com/us/products/2763701>

Attachment plug with surge protection, for coaxial signal interfaces with floating shield. Connection: BNC socket/plug



FL CAT5 PATCH 0,5 - Patch cable

2832263

<https://www.phoenixcontact.com/us/products/2832263>

Patch cable, CAT5, assembled, 0.5 m



EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>

Patch cable, CAT5, assembled, 1 m



FL CAT5 PATCH 2,0 - Patch cable

2832289

<https://www.phoenixcontact.com/us/products/2832289>

Patch cable, CAT5, assembled, 2 m



EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



FL CAT5 PATCH 3,0 - Patch cable

2832292

<https://www.phoenixcontact.com/us/products/2832292>

Patch cable, CAT5, assembled, 3 m



FL CAT5 PATCH 5,0 - Patch cable

2832580

<https://www.phoenixcontact.com/us/products/2832580>

Patch cable, CAT5, assembled, 5 m



EXTENDER 2010 ETH COAX-G - Ethernet extender



1319320


<https://www.phoenixcontact.com/us/products/1319320>

NBC-R4AC-R4AC-IE8A/.../... - Patch cable

1411854

<https://www.phoenixcontact.com/us/products/1411854>

Patch cable, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, cable outlet: straight, Ethernet



NBC-R4AC/10G-R4AC/10G-94F/2,0 - Patch cable

1408360

<https://www.phoenixcontact.com/us/products/1408360>

Patch cable, CAT6_A, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 2.0 m



EXTENDER 2010 ETH COAX-G - Ethernet extender



1319320


<https://www.phoenixcontact.com/us/products/1319320>

NBC-R4AC/10G-R4AC/10G-94F/3,0 - Patch cable

1408365

<https://www.phoenixcontact.com/us/products/1408365>

Patch cable, CAT6_A, 4-pair, shielded, connection not crossed (line), assembled at both ends with RJ45/IP20 connectors, outer sheath material: PUR, length: 3.0 m



FL CAT5 HEAVY CONF/ - Network cable

2744827

<https://www.phoenixcontact.com/us/products/2744827>

CAT5-SF/UTP cable (J-02YS(ST)C HP 2 x 2 x 24 AWG), heavy-duty installation cable, 2 x 2 x 0.22 mm², solid conductor, shielded, outer sheath: 7.8 mm diameter, inner sheath: 5.75 mm ± 0.15 mm diameter, preassembled on both sides with RJ45 plug, crossover or line



EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



VS-08-RJ45-5-Q/IP20 - RJ45 connector

1656725

<https://www.phoenixcontact.com/us/products/1656725>

RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Plastic, connection method: Insulation displacement connection, connection cross section: AWG 26- 23, cable outlet: straight, color: traffic grey A RAL 7042, Ethernet



FL CRIMPTOOL - Assembly tool

2744869

<https://www.phoenixcontact.com/us/products/2744869>

Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site



EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



FBS 2-5 GY - Plug-in bridge

3038969

<https://www.phoenixcontact.com/us/products/3038969>

Plug-in bridge, pitch: 5.2 mm, number of positions: 2, color: gray



ME-SAS - Shield connection clamp

2853899

<https://www.phoenixcontact.com/us/products/2853899>

Shield connection clamp for terminal points starting from 2.5 mm²



EXTENDER 2010 ETH COAX-G - Ethernet extender



1319320

<https://www.phoenixcontact.com/us/products/1319320>

ME-SAS MINI - Shield connection clamp

2200456

<https://www.phoenixcontact.com/us/products/2200456>

Shield connection clamp for terminal points starting from 1.5 mm²



FL DIN RA - DIN rail adapter

2891053

<https://www.phoenixcontact.com/us/products/2891053>

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.



EXTENDER 2010 ETH COAX-G - Ethernet extender

1319320

<https://www.phoenixcontact.com/us/products/1319320>



ME-MAX-NEF/QUINT20A - EMC filter

2319919

<https://www.phoenixcontact.com/us/products/2319919>

Filter for adherence to the EMC category EMC1 in shipbuilding for the QUINT-PS/1AC/24DC/20 power supply



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com