

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect professional, CCS type 2, HPC DC charging cable, up to 700 A in Boost mode, 500 A permanent, 1000 V DC, with cooled vehicle charging connector and cooled cable, cable: 3 m, black, straight, with replaceable mating face frame, with replaceable DC power contacts, with straight panel feed-through, with variable-speed fan, PHOENIX CONTACT logo, IEC 62196-3-1, for charging electric vehicles (EV) with direct current (DC)

Product description

DC charging cable with vehicle charging connector and free cable end for fast charging of electric vehicles (EV) with direct current (DC) via CCS type 2 vehicle charging inlets, for installation at charging stations for e-mobility (EVSE)

Your advantages

- Complete product range
- The right charging cable for every application, from the carport to the charging park
- Ultra-fast HPC charging, with temporary power up to 500 kW
- Convenient handling due to the ergonomic design
- Available with your logo on request - for consistent branding of your charging station
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Additional safety thanks to integrated leakage sensors and a wear indicator in the cable sheath
- Convenient communication interfaces via CAN bus and digital output
- Maintenance-friendly replacement of the mating face frame without draining the coolant
- Integrated strain relief of single-core wires directly in the panel feed-through
- Pre-assembled busbar screw connection for straightforward connection of the customer's busbars or cable lug solutions

Commercial data

Item number	1369277
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBLNI
GTIN	4063151723583
Weight per piece (including packing)	23 g
Weight per piece (excluding packing)	12,075 g
Customs tariff number	85444290
Country of origin	DE

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Technical data

Product properties

Product type	DC charging cable
Product family	CHARX connect professional
Technology	Combined Charging System
Application	High Power Charging
	for charging electric vehicles (EV) with direct current (DC)
	for installation at charging stations for electromobility (EVSE)
Design	with replaceable mating face frame
	with replaceable DC power contacts
	with straight panel feed-through
	with variable-speed fan
Charging standard	CCS type 2
Charging mode	Mode 4
Affixed logo	PHOENIX CONTACT logo
Label	8.9 mm x 28.9 mm (customer logo on request)

Electrical properties

Type of signal transmission	Pulse width modulation with modulated Powerline communication in accordance with ISO/IEC 15118 / DIN SPEC 70121
Note on the connection method	Single-core wires for four-wire measurement are not connected
Coding	1500 Ω (between PE and PP)

Charging power and current (DC charging)

Type of charging current	DC
Charging current	500 A DC
Charging power	500 kW
Rated voltage	1000 V

Charging power and current (DC charging in Boost Mode)

Type of charging current	DC Boost Mode
Charging current	up to 700 A DC
Charging power	up to 700 kW
Rated voltage	1000 V
Note	The specifications refer to charging in Boost Mode and are dependent on ambient conditions. For further details, see the packing slip in the download area.

Pin assignment (Leistungskontakte)

Number	3 (PE, DC+, DC-)
Rated voltage	1000 V DC
Rated current	500 A (up to 40 °C)

Pin assignment (Signalkontakte)

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A

Temperature sensors (NTC)

Sensor type	NTC
Attachment point	2 sensors for the replaceable front DC contacts 2 sensors for the internal DC power wires 1 sensor on the PCB in the housing
Switch-off temperature	90 °C

Temperature sensors (Pt 1000)


Sensor type	Pt 1000
Standards/regulations	DIN EN 60751
Attachment point	Sensor in the panel feed-through
Switch-off temperature	90 °C ±1 K (equivalent to a Pt 1000 value of 1346.5 Ω)
Long-term stability	0.06 % (after 1000 hours at 130 °C)
Recommended measured current	1 mA (1 V at 0°C)
Coefficient	3850 ppm/K
Ambient temperature	-50 °C ... 130 °C (Operation)

Ventilation (Fan)

Cooling	The fan provides additional cooling inside the panel feed-through to increase the charging current. The fan can be attached to the panel feed-through as an option.
Cable structure	2x AWG 26
Nominal voltage U_N	24 V
Nominal voltage range	18 V AC ... 24 V AC
Fan speed indication	4400 min-1
Fan volumetric flow	28 m³/h
Mechanical service life	70.000 h (at 40 °C)
Ambient temperature	-20 °C ... 40 °C

Dimensions

Vehicle charging connector

Dimensional drawing	
Width	72 mm

Make sure that the vehicle charging connector is placed in an appropriate charging connector holder, which ensures a minimum protection rating of IP24 in accordance with IEC 61851-1, for the entire time between charging. To create this charging connector holder, use the dimensions of the vehicle charging connector. Detailed dimensions can also be found in the Download area.

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable




1369277

<https://www.phoenixcontact.com/us/products/1369277>

Height	181.1 mm
Depth	285.3 mm

Panel feed-through


Dimensional drawing



Width	80 mm
Height	82 mm
Depth	227.69 mm

Cooling fan


Dimensional drawing



Width	81 mm
Height	133 mm
Depth	115 mm

Bore dimensions

Dimensional drawing



Drill hole spacing

Width	55 mm
Height	55 mm
Diameter	60 mm

Material specifications

Color (Housing)	black (9005)
Color (Handle area)	black (9005)
Color (Mating face)	black (9005)
Color (Cable)	black (9005)
Color (Panel feed-through)	black (9005)

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Material (Vehicle charging connector)	Plastic
Material (Cable outer sheath)	EVM-1 in accordance with EN 50620
Material (Panel feed-through)	Plastic
Material (Contact surface)	Silver
Flammability rating according to UL 94	V0 (Mating face)

Cable/line

Cable length	3 m ±45 mm
Wiring standards/regulations	according to UL 62 (File E515623, Vol 1)
	according to IEC 62893
Cable weight	max. 1938.00 kg/km
Cable type	straight
Cable structure	5 x 25 mm ² + 7 x 0.75 mm ²
External cable diameter	35.70 mm ±0.4 mm
Outer sheath, material	TPE-U in accordance with IEC 62893-1
Cable resistance	≤ 0.00078 Ω/m (based on a power core, at an ambient temperature of 20°C)
Bending radius	min. 357 mm (10x Ø)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 10000 (based on IEC 62196-1)
Insertion force	< 100 N
Withdrawal force	< 100 N

Environmental and real-life conditions

Ambient conditions

Degree of protection (Vehicle charging connector)	IP54 (plugged in; when plugged in and ready to operate, the degree of protection is only ensured if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
Degree of protection (Panel feed-through)	IP54
Ambient temperature (operation)	-30 °C ... 40 °C
	max. 55 °C (Current reduction required, observe the DC contact temperature limit value of 90°C)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	5000 m (above sea level)

Standards and regulations

Standards	
Standards/regulations	IEC 62196-3-1

Mounting

Mounting type Panel feed-through	Rear panel mounting
----------------------------------	---------------------

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Mounting type	Fans	Rear panel mounting (optional for increasing the charging current up to 500 A)
Fixing screws		M5x16


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Drawings



Make sure that the vehicle charging connector is placed in an appropriate charging connector holder, which ensures a minimum protection rating of IP24 in accordance with IEC 61851-1, for the entire time between charging. To create this charging connector holder, use the dimensions of the vehicle charging connector. Detailed dimensions can also be found in the Download area.


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging
cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Dimensional drawing



Drill hole spacing


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277


<https://www.phoenixcontact.com/us/products/1369277>

Dimensional drawing



Straight panel feed-through

Dimensional drawing



Fan for horizontal attachment to the panel feed-through


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Dimensional drawing



Fan for vertical attachment to the panel feed-through


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277


<https://www.phoenixcontact.com/us/products/1369277>

Schematic diagram



Pin assignment of the Vehicle Connector

Schematic diagram



Assembly instructions for attaching the touch protection using straight panel feed-through as an example



EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Schematic diagram



Select one option for mounting the fan. Illustrated using straight panel feed-through as an example.


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Schematic diagram





The resting position must be installed in the charging station such that the user cannot hang up the vehicle connector upside down (90° to 270°). However, positions rotated upward (45°) or downward (315°) are options for a resting position.

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>



Standalone, decentralized system: cooling unit and controller are integrated into the charging station. The choice of cooling unit can be passive or active (i.e., with or without chiller).


EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277


<https://www.phoenixcontact.com/us/products/1369277>

Schematic diagram



The Combined Charging System (CCS) principle - standard-compliant charging system for electric vehicles, which supports both conventional AC charging and fast DC charging. Both Vehicle Connectors fit into the CCS Vehicle Inlet.

Schematic diagram




EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Schematic diagram



Warning signal note

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Classifications

ECLASS

ECLASS-13.0	27144705
-------------	----------

ETIM

ETIM 9.0	EC002897
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

EV-T2HPCC-DC500A-3,0M50ECBK11S - DC charging cable



1369277

<https://www.phoenixcontact.com/us/products/1369277>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	6f15513b-91d3-416e-92a6-d887c86ad7fd

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com