

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect, Type 2, Infrastructure charging socket, 32 A, 480 V AC, Single wires, length: 0.7 m, locking actuator: 24 V, 4-pos., Rear panel mounting, for charging electric vehicles (EV) with alternating current (AC), PHOENIX CONTACT logo, IEC 62196-2

Product description

Infrastructure charging socket for charging electric vehicles (EV) with alternating current (AC), compatible with type 2 Infrastructure Plugs, for installation at charging stations for E-Mobility (EVSE)

Your advantages

- Complete product range
- Uniform, space-saving installation space
- Available with your logo on request - for consistent branding of your charging station
- Integrated interlock during charging
- Manual emergency release of the locking actuator
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001

Commercial data

Item number	1405216
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	EM01
Product key	XWBADC
GTIN	4046356738491
Weight per piece (including packing)	656.4 g
Weight per piece (excluding packing)	0.56 g
Customs tariff number	85444290
Country of origin	DE

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Technical data

Product properties

Product type	Infrastructure charging socket
Product family	CHARX connect
Application	for charging electric vehicles (EV) with alternating current (AC) compatible with infrastructure charging plugs
Charging standard	Type 2
Charging mode	Mode 3, Case B
Affixed logo	PHOENIX CONTACT logo
Customer variations	On request

Electrical properties

Type of signal transmission	Pulse width modulation
Note on the connection method	Crimp connection, cannot be disconnected

Charging power and current (AC charging (3-phase))

Type of charging current	AC 3-phase
Charging current	32 A AC (3-phase)
Charging power	26.6 kW (3-phase)
Charging power rating	22 kW (32 A, 3-phase)
Rated voltage	480 V

Pin assignment (Leistungskontakte)

Number	5 (L1, L2, L3, N, PE)
Rated voltage	480 V AC
Rated current	32 A

Pin assignment (Signalkontakte)

Number	2 (CP, PP)
Rated voltage	30 V AC
Rated current	2 A

Locking actuator

Locking actuator	24 V, 4-pos.
	Top center position
Possible power supply range at the motor	22 V ... 26 V
Maximum voltage for locking detection	30 V
Typical motor current for locking	0.05 A
Reverse current of the motor	max. 0.5 A
Max. dwell time with reverse current	1 s
Recommended adaptation time	600 ms
Pause time after entry or exit path	3 s
Service life insertion cycles	> 10000 load cycles

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Lock recognition	available
Mechanical emergency release	available
Ambient temperature (operation)	-30 °C ... 50 °C
Cable length	0.5 m
Cable structure	4 x 0.5 mm ²
Bending radius	min. 15 mm
External cable diameter	1.60 mm ±0.02 mm
Cable weight	7.00 kg/km
Cable resistance	≤ 37.1 Ω/m
Single wire, color	BU/RD, BU/GN, BU/YE, BU/BN

Dimensions

Dimensional drawing	
Max. wall thickness	max. 50.00 mm (Rear panel mounting, normative maximum specification for infrastructure plug)
	max. 28.00 mm (Rear mounting, normative maximum specification for infrastructure plug when using protective cover 1405217)
Bore dimensions	max. 10.00 mm (Front mounting, when using the locking mechanism)

Cable/line

Cable length	0.7 m (AC cables)
	0.5 m (Locking actuator cables)
Cable type	Single wires
Cable structure	5x 6.0 mm ² + 2x 0.5 mm ²

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-30 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Altitude

5000 m (above sea level)

Standards and regulations

Standards

Standards/regulations

IEC 62196-2

Mounting

Mounting type Infrastructure charging socket	Rear panel mounting (0 to 90 degree frontal inclination possible) Front mounting (only possible when the locking actuator is removed (see EV-T2M3SE...E00 versions))
Mounting type Protective cover	rear (available separately)
Mounting hole diameter	7.00 mm (ø)

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket




1405216

<https://www.phoenixcontact.com/us/products/1405216>

Drawings

Dimensional drawing



Hole image


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Dimensional drawing



Dimensional drawing


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Connection diagram



Pin assignment of infrastructure charging socket


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Schematic diagram



Rear mounting with rear protective cover screw connection

The screw connection for a protective cover from the accessories range (EV-T2SC) only supports rear mounting. The panel thickness must not exceed 5 mm. The sealing frame that is slid on from the rear must contact the housing panel flush with the flat side and must completely surround the infrastructure socket outlet.


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Schematic diagram



Front mounting with rear protective cover screw connection

Front mounting is only possible when the locking actuator is removed. We recommend using an infrastructure socket outlet without pre-assembled locking actuator (EV-T2M3SE-...E0..., e.g., 1621729).

The screw connection for a protective cover from the accessories range (EV-T2SC) only supports rear mounting. The panel thickness must not exceed 10 mm. The sealing frame that is slid on from the front must contact the housing panel flush with the flat side and must completely surround the infrastructure socket outlet.


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Schematic diagram



Operating instructions


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216


<https://www.phoenixcontact.com/us/products/1405216>

Schematic diagram



Detection of the Infrastructure Plug

Schematic diagram



Installation positions


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Schematic diagram



Panel thickness for rear mounting (max. 50 mm, with Phoenix Contact protective cover, max. 22 mm)


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Schematic diagram



Panel thickness for front mounting (in mm)



EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Diagram



Locking states of the locking actuator


EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Block diagram



Block diagram of the locking actuator

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Classifications

UNSPSC

UNSPSC 21.0

39121522

EV-T2M3SE24-3AC32A-0,7M6,0E10 - Infrastructure charging socket



1405216

<https://www.phoenixcontact.com/us/products/1405216>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-10 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+171) 944-1300
info@phoenixcon.com