

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply

2904598

<https://www.phoenixcontact.com/us/products/2904598>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Primary-switched power supply unit QUINT POWER, Screw connection, DIN rail mounting, input: 1-phase, output: 24 V DC / 2.5 A. Alternative item: 2909576

## Product description

In the power range of up to 100 W, QUINT POWER provides superior system availability in the smallest size. Preventative function monitoring and exceptional power reserves are available for applications in the low-power range.

## Your advantages

- Starting of heavy loads with dynamic boost
- Preventive function monitoring indicates critical operating states before errors occur
- High efficiency and long service life, with low power dissipation and low heating
- Space savings in the control cabinet, thanks to a narrow, slim-line design
- Free selection between Push-in and screw connection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2904598       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CM10          |
| Product key                          | CMPI13        |
| GTIN                                 | 4055626156040 |
| Weight per piece (including packing) | 335 g         |
| Weight per piece (excluding packing) | 335 g         |
| Customs tariff number                | 85044095      |
| Country of origin                    | VN            |

## Technical data

### Input data

#### AC operation

|                                          |                                                  |
|------------------------------------------|--------------------------------------------------|
| Input voltage range                      | 100 V AC ... 240 V AC -15 % ... +10 %            |
| Electric strength, max.                  | 300 V AC 30 s                                    |
| Typical national grid voltage            | 120 V AC                                         |
|                                          | 230 V AC                                         |
| Voltage type of supply voltage           | AC                                               |
| Inrush current                           | typ. 10 A (at 25 °C)                             |
| Inrush current integral ( $I^2t$ )       | < 0.1 A <sup>2</sup> s                           |
| Inrush current limitation                | 4.3 A (after 1 ms)                               |
|                                          | < 10 A                                           |
| Frequency range ( $f_N$ )                | 50 Hz ... 60 Hz -10 % ... +10 %                  |
|                                          | 16.7 Hz (acc. to EN 50163)                       |
| Mains buffering time                     | typ. 54 ms (120 V AC)                            |
|                                          | typ. 54 ms (230 V AC)                            |
| Current consumption                      | 0.85 A (100 V AC)                                |
|                                          | 0.7 A (120 V AC)                                 |
|                                          | 0.39 A (230 V AC)                                |
|                                          | 0.37 A (240 V AC)                                |
| Nominal power consumption                | 71 VA                                            |
| Protective circuit                       | Transient surge protection; Varistor             |
| Typical response time                    | 500 ms                                           |
| Input fuse                               | 3.15 A (slow-blow, internal)                     |
| Recommended breaker for input protection | 6 A ... 16 A (Characteristic B, C or comparable) |
| Discharge current to PE                  | < 0.25 mA (264 V AC, 60 Hz)                      |
|                                          | 0.22 mA (264 V AC, 60 Hz)                        |

#### DC operation

|                                |                                       |
|--------------------------------|---------------------------------------|
| Input voltage range            | 110 V DC ... 250 V DC -20 % ... +40 % |
| Voltage type of supply voltage | DC                                    |
| Current consumption            | 0.75 A (110 V DC)                     |
|                                | 0.33 A (250 V DC)                     |

### Output data

|                                                   |                                         |
|---------------------------------------------------|-----------------------------------------|
| Efficiency                                        | typ. 91.9 % (120 V AC)                  |
|                                                   | typ. 92.6 % (230 V AC)                  |
| Output characteristic                             | U/I Advanced                            |
| Nominal output voltage                            | 24 V DC                                 |
| Setting range of the output voltage ( $U_{Set}$ ) | 24 V DC ... 28 V DC (constant capacity) |
| Nominal output current ( $I_N$ )                  | 2.5 A                                   |
| Static Boost ( $I_{Stat.Boost}$ )                 | 3.125 A ( $\leq 40$ °C)                 |

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

|                                                    |                                                                                  |
|----------------------------------------------------|----------------------------------------------------------------------------------|
| Dynamic Boost ( $I_{\text{Dyn.Boost}}$ )           | 5 A ( $\leq 60^\circ\text{C}$ (5 s), Input $< 150\text{ V AC}$ Derating 0.5 %/V) |
| Derating                                           | $> 60^\circ\text{C}$ (2.5 %/K)                                                   |
| Feedback voltage resistance                        | $\leq 35\text{ V DC}$                                                            |
| Protection against overvoltage at the output (OVP) | $\leq 32\text{ V DC}$                                                            |
| Control deviation                                  | $< 0.5\%$ (Static load change 10 % ... 90 %)                                     |
|                                                    | $< 2\%$ (Dynamic load change 10 % ... 90 %, (10 Hz))                             |
|                                                    | $< 0.1\%$ (change in input voltage $\pm 10\%$ )                                  |
| Residual ripple                                    | $< 40\text{ mV}_{\text{PP}}$ (with nominal values)                               |
| Short-circuit-proof                                | yes                                                                              |
| No-load proof                                      | yes                                                                              |
| Output power                                       | 60 W                                                                             |
|                                                    | 75 W                                                                             |
|                                                    | 120 W                                                                            |
| Maximum no-load power dissipation                  | $< 1\text{ W}$ (230 V AC)                                                        |
|                                                    | $< 1\text{ W}$ (120 V AC)                                                        |
| Power loss nominal load max.                       | $< 5\text{ W}$ (230 V AC)                                                        |
|                                                    | $< 5\text{ W}$ (120 V AC)                                                        |
| Crest factor                                       | typ. 1.69 (120 V AC)                                                             |
|                                                    | typ. 1.82 (230 V AC)                                                             |
| Rise time                                          | 50 ms ( $U_{\text{Out}} = 10\% \dots 90\%$ )                                     |
| Connection in parallel                             | yes, for redundancy and increased capacity                                       |
| Connection in series                               | yes                                                                              |
| Signal (configurable)                              |                                                                                  |
| Digital                                            | 0 V DC 24 V DC 30 mA                                                             |
| Default                                            | 24 V DC 30 mA 24 V DC for $U_{\text{Out}} > 0.9 \times U_{\text{Set}}$           |

## Connection data

### Input

|                                                               |                      |
|---------------------------------------------------------------|----------------------|
| Connection method                                             | Screw connection     |
| Conductor cross-section, rigid min.                           | 0.14 mm <sup>2</sup> |
| Conductor cross-section, rigid max.                           | 2.5 mm <sup>2</sup>  |
| Conductor cross-section flexible min.                         | 0.14 mm <sup>2</sup> |
| Conductor cross-section flexible max.                         | 2.5 mm <sup>2</sup>  |
| Single conductor/terminal point, stranded, with ferrule, min. | 0.25 mm <sup>2</sup> |
| Single conductor/terminal point, stranded, with ferrule, max. | 2.5 mm <sup>2</sup>  |
| Conductor cross-section AWG min.                              | 26                   |
| Conductor cross-section AWG max.                              | 14                   |
| Stripping length                                              | 8 mm                 |
| Tightening torque, min                                        | 0.5 Nm               |
| Tightening torque max                                         | 0.6 Nm               |

### Output

|                   |                  |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

|                                                               |                      |
|---------------------------------------------------------------|----------------------|
| Conductor cross-section, rigid min.                           | 0.14 mm <sup>2</sup> |
| Conductor cross-section, rigid max.                           | 2.5 mm <sup>2</sup>  |
| Conductor cross-section flexible min.                         | 0.14 mm <sup>2</sup> |
| Conductor cross-section flexible max.                         | 2.5 mm <sup>2</sup>  |
| Single conductor/terminal point, stranded, with ferrule, min. | 0.25 mm <sup>2</sup> |
| Single conductor/terminal point, stranded, with ferrule, max. | 2.5 mm <sup>2</sup>  |
| Conductor cross-section AWG min.                              | 26                   |
| Conductor cross-section AWG max.                              | 14                   |
| Stripping length                                              | 8 mm                 |
| Tightening torque, min                                        | 0.5 Nm               |
| Tightening torque max                                         | 0.6 Nm               |

## Signal

|                                                               |                      |
|---------------------------------------------------------------|----------------------|
| Connection method                                             | Screw connection     |
| Conductor cross-section, rigid min.                           | 0.14 mm <sup>2</sup> |
| Conductor cross-section, rigid max.                           | 2.5 mm <sup>2</sup>  |
| Conductor cross-section flexible min.                         | 0.14 mm <sup>2</sup> |
| Conductor cross-section flexible max.                         | 2.5 mm <sup>2</sup>  |
| Single conductor/terminal point, stranded, with ferrule, min. | 0.25 mm <sup>2</sup> |
| Single conductor/terminal point, stranded, with ferrule, max. | 2.5 mm <sup>2</sup>  |
| Conductor cross-section AWG min.                              | 26                   |
| Conductor cross-section AWG max.                              | 14                   |
| Stripping length                                              | 8 mm                 |
| Tightening torque, min                                        | 0.5 Nm               |
| Tightening torque max                                         | 0.6 Nm               |

## Signaling

|                    |     |
|--------------------|-----|
| Types of signaling | LED |
|--------------------|-----|

## Signal output

|                  |                                                                                                                              |
|------------------|------------------------------------------------------------------------------------------------------------------------------|
| P <sub>Out</sub> | > P <sub>Thr</sub> (LED lights up yellow, output power > P <sub>Thr</sub> , depending on the rotary selector switch setting) |
| U <sub>Out</sub> | > 0.9 x U <sub>Set</sub> (LED lights up green)<br>< 0.9 x U <sub>Set</sub> (LED flashes green)                               |

## Electrical properties

|                                 |                                                                                                                                               |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Number of phases                | 1                                                                                                                                             |
| Insulation voltage input/output | 4 kV AC (type test)<br>3 kV AC (routine test)                                                                                                 |
| Switching frequency             | 4.00 kHz ... 70.00 kHz (Auxiliary converter stage)<br>30.00 kHz ... 150.00 kHz (PFC stage)<br>70.00 kHz ... 150.00 kHz (Main converter stage) |

## Product properties

|              |              |
|--------------|--------------|
| Product type | Power supply |
|--------------|--------------|

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

|                                    |                           |
|------------------------------------|---------------------------|
| Product family                     | QUINT POWER               |
| MTBF (IEC 61709, SN 29500)         | > 1347000 h (25 °C)       |
|                                    | > 734000 h (40 °C)        |
|                                    | > 295000 h (60 °C)        |
| Environmental protection directive | RoHS Directive 2011/65/EU |
|                                    | WEEE                      |
|                                    | Reach                     |

### Insulation characteristics

|                     |    |
|---------------------|----|
| Protection class    | II |
| Degree of pollution | 2  |

### Life expectancy (electrolytic capacitors)

|                 |          |
|-----------------|----------|
| Current         | 2.5 A    |
| Temperature     | 40 °C    |
| Time            | 148000 h |
| Additional text | 120 V AC |

### Life expectancy (electrolytic capacitors)

|                 |          |
|-----------------|----------|
| Current         | 2.5 A    |
| Temperature     | 40 °C    |
| Time            | 153000 h |
| Additional text | 230 V AC |


### Life expectancy (electrolytic capacitors)

|                 |          |
|-----------------|----------|
| Current         | 2.5 A    |
| Temperature     | 25 °C    |
| Time            | 419000 h |
| Additional text | 120 V AC |

### Life expectancy (electrolytic capacitors)

|                 |          |
|-----------------|----------|
| Current         | 2.5 A    |
| Temperature     | 25 °C    |
| Time            | 432000 h |
| Additional text | 230 V AC |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 32 mm                                                                                |

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

|        |       |
|--------|-------|
| Height | 99 mm |
| Depth  | 90 mm |

## Installation dimensions

|                                                    |                                       |
|----------------------------------------------------|---------------------------------------|
| Installation distance right/left (active)          | 15 mm / 15 mm ( $P_{Out} \geq 50\%$ ) |
| Installation distance right/left (passive)         | 5 mm / 5 mm ( $P_{Out} \geq 50\%$ )   |
| Installation distance top/bottom (active)          | 30 mm / 30 mm ( $P_{Out} \geq 50\%$ ) |
| Installation distance top/bottom (passive)         | 30 mm / 30 mm ( $P_{Out} \geq 50\%$ ) |
| Installation distance top/bottom (active, passive) | 30 mm / 30 mm ( $P_{Out} \leq 50\%$ ) |

## Mounting

|                         |                   |
|-------------------------|-------------------|
| Mounting type           | DIN rail mounting |
| Assembly note           | DIN rail mounting |
| With protective coating | no                |

## Material specifications

|                                                                    |               |
|--------------------------------------------------------------------|---------------|
| Flammability rating according to UL 94 (housing / terminal blocks) | V0            |
| Housing material                                                   | Plastic       |
| Type of housing                                                    | Polycarbonate |
| Hood version                                                       | Polycarbonate |

## Environmental and real-life conditions

### Ambient conditions

|                                                |                                                                                                |
|------------------------------------------------|------------------------------------------------------------------------------------------------|
| Degree of protection                           | IP20                                                                                           |
| Ambient temperature (operation)                | -25 °C ... 70 °C (> 60 °C Derating: 2,5 %/K)                                                   |
| Ambient temperature (storage/transport)        | -40 °C ... 85 °C                                                                               |
| Ambient temperature (start-up type tested)     | -40 °C                                                                                         |
| Maximum altitude                               | ≤ 5000 m (> 2000 m, observe derating)                                                          |
| Climatic class                                 | 3K3 (in acc. with EN 60721)                                                                    |
| Max. permissible relative humidity (operation) | ≤ 95 % (at 25 °C, non-condensing)                                                              |
| Shock                                          | 18 ms, 30g, in each space direction (according to IEC 60068-2-27)                              |
| Vibration (operation)                          | < 15 Hz, ±2.5 mm amplitude; 15 Hz ... 100 Hz: 2.3 g 90 Min. (in accordance with IEC 60068-2-6) |
| Temp code                                      | T4 (-25 ... +70 °C; > 60 °C, Derating: 2,5 %/K)                                                |

## Standards and regulations

|                                                  |               |
|--------------------------------------------------|---------------|
| Rail applications                                | EN 50121-3-2  |
|                                                  | EN 50121-4    |
|                                                  | EN 50121-5    |
|                                                  | IEC 62236-3-2 |
|                                                  | IEC 62236-4   |
|                                                  | IEC 62236-5   |
| Standard – Limitation of mains harmonic currents | EN 61000-3-2  |

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

|                                                                              |                        |
|------------------------------------------------------------------------------|------------------------|
| Standard - Electrical safety                                                 | IEC 61010-2-201 (SELV) |
| Standard – Safety extra-low voltage                                          | IEC 61010-1 (SELV)     |
|                                                                              | IEC 61010-2-201 (PELV) |
| Standard - Safe isolation                                                    | IEC 61558-2-16         |
|                                                                              | IEC 61010-2-201        |
| Standard - safety for equipment for measurement, control, and laboratory use | IEC 61010-1            |
| Standard - Safety of transformers                                            | EN 61558-2-16          |
| Standard - power supply devices for low voltage with DC output               | EN 61204-3             |

## Overvoltage category

|            |                      |
|------------|----------------------|
| EN 61010-1 | II ( $\leq 5000$ m)  |
| EN 62477-1 | III ( $\leq 2000$ m) |

## Approvals

|              |                                                                                                 |
|--------------|-------------------------------------------------------------------------------------------------|
| SIQ          | CB-Scheme (IEC 61010-1, IEC 61010-2-201)                                                        |
| UL approvals | UL Listed UL 61010-1                                                                            |
|              | UL Listed UL 61010-2-201                                                                        |
|              | UL 1310 Class 2 Power Units                                                                     |
|              | UL 121201 & CSA C22.2 No. 213-17 Class I, Division 2, Groups A, B, C, D T4 (Hazardous Location) |

## EMC data

|                                     |                                           |
|-------------------------------------|-------------------------------------------|
| Electromagnetic compatibility       | Conformance with EMC Directive 2014/30/EU |
| EMC requirements for noise emission | EN 61000-6-3                              |
|                                     | EN 61000-6-4                              |
| EMC requirements for noise immunity | EN 61000-6-1                              |
|                                     | EN 61000-6-2                              |
| EMC requirements for power supply   | IEC 61850-3 (G,H)                         |
|                                     | EN 61000-6-5 (switching devices)          |

## Conducted noise emission

|                       |                        |
|-----------------------|------------------------|
| Standards/regulations | EN 55016               |
|                       | EN 61000-6-3 (Class B) |

## Noise emission

|                       |                                                                                                       |
|-----------------------|-------------------------------------------------------------------------------------------------------|
| Standards/regulations | Additional basic standard EN 61000-6-5 (immunity in switching devices), IEC/EN 61850-3 (power supply) |
|-----------------------|-------------------------------------------------------------------------------------------------------|

## Noise emission

|                       |                        |
|-----------------------|------------------------|
| Standards/regulations | EN 55016               |
|                       | EN 61000-6-3 (Class B) |

## Harmonic currents

|                 |                 |
|-----------------|-----------------|
| Frequency range | 0 kHz ... 2 kHz |
|-----------------|-----------------|

## Flicker

|                 |                 |
|-----------------|-----------------|
| Frequency range | 0 kHz ... 2 kHz |
|-----------------|-----------------|

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

## Electrostatic discharge

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

## Electrostatic discharge

|                   |                     |
|-------------------|---------------------|
| Contact discharge | 8 kV (Test Level 4) |
| Discharge in air  | 8 kV (Test Level 3) |
| Comments          | Criterion A         |

## Electromagnetic HF field

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

## Electromagnetic HF field

|                     |                       |
|---------------------|-----------------------|
| Frequency range     | 80 MHz ... 1 GHz      |
| Test field strength | 20 V/m                |
| Frequency range     | 1 GHz ... 6 GHz       |
| Test field strength | 10 V/m (Test Level 3) |
| Comments            | Criterion A           |

## Fast transients (burst)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

## Fast transients (burst)

|          |                                    |
|----------|------------------------------------|
| Input    | 4 kV (Test Level 4 - asymmetrical) |
| Output   | 4 kV (Test Level 4 - asymmetrical) |
| Signal   | 4 kV (Test Level 4 - asymmetrical) |
| Comments | Criterion B                        |

## Surge voltage load (surge)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

## Surge voltage load (surge)

|          |                                    |
|----------|------------------------------------|
| Input    | 2 kV (Test Level 4 - symmetrical)  |
|          | 4 kV (Test Level 4 - asymmetrical) |
| Output   | 1 kV (Test Level 3 - symmetrical)  |
|          | 2 kV (Test Level 3 - asymmetrical) |
| Signal   | 2 kV (Test Level 4 - symmetrical)  |
|          | 4 kV (Test Level 4 - asymmetrical) |
| Comments | Criterion A                        |

## Conducted interference

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

## Conducted interference

|                     |                     |
|---------------------|---------------------|
| Input/output/signal | asymmetrical        |
| Frequency range     | 0.15 MHz ... 80 MHz |
| Comments            | Criterion A         |
| Voltage             | 10 V (Test Level 3) |

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

## Power frequency magnetic field

|                       |                 |
|-----------------------|-----------------|
| Standards/regulations | EN 61000-4-8    |
| Frequency             | 16.67 Hz        |
|                       | 50 Hz           |
|                       | 60 Hz           |
| Test field strength   | 100 A/m         |
| Additional text       | 60 s            |
| Comments              | Criterion A     |
| Frequency             | 50 Hz           |
|                       | 60 Hz           |
| Frequency range       | 50 Hz ... 60 Hz |
| Test field strength   | 1 kA/m          |
| Additional text       | 3 s             |
| Frequency             | 0 Hz            |
| Test field strength   | 300 A/m         |
| Additional text       | DC, 60 s        |

## Voltage dips

|                       |                          |
|-----------------------|--------------------------|
| Standards/regulations | EN 61000-4-11            |
| Voltage               | 100 V AC                 |
| Frequency             | 60 Hz                    |
| Voltage dip           | 70 %                     |
| Number of periods     | 0.5 / 1 / 25 periods     |
| Additional text       | Test Level 2             |
| Comments              | Criterion B              |
| Voltage dip           | 40 %                     |
| Number of periods     | 5 / 10 / 50 periods      |
| Additional text       | Test Level 2             |
| Comments              | Criterion B              |
| Voltage dip           | 0 %                      |
| Number of periods     | 0.5 / 1 / 5 / 50 periods |
| Additional text       | Test Level 2             |
| Comments              | Criterion B              |

## Pulse-shape magnetic field

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-9 |
| Test field strength   | 1000 A/m     |
| Comments              | Criterion A  |

## Attenuated sinusoidal oscillations (ring wave)

|                       |                     |
|-----------------------|---------------------|
| Standards/regulations | EN 61000-4-12       |
| Input                 | 2 kV (symmetrical)  |
|                       | 4 kV (asymmetrical) |
| Comments              | Criterion B         |

## Asymmetrical conducted disturbance variables

|                       |                                     |
|-----------------------|-------------------------------------|
| Standards/regulations | EN 61000-4-16                       |
| Test level 1          | 16.67 Hz 50 Hz 60 Hz (Test Level 3) |
| Voltage               | 30 V (Permanent)                    |
| Test level 2          | 16.67 Hz 50 Hz 60 Hz (Test Level 4) |
| Voltage               | 300 V (1 s)                         |
| Comments              | Criterion A                         |

## Attenuated oscillating wave

|                       |                                             |
|-----------------------|---------------------------------------------|
| Standards/regulations | EN 61000-4-18                               |
| Input/Output/Signal   | 1 kV (symmetrical)<br>2.5 kV (asymmetrical) |
| Comments              | Criterion B                                 |

## Criteria

|             |                                                                                                                                                            |
|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Criterion A | Normal operating behavior within the specified limits.                                                                                                     |
| Criterion B | Temporary impairment to operational behavior that is corrected by the device itself.                                                                       |
| Criterion C | Temporary adverse effects on the operating behavior, which the device corrects automatically or which can be restored by actuating the operating elements. |


# QUINT4-PS/1AC/24DC/2.5/SC - Power supply

2904598

<https://www.phoenixcontact.com/us/products/2904598>




## Drawings




Schematic diagram


## Housing




Diagram




Diagram



Diagram



Block diagram



# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904598>



**IECEE CB Scheme**

Approval ID: SI-8860



**EAC**

Approval ID: RU S-DE.BL08.W.00764



**UL Listed**

Approval ID: E123528



**cUL Listed**

Approval ID: E123528



**EAC**

Approval ID: RU S-DE.BL08.W.00764

**DNV**

Approval ID: TAA00000BV



**BV**

Approval ID: 44621/B0 BV



**cUL Listed**

Approval ID: E199827



**UL Listed**

Approval ID: E199827

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply

2904598

<https://www.phoenixcontact.com/us/products/2904598>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27040701 |
| ECLASS-15.0 | 27040701 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002540 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

# QUINT4-PS/1AC/24DC/2.5/SC - Power supply



2904598

<https://www.phoenixcontact.com/us/products/2904598>

## Environmental product compliance

### EU RoHS

|                                         |              |
|-----------------------------------------|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 6(c), 7(c)-I |

### China RoHS

|                                        |                                                                                                                                                                                                                                   |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-25                                                                                                                                                                                                                           |
|                                        | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 93541367-712a-43ff-943d-708f0e440eff |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)