

OSRAM GW KAFHB9.KM

Datasheet


Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

am  **OSRAM**

SOLERIQ™ S 9

GW KAFHB9.KM

The SOLERIQ™ S products were specifically designed for applications requiring large flux packages out of a compact area.



Applications

- Indoor Lighting

Features

- Package: Chip-on-Board
- Typ. Radiation: 120° (Lambertian emitter)
- Color temperature: 2700K - 6500K
- CRI: 90 (min.)
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- Luminous Flux: typ. 1560 lm @ 3000 K, 85 °C
- Luminous efficacy: typ. 169 lm/W @ 3000 K, 85 °C

Ordering Information

Type	Color temperature	Luminous Flux ¹⁾ $I_F = 270 \text{ mA}$ Φ_V	Ordering Code
GW KAFHB9.KM-C14-27S3	2700 K	1325 ... 1575 lm	Q65115A1917
GW KAFHB9.KM-C15-30S3	3000 K	1395 ... 1655 lm	Q65115A1916
GW KAFHB9.KM-C19-35S3	3500 K	1420 ... 1685 lm	Q65115A1897
GW KAFHB9.KM-C16-40S3	4000 K	1440 ... 1705 lm	Q65115A1883
GW KAFHB9.KM-C17-50S3	5000 K	1445 ... 1715 lm	Q65115A1882
GW KAFHB9.KM-C23-57S3	5700 K	1495 ... 1770 lm	Q65115A1881
GW KAFHB9.KM-C25-65S3	6500 K	1490 ... 1765 lm	Q65115A1880

Maximum Ratings

Parameter	Symbol	Values	
Operating Temperature	T_{op}	min.	-40 °C
		max.	105 °C
Storage Temperature	T_{stg}	min.	-40 °C
		max.	105 °C
Junction Temperature	T_j	max.	125 °C
Forward Current $T_j = 85 \text{ }^\circ\text{C}$	I_F	min.	30 mA
		max.	600 mA
Reverse voltage ²⁾	V_R	Not designed for reverse operation	
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}	2 kV	

Characteristics


$I_F = 270 \text{ mA}$; $T_J = 85 \text{ }^\circ\text{C}$

Parameter	Symbol	Values	
Viewing angle at 50% I_V	2ϕ	typ.	120 °
Forward Voltage ³⁾ $I_F = 270 \text{ mA}$	V_F	min. typ. max.	30.00 V 34.00 V 38.00 V
Reverse current ²⁾	I_R	Not designed for reverse operation	
Color Rendering Index ⁴⁾	CRI	min.	90
Electrical thermal resistance junction/solderpoint with efficiency $\eta_e = 51.4 \text{ \%}$	$R_{\text{thJS elec.}}$	typ.	0.39 K / W

Brightness Groups

Group	Luminous Flux ¹⁾ $I_F = 270 \text{ mA}$ min. Φ_v	Luminous Flux ¹⁾ $I_F = 270 \text{ mA}$ max. Φ_v
C14	1325 lm	1575 lm
C15	1395 lm	1655 lm
C19	1420 lm	1685 lm
C16	1440 lm	1705 lm
C17	1445 lm	1715 lm
C25	1490 lm	1765 lm
C23	1495 lm	1770 lm

Chromaticity Coordinate Groups ⁵⁾




Chromaticity Coordinate Groups

CCT	Center Cx	Center Cy	a	b	\emptyset
2700 K	0.4577	0.4098	0.008	0.0041	54.1
3000 K	0.4339	0.4032	0.0086	0.0042	53.7
3500 K	0.4077	0.3929	0.0093	0.0042	53.9
4000 K	0.3818	0.3796	0.0094	0.0041	53.4
5000 K	0.3446	0.3551	0.0081	0.0035	59.8
5700 K	0.3287	0.3425	0.0072	0.0032	58.8
6500 K	0.3123	0.3282	0.0066	0.0027	58.1


Relative Spectral Emission

$\Phi_{\text{rel}} = f(\lambda)$; $I_F = 270 \text{ mA}$; $T_J = 85 \text{ }^\circ\text{C}$




Radiation Characteristics

$I_{\text{rel}} = f(\varphi)$; $T_J = 85 \text{ }^\circ\text{C}$




Forward current

$I_F = f(V_F)$; $T_J = 85^\circ\text{C}$




Relative Luminous Flux

$\Phi_v/\Phi_v(270\text{ mA}) = f(I_F)$; $T_J = 85^\circ\text{C}$




Chromaticity Coordinate Shift

$\Delta Cx, \Delta Cy = f(I_F)$; $T_J = 85^\circ\text{C}$




Forward Voltage

$$\Delta V_F = V_F - V_F(85^\circ\text{C}) = f(T_j); I_F = 270 \text{ mA}$$




Relative Luminous Flux

$$\Phi_v/\Phi_v(85^\circ\text{C}) = f(T_j); I_F = 270 \text{ mA}$$




Chromaticity Coordinate Shift

$$\Delta Cx, \Delta Cy = f(T_j); I_F = 270 \text{ mA}$$




Max. Permissible Forward Current

$$I_F = f(T)$$




Dimensional Drawing ⁶⁾


Marking on backside of COB device



Marking Nomenclature



Dimensional Drawing ⁶⁾




C67062-A0533-A1-01

Further Information:

Approximate Weight: 494.5 mg


Tray ⁶⁾

50 pieces per tray



C67062-A0325-X1-02

Barcode-Product-Label (BPL)



OHA04563

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

This device is designed for specific/recommended applications only. Please consult OSRAM Opto Semiconductors Sales Staff in advance for detailed information on other non-recommended applications (e.g. automotive).

Change management for this component is aligned with the requirements of the lighting market.

For further application related information please visit <https://ams-osram.com/support/application-notes>

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.
If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Glossary

- 1) **Brightness:** Brightness values are measured during a current pulse of typically 10 ms, with a tolerance of +/- 7%.
- 2) **Reverse Operation:** Not designed for reverse operation. Continuous reverse operation can cause migration and damage of the device.
- 3) **Forward Voltage:** The Forward voltage is measured during a current pulse duration of typically 1 ms with a tolerance of $\pm 0.05V$.
- 4) **Color reproduction index:** Color reproduction index values (CRI-RA) are measured during a current pulse of typically 10 ms and with a tolerance of ± 2 .
- 5) **Chromaticity coordinate groups:** Chromaticity coordinate groups are measured during a current pulse duration of typically 10ms with a tolerance of ± 0.005 .
- 6) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ± 0.1 and dimensions are specified in mm.

Revision History

Version	Date	Change
1.0	2025-08-11	Initial Version
1.1	2025-10-15	Characteristics Brightness Groups Features
1.2	2025-10-24	Brightness Groups
1.3	2025-12-08	Certificate Logo



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；

按照中国的相关法规和标准，

不含有毒有害物质或元素。

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved

am  **OSRAM**