

# OSRAM KR EGLP41.22

## Datasheet

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved

**am** **OSRAM**

Chip LED 0402

# KR EGLP41.22



## Applications

- Access Control & Security
- Appliances & Tools
- Digital Diagnostic Devices
- Display Backlighting
- Home & Building Automation
- Projection & Display
- Smart Surface
- Vital Sign Monitoring

## Features

- Package: SMT package 0402, colorless diffused resin
- Chip technology: Volume emitter (InGaAlP)
- Typ. Radiation: 75° (horizontal = 0°), 140° (vertical = 90°)
- Color:  $\lambda_{\text{dom}} = 624.0 \text{ nm}$  (● red)

## Ordering Information

Type	Luminous Intensity <sup>1)</sup> $I_F = 20 \text{ mA}$ $I_v$	Ordering Code
KR EGLP41.22-PR-AD	$\geq 45.0 \text{ mcd}$	Q65112A7901

## Maximum Ratings

Parameter	Symbol	Values
Operating Temperature	$T_{op}$	min. -40 °C max. 85 °C
Storage Temperature	$T_{stg}$	min. -40 °C max. 100 °C
Forward current $T_s = 25 \text{ }^\circ\text{C}$	$I_F$	max. 20 mA
Forward Current pulsed $D = 0.005 ; T_s = 25 \text{ }^\circ\text{C}$	$I_{F_{pulse}}$	max. 40 mA
Reverse voltage <sup>2)</sup> $T_s = 25 \text{ }^\circ\text{C}$	$V_R$	max. 5 V
ESD withstand voltage acc. ANSI/ESDA/JEDEC JS-001 (HBM, Class 0)	$V_{ESD}$	ESD sensitive device

## Characteristics

$I_F = 20 \text{ mA}$ ;  $T_S = 25 \text{ }^\circ\text{C}$

Parameter	Symbol	Values	
Peak Wavelength	$\lambda_{\text{peak}}$	typ.	632.0 nm
Dominant Wavelength <sup>3)</sup>	$\lambda_{\text{dom}}$	typ.	624.0 nm
Spectral Bandwidth at 50% $I_{\text{rel,max}}$	$\Delta\lambda$	typ.	20.0 nm
Viewing angle at 50% $I_V$ values for 0°, 90°	$2\varphi$	typ.	75 °
Forward Voltage <sup>4)</sup>	$V_F$	typ.	1.93 V
Reverse current <sup>2)</sup> $V_R = 5 \text{ V}$	$I_R$	typ. max.	0.01 $\mu\text{A}$ 10 $\mu\text{A}$

## Brightness Groups

Group	Luminous Intensity <sup>1)</sup> $I_F = 20$ mA min. $I_v$	Luminous Intensity. <sup>1)</sup> $I_F = 20$ mA max. $I_v$
P	45.0 mcd	71.0 mcd
Q	71.0 mcd	112.0 mcd
R	112.0 mcd	180.0 mcd

## Group Name on Label

Example: P

Brightness


---

P

---


## Relative Spectral Emission <sup>5)</sup>

$I_{\text{rel}} = f(\lambda)$ ;  $I_F = 20 \text{ mA}$ ;  $T_S = 25 \text{ }^\circ\text{C}$




## Radiation Characteristics <sup>5)</sup>

$I_{\text{rel}} = f(\varphi)$ ;  $T_S = 25 \text{ }^\circ\text{C}$




**Forward current** <sup>5)</sup>

$I_F = f(V_F)$ ;  $T_S = 25^\circ\text{C}$




**Relative Luminous Intensity** <sup>5), 6)</sup>

$I_v/I_v(20 \text{ mA}) = f(I_F)$ ;  $T_S = 25^\circ\text{C}$




## Max. Permissible Forward Current <sup>7)</sup>

$$I_F = f(T)$$



## Dimensional Drawing <sup>8)</sup>



general tolerance  $\pm 0,1$   
lead finish Au 


C63062-A4388-A1-03

## Further Information:

**Approximate Weight:** 0.5 mg


## Electrical Internal Circuit

cathode




anode


## Recommended Solder Pad <sup>8)</sup>



□ foot print    □ Cu area




▨ solder resist



▨ solder stencil

### Component Location on Pad




E062.3010.257 - 01

For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for ultra sonic cleaning.

## Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) $25\text{ }^{\circ}\text{C}$ to $150\text{ }^{\circ}\text{C}$			2	3	K/s
Time $t_s$ $T_{S\min}$ to $T_{S\max}$	$t_s$	60	100	120	s
Ramp-up rate to peak*) $T_{S\max}$ to $T_p$			2	3	K/s
Liquidus temperature	$T_L$	217			$^{\circ}\text{C}$
Time above liquidus temperature	$t_L$	80	100	100	s
Peak temperature	$T_p$	245	260	260	$^{\circ}\text{C}$
Time within $5\text{ }^{\circ}\text{C}$ of the specified peak temperature $T_p - 5\text{ K}$	$t_p$	10	20	30	s
Ramp-down rate*) $T_p$ to $100\text{ }^{\circ}\text{C}$			3	6	K/s
Time $25\text{ }^{\circ}\text{C}$ to $T_p$			480	480	s

All temperatures refer to the center of the package, measured on the top of the component


\* slope calculation  $\text{DT}/\text{Dt}$ :  $\text{Dt}$  max. 5 s; fulfillment for the whole  $T$ -range

**Taping** <sup>8)</sup>



C63062-A4388-B1-02


**Tape and Reel** <sup>9)</sup>



**Reel Dimensions**


A	W	$N_{\min}$	$W_1$	$W_{2\max}$	Pieces per PU
180 mm	$8 + 0.3 / - 0.1$ mm	60 mm	$8.4 + 2$ mm	14.4 mm	3000

## Barcode-Product-Label (BPL)



OHA04563

## Dry Packing Process and Materials <sup>8)</sup>



OHA00539

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according to JEDEC-STD-033.

## Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

Based on very short life cycle times in chip technology this component is subject to frequent adaption to the latest chip technology.

For further application related information please visit <https://ams-osram.com/support/application-notes>

## Disclaimer

### **Attention please!**

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.  
If printed or downloaded, please find the latest version on our website.

### **Packing**

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

### **Product and functional safety devices/applications or medical devices/applications**

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

## Glossary

- 1) **Brightness:** Brightness groups are tested at a current pulse duration of 25 ms and a tolerance of  $\pm 11\%$ .
- 2) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- 3) **Wavelength:** Wavelengths are tested at a current pulse duration of 25 ms and a tolerance of  $\pm 1\text{ nm}$ .
- 4) **Forward Voltage:** Forward voltages are tested at a current pulse duration of 1 ms and a tolerance of  $\pm 0.1\text{ V}$ .
- 5) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 6) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- 7) **Thermal Resistance:**  $R_{th\ max}$  is based on statistic values ( $6\sigma$ ) used for Derating.
- 8) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with  $\pm 0.1$  and dimensions are specified in mm.
- 9) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

## Revision History

Version	Date	Change
1.0	2019-01-24	Initial Version
1.1	2020-02-11	Dimensional Drawing Taping
1.2	2020-04-24	Dimensions of Transportation Box
1.3	2021-09-28	Brand
1.4	2022-11-08	New Layout
1.5	2025-11-12	Electro - Optical Characteristics (Diagrams)



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；

按照中国的相关法规和标准，

不含有毒有害物质或元素。

**Published by ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved

**am**  **OSRAM**