

# OSRAM LR T64F

## Datasheet

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved

**am** **OSRAM**

TOPLED™ Black

# LR T64F

TOPLED Black is especially designed for variable message signs (VMS) and price changers. The black package offers premium contrast for display panels.



## Applications

- Projection & Display

## Features

- Package: black PLCC-2 package, colorless resin
- Chip technology: Thinfilm
- Typ. Radiation: 30°
- Color:  $\lambda_{\text{dom}} = 625 \text{ nm}$  (● red)
- Corrosion Robustness Class: 3B
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM)

## Ordering Information

Type	Partial Flux <sup>1)</sup> $I_F = 20 \text{ mA}$ $E_v$	Ordering Code
LR T64F-CADB-1-3A4B	2800 ... 7100 lx	Q65115A2588
LR T64F-BBDB-1-1	2240 ... 7100 lx	Q65111A0256*

\* Referring to former datasheet brightness bins – still valid and available but no longer promoted.

## Maximum Ratings

Parameter	Symbol	Values
Operating Temperature	$T_{op}$	min. -40 °C max. 100 °C
Storage Temperature	$T_{stg}$	min. -40 °C max. 100 °C
Junction Temperature	$T_j$	max. 125 °C
Forward current $T_s = 25 \text{ }^\circ\text{C}$	$I_F$	max. 50 mA
Surge current $t \leq 10 \mu\text{s}; D = 0.1; T_s = 25 \text{ }^\circ\text{C}$	$I_{FS}$	max. 100 mA
Reverse voltage <sup>1)</sup> $T_s = 25 \text{ }^\circ\text{C}$	$V_R$	max. 12 V
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM)	$V_{ESD}$	2 kV

## Characteristics

$I_F = 20 \text{ mA}$ ;  $T_S = 25 \text{ }^\circ\text{C}$

Parameter	Symbol	Values
Peak Wavelength	$\lambda_{\text{peak}}$	typ. 634 nm
Dominant Wavelength <sup>2)</sup> $I_F = 20 \text{ mA}$	$\lambda_{\text{dom}}$	min. 519 nm typ. 625 nm max. 531 nm
Spectral Bandwidth at 50% $I_{\text{rel,max}}$	$\Delta\lambda$	typ. 16 nm
Viewing angle at 50% $I_V$	$2\phi$	typ. 30 °
Forward Voltage <sup>3)</sup> $I_F = 20 \text{ mA}$	$V_F$	min. 1.80 V typ. 1.95 V max. 2.40 V
Reverse current <sup>1)</sup> $V_R = 12 \text{ V}$	$I_R$	typ. 0.01 $\mu\text{A}$ max. 10 $\mu\text{A}$
Temperature Coefficient of Peak Wavelength $-10 \text{ }^\circ\text{C} \leq T \leq 100 \text{ }^\circ\text{C}$	$\text{TC}_{\lambda_{\text{peak}}}$	typ. 0.14 nm / K
Temperature Coefficient of Dominant Wavelength $-10 \text{ }^\circ\text{C} \leq T \leq 100 \text{ }^\circ\text{C}$	$\text{TC}_{\lambda_{\text{dom}}}$	typ. 0.07 nm / K
Real thermal resistance junction/solderpoint <sup>4)</sup>	$R_{\text{thJS real}}$	max. 280 K / W

**Brightness Groups**

Group	Partial Flux <sup>5)</sup> $I_F = 20$ mA min. $E_v$	Partial Flux <sup>5)</sup> $I_F = 20$ mA max. $E_v$	Luminous Intensity <sup>6)</sup> $I_F = 20$ mA typ. $I_v$
CA	2800 lx	3550 lx	2600 mcd
CB	3550 lx	4500 lx	3300 mcd
DA	4500 lx	5600 lx	4140 mcd
DB	5600 lx	7100 lx	5200 mcd

**Forward Voltage Groups**


Group	Forward Voltage <sup>3)</sup> $I_F = 20$ mA min. $V_F$	Forward Voltage <sup>3)</sup> $I_F = 20$ mA max. $V_F$
3A	1.80 V	1.95 V
3B	1.95 V	2.10 V
4A	2.10 V	2.25 V
4B	2.25 V	2.40 V

**Wavelength Groups**

- red

Group	Dominant Wavelength <sup>2)</sup> $I_F = 20$ mA min. $\lambda_{\text{dom}}$	Dominant Wavelength <sup>2)</sup> $I_F = 20$ mA max. $\lambda_{\text{dom}}$
1	519 nm	531 nm

## Chromaticity Coordinate Groups



## Chromaticity Coordinate Groups

● red

Group	Cx	Cy
1	0.6823	0.3109
	0.6894	0.3104
	0.7017	0.2916
	0.7092	0.2907

---

**Group Name on Label**

**Example: CA-3A**

Brightness

Forward Voltage

---


CA

3A

---


## Relative Spectral Emission <sup>6)</sup>

$I_{\text{rel}} = f(\lambda)$ ;  $I_F = 20 \text{ mA}$ ;  $T_S = 25 \text{ }^\circ\text{C}$




## Radiation Characteristics <sup>6)</sup>

$I_{\text{rel}} = f(\varphi)$ ;  $T_S = 25 \text{ }^\circ\text{C}$




**Forward current** <sup>6), 7)</sup>

$I_F = f(V_F)$ ;  $T_S = 25^\circ\text{C}$




**Relative Partial Flux** <sup>6), 7)</sup>

$E_V/E_V(20\text{ mA}) = f(I_F)$ ;  $T_S = 25^\circ\text{C}$




### Forward Voltage <sup>6)</sup>

$$\Delta V_F = V_F - V_F(25^\circ\text{C}) = f(T_j); I_F = 20 \text{ mA}$$




### Relative Partial Flux <sup>6)</sup>

$$\frac{E_v}{E_v(25^\circ\text{C})} = f(T_j); I_F = 20 \text{ mA}$$




## Max. Permissible Forward Current <sup>4)</sup>

$$I_F = f(T)$$




## Permissible Pulse Handling Capability

$$I_F = f(t_p); D: \text{Duty cycle}; T_S = 25^\circ\text{C}$$




## Permissible Pulse Handling Capability

$$I_F = f(t_p); D: \text{Duty cycle}; T_S = 85^\circ\text{C}$$



## Dimensional Drawing <sup>8)</sup>



C63062-A4103-A1.-02

## Further Information:


**Approximate Weight:** 40.0 mg

**Package marking:** Cathode


**Corrosion test:** Class: 3B

Test condition: 40°C / 90 % RH / 15 ppm H<sub>2</sub>S / 14 days (stricter than IEC 60068-2-43)

## Recommended Solder Pad <sup>8)</sup>




## Recommended Solder Pad <sup>8)</sup>



For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for ultra sonic cleaning.

## Reflow Soldering Profile

Product complies to MSL Level 3 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly	Unit	
		Minimum	Recommendation	Maximum
Ramp-up rate to preheat*) 25 °C to 150 °C		2	3	K/s
Time $t_s$ $T_{S\min}$ to $T_{S\max}$	$t_s$	60	100	120 s
Ramp-up rate to peak*) $T_{S\max}$ to $T_p$		2	3	K/s
Liquidus temperature	$T_L$	217		°C
Time above liquidus temperature	$t_L$	80	100	s
Peak temperature	$T_p$	245	250	°C
Time within 5 °C of the specified peak temperature $T_p$ - 5 K	$t_p$	10	20	30 s
Ramp-down rate*) $T_p$ to 100 °C		3	4	K/s
Time 25 °C to $T_p$			480	s


All temperatures refer to the center of the package, measured on the top of the component

\* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

**Taping** <sup>8)</sup>




C63062-A4103-B1-02

Tape and Reel <sup>9)</sup>

## Reel Dimensions


A	W	$N_{\min}$	$W_1$	$W_{2\max}$	Pieces per PU
330 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	2000

## Barcode-Product-Label (BPL)



OHA04563


## Dry Packing Process and Materials <sup>8)</sup>



OHA00539

Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

## Schematic test method for partial flux measurement



## Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit <https://ams-osram.com/support/application-notes>

## Disclaimer

### Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.  
If printed or downloaded, please find the latest version on our website.

### Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

### Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

## Glossary

- 1) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.
- 2) **Wavelength:** The wavelength is measured at a current pulse of typically 25 ms, with an internal reproducibility of  $\pm 0.5$  nm and an expanded uncertainty of  $\pm 1$  nm (acc. to GUM with a coverage factor of  $k = 3$ ).
- 3) **Forward Voltage:** The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of  $\pm 0.05$  V and an expanded uncertainty of  $\pm 0.1$  V (acc. to GUM with a coverage factor of  $k = 3$ ).
- 4) **Thermal Resistance:**  $R_{th\ max}$  is based on statistic values ( $6\sigma$ ) used for Derating.
- 5) **Brightness:** Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of  $\pm 8$  % and an expanded uncertainty of  $\pm 11$  % (acc. to GUM with a coverage factor of  $k = 3$ ).
- 6) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 7) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.
- 8) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with  $\pm 0.1$  and dimensions are specified in mm.
- 9) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

## Revision History

Version	Date	Change
1.7	2022-07-12	New Layout Applications
1.8	2024-12-18	Features
1.9	2025-12-15	Ordering Information Brightness Groups



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；

按照中国的相关法规和标准，

不含有毒有害物质或元素。

**Published by ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

[ams-osram.com](http://ams-osram.com)

© All rights reserved

**am**  **OSRAM**