

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant



Profibus	CAN-Bus/Feldbus	CC-Link
CFBUS.PVC.001	CFBUS.PVC.020-CFBUS.PVC.022	CFBUS.PVC.035
Ethernet (CAT5/CAT5e/GigE/PoE)	Ethernet (CAT6/GigE/PoE)	Ethernet (CAT6 _A /PoE)
CFBUS.PVC.040-CFBUS.PVC.045	CFBUS.PVC.049	CFBUS.PVC.050
Ethernet (CAT7/PoE)	FireWire 800 (IEEE1394b)	Profinet (Type C)
CFBUS.PVC.052	CFBUS.PVC.056	CFBUS.PVC.060
USB 3.0		
CFBUS.PVC.068		

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee
and service life
calculator based
on 2 billion test
cycles per year




Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant



Cable structure



Conductor
Stranded conductor in especially bending-resistant version consisting of bare copper wires (following DIN EN 60228).

Core insulation
According to bus specification.

Core structure
According to bus specification.

Core identification
According to bus specification.
► Design table

Overall shield
Bending-resistant braiding made of tinned copper wires.
Coverage linear approx. 55%, optical approx. 80%

Outer jacket
Low-adhesion, oil-resistant PVC mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-4-1).
Colour: Red/lilac (similar to RAL 4001), Variants ► Table Mechanical information
Printing: black



,00000 m** igus chainflex CFBUS.PVC.---① -----② E310776 ③ cRUus ④

AWM Style ⑤ VW-1 AWM I/II A/B 80°C ⑥ V FT1 CE ---⑦

conform RoHS-II conform www.igus.de +++ chainflex cable works +++

* Length printing: Not calibrated. Only intended as an orientation aid.

① / ② Cable identification according to Part No. (see technical table).

③ Printing: E497341 instead of E310776 (for UL-Listed cables only).

④ Printing: CMX 75°C (for UL-Listed cables only).

⑤ Printing UL style (see related chapter).

⑥ Printing UL Voltage Rating (see related chapter).

⑦ Printing according to bus specification (inclusive wave resistance).

Example: ... chainflex CFBUS.PVC.001 (2x0.25)C E310776 ...

Guaranteed service life according to guarantee conditions

Double strokes	5 million	7.5 million	10 million
Temperature, from/to [°C]	R min. [x d]	R min. [x d]	R min. [x d]
+5/+15	15	16	17
+15/+60	12.5	13.5	14.5
+60/+70	15	16	17

Minimum guaranteed service life of the cable under the specified conditions.

The installation of the cable is recommended within the middle temperature range.

Example image

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant



Properties and approvals

	UV resistance	Medium
	Oil resistance	Oil-resistant (following DIN EN 50363-4-1), Class 2
	Flame-retardant	According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	PTFE-free	The design of these products does not contain PTFE
	UL-verified	Certificate No. V293650: „igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“
	UL-listed	CMX, 75°C (except CFBUS.PVC.068)
	UL/CSA AWM	Details see table UL/CSA AWM
	NFPA	Following NFPA 79-2018, chapter 12.9
	CLPA	CFBUS.PVC.045: CC-Link IE Field , Reference no. 153 CFBUS.PVC.049: CC-Link IE Field , Reference no. 154
	REACH	In accordance with regulation (EC) No. 1907/2006 (REACH)
	Lead-free	Following 2011/65/EC (RoHS-II/RoHS-III)
	Cleanroom	According to ISO Class 1. The outer jacket material of this series complies with CF240.02.24 - tested by IPA according to standard DIN EN ISO 14644-1
	CE	Following 2014/35/EU



Example image

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant



Properties and approvals

UL/CSA AWM Details

Part No.	UL style core insulation	UL style outer jacket	UL Voltage Rating [V]	UL Temperature Rating [°C]
CFBUS.PVC.001	10578	20601	300	80
CFBUS.PVC.020	10493	2571	30	80
CFBUS.PVC.021	10578	20601	300	80
CFBUS.PVC.022	10578	20601	300	80
CFBUS.PVC.035	10578	20601	300	80
CFBUS.PVC.040	11602	20601	300	80
CFBUS.PVC.045	11635	20601	300	80
CFBUS.PVC.049	11635	20601	300	80
CFBUS.PVC.050	11635	20601	300	80
CFBUS.PVC.052	10493	20601	300	80
CFBUS.PVC.056	10578	20601	300	80
CFBUS.PVC.060	11602	20601	300	80
CFBUS.PVC.068	11602 (AWG28) 11635 (AWG28)	20601	300	80



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Example image

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant



Dynamic information



Bend radius

e-chain® linear
flexible
fixed

minimum 12.5 x d
minimum 10 x d
minimum 7 x d



Temperature

e-chain® linear
flexible
fixed

+5°C up to +70°C
-5°C up to +70°C (following DIN EN 60811-504)
-15°C up to +70°C (following DIN EN 50305)



v max.

unsupported
gliding

3m/s
2m/s



a max.

30m/s²



Travel distance

Unsupported travels and up to 20m for gliding applications, Class 3



Typical lab test setup for this cable series


Test bend radius R approx. 75 - 100 mm

Test travel S approx. 1 - 15 m

Test duration minimum 2 - 4 million double strokes

Test speed approx. 0,5 - 2 m / s

Test acceleration approx. 0.5 - 1.5 m / s²



Typical application areas

- For medium duty applications, Class 4
- Unsupported travels and up to 20m for gliding applications, Class 3
- Light oil influence, Class 2
- No torsion, Class 1
- Preferably indoor applications, but also outdoor ones at temperatures > 5°C
- Machining units/packaging machines, handling, indoor cranes

Data sheet

chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
 • Oil-resistant • Flame-retardant



Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm ²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
Profibus (1x2x0.64 mm)				
CFBUS.PVC.001	(2x0.25)C	8.5	25	77
CAN-Bus				
CFBUS.PVC.020 ²⁾	(4x0.25)C	7.0	23	57
CFBUS.PVC.021	(2x0.5)C	8.5	32	86
CFBUS.PVC.022 ²⁾	(4x0.5)C	8.5	43	94
CC-Link				
CFBUS.PVC.035	(3x0.5)C	8.0	40	82
Ethernet/CAT5				
CFBUS.PVC.040 ²⁾ <small>EtherCAT®</small>	(4x0.25)C	6.5	29	70
Ethernet/CAT5e				
CFBUS.PVC.045 <small>CC-Link IE Field</small>	(4x(2x0.15))C	7.5	33	67
Ethernet/CAT6				
CFBUS.PVC.049 <small>CC-Link IE Field</small>	(4x(2x0.15))C	7.5	33	67
Ethernet/CAT6_A				
CFBUS.PVC.050	4x(2x0.20)C	10.0	65	123
Ethernet/CAT7				
CFBUS.PVC.052	(4x(2x0.15)C)C	9.5	89	136
Profinet				
CFBUS.PVC.060 ²⁾ ¹³⁾ <small>PROFINET theCAT®</small>	(4x0.38)C	7.0	33	67
USB 3.0				
CFBUS.PVC.068	(2x(2xAWG28)+2x(2xAWG28)C)C	7.0	39	68

The chainflex® types marked with ²⁾ are cables designed as a star-quad.

¹³⁾ Colour outer jacket: Yellow-green (RAL 6018)

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
 G = with green-yellow earth core x = without earth core



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




Profibus

CFBUS.PVC.001

Cable structure

(Electrical information please see next page)



Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.001	(2x0.25)C	red, green	

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant



Profibus

CFBUS.PVC.001

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.001
Nominal voltage	50 V 300 V (following UL)
Testing voltage (following DIN EN 50289-1-3)	500 V
Operating capacity	30 pF/m
Characteristic wave impedance (following DIN EN 50289-1-11)	150 ± 15 Ω (≥ 1 MHz)



Line attenuation approx. [dB/100m]

Part No.	9.6 kHz	38.4 kHz	4 MHz	16 MHz
CFBUS.PVC.001	0.3	0.5	2.5	2.9

Conductor nominal cross section [mm ²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Maximum current rating at 30 °C (following DIN VDE 0298-4) [A]
0.25	78.0	5

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Example image

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




CAN-Bus/Feldbus

CFBUS.PVC.020-CFBUS.PVC.022

Cable structure

(Electrical information please see next page)



1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall banding: Plastic fleece
3. Overall shield: Bending-resistant braiding made of tinned copper wires
4. Shield foil: Aluminium clad plastic foil
5. Banding: Plastic foil
6. Core insulation: Mechanically high quality TPE mixture (according to bus specification)
7. Conductor: Fine-wire strand in especially bending-stable version consisting of bare copper wires
8. Filler: Plastic dummy

Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.020	(4x0.25)C	white, green, brown, yellow (Star-quad)	
CFBUS.PVC.021	(2x0.5)C	white, brown	
CFBUS.PVC.022	(4x0.5)C	white, green, brown, yellow (Star-quad)	

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant



CAN-Bus/Feldbus

CFBUS.PVC.020-CFBUS.PVC.022

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.020	CFBUS.PVC.021	CFBUS.PVC.022
Nominal voltage	50 V 30 V (following UL)	50 V 300 V (following UL)	
Testing voltage (following DIN EN 50289-1-3)		500 V	
Operating capacity	42 pF/m	41 pF/m	42 pF/m
Characteristic wave impedance (following DIN EN 50289-1-11)		120 ± 12 Ω (≥ 1 MHz)	



Line attenuation approx. [dB/100m]

Part No.	0.1 MHz	1 MHz	5 MHz	10 MHz	20 MHz
CFBUS.PVC.020	1.3	1.9	4.8	6.9	9.5
CFBUS.PVC.021	0.6	1.3	3.3	4.7	6.8
CFBUS.PVC.022	0.8	1.8	4.0	5.8	8.5

Conductor nominal cross section	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)
[mm²]	[Ω/km]	[A]
0.25	84.0	5
0.5	39.0	10

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Example image

igus® chainflex® CFBUS.PVC.049

12/2025

© igus® SE & Co. KG. Subject to misprints and errors. Technical modifications are possible at any time. Maybe older batches do not have all 10/24 or other features. Please refer regarding the availability of the items especially the information in the latest chainflex® catalogue.

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




CC-Link

CFBUS.PVC.035

Cable structure

(Electrical information please see next page)



1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall shield: Bending-resistant braiding made of tinned copper wires
3. Overall banding: Plastic fleece
4. Shield foil: Aluminium clad plastic foil
5. Banding: Plastic foil
6. Core insulation: Mechanically high quality TPE mixture (according to bus specification)
7. Conductor: Fine-wire strand in especially bending-stable version consisting of bare copper wires
8. Filler: Plastic dummy

Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.035	(3x0.5)C	white, blue, yellow	

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant




CC-Link

CFBUS.PVC.035

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.035
Nominal voltage	50 V 300 V (following UL)
Testing voltage (following DIN EN 50289-1-3)	500 V
Characteristic wave impedance (following DIN EN 50289-1-11)	$110 \pm 16.5 \Omega (\geq 1 \text{ MHz})$



Example image

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




Ethernet (CAT5/CAT5e/GigE/PoE)

CFBUS.PVC.040-CFBUS.PVC.045

Cable structure

(Electrical information please see next page)



Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.040	(4x0.25)C	white, green, brown, yellow (Star-quad)	
CFBUS.PVC.045	(4x(2x0.15))C	white-blue/blue, white-orange/orange, white-green/green, white-brown/brown	

Example image
igus® chainflex® CFBUS.PVC.045

1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall banding: Plastic fleece
3. Shield foil: Aluminium clad plastic foil
4. Overall shield: Bending-resistant braiding made of tinned copper wires
5. Banding: Plastic foil
6. Separating element: Bending-stable TPE cross filler
7. Core insulation: Mechanically high quality TPE mixture (according to bus specification)
8. Conductor: Fine-wire strand in especially bending-stable version consisting of bare copper wires



Data sheet

chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
 ● Oil-resistant ● Flame-retardant



Ethernet (CAT5/CAT5e/GigE/PoE)

CFBUS.PVC.040-CFBUS.PVC.045

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.040		CFBUS.PVC.045	
Nominal voltage	50 V 300 V (following UL)			
Testing voltage (following DIN EN 50289-1-3)	500 V			
Operating capacity	50 pF/m		47 pF/m	
Nominal Velocity of Propagation (NVP)	67 %		72 %	
Characteristic wave impedance (following DIN EN 50289-1-11)	100 ± 15 Ω			



Line attenuation approx. [dB/100m]

Part No.	1 MHz	4 MHz	10 MHz	16 MHz	20 MHz	31.25 MHz	62.5 MHz	100 MHz
CFBUS.PVC.040	1.7	4.2	7.0	9.2	10.4	13.2	19.4	25.3
CFBUS.PVC.045	2.5	5.0	8.3	10.6	11.7	15.0	21.9	28.6

Conductor nominal cross section [mm²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)	
		[Ω/km]	[A]
0.15	145.0		2.5
0.25	94.0		5

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Part No.	Bus type	Link class	Maximum transmission length	
			Channel	Permanent
CFBUS.PVC.040	Ethernet/CAT5	Class D - (Data applications up to 100 MHz)	82m	70m
CFBUS.PVC.045	Ethernet/CAT5e	Class D - (Data applications up to 100 MHz)	82m	70m

Example image

igus® chainflex® CFBUS.PVC.045

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




Ethernet (CAT6/GigE/PoE)

CFBUS.PVC.049

Cable structure

(Electrical information please see next page)



1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall shield: Bending-resistant braiding made of tinned copper wires
3. Shield foil: Aluminium clad plastic foil
4. Banding: Plastic foil
5. Separating element: Bending-stable TPE cross filler
6. Core insulation: Mechanically high quality TPE mixture (according to bus specification)
7. Conductor: Fine-wire strand in especially bending-stable version consisting of bare copper wires

Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.049	(4x(2x0.15))C	white-blue/blue, white-orange/orange, white-green/green, white-brown/brown	

Example image



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant



Ethernet (CAT6/GigE/PoE)

CFBUS.PVC.049

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.049
Nominal voltage	50 V 300 V (following UL)
Testing voltage (following DIN EN 50289-1-3)	500 V
Operating capacity	47 pF/m
Nominal Velocity of Propagation (NVP)	72 %
Characteristic wave impedance (following DIN EN 50289-1-11)	100 ± 15 Ω



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Line attenuation approx. [dB/100m]

Part No.	1 MHz	4 MHz	10 MHz	16 MHz	20 MHz	31.25 MHz	62.5 MHz	100 MHz	155.5 MHz	200 MHz	250 MHz
CFBUS.PVC.049	2.5	5.0	8.3	10.6	11.7	15.0	21.9	28.6	38.6	42.9	47.7

Conductor nominal cross section	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)
[mm ²]	[Ω/km]	[A]

0.15

145.0

2.5

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Part No.	Bus type	Link class	Maximum transmission length	
			Channel	Permanent
CFBUS.PVC.049	Ethernet/CAT6	Class E - (Data applications up to 250 MHz)	74m	63m

Example image

igus® chainflex® CFBUS.PVC.049

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




Ethernet (CAT6A/PoE)

CFBUS.PVC.050

Cable structure

(Electrical information please see next page)



Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.050	4x(2x0.20)C	white-blue/blue, white-orange/orange, white-green/green, white-brown/brown	

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet

chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
● Oil-resistant ● Flame-retardant



Ethernet (CAT6_A/PoE)

CFBUS.PVC.050

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.050											
Nominal voltage	50 V 300 V (following UL)											
Testing voltage (following DIN EN 50289-1-3)	500 V											
Operating capacity	45 pF/m											
Nominal Velocity of Propagation (NVP)	76 %											
Characteristic wave impedance (following DIN EN 50289-1-11)	100 ± 15 Ω											

Line attenuation approx. [dB/100m]

Part No.	1 MHz	4 MHz	10 MHz	16 MHz	20 MHz	31.25 MHz	62.5 MHz	100 MHz	155.52 MHz	200 MHz	250 MHz	350 MHz	500 MHz
CFBUS.PVC.050	2.2	4.6	7.2	9.1	10.1	12.6	18.1	23.4	30.6	35.7	40.8	49.4	60.9

Conductor nominal cross section	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)
[mm ²]	[Ω/km]	[A]
0.2	113.0	3.5

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Part No.	Bus type	Link class	Maximum transmission length	
			Channel	Permanent
CFBUS.PVC.050	Ethernet/CAT6 _A	Class EA - (Data applications up to 500 MHz)	73m	62m

Example image

igus® chainflex® CFBUS.PVC.049



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




Ethernet (CAT7/PoE)

CFBUS.PVC.052

Cable structure

(Electrical information please see next page)



Example image

For detailed overview please see design table

1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall banding: Plastic fleece
3. Overall shield: Bending-resistant braiding made of tinned copper wires
4. Element shield: Bending-resistant braiding made of tinned copper wires
5. Element shield foil: Aluminium clad plastic foil
6. Banding: Plastic foil
7. Core insulation: Mechanically high quality TPE mixture (according to bus specification)
8. Conductor: Fine-wire strand in especially bending-stable version consisting of bare copper wires
9. Strain relief: Tensile stress-resistant centre element

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.052	(4x(2x0.15)C)C	white-blue/blue, white-orange/orange, white-green/green, white-brown/brown	

Example image
igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet

chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
● Oil-resistant ● Flame-retardant



Ethernet (CAT7/PoE)

CFBUS.PVC.052

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.052										
Nominal voltage	50 V 300 V (following UL)										
Testing voltage (following DIN EN 50289-1-3)	500 V										
Operating capacity	48 pF/m										
Nominal Velocity of Propagation (NVP)	68 %										
Characteristic wave impedance (following DIN EN 50289-1-11)	100 ± 15 Ω										

Line attenuation approx. [dB/100m]

Part No.	1 MHz	4 MHz	10 MHz	16 MHz	20 MHz	31.25 MHz	62.5 MHz	100 MHz	155.52 MHz	250 MHz	500 MHz	600 MHz
CFBUS.PVC.052	2.5	5.2	8.3	10.4	11.6	14.7	21.5	27.7	35.5	45.6	67.2	73.0

Conductor nominal cross section	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)
[mm ²]	[Ω/km]	[A]
0.15	149.0	2.5

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Part No.	Bus type	Link class	Maximum transmission length	
			Channel	Permanent
CFBUS.PVC.052	Ethernet/CAT7	Class F - (Data applications up to 600MHz)	71m	60m

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




Profinet (Type C)

CFBUS.PVC.060

Cable structure

(Electrical information please see next page)



Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.060	(4x0.38)C	white, orange, blue, yellow (Star-quad)	

Example image

igus® chainflex® CFBUS.PVC.049



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant



Profinet (Type C)

CFBUS.PVC.060

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.060
Nominal voltage	50 V 300 V (following UL)
Testing voltage (following DIN EN 50289-1-3)	500 V
Operating capacity	53 pF/m
Nominal Velocity of Propagation (NVP)	67 %
Characteristic wave impedance (following DIN EN 50289-1-11)	100 ± 15 Ω



Line attenuation approx. [dB/100m]

Part No.	1 MHz	4 MHz	10 MHz	16 MHz	20 MHz	31.25 MHz	62.5 MHz	100 MHz
CFBUS.PVC.060	2.0	4.1	6.2	7.8	8.7	11.0	16.3	21.2

Conductor nominal cross section	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)
[mm ²]	[Ω/km]	[A]
0.38	59.4	7

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Example image

Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) • For medium duty applications • PVC outer jacket • Shielded
• Oil-resistant • Flame-retardant




USB 3.0

CFBUS.PVC.068

Cable structure

(Electrical information please see next page)



1. Outer jacket: Pressure extruded, oil-resistant PVC mixture
2. Overall banding: Plastic fleece
3. Overall shield: Bending-resistant braiding made of tinned copper wires
4. Banding: Plastic foil
5. Element shield: Bending-resistant braiding made of tinned copper wires
6. Shield foil: Aluminium clad plastic foil
7. Core insulation: Mechanically high quality TPE mixture (according to bus specification)
8. Conductor: Fine-wire strand in especially bending-stable version consisting of tinned copper wires

Example image

For detailed overview please see design table

Design table

Part No.	Core group	Colour code	Core design
CFBUS.PVC.068	2x(2xAWG28)	red/black, green/white-green	
	2x(2xAWG28)C	blue/yellow, orange/violet	

Example image



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Data sheet chainflex® CFBUS.PVC



Bus cable (Class 4.3.2.1) ● For medium duty applications ● PVC outer jacket ● Shielded
● Oil-resistant ● Flame-retardant



USB 3.0

CFBUS.PVC.068

Electrical information

(Cable structure please see previous page)

Part No.	CFBUS.PVC.068	
Nominal voltage	50 V	300 V (following UL)
Testing voltage (following DIN EN 50289-1-3)	500 V	
Characteristic wave impedance (following DIN EN 50289-1-11)	STP: $90 \pm 18 \Omega$ (1-1200 MHz)	UTP: $105 \pm 16 \Omega$ (1-1200 MHz)
Operating capacity	STP: 60 pF/m	UTP: 52 pF/m
Nominal Velocity of Propagation (NVP)	STP: 70 %	UTP: 67 %



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Line attenuation approx. [dB/100m]

Part No.	1 MHz	625 MHz	1200 MHz
CFBUS.PVC.068	0.4	11.5	18.0

Conductor nominal cross section	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2)	Maximum current rating at 30 °C (following DIN VDE 0298-4)
[mm ²]	[Ω/km]	[A]
0.28	205.0	1

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

Example image