



RK ROSE+KRIEGER

A Phoenix Mecano Company

RK LEAN-Solution & RK Easywork

Tailored to your production process




LEAN production

Lean production is the reduction of the 7 forms of waste (overproduction, waiting time, transportation, unnecessary processing, stocks, movement, rejects/reworking). A number of methods help to achieve shorter lead times and delivery times and significantly lower stock levels.

We at RK Rose+Krieger would like to provide you with support for your optimisation plans by constructing your workstations, shelves or transport trolleys in accordance with your concepts and lean and ergonomics principles so that they are adapted ideally to the process, material and personnel.

We also offer you optimised and individual transport trolleys, material supply using Kanban, or a combination of all of the above.



Yesterday's workstations

Static, non-modifiable working environments. Employees had little to no options for making changes or adjustments.



Today's workstations

The working environment adapts to constant changes. Employees constantly improve work procedures.



To achieve optimum results, humans and workstations must harmonise. We would be happy to advise you on how to design the working environment for your employees in the best possible way.



RK LEAN-Solution Workshops

Raise production processes to a new level through effective LEAN management

RK Rose+Krieger, your expert for ergonomic lean (assembly) workstations, now also offers one-day LEAN solutions workshops where your employees actively participate in workplace development. Our aim is to reduce one-piece flow processing times, reduce waste and increase productivity.



During the LEAN solutions workshops, the team develops a wood and cardboard model of the future workstation.

LEAN solutions workshop - your benefits


- Staff experience is utilised, acceptance of change is encouraged
- Realistic simulations of the concept (cardboard engineering)
- Less space required
- Reduction in inventory and intermediate storage
- Shorter processing times
- Increased productivity
- Reduction in overall costs
- Ergonomics at the workstation,
positive influence on the performance and health of employees

Cardboard Engineering

- Our specialised LEAN consultants analyse the production and logistics at the current workstation together with your affected employees and then develop a concept for the future lean workstation.
- With the help of cardboard engineering, together we implement a realistic simulation of the concept as a 1:1 scale model made of wood and cardboard.
- At this cardboard workstation, employees can produce and keep improving it until everyone is happy with the processes and the results.
- In doing so, we optimise the material flow, the load carrier dimensioning and the ergonomics of material provision, each of which is precisely tailored to your individual needs.
- Those affected become participants in this method and bring their creativity, detailed knowledge and experience to the table.
- Our goal-oriented way of working will ensure that the result satisfies your requirements.
- This creates a one-piece-flow workstation that has successfully passed the practical test.



Tailor-made intralogistics



Shelves



Transport trolleys



Individual workstations

RK LEAN-Solution

The highest degree of efficiency in optimised workstations. You are familiar with your processes and your requirements. Our product specialists know the RK product portfolio. Together, we can develop the ideal solution for you. If you already have firm ideas, draw up a sketch and send it to our product specialists.



Innovative process structuring – Efficient sequences

We are happy to share our many years of experience in the field of lean production with you.

The RK Easywork workstation system is based on RK Rose+Krieger's complete modular system. We implement your ideas using our versatile RK product range.

PROFILE TECHNOLOGY



LINEAR TECHNOLOGY



CONNECTING TECHNOLOGY



Mix'n'match

Moving and positioning

Clamp and release solutions

BLOCAN® construction profiles made from aluminium and the electrically driven lifting columns offer a perfect combination for the creation of high-quality table concepts. Customers can choose between the simplest static tables or electrically height-adjustable work tables and configure their own combinations. Are you interested in an assistance system? Contact us for further details.

Use our online configurator

- Quick and simple operation
- Selection of table systems and accessories
- Immediate generation of CAD data in native formats
- Quotations can be requested simply based on the selected components
- You receive a written quotation promptly



Workstation systems

Compilation of a workstation system

- We will be happy to help with the design of your table systems
- Please contact us at: anfrage.vertrieb@rk-online.de


Telephone: 0571/9335-801

- Calculation details can also be found on our homepage: www.rk-rose-krieger.com/service




Work table: static

- Base frame made from profile 40 x 40 and 40 x 80
- Variable height (min. 750 mm max. 1250 mm), width and depth of the table
- ESD accessories available
- Different table top material options
- Optional portal which can be configured with accessories
- Various drawer cabinet versions



Code No.	Type RK Easywork table	Height max.	Width min.	Width max.	Depth min.	Depth max.
W10M1-----	Static / assembled	1250	750	2000	650	1200
W10U1-----	Static / unassembled					
W11M1-----	Static ESD / assembled					
W11U1-----	Static ESD / unassembled					



Workstation systems

Work table: electrically height adjustable with Multilift II


Multilift II ESD
(electrostatic discharge)




Multilift II impact
(integrated damping)



- Height adjustment using dual-column system (Multilift lifting columns), various designs
- Adjustment using 6-key hand switch/2-key hand switch and an electronic MultiControl synchronous controller
- Min. table height = 726 mm
Max. table height = 1171 mm
- Wide range of configuration and equipment options, as with the static version
- Max. load: 4000 N with evenly distributed load
see details, page 14



Code No.	Type RK Easywork table	Height min.	Height max.	Width min.	Width max.	Depth min.	Depth max.
W12M11081	ML II 355 assembled	726	1081				
W12U11081	ML II 355 unassembled	726	1081				
W12M11171	ML II 400 assembled	771	1171				
W12U11171	ML II 400 unassembled	771	1171				
W13M11081	ML II 355 ESD assembled	726	1081				
W13U11081	ML II 355 ESD unassembled	726	1081				
W13M11171	ML II 400 ESD assembled	771	1171				
W13U11171	ML II 400 ESD unassembled	771	1171				
W14M11090	ML II 355 impact assembled	735	1090				
W14U11090	ML II 355 impact unassembled	735	1090				
W14M11180	ML II 400 impact assembled	780	1180				
W14U11180	ML II 400 impact unassembled	780	1180				



**Work table:
electrically height adjustable
with Multilift II telescope**


Multilift II telescope




- Height adjustment using dual-column system (Multilift lifting columns), various designs
- Adjustment using 6-key hand switch/2-key hand switch and an electronic MultiControl synchronous controller
- Min. table height = 728 mm
Max. table height = 1378 mm

- Wide range of configuration and equipment options, as with the static version
- Max. load: 4000 N with evenly distributed load
see details, page 14

Multilift II ESD
(electrostatic discharge)




Code No.	Type	Height min.	Height max.	Width min.	Width max.	Depth min.	Depth max.
W15M11378	ML II telescope assembled						
W15U11378	ML II telescope unassembled	728	1378	750	2000	650	1000
W16M11378	ML II telescope ESD assembled						
W16U11378	ML II telescope ESD unassembled						




Load data

Work table: static




Work table static	
$F_{zmax a}$	800 N
$F_{zmax b}$	800 N
$F_{zmax c}$	800 N
$F_{zmax d}$	800 N
F_{zmax}	3200 N

Work table: electrically height adjustable



Work table (a = left/b = right)	
$F_{zmax a}$	2000 N
$M_{ymax a}$	200 Nm
$F_{zmax b}$	2000 N
$M_{ymax b}$	200 Nm
F_{zmax}	4000 N

Rear gantry



rear gantry (a = left/b = right)	
$F_{z1\max a}$	1600 N
$M_{y1\max a}$	150 Nm
$F_{z1\max b}$	1600 N
$M_{y1\max b}$	150 Nm
$F_{z2\max a}$	3500 N
$M_{y2\max a}$	400 Nm
$F_{z2\max b}$	3500 N
$M_{y2\max b}$	400 Nm


Workstation systems

Controller for height-adjustable work tables: MultiControl II duo

- Duty cycle, overcurrent and temperature monitoring for overload protection as standard
- Intuitive operation thanks to hand switch with graphics-capable display screen (6-key hand switch)
- The hand switch can be used to perform multiple functions, such as the storage of intermediate positions or user changes (6 positions can be saved)
- Simple connection to the master control system level using serial interface (RS-485) and standardised bus protocol (Modbus ASCII)
- Energy-efficient overall system (control incl. hand switch thanks to switched-mode power supply with wide-range input (standby consumption < 0.5 watts)
- LED for visual status indication
- Connection of external sensors
- Scope of delivery: without IEC cable (see table on page 12)
- Fastenings are included with the basic version of the work table



1 HS = Hand switch plug connector
 2 DATA = Interface for sensors
 (e.g. safety edge and synchronisation bus)
 3 M2 = Motor connector 2
 4 M1 = Motor connector 1 (must always be assigned)
 P = Power socket



Code No.	for drive	Weight
QST11H12AA000	Multilift II, Multilift II ESD	1 kg
QST12H12AA000	Multilift II telescope	1 kg
QST13H12AA000	Multilift II impact	1 kg

IEC cable


Code No.	Version	Type	Cable length
QZD070618	IEC cable (European version, earthed plug)	F	1,80 m
QZD020159	IEC cable (Swiss version, earthed plug)	J	1,80 m
QZD070619	IEC cable (UK version, earthed plug)	G	1,80 m
QZD070631	IEC cable (Japanese version, earthed plug)	B	1,80 m
QZD070622	IEC cable (US version, earthed plug)	B	2,00 m

Hand switch with display screen
(6 function keys)

Hand switch without display screen
(2 function keys)

Hand switch drawer
Fastenings are included with the basic version of the work table



Code No.	Version	Fig.	Weight
QZB11G07AV041	Hand switch with 6 function keys and display screen – 1 m spiral cable	1	0,17 kg
QZB11G07AB041	Hand switch with 2 function keys – 1 m spiral cable	2	0,15 kg
QZD000074	Hand switch drawer for hand switches with 6 and 2 function keys	3	0,11 kg

Attachments

Standard version:

The attachments are supplied loose with the base table (includes assembly instructions).

Special version:

You receive your work table fully assembled with all the desired attachments



1	Table top	14	RK monitor mounting
2	Frame/gantry	15	Tool holder
3	LED lamp	16	Monitor holder
4	Runner profile	17	Cup and device holder
5	Balancer	18	Drawer cabinet
6	Perforated boards /tool holders	19	Keyboard shelf
7	Mounting rail	20	PC holder (page 33)
8	Material tray level		
9	Pivoting material rail		
10	Document holder		
11	Grab containers		
12	Roller conveyors		
13	Power supply		

1 Table top

Different board materials can be selected depending on the area of application.



Laminated particleboard (HPL, MFB)

Decorative, plastic-coated, easy-care, banded edges



Beech multiplex panel

High load-bearing strength and flexural strength, easy to machine



ESD table top

Volume conductive particleboard core, high resistance to abrasion

Code No.	Type	Thickness	max. size	Weight [kg/m ²]
4012601	Laminated particleboard (melamine), light grey	22 mm	2000 x 2750 mm	15,0
4012602	Laminated particleboard (HPL), light grey	20 mm		15,0
4012603	Oiled multiplex board, beec	30 mm	1490 x 2490 mm	25,0
4012604	Oiled multiplex board, beech	40 mm		34,0
4012605	ESD table top (HPL), light grey	20 mm	2000 x 2750 mm	13,0
4012606	ESD table top (HPL), light grey	30 mm		19,5

Further versions available on request. Cut to specification.
ESD mat, see page „ESD table mat“ on page 34.

Attachments

2 Frame/Gantry

The frame/gantry is fitted to the rear of the tables and is used to mount lamps, grab containers, aids and tools etc.

Rear gantry





Rear frame



Attention: The fixing set is not included in the scope of delivery and must be ordered separately (see table „Fixing set“ below).

Rear gantry: load data, see details page 15



Code No.	Type
W17M1	Rear gantry, assembled, ESD compatible
W17U1	Rear gantry, unassembled, ESD compatible
W18M1	Rear frame, assembled, ESD compatible
W18U1	Rear frame, unassembled, ESD compatible

3. Depth (300-1200 mm)

2. Width (table width)

1. Height (328-2000 mm)

Fixing set

Code No.	Type
WAC042000300	Fixing set, static table
WAC042000301	Fixing set, electrically height adjustable dual-column system


3 LED lamp

(Workstation lighting,
protection rating IP40, protection class I)

Low-fatigue and efficient working requires an absolutely glare-free design and arrangement of lighting. The even illumination of the work surface is also imperative. It is a proven means of reducing error rates and increasing the performance of the employee.

Areas of application:

- Lighting for industrial assembly workstations and for general illumination
Temperature range: Ta -20°C to +40°C
- **Lighting technology:**
Optimised lighting technology using prismatically structured cover with a high level of transmission and diffuser foil
- Unidirectional structure makes for homogeneous appearance
- Even all-round glare elimination
- No direct image of the LED light source visible
LED service life: >100,000 h (L80/B10)
- Colour temperatures*: 4000 K (NW)
Colour reproduction index: Ra >80
- Dimming by reducing the power of all LEDs, no partial deactivation



Dimensions:
Length 982 mm,
Width 174 mm,
Height 28 mm




Scope of delivery: fastenings included

Code No.	Type	LED current	Number of LEDs	System output at 100% operation	Light source luminous flux Light colour NW	Weight
WAC042000208	LED lamp	100mA	90	31 W	3.200 lm	3,5 kg

- Permissible operating voltage:
220 – 240 V AC, 50/60 Hz
Output voltage SELV equivalent 20 – 54 V
Overload and over-temperature protection
Service life > 100,000 h (<B10)
- DALI interface, used internally for the dimming function, light source dimmable down to 1%
- Light management: Integrated button with TouchDIM functionality, thus facilitating continuously variable dimming with save function for the desired setting for optimised lighting level
- Housing:
Lamp housing made of corrosion-resistant aluminium (anodised) with large-area connection for LED modules for optimum heat dissipation (lamp housing simultaneously acts as heat sink)
Housing end caps made from cast aluminium, powder-coated, black
- Lamp cover made from UV-resistant PMM with integrated prisms for light deflection
- Electrical connection: power connection via integrated plug connection, 3-pin
- Lamp, including pre-fabricated connection cable, 3 m with earthed plug

Fastenings
(Flange bracket)




Installation on portal:

An assembly profile is required.
Please state the inner dimension.
Scope of delivery: fastenings included.

Code No.	Type	Weight
WAC042000314	Installation profile for LED lamp	1,28 kg

Inner dimension of assembly profile (length)



Inner dimension =
table width - 80 mm



Attachments

4 STP 40 runner profile



The runner profile is fitted to the portal, and is used to guide tools and aids (e.g. balancer, see below).

Material: aluminium profile, bright anodised,
Weight: 2.2 kg/m




Fastenings (flange bracket)

Installation on portal:

Please state the inner dimension.

Includes:

fixing material and 1 piece of carriage for balancer



Code No.	Type
WAC042000160	Carriage for balancer
WAC042000308	Runner profile

5 Balancer



The balancers make it possible to position tools „weightlessly” in the workstation so that they are within convenient reach. In order to guarantee optimum function, the entire weight of the tool (including any supply lines) must be within the specified load capacity range. The exact load capacity can be set on the device as required.


Material:

Material:
housing made of impact resistant plastic,
Stainless steel cable

Code No.	Load capacity range	Cable travel	Weight
WAC042000161	0,5 - 1,5 kg	1,7 m	0,3 kg
WAC042000162	1,5 - 3,0 kg	1,7 m	0,4 kg
WAC042000163	3,0 - 4,0 kg	1,7 m	0,5 kg

6

Perforated boards



The metal perforated boards can be fastened to the portal as panelling or a tool holder mount. The sheets have an impact and scratch resistant coating (RAL 7035).

Dimensions 450 x 1000 mm, sheet thickness 1.5 mm


The perforated boards can be fastened to the portal frame as required (on the left or right, in the middle, on the right and left). Alongside the perforated boards, the installation of the mounting rail for grab containers can also be useful (see page 20). This way, tools and assembly material are conveniently within reach.

When using perforated boards:


Minimum portal height ≥ 1368 mm

Maximum portal height = 2000 mm


Configuration examples:



Perforated board on left or right
(from table width >770 mm)



Perforated board in middle
(from table width >1010 mm)



Perforated board on left & right
(from table width >1260 mm)



Befestigungssatz




Code No.	Type	Weight
WAC042000335	Perforated boards 450 x 1000 mm	5,12 kg
WAC042000149	Fixing set (set of 4)	0,11 kg
WAC042000314	Assembly profile for perforated boards	1,28 kg

Inner dimension of assembly profile (length)

Attachments

7 Mounting rail (ESP 40 x 40) 7 for grab containers



Mounting rail (ESP 40 x 40)
for grab containers, „pivoting“




The grab containers are simply attached to the profile slot and positioned. The assembly profile can be ordered with a pivoting fixing set as required.

Material: aluminium profile, bright anodised


Weight: 1.1 kg/m

Scope of delivery: fixing set included

Clamping lever for
„pivoting“ fixing set



Mounting rail (ESP 40 x 40)
for grab containers, „non-pivoting“





Code No.	Type	Weight
2x 90210	Clamping lever for pivoting fixing set	0,04 kg
WAC042000307	Mounting rail (ESP 40 x 40), pivoting	1,15 kg/m
WAC042000313	Mounting rail (ESP 40 x 40), non-pivoting	1,10 kg/m

Inner dimension of assembly profile (length)

8 Material tray level

The material tray level is used to mount grab containers, tools or other aids. The level can be fastened to the portal at any height, and pivots in a longitudinal direction as required.

Pivoting range: $\pm 90^\circ$
Minimum portal height > 818 mm



Code No.	Type
W20M20030	Material tray level with steel swivel including fixing set


2. Depth (220-600 mm)

1. Inner dimension (width 180-2500 mm)

Code No.	Type
2x WAC042000144	Steel swivel with fixing set
2x WAC042000145	Clamping lever for fixing set

Attachments

9 Pivoting material rail



The pivoting material rails can be equipped with grab containers (see page 24) and pulled into the ergonomic working position as required.

Load capacity:

Single material rail max. 10 kg
Triple material rails max. 15 kg

Pivoting range: 180° for each joint



Single material rail (fixed)

Triple material rails (inclining)

Code No.	Type	Weight
WAC042000056	1 material rail	1,1 kg
WAC042000057	3 material rails	2,7 kg

10 Document holder



The document holder (10x, A4) can be fitted to the portal using the fixing set included in the scope of delivery. Drawings, assembly instructions and other important documents are thus ergonomically within reach at all times.

Code No.	Type	Weight
WAC042000024	Document holder	1 kg

11 Grab containers



Plastic container for storing assembly material.
Different colours and sizes available.

Code No.	Type	Colour	Weight
WAC042000114	170x100x50 mm (0,5 Liter)	blue	0,08 kg
WAC042000112		green	
WAC042000111		yellow	
WAC042000113		red	
WAC042000119	160x100x75 mm (0,9 Liter)	blue	0,1 kg
WAC042000117		green	
WAC042000116		yellow	
WAC042000118		red	
WAC042000124	230x150x122 mm (2,7 Liter)	blue	0,25 kg
WAC042000122		green	
WAC042000121		yellow	
WAC042000123		red	

12
Roller conveyors

Roller conveyor profile

Roller with flange



Roller without flange


Using roller conveyors, Kanban modules can easily be created and integrated into the Easywork tables in accordance with the customer's requirements.



The roller elements each have a length of 50 mm. They can be inserted/clipped into the roller conveyor profile.

The length of the profile track has to be ordered to suit the number of roller elements.

Code No.	Type	Weight
WAC042000330	Roller conveyor profile 6 mtr. bar	7,8 kg
WAC042000324	Roller conveyor profile	1,3 kg/m

Code No.	Type	lot sizes	Load capacity N	Weight
WAC042000322	Roller with flange	10, 20, 30... pcs	150	0,018 kg/pcs
WAC042000321	Roller without flange			0,016 kg/pcs

End plates: galvanised steel, including 4 screws


Code No.	Typ
WAC042000326	End plate 40x80x5
WAC042000325	End plate 40x40x5


Slot stone -N-

This slot stone slides into the end of the profile slot.

Material: galvanised steel

*RK profile system slot geometry


Code No.	Type	lot sizes	Slot geometry*	A	B	C	D	E	M
4026203	M6	10, 20, 30... pcs	40	8	10	13	15	4	M6



Attachments

13

Power supply Socket strips



90° turned sockets in plastic housing,
1.5 m supply cable with molded earthing contact plug,
max. connection load of 3600 W

45° turned sockets in aluminum housingframe,
2.0 m supply cable without plug,
max. connection load of 3600 W


Code No.	Type of socket strip	Weight
WAC042000318	Fig. 1 centrally switching, including fixing set	0,8 kg
WAC042000319	Fig. 2 individually switchable, including fixing set	1,0 kg
WAC042000320	Fig. 3 non-switchable, including fixing set	0,6 kg

Energy supply channel components available on request

The energy supply channel can be equipped with any combination of the individual components, and can be ordered on request.

Code No.	Type
WAC05	$L_{max} = 6004$ mm

Total length including end caps (2 mm each)



- 1. Energy supply channel
- 2. CEE power socket
- 3. Emergency stop button
- 4. Twin power socket
- 5. Power socket
- 6. Network outlet
- 7. Toggle switch
- 8. Pneumatic connection

14 RK monitor mounting

RK monitor mounting (rotary flange)



RK monitor mounting (ball joint)



Monitor mounting (compact)



Connecting plate VESA 50/75, VESA 75/100



These mounts for monitors, touch panels and other operating devices are flexible, provide many degrees of freedom and are thus suitable for universal use.

Features:

- Device connection using universal connecting plate or VESA connecting plate
- High-strength materials guarantee reliable processes and sustained loads
- Highly ergonomic working by adjusting the height to the body size of the operator
- Sideways turning for optimum setting of the field of vision
- Rotary flange and ball joint: vibration-proof inclination adjuster, latching in 15° increments
- Compact: half-cup version (makes subsequent assembly easier), optional reducing inserts available (round or square 20, 25, 30 mm)
- Connection to aluminium profile possible and thus to the machine frame using slot stones
- Universal fastening holes facilitate easy wall mounting

Code No.	Type	Weight	max. load
193000030C11	Rotary flange	0,37 kg	25 kg
193000042C11	Ball joint	0,34 kg	10 kg
193000052C11	Compact	0,29 kg	10 kg

Code No.	Type	Weight
94372	50/75	0,67 kg
94371	75/100	0,80 kg

Attachments

Profile console



Scope of delivery:
fastenings included
to 40 slot geometry BLOCAN®

Code No.	Type	Weight
193000298C66	Profile console	0,27 kg

Wall console




Scope of delivery: fastenings not included


Code No.	Type	Weight
193000358C66	Wall console	0,36 kg

Vario-Quick holding block K/KK

Type K



Type KK



Code No.	Type	lot sizes	Version
40181251	Holding block K	10, 20, 30... pcs	40 slot geometry*
40181271	Holding block KK	10, 20, 30... pcs	40 slot geometry*

* RK profile system slot geometry

Attention: for further components see also the „Connecting technology“ catalogue, chapter „Support arm/equipment carrier systems“, starting on page 254.

15 Tool holder

with inclined hook end, L=50



Code No.
WAC042000097

double, with inclined hook end, L=50



Code No.
WAC042000098

Magnetic holder, D=40



Code No.
WAC042000099

Pliers holder, W=55/D=20



Code No.
WAC042000100

Machine holder, D=60



Code No.
WAC042000103

Grab container holder



Code No.
WAC042000104

Tool holder for self-service packaging



Code No.
WAC042000315

The tool holders keep the workstation tidy and organised. They can be inserted into the perforated boards listed on page 21.

Impact and scratch resistant plastic coating, base plate thickness 1.5 mm, aluminium-coloured

Screwdriver holder, 8x



Code No.
WAC042000101

Screwdriver holder



Code No.
WAC042000309

Round tin holder



Code No.
WAC042000310

Hexagon socket key holder, D=1-11



Code No.
WAC042000102

Storage box



Code No.
WAC042000311

Shelf plate, W=350, D=125



Code No.
WAC042000105

Attachments



16 Monitor holder



Pivoting range: 180° for each joint
Angle of inclination: ±10°
Load capacity: max. 15 kg

Monitor holder as a space-saving and ergonomic solution for your LCD screen. The height and inclination of the holder can be adjusted continuously variably.

The scope of delivery includes a fixing set for connection to the workstation profile and an assembly plate with VESA hole pattern (75 x 75 and 100 x 100 mm).



Code No.	Type	Weight
WAC042000125	Monitor holder	3,17 kg

17 Cup and device holder

Open





Closed



Cup holder (open): tools and devices, e.g. drills, can be hung up securely.

Cup holder (closed): drinks are set down in a defined position and do not obstruct assembly work. The holder can be fastened directly to the profile slot. The fixing set is included in the scope of delivery.

Material: plastic



Code No.	Type	Weight
401A532	Cup holder, open	0,15 kg
401A533	Cup holder, closed	0,17 kg

18 Drawer cabinet



Workbench drawer cabinet made from powdercoated quality steel plate. The drawers run on a precision telescopic guide.

The drawer cabinet (**Colour:** RAL 7035) can be locked using a cylinder lock, and is supplied with two keys. Load per slide (drawer): 15 kg max.

A fixing set is included in the scope of delivery.

Please note the required minimum width (1000 mm) of the assembly workbenches.

Also to be a minimum depth of 680 mm must also be taken into account.

Static tables:

2 cabinets possible with a table width >1500 mm

Two-column system:

1 cabinets possible with a table width >1000 mm and table depth 680 mm

2 cabinets possible with a table width >1600 mm and table depth 680 mm

Code No.	Type	H x B x T	Weight
WAC042000304	1 drawer	230 x 460 x 550 mm	11,1 kg
WAC042000305	2 drawers	380 x 460 x 550 mm	15,8 kg
WAC042000306	3 drawers	380 x 460 x 550 mm	18,3 kg

19 Keyboard shelf



Keyboard shelf with ball bearing slides for pulling out and stowing the keyboard easily.

A fixing set is included in the scope of delivery.

Colour: black, material: plastic, stable design, storage tray with cover for writing implements.

Code No.	Type	Weight incl. fixing set
WAC042000317	Keyboard shelf	2,2 kg

20 PC holder



The PC holder for fastening underneath the table top can be adjusted without the use of tools.

Height adjustment: 307-532 mm

Width adjustment: 78 - 220 mm

A fixing set is included in the scope of delivery.

Colour: black, material: steel

Code No.	Type	Weight incl. fixing set
WAC042000316	PC holder	4,3 kg

Accessories

ESD table mat



Two-layer composite coating made from wearresistant synthetic rubber. Resistant to solder and heat, abrasion, halogen-free, permanently elastic, volume conductive.

Including 2 push-button connections 10 mm.

Typical bleeder resistance

RG= 106-107 ohms

Code No.	Type
WAC042000087	900 x 610 mm
WAC042000088	1220 x 610 mm

ESD wristband



Adjustable and elastic wristband without metal contact plate, antiallergenic. Push-button connection 3 mm

A highly elastic spiral cable (2.4 m) with the safety resistance value of 2x 1 MΩ is available as an accessory. Wristband connection 3 mm push-button, earthing contact connection 10 mm push-button



Code No.	Type
WAC042000089	Wristband
WAC042000090	Spiral cable 2.4 m

ESD earthing box



Box as central earthing connection point (EBP - earth bonding point) for personal grounding. Earth conductor 2 m in length. Connection type 4 mm threaded eye hook, per connection 1 MΩ safety resistance.

2x 10 mm push-button, 1x 4 mm safety socket.

Code No.	Type
WAC042000091	Earthing box

ESD central earthing strip

Central strip for connection of a maximum of 6 earth conductors with screw terminals for cable lugs with 4 mm eyelet.



Code No.	Type
WAC042000092	Central earthing strip

ESD earth bonding plug

Dummy plug for CEE 7/3 power socket for direct earthing of table and floor coverings or the central earthing strip.
With 2.4 m of spiral cable,
1 M Ω safety resistance,
10 mm push-button.



Code No.	Type
WAC042000094	2,0 m standard cable
WAC042000093	2,4 m spiral cable

ESD earth conductor

Earth conductor for table/floor covering.
Standard cable with 1 M Ω safety resistance,
10 mm push-button,
4 mm threaded eye hook.





Code No.	Type
WAC042000095	1,5 m cable
WAC042000096	3,0 m cable

Accessories

Vario-Quick cable bracket


For routing cables and hoses
 Simply screwed into the slot
 Can be opened and reused without any difficulty
Material: black plastic



Hammer foot (HF) version

Code No.	Type	lot sizes	Slot geometry	A	B	C	D	E	F
40181401	15 HF	10, 20, 30... pcs	40	28,5	17	10	19	9,5	28,5
40181411	25 HF	10, 20, 30... pcs	40	36,5	25	10	19	9,5	36,5
40181421	35 HF	10, 20, 30... pcs	40	47,5	35	10	19	9,5	47,5

Hook and eye cable ties




Code No.	lot sizes
91815	5, 10, 15... pcs

Slot stones




Spring clip




-K-




Spring clip



-R-



For additional fastening of attachments to the workstation. The slot stones can also be swivelled in or screwed into the profile slot retrospectively. The slot stone can be secured in any position thanks to the attached spring (type -F/K-).
Material: galvanised steel



[mm]

Code No.	Type	lot sizes	A	B	C	D	M
4006715	-F- / M4	10, 20, 30... pcs	10	14	4	–	M4
4006713	-F- / M5	10, 20, 30... pcs	10	14	4	–	M5
4016212	-K- / M6	10, 20, 30... pcs	21	14	4	7	M6
4016213	-K- / M8	10, 20, 30... pcs	21	14	4	7	M8
4026221	-R- / M6	10, 20, 30... pcs	15	9	10	–	M6
4026222	-R- / M8	10, 20, 30... pcs	15	9	10	–	M8

Slot stones -PA-



Version PA -R-




Version PA -F-



Version PA -K-

The -PA- slot stones have an equipotential bonding effect by destroying the anodised coating. The slot stones can be used in an assembly kit or be connected to each other using bridge pieces.

Material: black galvanised steel



Code No.	Type	lot sizes	Slot geometry	A	B	C	H	L	M
Slot stone PA -R-									
4006E21	M6	10, 20, 30... pcs	30	–	13	10	5	29	M6
Slot stone PA -F-									
4006E12	M6	10, 20, 30... pcs	30	–	12	10	4	10	M6
Slot stone PA -K-									
4006F12	M6	10, 20, 30... pcs	30	–	12	10	4	21	M6

Accessories


Cover profile - plastic-



For the flush covering of longitudinal slots.
Two versions are available.

Material: plastic


Please note that for typographical reasons, the colours listed here are only an approximate representation of the corresponding RAL colours.
Further special colours available on request.



	Black RAL 9005
	White aluminium RAL 9006
	Light grey RAL 7035
	Rape yellow RAL 1021
	Traffic red RAL 3020
	Signal blue RAL 5005

Code No.	Type	Colour	A	B	C
4000570	2	Black	12	11,2	6,4
4000575	2	Light grey	12	11,2	6,4
4000577	2	White aluminium	12	11,2	6,4
4000579	2	Rape yellow	12	11,2	6,4
4000581	2	Traffic red	12	11,2	6,4
4000583	2	Signal blue	12	11,2	6,4
4008570	1	Black	12	11,2	6,4
4000585	1	Rape yellow	12	11,2	6,4
4000586	1	Transparent	12	11,2	6,4

Cover profile - aluminium



Code No.	Type	Slot geometry	A	B	C	[mm]
4015570	1 Stück	40	12	10	5,2	

You will find further accessories and aluminium profiles in our main catalogue „BLOCAN® profile technology“



Configuration

Enquiry

Order

Table version static

<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
<input type="checkbox"/> ESD assembled	<input type="checkbox"/> ESD unassembled

Height: _____ mm (min. 750-1250mm max.)
 Width: _____ mm (min. 750-2000mm max.)
 Depth: _____ mm (min. 650-1200mm max.)





Table version electric height-adjustable



Multilift II 355	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
Multilift II 400	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
Multilift II ESD 355	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
Multilift II ESD 400	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
Multilift II impact 355	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
Multilift II impact 400	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled
Multilift II telescope	<input type="checkbox"/> assembled	<input type="checkbox"/> unassembled

Attachments

Standard version: The attachments are supplied loose with the base table (includes assembly instructions).

Special version: You receive your workbench fully assembled with all the desired attachments.

- Hand switch with display screen (6 function keys)
- Hand switch without display screen (2 function keys)
- Hand switch drawer
- IEC cable (Europe)
- IEC cable (Switzerland)
- IEC cable (United Kingdom)
- IEC cable (Japan, USA)

Worktop

- MFB particleboard (melamine) 22mm
- HPL particleboard (laminated) 23mm
- Beech Multiplex board 30mm
- Beech Multiplex board 40mm
- ESD table top 20mm
- ESD table top 30mm

Worktop: width _____, depth _____

Frame/Gantry

- completely mounted frame/gantry
- unmounted components

Height (min. 328-2000mm max.): _____

Width (max. Tischbreite): _____

Depth (min. 300-1200mm max.): _____

- LED lamp
- Runner profile (table width-80mm): _____
- Balancer, load capacity (min. 0,5-1,5 kg max.)
- Balancer, load capacity (min. 1,5-3,0 kg max.)
- Balancer, load capacity (min. 3,0-4,0 kg max.)
- perforated board(s) (1-2 unit, 450x1000mm each)
- mounting rail(s) for grab containers (1-3 units)
- Material tray level steel swivel
- 1 pivoting material rail (load capacity max. 10 kg)
- 3 pivoting material rails (load capacity max. 20 kg)
- Document holder

- grab container(s) (170x100x50) red blue green yellow
- grab container(s) (160x100x75) red blue green yellow
- grab container(s) (230x150x122) red blue green yellow
- Roller conveyor(s) length: _____
- Roller(s) with flange, purchase only in lot sizes 10, 20, 30... pcs.
- Roller(s) without flange, purchase only in lot sizes 10, 20, 30... pcs.
- End plate(s) 40x40x5 End plate(s) 40x80x5
- Slot stone -N-, purchase only in lot sizes 10, 20, 30... pcs.
- Socket strip, centrally switched
- Socket strip, individually switched
- Socket strip, non-switchable

RK monitor mounting

- With rotary flange With ball joint Compact
- Connecting plate Vesa 50/75 Connecting plate Vesa 75/100
- Profile console Wall console
- Vario-Quick holding block Typ K Vario-Quick holding block Typ KK
- Monitor holder aluminium (page 26)

Tool holder

<input type="checkbox"/> With inclined hook end	<input type="checkbox"/> Double, with inclined hook end
<input type="checkbox"/> Magnetic holder, D=40	<input type="checkbox"/> Pliers holder, B=55/T=20
<input type="checkbox"/> Machine holder, D=60	<input type="checkbox"/> Grab container holder
<input type="checkbox"/> Tool holder for self-service packaging	<input type="checkbox"/> Screwdriver holder, 8x
<input type="checkbox"/> Screwdriver holder	<input type="checkbox"/> Round tin holder
<input type="checkbox"/> Hexagon socket key holder, D=1-11	<input type="checkbox"/> Storage box
<input type="checkbox"/> Shelf plate, W=350/D=125	
<input type="checkbox"/> Cup and device holder, open	
<input type="checkbox"/> Cup and device holder, closed	

Drawer cabinet

- with 1 drawer 230x460x550mm
- with 2 drawers 380x460x550mm
- with 3 drawers 380x460x550mm
- Keyboard shelf
- PC holder

Accessories

<input type="checkbox"/> ESD table mat 900x610mm	<input type="checkbox"/> ESD table mat 1220x610mm
<input type="checkbox"/> ESD wristband	<input type="checkbox"/> ESD spiral cable 2.4 mtr.
<input type="checkbox"/> ESD earthing box	<input type="checkbox"/> ESD central earthing strip
<input type="checkbox"/> ESD earth bonding plug 2.0 mtr. standard cable	
<input type="checkbox"/> ESD earth bonding plug 2.4 mtr. spiral cable	
<input type="checkbox"/> ESD earth conductor 1.5 mtr. cable	
<input type="checkbox"/> ESD earth conductor 3.0 mtr. cable	

Attention: lot size

- Vario-Quick cable bracket(s) 15 HF / purchase only in lot sizes 10, 20, 30... pcs
- Vario-Quick cable bracket(s) 25 HF / purchase only in lot sizes 10, 20, 30... pcs
- Vario-Quick cable bracket(s) 35 HF / purchase only in lot sizes 10, 20, 30... pcs
- Hook and eye cable tie(s) / purchase only in lot sizes 5, 10, 15... pcs

Cover profile(s) 2 m bar

- pcs. Plastic, black RAL 9005
- pcs. Plastic, white aluminium RAL 9006
- pcs. Plastic, light grey RAL 7035
- pcs. Plastic, rape yellow RAL 1021
- pcs. Plastic, traffic red RAL 3020
- pcs. Plastic, signal blue RAL 5005
- pcs. Aluminium
- Slot stone(s) -F-, purchase only in lot sizes 10, 20, 30... pcs
- Slot stone(s) -K-, purchase only in lot sizes 10, 20, 30... pcs
- Slot stone(s) -R-, purchase only in lot sizes 10, 20, 30... pcs
- Slot stone(s) PA -R-, purchase only in lot sizes 10, 20, 30... pcs
- Slot stone(s) PA -F-, purchase only in lot sizes 10, 20, 30... pcs
- Slot stone(s) PA -K-, purchase only in lot sizes 10, 20, 30... pcs

Sketch/description:

--

RK Rose+Krieger GmbH

Potsdamer Straße 9

32423 Minden/Germany

+49 571 9335-0

E-Mail: anfrage.vertrieb@rk-online.de

Datum:

Customer number:.....

Company:.....

Project:.....

Telephone:.....

E-mail:.....

Contact:.....

Department:.....

Sketches / Notes



Application examples



RK ROSE+KRIEGER



RK Rose+Krieger GmbH
Verbindungs- und Positioniersysteme
Potsdamer Straße 9
32423 Minden, Germany
+49 571 93 35-0
info@rk-online.de
www.rk-rose-krieger.com



(Informationen)