

Datasheet

Part No:
FW.79.SMA.A

Description

700~930MHz ISM/NB-IoT/LoRa Flexible Terminal Mount Monopole Antenna with over molded SMA(M), 15.5mm(D) x 90mm(L)

Features:

Flexible Terminal Mount Monopole Antenna
Covering 700-930MHz
IP67 Waterproof Enclosure
Dims: Ø15.5 x 90 mm
Connector: SMA(M)
RoHS & Reach Compliant



1. Introduction	3
2. Specification	4
3. Mechanical Drawing	5
4. Packaging	6
5. Antenna Characteristics	8
6. Radiation Patterns	12

Changelog	25
-----------	----

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Ireland & USA
ISO 9001:2015
Certified



Taiwan
ISO 9001:2015
Certified



1. Introduction



The Taoglas Meteor Series FW.79 is a high-performance, compact monopole antenna designed for ISM, NB-IoT, LTE-M, and LoRa applications across the 700–930 MHz frequency range. With a peak gain of up to 3.25 dBi and excellent efficiency, this antenna delivers robust, long-range wireless connectivity in space-constrained designs.

Encased in a rugged, overmoulded polyurethane housing, the antenna is IP67-rated to withstand dust, water, and challenging environmental conditions, ensuring consistent performance in both indoor and outdoor deployments. Measuring only 90 mm in length and 15.5 mm in diameter, the FW.79 provides a discreet form factor without sacrificing on performance.

The antenna comes standard with an SMA(M) connector for quick and secure integration into gateways, routers, modems, or sensor devices. Its flexible, durable whip design resists impact and vibration, making it an ideal choice for field-deployed IoT and M2M applications.

Typical Applications

- Smart metering and utilities (water, gas, electricity)
- Industrial telemetry and SCADA systems
- Smart agriculture (soil, and irrigation monitoring)
- Smart city infrastructure (lighting, parking, waste, air quality)
- Asset tracking and logistics (trailers, containers, bins)

For more information or sample, contact your regional Taoglas office.


2. Specification

Electrical									
Band	Frequency (MHz)	Measurement	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Max. input power
698-894MHz	698-894	15x9cm PCB	60.5	-2.18	3.25	50 Ω	Linear	Omni directional	10W
		9x15cm PCB	75.0	-1.25	3.25				
		Free Space	23.5	-6.29	1.58				
880-960MHz	880-960	15x9cm PCB	56.3	-2.50	2.89				
		9x15cm PCB	69.4	-1.59	2.59				
		Free Space	32.6	-4.87	1.54				


Mechanical	
Dimensions	Ø15.5mm x 90 mm
Weight	11.4g
Mount	Terminal, connector
Material	Polyurethane
Connector	SMA(M)

Environmental	
Waterproof Rating	IP67 Rated Enclosure
Operation Temperature	-40°C to 85°C
Storage Temperature	-40°C to 85°C
Relative Humidity	Non-condensing 65°C 95% RH

3. Mechanical Drawing



4. Packaging




- 1 PCS / Small PE Bag
- Small PE Bag (mm): 140x40 (Ref)
- Weight (g): 11.4 ±3%



- 25 PCS / PE Bag
- PE Bag(mm): 300x210 (Ref)
- Weight (g): 295.2 ±3%
- SPQ Label




- 250 PCS / Box
- Box(mm): 290x210x120
- Weight (kg): 3.26 ±3%
- QTY Label




- 500 PCS / Carton
- Carton(mm): 312x230x290
- Weight (kg): 7 ±3%
- Carton Label

5. Antenna Characteristics


5.1 Test Setup




5.2 Return Loss




5.3 VSWR




5.4 Efficiency



5.5 Average Gain




5.6 Peak Gain



6. Radiation Patterns


6.1 Test Setup



Free Space





15x9cm Ground Plane





9x15cm Ground Plane



6.2 15x9cm Ground Plane Patterns at 704 MHz





6.3 9x15cm Ground Plane Patterns at 704 MHz





6.4 Free Space Patterns at 704 MHz





6.5 15x9cm Ground Plane Patterns at 798 MHz





6.6 9x15cm Ground Plane Patterns at 798 MHz





6.7 Free Space Patterns at 798 MHz





6.8 15x9cm Ground Plane Patterns at 869 MHz





6.9 9x15cm Ground Plane Patterns at 869 MHz





6.10 Free Space Patterns at 869 MHz





6.11 15x9cm Ground Plane Patterns at 915 MHz



6.12 9x15cm Ground Plane Patterns at 915 MHz



6.13 Free Space Patterns at 915 MHz



Changelog for the datasheet

SPE-25-8-269 - FW.79.SMA.A

Revision: B (Current Version)

Date:	2026-01-30
Changes:	Updated weight.
Changes Made by:	Gary West

Previous Revisions

Revision: A (Original First Release)

Date:	2025-09-29
Notes:	Initial Release
Author:	Gary West



TAOGLAS[®]

www.taoglas.com

