



Datasheet

Part No:
FPX75.07.0045B

Description

Atom FXP75 2.4GHz Flex Super Micro PCB Antenna,
45mm Ø0.81, I-PEX MHF® I (U.FL)

Features:

- Ultra Low Profile Flexible Wi-Fi Antenna
- Ideal for Bluetooth® earphones
- Worldwide smallest cabled 2.4GHz antenna
- Dims: 5.9 x 4.1 x 0.24mm
- Cable: 45mm of Ø 0.81mm mini-coaxial cable
- Connector: IPEX MHF1 Connector (U.FL compatible)
- RoHS and Reach Compliant

1. Introduction	3
2. Specification	4
3. Mechanical Drawing	5
4. Packaging	6
5. Antenna Characteristics	7
6. Radiation Patterns	11

Changelog	15
-----------	----

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

1. Introduction



The FXP75 Atom is an ultra-miniature, ultra-low-profile monopole antenna for the 2.4 GHz band, covering Bluetooth®, Wi-Fi®, ZigBee® and ISM applications. This Taoglas patent-pending antenna is one of the smallest true cabled 2.4 GHz antennas available. Manufactured from flexible polymer material, the FXP75 measures just 5.9 × 4.1 × 0.24 mm and features double-sided 3M adhesive for simple peel-and-stick integration.

Typical applications include:

- Bluetooth® earphones and headsets
- Wearable devices
- Compact IoT sensors
- Smart home and consumer electronics
- Space-constrained embedded devices

Built on a flexible polymer substrate, the FXP75 is engineered for high performance in compact IoT devices and wearables. Cables and Connectors can be fully customized based on customer requirements, please contact your regional Taoglas customer support team.


2. Specification

Electrical								
Band	Frequency (MHz)	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Max. input power
Wi-Fi - 2GHz	2400-2500	36.3	-4.4	0.84	50 Ω	Linear	Omni directional	2W

Mechanical	
Dimensions	5.9 x 4.1 x 0.24mm
Material	Polymer
Connector	IPEX MHF1
Cable	Ø0.81mm coaxial cable

Environmental	
Operation Temperature	-40°C to 85°C
Storage Temperature	-40°C to 85°C
Relative Humidity	Non-condensing 65°C 95% RH

3. Mechanical Drawing



NOTES:

- 1.No dregs or insufficient soldering. Solder thickness 0.2 ~1.7mm
- 2.The solder must be smooth and full to the edges of the pad.The solder must not extend outside of the pad area.
- 3.The connector position has special orientation to the PCB as per drawing.
- 4.All material must be RoHS compliant.
- 5.Open/short QC, VSWR required.
- 6.Soldered area. 


	Name	P/N	Material	Finish	QTY
1	FXP75 PCB	100112F010011A	Polymer 0.24 [△]	Black	1
2	0.81 Coaxial Cable	300815C010000A	FEP	Black	1
3	IPEX MHF1	204111E000013A	Brass	Au Plated	1
4	Double Side Adhesive	100112F010011A	3M 467	Brown Liner	1

4. Packaging

100pcs FXP75.07.0045B per PE Bag

Dimensions - 59*41*0.24mm


Weight - 105g



2000pcs per Large Carton


Carton Dimensions - 230*175*160mm

Weight - 2.1Kg




5. Antenna Characteristics

5.1 Test Setup




VNA Test Setup on 2mm ABS


5.2 Return Loss




5.3 VSWR




5.4 Efficiency



5.5 Average Gain





5.6 Peak Gain





6. Radiation Patterns

6.1 Test Setup





Chamber Test Setup on 2mm ABS



6.2 Patterns at 2400 MHz



6.3 Patterns at 2450 MHz



6.4 Patterns at 2500 MHz



Changelog for the datasheet

SPE-13-8-067 – FXP75.07.0045B

Revision: E (Current Version)

Date:	2026-02-05
Changes:	Full datasheet update.
Changes Made by:	Gary West

Previous Revisions

Revision: D

Date:	2024-09-13
Changes:	Updated product photos
Changes Made by:	Conor McGrath

Revision: C

Date:	2015-05-11
Changes:	Amended frequency labels on 3.4 and 3.5 tables
Changes Made by:	Aine Doyle

Revision: B

Date:	2015-02-05
Changes:	Added note on Gain
Changes Made by:	Aine Doyle

Revision: A (Original First Release)

Date:	2013-10-07
Notes:	
Author:	Technical Writer



TAOGLAS[®]

www.taoglas.com

