



ANR006 HIGH THROUGHPUT MODE

PROTEUS-II / PROTEUS-III / PROTEUS-III-SPI

VERSION 1.4

FEBRUARY 16, 2021

Revision history

Manual version	Notes	Date
1.0	Initial version	November 2018
1.1	Updated file name to new AppNote name structure. Updated important notes, legal notice & license terms chapters.	June 2019
1.2	Updated address of Division Wireless Connectivity & Sensors location	October 2019
1.3	Added new test results of Proteus-II and Proteus-III	February 2020
1.4	Added new test results of the Proteus-III-SPI	February 2021

Abbreviations

Abbreviation	Name	Description
Payload		The intended message in a frame / package.
RF	Radio frequency	Describes wireless transmission.
UART	Universal Asynchronous Receiver Transmitter	Allows the serial communication with the module.
[HEX] 0xhh	Hexadecimal	All numbers beginning with 0x are hexadecimal numbers. All other numbers are decimal, unless stated otherwise.

Contents

1	Introduction	4
1.1	Compatibility and risks	5
2	Usage	6
2.1	Maximum packet size	6
2.2	Bluetooth LE packet format	6
2.2.1	Example: Transmitting fragmented data	7
3	Throughput test	8
3.1	Test conditions	8
3.2	Test procedure	8
3.3	Test results	9
3.3.1	Test setup 1: Via USB interface and PC	9
3.3.2	Test setup 2: Via micro controller	10
4	Important notes	12
4.1	General customer responsibility	12
4.2	Customer responsibility related to specific, in particular safety-relevant applications	12
4.3	Best care and attention	12
4.4	Customer support for product specifications	12
4.5	Product improvements	13
4.6	Product life cycle	13
4.7	Property rights	13
4.8	General terms and conditions	13
5	Legal notice	14
5.1	Exclusion of liability	14
5.2	Suitability in customer applications	14
5.3	Trademarks	14
5.4	Usage restriction	14
6	License terms	16
6.1	Limited license	16
6.2	Usage and obligations	16
6.3	Ownership	17
6.4	Firmware update(s)	17
6.5	Disclaimer of warranty	17
6.6	Limitation of liability	17
6.7	Applicable law and jurisdiction	18
6.8	Severability clause	18
6.9	Miscellaneous	18

1 Introduction

The Proteus series is a product series of Bluetooth® modules based on the nRF52 Nordic Semiconductors SoC which presents various Bluetooth® LE and low power features. Bluetooth® LE enabled devices allow to transmit/receive data in a short interval after the connection event. During this period, by default one data packet of up to 251 Bytes is transmitted from master to slave and one data packet from slave to master. After the transmission, the device goes to sleep until the next connection event occurs (see figure 1).




Figure 1: Data transmission with 1 packet per connection interval

Due to this procedure, the device is suited for low power applications, but its default radio throughput is limited¹ to:

$$\frac{\text{Data per packet}}{\text{Connection interval}} [\text{Byte/s}] \quad (1)$$

To overcome this limitation, for Proteus-II and Proteus-III a new mode has been introduced. This so called "high throughput mode" enables to transmit/receive up to 4 Bluetooth® LE packets per connection interval (see figure 2). With this the throughput of a Bluetooth® LE connection can be increased, at the expense of a higher energy consumption.

¹Please note that there are further conditions that slow down the throughput, like the UART speed and the μC processor speed.




Figure 2: Improved data transmission with up to 4 packets per connection interval

1.1 Compatibility and risks

By default Bluetooth® LE enabled devices support the transmission of one data packet in a short period after the connection event. With upcoming new Bluetooth® LE devices an increasing number of data packets per connection interval is supported. Modern iOS devices support up to 4 packets, Android devices support up to 6 packets per connection interval:

Device	Number of packets per connection interval
Samsung Galaxy S8	4
Nexus 4, Nexus 6P	6
OnePlus 5	6
iPhone 6, 7, Xs	4

Table 1: Examples of Bluetooth® LE enabled devices supporting this feature

As only one packet per connection interval must be supported by a Bluetooth® LE connection, there is always a risk that the connection partner does not support this feature.

2 Usage

To enable the high throughput mode the corresponding bit in the `CfgFlags` has to be set by using the `CMD_SET_REQ` command.

2.1 Maximum packet size

During the connection setup the module outputs a `CMD_CHANNELOPEN_RSP` message on the UART. This message contains the maximum payload of a standard packet (Φ_{ST}). Keeping this value in mind, the maximum packet to be transmitted via the `CMD_DATA_REQ` in high throughput mode is calculated as:

$$\Phi_{HTM} = (\Phi_{ST} - 3 + 1) \times 4[\text{Bytes}] \quad (2)$$

In case of the largest maximum transmission unit (MTU), that is supported by the Proteus modules, the size of the standard packet Φ_{ST} is 243 (0xF3) Bytes. Therefore, the largest packet size Φ_{HTM} in high throughput mode calculates as 964 Bytes.

2.2 Bluetooth LE packet format

The standard Bluetooth® LE packet of a Proteus module has the following format

Bluetooth® LE packet	
AMBER header	Payload
1 Byte	Φ_{ST} Bytes

Table 2: Bluetooth® LE packet format of a standard packet

where:

AMBER header is **0x01** (`RF_HEADER_TYPE_DATA`), meaning that the following Bytes are payload.

To send bigger data packets, the data is fragmented to up to 4 single packets. These fragmented data packets contain an extended header of 3 Bytes length. The format of a fragmented packet is

Bluetooth® LE packet			
AMBER header	Sequence number	Fragment ID	Payload
1 Byte	1 Byte	1 Byte	$(\Phi_{ST} - 2)$ Bytes

Table 3: Bluetooth® LE packet format of a fragmented packet

where:

AMBER header is **0x04** (`RF_HEADER_TYPE_FRAGDATA`), guaranteeing that the fragmented packet can be distinguished from a standard packet with header **0x01** (`RF_HEADER_TYPE_DATA`).

Sequence number is a random number, that has to be the same for all fragments of a fragmented packet, but should differ for each packet.

Fragment ID is of the structure **0xAB** and will define the order of the fragments to be de-fragmented/combined again

A the first 4 bits define the current fragment number (starting with 1)

B the last 4 bits define the overall number of fragments

2.2.1 Example: Transmitting fragmented data

Let us assume that we have a fragment payload size of 5 Bytes, the random number has been chosen as 0x00 and we suppose to send data consisting of 12 Bytes 0xE1 - 0xEC. Then 3 fragments of the following structure have to be transmitted:

AMBER header	Sequence number	Fragment ID	Payload
0x04	0x00	0x13	0xE1 0xE2 0xE3 0xE4 0xE5

Table 4: Fragment 1

AMBER header	Sequence number	Fragment ID	Payload
0x04	0x00	0x23	0xE6 0xE7 0xE8 0xE9 0xEA

Table 5: Fragment 2

AMBER header	Sequence number	Fragment ID	Payload
0x04	0x00	0x33	0xEB 0xEC

Table 6: Fragment 3

When receiving fragmented data packets with header **0x04**, the fragments are combined and output by a CMD_DATA_IND message on the UART only if:

- all fragments have been received
- all fragments have the same overall number of fragments number (**B**, i.e. the last 4 bits of the **Fragment ID**)
- all fragments contain the same sequence number

In a case where at least one of this conditions is not satisfied the data will be discarded without further notice.

3 Throughput test

This chapter describes the throughput tests that have been performed. The following devices have been tested:

- Proteus-II in FW version 1.1.0
- Proteus-III in FW version 1.1.0
- Proteus-III SPI in FW version 1.2.0

3.1 Test conditions

To get the best throughput performance we choose the following settings of the Proteus module:

- The Proteus module operates in command mode.
- The UART/SPI must be set to maximum speed:
 - Proteus-II: The UART runs with baudrate 921600 Baud, 8n1, and uses the flow control pins *RTS* and *CTS*.
 - Proteus-III: The UART runs with baudrate 1000000 Baud, 8n1, and uses the flow control pins *RTS* and *CTS*.
 - Proteus-III SPI: The SPI runs with a datarate of 8 Mbit.
- The connection interval has been set to a fast value depending on the devices used (see chapter 3.3).
- Set the module to high throughput mode by setting the corresponding bit in the *CfgFlags*.
- The 2 Mbit mode PHY is used for fastest radio data transmission.



If data is transmitted from one Proteus module to another, both modules must be configured in the same manner.

3.2 Test procedure

The test procedure is as follows:

1. Setup a Bluetooth connection between the two Bluetooth® LE enabled devices. We call them here device A to device B.
2. Check if large data packets are supported, by reading the maximum transmission unit (MTU) from the *CMD_CHANNEL_OPEN_RSP* message during connection setup. The maximum supported data packets Φ_{ST} are:
 - a) Proteus to Proteus: $\Phi_{ST} = 243$ (0xF3) Bytes
 - b) Proteus to Android device: $\Phi_{ST} = 243$ (0xF3) Bytes
 - c) Proteus to iOS device: $\Phi_{ST} = 181$ (0xB5) Bytes

3. Switch the PHY to 2 Mbit using the CMD_PHYUPDATE_REQ command.
4. Iterate over:
 - a) Transmit a data packet of maximum size Φ_{HTM} Bytes using a CMD_DATA_REQ command. Φ_{HTM} calculates as:
 - i. Proteus to Proteus: $\Phi_{HTM} = (243 - 3 + 1) / 4 = 964$ Bytes
 - ii. Proteus to Android device: $\Phi_{HTM} = (243 - 3 + 1) / 4 = 964$ Bytes
 - iii. Proteus to iOS device: $\Phi_{HTM} = (181 - 3 + 1) / 4 = 716$ Bytes
 - b) Wait for the transmission success message (CMD_TXCOMPLETE_IND) that is returned on the UART as result of the previous transmission request.

3.3 Test results

The throughput tests have been performed in two different test setups.

3.3.1 Test setup 1: Via USB interface and PC

The Proteus modules are connected via FTDI-chip and USB cable to a PC. A PC tool triggers the repeated data transmission. In this case the USB latencies slow down the data transmission.

Device A	Device B	Connection interval [ms]	Throughput [kBytes/s]
Proteus-II	Proteus-II	8 - 8	24.7
Proteus-II	Proteus-II	8 - 30	16
Proteus-II	Proteus-II	20 - 75	6.3
Samsung Galaxy S8 (SM-G950F, Android 8.0)	Proteus-II	8 - 8	18.1
Samsung Galaxy S8 (SM-G950F, Android 8.0)	Proteus-II	8 - 30	11.28
Samsung Galaxy S8 (SM-G950F, Android 8.0)	Proteus-II	20 - 75	9.7
iPhone 7 (MN922 ZD/A, iOS 11.4)	Proteus-II	8 - 30	8.125
iPhone 7 (MN922 ZD/A, iOS 11.4)	Proteus-II	20 - 75	8.125

Table 7: Test results Proteus-II via USB

Device A	Device B	Connection interval [ms]	Throughput [kBytes/s]
Proteus-III	Proteus-III	8 - 8	21.3
Proteus-III	Proteus-III	8 - 30	15.9
Proteus-III	Proteus-III	20 - 75	6.3
Samsung Galaxy S8 (SM-G950F, Android 8.0)	Proteus-III	8 - 8	18.9
Samsung Galaxy S8 (SM-G950F, Android 8.0)	Proteus-III	8 - 30	8
Samsung Galaxy S8 (SM-G950F, Android 8.0)	Proteus-III	20 - 75	6.16
iPhone XS (iOS 12.2)	Proteus-III	8 - 30	8.7
iPhone XS (iOS 12.2)	Proteus-III	20 - 75	8.2

Table 8: Test results Proteus-III via USB

3.3.2 Test setup 2: Via micro controller

The Proteus modules' UARTs/SPIs are directly connected to a micro controller², that triggers the repeated data transmission.

Device A	Device B	Connection interval [ms]	Throughput [kBytes/s]
Proteus-II	Proteus-II	8 - 8	32.17
Proteus-II	Proteus-II	8 - 30	16.07
Proteus-II	Proteus-II	20 - 75	6.78
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-II	8 - 8	28.60
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-II	8 - 30	16.07
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-II	20 - 75	9.93
iPhone 7 (MN922 ZD/A, iOS 11.4)	Proteus-II	8 - 30	12.13
iPhone 7 (MN922 ZD/A, iOS 11.4)	Proteus-II	20 - 75	11.21

Table 9: Test results Proteus-II via micro controller

²In this test a STM32 on a NUCLEOL476RG has been used.

Device A	Device B	Connection interval [ms]	Throughput [kBytes/s]
Proteus-III	Proteus-III	8 - 8	42.9
Proteus-III	Proteus-III	8 - 30	16.43
Proteus-III	Proteus-III	20 - 75	6.75
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-III	8 - 8	28.69
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-III	8 - 30	16.07
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-III	20 - 75	6.30
iPhone XS (iOS 12.2)	Proteus-III	8 - 30	11.95
iPhone XS (iOS 12.2)	Proteus-III	20 - 75	11.95

Table 10: Test results Proteus-III via micro controller

Device A	Device B	Connection interval [ms]	Throughput [kBytes/s]
Proteus-III-SPI	Proteus-III-SPI	8 - 8	64.3
Proteus-III-SPI	Proteus-III-SPI	8 - 30	16.07
Proteus-III-SPI	Proteus-III-SPI	20 - 75	12.85
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-III-SPI	8 - 8	42.88
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-III-SPI	8 - 30	16.07
Samsung Galaxy S8 (Model SM-G950F, Android 8.0)	Proteus-III-SPI	20 - 75	6.42

Table 11: Test results Proteus-III SPI via micro controller

4 Important notes

The following conditions apply to all goods within the wireless connectivity product range of Würth Elektronik eiSos GmbH & Co. KG:

4.1 General customer responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact, it is up to the customer to evaluate, where appropriate to investigate and to decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not. Accordingly, the customer is cautioned to verify that the documentation is current before placing orders.

4.2 Customer responsibility related to specific, in particular safety-relevant applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. The same statement is valid for all software sourcecode and firmware parts contained in or used with or for products in the wireless connectivity and sensor product range of Würth Elektronik eiSos GmbH & Co. KG. In certain customer applications requiring a high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health, it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component.

4.3 Best care and attention

Any product-specific data sheets, manuals, application notes, PCN's, warnings and cautions must be strictly observed in the most recent versions and matching to the products firmware revisions. This documents can be downloaded from the product specific sections on the wireless connectivity homepage.

4.4 Customer support for product specifications

Some products within the product range may contain substances, which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case, the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

4.5 Product improvements

Due to constant product improvement, product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard, we inform about major changes. In case of further queries regarding the PCN, the field sales engineer, the internal sales person or the technical support team in charge should be contacted. The basic responsibility of the customer as per section 4.1 and 4.2 remains unaffected. All wireless connectivity module driver software "wireless connectivity SDK" and its source codes as well as all PC software tools are not subject to the Product Change Notification information process.

4.6 Product life cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this, we cannot ensure that all products within our product range will always be available. Therefore, it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

4.7 Property rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG. Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

4.8 General terms and conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

5 Legal notice

5.1 Exclusion of liability

Würth Elektronik eiSos GmbH & Co. KG considers the information in this document to be correct at the time of publication. However, Würth Elektronik eiSos GmbH & Co. KG reserves the right to modify the information such as technical specifications or functions of its products or discontinue the production of these products or the support of one of these products without any written announcement or notification to customers. The customer must make sure that the information used corresponds to the latest published information. Würth Elektronik eiSos GmbH & Co. KG does not assume any liability for the use of its products. Würth Elektronik eiSos GmbH & Co. KG does not grant licenses for its patent rights or for any other of its intellectual property rights or third-party rights.

Notwithstanding anything above, Würth Elektronik eiSos GmbH & Co. KG makes no representations and/or warranties of any kind for the provided information related to their accuracy, correctness, completeness, usage of the products and/or usability for customer applications. Information published by Würth Elektronik eiSos GmbH & Co. KG regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof.

5.2 Suitability in customer applications

The customer bears the responsibility for compliance of systems or units, in which Würth Elektronik eiSos GmbH & Co. KG products are integrated, with applicable legal regulations. Customer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of Würth Elektronik eiSos GmbH & Co. KG components in its applications, notwithstanding any applications-related information or support that may be provided by Würth Elektronik eiSos GmbH & Co. KG. Customer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences lessen the likelihood of failures that might cause harm and take appropriate remedial actions. The customer will fully indemnify Würth Elektronik eiSos GmbH & Co. KG and its representatives against any damages arising out of the use of any Würth Elektronik eiSos GmbH & Co. KG components in safety-critical applications.

5.3 Trademarks

AMBER wireless is a registered trademark of Würth Elektronik eiSos GmbH & Co. KG. All other trademarks, registered trademarks, and product names are the exclusive property of the respective owners.

5.4 Usage restriction

Würth Elektronik eiSos GmbH & Co. KG products have been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death,

unless the parties have executed an agreement specifically governing such use. Moreover, Würth Elektronik eiSos GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. Würth Elektronik eiSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component, which is used in electrical circuits that require high safety and reliability function or performance. By using Würth Elektronik eiSos GmbH & Co. KG products, the customer agrees to these terms and conditions.

6 License terms

This License Terms will take effect upon the purchase and usage of the Würth Elektronik eiSos GmbH & Co. KG wireless connectivity products. You hereby agree that this license terms is applicable to the product and the incorporated software, firmware and source codes (collectively, "Software") made available by Würth Elektronik eiSos in any form, including but not limited to binary, executable or source code form.

The software included in any Würth Elektronik eiSos wireless connectivity product is purchased to you on the condition that you accept the terms and conditions of this license terms. You agree to comply with all provisions under this license terms.

6.1 Limited license

Würth Elektronik eiSos hereby grants you a limited, non-exclusive, non-transferable and royalty-free license to use the software and under the conditions that will be set forth in this license terms. You are free to use the provided Software only in connection with one of the products from Würth Elektronik eiSos to the extent described in this license terms. You are entitled to change or alter the source code for the sole purpose of creating an application embedding the Würth Elektronik eiSos wireless connectivity product. The transfer of the source code to third parties is allowed to the sole extent that the source code is used by such third parties in connection with our product or another hardware provided by Würth Elektronik eiSos under strict adherence of this license terms. Würth Elektronik eiSos will not assume any liability for the usage of the incorporated software and the source code. You are not entitled to transfer the source code in any form to third parties without prior written consent of Würth Elektronik eiSos.

You are not allowed to reproduce, translate, reverse engineer, decompile, disassemble or create derivative works of the incorporated Software and the source code in whole or in part. No more extensive rights to use and exploit the products are granted to you.

6.2 Usage and obligations

The responsibility for the applicability and use of the Würth Elektronik eiSos wireless connectivity product with the incorporated Firmware in a particular customer design is always solely within the authority of the customer. Due to this fact, it is up to you to evaluate and investigate, where appropriate, and to decide whether the device with the specific product characteristics described in the product specification is valid and suitable for your respective application or not.

You are responsible for using the Würth Elektronik eiSos wireless connectivity product with the incorporated Firmware in compliance with all applicable product liability and product safety laws. You acknowledge to minimize the risk of loss and harm to individuals and bear the risk for failure leading to personal injury or death due to your usage of the product.

Würth Elektronik eiSos' products with the incorporated Firmware are not authorized for use in safety-critical applications, or where a failure of the product is reasonably expected to cause severe personal injury or death. Moreover, Würth Elektronik eiSos' products with the incorporated Firmware are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. You shall inform Würth Elektronik eiSos about the intent of such usage before design-in stage. In certain customer applications requiring a very high level of safety and in which the malfunction or failure of an electronic component could endanger human life or

health, you must ensure to have all necessary expertise in the safety and regulatory ramifications of your applications. You acknowledge and agree that you are solely responsible for all legal, regulatory and safety-related requirements concerning your products and any use of Würth Elektronik eiSos' products with the incorporated Firmware in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by Würth Elektronik eiSos. YOU SHALL INDEMNIFY WÜRTH ELEKTRONIK EISOS AGAINST ANY DAMAGES ARISING OUT OF THE USE OF WÜRTH ELEKTRONIK EISOS' PRODUCTS WITH THE INCORPORATED FIRMWARE IN SUCH SAFETY-CRITICAL APPLICATIONS.

6.3 Ownership

The incorporated Firmware created by Würth Elektronik eiSos is and will remain the exclusive property of Würth Elektronik eiSos.

6.4 Firmware update(s)

You have the opportunity to request the current and actual Firmware for a bought wireless connectivity Product within the time of warranty. However, Würth Elektronik eiSos has no obligation to update a modules firmware in their production facilities, but can offer this as a service on request. The upload of firmware updates falls within your responsibility, e.g. via ACC or another software for firmware updates. Firmware updates will not be communicated automatically. It is within your responsibility to check the current version of a firmware in the latest version of the product manual on our website. The revision table in the product manual provides all necessary information about firmware updates. There is no right to be provided with binary files, so called "Firmware images", those could be flashed through JTAG, SWD, Spi-Bi-Wire, SPI or similar interfaces.

6.5 Disclaimer of warranty

THE FIRMWARE IS PROVIDED "AS IS". YOU ACKNOWLEDGE THAT WÜRTH ELEKTRONIK EISOS MAKES NO REPRESENTATIONS AND WARRANTIES OF ANY KIND RELATED TO, BUT NOT LIMITED TO THE NON-INFRINGEMENT OF THIRD PARTIES' INTELLECTUAL PROPERTY RIGHTS OR THE MERCHANTABILITY OR FITNESS FOR YOUR INTENDED PURPOSE OR USAGE. WÜRTH ELEKTRONIK EISOS DOES NOT WARRANT OR REPRESENT THAT ANY LICENSE, EITHER EXPRESS OR IMPLIED, IS GRANTED UNDER ANY PATENT RIGHT, COPYRIGHT, MASK WORK RIGHT, OR OTHER INTELLECTUAL PROPERTY RIGHT RELATING TO ANY COMBINATION, MACHINE, OR PROCESS IN WHICH THE WÜRTH ELEKTRONIK EISOS' PRODUCT WITH THE INCORPORATED FIRMWARE IS USED. INFORMATION PUBLISHED BY WÜRTH ELEKTRONIK EISOS REGARDING THIRD-PARTY PRODUCTS OR SERVICES DOES NOT CONSTITUTE A LICENSE FROM WÜRTH ELEKTRONIK EISOS TO USE SUCH PRODUCTS OR SERVICES OR A WARRANTY OR ENDORSEMENT THEREOF.

6.6 Limitation of liability

Any liability not expressly provided by Würth Elektronik eiSos shall be disclaimed. You agree to hold us harmless from any third-party claims related to your usage of the Würth Elektronik eiSos' products with the incorporated Firmware, software and source code. Würth

Elektronik eiSos disclaims any liability for any alteration, development created by you or your customers as well as for any combination with other products.

6.7 Applicable law and jurisdiction

Applicable law to this license terms shall be the laws of the Federal Republic of Germany. Any dispute, claim or controversy arising out of or relating to this license terms shall be resolved and finally settled by the court competent for the location of Würth Elektronik eiSos' registered office.

6.8 Severability clause

If a provision of this license terms is or becomes invalid, unenforceable or null and void, this shall not affect the remaining provisions of the terms. The parties shall replace any such provisions with new valid provisions that most closely approximate the purpose of the terms.

6.9 Miscellaneous

Würth Elektronik eiSos reserves the right at any time to change this terms at its own discretion. It is your responsibility to check at Würth Elektronik eiSos homepage for any updates. Your continued usage of the products will be deemed as the acceptance of the change.

We recommend you to be updated about the status of new firmware and software, which is available on our website or in our data sheet and manual, and to implement new software in your device where appropriate.

By ordering a wireless connectivity product, you accept this license terms in all terms.

List of Figures

1	Data transmission with 1 packet per connection interval	4
2	Improved data transmission with up to 4 packets per connection interval . . .	5

List of Tables

1	Examples of Bluetooth® LE enabled devices supporting this feature	5
2	Bluetooth® LE packet format of a standard packet	6
3	Bluetooth® LE packet format of a fragmented packet	6
4	Fragment 1	7
5	Fragment 2	7
6	Fragment 3	7
7	Test results Proteus-II via USB	9
8	Test results Proteus-III via USB	10
9	Test results Proteus-II via micro controller	10
10	Test results Proteus-III via micro controller	11
11	Test results Proteus-III SPI via micro controller	11



more than you expect



**Internet
of Things**



**Monitoring
& Control**



**Automated Meter
Reading**

Contact:

Würth Elektronik eiSos GmbH & Co. KG
Division Wireless Connectivity & Sensors

Max-Eyth-Straße 1
74638 Waldenburg
Germany

Tel.: +49 651 99355-0
Fax.: +49 651 99355-69
www.we-online.com/wireless-connectivity

