

High Performance CMOS MEMS Oscillator for Automotive

Features

- Automotive AEC-Q100 Qualified
- Wide Frequency Range: 2.5 MHz to 170 MHz
- Very Low RMS Phase Jitter: <650 fs (typ.)
- High Stability: ± 20 ppm, ± 25 ppm, ± 50 ppm
- Wide Temperature Range:
 - Automotive Grade 1: -40°C to $+125^{\circ}\text{C}$
 - Automotive Grade 2: -40°C to $+105^{\circ}\text{C}$
 - Automotive Grade 3: -40°C to $+85^{\circ}\text{C}$
- Small Industry-Standard Footprints
 - 6-Lead 2.5 mm \times 2.0 mm VDFN
 - 6-Lead 3.2 mm \times 2.5 mm VDFN
 - 6-Lead 3.2 mm \times 5.0 mm VDFN
 - 6-Lead 7.0 mm \times 5.0 mm VDFN
- Excellent Shock and Vibration Immunity
 - Qualified to MIL-STD-883
- High Reliability
 - 20x Better MTF than Quartz Oscillators
- Supply Range of 2.25V to 3.63V
- Standby, Frequency Select, and Output Enable Functions
- Lead-Free and RoHS-Compliant

Applications

- Automotive Infotainment
- Automotive ADAS
- In-Vehicle Networking, CAN Bus, Ethernet

General Description


The DSA12x1 family of high performance oscillators utilizes the latest generation of silicon MEMS technology that reduces close-in noise and provides excellent jitter and stability over a wide range of supply voltages and temperatures. By eliminating the need for quartz or SAW technology, MEMS oscillators significantly enhance reliability and accelerate product development, while meeting stringent clock performance criteria for automotive applications.

The DSA12x1 family features a control function on pin 1 or pin 2 that permits either a standby feature (complete power down when STDBY is low), output enable (output is tri-stated with OE low), or a frequency select (choice of two frequencies selected by FS high/low). See the [Product Identification System](#) section for detailed information.


All oscillators are available in industry-standard packages, including the small 6-lead 2.5 mm \times 2.0 mm VDFN, and are “drop-in” replacements for standard 4-lead and 6-lead CMOS quartz crystal oscillators.

Package Types

DSA1201/1211/1221
6-Lead VDFN




DSA1231/1241/1251
6-Lead VDFN



DSA12X1

Functional Block Diagrams



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

Supply Voltage	–0.3V to +4.0V
Input Voltage	–0.3V to V_{DD} + 0.3V
ESD Protection (HBM)	4 kV
ESD Protection (MM)	400V
ESD Protection (CDM)	1.5 kV

† **Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS

Electrical Characteristics: $V_{DD} = 2.5V \pm 10\%$ or $3.3V \pm 10\%$; $T_A = -40^\circ\text{C}$ to $+125^\circ\text{C}$, unless noted.

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Supply Voltage	V_{DD}	2.25	—	3.63	V	Note 1
Supply Current	I_{DD}	—	27	—	mA	Output enabled, CMOS (no load), $f_{OUT} = 100$ MHz
		—	23	—		Output disabled (tri-state), $f_{OUT} = 100$ MHz
Standby Current	I_{STDBY}	—	2.5	5	μA	Input pin = \overline{STDBY} = Asserted ($V_{DD} = 3.3\text{V}$)
Frequency Stability	Δf	—	—	± 20	ppm	Includes frequency variations due to initial tolerance, temp., and power supply voltage
		—	—	± 25		
		—	—	± 50		
Aging	Δf	—	—	± 5	ppm	First year at 25°C
		—	—	± 1		Per year after first year
Startup Time	t_{SU}	—	5.5	6	ms	From 90% V_{DD} to valid clock output, $T = +25^\circ\text{C}$, Note 2
Input Logic Levels	V_{IH}	$0.75 \times V_{DD}$	—	—	V	Input logic high
	V_{IL}	—	—	$0.25 \times V_{DD}$		Input logic low
Output Disable Time	t_{DA}	—	—	25	ns	Note 3
Output Enable Time	t_{EN}	—	—	6	ms	\overline{STDBY}
		—	—	350	ns	OE
Enable Pull-Up Resistor	—	—	1.5	—	$\text{M}\Omega$	Pull-up resistor on pin 1, Note 4
Frequency	f_0	2.5	—	170	MHz	—
Output Logic Level High	V_{OH}	$0.8 \times V_{DD}$	—	—	V	$I = \pm 12 \text{ mA}$
Output Logic Level Low	V_{OL}	—	—	$0.2 \times V_{DD}$		
Output Transition Time, Rise 20% to 80%; $C_L = 15 \text{ pF}$	t_R	—	1.2	—	ns	—
Output Transition Time, Fall 20% to 80%; $C_L = 15 \text{ pF}$	t_F	—	1.1	—	ns	—

DSA12X1

ELECTRICAL CHARACTERISTICS (CONTINUED)

Electrical Characteristics: $V_{DD} = 2.5V \pm 10\%$ or $3.3V \pm 10\%$; $T_A = -40^\circ C$ to $+125^\circ C$, unless noted.

Parameter	Symbol	Min.	Typ.	Max.	Units	Conditions
Output Duty Cycle	SYM	45	—	55	%	—
Period Jitter, Peak-to-Peak	J_{PTP}	—	25	—	ps	$f_{OUT} = 100$ MHz
Cycle-to-Cycle Jitter, Peak	J_{CC}	—	22	—	ps	$f_{OUT} = 100$ MHz
Integrated Phase Noise (Random)	J_{PH}	—	0.65	—	ps _{RMS}	12 kHz to 20 MHz @ 100 MHz, $T_A = +105^\circ C$

Note 1: V_{DD} pin should be filtered with a 0.1 μF capacitor.

2: t_{SU} is the time to 100 ppm stable output frequency after V_{DD} is applied and outputs are enabled.

3: t_{DA} : See the [Output Waveform](#) and the [Test Circuit](#) sections for more information.

4: Output is enabled if pad is floated (not connected).

TEMPERATURE SPECIFICATIONS [Note 1](#)

Parameters	Symbol	Min.	Typ.	Max.	Units	Conditions
Temperature Ranges						
Maximum Junction Temperature	T_J	—	—	+150	°C	—
Storage Temperature Range	T_S	-55	—	+150	°C	—
Lead Temperature	—	—	—	+260	°C	Soldering, 40 seconds

Note 1: The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable junction temperature and the thermal resistance from junction to air (i.e., T_A , T_J , θ_{JA}). Exceeding the maximum allowable power dissipation will cause the device operating junction temperature to exceed the maximum $+150^\circ C$ rating. Sustained junction temperatures above $+150^\circ C$ can impact the device reliability.

2.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in [Table 2-1](#).

TABLE 2-1: DSA1201/1211/1221 PIN FUNCTION TABLE

Pin Number	DSA1201		DSA1211		DSA1221	
	Pin Name	Description	Pin Name	Description	Pin Name	Description
1	<u>STDBY</u>	Standby.	FS	Frequency select.	OE	Output enable.
2	NC	No connect.	NC	No connect.	NC	No connect.
3	GND	Power supply ground.	GND	Power supply ground.	GND	Power supply ground.
4	CLK	Clock output.	CLK	Clock output.	CLK	Clock output.
5	NC	No connect.	NC	No connect.	NC	No connect.
6	VDD	Power supply.	VDD	Power supply.	VDD	Power supply.

TABLE 2-2: DSA1231/1241/1251 PIN FUNCTION TABLE

Pin Number	DSA1231		DSA1241		DSA1251	
	Pin Name	Description	Pin Name	Description	Pin Name	Description
1	NC	No connect.	NC	No connect.	NC	No connect.
2	<u>STDBY</u>	Standby.	FS	Frequency select.	OE	Output enable.
3	GND	Power supply ground.	GND	Power supply ground.	GND	Power supply ground.
4	CLK	Clock output.	CLK	Clock output.	CLK	Clock output.
5	NC	No connect.	NC	No connect.	NC	No connect.

2.1 Standby

Complete power down when STDBY is low.

2.2 Frequency Select

Two frequencies may be chosen, selected by FS = High or Low. Please use the [ClockWorks](#) tool to customize frequencies.

2.3 Output Enable

Output buffers (only) are tri-stated when OE is low.

3.0 TERMINATION SCHEME




FIGURE 3-1: CMOS Termination.

4.0 OUTPUT WAVEFORM




FIGURE 4-1: CMOS Output Waveform.

TABLE 4-1: OUTPUT VOLTAGE SWING BY LOGIC TYPE

Output Logic Protocol	Typical Peak-to-Peak Output Swing
CMOS	V_{OH}, V_{OL}

5.0 TEST CIRCUIT




FIGURE 5-1: CMOS Test Circuit.

6.0 SOLDER REFLOW PROFILE




FIGURE 6-1: Solder Reflow Profile.

TABLE 6-1: SOLDER REFLOW

MSL 1 @ 260°C Refer to JSTD-020C	
Ramp-Up Rate (200°C to Peak Temp.)	3°C/sec. max.
Preheat Time 150°C to 200°C	60 to 180 sec.
Time Maintained above 217°C	60 to 150 sec.
Peak Temperature	255°C to 260°C
Time within 5°C of Actual Peak	20 to 40 sec.
Ramp-Down Rate	-6°C/sec. max.
Time 25°C to Peak Temperature	8 minutes max.

7.0 BOARD LAYOUT (RECOMMENDED)




FIGURE 7-1: DSA12x1 Recommended Board Layout.

8.0 PHASE NOISE




FIGURE 8-1: DSA12x1 Phase Noise at 25 MHz.





FIGURE 8-2: DSA12x1 Phase Noise at 125 MHz.

DSA12X1


9.0 PACKAGING INFORMATION

9.1 Package Marking Information

6-Lead VDFN*



Example



Legend: XX...X Product code or customer-specific information

Y Year code (last digit of calendar year)

YY Year code (last 2 digits of calendar year)

WW Week code (week of January 1 is week '01')

SSS Alphanumeric traceability code

(e3) Pb-free JEDEC® designator for Matte Tin (Sn)

* This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.


•, ▲, ▼ Pin one index is identified by a dot, delta up, or delta down (triangle mark).

Note: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information. Package may or may not include the corporate logo.

Underbar (_) and/or Overbar (‐) symbol may not be to scale.

6-Lead 2.5 mm x 2.0 mm VDFN (J7A) Package Outline and Recommended Land Pattern

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>




Microchip Technology Drawing C04-1005-J7A Rev E Sheet 1 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Dual Flatpack No-Leads (J7A) - 2.5x2.0 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Dimension Limits		MILLIMETERS		
		MIN	NOM	MAX
Number of Terminals	N		6	
Pitch	e		0.825 BSC	
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Overall Length	D		2.50 BSC	
Overall Width	E		2.00 BSC	
Terminal Width	b1	0.60	0.65	0.70
Terminal Width	b2	0.20	0.25	0.30
Terminal Length	L1	0.60	0.70	0.80
Terminal Length	L2	0.665	0.765	0.865

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated

3. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1005-J7A Rev E Sheet 2 of 2

6-Lead Very Thin Dual Flatpack No-Leads (J7A) - 2.5x2.0 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>

**RECOMMENDED LAND PATTERN**

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch		0.825 BSC		
Contact Pad Width (X4)	X1			0.65
Contact Pad Width (X2)	X2			0.25
Contact Pad Length (X6)	Y			0.85
Contact Pad Spacing	C		1.45	
Space Between Contacts (X4)	G1	0.38		
Space Between Contacts (X3)	G2	0.60		

Notes:




1. Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-3005-J7A Rev E

DSA12X1

6-Lead 3.2 mm × 2.5 mm VDFN (H5A) Package Outline and Recommended Land Pattern

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>




Microchip Technology Drawing C04-1007-H5A Rev C Sheet 1 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Plastic Dual Flatpack No-Lead (H5A) - 3.2x2.5 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Dimension Limits	Units	MILLIMETERS		
		MIN	NOM	MAX
Number of Terminals	N		6	
Pitch	e		1.05 BSC	
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Overall Length	D		3.20 BSC	
Overall Width	E		2.50 BSC	
Terminal Width	b1	0.85	0.90	0.95
Terminal Width	b2	0.45	0.50	0.55
Terminal Length	L	0.65	0.70	0.75
Terminal Pullback	L1		0.10 REF	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1007-H5A Rev C Sheet 2 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Plastic Dual Flatpack No-Lead (H5A) - 3.2x2.5 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E		1.05 BSC	
Contact Pad Spacing	C		1.60	
Contact Pad Width (X4)	X1			1.00
Contact Pad Width (X2)	X2			0.60
Contact Pad Length (X6)	Y			0.85
Space Between Contacts (X4)	G1	0.75		
Space Between Contacts (X3)	G2	0.25		
Pin 1 Index Chamfer (X4)	CH		0.25	

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing C04-3007-H5A Rev C

© 2024 Microchip Technology Inc.

6-Lead 3.2 mm x 5.0 mm VDFN (H7A) Package Outline and Recommended Land Pattern

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>




Microchip Technology Drawing C04-1009-H7A Rev B Sheet 1 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Plastic Dual Flat, No Lead Package (H7A) - 3.2x5.0 x0.9 Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Number of Terminals	N	6		
Pitch	e	1.27	BSC	
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Terminal Thickness	A3	0.203	REF	
Overall Length	D	5.00	BSC	
Overall Width	E	3.20	BSC	
Terminal Width	b	0.59	0.64	0.69
Terminal Length	L	0.90	1.00	1.10
Terminal 1 Index Chamfer	CH	0.25	REF	
Terminal-to-Terminal	K	1.20	REF	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.

2. Package is saw singulated

3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1009-H7A Rev B Sheet 2 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Plastic Dual Flat, No Lead Package (H7A) - 3.2x5.0 x0.9 Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

		Units	MILLIMETERS		
Dimension Limits			MIN	NOM	MAX
Contact Pitch	E		1.27	BSC	
Contact Pad Spacing	C		2.30		
Contact Pad Width (X6)	X			0.64	
Contact Pad Length (X6)	Y			1.10	
Contact Pad to Contact Pad (X4)	G		1.20	REF	

Notes:

- Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
- For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process


Microchip Technology Drawing C04-3009-H7A Rev B

© 2024 Microchip Technology Inc.

DSA12X1

6-Lead 7.0 mm × 5.0 mm VDFN (HPA) Package Outline and Recommended Land Pattern

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>




Microchip Technology Drawing C04-1227-HPA Rev B Sheet 1 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Dual Flatpack, No Lead Package (HPA) - 7x5 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



Units		MILLIMETERS		
Dimension	Limits	MIN	NOM	MAX
Number of Terminals	N		6	
Pitch	e		2.54 BSC	
Overall Height	A	0.80	0.85	0.90
Standoff	A1	0.00	0.02	0.05
Overall Length	D		7.00 BSC	
Overall Width	E		5.00 BSC	
Terminal Width	b	1.30	1.40	1.50
Terminal Length	L	1.00	1.10	1.20
Pullback	L1		0.10 REF	

Notes:

1. Pin 1 visual index feature may vary, but must be located within the hatched area.
2. Package is saw singulated
3. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.


REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-1227-HPA Rev B Sheet 2 of 2

© 2024 Microchip Technology Inc.

6-Lead Very Thin Dual Flatpack, No Lead Package (HPA) - 7x5 mm Body [VDFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at <http://www.microchip.com/packaging>



RECOMMENDED LAND PATTERN

Units		MILLIMETERS		
Dimension Limits		MIN	NOM	MAX
Contact Pitch	E		2.54 BSC	
Contact Pad Spacing	C		3.90	
Contact Pad Width (X6)	X1			1.55
Contact Pad Length (X6)	Y1			1.40

Notes:

1. Dimensioning and tolerancing per ASME Y14.5M
BSC: Basic Dimension. Theoretically exact value shown without tolerances.
2. For best soldering results, thermal vias, if used, should be filled or tented to avoid solder loss during reflow process

Microchip Technology Drawing C04-3227-HPA Rev B

© 2024 Microchip Technology Inc.

APPENDIX A: REVISION HISTORY

Revision A (July 2020)

- Initial release of DSA12x1 as Microchip data sheet DS20006385A.

Revision B (August 2024)

- Updated values and conditions for Output Logic Levels, Output Transition Times, Period Jitter, and Cycle-to-Cycle Jitter in the [Electrical Characteristics](#) table.

Revision C (August 2025)

- Updated package outline drawings with latest drawing versions.
- Removed all CDFN references throughout document and replaced with VDFN information as needed.
- Updated package marking drawing with DAP info.

DSA12X1

NOTES:

PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO.	X	X	X	X	X	X	-XXXXXXXX	X	XXX
Device	Control Pin	Output Format	Package	Temperature	Freq. Stability	Output Frequency	Media Type	Automotive Suffix	
Device:	DSA12:	High Performance CMOS MEMS Oscillator for Automotive							
Control Pin:	0	= Pin 1 <u>STDBY</u> with Pull-up							
	1	= Pin 1 Frequency Select with Pull-up							
	2	= Pin 1 OE with Pull-up							
	3	= Pin 2 <u>STDBY</u> with Pull-up							
	4	= Pin 2 Frequency Select with Pull-up							
	5	= Pin 2 OE with Pull-up							
Output Format:	1	= CMOS							
Package:	N	= 6-Lead 7.0 mm × 5.0 mm VDFN							
	B	= 6-Lead 3.2 mm × 5.0 mm VDFN							
	C	= 6-Lead 3.2 mm × 2.5 mm VDFN							
	D	= 6-Lead 2.5 mm × 2.0 mm VDFN							
Temperature:	A	= -40°C to +125°C (Automotive Grade 1)							
	L	= -40°C to +105°C (Automotive Grade 2)							
	I	= -40°C to +85°C (Automotive Grade 3)							
Frequency Stability:	1	= ±50 ppm							
	2	= ±25 ppm							
	3	= ±20 ppm							
Output Frequency:	xMxxxxxx	= <10 MHz							
	xxMxxxxx	= <100 MHz							
	xxxMxxxx	= >100 MHz							
	CCCCC	= with Frequency Select							
	PROG	= TimeFlash							
Media Type:	<blank>	= Bulk							
	T	= 1,000/Reel							
	B	= 3,000/Reel							
Automotive Suffix:	VXX	= Automotive suffix in which "XX" is assigned by Microchip. Default value is "AO" for standard automotive part							

Examples:

- a) DSA1201NI1-25M00000TVAO: Pin 1 STDBY with Pull-up, CMOS Output, 6-Lead 7.0 mm × 5.0 mm VDFN, -20°C to +85°C, ±50 ppm, 25 MHz Output Frequency, 1,000/Reel, Standard Automotive
- b) DSA1211CL3-C0013VAO: Pin 1 Frequency Select with Pull-up, CMOS Output, 6-Lead 3.2 mm × 2.5 mm VDFN, -40°C to +105°C, ±20 ppm, Frequency Select, 24 MHz & 25 MHz, Bulk, Standard Automotive
- c) DSA1221BI2-19M50000BVAO: Pin 1 OE with Pull-up, CMOS Output, 6-Lead 3.2 mm × 5.0 mm VDFN, -40°C to +85°C, ±25 ppm, 19.5 MHz Output Frequency, 3,000/Reel, Standard Automotive
- d) DSA1251DL3-55M82000TVAO: Pin 2 OE with Pull-up, CMOS Output, 6-Lead 2.5 mm × 2.0 mm VDFN, -40°C to +105°C, ±20 ppm, 55.82 MHz Output Frequency, 1,000/Reel, Standard Automotive
- e) DSA1231NI1-C0014BVAO: Pin 2 STDBY with Pull-up, CMOS Output, 7.0 mm × 5.0 mm VDFN, -40°C to +85°C, ±50 ppm, Frequency Select 100 MHz & 156.25 MHz, 3,000/Reel, Standard Automotive

Note 1: Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.

2: Please visit the [Microchip ClockWorks Configurator®](http://clockworks.microchip.com/timing) website to configure the part number for customized frequency select settings.
<http://clockworks.microchip.com/timing>

DSA12X1

NOTES:

Microchip Information

Trademarks

The "Microchip" name and logo, the "M" logo, and other names, logos, and brands are registered and unregistered trademarks of Microchip Technology Incorporated or its affiliates and/or subsidiaries in the United States and/or other countries ("Microchip Trademarks"). Information regarding Microchip Trademarks can be found at <https://www.microchip.com/en-us/about/legal-information/microchip-trademarks>.

ISBN: 979-8-3371-1686-0

Legal Notice

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at www.microchip.com/en-us/support/design-help/client-support-services.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.