







LOC	DIST	REVISIONS					
		P	LTN	DESCRIPTION	DATE	OWN	APVD
		G5		ADDED 2-2	16MAY2023	AB	SZ
		G6		ADDED 3-2170704-3	13AUG2024	AB	SZ
		G7		ADDED -57/-58/-62	09NOV2024	CZ	SZ
		G8		REVISED AS PER ECN-26-384842	28APR2026	SH	SZ



DETAIL A  
SCALE 8:1

2170704-2 AS SHOWN

- MATERIAL:  
 CAGE MATERIAL : 0.25 THICK NICKEL SILVER.  
 SPRING MATERIAL: COPPER ALLOY  
 HEAT SINK MATERIAL: ALUMINUM  
 CLIP MATERIAL: STAINLESS STEEL
- FINISH:  
 SPRING: NICKEL PLATING  
 HEAT SINK: BLACK ANODIZE/NICKEL PLATING
- DIMENSION APPLIES WITH MODULE INSTALLED IN THE CAGE TO TOP OF HEAT SINK.
- REFERENCE APPLICATION SPEC 114-32023 FOR RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMERS.
- MINIMUM PC BOARD THICKNESS : SINGLES SIDED: 1.57 MIN  
 DOUBLE SIDED: 2.20 MIN
- DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
- DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN
- MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.
- TOOLING NOT YET DONE
- MATERIAL 0.4 THICK NICKEL SILVER APPLIED FOR REAR CAGE COVER

26.7	2	WITHOUT	CUSTOMIZED	3-2170704-3
28.2	2	WITHOUT	CUSTOMIZED	2-2170704-2
13.2	2	WITHOUT	CUSTOMIZED	5-2170704-3
21.5	1	WITH	CUSTOMIZED	5-2170704-2
13.7	2	WITH	PCI	5-2170704-1
11.5	2	WITHOUT	CUSTOMIZED	2-2170704-1
12.6	2	WITHOUT	CUSTOMIZED	1-2170704-9
12.6	1	WITHOUT	CUSTOMIZED	1-2170704-7
12.6	2	WITHOUT	CUSTOMIZED	1-2170704-6
19.0	1	WITHOUT	CUSTOMIZED	1-2170704-5
19.0	0	WITHOUT	CUSTOMIZED	1-2170704-4
13.7	2	WITHOUT	CUSTOMIZED	1-2170704-3
13.7	2	WITHOUT	CUSTOMIZED	1-2170704-2
13.7	2	WITHOUT	PCI	1-2170704-1
19.0	2	WITHOUT	CUSTOMIZED	1-2170704-0
23.0	1	WITHOUT	NETWORKING	2170704-9
16.0	1	WITHOUT	SAN	2170704-8
13.7	1	WITHOUT	PCI	2170704-7
23.0	0	WITHOUT	NETWORKING	2170704-6
16.0	0	WITHOUT	SAN	2170704-5
13.7	0	WITHOUT	PCI	2170704-4
23.0	2	WITHOUT	NETWORKING	2170704-3
16.0	2	WITHOUT	SAN	2170704-2
13.7	2	WITHOUT	PCI	2170704-1
DIM A	#	INSULATING TAPE OPTION	APPLICATION	PART NUMBER

12.6	2	WITHOUT	CUSTOMIZED	1-2170704-9
16.0	2	WITHOUT	CUSTOMIZED	6-2170704-3
16.0	2	WITHOUT	CUSTOMIZED	6-2170704-2
17.2	0	WITH	CUSTOMIZED	5-2170704-8
17.2	2	WITH	CUSTOMIZED	5-2170704-7
DIM A	#	INSULATING TAPE OPTION	APPLICATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DWG: JASON YANG 23SEP2013  
 CHK: SEAN HAN 23SEP2013  
 APVD: SEAN HAN

**STE** TE Connectivity

NAME: CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK

PRODUCT SPEC: 108-19428  
 APPLICATION SPEC: 114-32023


SIZE: A1 CAGE CODE: 00779 DRAWING NO: 2170704  
 WEIGHT: -

MATERIAL: - FINISH: -


CUSTOMER DRAWING SCALE: 2:1 SHEET 1 OF 16 REV: G8

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	OWN	APVD		
-	-	SEE SHEET 1	-	-	-		


# HEAT SINK OPTIONS



PCI HEAT SINK  
SCALE 3:1




SAN HEAT SINK  
SCALE 3:1




NETWORKING HEAT SINK  
SCALE 3:1


# # OF REAR LEGS OPTIONS



2 REAR LEGS  
SCALE 5:1







1 REAR LEG  
SCALE 5:1



0 REAR LEG  
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN JASON YANG 23SEP2013	TE Connectivity
		CHK SEAN HAN 23SEP2013	
DIMENSIONS:		NAME	
mm	0 PLC ±0.25	CAGE ASSEMBLY, QSFP28, THRU BEZEL	
	1 PLC ±0.25	WITH EMI SPRING FINGER	
	2 PLC ±0.20	HEAT SINK	
	3 PLC ±0.100	PRODUCT SPEC 108-19428	RESTRICTED TO
	4 PLC ±	APPLICATION SPEC 114-32023	SIZE CAGE CODE DRAWING NO
	ANGLES	114-32023	A100779C=2170704
	FINISH	WEIGHT	SCALE 2:1 SHEET 2 OF 16 REV G8
MATERIAL		CUSTOMER DRAWING	

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		







1-2170704-2 ARE AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN JASON YANG 23SEP2013	TE Connectivity
		CHK SEAN HAN 23SEP2013	
DIMENSIONS:		NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CAGE ASSEMBLY, QSPF28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK	
0 PLC ±0.25	1 PLC ±0.25	PRODUCT SPEC	
2 PLC ±0.25	3 PLC ±0.25	108-19428	
4 PLC ±0.100	ANGLES ±°	APPLICATION SPEC	
FINISH		114-32023	
MATERIAL		WEIGHT	
CUSTOMER DRAWING		SIZE CAGE CODE DRAWING NO	RESTRICTED TO
		A100779C=2170704	
		SCALE 2:1	SHEET 3 OF 16 REV G8

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		

6-2170704-2 ARE AS SHOWN  
 UNMARKED DIMENSIONS SAME AS 2170704-2





THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN JASON YANG 23SEP2013	TE Connectivity	
		CHK SEAN HAN 23SEP2013		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME
mm	0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.20 3 PLC ±0.100 4 PLC ±	APVD		CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK
		PRODUCT SPEC		RESTRICTED TO
MATERIAL		APPLICATION SPEC		SIZE
		114-32023		A100779C=2170704
		WEIGHT		SCALE 2:1 SHEET 4 OF 16 REV G8
		CUSTOMER DRAWING		


LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		

6-2170704-3 ARE AS SHOWN  
 UNMARKED DIMENSIONS SAME AS 6-2170704-2

REAR CAGE COVER MATERIAL:  
 0.40 THICK NICKEL SILVER





SCALE 3:1





LASER POINTS FOR REF  
 (TWO SIDES)

SCALE 4:1





THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN: JASON YANG 23SEP2013	TE Connectivity
		CHK: SEAN HAN 23SEP2013	
DIMENSIONS:		NAME: CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC: 108-19428	RESTRICTED TO:
	0 PLC ±0.25	APPLICATION SPEC: 114-32023	SIZE: A1
	1 PLC ±0.25	WEIGHT: -	CAGE CODE: 100779
	2 PLC ±0.20	CUSTOMER DRAWING	DRAWING NO: 2170704
	3 PLC ±0.100	SCALE: 2:1	SHEET 5 OF 16
	4 PLC ±	REV: G8	
	ANGLES ±°		
	FINISH		


LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	OWN	APVD		
-	-	SEE SHEET 1	-	-	-		





1-2170704-3 AS SHOWN  
SCALE 4:1




1-2170704-3 ARE AS SHOWN  
SCALE 2:1




1-2170704-6 AS SHOWN  
SAME AS 1-2170704-3 EXCEPT MARKED DIMENSIONS  
SCALE 4:1




1-2170704-6 ARE AS SHOWN  
SCALE 2:1



1-2170704-7 AS SHOWN  
SAME AS 1-2170704-6 EXCEPT MARKED DIENSIONS





SCALE 4:1







1-2170704-7 AS SHOWN  
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JASON YANG 23SEP2013	TE Connectivity														
		CHK: SEAN HAN 23SEP2013															
DIMENSIONS:		NAME: CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC: 108-19428															
mm		APPLICATION SPEC: 114-32023															
<table border="1"> <tr><td>0 PLC</td><td>±0.25</td></tr> <tr><td>1 PLC</td><td>±0.25</td></tr> <tr><td>2 PLC</td><td>±0.25</td></tr> <tr><td>3 PLC</td><td>±0.100</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td>±</td></tr> </table>		0 PLC	±0.25	1 PLC	±0.25	2 PLC	±0.25	3 PLC	±0.100	4 PLC	±	ANGLES	±	FINISH	±	RESTRICTED TO: -	
0 PLC	±0.25																
1 PLC	±0.25																
2 PLC	±0.25																
3 PLC	±0.100																
4 PLC	±																
ANGLES	±																
FINISH	±																
MATERIAL: -		SIZE: A1	CAGE CODE: 100779														
		DRAWING NO: C=2170704	REV: G8														
		WEIGHT: -	SCALE: 2:1														
		CUSTOMER DRAWING	SHEET 6 OF 16														

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		





1-2170704-9 ARE AS SHOWN  
 SAME AS 1-2170704-6, EXCEPT HEATSINK FINS  
 SCALE 4:1



2-2170704-1 AS SHOWN  
 SAME AS 2170704-1 EXCEPT MARKED DIENSIOMS


THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN JASON YANG 23SEP2013	TE Connectivity
		CHK SEAN HAN 23SEP2013	
DIMENSIONS:		APVD	
mm	0 PLC ±0.25	PRODUCT SPEC	
	1 PLC ±0.25	108-19428	
	2 PLC ±0.20	APPLICATION SPEC	
	3 PLC ±0.100	114-32023	
	4 PLC ±"	WEIGHT	
	ANGLES FINISH	A100779C=2170704	
MATERIAL		CUSTOMER DRAWING	
		SCALE 2:1	SHEET 7 OF 16 REV G8

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		





INSULATING TAPE

5-2170704-1 WITH INSULATING TAPE  
SCALE 4:1



13.7 MAX

SCALE 4:1







11.42 REF


5-2170704-1 ARE AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 23SEP2013	TE Connectivity
		CHK: SEAN HAN 23SEP2013	
DIMENSIONS:		NAME: CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC: 108-19428	
mm		APPLICATION SPEC:	
0 PLC ±0.25		SIZE: 114-32023	
1 PLC ±0.25		CAGE CODE: A100779	
2 PLC ±0.20		DRAWING NO: C=2170704	
3 PLC ±0.100		RESTRICTED TO:	
4 PLC ±		SCALE: 2:1	
ANGLES ±°		SHEET: 8 OF 16	
FINISH		REV: G8	
MATERIAL:		CUSTOMER DRAWING	





LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	OWN	APVD		
-	-	SEE SHEET 1	-	-	-		




5-2170704-2 WITH INSULATING TAPE  
SCALE 4:1



5-2170704-2 ARE AS SHOWN





5-2170704-3 ARE AS SHOWN





THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JASON YANG 23SEP2013	TE Connectivity
		CHK: SEAN HAN 23SEP2013	
DIMENSIONS:		NAME: CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC: 108-19428	
mm		APPLICATION SPEC:	
0 PLC ±0.25		SIZE: 114-32023	
1 PLC ±0.25		CAGE CODE: A100779	
2 PLC ±0.20		DRAWING NO: C=2170704	
3 PLC ±0.100		RESTRICTED TO:	
4 PLC ±		CUSTOMER DRAWING	
ANGLES: °		SCALE: 2:1	
FINISH:		SHEET 9 OF 16	
		REV: G8	

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD		
-	-	SEE SHEET 1	-	-	-		





SCALE 4:1






2-2170704-2 ARE AS SHOWN  $\triangle$   
 SAME AS 2170704-3 EXCEPT MARKED DIMENSIONS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 23SEP2013	TE Connectivity
		CHK: SEAN HAN 23SEP2013	
DIMENSIONS:		APVD:	NAME:
mm	0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.25 3 PLC ±0.100 4 PLC ±	PRODUCT SPEC: 108-19428	CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK
TOLERANCES UNLESS OTHERWISE SPECIFIED: FINISH:		APPLICATION SPEC: 114-32023	RESTRICTED TO:
MATERIAL:		WEIGHT:	SIZE: A1
		CUSTOMER DRAWING	CAGE CODE: 00779 DRAWING NO: C=2170704
		SCALE: 2:1	SHEET 10 OF 16 REV: G8

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		



3-2170704-3  
SCALE 5:2





3-2170704-3 AS SHOWN  
 SAME AS 2170704-3 EXCEPT HS  
 SCALE 4:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN JASON YANG 23SEP2013	TE Connectivity
		CHK SEAN HAN 23SEP2013	
DIMENSIONS:		APVD	NAME
mm	0 PLC ±0.25	PRODUCT SPEC	CAGE ASSEMBLY, QSFP28, THRU BEZEL
	1 PLC ±0.25	108-19428	WITH EMI SPRING FINGER
	2 PLC ±0.20	APPLICATION SPEC	HEAT SINK
	3 PLC ±0.100	114-32023	SIZE CAGE CODE DRAWING NO
	4 PLC ±	WEIGHT	A100779C=2170704
	ANGLES ±	CUSTOMER DRAWING	RESTRICTED TO
MATERIAL	FINISH	SCALE 2:1	SHEET 11 OF 16 REV G8

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		



5-2170704-7 AS SHOWN



SCALE 5:2



SCALE 4:1





INSULATING TAPE

THIS PRINT IS  
**PRELIMINARY**  
 UNQUALIFIED PRODUCT  
 CONTACT PRODUCT ENGINEERING  
 BEFORE USING THIS PRINT




THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN: JASON YANG 23SEP2013	TE Connectivity
		CHK: SEAN HAN 23SEP2013	
DIMENSIONS:		APVD:	NAME:
mm	0 PLC ±0.25	PRODUCT SPEC:	CAGE ASSEMBLY, QSFP28, THRU BEZEL
	1 PLC ±0.25	108-19428	WITH EMI SPRING FINGER
	2 PLC ±0.20	APPLICATION SPEC:	HEAT SINK
	3 PLC ±0.100	SIZE: CAGE CODE   DRAWING NO:	A100779C=2170704
	4 PLC ±	RESTRICTED TO:	
	ANGLES ° ±	WEIGHT:	
	FINISH:	CUSTOMER DRAWING	SCALE 2:1 SHEET 12 OF 16 REV G8

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		

5-2170704-8 AS SHOWN







SCALE 5:2



THIS PRINT IS  
**PRELIMINARY**  
 UNQUALIFIED PRODUCT  
 CONTACT PRODUCT ENGINEERING  
 BEFORE USING THIS PRINT


THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN: JASON YANG 23SEP2013	TE Connectivity
		CHK: SEAN HAN 23SEP2013	
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD:	NAME:
mm	0 PLC ±0.25	PRODUCT SPEC:	CAGE ASSEMBLY, QSFP28, THRU BEZEL
	1 PLC ±0.25	APPLICATION SPEC:	WITH EMI SPRING FINGER
	2 PLC ±0.20	SIZE:	HEAT SINK
	3 PLC ±0.100	CAGE CODE:	A100779
	4 PLC ±	DRAWING NO:	C=2170704
	ANGLES ±	WEIGHT:	SCALE 2:1 SHEET 13 OF 16 REV G8
MATERIAL:	FINISH:	CUSTOMER DRAWING	

LOC		DIST		REVISIONS			
P	LTN	DESCRIPTION	DATE	DMN	APVD		
-	-	SEE SHEET 1	-	-	-		




THIS DRAWING IS A CONTROLLED DOCUMENT.		DMN JASON YANG 23SEP2013	TE Connectivity
		CHK SEAN HAN 23SEP2013	
DIMENSIONS:		NAME	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CAGE ASSEMBLY, QSPF28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK	
0 PLC	±0.25	PRODUCT SPEC	108-19428
1 PLC	±0.25	APPLICATION SPEC	114-32023
2 PLC	±0.20	SIZE	A100779
3 PLC	±0.100	CAGE CODE	C=2170704
4 PLC	±	DRAWING NO	2170704
ANGLES	±	RESTRICTED TO	
FINISH	±	SCALE	2:1
MATERIAL		SHEET	14 OF 16
		REV	G8
CUSTOMER DRAWING			


LOC	DIST	REV	DATE	BY	APPV
-	-	1	23SEP2013	JASON YANG	
-	-	2	23SEP2013	SEAN HAN	




RECOMMENDED PCB LAYOUT  
SINGLE TYPE OF 2 REAR HOLES OF LEGS  
PCB TOLERANCE: ±0.05  
SCALE 6:1



RECOMMENDED PCB LAYOUT  
SINGLE TYPE OF 1 REAR HOLES OF LEGS  
PCB TOLERANCE: ±0.05  
SCALE 6:1



RECOMMENDED PCB LAYOUT  
SINGLE TYPE OF 0 REAR HOLES OF LEGS  
PCB TOLERANCE: ±0.05  
SCALE 6:1




DETAIL B  
SCALE 8:1


HATCHED AREA DENOTES  
COMPONENT AND TRACE KEEP-OUT  
(EXCEPT CHASSIS GROUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JASON YANG 23SEP2013	TE Connectivity
DIMENSIONS: mm		CHK: SEAN HAN 23SEP2013	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD:	NAME: CAGE ASSEMBLY, QSPF28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK
0 PLC ±0.25	1 PLC ±0.25	PRODUCT SPEC: 108-19428	SIZE: A1
2 PLC ±0.20	3 PLC ±0.100	APPLICATION SPEC: 114-32023	CAGE CODE: 2170704
4 PLC ±0.100	ANGLES ±°	WEIGHT: -	RESTRICTED TO: -
MATERIAL: -	FINISH: -	CUSTOMER DRAWING	SCALE: 2:1 SHEET 15 OF 16 REV: G8


LOC	DIST	REV	DATE	BY	APPV
-	-	1	SEE SHEET 1	-	-




RECOMMENDED PCB LAYOUT  
BELLY TO BELLY TYPE OF 2 REAR HOLES OF LEGS  
PCB TOLERANCE: ±0.05  
SCALE 6:1



RECOMMENDED PCB LAYOUT  
BELLY TO BELLY TYPE OF 1 REAR HOLES OF LEGS  
PCB TOLERANCE: ±0.05  
SCALE 6:1



RECOMMENDED PCB LAYOUT  
BELLY TO BELLY TYPE OF 0 REAR HOLES OF LEGS  
PCB TOLERANCE: ±0.05  
SCALE 6:1



DETAIL C  
SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: JASON YANG 23SEP2013	 TE Connectivity
DIMENSIONS: mm		CHK: SEAN HAN 23SEP2013	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD:	NAME: CAGE ASSEMBLY, QSFP28, THRU BEZEL WITH EMI SPRING FINGER HEAT SINK
0 PLC	±0.25	PRODUCT SPEC:	108-19428
1 PLC	±0.25	APPLICATION SPEC:	114-32023
2 PLC	±0.20	SIZE:	A100779
3 PLC	±0.100	CAGE CODE:	C=2170704
4 PLC	±	WEIGHT:	SCALE 2:1 SHEET 16 OF 16 REV G8
ANGLES	±	CUSTOMER DRAWING	