

Datasheet



2.4GHz Miniature Screw Terminal Mount Monopole Antenna

Part No:
GW.26.0111.HT

Description

2.4GHz Miniature Screw Mount Monopole Antenna High Temperature

Features:

- 2.4GHz Wi-Fi® Bluetooth® Operational
- SMA(M) Connector
- IP Rating: IP65
- Height 30.3mm Diameter 7.9mm
- ROHS & REACH Compliant

1. Introduction	2
2. Specification	3
3. Antenna Characteristics	4
4. Radiation Patterns	10
5. Mechanical Drawing	4
6. Packaging	5

Changelog
17

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Ireland & USA
ISO 9001:2015
Certified



Taiwan
ISO 9001:2015
Certified



1. Introduction



The **GW.26** 2.4GHz Monopole SMA(M) terminal mount antenna is ideal for 2.4GHz wireless applications such as Bluetooth® and Wireless LAN.

Many module manufacturers specify peak gain limits for any antennas that are to be connected to that module. Those peak gain limits are based on free-space conditions. In practice, the peak gain of an antenna tested in free-space can degrade by at least 1 or 2dBi when put inside a device. So ideally you should go for a slightly higher peak gain antenna than mentioned on the module specification to compensate for this effect, giving you better performance.

Upon testing of any of our antennas with your device and a selection of appropriate layout, integration technique, or cable, Taoglas can make sure any of our antennas' peak gain will be below the peak gain limits. Taoglas can then issue a specification and/or report for the selected antenna in your device that will clearly show it complying with the peak gain limits, so you can be assured you are meeting regulatory requirements for that module.

For example, a module manufacturer may state that the antenna must have less than 2dBi peak gain, but you don't need to select an embedded antenna that has a peak gain of less than 2dBi in free-space. This will give you a less optimized solution. It is better to go for a slightly higher free-space peak gain of 3dBi or more if available. Once that antenna gets integrated into your device, performance will degrade below this 2dBi peak gain due to the effects of GND plane, surrounding components, and device housing. If you want to be absolutely sure, contact Taoglas and we will test. Choosing a Taoglas antenna with a higher peak gain than what is specified by the module manufacturer and enlisting our help will ensure you are getting the best performance possible without exceeding the peak gain limits.

Connector mount is fully customizable. It has a fully IP65 rated waterproof robust housing, ensuring high reliability.


2. Specification

Wi-Fi Electrical								
Band	Frequency (MHz)	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Polarization	Radiation Pattern	Power consumption
Wi-Fi - 2.4 GHz	2400-2500	48.7	-3.12	2.24	50 Ω	Vertical	Omni directional	10W

Mechanical	
Dimensions	30mm x Ø7.9mm
Weight	4g
Material	TPEE
Connector	SMA(M)

Environmental	
Operating Temperature	-40°C ~ +85°C
Storage Temperature	-40°C ~ +85°C
IP Rating	IP65


3. Mechanical Drawing




	Name	Material	Finish	QTY
①	GW.26 Housing High Temperature	TPEE	Black	1
②	SMA(M) ST	Brass	Ni Plated	1

4. Packaging


1pcs GW.26.011.HT per PE Bag
 Bag Dimensions – 74 x 42 mm
 Weight – 4.5g




100pcs GW.26.011.HT per Large PE Bag
 Bag Dimensions – 280 x 180 mm
 Weight – 450g



1500pcs GW.26.011.HT per carton
 Carton Dimensions – 360 x 310 x 160 mm
 Weight – 6.75Kg




Pallet Dimensions 1200 x 1000 x 1480 mm
 72 Cartons per pallet
 12 Cartons per layer
 6 Layers




5. Antenna Characteristics

5.1 Test Setup




Tested on 150x90mm Ground Plane


5.2 Return Loss




5.3 VSWR




5.4 Efficiency



5.5 Average Gain





5.6 Peak Gain





6. Radiation Patterns

6.1 Test Setup





Tested on 150x90mm Ground Plane



6.2 Patterns at 2400 MHz





6.3 Patterns at 2420 MHz





6.4 Patterns at 2440 MHz





6.5 Patterns at 2460 MHz



6.6 Patterns at 2480 MHz



6.7 Patterns at 2500 MHz



Changelog for the datasheet

SPE-11-8-021 – GW.26.0111.HT

Revision: I (Current Version)

Date:	2025-11-17
Notes:	Updated weight figures in packaging section of the datasheet.
Author:	Conor McGrath

Previous Revisions

Revision: H

Date:	2016-05-18
Notes:	Amended Peak Gain
Author:	Aine Doyle

Revision: C

Date:	2011-05-08
Notes:	
Author:	Unknown

Revision: G

Date:	2015-08-24
Notes:	Added Note on Gain
Author:	Aine Doyle

Revision: B

Date:	2011-07-20
Notes:	
Author:	Unknown

Revision: F

Date:	2014-03-12
Notes:	Amended Bandwidth to 100MHz
Author:	Aine Doyle

Revision: A (First Release)

Date:	2011-07-14
Notes:	
Author:	Unknown

Revision: E

Date:	2013-09-16
Notes:	Amended table heading o Page 2 - general formatting
Author:	Aine Doyle

Revision: D

Date:	2012-03-26
Notes:	
Author:	Unknown



TAOGLAS.[®]

www.taoglas.com

