



TAOGLAS®



Datasheet

Accura Series

Part No:
TS.15.0111

Description

Passive GPS/GLONASS/Galileo/BeiDou Antenna

Features:

High Performance Passive GPS Direct Mount Antenna
Robust IP67 Waterproof Enclosure
Dims: Ø27.25mm * 60mm
Connector: SMA Male
RoHS & Reach Compliant

1.	Introduction	3
2.	Specification	4
3.	Antenna Characteristics	6
4.	Radiation Patterns	9
5.	Mechanical Drawing	13
6.	Installation Guide	14
7.	Packaging	15
	Changelog	17

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.



1. Introduction



The **TS.15.0111 Accura Series** from Taoglas is a small, lightweight, high-performance GNSS direct SMA(M) mount passive antenna. Covering GPS L1, Galileo E1, GLONASS G1 and BeiDou B1 bands, it is also engineered to cover the L-Band used in modern GNSS correctional services. The direct mount enclosure is built to withstand the harshest environments, making it ideal for applications in transportation, navigation, connected robotics and UAV's, and remote asset tracking.

Some key features for the TS.15 include:

- **IP67 water resistance:** Withstands rain, dust, and even temporary submersion.
- **Waterproof O-ring:** Keeps water out, even in the most challenging conditions.
- **Robust external enclosure:** Protects the antenna from shock, vibration, and impact.
- **Secure mounting:** Unique indented SMA(M) connector ensure a solid, reliable connection.

Whether you're tracking vehicles, autonomous robotics or UAV's, navigating remote areas, or connecting your enterprise assets, the TS.15 delivers reliable GPS performance you can count on. For an active version of the product, look at the **TS.16.0111** on www.taoglas.com.

Contact your local Taoglas customer support team to learn more about how this versatile antenna can meet your specific needs.

2. Specification

GNSS Frequency Bands					
GPS	L1 1575.42 MHz	L2 1227.6 MHz	L5 1176.45 MHz		
	■	□	□		
GLONASS	G1 1602 MHz	G2 1248 MHz	G3 1207 MHz		
	■	□	□		
Galileo	E1 1575.24 MHz	E5a 1176.45 MHz	E5b 1201.5 MHz	E6 1278.75 MHz	
	■	□	□	□	
BeiDou	B1C 1575.42 MHz	B1I 1561 MHz	B2a 1176.45 MHz	B2b 1207.14 MHz	B3 1268.52 MHz
	■	■	□	□	□
L-Band	L-Band 1542 MHz				
	■				
QZSS (Regional)	L1 1575.42 MHz	L2C 1227.6 MHz	L5 1176.45 MHz	L6 1278.75e6	
	■	□	□	□	
IRNSS (Regional)	L5 1176.45 MHz				
	□				
SBAS	L1/E1/B1 1575.42 MHz	L5/B2a/E5a 1176.45 MHz	G1 1602 MHz	G2 1248 MHz	G3 1207 MHz
	■	□	■	□	□



GNSS Bands and Constellations


GNSS Electrical			
Frequency (MHz)	1561	1575.42	1603
VSWR (max.)	2:1	2:1	2:1
Passive Antenna Efficiency (%)	52.35	56.13	48.58
Passive Antenna Gain at Zenith (dBi)	1.19	2.29	1.4
Axial Ratio (dB)	0.49	0.77	0.94
Group Delay Mean (ns)	-4.8	-3.02	46.73
Polarization		RHCP	
Impedance		50 Ω	

Mechanical	
Dimensions	60 x 27.25 mm
Weight	17g
Material	PC+ASA
Connector	SMA Male Connector


Environmental	
Operation Temperature	-40°C - +85°C
Storage Temperature	-40°C - +85°C
Waterproof	IP67

3. Antenna Characteristics


3.1 Return Loss




3.2 VSWR




3.3 Efficiency




3.4 Average Gain



3.5 Peak Gain





3.6 Axial Ratio




4. Radiation Patterns

4.1 Test Setup



TS.15 Tested in Free Space




TS.15 Tested on 9x15cm
Ground Plane




TS.15 Tested on 15x9cm
Ground Plane


4.2 TS.15.0111 Patterns at 1561 MHz




XZ Plane




YZ Plane




XY Plane




4.3 TS.15.0111 Patterns at 1575 MHz for Gtotal




XZ Plane




YZ Plane




XY Plane




4.4 TS.15.0111 Patterns at 1602 MHz




XZ Plane





YZ Plane



XY Plane




5. Mechanical Drawing



ITEM NO.	DESCRIPTION	QTY.
2	BOTTOM AND CONNECTOR	1
3	RUBBER GASKET	1
4	term mount helix housig REV 3	1

6. Installation Guide



Hand-tighten only. The bottom rubber gasket must fully seat to ensure a watertight seal.

The TS.15 and TS.16 do not require a ground plane; they can be mounted to a bulkhead-mount SMA with a cable, or on a board-edge SMA at a right angle to a PCB. It should not be placed directly in the middle of a large (>15cm) ground plane, as this could degrade the axial ratio performance.

7. Packaging


1 pc TS.15.0111 per small pe bag



50 pcs TS.15.0111 per large pe bag



300 pcs TS.15.0111 per carton
Carton dimensions: 370x370x300mm



Changelog for the datasheet

SPE-24-8-022 – TS.15.0111

Revision: A (Original First Release)	
Date:	2024-01-31
Notes:	Initial Release
Author:	Gary West

Previous Revisions



www.taoglas.com

