

Distance-settable Photoelectric Sensor TOF Laser Sensor E3AS-F Series

Achieving “innovations in distance” for reflective-type photoelectric sensors
Optimal sensing distance (50 to 1,500 mm) for use on conveyor lines



- Wide sensing distance of 50 to 1,500 mm *1, enabling use on any conveyor line width
- TOF-type sensors for used with any type of conveyed workpiece
- Compact-sized body can be mounted anywhere (Metal case type (SUS316L), Plastic case type)
- Teaching method allows anyone to set optimal threshold values
- Manufactured using OMRON's proprietary laser sealing method (IP67/IP69K/IP67G *2)
- Antifouling coatings reduce the cleaning frequency on the sensing surface.
- IO-Link reduces the time required for startups and changeovers

*1. The sensing distance of the E3AS-F1500 series.

*2. Only for sensor units.

*** Coming soon**
Pre-wired models and
M8/M12 Pre-wired Connector models.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Refer to *Safety Precautions* on page 8.

Ordering Information

Sensors [Refer to *Dimensions* on page 10.]

Metal case type

Infrared light

Connection method	Sensing distance (white paper)	Output	Model		
		IO-Link baud rate	NPN output	PNP output	PNP output
			---	COM2 (38.4 kbps)	COM3 (230.4 kbps)
M8 Connector	50 mm to 1,500 mm		E3AS-F1500IMN M3	E3AS-F1500IMD M3	E3AS-F1500IMT M3
	50 mm to 1,000 mm		E3AS-F1000IMN M3	E3AS-F1000IMD M3	E3AS-F1000IMT M3

Plastic case type

Connection method	Sensing distance (white paper)	Output	Model		
		IO-Link baud rate	NPN output	PNP output	PNP output
			---	COM2 (38.4 kbps)	COM3 (230.4 kbps)
M8 Connector	50 mm to 1,500 mm		E3AS-F1500IPN M3	E3AS-F1500IPD M3	E3AS-F1500IPT M3
M8 Connector	50 mm to 1,000 mm		E3AS-F1000IPN M3	E3AS-F1000IPD M3	E3AS-F1000IPT M3

E3AS-F Series

Accessories (Sold Separately)

Sensor I/O Connectors (Sockets on One Cable End)

(Models for Connectors / Pre-wired Connectors)

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Round Water-resistant Connectors XS3F-M8 series

Appearance	Cable specification	Cable diameter (mm)	Cable connection direction	Cable length (m)	Sensor I/O Connector model number
M8 Connector Straight type  Right-angle type 	PVC cable	5 dia.	Straight	2	XS3F-M8PVC4S2M
				5	XS3F-M8PVC4S5M
			Right-angle	2	XS3F-M8PVC4A2M
				5	XS3F-M8PVC4A5M

Note: 1. The XS3W (Socket and Plug on Cable Ends) is also available. Refer to *XS3W-M8/XS3F-M8 Series Datasheet* (Cat. No. G140).

2. The connectors will not rotate after they are connected.

3. The cable is fixed at an angle of 180° from the sensor emitter/receiver surface.

Mounting Brackets [Refer to *Dimensions* on page 10.]

A Mounting Bracket is not enclosed with the Sensor. Order a Mounting Bracket separately if required.

Appearance	Model (material)	Applicable Sensor E3AS-F series
L-shaped Mounting Bracket 	E39-L211 (SUS304)	M8 Connector
Horizontal Protective Cover Bracket 	E39-L212 (SUS304)	
Robust Mounting Bracket 	E39-L214 (SUS304)	

Note: Use an L-shaped Sensor I/O Connector. Straight types cannot be installed.

Ratings and Specifications

Model		Sensing method		TOF (Time of flight)	
		Type		Metal case (□: M), Plastic case (□: P)	
		NPN output		E3AS-F1500□N	
		PNP output/ COM2		E3AS-F1500□D	
Item		PNP output/ COM3		E3AS-F1500□T	
Sensing distance				50 mm to the set distance (White paper or black paper 200 × 200 mm)	
Setting range				100 to 1,500 mm (White paper 200 × 200 mm) 100 to 1,000 mm (Black paper 200 × 200 mm)	
Spot diameter (reference value)				95 mm dia. (at distance of 1,000 mm)	
Differential travel				15% max. of set distance (Set distance 200 mm min.)	
Reflectivity characteristic (black/white error)				10% max. of set distance (Set distance 200 mm min.)	
Light source (wavelength)				Infrared laser (940 nm) Class1 (IEC/EN60825-1:2014)	
Power supply voltage				10 to 30 VDC (including 10% ripple (p-p)), Class2	
Current consumption				30 mA max.	
Input/output		Control output		Load power supply voltage: 30 VDC max., Class2, Load current: 100 mA max. (Residual voltage: Load current of less than 10 mA: 1 V max. Load current of 10 to 100 mA: 2 V max.) Open-collector output (NPN/PNP output depending on model)	
		NPN		OUTPUT 1: NO (Normally open), OUTPUT 2: NC (Normally closed)	
		PNP/COM2 PNP/COM3		OUTPUT 1: NO (Normally open)/COM□, OUTPUT 2: NC (Normally closed)	
Protection circuits				Power supply reverse polarity protection, Output short-circuit protection, and Output reverse polarity protection	
Response time				Operate or reset: 150 ms max.	
Distance setting				Teaching method/IO-Link communications	
Ambient illumination (Receiver side)				Incandescent lamp: 3,000 lx max., Sunlight: 10,000 lx max.	
Ambient temperature range				Operating: -20 to 55°C, Storage: -40 to 70°C (with no icing or condensation)	
Ambient humidity range				Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)	
Insulation resistance				20 MΩ min. at 500 VDC	
Dielectric strength				1,000 VAC, 50/60 Hz for 1 min	
Vibration resistance				10 to 55 Hz with a 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions	
Shock resistance				500 m/s ² for 3 times each in X, Y, and Z directions	
Degree of protection				IP67 (IEC60529) and IP67G *1 (JIS C 0920 Annex 1), IP69K (ISO20653)	
Indicators				Operation indicator (orange), stability/communication indicator (green *2) *2. IO-Link mode: blinking	
Connection method				M8 Connector	
Weight (packed state/Sensor only)				Metal case type: Approx. 75 g/approx. 30 g Plastic case type: Approx. 60 g/approx. 15 g	
Materials		Case		Metal case type: Main unit/mounting part/connector part Stainless steel (SUS316L) Plastic case type: Main unit Polybutylene terephthalate (PBT) /polycarbonate (PC), Mounting part/connector part Nickel-plated brass	
		Lens		Methacrylate resin (PMMA)	
		Display		Metal case type: Polyamide 11 (PA11) Plastic case type: Polyethersulfone (PES)	
Main IO-Link functions				Operation mode switching between NO and NC, execution of teaching (2-point teaching, teaching without workpiece), setup of the threshold, timer function of the control output and timer time selecting, monitor output (Detection level, Incident light level), Restore Factory Settings, Key Lock (Unlock, Lock, Lock (No Button))	
IO-Link Communication specifications		IO-Link specification		Ver. 1.1	
		Baud rate		COM2 (38.4 kbps), COM3 (230.4 kbps)	
		Data length		PD size: 4 bytes, OD size: 1 byte (M-sequence type: TYPE_2_V)	
		Minimum cycle time		COM2: 3.5 ms, COM3: 1.2 ms	
Accessories				Instruction manual, compliance sheet, index list (attached for IO-Link type only) and FDA certification label, Note: Mounting Brackets must be ordered separately.	

*1. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.


E3AS-F Series

Engineering Data (Reference Value)


Operating Range

E3AS-F1500□

Z directions




Y directions




E3AS-F1000□

Z directions




Y directions



Spot Diameter vs. Sensing Distance


E3AS-F1500□

E3AS-F1000□




Close-range Characteristics

E3AS-F1500□




E3AS-F1000□




Differential distance for each sensing object Vs. Distance

E3AS-F1500□




E3AS-F1000□




Sensing Object Angle Characteristics

E3AS-F1500□

Vertical




Horizontal




E3AS-F1000□

Vertical




Horizontal



Sensing Distance vs. Sensing Object Material


E3AS-F1500□

(Set Distance of 1,500 mm using White Paper)



E3AS-F1000□

(Set Distance of 1,000 mm using White Paper)



I/O Circuit Diagrams/ Timing Charts

NPN Output

Model	Timing chart	Output circuit
E3AS-F1500□□N□ E3AS-F1000□□N□	Stability&Communication indicator (green) Operation indicator (orange) Control output 1 Control output 2 *	Connector Pin Arrangement M8 Connector

* The initial value of control output 2 is reverse of control output 1.

PNP Output

Model	Output circuit	
	Standard I/O mode (SIO mode) *1	IO-Link Communication mode (COM mode) *2
E3AS-F1500□□D□ E3AS-F1500□□T□ E3AS-F1000□□D□ E3AS-F1000□□T□	Connector Pin Arrangement M8 Connector	IO-Link Master Unit Connector Pin Arrangement M8 Connector

*1. Standard I/O mode is used as PNP ON/OFF output.

*2. IO-Link Communication mode is used for communications with the IO-Link Master. C/Q performs IO-Link communications. Sensor output DO performs ON/OFF output.

Timing charts	
Output mode	Timing chart
Standard I/O mode (SIO mode)	Stability&Communication indicator (green) Operation indicator (orange) Control output 1 *2 Control output 2 *1, *2
IO-Link Communication mode (COM mode)	Stability&Communication indicator (green) Flashing (1 second cycle) Operation indicator (orange) Communication output Control output 2 *1, *2

*1. The initial value of control output 2 is reverse of control output 1.

*2. The timer function of the control output can be set up by the IO-Link communications. (It is able to select ON delay, OFF delay, or one-shot function and select a timer time of 1 to 9,999 ms (T).)

ON delay		OFF delay		One Shot	
Sensing object	Present/Not present	Sensing object	Present/Not present	Sensing object	Present/Not present
NO	ON 1 / OFF 0	NO	ON 1 / OFF 0	NO	ON 1 / OFF 0
NC	ON 1 / OFF 0	NC	ON 1 / OFF 0	NC	ON 1 / OFF 0

Please contact your OMRON sales representative regarding the IO-Link setup file (IODD file).


Note: Shown above are the factory settings. Refer to the index list for the default settings at time of shipment from factory.

PNP/COM output logic can be reversed by IO-Link communication.

The operation indicator (orange) lights up when control output 1 is ON or communication output is 1.

Nomenclature

E3AS-F1500□□
E3AS-F1000□□



Note: The indicators work differently depending on sensor status.

Safety Precautions

Be sure to read the precautions for all models in the website at: <http://www.ia.omron.com/>.

Warning Indications

 WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
 CAUTION	Caution level Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

	General prohibition Indicates the instructions of unspecified prohibited action
	Caution, explosion Indicates the possibility of explosion under specific conditions
	Laser Caution Indicates information related to laser safety

 **WARNING**

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purpose.



 **CAUTION**

Never use the product with an AC power supply. Otherwise, explosion may result.



To safely use laser products

WARNING

Do not expose your eyes to the laser beam either directly or indirectly (i.e., after reflection from a mirror or shiny surface). The laser beam has a high power density and exposure may result in loss of sight.



Laser safety measures for laser equipment are stipulated in Japan and other countries. For usage in Japan and for export to other countries combined with other products, follow the instructions described below categorized in three cases respectively.

1. Usage in Japan

The JIS C6802:2014 standard stipulates the safety precautions that users must take according to the class of the laser product. This product is classified into Class 1 defined by this standard.

2. Usage in U.S.

When this product is installed in a device and exported to the U.S., it is subjected to the U.S. FDA (Food and Drug Administration) laser regulations. This product is classified into Class 1 by the IEC 60825-1:2007 standard according to the provisions of Laser Notice No. 50 of the FDA standard. This product is already reported to CDRH (Center for Devices and Radiological Health).

Accession Number: 1920014-000

Because the product is small, we can not attach an FDA certification label on the main body, so we enclose it in the packing box. When exporting a device equipped with the product to the U.S., attach an FDA certification label near the sensor mounting of customer equipment.

This laser product complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007
OMRON Corporation
Shikokuji Horikawa, Shimo-ku,
Kyoto 600-8530 JAPAN
Place of manufacture:
Shanghai Factory, OMRON Corp.
Manufactured in

FDA certification label

3. Usage in China

This product is classified into Class 1 by the IEC60825-1:2007 standard.

4. Usage in a country other than U.S. and China.

This product is classified into Class 1 by the IEC60825-1:2014 standard.

Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- (1) Do not reverse the power supply connection or connect to an AC current.
- (2) Do not short the load.
- (3) Be sure that before making supply the supply voltage is less than the maximum rated supply voltage (30 VDC).
- (4) Do not use the product in environments subject to flammable or explosive gases.
- (5) Do not use the product under a chemical or an oil environment without prior evaluation.
- (6) Do not attempt to modify the product.

Precautions for Correct Use

- (1) Do not hit the product using a hammer for installation.
- (2) The product must be installed with the specified torque or less. For M8 connector, the proper tightening torque is from 0.3 to 0.4 N·m.
- (3) Do not use the product in any atmosphere or environment that exceeds the ratings.
- (4) Output pulses may occur when the power supply is turned OFF. We recommend that you turn OFF the power supply to the load or load line first.
- (5) Use an extension cable less than 100 m long for Standard I/O mode and less than 20 m for IO-Link Communication mode.
- (6) Do not pull on the cable with excessive strength.
- (7) Please wait for at least 500 ms after turning on the product's power until it is available for use.
- (8) Though this is type IP67, do not use in the water, rain or outdoors.
- (9) If the Sensor wiring is placed in the same conduits or ducts as high-voltage or high-power lines, inductive noise may cause malfunction or damage. Wire the cables separately or use a shielded cable.
- (10) Do not use the product in locations subject to direct sunlight.
- (11) Do not use the product where humidity is high and dew condensation may occur.
- (12) Do not use the product where corrosive gases may exist.
- (13) If high-pressure washing water and so on hits the teach button, it might lead to malfunctioning. So, consider use of the key lock function.
- (14) Do not use the product at a location subject to shock or vibration.
- (15) To use a commercially available switching regulator, FG (frame ground) must be grounded.
- (16) Do not use organic solvents (e.g. paint thinner and alcohol) for cleaning. Otherwise optical properties and protective structure may deteriorate.
- (17) Be sure to check the influence caused by surrounding environments such as background objects and LED lighting before using the product.
- (18)  Please dispose in accordance with applicable regulations.



E3AS-F Series

Dimensions

(Unit: mm)


Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.

Sensors

Connector Models

E3AS-F1500□ M3


E3AS-F1000□ M3




Accessories (Sold Separately)

Mounting Brackets

E39-L211



Photoelectric Sensor Accessory
are installed
(Example of E3AS-F1500□)




Material: Stainless steel (SUS304)


* Accessories

2-M3-L12 Cross Recessed Pan Head Screws (Attached to SW+JIS W)

E39-L212




Photoelectric Sensor Accessory
are installed
(Example of E3AS-F1500□)




Material: Stainless steel (SUS304)

* Accessories
2-M3-L12 Cross Recessed Pan Head Screws (Attached to SW+JIS W)

E39-L214



Photoelectric Sensor Accessory
are installed
(Example of E3AS-F1500□)



Material: Stainless steel (SUS304)

* Accessories
2-M3-L12 Cross Recessed Pan Head Screws (Attached to SW+JIS W)

[illegible]

Distance-settable Photoelectric Sensor E3AS-L Series

Reflective sensor with a triangular method detects low-reflective workpieces more accurately

- Equipped with OMRON's proprietary light emitting element for stable detection of low-reflective workpieces
- Teaching method allows anyone to set optimal threshold values
- Manufactured using OMRON's proprietary laser sealing method (IP67/IP69K/IP67G *)
- IO-Link reduces the time required for startups and changeovers.

* Only for sensor units.



Refer to *Safety Precautions* on page 19.



ECOLAB®

IO-Link




*** Coming soon**
Pre-wired models and
M8/M12 Pre-wired Connector models.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors [Refer to *Dimensions* on page 20.]

 Red light

Connection method	Sensing distance (white paper)	Output	Model		
		IO-Link baud rate	NPN output	PNP output	PNP output
			---	COM2 (38.4 kbps)	COM3 (230.4 kbps)
M8 Connector			E3AS-L200MN M3	E3AS-L200MD M3	E3AS-L200MT M3
			E3AS-L80MN M3	E3AS-L80MD M3	E3AS-L80MT M3

E3AS-L Series

Accessories (Sold Separately)

Sensor I/O Connectors (Sockets on One Cable End)

(Models for Connectors / Pre-wired Connectors)

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Round Water-resistant Connectors XS3F-M8 series

Appearance	Cable specification	Cable diameter (mm)	No. of cable cores (Poles)	Cable connection direction	Cable length (m)	Sensor I/O Connector model number
M8 Connector	PVC cable	5 dia.	4	Straight	2	XS3F-M8PVC4S2M
Straight type					5	XS3F-M8PVC4S5M
				Right-angle	2	XS3F-M8PVC4A2M
					5	XS3F-M8PVC4A5M

Note: 1. The XS3W (Socket and Plug on Cable Ends) is also available. Refer to *XS3W-M8/XS3F-M8 Series Datasheet* (Cat. No. G140).

2. The connectors will not rotate after they are connected.

3. The cable is fixed at an angle of 180° from the sensor emitter/receiver surface.

Mounting Brackets [Refer to *Dimensions* on page 20.]

A Mounting Bracket is not enclosed with the Sensor. Order a Mounting Bracket separately if required.

Appearance	Model (material)	Applicable Sensor E3AS-L series
L-shaped Mounting Bracket 	E39-L211 (SUS304)	M8 Connector
Horizontal Protective Cover Bracket 	E39-L212 (SUS304)	
Robust Mounting Bracket 	E39-L214 (SUS304)	

Note: Use an L-shaped Sensor I/O Connector. Straight types cannot be installed.

Ratings and Specifications

Sensing method		Distance-settable	
Item	Model	E3AS-L200MN	E3AS-L80MN
	NPN output	E3AS-L200MD	E3AS-L80MD
	PNP output/ COM2	E3AS-L200MT	E3AS-L80MT
Sensing distance		10 mm to the set distance (White paper or black paper 100 × 100 mm)	
Setting range		40 to 200 mm (White paper or black paper 100 × 100 mm)	20 to 80 mm (White paper or black paper 100 × 100 mm)
Spot diameter (reference value)		25 × 25 mm at distance of 200 mm	4 mm dia. (at distance of 80 mm)
Differential travel		10% max. of set distance	White paper: 2% max. of set distance Black paper: 5% max. of set distance
Reflectivity characteristic (black/white error)		10% max. of set distance	5% max. of set distance
Light source (wavelength)		Red LED (624 nm)	Red LED (650 nm)
Power supply voltage		10 to 30 VDC (including 10% ripple (p-p)), Class2	
Current consumption		35 mA max.	
Input/output	Control output		Load power supply voltage: 30 VDC max., Class2, Load current: 100 mA max. (Residual voltage: Load current of less than 10 mA: 1 V max. Load current of 10 to 100 mA: 2 V max.) Open-collector output (NPN/PNP output depending on model)
	NPN	OUTPUT 1: NO (Normally open), OUTPUT 2: NC (Normally closed)	
	PNP/COM2 PNP/COM3	OUTPUT 1: NO (Normally open)/COM□, OUTPUT 2: NC (Normally closed)	
Protection circuits		Power supply reverse polarity protection, Output short-circuit protection, and Output reverse polarity protection	
Response time		Operate or reset: 1 ms max.	
Distance setting		Teaching method/IO-Link communications	
Ambient illumination (Receiver side)		Incandescent lamp: 3,000 lx max., Sunlight: 10,000 lx max.	
Ambient temperature range		Operating: -25 to 55°C, Storage: -40 to 70°C (with no icing or condensation)	
Ambient humidity range		Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)	
Insulation resistance		20 MΩ min. at 500 VDC	
Dielectric strength		1,000 VAC, 50/60 Hz for 1 min	
Vibration resistance		10 to 55 Hz with a 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions	
Shock resistance		500 m/s² for 3 times each in X, Y, and Z directions	
Degree of protection		IP67 (IEC60529) and IP67G *1 (JIS C 0920 Annex 1), IP69K (ISO20653)	
Indicators		Operation indicator (orange), Stability & Communication indicator (green *2) *2. IO-Link Communication mode: blinking	
Connection method		M8 Connector	
Weight (packed state/Sensor only)		Approx. 75 g/approx. 30 g	
Materials	Case	Stainless steel (SUS316L)	
	Lens	Methacrylate resin (PMMA)	
	Display	Polyamide 11 (PA11)	
Main IO-Link functions		Operation mode switching between NO and NC, execution of teaching (2-point teaching, teaching without workpiece), setup of the threshold, timer function of the control output and timer time selecting, Restore Factory Settings, Key Lock (Unlock, Lock, Lock (No Button))	
IO-Link Communication specifications	IO-Link specification	Ver. 1.1	
	Baud rate	COM2 (38.4 kbps), COM3 (230.4 kbps)	
	Data length	PD size: 1 byte, OD size: 1 byte (M-sequence type: TYPE_2_1)	
	Minimum cycle time	COM2: 3.5 ms, COM3: 1.2 ms	
Accessories		Instruction manual, compliance sheet and index list (attached for IO-Link type only), Note: Mounting Brackets must be ordered separately.	


*1. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).
The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

E3AS-L Series


Engineering Data (Reference Value)

Operating Range

E3AS-L200




E3AS-L80




Spot Diameter vs. Sensing Distance

E3AS-L200




E3AS-L80




Close-range Characteristics

E3AS-L200




E3AS-L80




Differential distance for each sensing object Vs. Distance

E3AS-L200




E3AS-L80




Sensing Object Angle Characteristics

E3AS-L200

Vertical




Horizontal




E3AS-L80

Vertical




Horizontal



Sensing Distance vs. Sensing Object Material


E3AS-L200

(Set Distance of 200 mm using White Paper)



E3AS-L80

(Set Distance of 80 mm using White Paper)



E3AS-L Series

I/O Circuit Diagrams/ Timing Charts

NPN Output

Model	Timing chart	Output circuit
E3AS-L□N	Stability&Communication indicator (green) *1 Operation indicator (orange) Control output 1 Control output 2 *2	Connector Pin Arrangement M8 Connector

- *1. Turns off when there is insufficient margin for incident light. In that case, place the workpiece closer to ensure sufficient receiving light intensity.
*2. The initial value of control output 2 is reverse of control output 1.

PNP Output

Model	Output circuit	
	Standard I/O mode (SIO mode) *1	IO-Link Communication mode (COM mode) *2
E3AS-L□D E3AS-L□T	Connector Pin Arrangement M8 Connector	Connector Pin Arrangement M8 Connector


- *1. Standard I/O mode is used as PNP ON/OFF output.
*2. IO-Link Communication mode is used for communications with the IO-Link Master. C/Q performs IO-Link communications. Sensor output DO performs ON/OFF output.

Output mode	Timing charts	
	Standard I/O mode (SIO mode)	IO-Link Communication mode (COM mode)
Standard I/O mode (SIO mode)	Stability&Communication indicator (green) *1 Operation indicator (orange) Control output 1 *3 Control output 2 *2	*1. Turns off when there is insufficient margin for incident light. In that case, place the workpiece closer to ensure sufficient receiving light intensity. *2. The initial value of control output 2 is reverse of control output 1. *3. The timer function of the control output 2 can be set up by the IO-Link communications. (It is able to select ON delay, OFF delay, or one-shot function and select a timer time of 1 to 9,999 ms (T).)
IO-Link Communication mode (COM mode)	Stability&Communication indicator (green) (Flashing (1 second cycle)) Operation indicator (orange) Communication output Control output 2 *2	ON delay OFF delay One Shot

Note: Shown above are the factory settings. Refer to the index list for the default settings at time of shipment from factory.
PNP/COM output logic can be reversed by IO-Link communication.
The operation indicator (orange) lights up when control output 1 is ON or communication output is 1.

Nomenclature

E3AS-L200
E3AS-L80



Note: The indicators work differently depending on sensor status.

Safety Precautions

Be sure to read the precautions for all models in the website at: <http://www.ia.omron.com/>.

Warning Indications

 WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
 CAUTION	Caution level Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

	General prohibition Indicates the instructions of unspecified prohibited action
	Caution, fire Indicates the possibility of fires under specific conditions
	General Caution Indicates unspecified general alert
	Caution, explosion Indicates the possibility of explosion under specific conditions

WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purpose.



Do not use the product with voltage in excess of the rated voltage.
Excess voltage may result in malfunction or fire.



CAUTION

Its component may be damaged and/or degree of protection may be degraded.
Please do not apply high pressure water intensively at one place during cleaning.



Never use the product with an AC power supply. Otherwise, explosion may result.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- (1) Do not reverse the power supply connection or connect to an AC current.
- (2) Do not short the load.
- (3) Be sure that before making supply the supply voltage is less than the maximum rated supply voltage (30 VDC).
- (4) Do not use the product in environments subject to flammable or explosive gases.
- (5) Do not use the product under a chemical or an oil environment without prior evaluation.
- (6) Do not attempt to modify the product.

Precautions for Correct Use

- (1) Do not hit the product using a hammer for installation.
- (2) The product must be installed with the specified torque or less. For M8 connector, the proper tightening torque is from 0.3 to 0.4 N·m.
- (3) Do not use the product in any atmosphere or environment that exceeds the ratings.
- (4) Output pulses may occur when the power supply is turned OFF. We recommend that you turn OFF the power supply to the load or load line first.
- (5) Use an extension cable less than 100 m long for Standard I/O mode and less than 20 m for IO-Link Communication mode.
- (6) Do not pull on the cable with excessive strength.
- (7) Please wait for at least 100 ms after turning on the product's power until it is available for use.
- (8) Though this is type IP67, do not use in the water, rain or outdoors.
- (9) If the Sensor wiring is placed in the same conduits or ducts as high-voltage or high-power lines, inductive noise may cause malfunction or damage. Wire the cables separately or use a shielded cable.
- (10) Do not use the product in locations subject to direct sunlight.
- (11) Do not use the product where humidity is high and dew condensation may occur.
- (12) Do not use the product where corrosive gases may exist.
- (13) If high-pressure washing water and so on hits the teach button, it might lead to malfunctioning. So, consider use of the key lock function.
- (14) Do not use the product at a location subject to shock or vibration.
- (15) To use a commercially available switching regulator, FG (frame ground) must be grounded.
- (16) Do not use organic solvents (e.g. paint thinner and alcohol) for cleaning. Otherwise optical properties and protective structure may deteriorate.
- (17) Be sure to check the influence caused by surrounding environments such as background objects and LED lighting before using the product.
- (18)  Please dispose in accordance with applicable regulations.


E3AS-L Series

Dimensions

(Unit: mm)
Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.

Sensors


Connector Models
E3AS-L200□ M3
E3AS-L80□ M3




Accessories (Sold Separately)

Mounting Brackets

E39-L211




Photoelectric Sensor
Accessory are installed
(Example of E3AS-L200□)






Material: Stainless steel (SUS304)
* Accessories
2-M3-L12 Cross Recessed Pan Head Screws (Attached to SW+JIS W)

E39-L212



Photoelectric Sensor
Accessory are installed
(Example of E3AS-L200□)




Material: Stainless steel (SUS304)




* Accessories

2-M3-L12 Cross Recessed Pan Head Screws (Attached to SW+JIS W)

E39-L214



Photoelectric Sensor
Accessory are installed
(Example of E3AS-L200□)



Material: Stainless steel (SUS304)

* Accessories

2-M3-L12 Cross Recessed Pan Head Screws (Attached to SW+JIS W)

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <http://www.omron.com/global/> or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

• Ecolab and its logo are registered trademarks of Ecolab USA Inc.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company
Kyoto, JAPAN

Contact: www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200
Hoffman Estates, IL 60169 U.S.A.
Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2),
Alexandra Technopark,
Singapore 119967
Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

© OMRON Corporation 2019 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.

CSM_1_1_0919
Cat. No. E588-E1-01

0919 (0919)