

PI6CG33A06
6-Output PCIe 5.0/6.0/7.0 Clock Generator With On-chip Termination

Description

The PI6CG33A06 is a 6-output very low jitter clock generator. It takes a reference input to generate 25MHz and 100MHz outputs. The on-chip termination can save 24 external resistors and make layout easier. Individual OE pin for each output provides easier power management. It uses Diodes' proprietary design to achieve very low jitter that meets PCIe® 5.0/6.0/7.0 clock requirements.


Features

- Supports Intel's CK440Q Spec.
- 3.3V Supply Voltage
- 25MHz Crystal or an Input from a XO / TCXO / OCXO for Meeting Customer Specific PPM Requirements
- 6 Differential Clock Output Pairs @ 1.4V Differential into PCI Express* (PCIe*) Compliant Test Load
 - 3 Dedicated 100MHz Outputs
 - 1 Dedicated 25MHz Outputs
 - 2 Selectable Outputs Capable of Driving 25M or 100MHz
- 85Ω Differential Drivers
- Programmable SSC on the 100MHz
- SMBus Programmable Configurations with Multiple SMBus Addresses
- One Tri-level Addresses Selection
- PCIe Compatible OE# Control on 3 Pins, and 3 Wire Shift/ Load Control on All Outputs
- PCIe 7.0 Common Clock (RMS) Jitter <30fs
- Packaging (Pb-free & Green):
 - 40-Pin, 5mm × 5mm VQFN (ZLF)
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please [contact us](https://www.diodes.com/quality/product-definitions/) or your local Diodes representative.


Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Block Diagram



Pin Configuration



Pin Description

Pin Number	Pin Name	Type		Description
1	VDDA25M	Power		Analog power supply for 25M outputs.
2	NC			Not Connected
3	VDDPT	Power		Power supply for platform time circuit and digital.
4	NC			Not Connected
5	SDATA	Input/ Output	Open Drain	Open drain bi-directional SMBus data pin.
6	SCLK	Input, PDT	LVTTL	SMBus slave clock input.
7	SMB_ ADR0_tri	Input	LVTTL	Tri-level LVTTL input to select SMBus address. This pin has internal pull up and pull down resistors. Refer to tri-level input threshold table.
8	VDDXTAL	Power		Power supply for crystal and clock input.
9	XIN_CLKIN	Input, PDT		Crystal input/Single-ended input.
10	XOUT	Output		Output of internal crystal oscillator. This pin should be left floating if CLK_ IN function is being used.
11	GNDXTAL	GND		Ground for crystal
12	NVGND	GND		Ground

PI6CG33A06

Pin Number	Pin Name	Type		Description
13	SSC_EN_tri	Input	LVTTL	Tri-level input to enable or disable spread spectrum. Refer to tri-level input threshold table. Default: 0 = SSC off, MID = -0.3% max, and HIGH = -0.5% max. It has internal pull down resistor." After setting Byte 46 = 33 (hex) and Byte 47 = A7 (hex) for PCIe 7.0 SRIS test 0 = SSC off, MID = -0.15% max, and HIGH = -0.3% max. It has internal pull down resistor."
14	PWRGD/ PWRDN#	Input	LVTTL	Input to power up or power down the device. It has internal pull up resistor.
15	VDDA100M	Power		Analog power supply for 100M outputs.
16	100M3#	Output	HCSL	±0.7V differential 100MHz clock complement output.
17	100M3	Output	HCSL	±0.7V differential 100MHz clock true output.
18	OE3#	Input, PDT	LVTTL	Active low input for enabling 100M3. 1 = disable output, 0 = enable output. It has internal pull down resistor.
19	VDD100M	Power		Power supply for 100M outputs.
20	NC			Not Connected
21	VDD100M	Power		Power supply for 100M outputs.
22	OE1#	Input, PDT	LVTTL	Active low input for enabling 100M1. 1 = disable output, 0 = enable output. It has internal pull down resistor.
23	100M1#	Output	HCSL	±0.7V differential 100MHz clock complement output.
24	100M1	Output	HCSL	±0.7V differential 100MHz clock true output.
25	100M0#	Output	HCSL	±0.7V differential 100MHz clock complement output.
26	100M0	Output	HCSL	±0.7V differential 100MHz clock true output.
27	OE0#	Input, PDT	LVTTL	Active low input for enabling 100M0. 1 = disable output, 0 = enable output. It has internal pull down resistor.
28	VDDMXCK	Power		Power supply for MXCK outputs.
29	MXCK5#	Output	HCSL	±0.7V differential multiplexable clock complement output.
30	MXCK5	Output	HCSL	±0.7V differential multiplexable clock true output.
31	MXCK4#	Output	HCSL	±0.7V differential multiplexable clock complement output.
32	MXCK4	Output	HCSL	±0.7V differential multiplexable clock true output.
33	VDDMXCK	Power		Power supply for MXCK outputs.
34	SHFT_LD#	Input, PDT	LVTTL	Input to control shifting and loading of the Side-Band Interface to the Output Enable Control Register. The pin has internal pull down resistor.
35	SBI_OUT	Output	LVTTL	Side Band Interface data output.
36	SBI_CLK	Input, PDT	LVTTL	Side Band Interface clock input for shifting/loading the SBI interface. It has internal pull down resistor.
37	SBI_IN	Input, PDT	LVTTL	Side Band Interface data input. It has internal pull down resistor.
38	25M2#	Output	HCSL	±0.7V differential 25MHz clock complement output.

PI6CG33A06

Pin Number	Pin Name	Type		Description
39	25M2	Output	HCSL	$\pm 0.7V$ differential 25MHz clock true output.
40	25MPG	Input, PDT	LVTTL	Input to assert power good for the 25M2 output pair before PWRGD is asserted. It has internal pull down resistor.
C1	EPAD	GND		Connect EPAD to ground

Power Down Tolerant (PDT)

The pins with PDT type may be driven by external signals when the device is in a power down or reset condition. The device must reset and power up properly if these pins are driven to any valid voltage prior to the assertion of VDD or PWRGD#.

Table 1. Power Management Table for 100M[3,1,0] Outputs

PWRGD/PWRDN#	OEx# Pin	SMBus OE Bit	SBI Mask Bit	SBI Output Control Register	100M[3,1,0]
0	X	X	X	X	Disabled
1	1	X	X	X	Disabled
	1	0	X	X	Disabled
	1	1	0	0	Disabled
	0	1	X	1	Running
	0	1	1	X	Running

Table 2. Power Management Table for 25M and MXCK[5,4] Outputs

PWRGD/PWRDN#	SMBus OE Bit	SBI Mask Bit	SBI Output Control Register	25M MXCK[5,4]
0	X	X	X	Disabled
1	0	X	X	Disabled
	1	0	0	Disabled
	1	X	1	Running
	1	1	X	Running

Power Good and Power Down

PWRGD is asserted high and de-asserted low. De-assertion of PWRGD (pulling the signal low) is equivalent to indicating a power down condition. PWRGD (assertion) is used by the PI6CG33A06 to sample initial configurations such as SMB_ADR0_tri selections.

After PWRGD has been asserted high for the first time, the pin becomes a PWRDN# (Power Down) pin that can be used to shut off all clocks cleanly and instruct the device to invoke power savings mode. PWRDN# is a completely asynchronous active low input. When entering power savings mode, PWRDN# should be asserted low prior to shutting off the input clock or power to ensure all clocks shut down in a glitch free manner. When PWRDN# is de-asserted high, all clocks will start and stop without any abnormal behavior and will meet all AC and DC parameters. The assertion and de-assertion of PWRDN# is asynchronous.

When PWRDN# is sampled low by two consecutive rising edges of 100M#, all differential outputs must held low on the next 100M# high to low transition, as shown in Figure 1.

PWRGD to the clock buffer shall not be asserted before VDD reaches VDDmin. Prior to VDDmin it is recommended to hold PWRGD low (less than 0.5V).

The power-up latency TSTABLE is to be less than 5ms. This is the time from the assertion of the PWRGD signal to the time that stable clocks are output from the buffer chip. All differential outputs stopped in a Low/Low condition resulting from power down must be driven high in less than 300µs of PWRGD assertion to a voltage greater than 200mV, as shown in Figure 2.

PWRDN# Assertion




Figure 1. PWRDN# Assertion Timing

PWRGD Assertion




Figure 2. PWRGD Assertion Timing

Output Enable Control

The PI6CG33A06 has three methods for enabling and disabling outputs. In order for an output to be enabled, ALL three methods must enable the output. If ANY method disables the output, the output will be disabled. Clocks always start and stop in a glitch free manner, meaning duty cycle requirements are still met.

The first is the traditional method of OE# pins that are used for PCI Express clock enabling at the PCIe connector. Each of the 3 dedicated 100MHz clock outputs can be enabled or disabled with the OE[3,1,0]# pins individually. The OE# pin must be pulled low to enable the output.

The second method is by using the SMBus output enable bits. Any of the 6 outputs have dedicated SMBus output enable bits in Bytes[0:2] of the SMBus register set that can enable or disable the clock outputs. The Output Enable bits in the SMBus registers are active high and are set to enable by default.

The third is using the Side Band Interface (SBI). This is a DB2000QL compatible method of enabling outputs using a hardware shift / load method. Refer to Power Management Tables for the truth table for enabling and disabling outputs via hardware and software. All three methods must be set to “enable” for the clock to be active on that pin.

Side-Band Interface

This interface consists of SBI_IN, SBI_CLK, SHFT_LD#, and SBI_OUT pins. When the SHFT_LD# pin is high, the rising edge of SBI_CLK can shift DATA into the shift register. After shifting data, the falling edge of SHFT_LD# loads the shift register contents to the output control register.

Since the PI6CG33A06 has dedicated pins for the SBI, both SBI and the traditional SMBus methods are active at the same time. There are SMBus registers for masking off the disable function of the SBI interface. When set to a one, the mask register forces the SBI interface for its respective output to indicate ‘enabled’. This prevents accidentally disabling critical outputs when using the SBI. However the traditional SMBus enable bits and the OE# pins may still disable an output. If the application does not use the SBI, the SBI input pins may be tied ‘Low’. Figure 3 provides a high level functional description of the SBI.




Figure 3. Side-band Interface Control Logic – Functional Description

Output Enable / Disable Priority

The PI6CG33A06 requires that outputs be enabled by an 'AND' function of all methods of enabling the output. Figure 4 illustrates this. There are three enable/disable paths: OE# pin (if present), a SMBus OE bit and the Side-Band Interface. All three must indicate 'enable' for the output to be enabled. Conversely, any single enable/disable path can disable an output if it indicates 'disable'.

Additionally, the Side-Band Interface indicates a 'high' if the SBI_Mask_Bit OR the SBI_Output Register Bit are 'high'. This means that the SBI_MASK_Bit can prevent the SBI interface from disabling an output. Note that the SBI_MASK_Bits are SMBus registers. The shift order follows the order of the SMBus enable bits in Byte[2:0] as shown in Figure 5.

The SMBus registers for the SBI Output and SBI_Mask follow the same bit order. Note that the SBI Output register contains the value latched from the shift register. Software must apply the SBI Mask bits to this value to get the output of the Side-Band Interface OR gate in Figure 4. Figure 6 shows the basic timing of the side-band interface. The SHFT_LD# pin goes high to enable the SBI_CLK input. Next, the rising edge of SBI_CLK clocks SBI_IN data into the shift register. After the 20th clock, stop the clock low and drive the SHFT_LD# pin low. The falling edge of SHFT_LD# latches the shift register contents to the output control register, enabling or disabling the outputs. Always shift 20 bits of data into the shift register to control the outputs.

The SBI interface supports clock rates up to 25MHz. The PI6CG33A06 allows two SBI connection topologies – star and daisy chain. In a star topology, multiple devices may share SBI_CLK and SBI_IN pins. In this topology, each PI6CG33A06 has a dedicated SHFT_LD# pin. In a daisy-chain topology, the SBI_OUT of one device connects to the SBI_IN device of a downstream device. When using the daisy chain topology, the user must shift a complete set of bits for the combined devices. Two daisy-chained PI6CG33A06 devices require shifting of 40 bits. When the SHFT_LD# pin is low, the SBI interface ignores any activity on the SBI_CLK and SBI_IN pins. Figure 7 illustrates a star topology connection for the PI6CG33A06 SBI interface. The star topology allows independent configuration of each device. For PI6CG33A06, this means shifting 20 bits at a time. A disadvantage is that a separate SHFT_LD# pin is required for each device.

The daisy chain topology allows configuration of any number of devices with only three signals from the SBI controller. It utilizes the SBI_OUT pin of one device to drive the SBI_IN pin of the next device in the daisy chain. Users must take care to shift the proper number of bits in this configuration. For the example shown in Figure 8, the SBI bit stream consists of 40 bits.




Figure 4. Output Enable Logic (per output)




Figure 5. Side-Band Shift Order




Figure 6. Side Band Interface Functional Timing




Figure 7. Star SBI Topology




Figure 8. Daisy-Chain SBI Topology

Maximum Ratings

(Above which useful life may be impaired. For user guidelines, not tested.)

Storage Temperature.....	-65°C to +150°C
Supply Voltage to Ground Potential, V_{DDXX}	-0.5V to +4.0V
Input Control Pins Voltage	-0.5V to $V_{DD}+0.5V$
CLK+/- Pins	-0.5V to 2.5V
SMBus, Input High Voltage	3.6V
ESD Protection (HBM)	2000V
Junction Temperature	125°C max

Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Operating Conditions

Temperature = T_A ; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Typ.	Max.	Units
V_{DD}, V_{DD_A}	Power Supply Voltage		3.135	3.3	3.465	V
I_{DDMXCK}	Normal Operating Mode Power Supply Current ⁽¹⁾	$V_{DDMXCK}, MXCK[5,4]$ at 100MHz		18.3	24	mA
I_{DD100M}		$V_{DD100M}, 100M[3,1,0]$		25.9	34	mA
I_{DDXTAL}		$V_{DDXTAL}, 25MHz$ Xtal		17.2	23	mA
I_{DDPT}		V_{DDPT}		0.8	1	mA
I_{DDA25M}		$V_{DDA25M}, 25M$ on		6.9	9	mA
$I_{DDA100M}$		$V_{DDA100M}, 100M[3,1,0]$ on, SSC on		29.4	39	mA
I_{DDMXCK}	25MPG Mode Power Supply Current ⁽²⁾	$V_{DDMXCK}, MXCK[5,4]$		2.1	3	mA
I_{DD100M}		$V_{DD100M}, 100M[3,1,0]$		2.3	3	mA
I_{DDXTAL}		$V_{DDXTAL}, 25MHz$ Xtal		2.9	4	mA
I_{DDPT}		V_{DDPT}		0.8	1	mA
I_{DDA25M}		$V_{DDA25M}, 25M[2]$ on		6.8	9	mA
$I_{DDA100M}$		$V_{DDA100M}$		0.5	1	mA
I_{DDMXCK}	Power Down Mode Power Supply Current ⁽³⁾	$V_{DDMXCK}, MXCK[5,4]$		2.1	3	mA
I_{DD100M}		$V_{DD100M}, 100M[3,1,0]$		2.3	3	mA
I_{DDXTAL}		$V_{DDXTAL}, 25MHz$ Xtal		2.9	4	mA
I_{DDPT}		V_{DDPT}		0.8	1	mA
I_{DDA25M}		$V_{DDA25M}, 25M[2]$ off		4.5	6	mA
$I_{DDA100M}$		$V_{DDA100M}$		0.5	1	mA
T_A	Ambient Temperature	Industrial grade	-40		85	°C

Note:

1. PWRGD/PWRGDN# = 1, all outputs enabled.
2. PWRGD/PWRGDN# = 0, 25MPG = 1.
3. PWRGD/PWRGDN# = 0, 25MPG = 0.

Input Electrical Characteristics

Symbol	Parameters	Min.	Typ.	Max.	Units
R _{pu}	Internal pull up resistance		120		KΩ
R _{dn}	Internal pull down resistance		120		KΩ
L _{PIN}	Pin inductance			7	nH

Crystal Characteristics

Symbol	Parameters	Min.	Typ.	Max.	Units
OSCmode	Mode of Oscillation	Fundamental			–
FREQ	Frequency		25		MHz
ESR ⁽¹⁾	Equivalent Series Resistance			50	Ω
Cload	Load Capacitance		8		pF
Cshunt	Shunt Capacitance			7	pF
–	Drive Level			200	μW

Note:

1. ESR value is dependent upon frequency of oscillation

SMBus Electrical Characteristics

Temperature = T_A; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Typ.	Max.	Units
V _{DDSMB}	Nominal bus voltage		2.7		3.6	V
V _{IHSMB}	SMBus Input High Voltage	SMBus, V _{DDSMB} = 3.3V	2.1		3.6	V
		SMBus, V _{DDSMB} < 3.3V	0.65* V _{DDSMB}			
V _{ILSMB}	SMBus Input Low Voltage	SMBus, V _{DDSMB} = 3.3V			0.6	V
		SMBus, V _{DDSMB} < 3.3V			0.6	
I _{SMBSINK}	SMBus sink current	SMBus, at V _{OLSMB}	4			mA
V _{OLSMB}	SMBus Output Low Voltage	SMBus, at I _{SMBSINK}			0.4	V

SMBus Standard Mode at 100kb/s (100k Class)

f _{MAXSMB}	SMBus operating frequency	Maximum frequency			100	kHz
t _{BUF}	Bus Free Time	Between STOP and START	4.7			us
t _{HD_STA}	Hold Time	After (REPEATED) START	4			us
t _{SU_STA}	Setup Time	REPEATED START	4.7			us
t _{SU_STO}	Setup Time	STOP	4			us
t _{HD_DAT}	Hold Time	Data	300			ns
t _{SU_DAT}	Setup Time	Data	250			ns

PI6CG33A06

Symbol	Parameters	Conditions	Min.	Typ.	Max.	Units
t _{TIMEOUT}	Timeout	Detect SMBDAT Low	25		35	ms
t _{TIMEOUT}	Timeout	Detect Clock Low	25		35	ms
t _{LOW}	Clock Low Period		4.7			us
t _{HIGH}	Clock High Period		4		50	us
t _{RMSB}	SMBus rise time	(Max V _{IL} - 0.15) to (Min V _{IH} + 0.15)			1000	ns
t _{FMSB}	SMBus fall time	(Min V _{IH} + 0.15) to (Max V _{IL} - 0.15)			300	ns
t _{POR}	Time after power on reset	Power on and PWRGD/PWRDN# = 1			5	ms
SMBus Fast Mode at 400kb/s (400k Class)						
f _{MAXSMB}	SMBus operating frequency	Maximum frequency			400	kHz
t _{BUF}	Bus Free Time	Between STOP and START	1.3			us
t _{HD_STA}	Hold Time	After (REPEATED) START	0.6			us
t _{SU_STA}	Setup Time	REPEATED START	0.6			us
t _{SU_STO}	Setup Time	STOP	0.6			us
t _{HD_DAT}	Hold Time	Data	300			ns
t _{SU_DAT}	Setup Time	Data	100			ns
t _{TIMEOUT}	Timeout	Detect SMBDAT Low	25		35	ms
t _{TIMEOUT}	Timeout	Detect Clock Low	25		35	ms
t _{LOW}	Clock Low Period		1.3			us
t _{HIGH}	Clock High Period		0.6		50	us
t _{RMSB}	SMBus rise time	(Max V _{IL} - 0.15) to (Min V _{IH} + 0.15)			300	ns
t _{FMSB}	SMBus fall time	(Min V _{IH} + 0.15) to (Max V _{IL} - 0.15)			300	ns
t _{POR}	Time after power on reset	Power on and PWRGD/PWRDN# = 1			5	ms

Note:

- After this period, the first clock is generated.
- The device maintains 300ns data hold time for backwards compatibility with the SMBus 2.0 specification. Newer versions of the SMBus specification call out 0ns data hold time for both 100kHz and 400kHz classes.
- The device provided additional SMBus protection by implementing a timeout for SMBDATA being held low in excess of t_{TIMEOUT}, in addition to the SMBCLK low timeout.
- Devices participating in a transfer can abort the transfer in progress and release the bus when any single clock low interval exceeds the value of t_{TIMEOUT}, Minimum. After the master in a transaction detects this condition, it must generate a stop condition within or after the current data byte in the transfer process. Devices that have detected this condition must reset their communication and be able to receive a new START condition no later than t_{TIMEOUT}, Maximum. Typical device examples include the host controller, and embedded controller, and most devices that can master the SMBus. Some simple devices do not contain a clock low drive circuit; this simple kind of device typically may reset its communications port after a start or a stop condition. A timeout condition can only be ensured if the device that is forcing the timeout holds the SMBCLK low for t_{TIMEOUT}, Maximum or longer.
- t_{HIGH}, Maximum provides a simple guaranteed method for masters to detect bus idle conditions. A master can assume that the bus is free if it detects that the clock and data signals have been high for greater than t_{HIGH}, Maximum.

LVCMOS DC Electrical Characteristics

Temperature = T_A ; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Typ.	Max.	Units
V_{IH}	Input High Voltage	Single-ended inputs, except tri-level pins	2		$V_{DD} + 0.3$	V
V_{IL}	Input Low Voltage	Single-ended inputs, except tri-level pins	-0.3		0.8	V
V_{IH}	Input High Voltage	Single-ended trilevel inputs	2.5		$V_{DD} + 0.3$	V
V_{IM}	Input Mid Voltage	Single-ended trilevel inputs	1.2	$0.5V_{DD}$	1.8	V
V_{IL}	Input Low Voltage	Single-ended trilevel inputs	-0.3		0.8	V
I_{IH}	Input High Current	Single-ended inputs, $V_{IN} = V_{DD}$			5	mA
		Single-ended inputs with pull down resistor, $V_{IN} = V_{DD}$			50	mA
I_{IL}	Input Low Current	Single-ended inputs, $V_{IN} = 0$	-5			μA
		Single-ended inputs with pull up resistor, $V_{IN} = 0$	-50			μA
C_{IN}	Input Capacitance ⁽¹⁾	Logic inputs, except differential inputs			4.5	pF
		Differential clock inputs	1.5		2.7	pF
C_{OUT}	Output Capacitance ⁽¹⁾	Output pin capacitance			4.5	pF

LVCMOS AC Electrical Characteristics

Temperature = T_A ; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Typ.	Max.	Units
f_{IN}	Input Frequency			25		MHz
t_{STAB}	Clock Stabilization	From VDD power-up and after input clock stabilization or de-assertion of PWRDN# to valid outputs.			5	ms
t_{PDLAT}	PD# de-assertion	Differential outputs enable after PD# de-assertion		200	300	us
t_{OELAT}	Output enable latency	100M start after OE# assertion 100M stop after OE# deassertion	4		10	clocks
t_{PDLAT}	PWRDN# de-assertion	Differential outputs enable after PWRDN# de-assertion		10	50	us
t_{RF}	Rise and Fall Time	Control inputs ⁽²⁾			5	ns

Note:

- Guaranteed by design and characterization, not 100% tested in production.
- Control input must be monotonic from 20% to 80% of input swing.

HCSL Output Characteristics

Temperature = T_A ; Supply voltages per normal operation conditions; See test circuits for the load conditions

Symbol	Parameters	Conditions	Min.	Typ.	Max.	Units
Outputs Driving High Impedance Receiver						
V_{MAX}	Maximum Output Voltage ^(1,5,6)	Measurement on single ended signal using absolute value	660	800	1150	mV
V_{MIN}	Minimum Output Voltage ^(1,5,6)		-150	20	150	mV
$V_{cross\ abs}$	Absolute Crossing Point Voltage	Scope averaging off.	250	400	500	mV
$V_{cross\ rel}$	Relative Crossing Point Voltage	Scope averaging off.		0	100	mV
t_{RF}	Slew Rate ^(1,2,3)	Scope averaging on, 10 inch trace	2	3.0	4	V/ns
Dt_{RF}	Slew Rate Matching ^(1,2,4)	Scope averaging on, 10 inch trace		6	19	%
Outputs Driving Terminated Receiver (Double Termination, see test setup in Figure 10)						
V_{MAX}	Maximum Output Voltage ^(1,5,6)	Measurement on single ended signal using absolute value			$V_{OH} + 75$	mV
V_{MIN}	Minimum Output Voltage ^(1,5,6)		$V_{OL} - 75$			mV
V_{OH}	Output High Voltage		225		270	mV
V_{OL}	Output Low Voltage		10		150	mV
$V_{cross\ abs}$	Absolute Crossing Point Voltage	Scope averaging off.	130		200	mV
Diff-Z	Output Differential Impedance	Measured at V_{OL} / V_{OH}	85 - 5%		85 + 5%	Ω
t_{SKEWGP}	Output Skew Within a Group ^(1,2)	Groups are 25M, MXCK[5,4], and 100M[3,1,0]		25		ps
$t_{SKEWGP2GP}$	Output Skew Across Groups ^(1,2)	Across 25M and MXCK[5,4] set to 25MHz or 100M[3,1,0] and MXCK[5,4] set to 100MHz		100		ps
t_{DC100M}	Duty Cycle	100MHz Outputs and MXCLK outputs set to 100MHz.	45		55	%
t_{DC25M}	Duty Cycle	25MHz Outputs and MXCLK outputs set to 25MHz with XTAL as source	47		53	%
t_{DC100M}	Duty Cycle	25MHz Outputs and MXCLK outputs set to 25MHz with XO as source with 44/55% duty cycle	45		55	%
$t_{j-c-100M}$	Cycle to Cycle Jitter ^(1,2)	100MHz Outputs and MXCLK outputs set to 100MHz		25	40	ps

Note:

- Guaranteed by design and characterization, not 100% tested in production
- Measured from differential waveform
- Slew rate is measured through the V_{swing} voltage range centered around differential 0V, within +/-150mV window
- Slew rate matching is measured through +/-75mV window centered around differential zero
- At default SMBus settings.
- Includes 300mV of overshoot for V_{max} and 300mV of undershoot for V_{min} .

PCIe Common Clock (CC) Architecture Jitter

Symbol	Parameters	Condition	Min.	Typ.	Max.	Spec Limit	Units
t _{JPHASE}	Integrated phase jitter (RMS)	PCIe 1.0		20	60	86	ps (pkpk)
		PCIe 2.0 Low Band, 10kHz < f < 1.5MHz (PLL BW 5-16MHz or 8-5MHz, CDR = 10MHz)		0.06	0.15	3	ps
		PCIe 2.0 High Band, 1.5MHz < f < Nyquist (50MHz); (PLL BW 5-16MHz or 8-5MHz, CDR = 10MHz)		0.2	0.45	3.1	ps
		PCIe 3.0 (PLL BW 2-4MHz or 2-5MHz, CDR = 10MHz)		0.07	0.15	1	ps
		PCIe 4.0 (PLL BW 2-4MHz or 2-5MHz, CDR = 10MHz)		0.03	0.15	0.5	ps
		PCIe 5.0		0.03	0.06	0.15	ps
		PCIe 6.0		0.01	0.05	0.1	ps
		PCIe 7.0		0.015	0.03	0.067	ps

PCIe Independent Reference Clock Architecture Jitter

Symbol	Parameters	Condition	Min.	Typ.	Max.	Spec Limit	Units
t _{JPHASE}	Integrated phase jitter (RMS)	PCIe 3.0 SRIS (PLL BW 2-4MHz or 2-5MHz, CDR = 10MHz)		0.1	0.3		ps
		PCIe 4.0 SRIS (PLL BW 2-4MHz or 2-5MHz, CDR = 10MHz)		0.1	0.3		ps
		PCIe 5.0 SRIS		0.03	0.1		ps
		PCIe 6.0 SRIS		0.06	0.1		ps
		PCIe 7.0 SRIS		0.015	0.03		ps

Side Band Signal Characteristics

Symbol	Parameters	Condition	Min.	Typ.	Max.	Units
t _{PERIOD}	Clock Period		40			ns
t _{SETUP}	SHFT Setup Time to Clock	SHFT_LD# high to SBI_CLK rising edge	10			ns
t _{SHD} ⁽¹⁾	SHFT Hold Time to Clock	SHFT_LD# hold (high) after SBI_CLK rising edge (SBI_CLK to SHFT_LD# falling edge)	10			ns

PI6CG33A06

Symbol	Parameters	Condition	Min.	Typ.	Max.	Units
$t_{DSU}^{(1)}$	SBI_IN Setup Time	SBI_IN setup to SBI_CLK rising edge	5			ns
$t_{DHD}^{(1)}$	SBI_IN Hold Time	SBI_IN hold after SBI_CLK rising edge	2			ns
$t_{COUT}^{(1)}$	SBI_CLK to SBI_OUT	SBI_CLK rising edge to SBI_OUT valid	2			ns
$t_{EN}^{(1)}$	Enable/Disable Time	Delay from SHFT_LD# falling edge to next output configuration taking effect. Refers to device differential input clock	4		10	clocks
$t_{SLEW}^{(1,2)}$	Slew Rate	SBI_CLK input (between 20% and 80%)	0.7		4	V/ns

Note:

1. Guaranteed by design and characterization, not 100% tested in production
2. Control input must be monotonic from 20% to 80% of input swing.




Figure 9. Side Band Interface Timing

AC/DC Test Load





Figure 10. Test Setup for PCIe Jitter Measurement

Power Supply Noise Profile

Symbol	Parameters	Condition	Min.	Typ.	Max.	Units
V _{DD_AC}	Power Supply Noise	Single tone AC noise, swept		40		mV
V _{DDA_AC}	Power Supply Noise	VDDA electrical noise > 20MHz.		20		mV
V _{DDXTAL}	Power Supply Noise	VDDXTAL electrical noise 12kHz to 25MHz.		20		mV

Note:

1. Guaranteed by design and characterization, not 100% tested in production
2. Control input must be monotonic from 20% to 80% of input swing.




Figure 11. Power Supply Filter

SMBus Serial Data Interface

PI6CG33A06 is a slave only device that supports block read and block write protocol using a single 7-bit address and read/write bit as shown below.

Read and write block transfers can be stopped after any complete byte transfer.

Address Assignment

Table 3. SMBus Address Selection

SMB_ADR0_tri	SMBus Address
L	B2
M	B4
H	B6

How to Write

1 bit	7 bits	1 bit	1 bit	8 bits	1 bit	8 bits	1 bit	8 bits	1 bit		8 bits	1 bit	1 bit
Start bit	Add.	W(0)	Ack	Beginning Byte loca- tion = N	Ack	Data Byte count = X	Ack	Beginning Data Byte (N)	Ack		Data Byte (N+X-1)	Ack	Stop bit

How to Read

1 bit	7 bits	1 bit	1 bit	8 bits	1 bit	1 bit	7 bits	1 bit	1 bit	8 bits	1 bit	8 bits	1 bit
Start bit	Address	W(0)	Ack	Beginning Byte loca- tion = N	Ack	Repeat Start bit	Address	R(1)	Ack	Data Byte count = X	Ack	Beginning Data Byte (N)	Ack

	8 bits	1 bit	1 bit
.....	Data Byte (N+X-1)	NAck	Stop bit

Byte 0: Output Enable Register 0

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved	Reserved	RW	0		
6	Reserved	Reserved	RW	0		
5	Reserved	Reserved	RW	0		
4	Reserved	Reserved	RW	0		
3	OE_100M3	Output Enable for 100M3	RW	1	Disabled	Enabled
2	Reserved	Reserved	RW	0		
1	OE_100M1	Output Enable for 100M1	RW	1	Disabled	Enabled
0	OE_100M0	Output Enable for 100M0	RW	1	Disabled	Enabled

PI6CG33A06
Byte 1: Output Enable Register 1

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved	Reserved	RW	0		
6	Reserved	Reserved	RW	0		
5	OE_MXCK5	Output Enable for MXCK5	RW	1	Disabled	Enabled
4	OE_MXCK4	Output Enable for MXCK4	RW	1	Disabled	Enabled
3	Reserved	Reserved	RW	0		
2	Reserved	Reserved	RW	0		
1	Reserved	Reserved	RW	0		
0	Reserved	Reserved	RW	0		

Byte 2: Output Enable Register 2

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	MXCK_SEL	MXCK[5,4] Frequency Select	RW	1	100MHz	25MHz
6	MXCK_SEL Control	MXCK[5,4] Select control	RW	1	Pin control	Register control
5	Reserved	Reserved	RW	0		
4	Reserved	Reserved	RW	0		
3	Reserved	Reserved	RW	0		
2	OE_25M2	Output Enable for 25M2	RW	1	Disabled	Enabled
1	Reserved	Reserved	RW	0		
0	Reserved	Reserved	RW	0		

Byte 3 to 5: Reserved

PI6CG33A06
Byte 6: SSC PLL Control Register

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved	Reserved		Reserved		
6	Reserved	Reserved		Reserved		
5	SSC_ENABLE_RB	Readback of SSC_ENABLE pin for 100M[3,1,0] and MXCK[5,4] if MXCK_SEL is low	R	Realtime	Bit[1:0]: SSC State 00: SSC Off 01: SSC = -0.3% 10: Reserved 11: SSC = -0.5%	
4			R	Realtime		
3	SSC PLL Input Source	SSC source for 100M[3,1,0] and MXCK[5,4] if MXCK_SEL is low	RW	0	Xtal	
2	SSC_Ctr	SSC control for 100M[3,1,0] and MXCK[5,4] if MXCK_SEL is low	RW	0	Enabled	Disabled
1	SSC_SEL	100M[3,1,0] and MXCK[5,4] if MXCK_SEL is low	RW	Latch SSC pin on power-up	Bit[1:0]: SSC State 00: SSC Off 01: SSC = -0.3% 10: Reserved 11: SSC = -0.5%	
0		100M[3,1,0] and MXCK[5,4] if MXCK_SEL is low	RW	Latch SSC pin on power-up		

Note:

After setting Byte 46 = 33 (hex) and Byte 47 = A7 (hex)

01: SSC = -0.15%, 11:SSC = -0.3% for PCIe 7.0 SRIS test

Byte 7: OE# Pin Realtime Readback Control Register

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved	0	R	0		
6	Reserved	Reserved	R	0		
5	Reserved	Reserved	R	0		
4	Reserved	Reserved	R	0		
3	OE_3#_100M3	Realtime Readback of OE_3# pin	R	Realtime	OE_3# Low	OE_3# High
2	Reserved	Reserved	R	0		
1	OE_1#_100M1	Realtime Readback of OE_1# pin	R	Realtime	OE_1# Low	OE_1# High
0	OE_0#_100M0	Realtime Readback of OE_0# pin	R	Realtime	OE_0# Low	OE_0# High

PI6CG33A06
Byte 8: Vendor/Revision Identification Control Register

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Revision Code Bit 3	Die Revision	R	0		
6	Revision Code Bit 2		R	0		
5	Revision Code Bit 1		R	0		
4	Revision Code Bit 0		R	0		
3	Vendor ID Bit 3	Diodes/Pericom ID: 0011	R	0		
2	Vendor ID Bit 2		R	0		
1	Vendor ID Bit 1		R	1		
0	Vendor ID Bit 0		R	1		

Byte 9: Device ID Control Register

Bit	Control Function	Description	Type	Power-up Condition	0	1
7	DTYPE1	Device type	R	0	'00' = CG, '01' = ZDB, '10' = Reserve, '11' = NZDB	
6	DTYPE0		R	0		
5	DID5	Device ID	R	0	000111 binary, 07Hex	
4	DID4		R	0		
3	DID3		R	0		
2	DID2		R	1		
1	DID1		R	1		
0	DID0		R	1		

Byte 10: Byte Count Register

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved			0		
6	Reserved			0		
5	BC5	Writing to these registers configures how many bytes will be read back	RW	0		
4	BC4		RW	0		
3	BC3		RW	1		
2	BC2		RW	0		
1	BC1		RW	0		
0	BC0		RW	0		

Byte 11: Side-Band Interface Mask Register 0

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved		RW	0		
6	Reserved		RW	0		
5	Reserved		RW	0		
4	Reserved		RW	0		
3	Mask_100M3	SBI Mask for 100M3	RW	0	Off	On
2	Reserved		RW	0		
1	Mask_100M1	SBI Mask for 100M1	RW	0	Off	On
0	Mask_100M0	SBI Mask for 100M0	RW	0	Off	On

Note: If '0', the Side-Band Interface register may disable the output. If '1', the Side-Band Interface cannot disable the output. Such an output may only be disabled by the respective SMBus bit, or OE# pin (present only for 100M outputs).

Byte 12: Side-Band Interface Mask Register 1

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved		RW	0		
6	Reserved		RW	0		
5	Mask_MXCK5	SBI Mask for MXCK5	RW	0	Off	On
4	Mask_MXCK4	SBI Mask for MXCK4	RW	0	Off	On
3	Reserved		RW	0		
2	Reserved		RW	0		
1	Reserved		RW	0		
0	Reserved		RW	0		

Note: If '0', the Side-Band Interface register may disable the output. If '1', the Side-Band Interface cannot disable the output. Such an output may only be disabled by the respective SMBus bit.

Byte 13: Side-Band Interface Mask Register 2

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved			0		
6	Reserved			0		
5	Reserved			0		
4	Reserved			0		
3	Reserved		RW	0		
2	Mask_25M2	SBI Mask for 25M2	RW	0	Off	On
1	Reserved		RW	0		
0	Reserved		RW	0		

Note: If '0', the Side-Band Interface register may disable the output. If '1', the Side-Band Interface cannot disable the output. Such an output may only be disabled by the respective SMBus bit.

PI6CG33A06
Byte 14: Side-Band Interface Readback Register 0

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved	Reserved	R	1		
6	Reserved	Reserved	R	1		
5	Reserved	Reserved	R	1		
4	Reserved	Reserved	R	1		
3	100M3_RB	SBI Readback 100M3	R	1	Disabled	Enabled
2	Reserved	Reserved	R	1		
1	100M1_RB	SBI Readback 100M1	R	1	Disabled	Enabled
0	100M0_RB	SBI Readback 100M0	R	1	Disabled	Enabled

Note: If the Side-Band interface is used, this register latches the content of the shift register. A '0' indicates that the corresponding differential output is disabled unless the bit has been masked off in SBI Mask register. A '1' indicates that the output is enabled if the corresponding SMBus OE bit is set high and OE# pin (present only for 100M outputs) is pulled low.

Byte 15: Side-Band Interface Readback Register 1

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved		R	1		
6	Reserved		R	1		
5	MXCK5_RB	SBI Readback MXCK5	R	1	Disabled	Enabled
4	MXCK4_RB	SBI Readback MXCK4	R	1	Disabled	Enabled
3	Reserved		R	1		
2	Reserved		R	1		
1	Reserved		R	1		
0	Reserved		R	1		

Note: If '0', the Side-Band Interface register may disable the output. If '1', the Side-Band Interface cannot disable the output. Such an output may only be disabled by the respective SMBus bit.


Byte 16: Side-Band Interface Readback Register 2

Bit	Control Function	Description	Type	Power Up Condition	0	1
7	Reserved		R	0		
6	Reserved		R	0		
5	Reserved		R	0		
4	Reserved		R	0		
3	Reserved		R	1		
2	25M2_RB	SBI Readback 25M2	R	1	Disabled	Enabled
1	Reserved		R	1		
0	Reserved		R	1		

Note: If the Side-Band interface is used, this register latches the content of the shift register. A '0' indicates that the corresponding differential output is disabled unless the bit has been masked off in SBI Mask register. A '1' indicates that the output is enabled if the corresponding SMBus OE bit is set high and OE# pin (present only for 100M outputs) is pulled low.

PI6CG33A06


Part Marking





PI6CG33A06

Packaging Mechanical

40-VQFN (ZLF)



SYMBOLS	MIN.	NOM.	MAX.
A	0.80	0.85	0.90
A1	0.00	0.02	0.05
A3	0.203 REF.		
b	0.15	0.20	0.25
D	4.90	5.00	5.10
E	4.90	5.00	5.10
e	0.40 BSC		
L	0.35	0.40	0.45
L1	0.33	0.38	0.43
D2	3.40	3.50	3.60
E2	3.40	3.50	3.60



NOTE :

1. ALL DIMENSIONS ARE IN mm. ANGLES IN DEGREES.
2. COPLANARITY APPLIES TO THE EXPOSED THERMAL PAD AS WELL AS THE TERMINALS.
3. REFER JEDEC MO-220
4. RECOMMENDED LAND PATTERN IS FOR REFERENCE ONLY.
5. THERMAL PAD SOLDERING AREA (MESH STENCIL DESIGN IS RECOMMENDED).


DATE: 05/09/23
DESCRIPTION: V-QFN5050-40
PACKAGE CODE: ZLF (ZLF40)
DOCUMENT CONTROL #: PD-2284
REVISION: --

For latest package info.

please check: <http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/>

Mechanical Data

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - Matte Tin (Sn) Plated Leads. Solderable per MIL-STD-202, Method 208 ③
- Weight: 0.066 grams (Approximate)

PI6CG33A06

Ordering Information

Orderable Part Number	Package Code	Package Description	Pin 1 Orientation
PI6CG33A06ZLFEX	ZLF	V-QFN5050-40	Top Right Corner
PI6CG33A06ZLFEX-13R	ZLF	V-QFN5050-40	Top Left Corner

Notes:

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
4. E = Pb-free and Green
5. X suffix = Tape/Reel
6. For packaging detail, go to our website at: <https://www.diodes.com/assets/MediaList-Attachments/Diodes-Package-Information.pdf>

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (<https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/>) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at <https://www.diodes.com/about/company/terms-and-conditions/important-notice>

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.

All other trademarks are the property of their respective owners.

© 2026 Diodes Incorporated. All Rights Reserved.

www.diodes.com