




DIODES

TVS and ESD Protection

Diodes for TVS and ESD Protection



FEATURED PRODUCTS

TransZorb® Avalanche Transient Voltage Suppressors

PAR® Automotive Transient Voltage Suppressors

Special Function Transient Voltage Suppressors

ESD Protection Devices

EMI Filter Devices with ESD Protection

Power Voltage Regulating Diodes

RESOURCES

- For technical questions contact TVS@vishay.com, ESDProtection@vishay.com
- For more information contact DiodesAmericas@vishay.com, DiodesEurope@vishay.com, DiodesAsia@vishay.com

One of the World's Largest Manufacturers of
Discrete Semiconductors and Passive Components





DIODES

Transient Voltage Suppressors

TRANSZORB® Avalanche

Vishay's TRANSZORB® Transient Voltage Suppressors (TVS) use state-of-the-art technology to offer the highest voltage range in the industry. Their design enables these avalanche breakdown diode TVS devices to absorb large amounts of energy for short time durations without sustaining damage. Vishay's TRANSZORB TVSs do not exhibit a wear-out mechanism, have extremely fast turn-on times, and provide excellent clamping characteristics.

P _{PPM} ⁽¹⁾ (W)	Device ⁽²⁾	Package		V _{WM} Range (V)	V _(BR) Range ⁽³⁾ (V)	V _(BR) Tolerance (Suffix)
		Family	Type			
150	MSPxxA ⁽⁵⁾	Surface Mount	MicroSMP	3.3 to 5.0	4.1 to 6.4	5 %
	MSMPxxA ⁽⁵⁾	Surface Mount	MicroSMP	6.0 to 20	6.67 to 24.5	5 %
200	TGL41-nnA ⁽⁶⁾	Surface Mount	DO-213AB (MELF)	81 to 171	100 to 200	5 %
300	P4KE530 and P4KE550 ⁽⁵⁾	Plastic Axial	DO-204AL (DO-41)	477 and 495	530 and 550 ^(m)	N/A
	SMAJ530 and SMAJ550 ⁽⁵⁾	Surface Mount	DO-214AC (SMA)	477 and 495	530 and 550 ^(m)	N/A
	P4SMAAnnA ⁽⁵⁾	Surface Mount	DO-214AC (SMA)	85.5 to 459	100 to 540	5 %
	P4SMAAnnCA	Surface Mount	DO-214AC (SMA)	85.5 to 185	100 to 220	5 %
	SMAJxxA ⁽⁵⁾	Surface Mount	DO-214AC (SMA)	85 to 188	94.4 to 209	5 %
	SMAJxxCA	Surface Mount	DO-214AC (SMA)	85 to 188	94.4 to 209	5 %
400	BZW04-xx, B	Plastic Axial	DO-204AL (DO-41)	5.8 to 376	6.45 to 418	5 %
	P4KEnnA ⁽⁵⁾	Plastic Axial	DO-204AL (DO-41)	5.5 to 459	6.8 to 540	5 %
	P4KEnnCA	Plastic Axial	DO-204AL (DO-41)	5.5 to 376	6.8 to 440	5 %
	P4SMAAnnA ⁽⁵⁾	Surface Mount	DO-214AC (SMA)	5.8 to 77.8	6.8 to 91	5 %
	P4SMAAnnCA	Surface Mount	DO-214AC (SMA)	5.8 to 77.8	6.8 to 91	5 %
	SMAJxxA ⁽⁵⁾	Surface Mount	DO-214AC (SMA)	5.0 to 78	6.4 to 86.7	5 %
	SMAJxxCA	Surface Mount	DO-214AC (SMA)	5.0 to 78	6.4 to 86.7	5 %
	SMPxxA	Surface Mount	DO-220AA (SMP)	3.3 to 36	4.10 to 40.0	5 %
	TGL41-nnA ⁽⁵⁾	Surface Mount	DO-213AB (MELF)	5.5 to 77.8	6.8 to 91	5 %
500	SAxxA, CA	Plastic Axial	DO-204AC (DO-15)	5.0 to 170	6.4 to 189	5 %
	SMA5JxxA, CA	Surface Mount	DO-214AC (SMA)	5.0 to 40	6.4 to 44.4	5 %
600	P6KEnnA ⁽⁵⁾	Plastic Axial	DO-204AC (DO-15)	5.5 to 459	6.8 to 540	5 %
	P6KEnnCA	Plastic Axial	DO-204AC (DO-15)	5.5 to 376	6.8 to 440	5 %
	P6SMBnnA ⁽⁵⁾	Surface Mount	DO-214AA (SMB)	5.8 to 459	6.8 to 540	5 %
	P6SMBnnCA	Surface Mount	DO-214AA (SMB)	5.8 to 185	6.8 to 220	5 %
	SM6TnnA, CA	Surface Mount	DO-214AA (SMB)	5.8 to 188	6.8 to 220	5 %
	SMA6FxxA ⁽⁵⁾	Surface Mount	DO-220A (SlimSMA)	5.0 to 20	6.40 to 24.5	5 %
	SMA6JxxA ⁽⁵⁾	Surface Mount	DO-214AC (SMA)	5.0 to 28	6.40 to 34.4	5 %
	SMBGxxA, CA	Surface Mount	DO-214AA (SMB)	5.0 to 188	6.4 to 209	5 %
	SMBJxxA, CA	Surface Mount	DO-214AA (SMB)	5.0 to 188	6.4 to 209	5 %
800	SMBJ3V3 ⁽⁵⁾	Surface Mount	DO-214AA (SMB)	3.3	4.1 Minimum	
	SMB8JxxCA	Surface Mount	DO-214AA (SMB)	5.0 to 40	6.4 to 44.4	5 %
1000	SMB10JxxA ⁽⁵⁾	Surface Mount	DO-214AA (SMB)	5.0 to 40	6.4 to 44.4	5 %
1500	1.5KEnnA ⁽⁵⁾	Plastic Axial	1.5KE	5.5 to 185	6.8 to 220	5 %
	1.5KEnnCA	Plastic Axial	1.5KE	5.5 to 185	6.8 to 220	5 %
	1N6267 - 1N6303 ⁽⁵⁾	Plastic Axial	1.5KE	5.5 to 171	6.8 to 200	5 %
	1.5SMCnnA ⁽⁵⁾	Surface Mount	DO-214AB (SMC)	5.8 to 459	6.8 to 540	5 %
	1.5SMCnnCA	Surface Mount	DO-214AB (SMC)	5.8 to 185	6.8 to 220	5 %
	ICTE-xx ⁽⁵⁾	Plastic Axial	1.5KE	5.0 to 18	6.0 to 21.2	N/A

Notes:

- (1) Tested with 10/1000 μ s pulse
- (2) In part numbers, "xx" designates VWM and "nn" designates nominal voltage
- (3) Nominal voltages are specified for part numbers with "nn" and minimum voltages are specified for part numbers with "xx" or (m) footnote. Higher voltages are planned (up to 600 V). Contact local sales office for availability

- (4) Types are offered in bi-directional polarity by adding suffix "CA" (BZW04 use suffix "B")

- (5) Uni-directional polarity only

- (6) Most Vishay TVS products have Underwriters Laboratory Recognition for the classification of protectors (QVGG2) under the UL standard for safety 497B, and file number E136766 for both uni-directional and bi-directional devices. See the individual data sheets for specific information.

TRANSZORB® Avalanche (cont'd.)

P _{PPM} (W) ⁽¹⁾	Device ⁽²⁾	Package		V _{WM} Range (V)	V _(BR) Range ⁽³⁾ (V)	V _(BR) Tolerance (Suffix)
		Family	Type			
1500 cont'd	ICTE-xxC	Plastic Axial	1.5KE	8.0 to 18	9.4 to 21.2	N/A
	1N6373 - 1N6378 ⁽⁵⁾	Plastic Axial	1.5KE	5.0 to 18	6.0 to 21.2	N/A
	1N6382 - 1N6386	Plastic Axial	1.5KE	8.0 to 18	9.4 to 21.2	N/A
	SM15TnnA, CA	Surface Mount	DO-214AB (SMC)	5.8 to 188	6.8 to 220	5 %
	SMCGxxA, CA	Surface Mount	DO-214AB (SMC)	5.0 to 188	6.4 to 209	5 %
	SMCJxxA, CA	Surface Mount	DO-214AB (SMC)	5.0 to 188	6.4 to 209	5 %
	SMPCxxA	Surface Mount	TO-277A (SMPC)	5.0 to 36	6.4 to 40	5 %
3000	SMC3KxxCA	Surface Mount	DO-214AB (SMC)	22 to 78	24.4 to 86.7	5 %
5000	5KPxxA ⁽⁵⁾	Plastic Axial	P600	5.0 to 188	6.4 to 209	5 %

Notes:

(1) Tested with 10/1000 µs pulse

(2) In part numbers, "xx" designates VWM and "nn" designates nominal voltage

(3) Nominal voltages are specified for part numbers with "nn" and minimum voltages are specified for part numbers with "xx" or (m) footnote. Higher voltages are planned (up to 600 V). Contact local sales office for availability

(4) Types are offered in bi-directional polarity by adding suffix "CA" (BZW04 use suffix "B")

(5) Uni-directional polarity only

(6) Most Vishay TVS products have Underwriters Laboratory Recognition for the classification of protectors (QVGQ2) under the UL standard for safety 497B, and file number E136766 for both uni-directional and bi-directional devices. See the individual data sheets for specific information.

PAR® Automotive

Vishay's Automotive Transient Voltage Suppressors (TVS) using the patented PAR® process have superior stability and power handling capability over a wider temperature range (up to 185 °C) than other avalanche TVS diodes. The product portfolio includes devices specifically designed for load dump surge protection in both axial and surface-mount packages.

P _{PPM} (W) ⁽¹⁾	Device ⁽²⁾	Package		V _{WM} Range (V)	V _(BR) Range ⁽³⁾ (V)	V _(BR) Tolerance (Suffix)
		Family	Type			
250	TPSMPnn(A)	Surface Mount	DO-220AA (SMP)	5.5 - 5.8	6.8	5%(A)/10%(blank)
300	TPSMPnn(A)	Surface Mount	DO-220AA (SMP)	6.05 - 10.2	7.5 - 12	5%(A)/10%(blank)
400	TPSMPnn(A)	Surface Mount	DO-220AA (SMP)	10.5 to 36.8	13 to 43	5 % (A)/10 % (blank)
	TPSMAnn(A)	Surface Mount	DO-214AC (SMA)	5.5 to 36.8	6.8 to 43	5 % (A)/10 % (blank)
	IMPG06-nn(A)	Plastic Axial	MPG06	8.1 to 36.8	10 to 43	5 % (A)/10 % (blank)
	P4KAnn(A)	Plastic Axial	DO-204AL (DO to 41)	5.5 to 36.8	6.8 to 43	5 % (A)/10 % (blank)
600	TA6FnnA	Surface Mount	DO-220A (SlimSMA)	5.8 to 43.6	6.8 to 51	5 %
	TPSMBnn(A)	Surface Mount	DO-214AA (SMB)	5.5 to 36.8	6.8 to 43	5 % (A)/10 % (blank)
	P6KAnn(A)	Plastic Axial	DO-204AC (DO to 15)	5.5 to 36.8	6.8 to 43	5 % (A)/10 % (blank)
	TPCnn(A)	Surface Mount	TO-277A (SMPC)	5.5 to 43.6	6.8 to 51	5 % (A)/10 % (blank)
1500	TPSMCnn(A)	Surface Mount	DO-214AB (SMC)	5.5 to 40.2	6.8 to 47	5 % (A)/10 % (blank)
	1.5KAnn(A)	Plastic Axial	1.5KA	5.5 to 40.2	6.8 to 47	5 % (A)/10 % (blank)
3000	3KASMCnn(A)	Surface Mount	DO-214AB (SMC)	10 to 43	11.1 to 52.8	5 % (A)/10 % (blank)
3600 ⁽⁴⁾	SM5A27	Surface Mount	DO-218AB	22	27	±3 V
	SM5A27T	Surface Mount	DO-218AB	22	27	±3 V
	SM5Sxx(A)	Surface Mount	DO-218AB	10 to 36	11.1 to 40	5 % (A)/10 % (blank)
4600 ⁽⁴⁾	SM6A27	Surface Mount	DO-218AB	22	27	±3 V
	SM6A27T	Surface Mount	DO-218AB	22	27	±3 V
	SM6Sxx(A)	Surface Mount	DO-218AB	10 to 36	11.1 to 40	5 % (A)/10 % (blank)
5000	5KASMCxxA	Surface Mount	DO-214AB (SMC)	10 to 43	11.1 to 47.8	5 %
6000 ⁽⁴⁾	6KA24	Plastic Axial	P600	24	29.7	10 %
6600 ⁽⁴⁾	SM8A27	Surface Mount	DO-218AB	22	27	±3 V
	SM8A27T	Surface Mount	DO-218AB	22	27	±3 V
	SM8Sxx(A)	Surface Mount	DO-218AB	10 to 43	11.1 to 47.8	5 % (A)/10 % (blank)

Notes:

(1) Tested with 10/1000 µs pulse

(2) In part numbers, "xx" designates VWM and "nn" designates nominal voltage

(3) Nominal voltages are specified for part numbers with "nn" and minimum voltages are specified for part numbers with "xx"

(4) For 10 µs/10 ms load-dump pulse rating, see datasheet

(5) All automotive TVS are uni-directional polarity only

(6) All automotive TVS use the patented PAR process for superior high-temperature performance

(7) Most Vishay TVS products have Underwriters Laboratory Recognition for the classification of protectors (QVGQ2) under the UL standard for safety 497B, and file number E136766 for both uni-directional and bi-directional devices. See the individual data sheets for specific information.



DIODES

Special Function Transient Voltage Suppressors

Special Function Transient Voltage Suppressor

Low Capacitance Transient Voltage Suppressors

P _{PPM} ⁽¹⁾ (W)	Device ⁽²⁾	Package		V _{WM} Range (V)	V _(BR) Range ⁽³⁾ (V)	V _(BR) Tolerance (Suffix)
		Family	Type			
500	SACxx	Plastic Axial	DO-204AC (DO-15)	5.0 to 50	7.6 to 55.5	N/A
1500	LCExx(A)	Plastic Axial	1.5KE	6.5 to 28	7.22 to 31.1	5 %(A)/10 %(blank)

Low Forward Voltage Transient Voltage Suppressors

P _{PPM} ⁽¹⁾ (W)	Device ⁽²⁾	Package		V _{WM} (V)	V _(BR) Range ⁽³⁾ (V)	Max I _D @ V _{WM} (μA)
		Family	Type			
600	LVB14A	Surface Mount	DO-214AA (SMB)	12	13.2 to 14.8	5%

Notes:

(1) Tested with 10/1000 μs pulse

(2) In part numbers, "xx" designates VWM and "nn" designates nominal voltage

(3) Nominal voltages are specified for part numbers with "nn" and minimum voltages are specified for part numbers with "xx" or (m) footnote

TVS Package Dimensions

Surface-Mount	Length	Width	Height
DO-218AB	13.5	8.5	4.85
DO-214AA (SMB J)	4.3	3.6	2.3
DO-214AB (SMC J)	6.8	5.9	2.3
DO-214AC (SMA)	4.2	2.6	2.14
DO-215AA (SMB G)	4.3	3.6	2.3
DO-215AB (SMC G)	6.8	5.9	2.3
Micro SMP	2.2	1.3	0.65
DO-220AA (SMP)	3.4	2	1
DO-221AC (SlimSMA)	5.2	2.6	0.95
TO-277A (SMPC)	6.1	4.3	1.1

Axial	Body Length	Body Diameter	Lead Length	Lead Diameter
MPG06	3.1	2.4	25.4	0.61
DO-204AL (DO-41)	4.6	2.4	25.4	0.79
DO-204AC (DO-15)	6.7	3.1	25.4	0.79
1.5KE	8.4	5.1	25.4	1.02
P600	8.8	8.8	25.4	1.27

Unit: Millimeter



DIODES

ESD Protection Devices and EMI Filters

ESD Protection Devices

Part Number	Package Name	V _{RWM} Working Range	I _R Reverse Leakage Current @ V _{RWM}	V _{BR min} Break Down Voltage @1mA (*)=10mA	V _C Clamping Voltage @ I _{PPM}	I _{PPM} Peak Pulse Current acc. IEC 61000-4-5@8/20µs (*) = @ 10/1000	P _{PP} Peak Pulse Power acc. IEC 61000-4-5 @ 8/20µs (*) = @ 10/1000	C _D max. Load Capacitance @ V _R = 0 V	ESD acc. Immunity IEC 61000-4-2 contact discharge	Number of Protected Lines		
		(V)	(µA)	(V)	(V)	[A]	(W)	(pF)	(kV)	BiAs	BiSy	Uni
BZG04-8V2	DO214AC(SMA)	8.2	20	9 (*)	14.8 (*)	20.3 (*)	300 (*)	1200	30	1		
BZG04-9V1	DO214AC(SMA)	9.1	5	10 (*)	15.7 (*)	19.1 (*)	300 (*)	1100	30	1		
BZG04-10	DO214AC(SMA)	10	5	11 (*)	17 (*)	17.7 (*)	300 (*)	1000	30	1		
BZG04-11	DO214AC(SMA)	11	5	12 (*)	18.9 (*)	15.9 (*)	300 (*)	850	30	1		
BZG04-12	DO214AC(SMA)	12	5	14 (*)	20.9 (*)	14.4 (*)	300 (*)	815	30	1		
BZG04-13	DO214AC(SMA)	13	5	15 (*)	22.9 (*)	13.1 (*)	300 (*)	785	30	1		
BZG04-15	DO214AC(SMA)	15	5	17 (*)	25.6 (*)	11.7 (*)	300 (*)	710	30	1		
BZG04-16	DO214AC(SMA)	16	5	19 (*)	28.4 (*)	10.6 (*)	300 (*)	655	30	1		
BZG04-18	DO214AC(SMA)	18	5	21 (*)	31 (*)	9.7 (*)	300 (*)	610	30	1		
BZG04-20	DO214AC(SMA)	20	5	23 (*)	33.8 (*)	8.9 (*)	300 (*)	570	30	1		
BZG04-22	DO214AC(SMA)	22	5	25 (*)	38.1 (*)	7.9 (*)	300 (*)	545	30	1		
BZG04-24	DO214AC(SMA)	24	5	28 (*)	42.2 (*)	7.1 (*)	300 (*)	505	30	1		
BZG04-27	DO214AC(SMA)	27	5	31 (*)	46.2 (*)	6.5 (*)	300 (*)	475	30	1		
BZG04-30	DO214AC(SMA)	30	5	34 (*)	50.1 (*)	6 (*)	300 (*)	450	30	1		
BZG04-33	DO214AC(SMA)	33	5	37 (*)	54.1 (*)	5.5 (*)	300 (*)	420	30	1		
BZG04-36	DO214AC(SMA)	36	5	40 (*)	60.7 (*)	4.9 (*)	300 (*)	390	30	1		
BZG04-39	DO214AC(SMA)	39	5	44 (*)	65.5 (*)	4.6 (*)	300 (*)	370	30	1		
BZG04-43	DO214AC(SMA)	43	5	48 (*)	70.8 (*)	4.2 (*)	300 (*)	350	30	1		
BZG04-47	DO214AC(SMA)	47	5	52 (*)	78.6 (*)	3.8 (*)	300 (*)	330	30	1		
BZG04-51	DO214AC(SMA)	51	5	58 (*)	86.5 (*)	3.5 (*)	300 (*)	310	30	1		
BZG04-56	DO214AC(SMA)	56	5	64 (*)	94.4 (*)	3.2 (*)	300 (*)	291	30	1		
BZG04-62	DO214AC(SMA)	62	5	70 (*)	103.5 (*)	2.9 (*)	300 (*)	280	30	1		
BZG04-68	DO214AC(SMA)	68	5	77 (*)	114 (*)	2.6 (*)	300 (*)	275	30	1		
BZG04-75	DO214AC(SMA)	75	5	85 (*)	126 (*)	2.4 (*)	300 (*)	260	30	1		
BZG04-82	DO214AC(SMA)	82	5	94 (*)	139 (*)	2.2 (*)	300 (*)	250	30	1		
BZG04-91	DO214AC(SMA)	91	5	104 (*)	152 (*)	2 (*)	300 (*)	243	30	1		
BZG04-100	DO214AC(SMA)	100	5	114 (*)	167 (*)	1.8 (*)	300 (*)	170	30	1		
BZG04-110	DO214AC(SMA)	110	5	124 (*)	185 (*)	1.6 (*)	300 (*)	153	30	1		
BZG04-120	DO214AC(SMA)	120	5	138 (*)	204 (*)	1.5 (*)	300 (*)	150	30	1		
BZG04-130	DO214AC(SMA)	130	5	153 (*)	224 (*)	1.3 (*)	300 (*)	145	30	1		
BZG04-150	DO214AC(SMA)	150	5	168 (*)	249 (*)	1.2 (*)	300 (*)	140	30	1		
BZG04-160	DO214AC(SMA)	160	5	188 (*)	276 (*)	1.1 (*)	300 (*)	135	30	1		
BZG04-180	DO214AC(SMA)	180	5	208 (*)	305 (*)	1 (*)	300 (*)	131	30	1		
BZG04-200	DO214AC(SMA)	200	5	228 (*)	336 (*)	0.9 (*)	300 (*)	122	30	1		
BZG04-220	DO214AC(SMA)	220	5	251 (*)	380 (*)	0.8 (*)	300 (*)	120	30	1		
GL05T	SOT-23	5	20	6	-	17	300	5	25			1
GL12T	SOT-23	12	1	13.3	-	12	300	5	25			1
GL15T	SOT-23	15	1	16.7	-	10	300	5	25			1
GL24T	SOT-23	24	1	26.7	55	5	300	5	25			1
GMF05C-HSF	LLP75-6L	5	1	6	12.5	12	200	150	30	5	4	
GMF05LC-HSF	LLP75-6L	5	0.1	6	12.5	5	70	50	30	5	4	
GSOT03	SOT-23	3.3	100	4	12.3	30	369	600	30	1		
GSOT03C	SOT-23	3.3	100	4	12.3	30	369	600	30	2	1	
GSOT04	SOT-23	4	20	5	14.3	30	429	450	30	1		

1) BiAs = Bidirectional and Asymmetrical clamping performance - protects in both directions but with different clamping levels

BiSy = Bidirectional and Symmetrical Clamping performance - protects in both directions with the same clamping level

Uni = Unidirectional clamping performance - protects only in one direction



DIODES

ESD Protection Devices and EMI Filters

ESD Protection Devices, (cont'd.)

Part Number	Package Name	V _{RWM} Working Range	I _R Reverse Leakage Current @ V _{RWM}	V _{BR min} Break Down Voltage @1mA (*)=10mA	V _C Clamping Voltage @ I _{PPM}	I _{PPM} Peak Pulse Current acc. IEC 61000-4-5 @ 8/20µs (*) = @ 10/1000	P _{PP} Peak Pulse Power acc. IEC 61000-4-5 @ 8/20µs (*) = @ 10/1000	C _D max. Load Capacitance @ V _R = 0 V	ESD acc. Immunity IEC 61000-4-2 contact discharge	Number of Protected Lines		
		(V)	(µA)	(V)	(V)	[A]	(W)	(pF)	(kV)	BiAs	BiSy	Uni
GSOT04C	SOT-23	4	20	5	14.3	30	429	450	30	2	1	
GSOT05	SOT-23	5	10	6	16	30	480	350	30	1		
GSOT05C	SOT-23	5	10	6	16	30	480	350	30	2	1	
GSOT08	SOT-23	8	5	9	19.2	18	345	250	30	1		
GSOT08C	SOT-23	8	5	9	19.2	18	345	250	30	2	1	
GSOT12	SOT-23	12	1	13.5	26	12	312	150	30	1		
GSOT12C	SOT-23	12	1	13.5	26	12	312	150	30	2	1	
GSOT15	SOT-23	15	1	16.5	28.8	8	230	120	30	1		
GSOT15C	SOT-23	15	1	16.5	28.8	8	230	120	30	2	1	
GSOT24	SOT-23	24	1	27	47	5	235	80	30	1		
GSOT24C	SOT-23	24	1	27	47	5	235	80	30	2	1	
GSOT36	SOT-23	36	1	39	71	3.5	248	65	30	1		
GSOT36C	SOT-23	36	1	39	71	3.5	248	65	30	2	1	
SMF5V0A	SMF	5	5	6.4 *	9.2 (*)	21.7 (*)	1000	1120	30	1		
SMF6V0A	SMF	6	26	6.67 *	10.3 (*)	19.4 (*)	1000	1063	30	1		
SMF6V5A	SMF	6.5	20	7.22 *	11.2 (*)	17.9 (*)	1000	938	30	1		
SMF7V0A	SMF	7	3	7.78 *	12 (*)	16.7 (*)	1000	843	30	1		
SMF7V5A	SMF	7.5	0.1	8.33	12.9 (*)	15.5 (*)	1000	773	30	1		
SMF8V0A	SMF	8	0.1	8.89	13.6 (*)	14.7 (*)	1000	706	30	1		
SMF8V5A	SMF	8.5	0.1	9.44	14.4 (*)	13.9 (*)	1000	674	30	1		
SMF9V0A	SMF	9	0.1	10	15.4 (*)	13.5 (*)	1000	640	30	1		
SMF10A	SMF	10	0.1	11.1	17 (*)	11.8 (*)	1000	562	30	1		
SMF11A	SMF	11	0.1	12.2	18.2 (*)	11 (*)	1000	509	30	1		
SMF12A	SMF	12	0.1	13.3	19.9 (*)	10.1 (*)	1000	483	30	1		
SMF13A	SMF	13	0.1	14.4	21.5 (*)	9.3 (*)	1000	423	30	1		
SMF14A	SMF	14	0.1	15.6	23.2 (*)	8.6 (*)	1000	392	30	1		
SMF15A	SMF	15	0.1	16.7	24.4 (*)	8.2 (*)	1000	367	30	1		
SMF16A	SMF	16	0.1	17.8	26 (*)	7.7 (*)	1000	343	30	1		
SMF17A	SMF	17	0.1	18.9	27.6 (*)	7.2 (*)	1000	324	30	1		
SMF18A	SMF	18	0.1	20	29.2 (*)	5.8 (*)	1000	320	30	1		
SMF20A	SMF	20	0.1	22.2	32.4 (*)	6.2 (*)	1000	283	30	1		
SMF22A	SMF	22	0.1	24.4	35.5 (*)	5.6 (*)	1000	271	30	1		
SMF24A	SMF	24	0.1	26.7	38.9 (*)	5.1 (*)	1000	244	30	1		
SMF26A	SMF	26	0.1	28.9	42.1 (*)	4.8 (*)	1000	230	30	1		
SMF28A	SMF	28	0.1	31.1	45.4 (*)	4.4 (*)	1000	227	30	1		
SMF30A	SMF	30	0.1	33.3	48.4 (*)	4.1 (*)	1000	207	30	1		
SMF33A	SMF	33	0.1	36.7	53.3 (*)	3.8 (*)	1000	198	30	1		
SMF36A	SMF	36	0.1	40	58.1 (*)	3.4 (*)	1000	178	30	1		
SMF40A	SMF	40	0.1	44.4	64.5 (*)	3.1 (*)	1000	172	30	1		
SMF43A	SMF	43	0.1	47.8	69.4 (*)	2.9 (*)	1000	165	30	1		
SMF45A	SMF	45	0.1	50	72.7 (*)	2.8 (*)	1000	162	30	1		

1) BiAs = Bidirectional and Asymmetrical clamping performance - protects in both directions but with different clamping levels

BiSy = Bidirectional and Symmetrical Clamping performance - protects in both directions with the same clamping level

Uni = Unidirectional clamping performance - protects only in one direction!



DIODES

ESD Protection Devices and EMI Filters

ESD Protection Devices, (cont'd.)

Part Number	Package Name	V _{RWM} Working Range	I _R Reverse Leakage Current @ V _{RWM}	V _{BR min} Break Down Voltage @1mA (*)=10mA	V _C Clamping Voltage @ I _{PPM}	I _{PPM} Peak Pulse Current acc. IEC 61000-4-5 @ 8/20µs (*) = @ 10/1000	P _{PP} Peak Pulse Power acc. IEC 61000-4-5 @ 8/20µs (*) = @ 10/1000	C _D max. Load Capacitance @ V _R = 0 V	ESD acc. Immunity IEC 61000-4-2 contact discharge	Number of Protected Lines		
		(V)	(µA)	(V)	(V)	[A]	(W)	(pF)	(kV)	BiAs	BiSy	Uni
SMF48A	SMF	48	0.1	53.3	77.4 (*)	2.6 (*)	1000	161	30	1		
SMF51A	SMF	51	0.1	56.7	82.4 (*)	2.4 (*)	1000	151	30	1		
SMF54A	SMF	54	0.1	60	87 (*)	2.3 (*)	1000	148	30	1		
SMF58A	SMF	58	0.1	64.4	93 (*)	2.1 (*)	1000	144	30	1		
VBUS051BD-HD1	LLP1006-2L	5	0.1	6.9	16	3	45	1.3	15	1		
VBUS051CD-HD1	LLP1006-2L	5.5	0.1	6.5	14	2	28	0.8	15	1		
VBUS052BD-HTF	LLP75-4L	5	0.1	6.9	16	3	45	2.5	15	2		
VBUS052CD-FAH	LLP1713-7L	5	0.1	6.9	18	3.5	63	1	15	2		
VBUS053AZ-HAF (Pin 1,2,3 to 7)	LLP75-7L	5.5	0.1	6.5	18	3	36	1	15	3		
VBUS053AZ-HAF (Pin 6 to 7)	LLP75-7L	12	0.1	15	30	8	240	80	30	1		
VBUS053BZ-HNH (Pin 1-3 to 9)	LLP1713-9L	5.5	1	6.5	18	3	36	1	12	3		
VBUS053BZ-HNH (Pin 4 to 9)	LLP1713-9L	12	0.1	15	30	8	240	85	30	1		
VBUS053CZ-HAF (Pin 1,2,3 to 7)	LLP75-7L	5.5	1	6.5	18	3	36	1	15	3		
VBUS053CZ-HAF (Pin 6 to 7)	LLP75-7L	28	0.1	32	60	3	180	50	30	1		
VBUS054B-HSF	LLP75-6L	5	0.1	6.3	15	3	45	1	15	4		
VBUS054CD-FHI	LLP2513-11L	5	0.1	6.9	18	3.5	63	1	15	4		
VBUS054CV-HSF	LLP75-6L	5	0.1	6	22	11	242	2.5	30	4		
VBUS054DD-HF4	LLP1010-5L	5	0.1	6.9	19	3	57	1	15	4		
VBUS054DD-HS4	LLP1010-6M	5.5	0.1	6.9	19	3	57	1	15	4		
VBUS05L1-DD1	LLP1006-2M	5.5	0.05	7	17	2	34	0.4	15		1	
VBUS054ED-FBL	LLP2510-10L	5.5	0.1	6.9	12.5	2	25	0.8	15	4		
VCUT03B1-DD1	LLP1006-2M	3.5	0.1	5.8	11.5	3.5	40	15	18		1	
VCUT0505B-HD1	LLP1006-2L	5	0.1	7	16	3.5	56	20	20		1	
VCUT05B1-DD1	LLP1006-2M	5.5	0.1	6	12.5	3	38	13	30		1	
VCUT05D1-SD0	CLP0603	5.5	0.1	6	14	6	78	14	30		1	
VBUS05A1-SD0	CLP0603	5.5	0.1	6	18	2.5	45	0.8	13		1	
VCUT07B1-HD1	LLP1006-2L	7	0.1	7.3	15	4	60	16	30		1	
VCUT0714A-HD1	LLP1006-2L	14	0.1	14.5	30	2	54	8.5	25	1	1	
VCUT0714A-HD1	LLP1006-2L	7	0.1	7.3	17	5	85	8.5	25	1	1	
VESD01-02V	SOD-523	1	100	1.5	9	7	63	180	8	1		
VESD03-02V	SOD-523	3	20	4	12	9	108	110	8	1		
VESD03A1B-HD1	LLP1006-2L	3.3	0.5	5	9	3.5	31	28	30	1		
VESD03A1C-HD1	LLP1006-2L	3.3	1	5	10	9.5	95	90	30	1		
VESD05-02V	SOD-523	5	0.1	6.5	20	6	120	55	8	1		
VESD05A1-02V	SOD-523	5	1	6	12	16	192	150	30	1		
VESD05A1A-HD1	LLP1006-2L	5	1	6	12	16	192	150	30	1		

1) BiAs = Bidirectional and Asymmetrical clamping performance - protects in both directions but with different clamping levels

BiSy = Bidirectional and Symmetrical Clamping performance - protects in both directions with the same clamping level

Uni = Unidirectional clamping performance - protects only in one direction!



DIODES

ESD Protection Devices and EMI Filters

ESD Protection Devices, (cont'd.)

Part Number	Package Name	V _{RWM} Working Range	I _R Reverse Leakage Current @ V _{RWM}	V _{BR min} Break Down Voltage @1mA (*)=10mA	V _C Clamping Voltage @ I _{PPM}	I _{PPM} Peak Pulse Current acc. IEC 61000-4-5@8/20μs (*) = @ 10/1000	P _{PP} Peak Pulse Power acc. IEC 61000-4-5 @ 8/20μs (*) = @ 10/1000	C _D max. Load Capacitance @ V _R = 0 V	ESD acc. Immunity IEC 61000-4-2 contact discharge	Number of Protected Lines		
		(V)	(μA)	(V)	(V)	[A]	(W)	(pF)	(kV)	BiAs	BiSy	Uni
VESD05A1B-02V	SOD-523	5	0.1	6	11	3	33	23	20	1		
VESD05A1B-HD1	LLP1006-2L	5	0.1	6	11	3	33	23	30	1		
VESD05A1C-HD1	LLP1006-2L	5	0.2	6	10	8	80	63	30	1		
VESD05A4A-HS4	LLP1010-6L	5	0.1	6	12	2.5	30	15	15	4	3	
VESD05A5A-HSF	LLP75-6L	5	0.1	6	13	2.5	33	15	15	5	4	
VESD05A6A-HAF	LLP75-7L	5	0.1	6	13	2.5	33	15	15	6	5	
VESD05A6-HAF	LLP75-7L	5	1	6	12	5	60	50	30	6	5	
VESD05A8A-HNH	LLP1713-9L	5	1	6	13	5	65	35	25	8	7	
VESD05A8B-HNH	LLP1713-9L	5	0.5	6	13	4	52	23	17	8	7	
VESD05A8C-HNH	LLP1713-9L	5	0.1	6	13	2.5	33	13	8	8	7	
VESD08-02V	SOD-523	8	0.1	9	30	4	120	35	8	1		
VESD09A4A-HS4	LLP1010-6L	9	0.1	11.2	23	1.5	30	10	8	4		
VESD09A4A-HSF	LLP75-6L	9	0.1	11.2	23	1.5	30	10	8	4		
VESD12-02V	SOD-523	12	0.1	14	25	2	50	30	8	1		
VESD12A1A-HD1	LLP1006-2L	12	0.1	13.5	24	8	200	65	30	1		
VESD12A1C-HD1	LLP1006-2L	12	0.1	13.5	23	4	92	36	30	1		

1) **BiAs** = Bidirectional and **Asymmetrical** clamping performance - protects in both directions but with different clamping levels

BiSy = Bidirectional and **Symmetrical** Clamping performance - protects in both directions with the same clamping level

Uni = Unidirectional clamping performance - protects only in one direction!



DIODES

EMI Filter devices with ESD Protection

Part Number	Package Name	V _{RWM} Working Range	I _R Reverse Leakage Current @ V _{RWM}	V _{BR} min Break Down Voltage @ 1mA (*)= 10mA	V _C Clamping Voltage @ I _{PPM}	I _{PPM} Peak Pulse Current acc. IEC 61000-4-5 @ 8/20 μs (*)= @10/1000	C _D max.Load Capaci- tance @ V _R = 0 V	ESD- Immunity acc. IEC 61000- 4-2 contact discharge	Number of protected lines
		(V)	(μA)	(V)	(V)	(A)	(pF)	(kV)	BiAs
VEMI353A-HAF	LLP75-7L	5	1	6	8	4	60	30	3
VEMI355A-HAF	LLP75-7L	5	1	6	8	4	60	30	3
VEMI35AA-HAF	LLP75-7L	5	1	6	8	4	60	30	3
VEMI45AA-HNH	LLP1713-9L	5	1	6	8	4	60	30	4
VEMI45AB-HNH	LLP1713-9L	5	1	6	8	4	40	18	4
VEMI45AC-HNH	LLP1713-9L	5	1	6	8	2	20	10	4
VEMI65AA-HCI	LLP2513-13L	5	1	6	8	4	60	30	6
VEMI65AB-HCI	LLP2513-13L	5	1	6	8	4	40	18	6
VEMI65AC-HCI	LLP2513-13L	5	1	6	8	2	20	10	6
VEMI85AA-HGK	LLP3313-17L	5	1	6	8	4	60	30	8
VEMI85AB-HGK	LLP3313-17L	5	1	6	8	4	40	18	8
VEMI85AC-HGK	LLP3313-17L	5	1	6	8	2	20	10	8

2) **BiAs** = **B**idirectional and **A**symmetrical clamping performance - protects in both directions but with different clamping levels

ESD Package Dimensions

Surface-Mount	Length	Width	Height
CLP0603	0.6	0.3	0.27
SOD-523	1.6	0.8	0.6
SMF	3.7	1.8	0.98
LLP75-4L	1.6	1.6	0.57
LLP75-6A	1.6	1.6	0.75
LLP75-6L	1.6	1.6	0.57
LLP75-7L	1.6	1.6	0.57
LLP1006-2L/LLP1006-2M	1.0	0.6	0.38
LLP1010-6L	1.0	1.0	0.38
LLP1713-9L	1.7	1.35	0.55
LLP2513-13L	2.5	1.35	0.55
LLP3313-17L	3.3	1.35	0.55
LLP1010-5L	1.0	1.0	0.38
LLP1713-7L	1.7	1.35	0.55
LLP2510	2.5	1.35	0.55
LLP2513-11L	2.5	1.35	0.55
SOT-23	2.85	2.50	1.0



DIODES

Power Voltage-Regulating Diodes

Power Voltage-Regulating Diodes

PPPM ⁽¹⁾	Device ⁽¹⁾	Package	Zener Voltage Range	Zener Voltage Tolerances
(mW)			$V_z(V)$	(Suffix)
1000.0	ZGL41nnA	DO213AB (MELF)	100 - 200	5%
1500	PTV3.9B - PTV36B	DO-220AA (SMP)	3.9 - 36	5%
	SMAZ5919B - SMAZ5945B	DO-214AC (SMA)	5.6 - 68	5%
	SMPZ3919B - SMPZ3940B	DO-220AA (SMP)	5.6 - 43	5%
	SMZG3788B - SMZG3809B	DO-215AA (SMBG)	9.1 - 68	5%
	SMZJ3788B - SMZJ3809B	DO-214AA (SMBJ)	9.1 - 68	5%
	Z4KEnnA	DO-204AL (DO-41)	100 - 200	5%
3000.0	SMBZ5919B - SMBZ5945B	DO-214AA (SMBJ)	5.6 - 68	5%

(1) In part numbers, "nn" designates nominal voltage

(2) Most Vishay TVS products have Underwriters Laboratory Recognition for the classification of protectors (QVGG2) under the UL standard for safety 497B, and file number E136766 for both uni-directional and bi-directional devices. See the individual data sheets for specific information.



DIODES Packages

Diodes - Protect Against Transient Voltage Surge and ESD

DO-218AB

DO-214AB (SMC J)

DO-215AB (SMC G)

DO-215AA (SMB G)

DO-214AA (SMB-J)

TO-277A (SMPC)

DO-214AC (SMA)

MPG06

DO-204AL (DO-41)

DO-204AC (DO-15)

DO-220AA (SMP)

Micro SMP

1.5KE

DO-221AC (SlimSMA)

P600



DIODES
Packages

Diodes - Protect Against Transient Voltage Surge and ESD


CLP0603




SOD-523



SMF




LLP75-4L




LLP2510




LLP75-6A



LLP75-6L



LLP75-7L



LLP1006-2L
LLP1006-2M




LLP1010-6L




LLP1010-5L




LLP1713-9L




LLP1713-7L




LLP2513-13L




LLP2513-11L



LLP3313-17L



SOT-23





DIODES

TVS and ESD Protection

Diodes - Protect Against Transient Voltage Surge and ESD

Notes:



DIODES

TVS and ESD Protection

Diodes - Protect Against Transient Voltage Surge and ESD

Notes:



DIODES

TVS and ESD Protection

Diodes - Protect Against Transient Voltage Surge and ESD

Notes:

**DIODES****TVS and ESD Protection****WORLDWIDE SALES CONTACTS****THE AMERICAS****UNITED STATES**

VISHAY AMERICAS
ONE GREENWICH PLACE
SHELTON, CT 06484
UNITED STATES
PH: +1-402-563-6866
FAX: +1-402-563-6296

ASIA**SINGAPORE**

VISHAY INTERTECHNOLOGY ASIA PTE LTD.
37A TAMPINES STREET 92 #07-00
SINGAPORE 528886
PH: +65-6788-6668
FAX: +65-6788-0988

P.R. CHINA

VISHAY CHINA CO., LTD.
15D, SUN TONG INFOPORT PLAZA
55 HUAI HAI WEST ROAD
SHANGHAI 200030
P.R. CHINA
PH: +86-21-5258 5000
FAX: +86-21-5258 7979

JAPAN

VISHAY JAPAN CO., LTD.
SHIBUYA PRESTIGE BLDG. 4F
3-12-22, SHIBUYA
SHIBUYA-KU
TOKYO 150-0002
JAPAN
PH: +81-3-5466-7150
FAX: +81-3-5466-7160

EUROPE**GERMANY**

VISHAY ELECTRONIC GMBH
DR.-FELIX-ZANDMAN-PLATZ 1
95100 SELB
GERMANY
PH: +49-9287-71-0
FAX: +49-9287-70435

FRANCE

VISHAY S.A.
199, BD DE LA MADELEINE
06003 NICE, CEDEX 1
FRANCE
PH: +33-4-9337-2727
FAX: +33-4-9337-2726

UNITED KINGDOM

VISHAY LTD.
SUITE 6C, TOWER HOUSE
ST. CATHERINE'S COURT
SUNDERLAND ENTERPRISE PARK
SUNDERLAND SR5 3XJ
UNITED KINGDOM
PH: +44-191-516-8584
FAX: +44-191-549-9556