

Amphenol

Australia



ENTERTAINMENT@AMPHENOL
TRUSTED GLOBALLY

ENTERTAINMENT INTERCONNECT CATALOGUE



Amphenol Australia Pty. Ltd.

Amphenol Australia's head office is based in Melbourne, Victoria and is the Sales, Marketing and Engineering centre of excellence for an extensive range of professional connector and cabling products.

Amphenol's global presence allows us to take full advantage of our numerous corporate resources and product portfolio to provide you with a vast offering and choice. Our extensive range is designed to meet the specific needs of the entertainment markets to make the selection of your interconnect partner an easy choice.

The company has been producing products for the pro-audio industry for over fifty years. Since the development of our XLR AC Series connectors, we have continued to provide our customers with exacting quality in an increasingly competitive environment.

Continuous improvement through ISO9001, a focus on environmental awareness and development of next generation industry leading products is our philosophy. As the entertainment industry moves into the future the emerging technologies from other industries has become more prevalent and more challenging. Amphenol Australia's global presence combined with its close technical relationships with other Amphenol sister divisions, each a specialist and leader in their own interconnect field, places it well to support innovation and meet this challenge head on.

The ability of Amphenol to provide a full range of design services required to support the customers applications design and modelling, applications engineering, fabrication, value-added assembly and testing, coupled with the largest interconnect offering on the market means that we can support all of your system level needs.

CONTENTS



XLR Connectors

AX Series Cable Connectors	2
AC Series Cable Connectors	9
AC Series PCB Chassis Mount (A Type)	25
AC Series PCB Chassis Mount (B Type)	28
AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount	38
G-Type Miniature XLR Connectors	47



Plugs & Jacks

T-Series Plugs	93
T-Series SwitchPlug	97
Q-Series Plugs	99
Musician Series II Plugs	101
Musician / OEM Range 1/4" Phone Jacks	106
K-Series Plugs (3.5mm) Plugs	117
RCA Series	120



Data Connectors

Amphe-Dante Connectors	69
XLRnet RJ45 Ethernet Series	72
USB/HDMI Chassis Mount	84



Speaker Connectors

SP Series	52
EP Series	61
AP Series	63



Coax Connectors

BNC 75Ω RF Connectors	85
BNC Patch Panels	88



Power Connectors

HP Series	66
HPT Series	68



Multipin Connectors

MP-41 Series	124
MP-62 / MP-65 Series	129



Miscellaneous

Accessories	132
Connector Wiring Information	136

XLR Connectors

AX Series Cable Connectors



The revolutionary AX series of XLR connectors introduce an exciting contemporary look and feel to the professional audio interconnect market. They are designed to complement modern audio architecture and truly "fit" within their environment. An impressive list of features guarantees pure sound performance in the most demanding applications providing unrivalled value.

Features

- Unique Australian designed shell and housing.
- One piece ground / latch spring design incorporating twin wipe contacts for a direct connection path from mating shell to ground providing enhanced connection and EMI performance.
- Ergonomic sleeve design for improved grip.
- Channel I.D capability with coloured sleeves.
- Oversized ergonomic latch for quick and easy mating.
- Leading first mate last break pin 1 on socket connectors.
- Chuck style cable clamp to suit 3mm - 8mm (0.118" - 0.314") cable O.D. with integrated split to allow inclusion after soldering.
- Concealed latching point for improved aesthetics, sealing and strength.
- Overmolded boot with flex bend relief for improved aesthetics, cable protection and boot retention.
- Concentric socket contact design provides optimal contact resistance
- Precision machined pin contacts as standard.
- Compact solder buckets to reduce termination time and material wastage during the soldering process.
- Zinc diecast shell housing for robustness and wear with Satin nickel or Black finish.
- Available in 3,4 and 5 contact arrangements.

Options

- Coloured I.D sleeves.
- Satin nickel or Black shell finish.
- Single or Bulk packaging.
- Gold plated contacts.

Ordering Codes

We have listed the more common ordering codes in each section. For further options please refer to the part number breakdown charts. Please contact us if you need any further assistance.

AX SERIES XLR CABLE CONNECTORS

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.



Features:

- Unique Australian designed shell and housing.
- Ergonomic stylish sleeve design for improved grip.
- Oversized latch lever preserves your thumb.
- Leading first mate last break pin 1 on socket connectors.
- Chuck style cable clamp to suit 3mm - 8mm (0.118" - 0.314") cable O.D. with integrated split to allow inclusion after soldering.
- Overmolded cable support boot.
- New socket contact design for improved contact resistance.
- Precision machined pin contacts as standard.
- Compact solder buckets to reduce soldering time and wastage.
- Zinc diecast shell housing with Satin nickel or Matt black finish.
- Available in 3,4 and 5 contact arrangements.

Options:

- Coloured I.D sleeves.
- Satin nickel or Matt black shell finish.
- Single or Bulk packaging.

Part Number Breakdown: Page 5

Specifications: Page 8

Assembly Instructions: Page 6 & 7

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		71 - 74 [2.80-2.90"]	XLR 3 pole male Machined contacts Nickel Finish	Standard	AX3M
				Bulk Pack	AX3M BULK
		71 - 74 [2.80-2.90"]	XLR 3 pole male Machined contacts Black Finish	Standard	AX3MB
				Gold Plated Contacts	AX3MB-AU
				Bulk Pack	AX3MB BULK
		71 - 74 [2.80-2.90"]	XLR 3 pole female Stamped contacts Nickel Finish	Standard	AX3F
				Bulk Pack	AX3F BULK
		71 - 74 [2.80-2.90"]	XLR 3 pole female Stamped contacts Black Finish	Standard	AX3FB
				Gold Plated Contacts	AX3FB-AU
				Bulk Pack	AX3FB BULK
		71 - 74 [2.80-2.90"]	XLR 4 pole male Machined contacts Nickel Finish	Standard	AX4M
				Bulk Pack	AX4M BULK

*PI538 is available for download at www.amphenolaudio.com

XLR Connectors

AX Series Cable Connectors

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]	XLR 4 pole male Machined contacts Black Finish	Standard	AX4MB
				Gold Plated Contacts	AX4MB-AU
				Bulk Pack	AX4MB BULK
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]	XLR 4 pole female Machined contacts Nickel Finish	Standard	AX4F
				Bulk Pack	AX4F BULK
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]		Standard	AX4FB
				Gold Plated Contacts	AX4FB-AU
				Bulk Pack	AX4FB BULK
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]	XLR 5 pole male Machined contacts Nickel Finish	Standard	AX5M
				Bulk Pack	AX5M BULK
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]		Standard	AX5MB
				Gold Plated Contacts	AX5MB-AU
				Bulk Pack	AX5MB BULK
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]	XLR 5 pole female Machined contacts Nickel Finish	Standard	AX5F
				Bulk Pack	AX5F BULK
		71 - 74 [2.80-2.90"] Ø19.0 [0.748] Ø15.7 [0.618]		Standard	AX5FB
				Gold Plated Contacts	AX5FB-AU
				Bulk Pack	AX5FB BULK

PART NUMBER BREAKDOWN


METAL SHELL TYPE - SOLDER

E. G . **AX3MB2M-AU BULK**
AX (Series Prefix), 3 contacts, Male, Black Finish,
2 (Red Sleeve) M (Sleeve Marking) - AU (Gold Plated Contacts), Bulk Packaged.

SERIES PREFIX	AX	=	Series Prefix
CONTACT LAYOUTS	3	=	3 Contacts
	4	=	4 Contacts
	5	=	5 Contacts
GENDER	F	=	Female Socket Contacts
	M	=	Male Pin Contacts
SHELL FINISH	Blank	=	Nickel Plated Finish
	B	=	Black Finish
SLEEVE COLOUR OPTION	Blank	=	Black
	1	=	Brown
	2	=	Red
	3	=	Orange
	4	=	Yellow
	5	=	Green
	6	=	Blue
	7	=	Violet
	8	=	Grey
	9	=	White
SLEEVE MARKING	Blank	=	Standard Sleeve
	OM	=	Marking Sleeve (Black)
	M	=	Marking Sleeve (Colour)
CONTACT PLATING	Blank	=	Standard Plating (Silver or Tin) (Refer to Standard Data)
	AU	=	Gold Plated
PACKAGING	Blank	=	Individual Bags
	BULK	=	Bulk Packed


SERIES PREFIX
CONTACT LAYOUTS
GENDER
SHELL FINISH
SLEEVE COLOUR OPTION
SLEEVE MARKING
CONTACT PLATING
PACKAGING

AX 3 M B 2 M - AU BULK




XLR Connectors

AX Series Cable Connectors



Slide the nut (Backshell) onto the cable



Strip the cable



Push back the insert only enough to expose the solder buckets. It is not necessary to remove the insert. Solder the wires to the contacts.

1



Install the cable clamp, flush to the insert making sure to align the top slot with the spring. Then push the insert & cable clamp together into the shell.

4




Thread the nut (Backshell) onto the shell (Torque 0.8Nm - 1.2Nm) to activate the cable clamp and close the connector assembly.

5


PI539 ASSEMBLY INSTRUCTIONS

AX SERIES FEMALE XLR
CABLE CONNECTOR




6

Close the cable clamp slightly and push the boot over the clamp ensuring the wires fit inside the boot.




7


Final assembly can be achieved either by manually screwing the boot on, or by using an Amphenol Australia T2860 termination tool.



Slide the nut (Backshell) onto the cable



Strip the cable



Solder the wires to the contacts.



Install the cable clamp flush to the insert making sure to align the slot with the ground contact.



Align the key of the insert with the keyway on the shell then push the pin insert & cable clamp together in the shell.

PI538 ASSEMBLY INSTRUCTIONS

AX SERIES MALE XLR
CABLE CONNECTOR





Thread the nut (Backshell) onto the shell (Torque 0.8Nm - 1.2Nm) to activate the cable clamp and close the connector assembly.

XLR Connectors

AX Series Cable Connectors

STANDARD DATA AX SERIES CABLE CONNECTORS

		VALUE		
GENERAL CHARACTERISTICS	Number of contacts	3	4	5
	AX Series Contact Arrangements (Front view of pin inserts)			
	Termination	SOLDER		
	Max. Wire Gauge - Stranded wire: Solder	14AWG	16AWG	18AWG
	Flammability rating of insulator plastics and housings	UL94V-0		
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU		
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	133V ¹⁾		
	Test Voltage AC RMS	1400V		
	Current carrying capacity: Solder	15A	10A	7.5A
	Typical Contact Resistance	≤3mΩ		
	Insulation Resistance	≥1GΩ		
CLIMATIC CHARACTERISTICS	Protection Class	IP40		
	Operating Temperature	-25°C to +75°C (-13°F to -167°F)		
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal force	≥10N - ≤30N		
	Weight ²⁾	31g (0.068lb)	33g (0.073lb)	33g (0.073lb)
	Typical Cable retention force	22Kg to 44Kg (50lb to 100lb) - Dependent on cable material and diameter.		
	Cable O.D. range	3mm to 8mm (0.118" to 0.314")		
	Mechanical Operations	1000 mating cycles		
MATERIALS	Connector shell - Metal Shell finish	Diecast Zinc Alloy Satin nickel or Black		
	Insulators	UL94V-0 PA66, 30% Glass Filled		
	Boot / Backshell Finish	UL94V-0 Noryl N190 / Santoprene Black, other colours available - see page 80		
	Cable clamp	Noryl N190		
	Sleeve	Noryl N190		
	Male Contact Machined - Solder / Plating	Brass / Silver or Gold (Optional)		
	Female Contact Stamped - Solder / Plating	Phosphor Bronze / Tin or Gold (Optional)		

¹⁾ Not suitable for domestic applications above 50V

²⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.



AC SERIES XLR CABLE CONNECTORS

Amphenol Australia have been manufacturing and designing innovative XLR connectors since 1955. The AC series cable connector range complies with IEC268-12 and AES 14-1992 standards. CSA File Number 68598.

Features

- AC series XLR connectors feature the unique Australian design and patented "Jaws" cable retention system
- A leading first mate last break socket contact is standard on all female connectors (Pin 1).
- The "Jaws" cable retention system provides up to 44kg (100lb) of strain.
- The AC series connector can be quickly and easily assembled without screws – by hand or portable termination tool. (Part number T2860)
- Available in 3, 4, 5, 6A and 7 contact arrangements.
- Compatible with all major XLR brands.

Options

- Solder Bucket termination
- Thermoplastic shell
- Zinc Diecast shell - Satin Nickel Finish
- Zinc Diecast shell - Black Polyester Finish
- Gold, Silver or Tin Plated contacts
- Bulk Style Packaging
- Single Bag packs
- Precision machined contacts
- Cost effective stamped contacts on 3 pole
- Standard Jaws cable clamp, Cable O.D 3mm to 6.5mm (0.118" to 0.255")
- Large Jaws cable clamp, Cable O.D 6.5mm to 8mm (0.255" to 0.314")
- Metal Boots / Backshells
- Coloured Boots / Backshells
- Coloured Identification rings
- Termination / Assembly tooling

Jaws Cable Clamp Options



Standard Jaws cable clamp (Black), Cable O.D 3mm to 6.5mm (0.118" to 0.255")



Large Jaws cable clamp (Purple), Cable O.D 6.5mm to 8mm (0.255" to 0.314")

Ordering Codes

We have listed the more common ordering codes in each section. For further options please refer to the part number breakdown charts. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

XLR Connectors

AC Series Cable Connectors



Features:

- Zinc Diecast Shell.
- Solder Bucket connections.
- "Jaws" Cable Retention System.
- Contact layouts in 3, 4, 5, 6A and 7.
- Precision machined or Stamped contacts.
- Leading first mate last break socket contact.
- Quick and easy assembly without screws – by hand or portable termination tool. (Part number T2860.)

Options: Stamped Contacts (3 contact only), Gold plated contacts, Large or Small Jaws Cable Clamp, Black Finish Shell, Bulk Pack, Coloured Boots / Backshells









Part Number Breakdown: Page 13

Specifications: Page 15

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			XLR 3 pole male, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC3MM
				Bulk Pack	AC3MM BULK
			XLR 3 pole male, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC3MMB
				Gold Plated Contacts	AC3MMB-AU
				Bulk Pack	AC3MMB BULK
			XLR 3 pole male, Stamped contacts, Nickel Finish, Jaws cable clamp	Standard	AC3M
				Large Cable Clamp	AC3MJ
				Bulk Pack	AC3M BULK
			XLR 3 pole male, Stamped contacts, Black Finish, Jaws cable clamp	Standard	AC3MB
				Gold Plated Contacts	AC3MB-AU
				Large Cable Clamp	AC3MBJ
				Bulk Pack	AC3MB BULK
			XLR 3 pole female, Stamped contacts, Nickel Finish, Jaws cable clamp	Standard	AC3F
				Large Cable Clamp	AC3FJ
				Bulk Pack	AC3F BULK
			XLR 3 pole female, Stamped contacts, Black Finish, Jaws cable clamp	Standard	AC3FB
				Gold Plated Contacts	AC3FB-AU
				Large Cable Clamp	AC3FBJ
				Bulk Pack	AC3FB BULK








XLR Connectors

AC Series Cable Connectors

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		XLR 4 pole male, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC4M	
			Large Cable Clamp	AC4MJ	
			Bulk Pack	AC4M BULK	
		XLR 4 pole male, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC4MB	
			Gold Plated Contacts	AC4MB-AU	
			Large Cable Clamp	AC4MBJ	
			Bulk Pack	AC4MB BULK	
		XLR 4 pole female, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC4F	
			Large Cable Clamp	AC4FJ	
			Bulk Pack	AC4F BULK	
		XLR 4 pole female, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC4FB	
			Gold Plated Contacts	AC4FB-AU	
			Large Cable Clamp	AC4FBJ	
			Bulk Pack	AC4FB BULK	
		XLR 5 pole male, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC5M	
			Large Cable Clamp	AC5MJ	
			Bulk Pack	AC5M BULK	
		XLR 5 pole male, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC5MB	
			Gold Plated Contacts	AC5MB-AU	
			Large Cable Clamp	AC5MBJ	
			Bulk Pack	AC5MB BULK	
		XLR 5 pole female, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC5F	
			Large Cable Clamp	AC5FJ	
			Bulk Pack	AC5F BULK	
		XLR 5 pole female, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC5FB	
			Gold Plated Contacts	AC5FB-AU	
			Large Cable Clamp	AC5FBJ	
			Bulk Pack	AC5FB BULK	

XLR Connectors

AC Series Cable Connectors


PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		82.0 [3.228"]	XLR 6A pole male, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC6AM
				Large Cable Clamp	AC6AMJ
				Bulk Pack	AC6AM BULK
		82.0 [3.228"]	XLR 6A pole male, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC6AMB
				Gold Plated Contacts	AC6AMB-AU
				Large Cable Clamp	AC6AMBJ
				Bulk Pack	AC6AMB BULK
		82.0 [3.228"]	XLR 6A pole female, Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC6AF
				Large Cable Clamp	AC6AFJ
				Bulk Pack	AC6AF BULK
		82.0 [3.228"]	XLR 6A pole female, Machined contacts, Black Finish, Jaws cable clamp	Standard	AC6AFB
				Gold Plated Contacts	AC6AFB-AU
				Large Cable Clamp	AC6AFBJ
				Bulk Pack	AC6AFB BULK
		82.0 [3.228"]	XLR 7 pole male, Gold plated Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC7M
				Large Cable Clamp	AC7MJ
				Bulk Pack	AC7M BULK
		82.0 [3.228"]	XLR 7 pole male, Gold plated Machined contacts, Black Finish, Jaws cable clamp	Standard	AC7MB
				Large Cable Clamp	AC7MBJ
				Bulk Pack	AC7MB BULK
		82.0 [3.228"]	XLR 7 pole female, Gold plated Machined contacts, Nickel Finish, Jaws cable clamp	Standard	AC7F
				Large Cable Clamp	AC7FJ
				Bulk Pack	AC7F BULK
		82.0 [3.228"]	XLR 7 pole female, Gold plated Machined contacts, Black Finish, Jaws cable clamp	Standard	AC7FB
				Large Cable Clamp	AC7FBJ
				Bulk Pack	AC7FB BULK

PART NUMBER BREAKDOWN

METAL SHELL TYPE - SOLDER

E. G . AC3MMBJ-AU BULK
AC (Series Prefix), **3** contacts, **Male**, **Machined Contacts**, **Black Polyester Finish**,
J (Large Jaws),- **AU** (Gold Plated Contacts), **Bulk** Packaged.

SERIES PREFIX	AC	=	Series Prefix
CONTACT LAYOUTS	3	=	3 Contacts
	4	=	4 Contacts
	5	=	5 Contacts
	6A	=	6 Contacts
	7	=	7 Contacts
GENDER	F	=	Female Socket Contacts
	M	=	Male Pin Contacts
CONTACT¹	Blank	=	Stamped Contacts
	M	=	Machined Contacts
	G	=	Stamped Contacts, Ground Tag
	MG	=	Machined Contacts, Ground Tag (Applicable 3 male pin contacts, option M & MG only)
SHELL FINISH²	Blank	=	Nickel Plated Finish
	B	=	Black Polyester Finish
CABLE CLAMP	Blank	=	Standard Jaws 3mm - 6.5mm cable O.D. (0.118" to 0.255")
	J	=	Large Jaws 6.5mm - 8mm cable O.D. (0.255" to 0.314")
CONTACT PLATING³	Blank	=	Standard Plating (Silver or Tin) (Refer to Standard Data)
	AU	=	Gold Plated
PACKAGING	Blank	=	Individual Bags
	BULK	=	Bulk Packed



Note:

¹ 4 - 7 contact connectors have machined contacts and grounding as standard.

² Ground contacts are not supplied with the black polyester finish shell option.

³ 7 Contact is gold plated as standard.

⁴ All AC Series Connectors are available with optional colour coded boot / backshell. Refer to page 134 and simply add colour to end of part number. Example: AC3MM - RED

XLR Connectors

AC Series Cable Connectors



Features:

- Thermoplastic Shell.
- Solder Bucket Connections.
- "Jaws" Cable Retention System.
- Stamped or Machined Contacts.
- Leading first mate last break socket contact.
- Quick and easy assembly without screws – by hand or portable termination tool. (Part number T2860.)

Options: Gold Plated Contacts, Stamped Contacts (3 Contact only), Bulk Pack, Coloured Boots / Backshells 3, 4, 5, 6A and 7 Contacts.

Specifications: [Page 15](#)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		XLR 3 pole male, Machined contacts, Thermoplastic shell, Jaws cable clamp	Standard	AC3MMCP	
			Bulk Pack	AC3MMCP BULK	
		XLR 3 pole male, Stamped contacts, Thermoplastic shell, Jaws cable clamp	Standard	AC3MCP	
			Bulk Pack	AC3MCP BULK	
		XLR 3 pole female, Stamped contacts, Thermoplastic shell, Jaws cable clamp	Standard	AC3FCP	
			Bulk Pack	AC3FCP BULK	

Note: Thermoplastic shell connectors are also available in 4 - 7 contact arrangements, please contact us for ordering code.

STANDARD DATA AC CABLE CONNECTORS


		VALUE										
GENERAL CHARACTERISTICS	Number of contacts	3	4	5	6A	7						
	AC Series Contact Arrangements (Front view of pin inserts)											
	Termination	SOLDER										
	Max. Wire Gauge - Stranded wire: Solder	14AWG	16AWG	18AWG	20AWG							
	Flammability rating (insulator plastics & housings)	UL94V-0										
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU										
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	133V ¹										
	Test Voltage AC RMS	1400V										
	Current carrying capacity: Solder	15A	10A	7.5A	5A							
	Typical Contact Resistance	≤3mΩ										
	Insulation Resistance	≥1GΩ										
CLIMATIC CHARACTERISTICS	Protection Class	IP40										
	Operating Temperature	-25 °C to +75 °C (-13°F to +167°F)										
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal force	≥10N - ≤30N										
	Weight - Metal ²	36g (0.080lb)	37g (0.081lb)	38g (0.083lb)								
	Weight - Thermoplastic ²	18g (0.039lb)	19g (0.041lb)	20g (0.044lb)								
	Typical Cable retention force	22Kg to 44Kg (50lb to 100lb) - Dependent on cable material and diameter.										
	Cable O.D. range - JAWS clamp	Standard Large	3mm to 6.5mm (0.118" to 0.255") 6.5mm to 8mm (0.255" to 0.314")									
	Mechanical Operations	1000 mating cycles										
	Connector shell - Metal Shell finish	Diecast Zinc Alloy Satin nickel or Black polyester										
MATERIALS	Connector shell - Thermoplastic Shell finish	Thermoplastic, UL94V-0 Modified PPE Resin Black										
	Insulators	UL94V-0 PBT Resin or Modified PPE Resin										
	Boot / Backshell Finish	UL94V-0 Modified PPE Resin or Machined Brass Black, other colours available - see page 134										
	Cable clamp (JAWS)	Standard Solder Large Solder	UL94V-0 Modified PPO Resin (Black) UL94V-0 Modified PPO Resin (Purple)									
	Cable Bushing	Santoprene										
	Male Contact (Solder / Plating)	Stamped Machined	Phosphor Bronze / Silver or Gold (Optional) Brass / Silver or Gold (Optional)									
	Female Contact (Solder / Plating)	Stamped Machined	Phosphor Bronze / Tin or Gold (Optional) Brass / Silver or Gold (Optional)									

¹⁾ Not suitable for domestic applications above 50V

²⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

XLR Connectors

AC "Z" Series Chassis Mount



The metal chassis mount "Z" series connectors are designed for the audio user where durability, reliability and strength across a wide range of applications are important. All AC products are manufactured to the highest quality standards and will withstand the harshest environments. This range complies with IEC268-12 and AES 14-1992 standards. CSA File Number 68598

Features

- The "D" size housing can be either front or rear mounted using the same panel cutout.
- The "P" size housing is the original wide flange front mounting XLR connector. "PN" is the original narrow flange front mounting male connector.
- A leading first mate last break socket contact is standard on all female connectors (Pin 1).
- Solder cup or Vertical PCB versions.
- Connectors are fitted with a grounding system for RFI shielding applications.
- Available in 3, 4, 5, 6A and 7 contact arrangements.
- Compatible with all other XLR brands.

Options

- Solder Bucket termination
- Vertical PCB contacts
- Zinc Diecast Shell - Satin Nickel Finish
- Zinc Diecast Shell - Black Polyester Finish
- Gold, Silver or Tin Plated Contacts
- Bulk Packaging
- Single Bag packs
- Precision machined contacts
- Cost effective stamped contacts on 3 pole
- Latchless versions (Non-Latching)
(Female only)

AC "Z" SERIES XLR METAL CHASSIS MOUNT CONNECTORS

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

XLR Connectors

AC "Z" Series Chassis Mount



Features:

- Zinc Diecast Shell.
- D size housing can be front or rear mounted using the same panel cutout.
- Solder Bucket connections.
- Vertical PCB mounting (not available in 4 contact female).
- Precision machined or Stamped contacts (3 pin only).
- Leading first mate last break socket contact.
- Positive latch lock system.




Options: Stamped contacts (3 contact only), Gold plated contacts, Vertical PCB contacts, Black finish, Non-Latching (Female only), Bulk Pack.

Part Number Breakdown: Page 21

Specifications: Page 22







PCB Footprints: Page 23

Panel Cutouts: Page 23

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		XLR 3 pole male, D Flange, Machined contacts, Nickel Finish	Standard	AC3MMDZ	
			Vertical PCB	AC3MMDZV	
			Bulk Pack	AC3MMDZ BULK	
		XLR 3 pole male, D Flange, Machined contacts, Black Finish	Standard	AC3MMDZB	
			Gold Plated Contacts	AC3MMDZB-AU	
			Vertical PCB	AC3MMDZVB	
			Bulk Pack	AC3MMDZB BULK	
		XLR 3 pole male, D Flange, Stamped contacts, Nickel Finish	Standard	AC3MDZ	
			Bulk Pack	AC3MDZ BULK	
			Standard	AC3MDZB	
		XLR 3 pole male, D Flange, Stamped contacts, Black Finish	Gold Plated Contacts	AC3MDZB-AU	
			Vertical PCB	AC3MDZVB	
			Bulk Pack	AC3MDZB BULK	
		XLR 3 pole female, D Flange, Stamped contacts, Nickel Finish	Standard	AC3FDZ	
			Bulk Pack	AC3FDZ BULK	
			Standard	AC3FDZB	
		XLR 3 pole female, D Flange, Stamped contacts, Black Finish	Gold Plated Contacts	AC3FDZB-AU	
			Vertical PCB	AC3FDZVB	
			Bulk Pack	AC3FDZB BULK	








XLR Connectors

AC "Z" Series Chassis Mount

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			XLR 4 pole male, D Flange, Machined contacts, Nickel Finish	Standard	AC4MDZ
				Vertical PCB	AC4MDZV
				Bulk Pack	AC4MDZ BULK
			XLR 4 pole male, D Flange, Machined contacts, Black Finish	Standard	AC4MDZB
				Gold Plated Contacts	AC4MDZB-AU
				Vertical PCB	AC4MDZB
				Bulk Pack	AC4MDZB BULK
			XLR 4 pole female, D Flange, Machined contacts, Nickel Finish	Standard	AC4FDZ
				Vertical PCB	AC4FDZV
				Bulk Pack	AC4FDZ BULK
			XLR 4 pole female, D Flange, Machined contacts, Black Finish	Standard	AC4FDZB
				Gold Plated Contacts	AC4FDZB-AU
				Vertical PCB	AC4FDZB
				Bulk Pack	AC4FDZB BULK
			XLR 5 pole male, D Flange, Machined contacts, Nickel Finish	Standard	AC5MDZ
				Vertical PCB	AC5MDZV
				Bulk Pack	AC5MDZ BULK
			XLR 5 pole male, D Flange, Machined contacts, Black Finish	Standard	AC5MDZB
				Gold Plated Contacts	AC5MDZB-AU
				Vertical PCB	AC5MDZB
				Bulk Pack	AC5MDZB BULK
			XLR 5 pole female, D Flange, Machined contacts, Nickel Finish	Standard	AC5FDZ
				Vertical PCB	AC5FDZV
				Bulk Pack	AC5FDZ BULK
			XLR 5 pole female, D Flange, Machined contacts, Black Finish	Standard	AC5FDZB
				Gold Plated Contacts	AC5FDZB-AU
				Vertical PCB	AC5FDZB
				Bulk Pack	AC5FDZB BULK

XLR Connectors

AC "Z" Series Chassis Mount

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			XLR 6A pole male, D Flange, Machined contacts, Nickel Finish	Standard	AC6AMDZ
				Vertical PCB	AC6AMDZV
				Bulk Pack	AC6AMDZ BULK
			XLR 6A pole male, D Flange, Machined contacts, Black Finish	Standard	AC6AMDZB
				Gold Plated Contacts	AC6AMDZB-AU
				Vertical PCB	AC6AMDZB
				Bulk Pack	AC6AMDZB BULK
			XLR 6A pole female, D Flange, Machined contacts, Nickel Finish	Standard	AC6AFDZ
				Vertical PCB	AC6AFDZV
				Bulk Pack	AC6AFDZ BULK
			XLR 6A pole female, D Flange, Machined contacts, Black Finish	Standard	AC6AFDZB
				Gold Plated Contacts	AC6AFDZB-AU
				Vertical PCB	AC6AFDZB
				Bulk Pack	AC6AFDZB BULK
			XLR 7 pole male, D Flange, Gold Plated, Machined contacts, Nickel Finish	Standard	AC7MDZ
				Vertical PCB	AC7MDZV
				Bulk Pack	AC7MDZ BULK
			XLR 7 pole male, D Flange, Gold Plated, Machined contacts, Black Finish	Standard	AC7MDZB
				Vertical PCB	AC7MDZB
				Bulk Pack	AC7MDZB BULK
			XLR 7 pole female, D Flange, Gold Plated, Machined contacts, Nickel Finish	Standard	AC7FDZ
				Vertical PCB	AC7FDZV
				Bulk Pack	AC7FDZ BULK
			XLR 7 pole female, D Flange, Gold Plated, Machined contacts, Black Finish	Standard	AC7FDZB
				Vertical PCB	AC7FDZB
				Bulk Pack	AC7FDZB BULK

XLR Connectors

AC "Z" Series Chassis Mount



Features:

- Zinc Diecast shell.
- The P size housing is the original wide flange front mounting XLR connector. PN is the original narrow, front mounting male connector.
- Solder Bucket connections.
- Precision Machined or Stamped contacts (3 pin only).
- Leading first mate last break socket contact.
- Positive latch lock system.

Options: Stamped contacts (3 contact only), Gold plated contacts, Black Finish, Non-Latching (Female only), Bulk Pack.

Part Number Breakdown: Page 21

PCB Footprints: Page 23

Specifications: Page 22

Panel Cutouts: Page 23

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	POLES	PART NUMBER
AC3MPNZ		Dimensions in mm (inches)	XLR male, Narrow flange, Machined contacts	3	AC3MPNZ
AC3MPNZ		Dimensions in mm (inches)	XLR male, Narrow flange, Stamped contacts,	3	AC3MPNZ
				4	AC4MPNZ
				5	AC5MPNZ
				6	AC6AMPNZ
				7	AC7MPNZ
AC3MMP		Dimensions in mm (inches)	XLR male, Wide flange, Machined contacts	3	AC3MMP
AC3MP		Dimensions in mm (inches)	XLR male, Wide flange, Stamped contacts	3	AC3MP
				4	AC4MP
				5	AC5MP
				6	AC6AMP
				7	AC7MP
AC3FPZ		Dimensions in mm (inches)	XLR female, Wide flange, Stamped contacts	3	AC3FPZ
AC3FPZ		Dimensions in mm (inches)	XLR female, Wide flange, Stamped contacts	4	AC4FPZ
				5	AC5FPZ
				6	AC6AFPZ
				7	AC7FPZ


*Black finish available on special request please contact factory.

PART NUMBER BREAKDOWN

METAL TYPE FLANGE

E. G. **AC3MMPNZB-AU BULK**
AC (Series Prefix), **3** contacts, **M**ale, **M**achined Contacts, **PN** (Narrow Flange), **Z** (Metal Chassis Series), **B**lack Polyester Finish, - **AU** (Gold Plated Contacts), **Bulk** Packaged.

SERIES PREFIX	AC	=	Series Prefix
CONTACT LAYOUTS	3	=	3 Contacts
	4	=	4 Contacts
	5	=	5 Contacts
	6A	=	6 Contacts
	7	=	7 Contacts
GENDER	F	=	Female Socket Contacts
	M	=	Male Pin Contacts
MACHINED CONTACTS ¹	Blank	=	Stamped Contacts
	M	=	Machined Contacts (Applicable 3 male pin contacts only)
SHELL STYLE	D	=	Small Flange (front or rear mounting)
	P	=	Large Shell with Wide Flange
	PN	=	Large Shell with Narrow Flange (male only)
SHELL SERIES	Blank	=	Male P Shell Style Only
	Z	=	Metal Chassis Series
SHELL FINISH ²	Blank	=	Nickel Plated Finish
	B	=	Black Polyester Finish
CONTACT PLATING ³	Blank	=	Standard Plating (Silver or Tin - refer to Standard Data)
	AU	=	Gold Plated
PACKAGING	Blank	=	Individual Bags
	BULK	=	Bulk Packed



Note:

¹ 4 - 7 contact connectors have machined contacts and grounding as standard. They are not available in stamped contacts.

² Ground contacts are not supplied with the black polyester finish shell option.

³ 7 Contact is gold plated as standard.

⁴ Non-Latching Versions (Female) available - Please contact us for part number options.

XLR Connectors

AC "Z" Series Chassis Mount

STANDARD DATA AC SERIES CHASSIS - METAL "Z"

		VALUE				
GENERAL CHARACTERISTICS	Number of contacts	3	4	5	6A	7
	Contact Arrangement (Front view of pin inserts)					
	Termination	Solder Bucket / Printed Circuit Board (PCB)				
	Max. Wire Gauge - Stranded wire: Solder Printed Circuit Board - PCB	14AWG N/A	16AWG N/A	18AWG N/A	18AWG N/A	20AWG N/A
	Flammability rating of plastics	UL94V-0				
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU				
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	133V ¹⁾				
	Test Voltage AC RMS	1400V				
	Current carrying capacity: Solder Printed Circuit Board (PCB)	15A 15A	10A	7.5A	7.5A	5A
	Typical Contact Resistance	≤3mΩ				
	Insulation Resistance	≥1000MΩ				
CLIMATIC CHARACTERISTICS	Protection Class	IP40				
	Operating Temperature	-25°C to +75°C (-13°F to +167°F)				
MECHANICAL CHARACTERISTICS	Weight - Metal ²⁾	31g (0.068lb)	32g (0.070lb)	33g (0.072lb)	33g (0.072lb)	33g (0.072lb)
	Mechanical Operations	1000 mating cycles				
MATERIALS	Connector Shell	Diecast Zinc Alloy				
	Shell Finish	Satin Nickel or Black Polyester				
	Insulators	UL94V-0 PBT Resin or Modified PPE Resin				
	Male Contact					
	Stamped Solder and PCB-(Material/Plating)	Phosphor Bronze / Silver or Gold (optional)				
	Machined Solder-(Material/Plating)	Brass / Silver or Gold (optional)				
	Female Contact					
	Stamped Solder and PCB-(Material/Plating)	Phosphor Bronze / Tin or Gold (optional)				
	Machined Solder-(Material/Plating)	Brass / Silver or Gold (Optional)				


¹⁾ Not suitable for domestic applications above 50V

²⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.


AC SERIES CHASSIS METAL "Z"

PCB FOOTPRINTS STRAIGHT (V)


CONNECTOR SIDE OF PCB




AC3MM*ZV




AC4F*ZV




AC4M*ZV




AC5F*ZV




AC5M*ZV




AC6AF*ZV



AC6AM*ZV




AC7F*ZV




AC7M*ZV

PANEL CUTOUT DIMENSIONS


FRONT VIEW




+ Panel cutout Centre Line




+ Panel cutout Centre Line



AC*FPZ



AC*MP



AC*MPN

XLR Connectors

AC Series PCB Chassis Mount



AC SERIES XLR PCB CHASSIS MOUNT CONNECTORS

The AC series, A and B type XLR chassis receptacles have been designed and manufactured with the Original Equipment Manufacturers' (OEM) needs in mind. The compact shell design allows a significant space saving over the traditional 'D' type shell. Gold plated contacts improve the performance, ensuring a reliable contact and the unique grounding link options offer flexibility in design.

Features

- A leading first mate last break socket contact is standard on all female connectors (Pin 1).
- Vertical and Horizontal PCB versions available.
- Latching and Non-latching versions available.
- A range of different grounding options are available including:
 - Mating connector shell to Pin 1
 - Mating connector shell to Chassis
 - Mating connector shell to pin 1 to Chassis
- A type is available in 3, 4 or 5 contacts.
- B type is available in 3 contact only.
- Compatible with all other XLR brands.
- Metal Mounting Flange (B type)

Options

- Vertical PCB contacts
- Horizontal PCB contacts
- Precision Machined Pin contacts
- Cost effective Stamped Socket contacts
- Gold Plated contacts (Standard)
- Silver Plated contacts (Optional)
- Bulk Packaging
- Integrated Switch

Ordering Codes

We have listed the more common ordering codes in each section. For further options please refer to the part number breakdown charts. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

XLR Connectors

AC Series PCB Chassis Mount (A Type)



Features:

- Thermoplastic Shell
- Contact layouts in 3,4 or 5
- Industry standard PCB footprints.
- Vertical or Horizontal PCB mounting.
- Precision machined pin contacts.
- Gold plated contacts.
- Leading first mate last break socket contact.
- Bulk packed in trays, 100 to a box as standard.
- Positive latch lock system.

Options: Vertical or Horizontal PCB, Various grounding methods, Latching or Non-Latching.

Part Number Breakdown: Page 32 Specifications: Page 35

PCB Footprints: Page 36











Panel Cutouts: Page 37

Recommended Fastener: Page 132

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	GROUND LINK VARIATIONS	PART NUMBER
			XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack	No Ground Link	AC3MAH-AU-PRE
			XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Pin 1 to Chassis to Mating connector shell	AC3MAH1-AU-PRE
			XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground	AC3MAH2-AU-PRE
			XLR 3 pole male with integrated switch, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis to PCB, Pin 1 sep. Ground	AC3MAH4-SW-B
			XLR 3 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack	No Ground Link	AC3MAV-AU-PRE










XLR Connectors

AC Series PCB Chassis Mount (A Type)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	GROUND LINK VARIATIONS	PART NUMBER
			XLR 3 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground	AC3MAV2-AU-PRE
			XLR 3 pole male, Solder Buckets, Gold Plated Contacts, Bulk Pack	No Ground Link	AC3MA-AU-B
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack	No Ground Link	AC3FAH-AU-PRE
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack	Pin 1 to Chassis to Mating connector shell	AC3FAH1-AU-PRE
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground	AC3FAH2-AU-PRE
			XLR 3 pole female, Horizontal PCB, Non-Latching Type Gold Plated Contacts, Bulk Pack	No Ground Link	AC3FAHL-AU-PRE
			XLR 3 pole female, Horizontal PCB, Non-Latching Type Gold Plated Contacts, Bulk Pack	Pin 1 to Chassis to mating connector shell	AC3FAHL1-AU-PRE
			XLR 3 pole female, Horizontal PCB, Non-Latching Type Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground.	AC3FAHL2-AU-PRE
			XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack	No Ground Link	AC3FAV-AU-PRE
			XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack	Pin 1 to Chassis to Mating connector shell	AC3FAV1-AU-PRE

XLR Connectors

AC Series PCB Chassis Mount (A Type)

PRODUCT - FIGURE	DRAWING	DESCRIPTION	GROUND LINK VARIATIONS	PART NUMBER
		XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground.	AC3FAV2-AU-PRE
		XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack	No Ground Link	AC3FAVL-AU-PRE
		XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack	Pin 1 to Chassis to Mating connector shell	AC3FAVL1-AU-PRE
		XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground.	AC3FAVL2-AU-PRE
		XLR 4 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis - Pin 1 sep. Ground	AC4MAH-AU-B
		XLR 5 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis to PCB, Pin 1 sep. Ground	AC5MAH-AU-B
		XLR 5 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis to PCB, Pin 1 sep. Ground	AC5MAV-AU-B
		XLR 5 pole female, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis to PCB, Pin 1 sep. Ground	AC5FAH-AU-B
		XLR 5 pole female, Vertical PCB, Gold Plated Contacts, Bulk Pack	Mating connector shell to Chassis to PCB, Pin 1 sep. Ground	AC5FAV-AU-B

XLR Connectors

AC Series PCB Chassis Mount (B Type)



Features:

- Thermoplastic Shell with Metal Mounting Flange
- Contact layouts in 3 or 5
- Industry standard PCB footprints
- Improved grounding performance
- Vertical or Horizontal PCB mounting
- Precision machined pin contacts
- Gold plated contacts
- Leading first mate last break socket contact
- Bulk packed in trays, 100 to a box as standard
- Positive latch lock system

Options: Silver plated contacts, Vertical or Horizontal PCB, Various grounding methods, Latching or Non-Latching.

Part Number Breakdown: Page 32 **Specifications:** Page 35

PCB Footprints: Page 36









Panel Cutouts: Page 37

Recommended Fastener: Page 132

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION/ GROUND LINK	MOUNTING FLANGE VARIATIONS	PART NUMBER
		Dimensions in mm (inches)	XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3MBH-AU-B
		Dimensions in mm (inches)	XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis to Mating connector shell	Nickel Finish	AC3MBH1-AU-B
		Dimensions in mm (inches)	XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack Mating connector shell to Chassis - Pin 1 sep. Ground	Nickel Finish	AC3MBH2-AU-B
		Dimensions in mm (inches)	XLR 3 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack Mating connector shell to Pin 1	Nickel Finish	AC3MBH3-AU-B
		Dimensions in mm (inches)	XLR 3 pole male, Horizontal PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3MBHL-AU-B
		Dimensions in mm (inches)	XLR 3 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3MBV-AU-B









XLR Connectors

AC Series PCB Chassis Mount (B Type)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION/ GROUND LINK	MOUNTING FLANGE VARIATIONS	PART NUMBER
			XLR 3 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis to Mating connector shell	Nickel Finish	AC3MBV1-AU-B
			XLR 3 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack Mating connector shell to Chassis - Pin 1 sep. Ground	Nickel Finish	AC3MBV2-AU-B
			XLR 3 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack Mating connector shell to Pin 1	Nickel Finish	AC3MBV3-AU-B
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3FBH-AU-B
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis to Mating connector shell	Nickel Finish	AC3FBH1-AU-B
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack Mating connector shell to Chassis - Pin 1 sep. Ground	Nickel Finish	AC3FBH2-AU-B
			XLR 3 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis	Nickel Finish	AC3FBH3-AU-B
			XLR 3 pole female, Horizontal PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3FBHL-AU-B

XLR Connectors

AC Series PCB Chassis Mount (B Type)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION/ GROUND LINK	Mounting Flange Variations	Part Number
			XLR 3 pole female, Horizontal PCB, Non-Latching Type Gold Plated Contacts, Bulk Pack Pin 1 to Chassis to mating connector shell	Nickel Finish	AC3FBHL1-AU-B
			XLR 3 pole female, Horizontal PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack Mating connector shell to Chassis - Pin 1 sep. Ground.	Nickel Finish	AC3FBHL2-AU-B
			XLR 3 pole female, Horizontal PCB, Non-Latching Type Gold Plated Contacts, Bulk Pack Pin 1 to Chassis	Nickel Finish	AC3FBHL3-AU-B
			XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3FBV-AU-B
			XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis to mating connector shell	Nickel Finish	AC3FBV1-AU-B
			XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack Mating connector shell to Chassis - Pin 1 sep. Ground.	Nickel Finish	AC3FBV2-AU-B
			XLR 3 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis	Nickel Finish	AC3FBV3-AU-B
			XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack No Ground Link	Nickel Finish	AC3FBVL-AU-B

XLR Connectors

AC Series PCB Chassis Mount (B Type)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION/ GROUND LINK	MOUNTING FLANGE VARIATIONS	PART NUMBER
			XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis to Mating connector shell	Nickel Finish	AC3FBVL1-AU-B
			XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack Mating connector shell to Chassis-Pin 1 sep. Ground.	Nickel Finish	AC3FBVL2-AU-B
			XLR 3 pole female, Vertical PCB, Non-Latching Type, Gold Plated Contacts, Bulk Pack Pin 1 to Chassis	Nickel Finish	AC3FBVL3-AU-B
			XLR 5 pole female, Horizontal PCB, Latching Type, Gold Plated Contacts, Bulk Pack	Nickel Finish	AC5FBH-AU-PRE
			XLR 5 pole female, Vertical PCB, Latching Type, Gold Plated Contacts, Bulk Pack	Nickel Finish	AC5FBV-AU-PRE
			XLR 5 pole male, Horizontal PCB, Gold Plated Contacts, Bulk Pack	Nickel Finish	AC5MBH-AU-PRE
			XLR 5 pole male, Vertical PCB, Gold Plated Contacts, Bulk Pack	Nickel Finish	AC5MBV-AU-PRE

XLR Connectors


AC Series PCB Chassis Mount

PART NUMBER BREAKDOWN

AC SERIES A AND B TYPE MALE - 3 CONTACT

E. G. **AC3MAVL3-AU B**
AC (series prefix), **3** contacts, **M**ale, **A** Type, **V**ertical Printed Circuit Board, **L**atchless, **3** (Mating Shell to Pin 1 Grounding), - **AU** (Gold Plated Contacts), **B**ulk Packaged.

SERIES PREFIX	AC	=	Series Prefix
CONTACT LAYOUT	3	=	3 Contact only
GENDER	M	=	Male Socket Contacts
SHELL SERIES	A	=	A Type
	B	=	B Type
TERMINATION	H	=	Horizontal Printed Circuit Board
	V	=	Vertical Printed Circuit Board
	Blank	=	Solder Bucket Contacts
MOUNTING FLANGE FINISH (B TYPE ONLY)	Blank	=	Nickel
LOCKING MECHANISM	Blank	=	Latching
	L	=	Latchless
GROUNDING LINK OPTIONS	Blank	=	No Ground Link
	1	=	Pin 1 to Chassis to mating connector shell
	2	=	Mating Connector shell to Chassis, Pin 1 to separate ground
	3	=	Mating connector to Pin 1
	4	=	Mating connector to Shell to Chassis to PCB, Pin 1 separate ground
CONTACT PLATING	AU	=	Gold Plated Contacts
	AG	=	Silver Plated Contacts (Non-Standard)
PACKAGING	PRE	=	Bulk Packed
	PRD	=	Disassembled push latch




PART NUMBER BREAKDOWN

AC SERIES A AND B TYPE FEMALE - 3 CONTACT

E. G. **AC3MAVL3-AU**
AC (series prefix), 3 contacts, Female, A Type, Vertical Printed Circuit Board, Latchless, 3 (Pin 1 to Chassis Grounding), - AU (Gold Plated Contacts), Bulk Packaged.

SERIES PREFIX	AC	=	Series Prefix
CONTACT LAYOUT	3	=	3 Contact only
GENDER	F	=	Female Socket Contacts
SHELL SERIES	A	=	A Type
	B	=	B Type
TERMINATION	H	=	Horizontal Printed Circuit Board
	V	=	Vertical Printed Circuit Board
LOCKING MECHANISM	Blank	=	Latching
	L	=	Latchless
GROUNDING LINK OPTIONS	Blank	=	No Ground Link
	1	=	Pin 1 to Chassis to mating connector shell
	2	=	Mating Connector shell to Chassis, Pin 1 to separate ground
	3	=	Pin 1 to Chassis
CONTACT PLATING	AU	=	Gold Plated Contacts
	AG	=	Silver Plated Contacts (Non-Standard)
PACKAGING	PRE	=	Bulk Packed
	PRD	=	Disassembled push latch




XLR Connectors

AC Series PCB Chassis Mount

PART NUMBER BREAKDOWN

AC SERIES A AND B TYPE MALE AND FEMALE - 4 / 5 CONTACT



E. G. **AC5FAV-AU-B**
AC (series prefix), 5 contacts, Female, A Type, Vertical Printed Circuit Board, AU (Gold Plated Contacts) - Bulk Packaged.

SERIES PREFIX	AC	=	Series Prefix
CONTACT LAYOUT	4	=	4 Contact
	5	=	5 Contact
GENDER	F	=	Female Socket Contacts
	M	=	Male Pin Contacts
SHELL SERIES	A	=	A Type
	B	=	B Type
TERMINATION	H	=	Horizontal Printed Circuit Board
	V	=	Vertical Printed Circuit Board
CONTACT PLATING	AU	=	Gold Plated Contacts
PACKAGING	B	=	Bulk Packed
	PRE	=	PRE Series Bulk Packed

STANDARD DATA AC SERIES A AND B TYPE CHASSIS

		VALUE		
GENERAL CHARACTERISTICS	Number of contacts	3	4	5
	Contact Arrangements (Front view of pin insert)			
	Termination	Printed Circuit Board (PCB)		
	Flammability rating of plastics	UL94V-0		
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU		
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	133V ¹		
	Test Voltage AC RMS	1500V		
	Current carrying capacity	6A		3A
	Typical Contact Resistance	$\leq 5\text{m}\Omega$		
	Insulation Resistance (initial)	$\geq 2\text{G}\Omega$		
	Insulation Resistance (after damp heat test)	$\geq 1\text{G}\Omega$		
	Protection Class	IP40		
CLIMATIC CHARACTERISTICS	Operating Temperature	-25 °C to +75 °C (-13°F to +167°F)		
	Weight ²	14g (0.030lb)		
MECHANICAL CHARACTERISTICS	Retention Spring separating force	$\geq 20\text{N}$		
	Mounting Screw torque max.	1.5Nm		
	Mechanical Operations	1500 mating cycles		
	Fastening A Type Connectors ³	Self-Tapping PT screw with thread 2.9 x 1.06 and of Tri-rondular configuration		
	Fastening B Type Connectors ³	Self-Tapping screw M2.5		
	Connector Flange - B-Type	Diecast Zinc Alloy		
	Flange Finish - B-Type	Nickel		
MATERIALS	Insulators	PA6.6 + 25% glass fibre reinforced, UL94V-0		
	Male Contact Material	Brass		
	Male Contact Plating	$0.05\mu\text{m}$ gold over $2\mu\text{m}$ nickel		
	Female Contact Material	Bronze		
	Female Contact Plating	$0.05\mu\text{m}$ gold over $2\mu\text{m}$ nickel		
	Latch lock and Spring	Spring Steel		
	Ground element	Spring Steel		


¹ Not suitable for domestic applications above 50V

² Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.


³ Refer to page 132

AC SERIES A AND B TYPE CHASSIS PANEL CUTOUT DIMENSIONS - FRONT VIEW


A TYPE




B TYPE



**A AND B
TYPE MALE
MOUNTING
PITCH**




**A AND
B TYPE
FEMALE
MOUNTING
PITCH**




AC3FA/BH/V SCHEMATIC CHART


AC3FA/BH/V3-AU
AC3FA/BH/VL3-AU




AC3FA/BH/V2-AU
AC3FA/BH/VL2-AU




AC3FA/BH/V1-AU
AC3FA/BH/VL1-AU




AC3FA/BH/V-AU
AC3FA/BH/VL-AU




AC3MA/BH/V3-AU
AC3MA/BH/VL3-AU




AC3MA/BH/V2/4-AU
AC3MA/BH/VL2/4-AU



AC3MA/BH/V1-AU
AC3MA/BH/VL1-AU



AC3MA/BH/V-AU
AC3MA/BH/VL-AU



XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount



The AC Series C type chassis receptacles feature two connectors in the one space saving housing. A combined XLR female receptacle together with a 6.35mm (1/4") phone jack give the designer more flexibility ensuring premium board space is saved. The new low profile high density C type offers a 15% space saving over the traditional C type. Various configurations are available in either stereo or mono layouts with Vertical, Horizontal Printed Circuit Board or Solder contacts.

Features

- Standard or low profile / high density shell design
- Two connectors in the one housing.
- Industry standard PCB footprint layout on standard C type.
- Vertical or Horizontal PCB mounting.
- Bulk packed.
- Positive latch lock system (XLR).

Options

- Solder contacts
- Vertical PCB contacts
- Horizontal PCB contacts
- Bulk Packaging
- Overmoldable connector housing

Ordering Codes

We have listed the more common ordering codes in each section. For further options please refer to the part number breakdown charts. Please contact us if you need any further assistance.

AC SERIES DUAL 1/4" (6.35mm) / XLR

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount



Features:

- Two connectors in the one housing.
- Low profile design offers a 15% space saving over the traditional design.
- Vertical or Horizontal PCB mounting.
- Bulk packed in trays, 100 to a box as standard.
- Positive latch lock system (XLR).

Part Number Breakdown: Page 44

Specifications: Page 46







PCB Footprints: Page 45

Recommended Fastener: Page 132

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			Low Profile XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Horizontal PCB mount, Bulk Pack	Latching	ACJC6AH BULK
			Low Profile XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Horizontal PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC6AHL BULK
			Low Profile XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Vertical PCB mount, Bulk Pack	Latching	ACJC6AV2 BULK
			Low Profile XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Vertical PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC6AV2L BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack, Horizontal PCB mount, Bulk Pack	Latching	ACJC9AH BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack, Horizontal PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC9AHL BULK


XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack, Vertical PCB mount, Bulk Pack	Latching	ACJC9AV2 BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack, Vertical PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC9AV2L BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Horizontal PCB mount, Bulk Pack	Latching	ACJC10AH BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Horizontal PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC10AHL BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Vertical PCB mount, Bulk Pack	Latching	ACJC10AV2 BULK
			Low Profile XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Vertical PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC10AV2L BULK

XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount



Features:

- Two connectors in the one housing.
- Space saving design.
- Industry standard PCB footprint layout.
- Vertical or Horizontal PCB mounting.
- Bulk packed in trays, 100 to a box as standard.
- Positive latch lock system (XLR).

Part Number Breakdown: [Page 44](#)

Specifications: [Page 46](#)









PCB Footprints: [Page 45](#)

Recommended Fastener: [Page 132](#)

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			XLR 3 pole female receptacle with 1/4" mono jack without switching contact, Horizontal PCB mount, Bulk Pack	Latching	ACJC5H BULK
			XLR 3 pole female receptacle with 1/4" mono jack without switching contact, Horizontal PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC5HL BULK
			XLR 3 pole female receptacle with 1/4" mono jack without switching contact, Vertical PCB mount, Bulk Pack	Latching	ACJC5V BULK
			XLR 3 pole female receptacle with 1/4" mono jack without switching contact, Vertical PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC5VL BULK
			XLR 3 pole female receptacle with 1/4" mono jack without switching contact, Solder Contacts, Bulk Pack	Latching	ACJC5S BULK
			XLR 3 pole female receptacle with 1/4" mono jack without switching contact, Solder Contacts, Bulk Pack	Non-latching, Retention Spring	ACJC5SL BULK

















XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		<p>XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Horizontal PCB mount, Bulk Pack</p>	Latching		ACJC6 BULK
		<p>XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Horizontal PCB mount, Bulk Pack</p>	Non-latching, Retention Spring		ACJC6HL BULK
		<p>XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Vertical PCB mount, Bulk Pack</p>	Latching		ACJC6V BULK
		<p>XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Vertical PCB mount, Bulk Pack</p>	Non-latching, Retention Spring		ACJC6VL BULK
		<p>XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Solder Contacts, Bulk Pack</p>	Latching		ACJC6S BULK
		<p>XLR 3 pole female receptacle with 1/4" stereo jack without switching contact, Solder Contacts, Bulk Pack</p>	Non-latching, Retention Spring		ACJC6SL BULK
		<p>XLR 3 pole female receptacle with 1/4" switching stereo jack, Horizontal PCB mount, Bulk Pack</p>	Latching		ACJC9H BULK
		<p>XLR 3 pole female receptacle with 1/4" switching stereo jack, Horizontal PCB mount, Bulk Pack</p>	Non-latching, Retention Spring		ACJC9HL BULK



XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			XLR 3 pole female receptacle with 1/4" switching stereo jack, Vertical PCB mount, Bulk Pack	Latching	ACJC9V BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack, Vertical PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC9VL BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack, Solder Contacts, Bulk Pack	Latching	ACJC9S BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack, Solder Contacts, Bulk Pack	Non-latching, Retention Spring	ACJC9SL BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Horizontal PCB mount, Bulk Pack	Latching	ACJC10H BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Horizontal PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC10HL BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Vertical PCB mount, Bulk Pack	Latching	ACJC10V BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Vertical PCB mount, Bulk Pack	Non-latching, Retention Spring	ACJC10VL BULK

XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Solder Contacts, Bulk Pack	Latching	ACJC10S BULK
			XLR 3 pole female receptacle with 1/4" switching stereo jack and switching ground contact, Solder Contacts, Bulk Pack	Non-latching, Retention Spring	ACJC10SL BULK


PART NUMBER BREAKDOWN

AC SERIES THERMOPLASTIC C TYPE


SERIES PREFIX CONNECTOR TYPE CONTACT OPTIONS HOUSING TYPE CONTACT ORIENTATION LOCKING MECHANISM PACKAGING

E. G. ACJC5HL BULK AC (Series Prefix),JC Jack/Connector XLR, 5 Mono, Horizontal Printed Circuit Board, Latchless, Bulk Packaged.	AC	JC	5	H	L	BULK
SERIES PREFIX	AC	=	Series Prefix			
CONNECTOR TYPE	JC	=	Jack / Connector XLR			
CONTACT OPTIONS	5	=	Mono, Non Switching, XLR Grounded			
	6	=	Stereo, Non Switching, XLR Grounded			
	9	=	Stereo, Switching, XLR Grounded			
	10	=	Stereo, Switching, XLR with Ground Switch			
HOUSING TYPE	Blank	=	Standard			
	A	=	Low Profile / High Density			
CONTACT TYPE	V	=	Vertical Printed Circuit Board			
	V2	=	Vertical Printed Circuit Board (24mm)			
	H	=	Horizontal Printed Circuit Board			
	S	=	Solder Contacts			
LOCKING MECHANISM	Blank	=	Latching			
	L	=	Latchless			
PACKAGING	Blank	=	Individual Bags			
	BULK	=	Bulk Packed			


AC SERIES C TYPE SERIES




ACJC5H & ACJC5HL




ACJC5V & ACJC5VL




ACJC6H & ACJC6HL




ACJC6V & ACJC6VL




ACJC9H & ACJC9HL




ACJC9V & ACJC9VL




ACJC10H & ACJC10HL




ACJC10V & ACJC10VL




ACJC6AH & ACJC6AHL




ACJC6AV2 & ACJC6AV2L




ACJC9AH & ACJC9AHL




ACJC9AV2 & ACJC9AV2L




ACJC10AH & ACJC10AHL




ACJC10AV2 & ACJC10AV2L




C TYPE PANEL CUTOUT



C TYPE MOUNTING PITCH



C TYPE LOW PROFILE PANEL CUTOUT



C TYPE LOW PROFILE MOUNTING PITCH

XLR Connectors

AC Series Dual 1/4" (6.35mm) / XLR Chassis Mount

STANDARD DATA C TYPE CHASSIS RECEPTACLES

		VALUE	
		LOW PROFILE TYPE	STANDARD C TYPE
GENERAL CHARACTERISTICS	Number of contacts	5, 6, 9 or 10	
	Termination	Printed Circuit Board (PCB)	Printed Circuit Board (PCB) or Solder Bucket
	Flammability	UL 94HB	
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU	
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	50V	
	Test Voltage AC RMS	1500V	
	Current carrying capacity	7.5A	
	Typical Contact Resistance	≤50mΩ	
	Insulation Resistance (initial)	> 0.5GΩ	
	Insulation Resistance (after damp heat test)	> 0.2GΩ	
CLIMATIC CHARACTERISTICS	Protection Class	IP40	
	Operating Temperature	-25°C to +70°C	
MECHANICAL CHARACTERISTICS	Weight**	9.2g (0.02lb)	14g (0.030lb)
	Retention Spring separating force	≥20N	
	Mounting Screw torque max.	1.5Nm	
	Mechanical Operations	1500 mating cycles	
	Fastening***	Self-Tapping PT screw with thread 2.9 x 1.06 and of Tri-rondular configuration	
MATERIALS	Connector Shell	PA6.6 + 30% glass fibre reinforced, UL94HB	PA6.6 + 20% glass fibre reinforced, UL94HB
	Shell Finish	Black	
	Insulators	PA6.6 glass fibre reinforced, UL94HB	PA6.6 + 20% glass fibre reinforced, UL94HB
	XLR Contact		
	Material	Bronze	
	Plating	Gold over Nickel plated	
	Jack Contact		
	Material	Bronze	Brass
	Plating	Gold over Nickel plated	Silver over Copper plated
	Latch lock and Spring	Nickel Plated	
	Ground element	Nickel Plated	Silver over Copper plated

**Approximate weight in grams not including packaging. Please contact us for exact weight for shipping purposes.

***Refer to Page 132

Rev 6 - 03/2013



Features:

- Miniature version of the standard XLR series
- Diecast or Precision machined metal housings
- Metal cable clamp
- Precision machined pin contacts
- Stamped socket contacts
- Solder cup or Printed Circuit board contacts
- Available in 3, 4, 5 or 6 contacts
- Positive latchlock
- Flexible cable grommet

Part Number Breakdown: Page 48 **Specifications: Page 49**
PCB Footprints: Page 50 **Panel Cutouts: Page 50**

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		Dimensions in mm (inches)	Male cable connector, Machined contacts, Nickel Finish	3 pole	AG3M
		Dimensions in mm (inches)		4 pole	AG4M
		Dimensions in mm (inches)		5 pole	AG5M
		Dimensions in mm (inches)		6 pole	AG6M
		Dimensions in mm (inches)	Female cable connector, Stamped contacts, Nickel Finish	3 pole	AG3F
		Dimensions in mm (inches)		4 pole	AG4F
		Dimensions in mm (inches)		5 pole	AG5F
		Dimensions in mm (inches)		6 pole	AG6F
		Dimensions in mm (inches)	Female cable connector with locking ring, Stamped contacts, Nickel Finish.	3 pole	AG3FL
		Dimensions in mm (inches)		4 pole	AG4FL
		Dimensions in mm (inches)		5 pole	AG5FL
		Dimensions in mm (inches)		6 pole	AG6FL
		Dimensions in mm (inches)	Male chassis connector, Machined contacts, Nickel Finish	3 pole	AG3MCC
		Dimensions in mm (inches)		4 pole	AG4MCC
		Dimensions in mm (inches)		5 pole	AG5MCC
		Dimensions in mm (inches)		6 pole	AG6MCC
		Dimensions in mm (inches)	Female chassis connector, Stamped contacts, Nickel Finish	3 pole	AG3FCE
		Dimensions in mm (inches)		4 pole	AG4FCE
		Dimensions in mm (inches)		5 pole	AG5FCE
		Dimensions in mm (inches)		6 pole	AG6FCE
		Dimensions in mm (inches)	Male chassis connector, Horizontal PCB, Machined contacts, Nickel Finish	3 pole	AG3MCCH
		Dimensions in mm (inches)		4 pole	AG4MCCH
		Dimensions in mm (inches)		5 pole	AG5MCCH
		Dimensions in mm (inches)		6 pole	AG6MCCH
		Dimensions in mm (inches)	Female chassis connector, Horizontal PCB, Stamped contacts, Nickel Finish	3 pole	AG3FCCH
		Dimensions in mm (inches)		4 pole	AG4FCCH
		Dimensions in mm (inches)		5 pole	AG5FCCH
		Dimensions in mm (inches)		6 pole	AG6FCCH

XLR Connectors

G-Type Miniature XLR Connectors


		Male chassis connector, Horizontal PCB, Machined contacts, Thermoplastic shell	4 pole	AG4MPCH
		Female chassis connector, Stamped contacts, Nickel Finish	3 pole	AG3FCRV
	4 pole		AG4FCRV	
	5 pole		AG5FCRV	
	6 pole		AG6FCRV	

PART NUMBER BREAKDOWN

G TYPE CONNECTORS

E. G. **AG3MCCHB**
AG (Series Prefix), **3** contacts, **Male**, **Chassis Connector**, **Horizontal PCB Contacts**, **Black finish**.

SERIES PREFIX	AG	=	Series Prefix
CONTACT LAYOUTS	3	=	3 Contacts
	4	=	4 Contacts
	5	=	5 Contacts
	6	=	6 Contacts
GENDER	F	=	Female Socket Contacts
	M	=	Male Pin Contacts
	Blank	=	Cable Connector Standard (Male or Female)
SHELL STYLE	J	=	Cable Connector Large Cable clamp / boot O.D (Male or Female)
	L	=	Cable Connector with locking ring (Female)
	LL	=	Latchless (Chassis Connector)
	CC	=	Chassis Connector Circular Metal (Male)
	CE	=	Rear Mount (Chassis Connector)
	CM	=	Mid Mount (Chassis Connector)
	CR	=	Chassis Connector Rectangular Metal (Female)
	PC	=	Chassis Connector Plastic (Male)
	Blank	=	Solder Buckets (All styles except PC, CR)
CONTACT TYPE	H	=	Horizontal PCB (Style CC, PC only)
	V	=	Vertical PCB (Style CR only)
	Blank	=	Nickel Plated Finish
SHELL FINISH	B	=	Black Finish



STANDARD DATA G TYPE

		VALUE			
GENERAL CHARACTERISTICS	Number of Contacts	3	4	5	6
	Termination	Printed Circuit Board (PCB) or Solder Bucket			
	Max. Wire Gauge - Stranded Wire	AWG 24 - 0.5mm ²			AWG 28 - 0.38mm ²
	Flammability	UL94V-HB			
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU			
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	5A	5A	4A	1.2A
	Typical Contact Resistance	$\leq 10\text{m}\Omega$			
	Insulation resistance (initial) After Damp Heat Test	$\geq 510\text{M}\Omega$ $\geq 10\text{M}\Omega$			
	Dielectric Strength	1000 V dc			250 V dc
CLIMATIC CHARACTERISTICS	Protection Class	IP00			
	Operating Temperature	-30°C to +80°C (-20F - +176F)			
MECHANICAL CHARACTERISTICS	Insertion Spring Separating Force	$\geq 20\text{N}$			
	Cable O.D. Standard	2mm to 3.5mm (0.078" to 0.137")			
		3mm to 5mm (0.118" to 0.196")			
	Mechanical Operations	5000 mating cycles			2000 mating cycles
MATERIALS	Weight	13.5g (0.029lb)			
	Connector Shell	Bronze & Zinc			
	Connector Shell Finish	Nickel Plated			
	Insulators	PPS - Black			
	Male Contact	Material - Brass C3604 Plating - Gold over Silver Plated			
	Female Contact	Material - Brass C5210P Plating - Gold over Silver Plated			
	Latch Lock and Spring	SUS (AISI - 301) - Nickel Plated			
	Adaptor	PPS - Black			
	Cable Clamp	Bronze - Nickel Plated			
	Boot/Backshell	ABS - Black			
	Grommet	PU - Black			

¹⁾Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.


Rev 5 - 06/2017

XLR Connectors


G-Type Miniature XLR Connectors

PANEL CUTOUTS


- CONNECTOR SIDE OF PCB




AG3MCC




AG4MCC




AG5MCC




AG6MCC




AG3FCCH




AG4MCCH




AG4FCCH




AG4MCCH




AG5FCCH




AG5MCCH




AG6FCCH




AG6MCCH




AG3FCRV




AG4FCRV




AG5FCRV



AG6FCRV




AG4MPCH




AG3FCE


PANEL CUTOUTS - FRONT VIEW



AG3MCC
AG4MCC
AG5MCC
AG6MCC



AG3MCC
AG4MCC
AG5MCC
AG6MCC
AG4MPCH



AG3FCRV
AG4FCRV
AG5FCRV
AG6FCRV



SP/EP/AP SERIES LOUDSPEAKER CONNECTORS

SP Series

The SP Series are available in 2 or 4 pole chassis mount connectors. The durable thermoplastic housings are fitted with high power contacts to ensure optimal current carrying capacity. Completely intermataable with industry standard loudspeaker connections.

Features

- High current contacts for distortion free signal.
- Cost effective durable thermoplastic shell
- Available in 2 and 4 contact arrangements.
- Overmolded cable support boot or PG gland with or without cable support strain relief.
- Quick release, vibration resistant latch lock.
- UL, cUL recognized components (File no. E339831)
- Precision machined contacts
- Thermoplastic shell

Options

- Solder termination / Tab or Printed Circuit Board versions, Screw Terminals
- Nickel Plated Zinc Alloy shell
- Black finished Zinc Alloy shell

EP Series

The EP Series incorporates a rugged zinc diecast shell to give it maximum durability when used in demanding situations. The EP cable connector cable flex relief design minimises cable bend stress at point of entry into the connector housing.

Features

- High current contacts for distortion free signal.
- Tough, durable zinc diecast shell
- Cable clamp capable of supporting cables from 9mm (0.35") to 16mm (0.63") in diameter.
- Quick release, vibration resistant latch lock.
- AP & EP series are completely intermataable.
- Precision machined contacts

Options

- Nickel Plated Zinc Alloy shell
- Black finished Zinc Alloy shell
- Available in 3, 4, 5, 6 and 8 contact arrangements

AP Series

The AP Series Shell is manufactured from tough, durable thermoplastic, and ideal for fixed indoor installations. Both the EP and AP Series utilise the same contact and insulator components.

Features

- High current contacts for distortion free signal.
- Cost effective durable thermoplastic shell
- Quick release, vibration resistant latch lock.
- AP & EP series are completely intermataable.
- Precision machined contacts
- Thermoplastic shell

Options

- Available in 4, 5, 6, and 8 contact arrangements.

Ordering Codes

We have listed the more common ordering codes in each section. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

Speaker Connectors

SP Series



SP SERIES

Amphenol's range of loudspeaker connectors have been further enhanced with the introduction of the SP Series. Designed to complement the popular EP/AP Series, we now offer a range of loudspeaker connectors to suit most applications. SP Series chassis connectors are available in industry standard PCB footprints with solder tabs. SP Series cable plugs are available with screw or solder terminals.

Features:

- Quick release, vibration resistant latch lock
- 2 or 4 pole
- Solder tabs, PCB Contacts, Solder or Screw Terminals
- Chuck type or PG Gland cable clamp
- Various mounting hole options
- 30A Current rating
- Thermoplastic or Metal housing (Cable Plugs)
- UL, cUL recognized components (File no. E339831)
- Industry standard mating









Part Number Breakdown: Page 56 **Specifications: Page 60**
PCB Footprints: Page 58 **Assembly Instructions: 59**

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	CONTACT TYPE	SHELL COLOUR	PART NUMBER
		87 [3.43"] 110 [4.33"] 28 [1.10"]	2 pole, Cable connector, Thermoplastic shell, Blue sleeve	Screw	Black	SP-2-F
				Solder	Black	SP-2-FS
		111 [4.36"] 109 [4.33"] 28 [1.10"]	2 pole, Cable connector, Thermoplastic shell, Blue sleeve, PG Gland	Screw	Black	SP-2-FG
				Solder	Black	SP-2-FSG
		179 [7.06"] 110 [4.33"] 28 [1.10"]	2 pole, Cable connector, Thermoplastic shell, Blue sleeve, PG Gland strain relief	Screw	Black	SP-2-FL
				Solder	Black	SP-2-FSL
		87 [3.43"] 110 [4.33"] 28 [1.10"]	2 pole, Cable connector, Metal shell, Blue sleeve	Screw	Nickel	SP-2-FN
				Solder	Nickel	SP-2-FNS
				Screw	Black	SP-2-FB
				Solder	Black	SP-2-FBS
		111 [4.36"] 109 [4.33"] 28 [1.10"]	2 pole, Cable connector, Metal shell, Blue sleeve, PG Gland	Screw	Nickel	SP-2-FNG
				Solder	Nickel	SP-2-FNSG
				Screw	Black	SP-2-FBG
				Solder	Black	SP-2-FBSG
		179 [7.06"] 110 [4.33"] 28 [1.10"]	2 pole, Cable connector, Metal shell, Blue sleeve, PG Gland strain relief	Screw	Nickel	SP-2-FNL
				Solder	Nickel	SP-2-FNSL
				Screw	Black	SP-2-FBL
				Solder	Black	SP-2-FBSL









Speaker Connectors

SP Series

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	CONTACT TYPE	SHELL COLOUR	PART NUMBER
		4 pole, Cable connector, Thermoplastic black shell, Blue sleeve	Screw	Black	SP-4-F	
						SP-4-FS
		4 pole, Cable connector, Thermoplastic black shell, Blue sleeve, PG Gland	Screw	Black	SP-4-FG	
						SP-4-FSG
		4 pole, Cable connector, Thermoplastic black shell, Blue sleeve, PG Gland strain relief	Screw	Black	SP-4-FL	
						SP-4-FSL
		4 pole, Cable connector, Metal shell, Blue sleeve	Screw	Nickel	SP-4-FN	
						SP-4-FNS
			Solder	Nickel	SP-4-FB	
						SP-4-FBS
		4 pole, Cable connector, Metal shell, Blue sleeve, PG Gland	Screw	Nickel	SP-4-FNG	
						SP-4-FNSG
			Solder	Black	SP-4-FBG	
						SP-4-FBSG
		4 pole, Cable connector, Metal shell, Blue sleeve, PG Gland strain relief	Screw	Nickel	SP-4-FNL	
						SP-4-FNSL
			Solder	Black	SP-4-FBL	
						SP-4-FBSL







Speaker Connectors

SP Series

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 4.3 [0.169"], 23.5 [0.925"], 5.7 [0.224"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	2 pole, D flange, Thru holes, Solder tabs 3/16"	Black	SP-2-MD
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 5.7 [0.224"], 23.5 [0.925"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	2 pole, D flange, Thru holes, Horizontal PCB	Black	SP-2-MDH
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 4.3 [0.169"], 23.5 [0.925"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	2 pole, D flange, Thru holes, Vertical PCB	Black	SP-2-MDV
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 4.3 [0.169"], 23.5 [0.925"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	4 pole, D flange, Thru holes, Solder tabs 3/16"	Black	SP-4-MD
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 4.3 [0.169"], 23.5 [0.925"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	4 pole, D flange, Thru holes, Solder tabs 3/16"	Grey	SP-4-MD-8
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 4.3 [0.169"], 23.5 [0.925"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	4 pole, D flange, Self Tapping holes, Solder tabs 3/16"	Black	SP-4-MDT
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 28.2 [1.110"], 5.7 [0.224"], 23.5 [0.925"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	4 pole, D flange, Thru holes, Horizontal PCB	Black	SP-4-MDH
		Dimensions in mm (inches): 26.0 [1.024"], 31.0 [1.220"], 19.0 [0.748"], 24.0 [0.945"], 2.5 [0.098"], 4.5 [0.177"], 35.7 [1.406"], 9.6 [0.378"], 6.3 [0.248"]	4 pole, D flange, Thru holes, Solder tabs 1/4"	Black	SP-4-MDQ

Speaker Connectors

SP Series

PRODUCT - FIGURE		DESCRIPTION	VARIATIONS	PART NUMBER
		4 pole, D flange, Self Tapping holes, Horizontal PCB	Grey	SP-4-MDHT-8
		4 pole, D flange, Self Tapping holes, Horizontal PCB	Black	SP-4-MDHT
		4 pole, D flange, Thru holes, Vertical PCB	Black	SP-4-MDV
		4 pole, D flange, Thru holes, Vertical PCB	Red	SP-4-MDV-2
		4 pole, D flange, Self Tapping holes, Vertical PCB	Grey	SP-4-MDVT-8
		4 pole, EP flange, Thru holes, Solder tabs 3/16"	Black	SP-4-MC

Speaker Connectors

SP Series

PART NUMBER BREAKDOWN


SP SERIES - CABLE CONNECTORS

E. G. **SP-4-FNSG**
SP (Series Prefix), 4 contacts, F (Cable Connector), N (Metal Shell Nickel Finish),
S (Solder Terminals), G (PG Gland)

SERIES PREFIX	SP	-	4	-	F	N	S	G	-	B	PACKAGING
CONTACT LAYOUTS					GENDER					BACKSHELL TYPE	
GENDER					SHELL FINISH					TERMINATION	
SHELL FINISH	Blank	=	Thermoplastic - Black								
	N	=	Metal - Nickel Finish								
	B	=	Metal - Black Finish								
TERMINATION	Blank	=	Screw Terminals								
	S	=	Solder Terminals								
BACKSHELL TYPE	Blank	=	Standard								
	G	=	PG Gland								
	L	=	PG Gland Strain Relief								
PACKAGING	Blank	=	Individual Bags								
	B	=	Bulk Packed								

PART NUMBER BREAKDOWN

SP SERIES - CHASSIS CONNECTORS



E. G. SP-4-MDHT-8B

SP (Series Prefix), 4 contacts, M(Chassis Connector), D (D Shell), Horizontal Printed Circuit Board, Self Tapping mounting holes - 8 (Grey), Bulk Packaged.


SERIES PREFIX	SP	≡	Series Prefix
CONTACT LAYOUT	2	≡	2 Contacts
	4	≡	4 Contacts
GENDER	M	≡	Chassis Connector
SHELL STYLE	D	≡	Standard 'D' Type flange
	C	≡	EP Series Circular flange
TERMINATION	Blank	≡	Solder tabs - 3/16" terminals
	Q	≡	Solder tabs - 1/4" terminals
	V	≡	Vertical Printed Circuit Board
	H	≡	Horizontal Printed Circuit Board
MOUNTING HOLE	Blank	≡	Thru Hole
	T	≡	Self Tapping
SHELL COLOUR	Blank	≡	Black
	2	≡	Red
	8	≡	Grey
PACKAGING	Blank	≡	Individual Bags
	B	≡	Bulk Packed

Speaker Connectors


SP Series

SP SERIES


SP-2-MDH




SP-2-MDV



SP-4-MDH
SP-4-MDHT-8
SP-4-MDHT




SP-4-MDV
SP-4-MDV-2
SP-4-MDVT-8




SP SERIES PANEL CUTOUT

SP-2-MD ***
SP-4-MD ***




SP-4-MC






Slide the nut onto the cable




Strip the cable and twist the conductors.



Insert the conductors into the rear of contacts on the insert. Tighten the screws to 0.35Nm (3.0 lb-in) using a flat screwdriver with tip width of 2.5mm max.




Install the cable clamp, flush to the insert making sure to align the slot as shown in the picture.



Orientate the insert and cable clamp as shown then push all together into the shell.

PI 1070 ASSEMBLY INSTRUCTIONS

SP SERIES CABLE CONNECTOR



Thread the nut onto the shell to activate the cable clamp and close the connector assembly.

Speaker Connectors

SP Series

STANDARD DATA SP SERIES CONNECTORS

		VALUE
GENERAL CHARACTERISTICS	Number of contacts	2 or 4
	Termination (Chassis)	Printed Circuit Board (PCB) or Solder Tabs 3/16"
	Termination (Cable Plugs)	Screw or Solder Terminals
	Flammability	UL94HB
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	133V ¹⁾
	Test Voltage AC RMS	1500V
	Current carrying capacity	30A
	Typical Contact Resistance	≤3mΩ
	Insulation Resistance (initial)	≥2GΩ
	Insulation Resistance (after damp heat test)	≥1GΩ
CLIMATIC CHARACTERISTICS	Protection Class (Mated Condition)	IP20 (IP40)
	Operating Temperature	-25 °C to +75 °C (-13°F to +167°F)
MECHANICAL CHARACTERISTICS	Weight** - Chassis Connectors	12g (0.026lb)
	Weight** - Cable Plug	
	- Thermoplastic	44g (0.097lb)
	- Metal	65g (0.143lb)
	Weight** - Cable Plug PG	
	- Thermoplastic	44g (0.097lb)
	- Metal	65g (0.143lb)
	Weight** - Cable Plug PG S/Relief	
	- Thermoplastic	68g (0.150lb)
	- Metal	89g (0.196lb)
MATERIALS	Typical Cable retention force	200N (Subject to cable material and O.D.)
	Cable O.D range	
	- Chuck Clamp	2 pole 5-10mm (0.19" - 0.39")
	- PG16 Gland	9-14mm (0.35" - 0.55")
	- PG16 Gland S/Relief	6-12mm (0.23" - 0.47") 9-14mm (0.35" - 0.55")
	Conductor Size	8-14mm (0.31" - 0.55")
	- Screw Terminals	1.5mm ² - 4mm ² (AWG16 - AWG12)
	- Solder Bucket	1.5mm ² - 6mm ² (AWG16 - AWG10)

**Approximate weight in grams not including packaging. Please contact us for exact weight for shipping purposes.

¹⁾Not suitable for domestic applications above 50V



EP SERIES

The EP Series has set the standard in high performance speaker connectors. Apart from its durability and strength, it offers consistent superior power handling capabilities.

Features:

- Solder Bucket connections.
- Precision machined contacts.
- Diecast Metal Housings
- High current contacts
- Male and female cable and chassis connectors available.

Options: Black Finish Shell

Specifications: Page 64

Panel Cutouts: Page 65

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
ISO ASSEMBLY OF EP MALE		EP Male cable connector, Machined contacts, Metal Shell	3 pole nickel finish	EP-3-12	
			3 pole black finish	EP-3-12B	
			4 pole nickel finish	EP-4-12	
			4 pole black finish	EP-4-12B	
			5 pole nickel finish	EP-5-12	
			5 pole black finish	EP-5-12B	
			6 pole nickel finish	EP-6-12	
			6 pole black finish	EP-6-12B	
			8 pole nickel finish	EP-8-12	
			8 pole black finish	EP-8-12B	
ISO ASSEMBLY OF EP FEMALE		EP Female cable connector, Machined contacts, Metal Shell	3 pole nickel finish	EP-3-11P	
			3 pole black finish	EP-3-11PB	
			4 pole nickel finish	EP-4-11P	
			4 pole black finish	EP-4-11PB	
			5 pole nickel finish	EP-5-11P	
			5 pole black finish	EP-5-11PB	
			6 pole nickel finish	EP-6-11P	
			6 pole black finish	EP-6-11PB	
			8 pole nickel finish	EP-8-11P	
			8 pole black finish	EP-8-11PB	

Speaker Connectors

EP Series

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			EP Male chassis mount, Round Flange, Machined contacts, Metal Shell	3 pole nickel finish 3 pole black finish 4 pole nickel finish 4 pole black finish 5 pole nickel finish 5 pole black finish 6 pole nickel finish 6 pole black finish 8 pole nickel finish 8 pole black finish	EP-3-14 EP-3-14B EP-4-14 EP-4-14B EP-5-14 EP-5-14B EP-6-14 EP-6-14B EP-8-14 EP-8-14B
			EP Female chassis mount, Round Flange, Machined contacts, Metal Shell	3 pole nickel finish 3 pole black finish 4 pole nickel finish 4 pole black finish 5 pole nickel finish 5 pole black finish 6 pole nickel finish 6 pole black finish 8 pole nickel finish 8 pole black finish	EP-3-13P EP-3-13PB EP-4-13P EP-4-13PB EP-5-13P EP-5-13PB EP-6-13P EP-6-13PB EP-8-13P EP-8-13PB



AP SERIES

The AP Series provides the same power handling performance as the EP Series in a cost effective, yet durable Thermoplastic housing.

Features:

- Solder Bucket connections.
- Precision machined contacts.
- Thermoplastic Housings
- High current contacts
- Male & Female Cable and Chassis connectors available.

Specifications: Page 64






Panel Cutouts: Page 65

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		AP Male cable connector, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-12	
			5 pole	AP-5-12	
			6 pole	AP-6-12	
			8 pole	AP-8-12	
		AP Female cable connector, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-11	
			5 pole	AP-5-11	
			6 pole	AP-6-11	
			8 pole	AP-8-11	
		AP Male chassis mount, Round Flange, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-14	
			5 pole	AP-5-14	
			6 pole	AP-6-14	
			8 pole	AP-8-14	
		AP Female chassis mount, Round Flange, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-13	
			5 pole	AP-5-13	
			6 pole	AP-6-13	
			8 pole	AP-8-13	
		AP Male chassis mount, Rectangular Flange, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-22	
			5 pole	AP-5-22	
			6 pole	AP-6-22	
			8 pole	AP-8-22	
		AP Female chassis mount, Rectangular Flange, Machined contacts, Thermoplastic Black shell.	4 pole	AP-4-21	
			5 pole	AP-5-21	
			6 pole	AP-6-21	
			8 pole	AP-8-21	

Speaker Connectors

AP Series

STANDARD DATA EP/AP

		VALUE				
GENERAL CHARACTERISTICS	Number of contacts	3	4	5	6	8
	Contact Arrangements (Front view of pin insert)					
	Termination	SOLDER				
	Wire Gauge - Stranded wire:	12AWG	12AWG	12AWG	12AWG	14AWG
	Flammability	UL94V-0				
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU				
ELECTRICAL CHARACTERISTICS	Service Voltage RMS ¹⁾	460V	660V	200V	200V	100V
	Test Voltage AC RMS	2400V	3000V	1600V	1600V	1300V
	Current carrying capacity	20A	20A	20A	20A	15A
	Typical Contact Resistance	≤3mΩ				
	Insulation Resistance	≥1000MΩ				
CLIMATIC CHARACTERISTICS	Protection Class	IP40				
	Operating Temperature	-25°C to +75°C (-13°F to +167°F)				
MECHANICAL CHARACTERISTICS	Weight - EP 11 & 12 ²⁾	80g (0.176lb)	84g (0.185lb)	86g (0.189lb)	86g (0.189lb)	86g (0.189lb)
	Weight - EP 13 & 14 ²⁾	48g (0.105lb)	50g (0.110lb)	54g (0.119lb)	54g (0.119lb)	54g (0.119lb)
	Weight - AP 11 & 12 ²⁾	N/A (0.092lb)	42g (0.097lb)	44g (0.097lb)	44g (0.097lb)	44g (0.097lb)
	Weight - AP 13, 14, 21 & 22 ²⁾	N/A (0.057lb)	26g (0.066lb)	30g (0.066lb)	30g (0.066lb)	28g (0.061lb)
	Typical Cable retention force	22Kg to 44Kg (50lb to 100lb) - Dependant on cable material and diameter				
	Mechanical operations	1000 mating cycles				

Rev 3 - 03/2013

¹⁾ Not suitable for domestic applications above 50V

²⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.


STANDARD DATA EP/AP (CONT'D)

		DETAILS	
MATERIALS	TYPE	AP	EP
	Connector shell	Modified PPE Resin	Diecast Zinc Alloy
	Shell finish	Black	Satin Nickel or Black
	Insulators	UL94V-0 PBT Resin	
	Cable Bushing	Silicon Rubber	UL94 HB Thermoplastic Elastomer
	Male contact Machined - Solder		
	Material / Plating	Brass / Bright Tin	
	Female contact Machined - Solder		
	Material / Plating	Brass / Bright Tin	
CLAMPING CHARACTERISTICS	Cable OD Range	11mm to 17mm (0.43" to 0.67")	9mm to 16mm (0.35" to 0.63")
	Retention Method	Two opposing plastic screws	Metal saddle clamp


Rev 3 - 03/2013

EP/AP SERIES PANEL CUTOUT DATA - FRONT VIEW

EP 13/AP 13/AP 21



EP 14/AP 14/AP 22



Power Connectors

HP Series



HP Series

HP Series connectors are suitable for AC power supply where a latch locking connector is required. They are rated at 25 A / 250 Vac. Connectors are keyed and colour coded for power-in (Blue) and power-out (Grey).

⚠ THE HP SERIES OF CONNECTORS ARE NOT DESIGNED TO BE "HOT PLUGGED" AND SO ARE WITHOUT "BREAKING CAPACITY". IN OTHER WORDS, THE CONNECTORS SHOULD NOT BE CONNECTED OR DISCONNECTED LIVE OR WHEN UNDER LOAD

Features:

- Quick release, vibration resistant latch lock
- 3 pole
- Screw Terminals or Solder Tab 3/16"
- Chuck type cable clamp
- 25A Current rating
- Thermoplastic housing
- Industry standard mating
- UL, cUL recognized components (File no. E339831)



PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	CONTACT TYPE	SHELL COLOUR	PART NUMBER
		Dimensions in mm (inches)	3 pole, Cable connector, Thermoplastic shell, Blue sleeve, keyed for power-in	Screw	Blue	HP-3-F
		Dimensions in mm (inches)	3 pole, Cable connector, Thermoplastic shell, Grey sleeve, keyed for power-out	Screw	Grey	HP-3-FG
		Dimensions in mm (inches)	3 pole, Chassis connector, Thermoplastic shell, Blue, keyed for power-in	Solder Tab 3/16"	Blue	HP-3-MD
		Dimensions in mm (inches)	3 pole, Chassis connector, Thermoplastic shell, Grey, keyed for power-out	Solder Tab 3/16"	Grey	HP-3-MDG
		Dimensions in mm (inches)	3 pole, Chassis connector, Thermoplastic shell, Blue, keyed for power-in, without insulation divider	Solder Tab 3/16"	Blue	HP-3-MDW
		Dimensions in mm (inches)	3 pole, Chassis connector, Thermoplastic shell, Grey, keyed for power-out, without insulation divider	Solder Tab 3/16"	Grey	HP-3-MDGW

STANDARD DATA HP SERIES CONNECTORS

		VALUE
GENERAL CHARACTERISTICS	Number of contacts	2 + PE
	Termination	Screw or Solder Tab 3/16"
	Flammability	UL94V-0
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Rated Operating Voltage	250VAC
	Test Voltage AC RMS	3200V
	Current carrying capacity	25A
	Typical Contact Resistance	$\leq 3\text{m}\Omega$
	Insulation Resistance (initial)	$\geq 2\text{G}\Omega$
	Insulation Resistance (after damp heat test)	$\geq 1\text{G}\Omega$
CLIMATIC CHARACTERISTICS	Protection Class	IP20
	Operating Temperature	-25°C to +75°C (-13°F to +167°F)
MECHANICAL CHARACTERISTICS	Weight** - Chassis Connector - Cable Plug	12g (0.026lb) 32g (0.070lb)
	Typical Cable retention force	200N (Subject to cable material and O.D.)
	Cable O.D range - Blue Chuck Clamp - Black Chuck Clamp	5mm - 7.5mm (0.19" - 0.29") 7.5mm - 15mm (0.29" - 0.59")
	Conductor Size - Screw Terminals	2.5mm² (AWG14)
MATERIALS	Connector Shell / Finish	PA66 GF30 / Black
	Insulators	PA66 GF30
	Cable Boot / Backshell	Santoprene / PBT
	Cable Clamp (Chuck)	P.O.M
	Contact Plug - Material / Plating	Brass / Silver
	Contact Chassis - Material / Plating	Phosphor Bronze / Silver

**Approximate weight in grams not including packaging. Please contact us for exact weight for shipping purposes.

Rev 4 - 08/2016

Power Connectors

HPT Series



HPT Series

HPT Series connectors are suitable for AC power supply where a durable latch locking connector is required. They are rated at 16A, 250 Vac. HPT Series connectors can be connected or disconnected under load and are IP65 rated.

Features:

- Quick release, vibration resistant latch lock
- 3 pole
- Chuck type cable clamp
- 16A current rating
- Thermoplastic housing
- Industry standard mating
- IP65 rated
- US. Patents Pending

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	CONTACT TYPE	SHELL COLOUR	PART NUMBER
		79 [3.098"] 29.3 [1.152"] Ø26.5 [Ø1.043"]	3 pole, Female Cable connector, Locking, Thermoplastic shell, Screw terminals	Screw	Black/ Yellow	HPT-3-F
		77 [3.043"] 32.0 [1.260"] Ø26.5 [Ø1.043"]	3 pole, Male Cable connector, Locking, Thermoplastic shell, Screw terminals	Screw	Black/ Yellow	HPT-3-M
		19.0 [.748"] Ø3.2 [Ø.126"] 31.0 [1.220"] 24.0 [945"] 26.0 [1.023"] 23.7 [.933"] 4.5 [.177"] 2.5 [.098"] 40.5 [.413"]	3 pole, Chassis Inlet connector, Thermoplastic shell, 1/4" flat tab terminals	Tab 1/4"	Black/ Yellow	HPT-3-MD
		19.0 [.748"] Ø3.2 [Ø.126"] 31.0 [1.220"] 24.0 [945"] 26.0 [1.024"] 23.7 [.933"] 4.5 [.177"] 2.5 [.098"] 40.5 [.413"]	3 pole, Chassis Inlet connector, Thermoplastic shell, without insulation divider, 1/4" flat tab terminals	Tab 1/4"	Black/ Yellow	HPT-3-MDW
		24.4 [Ø.961"] Ø3.2 [Ø.126"] 35.4 [1.394"] 24.4 [961"] 35.4 [1.394"] 26.0 [.945"] 4.5 [.177"] 5.7 [.224"] 40.5 [.413"]	3 pole, Chassis Outlet connector, Thermoplastic shell, 1/4" flat tab terminals	Tab 1/4"	Black/ Yellow	HPT-3-FD
			3 pole, Chassis Outlet connector, Thermoplastic shell, Screw terminals	Screw	Black/ Yellow	HPT-3-FDS
		50.0 [1.969"] 35.4 [1.394"] 61.0 [2.402"] 24.4 [961"] 23.7 [.934"] 26.2 [.103"] 4.5 [.177"] 5.7 [.224"] 9.5 [.374"]	3 pole, Chassis Inlet-Outlet combination, Thermoplastic shell, 1/4" flat tab terminals	Tab 1/4"	Black/ Yellow	HPT-3-CC



 **Dante™**

Amphe-Dante Adapters

Amphe-Dante are Dante™ audio to analogue audio adapters, each with one RJ45 Dante input, and one and two (respectively) AX series XLR analogue outputs in a molded housing.

Amphe-Dante products enable simple connection of analogue equipment to a Dante network and can receive audio channels from a Dante network and provide studio-quality, low-latency audio via an XLR connector to analogue audio equipment. Any audio available on the Dante network can be routed via the XLR outputs to an amplifier, powered speaker, mixing console, digital signal processor (DSP), or other analogue audio device.

Amphe-Dante feature high-quality digital-to-analogue converters, and support a range of sample rates and bit depths. They can provide a hardware master clock for a Dante network. As with other Dante products, the freely available Dante Controller software application is used to automatically discover and configure Amphe-Dante devices connected to the Dante network. Device names, channel labels, signal routing and other parameters (for example, sample rate and latency) can be configured via the network using Dante Controller. A variety of network and clock synchronisation diagnostic tools are also available in Dante Controller.

Amphe-Dante products use Power over Ethernet (PoE). Power can be provided through the Ethernet cable from a PoE-capable network switch, or from a separate PoE injector.

Available Software Options (required)

Dante Controller

Dante Controller is a free software application that enables you to route audio and configure devices on a Dante network. As well as automatic device discovery, one-click signal routing and user-editable device and channel labels, Dante Controller provides essential device status information and powerful real-time network monitoring, including device-level latency and clock stability stats, multicast bandwidth usage, and customized event logging, enabling you to quickly identify and resolve any potential network issues.


Dante Via

Dante Via is powerful and easy-to-use software that delivers unprecedented routing of computer-based audio, allowing a wide range of applications and devices to be networked and interconnected, easily and inexpensively. Dante Via network-enables locally-connected USB and Firewire devices, and a huge range of software applications, allowing you to route computer-based audio across an existing Dante network, and create standalone Dante networks without dedicated Dante hardware.

Dante Virtual Soundcard

Dante Virtual Soundcard turns your computer into a Dante-powered workstation, seamlessly integrating your PC or Mac with Dante audio devices on your network. You can instantly connect to a Dante network to record, process and playout using any audio application and any combination of Dante-enabled devices.

Dante Controller



All software can be purchased and downloaded at amphenolaudio.com/products/dante

Data Connectors


Amphe-Dante Connectors




Features:

- Dante™ audio input
- One channel or Two channel analogue output
- Durable overmolded housing
- Resilient cable strain relief
- RJ45 metal connectors with integrated LED's
- AX Series XLR connectors

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	LENGTH	PART NUMBER
A photograph of the single-channel Amphe-Dante connector.	A technical drawing of the single-channel Amphe-Dante connector. It shows the RJ45 input and XLR output with dimensions: total length 101mm, RJ45 length 72mm, and XLR length 29.2mm.		Dante™ audio to analogue audio adapter, 0x1, RJ45 input, 1 channel XLR output.	500mm	RJD1112-0050
A photograph of the two-channel Amphe-Dante connector.	A technical drawing of the two-channel Amphe-Dante connector. It shows the RJ45 input and two XLR outputs with dimensions: total length 101mm, RJ45 length 72mm, and XLR length 29.2mm.		Dante™ audio to analogue audio adapter, 0x2, RJ45 input, 2 channel XLR output.	500mm	RJD1212-0050



Example 1



Example 2

Example 1 - Connecting analog audio equipment to a Dante system

Amphe-Dante can be used to easily integrate traditional analog audio equipment into a networked Dante system. A large ecosystem of Dante devices is available, including Dante-enabled mixing consoles, DSP units and wall plates. In the far left diagram, a zoned audio system is shown with traditional analog amplifiers and speakers connected to the Dante network using Amphe-Dante devices.

Example 2 - Routing local computer audio to traditional devices over a Dante network

In combination with Dante Via software, Amphe-Dante can create simple audio systems using computer software (e.g. iTunes®, Spotify®, etc) and USB audio devices (e.g. a microphone). In the adjacent near left diagram below, a simple background music system with a microphone input for announcements is shown, where Amphe-Dante is used to connect networked audio channels to a pair of traditional analog powered loudspeakers.

Dante™ is a trademark of Audinate Pty Ltd. Audinate® is a registered trademark of Audinate Pty Ltd.


SPECIFICATIONS

		RJD1112-XXXX*	RJD1212-XXXX*
GENERAL	Input Connector	1 x RJ45 (Ethernet)	
	Output Connector	1x XLR Male	2x XLR Male
ELECTRICAL	Power Consumption	< 2 Watt	
	Power over Ethernet (Required)	Class 1 IEEE 802.3af POE PD compliant	
ANALOG AUDIO	Output level (Balanced)	+4dBu @ 0dBFS	
	Output Impedance	150 ohm balanced or 75 ohm unbalanced	
	Frequency Response	20 Hz to 20 kHz (-/+0.5 dB)	
	Dynamic Range	> 100 dB	
	Signal to Noise	> 100 dB	
	Total Harmonic Distortion	< 0.05% at +4 dBu	
	Channel Separation	N/A	> 100 dB
DANTE® AUDIO	Channel Matching	N/A	< 0.25 dB
	Number of Channels	1 output channel	2 output channels
	Sample Rate	44.1 kHz, 48 kHz (default), and 96 kHz	
	Bit Depth	24 bits	
	Network Speed	100 Mbps	
CLIMATIC	Network Interface	Latency from 1ms	
	Protection Class	IP41	
MECHANICAL	Operating Temperature	-5°C to +60°C (23°F to +140°F)	
	Insertion and Withdrawal Force	≥10N - ≤30N	
MATERIALS	Weight	Single Channel XLR Two Channel XLR	136g (0.299lb) 192g (0.423lb)
	Housing	PVC 60P Black	

*XXXX denotes length

Rev 2 - 12/2017

LED STATUS



FUNCTION	LEFT LED	RIGHT LED	COMMENT
Off	OFF	OFF	No Power
Device is booting	Solid GREEN	Solid RED	
Slave with sync	Blinking GREEN	Solid GREEN	Normal operation
Clock Master	Blinking GREEN	Blinking GREEN	Normal operation
Any runtime error	Blinking GREEN	Blinking RED	Normal operation
Identify	Alternating RED and GREEN	Alternating RED and GREEN	Blinking for 6 seconds (cycle every 0.5 seconds)
Failsafe (bootloader)	Blinking RED	Blinking RED	Failsafe, Corrupt Capability (red in DC)
Upgrade (bootloader)	Blinking ORANGE	Blinking ORANGE	Device is upgrading

Data Connectors

XLRnet RJ45 Ethernet Series



XLRnet was designed in conjunction with the Amphenol Data / Telecom product group of Amphenol Canada Corp., a subsidiary of Amphenol Corporation. Utilising our combined expertise and knowledge of the professional audio and high-speed data markets we are proud to offer the XLRnet series. Featuring Class D (10/100 BASE-T), CAT5E (1000 BASE-T) or CAT6 (10GBASE-T) ethernet performance in A, B or D shell housings with integrated LED's and complete shielding options we have your high-speed data requirements covered.

Features

- Class D (10/100 BASE-T), CAT5E (1000 BASE-T) or CAT6 (10GBASE-T) ethernet performance
- A, B or D type chassis housings
- IDC or IDC 110 punch down terminals
- RJ45 feedthrough panel connectors
- Shielded or non-shielded
- LED indicators in a variety of colours.
- Compact design
- Cable plug housings
- Quick and simple installation

Options

- Horizontal or Vertical PCB contacts
- Bulk Packaging
- LED colour - Red, Green, Yellow or Blue combinations

Ordering Codes

We have listed the more common ordering codes in each section. Please contact us if you need any further assistance.

XLRnet Connectors

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.



XLRnet SERIES

Features/Benefits:

- XLR RJ45 Cable plug housing.
- Designed for pre-assembled RJ45 cables.
- Quick and simple installation.
- Cost effective method for harsh environments.
- No cabling in field required.
- No tools required for installation.
- Available in Nickel or Black housings.
- Coloured boots / Backshells

Specifications: Page 74


Part Number Breakdown : Page 74

Assembly Instructions: Page 75

NOTE* RJ45 preassembled cable sold separately and is not included with the XLRnet connector.

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		84 [3.31"]	XLRnet, XLR cable plug housing to suit preassembled RJ45 cables, Nickel Finish	Standard	RJX8M
			Bulk Pack	RJX8M BULK	
		84 [3.31"]	XLRnet, XLR cable plug housing to suit preassembled RJ45 cables, Black Finish	Standard	RJX8MB
			Bulk Pack	RJX8MB BULK	

ISO VIEW OF RJX8M



Data Connectors

XLRnet RJ45 Ethernet Series

PART NUMBER BREAKDOWN

XLRnet SERIES


	SERIES PREFIX	CONTACT LAYOUTS	GENDER	SHELL FINISH	PACKAGING
	RJX	8	M	B	BULK
E. G. RJX8MB BULK RJX (Series Prefix), 8 contacts, M (Cable Connector), B (Black Finish), Bulk Packaged					
SERIES PREFIX	RJX	=	Series Prefix		
CONTACT LAYOUT	8	=	RJ45 Cable Housing		
GENDER	M	=	Male Cable Plug		
SHELL FINISH	Blank	=	Nickel Plated Finish		
	B	=	Metal - Black Finish		
PACKAGING	Blank	=	Individual Bags		
	BULK	=	Bulk Packed		

STANDARD DATA XLRnet SERIES

		VALUE
GENERAL CHARACTERISTICS	Termination	Preassembled RJ45 Cable (Not supplied)
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
CLIMATIC CHARACTERISTICS	Protection Class	IP40
	Operating Temperature	-25°C to +75°C (-13°F to -167°F)
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal force	≥10N - ≤20N
	Weight ²⁾	26g (0.057lb)
	Cable O.D. range	5 or 8mm (0.20" or 0.31")
	Mechanical Operations	1000 mating cycles
MATERIALS	Connector shell - Metal Shell finish	Diecast Zinc Alloy Satin nickel or Black
	Boot / Backshell Finish	UL94V-0 Noryl N190 / Valox Black
	Cable clamp	PA6
	Sleeve	Valox

²⁾ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

XLRnet SERIES CABLE ASSEMBLY INSTRUCTIONS




1
Snap or cut off release tab of the RJ45 plug.
Failure to remove the RJ45's Release Tab will make the XLRnet assembly permanently latching. The XLRnet series has an independent panel side latching system.



4

Close clamp-boot, fasten the two tabs together to lock.




6

Thread the nut (backshell) onto the shell (torque 0.8Nm-1.2Nm) to close the connector assembly.



5

Push clamp-boot & cable together into the shell



3

Install the cable clamp-boot.

Data Connectors

XLRnet RJ45 Ethernet Series



XLRnet SERIES A & B Type

Features:

- RJ45 Class D (10/100 BASE-T), CAT5E (1000 BASE-T) or CAT6 (10GBASE-T) Ethernet performance
- A or B type chassis housings
- Shielded or non-shielded
- LED indicators in a variety of colours.
- Horizontal or Vertical PCB
- Mates with XLRnet cable plugs or standard RJ45 plug.

Part Number Breakdown: Page 79

Specifications: Page 83

PCB Footprints: Page 82

Recommended Fastener: Page 133

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	TYPE	LED* LHS/RHS	PART NUMBER
			XLRnet chassis, A type, Horizontal PCB	Class D	-	RJX8FA3HB
				CAT5E	-	RJX8FA5HB
				CAT6	-	RJX8FA6HB
			XLRnet chassis, B type, Horizontal PCB	Class D	-	RJX8FB3HB
				CAT5E	-	RJX8FB5HB
				CAT6	-	RJX8FB6HB
			XLRnet chassis, B type, LEDs, Horizontal PCB, Bulk packed	CAT5E	R G	RJX8FB5HRGB
					R Y	RJX8FB5HRYB
					R R	RJX8FB5HRRB
					G R	RJX8FB5HGRB
					G Y	RJX8FB5HGYB
					U U	RJX8FB5HUUB
				CAT6	R G	RJX8FB6HRGB
					R Y	RJX8FB6HRYB
					R R	RJX8FB6HRRB
					G R	RJX8FB6HGRB
					G Y	RJX8FB6HGYB
					U U	RJX8FB6HUUB
			XLRnet chassis, B type, Shielded Hood, Horizontal PCB, Bulk packed	Class D	-	RJX8FB3HEB
				CAT5E	-	RJX8FB5HEB
				CAT6	-	RJX8FB6HEB

*Note: LED colours are denoted left to right from the panel side front view. Refer page 82

R = Red, G = Green, Y = Yellow, U = Blue


PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	TYPE	LED* LHS/RHS	PART NUMBER
		XLRnet chassis, B type, Shielded Hood, LEDs, Horizontal PCB, Bulk packed	CAT5E	R G	RJX8FB5HRGEB	
				R Y	RJX8FB5HRYEB	
				R R	RJX8FB5HRREB	
				G R	RJX8FB5HGREB	
				G Y	RJX8FB5HGYEB	
				U U	RJX8FB5HUEB	
			CAT6	R G	RJX8FB6HRGEB	
				R Y	RJX8FB6HRYEB	
				R R	RJX8FB6HRREB	
				G R	RJX8FB6HGREB	
				G Y	RJX8FB6HGYEB	
				U U	RJX8FB6HUEB	
		XLRnet chassis, A type, Vertical PCB	Class D	-	-	RJX8FA3VB
			CAT5E			RJX8FA5VB
			CAT6			RJX8FA6VB
		XLRnet chassis, B Type, Vertical PCB	Class D	-	-	RJX8FB3VB
			CAT5E			RJX8FB5VB
			CAT6			RJX8FB6VB
		XLRnet chassis, B type, LEDs, Vertical PCB, Bulk packed	CAT5E	R G	RJX8FB5VRGB	
				R Y	RJX8FB5VRYB	
				R R	RJX8FB5VRRB	
				G R	RJX8FB5VGRB	
				G Y	RJX8FB5VGYB	
				U U	RJX8FB5VUUB	
			CAT6	R G	RJX8FB6VRGB	
				R Y	RJX8FB6VRYB	
				R R	RJX8FB6VRRB	
				G R	RJX8FB6VGRB	
				G Y	RJX8FB6VGYB	
				U U	RJX8FB6VUUB	
		XLRnet chassis, B type, Shielded Hood, Vertical PCB, Bulk packed	Class D	-	-	RJX8FB3VEB
			CAT5E			RJX8FB5VEB
			CAT6			RJX8FB6VEB

*Note: LED colours are denoted left to right from the panel side front view. Refer page 82

R = Red, G = Green, Y = Yellow, U = Blue

Data Connectors

XLRnet RJ45 Ethernet Series

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	TYPE	LED* LHS/RHS	PART NUMBER
		XLRnet chassis, B type, Shielded Hood, LEDs, Vertical PCB, Bulk packed	CAT5E	R G	RJX8FB5VRGEB	
				R Y	RJX8FB5VRYEB	
				R R	RJX8FB5VRREB	
				G R	RJX8FB5VGREB	
				G Y	RJX8FB5VGYEB	
				U U	RJX8FB5VUEB	
		XLRnet chassis, B type, Shielded Hood, LEDs, Vertical PCB, Bulk packed	CAT6	R G	RJX8FB6VRGEB	
				R Y	RJX8FB6VRYEB	
				R R	RJX8FB6VRREB	
				G R	RJX8FB6VGREB	
				G Y	RJX8FB6VGYEB	
				U U	RJX8FB6VUEB	

*Note: LED colours are denoted left to right from the panel side front view. Refer page 82

R = Red, G = Green, Y = Yellow, U = Blue

PART NUMBER BREAKDOWN

XLRnet A AND B TYPE Printed Circuit Board Connectors

E. G. **RJX8FB5HLRREB**
RJX (Series Prefix), 8 (Contacts), Female B type, 5 Cat5E Horizontal, Latchless, Red - Red LEDs, EMI / RFI Hood, Bulk Packaged.



SERIES PREFIX	RJX	=	Series Prefix
CONTACT LAYOUT	8	=	RJ45 type
GENDER	F	=	Receptacle housing
SHELL SERIES	A	=	A Type
	B	=	B Type
TRANSMISSION CLASS	3	=	Class D
	5	=	CAT 5e
	6	=	CAT 6
TERMINATION	H	=	Horizontal Printed Circuit Board
	V	=	Vertical Printed Circuit Board
LOCKING MECHANISM	Blank	=	Latching
	P	=	Push lever supplied separately for customer installation (Contact factory for detailed fitting instructions)
LED COLOUR SEQUENCE*	Blank	=	No LEDs
	RG	=	Red / Green
	RY	=	Red / Yellow
	RR	=	Red / Red
	GR	=	Green / Red
	GY	=	Green / Yellow
	GG	=	Green / Green
	YR	=	Yellow / Red
	YY	=	Yellow / Yellow
	YG	=	Yellow / Green
	UU	=	Blue / Blue
EMI / RFI SHIELDING HOOD	Blank	=	No shield hood
	E	=	EMI / RFI shield hood
PACKAGING	Blank	=	Individual
	B	=	Bulk packed

*Note: LED colours are denoted left to right from the panel side front view.

Refer Page 82

Data Connectors

XLRnet RJ45 Ethernet Series



XLRnet SERIES

D Type

Features:

- RJ45 Class D (10/100 Base-T), CAT5E (1000 Base-T) or CAT6 (10GBASE-T) Ethernet performance
- D type XLR standard housings
- IDC Punchdown block
- Thru-adaptor / Feedthrough
- Horizontal or Vertical PCB

Part Number Breakdown: Page 81

Specifications: Page 83


PCB Footprints: Page 82

Recommended Fastener: Page 133

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	TYPE	PART NUMBER
			XLRnet chassis, D type, Feedthrough, Nickel Finish	CAT5E	RJX8FD5T
			XLRnet chassis, D type, IDC Terminals, 110 type, Nickel Finish	CAT5E	RJX8FD5110
				CAT6	RJX8FD6110
			XLRnet chassis, D type, IDC Terminals, Nickel Finish	CAT5E	RJX8FD5I
				CAT6	RJX8FD6I
			XLRnet chassis, D type, Horizontal PCB, Nickel Finish	Class D	RJX8FD3HB
				CAT5E	RJX8FD5HB
				CAT6	RJX8FD6HB
			XLRnet chassis, D type, Vertical PCB, Nickel Finish	Class D	RJX8FD3VB
				CAT5E	RJX8FD5VB
				CAT6	RJX8FD6VB

PART NUMBER BREAKDOWN

XLRnet D TYPE Chassis Connectors



*Note: LED colours are denoted left to right from the panel side front view.

Refer Page 82

STANDARD DATA XLRnet CHASSIS RECEPTACLES

	VALUE		
	Class D	CAT5E	CAT6
GENERAL CHARACTERISTICS	Number of contacts	8	
	Contact Arrangement	RJ45	
	Termination	Printed Circuit Board (PCB) - through hole, Feedthrough, IDC Terminal	
	Flammability	UL94V-0	
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU	
	Solderability	MIL-STD 202, Method 208	
ELECTRICAL CHARACTERISTICS	Rated current per contact	1.5 A	
	Rated Voltage	125V AC	
	Typical Contact Resistance	20mΩ	
	Insulation Resistance	> 500MΩ	
	Dielectric Strength	1000 VAC, 60 secs	
	Max. Frequency	100Mhz	250MHz
	Ethernet Standard	10/100 BASE-T	1000 BASE-T
	Transmission Spec.	EIA/ TIA568-C.2, ISO/IEC 11801, EN50173	
	PoE+	802.3at Type 2	
	LED Type	Round, single pole, indicator	
CLIMATIC CHARACTERISTICS	Protection Class	IP40 (with EMI/RFI shield)	
	Operating Temperature	-40°C to +80°C (-40°F to +176°F)	
MECHANICAL CHARACTERISTICS	Weight** - A & B Housing - Shielded Housing - D Shell	11g (0.024lb) 17g (0.037lb) 25g (0.055lb)	
	Mechanical Operations	1000	
	Insertion and Withdrawal Force	≤ 21N	
	Latch	Spring Steel	
	Panel Thickness max.	3mm	
	Mounting screw torque max.	0.35Nm	
	Fastener	Self-Tapping screw M2.5	
MATERIALS	Connector Shell / Housing	Thermoplastic, DSM Stanyl UL94V-0, 30% GF / PA66 30% GF	
	Flange (A type)	Thermoplastic, DSM Stanyl UL94V-0, 30% GF	
	Flange (B type)	Diecast Zinc Alloy 3	
	Flange Finish (B type)	Satin Nickel	
	Contact	Phosphor Bronze	
	Contact Finish - Ground - RJ45	0.38µm Au over 1.27µm Ni 1.27µm Au over 1.27µm Ni	
	Metal Hood Shield EMI/RFI	Brass, nickel plated	
	Latch lock and Spring	Spring steel	

**Approximate weight in grams not including packaging. Please contact us for exact weight for shipping purposes.

Rev 3 - 05/2015

Data Connectors

USB/HDMI Chassis Mount






USB/HDMI Series

Features:

- Data connectors
- Feedthrough adaptors
- USB 3 Type A
- HDMI receptacles

Options: Nickel or Black Shell Finish

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
 		 	USB 3.0, Feedthrough adapter, D Flange, Nickel Finish	Type A / Type A	AC-USB3-AA
			USB 3.0, Feedthrough adapter, D Flange, Black Finish	Type A / Type A	AC-USB3-AAB
 		 	HDMI, Feedthrough adapter, D Flange, Nickel Finish	HDMI / HDMI	AC-HDMI-RR
			HDMI, Feedthrough adapter, D Flange, Black Finish	HDMI / HDMI	AC-HDMI-RRB



PANEL CUTOUT DIMENSIONS

FRONT VIEW

AC-****



Amphenol offers a complete range of high-performance BNC plugs for use in digital/HD video applications. Amphenol's True 75 Ohm BNC connectors perform well up to and beyond 3GHz and are designed to terminate to a variety of popular coaxial cable types. We can also offer custom connectors to suit non-standard cables on request. Plugs feature a precision machined brass body and coupling nut plated with cost effective nickel plating.

Applications

- Broadcast
- High bandwidth video equipment
- D1/D2 serial digital
- Graphic work stations
- Telephony / Workstations

Options

- Crimp Plugs
- Jack to Jack adapters
- Patch Panels
- 'D' Shell Jacks
- Plug to Plug U-Link connectors
- Crimp Tools

Ordering Codes

We have listed the more common ordering codes in each section. Amphenol offer an extensive range of RF connectors for most applications.

Please visit www.amphenolconnex.com for further information. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

Coax Connectors

BNC 75Ω RF Connectors




Amphenol manufactures a large range of connectors to suit cables other than those listed below, for example Belden YR23769 and 46899, please contact us to discuss your specific requirements.

The complete Amphenol Connex catalogue featuring a wide range of RF connector products is available on request. Item code CAT-CONNEX-01.


	PART NO.	CABLE TYPE RG-/U	INSULATOR	TOOL	TOOL SET ¹	DIE-SET ONLY	DIE CAVITIES
#1	112119	59 / 62 / 140 / 210	Delrin	A	47-10070	47-20000	.255 / .068
	112507	59 / U-20AWG	Delrin	A	47-10070	47-20000	.255 / .068
	112606	11 / U-14AWG / B8213 / B9292 / B7731 / B1859A	Teflon	D	47-10090	47-20003	.429 / .100 / .080
	112508	6 / 143 / 212	Delrin	E	47-10110	47-20001	.324 / .068
	112509	B8281 / B9231 / B9141	Delrin	E	47-10110	47-20001	.324 / .068
	112519	6 PLENUM / B1695A	Delrin	E	47-10110	47-20001	.255 / .068
	112565	B1694A / B9248	Delrin	E	47-10110	47-20001	.324 / .068
	112951*	B1505A	Teflon	E	47-10110	47-20001	.324 / .255 / .068 / .042
	112952*	59 / 62 / 140 / 210	Teflon	E	47-10110	47-20001	.255 / .042
	112953*	B8281 / B9231 / B9141	Teflon	E	47-10110	47-20001	.324 / .042
	112956*	59 / U-20AWG	Teflon	E	47-10110	47-20001	.255 / .042
	112957*	B1694A / B9248	Teflon	E	47-10110	47-20001	.324 / .042
#2	112950*	B735A1	Teflon	F	47-10120	47-20002	.178 / .042
	B1121A1-ND3G-4CFB-75	CANARE 4CFB	Delrin	A	47-10070	47-20000	.255 / .213 / .068
	112133	179 / 187 / B9221	Delrin	B	47-10150	47-20004	.178 / .068
	112521	180 / 195 / 122 / B8218 / B1865A / B1855	Delrin	B	47-10150	47-20004	.178 / .068
	112955*	180 / 195 / 122 / B8218 / B1865A / B1855	Teflon	F	47-10120	47-20002	.213 / .178 / .068 / .042

Note: *True 75 ohm.

¹Complete crimp tool with Die-set refer page 90 for additional details



Straight Crimp Plug - Captive Contact- Standard Cable
Assembly Instruction A - page 90



Straight Crimp Plug-Captive Contact-Miniature Cable
(Remark: With Teflon sleeve / Hex crimp size .178")
Assembly Instruction B - page 90

BNC 75 RF ACCESSORIES AND TOOLING

PRODUCT - FIGURE	DESCRIPTION	DIE CAVITIES	CABLE TYPE RG-/U	CONNECTOR GUIDE	PART NUMBER
	Crimp tool with Die Set	.255 / .213 / .068	59 / 62	A	47-10070
		.178 / .128 / .068	179 / 187 / 180 / 195	B	47-10150
		.429 / .100 / .080	11	D	47-10090
		.324/.255 / .068/.042	6 / 59 / B8281	E	47-10110
		.213/.178 / .068/.042	AT&T 735A, B1855A, B8218	F	47-10120

Note: *True 75 ohm.

Coax Connectors

BNC Patch Panels



BNC Patch Panels

Features:

- Amphenol True 75 Ohm Connectors
- Bayonet lock or Push-on types
- Supplied with adhesive strip ID labels

Options:


- 1RU, 20 BNC connectors or 2RU, 40 BNC connectors
- Aluminium in Clear or Black anodised
- Steel in Black powder coat
- Customised versions available on request

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	MATERIAL / FINISH	LOADED WITH (refer to page 84 for specifications)	PART NUMBER
1RU 1X20 Patch Panel, Supplied with 1 ID label			1RU 1X20 Patch Panel, Supplied with 1 ID label	Steel / Black	Empty Panel	AC-BNC20M
				Steel / Black	AC-BNC-JJA-75	AC-BNC20MJ75
				Steel / Black	AC-BNC-PJA-75	AC-BNC20MP75
				Aluminium / Clear	Empty Panel	AC-BNC20A
				Aluminium / Clear	AC-BNC-JJA-75	AC-BNC20AJ75
				Aluminium / Clear	AC-BNC-PJA-75	AC-BNC20AP75
				Aluminium / Black	Empty Panel	AC-BNC20B
				Aluminium / Black	AC-BNC-JJA-75	AC-BNC20BJ75
				Aluminium / Black	AC-BNC-PJA-75	AC-BNC20BP75
2RU 2X20 Patch Panel, Supplied with 2 ID labels			2RU 2X20 Patch Panel, Supplied with 2 ID labels	Steel / Black	Empty Panel	AC-BNC40M
				Steel / Black	AC-BNC-JJA-75	AC-BNC40MJ75
				Steel / Black	AC-BNC-PJA-75	AC-BNC40MP75
				Aluminium / Clear	Empty Panel	AC-BNC40A
				Aluminium / Clear	AC-BNC-JJA-75	AC-BNC40AJ75
				Aluminium / Clear	AC-BNC-PJA-75	AC-BNC40AP75
				Aluminium / Black	Empty Panel	AC-BNC40B
				Aluminium / Black	AC-BNC-JJA-75	AC-BNC40BJ75
				Aluminium / Black	AC-BNC-PJA-75	AC-BNC40BP75
Panel ID label			Panel ID label	Plastic	Not Applicable	AC-BNC-LABEL


BNC 75 RF ASSEMBLY INSTRUCTIONS

ASSEMBLY A


STEP 1




STEP 2




STEP 3



STEP 4



STEP 5



STEP 1. All parts of the connector are shown. A crimp tool is necessary to complete the connection.

STEP 2. Strip the cable inner conductor, dielectric, braid, and jacket as per "RECOMMENDED CABLE STRIPPING DIM'S" in catalogue.


STEP 3. Insert inner conductor into the CONTACT PIN, crimp it with the crimp tool as shown. Then slide the FERRULE onto cable.

STEP 4. Insert the MAIN BODY into braid and dielectric.


STEP 5. Slide the FERRULE over braid, crimp it with the crimp tool as shown.

ASSEMBLY B


STEP 1




STEP 2




STEP 3



STEP 4



STEP 5



STEP 1. All parts of the connector are shown. A crimp tool is necessary to complete the connection.

STEP 2. Strip the inner conductor, dielectric, and jacket as per "RECOMMENDED CABLE STRIPPING DIM'S" in catalogue.

STEP 3. Slide the FERRULE on to cable, then fold back braid wire and slide the INSULATOR on to dielectric as shown.

STEP 4. Insert inner conductor into the CONTACT PIN, crimp it with crimp tool as shown.

STEP 5. Push cable and parts into the MAIN BODY until it stops. Then slide the FERRULE over braid wire and against the MAIN BODY, crimp it with the crimp tool as shown.

Coax Connectors

BNC 75Ω RF Connectors

STANDARD DATA BNC 75 RF CONNECTORS


		VALUE
GENERAL CHARACTERISTICS	Mating	Bayonet Lock
	Cable Attachment	Crimp - Crimp
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Impedance	75Ω
	Frequency Range - Standard	0 - 1 GHz
	- True 75 Ohm	0 - 4 GHz
	Voltage Rating	500V RMS
	Dielectric withstanding voltage	1500 Volts RMS
	VSWR - Standard	1.05 + 0.1f(GHz) DC to 1 GHz
	- True 75 Ohm	1.5 + 0.1f(GHz) DC to 4 GHz
	Contact Resistance	
	Centre Contact	1.5 milliohm
	Outer Contact	1.0 milliohm
MATERIALS	Insulation Resistance	5000 MΩ (min.)
	Part	Material
	Body, Coupling sleeves	Brass
	Crimp Ferrule	Annealed Copper
	Male Contact	Brass
	Female Contact	Beryllium Copper or Phosphor Bronze
	XLR Housing	Diecast Zinc Alloy
	Insulators	Teflon or Delrin
		Finish
		Nickel
		Nickel
		Gold
		Gold
		Satin Nickel or Black Polyester
		Natural

Rev 4 - 03/2013


NOTE: These characteristics are typical and may not apply to all connectors.

PANEL CUTOUTS - FRONT VIEW

AC-BNC-PJ-75
AC-BNC-JJ-75



AC-BNC-PJA-75
AC-BNC-JJA-75



1/4" PHONE CONNECTORS

Amphenol offers two ranges of 1/4" Phone plug connectors to satisfy the needs of the manufacturer and the end user. The PRO – a heavy duty on-road plug and the MUSICIAN - a solid performing general use plug. Both series offer different features and benefits and the most suitable type will be determined by application, budget and personal choice.



Applications

- Audio Cables and Snakes
- Amplifiers
- Mixing desks
- Patch panel

PRO RANGE 1/4" Phone Plug T-Series

Features / Options

- Mono or Stereo (TRS)
- Switching Plugs
- Nickel or Gold contact plating
- Straight or Right Angle
- Optional heavy duty metal backshell / boot
- Increased solder area on ground contact
- "Jaws" Cable Clamp
- Precision machined contacts
- Coloured Grommet
- JUMBO Series Plugs

PRO RANGE 1/4" Phone Plug Q-Series

Features / Options

- Mono or Stereo (TRS)
- Slimline design
- Quick and Easy to assemble
- Nickel or Gold contact plating
- Chuck style cable clamp
- Nickel or Black shell finish
- Molded backshell

MUSICIAN RANGE 1/4" Phone Plug

Features / Options

- Mono or Stereo (TRS)
- Compact Shell
- Straight or Right angle
- Flexible grommet cable protection
- Nickel or Gold contact plating
- Satin Nickel or Black finish
- Coloured Grommet

Jaws Cable Clamp Options for T-Series*



Standard Jaws cable clamp (Black), Cable O.D 3mm to 6mm (0.118" to 0.236")



Large Jaws cable clamp (Purple), Cable O.D 6mm to 7mm (0.236" to 0.275")

*Note: Applicable to T-Series straight cable connectors only. Refer to page 100 for right angle connector Jaws cable clamp specifications.

Chuck Clamp for Q-Series



Standard Chuck clamp (Black), Cable O.D 3mm to 7mm (0.118" to 0.275")

Musician Range Cable Clamp Options



M-Series, Cable O.D 3mm to 6.5mm (0.118" to 0.256")



M-Series II, Cable O.D 6.5mm to 8mm (0.256" to 0.315")

Ordering Codes

We have listed the more common ordering codes in each section. Refer to our 1/4" plug product feature matrix found on the next page for assistance on selecting the right plug for your application.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

1/4" PLUG FEATURE MATRIX

FEATURES	T SERIES (STRAIGHT)	T SERIES (RIGHT ANGLE)	JUMBO T SERIES	SWITCHPLUG T SERIES (STRAIGHT)	SWITCHPLUG T SERIES (RIGHT ANGLE)	Q SERIES (STRAIGHT)	M SERIES	M SERIES II	CUSTOM SERIES ¹
PRECISION MACHINED CONTACTS	X	X	X	X	X	X	X	X	X
CENTER CONTACT	1 pc. Center Contact	X	X	X	X				X*
	2 pc Press Fit Tip/Center Contact					X	X	X	X*
BARREL:	Machined Tube	X	X	X	X				
	Precision Extruded Tube					X	X	X	X
JAWS CABLE CLAMP	X	X		X	X				
MIN. CABLE OD	Black Jaw: 3mm/0.118"	X	X		X	X			
	Purple Jaw: 6mm/0.236"	X			X				
	Purple Jaw: 5.5mm/0.216"		X			X			
MAX. CABLE OD	Black Jaw: 6mm/0.236"	X			X				
	Black Jaw: 5.5mm/0.216"		X			X			
	Purple Jaw: 7.5mm/0.295"	X			X				
	Purple Jaw: 6.5mm/0.255"		X			X			
CHUCK CABLE CLAMP									
MIN. CABLE OD	Black Chuck: 3.5mm/0.137"						X		
MAX. CABLE OD	Black Jaw: 7mm/0.275"						X		
STANDARD CABLE CLAMP				X			X	X	X
MIN. CABLE OD	7.5mm/0.295"			X					
MAX. CABLE OD	6mm/0.236"						X		
	8mm/0.315"							X	
	8.8mm/0.345"								X
	10.5mm/0.413"		X						
BACKSHELL FINISH	Satin Nickel	X	X	X	X	X	X	X	
	Black	X	X	X	X	X	X	X	
	Bright Nickel								X
	Bright Gold								X
CONTACT MATERIAL/ FINISH OPTIONS	Brass/Nickel (Ni)	X	X	X	X	X	X	X	X
	Brass/Gold over 2µm (Ni)	X	X	X	X	X	X	X	X

¹Custom Series - Minimum order quantities apply. Contact us for further details.



T-Series

Features:

- Mono or Stereo (TRS).
- Stylised shell design with Ergonomic grip.
- Straight or Right Angle.
- Robust diecast shell in Satin nickel or Black finish.
- Nickel or Gold contact plating.
- Keyed shell.
- Optional heavy duty metal backshell / boot.
- Great solderability.
- Increased solder area on ground contact.
- "Jaws" Cable Clamp.
- Precision machined contacts.
- Quick and easy assembly.

Options: Gold Contacts, Large or Small Jaws Cable Clamp, Black Shell, Metal Backshell / Boot, Bulk Pack. Coloured grommets (ordered separately)

Part Number Breakdown: Page 97

Specifications: Page 98

PRODUCT - FIGURE	DRAWING	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mm) Mono Phone plug, Jaws cable clamp, Thermoplastic backshell, Satin finish.	Standard	TM2P
			Gold Plated Contacts	TM2P-AU
			Large Cable Clamp	TM2PJ
			Bulk Pack	TM2P BULK
		1/4" (6.35mm) Mono Phone plug, Jaws cable clamp, Thermoplastic backshell, Black finish.	Standard	TM2PB
			Gold Plated Contacts	TM2PB-AU
			Large Cable Clamp	TM2PBJ
			Bulk Pack	TM2PB BULK
		1/4" (6.35mm) Stereo Phone plug, Jaws cable clamp, Thermoplastic backshell, Satin finish.	Standard	TS3P
			Gold Plated Contacts	TS3P-AU
			Large Cable Clamp	TS3PJ
			Bulk Pack	TS3P BULK
		1/4" (6.35mm) Stereo Phone plug, Jaws cable clamp, Thermoplastic backshell, Black finish.	Standard	TS3PB
			Gold Plated Contacts	TS3PB-AU
			Large Cable Clamp	TS3PBJ
			Bulk Pack	TS3PB BULK

Plugs & Jacks

T-Series Plugs

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		94 [3.685"] 63 [2.483"] Ø16.0 [Ø.630"] 53.9 [2.12] 30.5 [1.20] 8 [33]	1/4" (6.35mmØ) Mono Phone plug, Jaws cable clamp, Metal backshell, Satin finish.	Standard	TM2PN
				Gold Plated Contacts	TM2PN-AU
				Large Cable Clamp	TM2PNJ
				Bulk Pack	TM2PN BULK
		615 [2.42] 53.9 [2.12] 30.5 [1.20] 8 [33]	1/4" (6.35mmØ) Mono Phone plug, Right angle, Jaws cable clamp*, Thermoplastic back- shell, Satin finish.	Standard	TM2RJ
				Gold Plated Contacts	TM2RJ-AU
		615 [2.42] 53.9 [2.12] 30.5 [1.20] 8 [33]	1/4" (6.35mmØ) Mono Phone plug, Right angle, Jaws cable clamp*, Thermoplastic back- shell, Black finish.	Standard	TM2RBJ
				Gold Plated Contacts	TM2RBJ-AU
				Bulk Pack	TM2RBJ BULK
		615 [2.42] 53.4 [2.10] 30.5 [1.20] 8 [30]	1/4" (6.35mmØ) Stereo Phone plug, Right angle, Jaws cable clamp*, Thermoplastic back- shell, Satin finish.	Standard	TS3RJ
				Gold Plated Contacts	TS3RJ-AU
		615 [2.42] 53.4 [2.10] 30.5 [1.20] 8 [30]	1/4" (6.35mmØ) Stereo Phone plug, Right angle, Jaws cable clamp*, Thermoplastic back- shell, Black finish.	Standard	TS3RBJ
				Gold Plated Contacts	TS3RBJ-AU

*NOTE: Refer to page 100 for Jaws cable clamp specifications applicable to right angle connectors.







T-Series (Jumbo)

Features:

- JUMBO Cable clamping capacity
- Suits Cable OD 7.5mm (0.295") to 10.5mm (0.413")
- Mono or Stereo (TRS).
- Stylised shell design with Ergonomic grip.
- Robust diecast shell in Satin nickel or Black finish.
- Nickel or Gold contact plating.
- Keyed shell.
- Great solderability.
- Increased solder area on ground contact.
- Precision machined contacts.
- Quick and easy assembly.

Options: Gold Contacts, Bulk Pack

Specifications: Page 100

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mm \varnothing) JUMBO Mono Phone plug, Thermoplastic back- shell, Satin finish.	Standard	JM2P	
			Gold Plated Contacts	JM2P-AU	
			Bulk Pack	JM2P BULK	
		1/4" (6.35mm \varnothing) JUMBO Mono Phone plug, Thermoplastic back- shell, Black finish.	Standard	JM2PB	
			Gold Plated Contacts	JM2PB-AU	
		1/4" (6.35mm \varnothing) JUMBO Stereo Phone plug, Thermoplastic back- shell, Satin finish.	Standard	JS3P	
			Gold Plated Contacts	JS3P-AU	
		1/4" (6.35mm \varnothing) JUMBO Stereo Phone plug, Thermoplastic back- shell, Black finish.	Standard	JS3PB	
			Gold Plated Contacts	JS3PB-AU	

NOTE: Contact factory for availability of metal backshells.

Plugs & Jacks

T-Series Jumbo Plugs


PART NUMBER BREAKDOWN

T-SERIES (PRO RANGE)

E. G. **TS3PBMJ-AU BULK**
T (Series Prefix), **S3**(Stereo), **P**lug **B**lack, **M**etal Nut (Black), **J** (Large Jaws),
- **AU** (Gold Plated Contacts), **BULK** Packaged.

	SERIES PREFIX	CONTACT TYPE	SHELL TYPE AND FINISH	BACKSHELL STYLE	CABLE CLAMP	CONTACT PLATING	PACKAGING	
	T	S3	PB	M	J	-	AU	BULK
SERIES PREFIX	T							
CONTACT TYPE	M1	=	Switch Plug					
	M2	=	2 Pole (mono)					
	S3	=	3 Pole, tip/ring/sleeve (stereo)					
SHELL TYPE AND FINISH	P	=	Plug Satin Nickel					
	PB	=	Plug Matt Black					
	R	=	Right Angle Plug Satin Nickel					
	RB	=	Right Angle Plug Matt Black					
BACKSHELL TYPE	Blank	=	Plastic Nut					
	M	=	Metal Nut - Black					
	N	=	Metal Nut - Satin Nickel					
CABLE CLAMP	Blank	=	Small Jaws					
	J	=	Large Jaws					
CONTACT PLATING	Blank	=	Nickel Plated Contacts (Standard)					
	AU	=	Gold Plated Contacts					
PACKAGING	Blank	=	Individual Bags					
	BULK	=	Bulk Packed					

ISO VIEW OF TM2P





T-Series SwitchPlug

The Amphenol T series SwitchPlug uses a unique 360 degree precision sliding helical spring contact design to quietly and accurately switch the signal circuit safely to ground during instrument changes under load, thereby avoiding annoying thumps, pops and squeals. The sliding ring contact self-cleans every time the plug is connected preventing excessive build up of oxidation and contamination. Activation is directly off the jacks full front face assuring a positive reference point every time, and as it works instantaneously on the main circuits there is no need for the use of magnets or other elaborate switching mechanisms.

WARNING!
For use with
instrument (guitar)
applications only.

Part Number Breakdown: Page 96
Specifications: Page 100

US Patent No.8,162,697

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mm \varnothing) Switch Phone plug, Jaws cable clamp, Thermoplastic backshell, Satin finish	Standard	TM1P	
			Gold Plated Contacts	TM1P-AU	
			Large Cable Clamp	TM1PJ	
		1/4" (6.35mm \varnothing) Switch Phone plug, Jaws cable clamp, Thermoplastic backshell, Black finish	Standard	TM1PB	
			Gold Plated Contacts	TM1PB-AU	
			Large Cable Clamp	TM1PBJ	
		1/4" (6.35mm \varnothing) Switch Phone plug, Right angle, Jaws cable clamp*, Thermoplastic backshell, Satin Finish	Standard	TM1RJ*	
			Gold Plated Contacts	TM1RJ-AU*	
		1/4" (6.35mm \varnothing) Switch Phone plug, Right angle, Jaws cable clamp*, Thermoplastic backshell, Black Finish	Standard	TM1RBJ*	
			Gold Plated Contacts	TM1RBJ-AU*	

*NOTE: Refer to page Page 100 for Jaws cable clamp specifications applicable to right angle connectors.

Plugs & Jacks


T-Series SwitchPlug

SwitchPlug - User Instruction




CAUTION!

Use with instrument (guitar) cables only.
DO NOT connect to amplifier output.
Equipment damage may result from incorrect use.





INCORRECT



CORRECT

SwitchPlug - Technology*



*US Patent No. 8,162,697



Q-Series

Features:

- Mono or Stereo (TRS)
- Slimline design
- Quick and Easy to assemble
- Nickel or Gold contact plating
- Chuck style cable clamp
- Nickel or Black shell finish
- Molded backshell

Options: Gold Plated Contacts, Black Shell, Bulk Pack.

Part Number Breakdown: Page 97

Specifications: Page 98

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		83 [3.266"] 53 [2.073"] Ø14 [Ø 549"]	1/4" (6.35mmØ) Mono Phone plug, Chuck cable clamp, Molded boot, Satin Finish	Standard	QM2P
		83 [3.266"] 53 [2.073"] Ø14 [Ø 549"]	1/4" (6.35mmØ) Mono Phone plug, Chuck cable clamp, Molded boot, Black Finish	Gold Plated Contacts	QM2PB-AU
		83 [3.266"] 53 [2.073"] Ø14 [Ø 549"]	1/4" (6.35mmØ) Stereo Phone plug, Chuck cable clamp, Molded boot, Satin Finish	Standard	QS3P
		83 [3.266"] 53 [2.073"] Ø14 [Ø 549"]	1/4" (6.35mmØ) Stereo Phone plug, Chuck cable clamp, Molded boot, Black Finish	Gold Plated Contacts	QS3PB-AU

Plugs & Jacks

Q-Series Plugs

1/4" PHONE PLUG TECHNICAL DATA

		VALUE		
		Straight	Right Angle	Jumbo
GENERAL CHARACTERISTICS	Number of Contacts	3 Pole Tip Ring Sleeve (Stereo)		
	Termination	Solder		
	Max. Wire Gauge - Stranded Wire	2 Pole (Mono): AWG 16- 1.5mm 3 Pole (Stereo): AWG 18- 1mm		
	Flammability rating of insulating plastics	UL94V-0		
	Solderability, complies with	IEC 68-2-20		
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU		
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	10A (Depends on Mating Connector and Cable)		
	Typical Contact Resistance	Depends on Mating Connector		
	Insulation Resistance (initial)	>2GΩ		
	After Damp Heat Test	≥1GΩ		
	Dielectric Withstand Voltage	2 Pole : 1.5 kV dc 3 Pole : 1 kV dc		
CLIMATIC CHARACTERISTICS	Protection Class	IP40		
	Operating Temperature	-25°C to +75°C (-13°F to + 167°F)		
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal Force	≥10N - ≤30N		
	Weight ¹	Thermoplastic Backshell 28g (0.061lb)		
		Metal Backshell 35g (0.077lb)		
	Typical Cable Retention Force	22kg to 44kg (50lb to 100lb) - Dependent on cable material and diameter.		
	Cable O.D.	Standard Jaw (T-Series)	3mm to 6mm (0.118" to 0.236")	3mm to 5.5mm (0.118" to 0.216")
		Large Jaw (T-Series)	6mm to 7mm (0.236" to 0.275")	5.5mm to 6.5mm (0.216" to 0.255")
		Standard Clamp (Q-Series)	3.5mm to 7mm (0.137" to 0.275")	N/A
		Jumbo	NA	NA
	7.5mm to 10.5mm (0.295" to 0.413")			
	Mechanical Operations	1000		
MATERIALS	Connector Shell Material	Diecast Zinc Alloy EZDA No.3		
	Shell Finish	Satin Nickel or Black Polyester		
	Insulators	UL94 V-0 PBT Resin or Modified PPE Resin - Black		
	Boot / Backshell	UL94 V-0 PBT Resin or Modified PPE Resin - Black or Metal CuZn ³⁹ Pb ³		
	Cable Clamp	UL94 V-0 PBT Modified PPO Resin - Black		
	Cable Bushing	Santoprene		
	Contacts / Plating	Brass/Ni or Au over 2μm Ni		

¹ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.



Musician Series II

Features:

- Mono or Stereo (TRS).
- AX Series inspired shell design.
- Large cable O.D. Entry to 8mm (0.315")
- Robust diecast shell in Satin nickel or Black finish.
- Nickel or Gold contact plating.
- Flexible grommet cable protection.
- Improved solderability.
- Precision machined contacts.
- Standard or Bulk packaging.





Clamp Info:



Cable O.D 6.5mm to 8mm
(0.256" to 0.315")

Options: Black Shell, Gold contacts.
Coloured grommets (ordered separately)

Specifications: Page 112

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mmØ) Mono Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPM-KN	
					Gold Plated Contacts
		1/4" (6.35mmØ) Mono Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPM-KB	
					Gold Plated Contacts
		1/4" (6.35mmØ) Stereo Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPS-KN	
					Gold Plated Contacts
		1/4" (6.35mmØ) Stereo Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPS-KB	
					Gold Plated Contacts

*NOTE: Refer to page 103 for Jaws cable clamp specifications applicable to right angle connectors.

Plugs & Jacks

Musician Series II Plugs

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mm) Mono Phone plug, Right angle, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPM-TN	
			Gold Contacts	ACPM-TN-AU	
			Bulk Pack	ACPM-TN BULK	
		1/4" (6.35mm) Mono Phone plug, Right angle, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPM-TB	
			Gold Contacts	ACPM-TB-AU	
			Bulk Pack	ACPM-TB BULK	
		1/4" (6.35mm) Stereo Phone plug, Right angle, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPS-TN	
			Gold Contacts	ACPS-TN-AU	
			Bulk Pack	ACPS-TN BULK	
		1/4" (6.35mm) Stereo Phone plug, Right angle, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPS-TB	
			Gold Contacts	ACPS-TB-AU	
			Bulk Pack	ACPS-TB BULK	



Features:

- Mono or Stereo (TRS).
- Stylish shell design.
- Robust diecast shell in Satin nickel or Black finish.
- Nickel or Gold contact plating.
- Flexible grommet cable protection.
- Improved solderability.
- Precision machined contacts.
- Standard or Bulk packaging.
- Cable OD Entry to 6.5mm (0.256")

Options: Black Shell, Gold contacts. Coloured grommets (ordered separately)

Specifications: Page 114

Clamp Info:







Cable O.D 3mm to 6.5mm (0.118" to 0.256")

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mmø) Mono Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPM-GN	
			Gold Plated Contacts	ACPM-GN-AU	
			Bulk Pack	ACPM-GN BULK	
		1/4" (6.35mmø) Mono Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPM-GB	
			Gold Plated Contacts	ACPM-GB-AU	
			Bulk Pack	ACPM-GB BULK	
		1/4" (6.35mmø) Stereo Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPS-GN	
			Gold Plated Contacts	ACPS-GN-AU	
			Bulk Pack	ACPS-GN BULK	
		1/4" (6.35mmø) Stereo Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPS-GB	
			Gold Plated Contacts	ACPS-GB-AU	
			Bulk Pack	ACPS-GB BULK	

Plugs & Jacks

Musician Series II Plugs

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	TYPE	PART NUMBER
		1/4" (6.35mmØ) Mono Phone plug, Right angle, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPM-RN	
			Gold contacts	ACPM-RN-AU	
			Bulk Pack	ACPM-RN BULK	
		1/4" (6.35mmØ) Mono Phone plug, Right angle, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPM-RB	
			Gold contacts	ACPM-RB-AU	
			Bulk Pack	ACPM-RB BULK	
		1/4" (6.35mmØ) Stereo Phone plug, Right angle, Diecast Shell, Satin finish, Flexible grommet.	Standard	ACPS-RN	
			Gold contacts	ACPS-RN-AU	
			Bulk Pack	ACPS-RN BULK	
		1/4" (6.35mmØ) Stereo Phone plug, Right angle, Diecast Shell, Black finish, Flexible grommet.	Standard	ACPS-RB	
			Gold contacts	ACPS-RB-AU	
			Bulk Pack	ACPS-RB BULK	

PART NUMBER BREAKDOWN

M / M SERIES II (MUSICIAN RANGE)

	ACP	S	G	B	-	AU	BULK	
SERIES PREFIX								PACKAGING
CONTACT TYPE								CONTACT PLATING
E. G. ACPM-GB-AU BULK ACP (Series Prefix), Male, G(Shell Type), Black, - AU (Gold Plated Contacts), Bulk Packaged.	ACP	S	G	B	-	AU	BULK	
SERIES PREFIX	ACP	=	Series Prefix					
CONTACT TYPE	M	=	2 pole (Mono)					
	S	=	3 pole Tip/Ring/Sleeve (Stereo)					
SHELL TYPE	G	=	M Series Straight					
	K	=	M Series II Straight					
	R	=	M Series Right Angle					
	T	=	M Series II Right Angle					
SHELL FINISH	N	=	Satin Nickel					
	B	=	Matt Black					
CONTACT PLATING	Blank	=	Nickel Plating					
	AU	=	Gold Plated					
PACKAGING	Blank	=	Individual Bags					
	BULK	=	Bulk Packed					

Plugs & Jacks

Musician / OEM Range 1/4" Phone Jacks




Applications

- Audio Cables and Snakes
- Amplifiers
- Speakers
- Mixing desks
- Rack mount equipment
- Patch panel

Features / Options – OEM RANGE Phone Jack

- Mono or Stereo (TRS)
- Stackable (Piggy back) mounting
- Vertical or horizontal PCB mount
- Mono and Stereo switched contacts
- Solder contacts
- Combo Contacts
- Metal nut
- Plastic Nut
- 1/4" (6.35mm)
- 3.5mm
- Dual 1/4" (6.35mm) and 3.5mm
- EMI Shielding plates
- Metal Mounting threads
- Plastic Mounting threads
- Chassis Ground connections
- Half, Full or No threads
- Grounded or Isolated Jacks

1/4" Phone Jack Grounding/ Shielding Options



1/4" Gripper - Grounding points



1/4" Shielding Plate

1/4" PHONE JACK CONNECTORS


Amphenol phone connectors are available in 1/4" (6.35mm) and 3.5mm jack sockets or dual jack socket versions featuring combinations of both sizes. The standard heavy duty contacts provide excellent signal performance and the rugged designs excel in professional audio applications. Our wide range of options ensures we have the connector to suit your specific requirements. Custom jacks can also be developed to suit unique applications on request.

Ordering Codes

We have listed the more common ordering codes in each section. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.



Features:

- 3.5mm and 6.35mm (1/4") options
- Mono or Stereo (TRS)
- Single or Dual mounting
- Vertical or Horizontal PCB mount
- Mono and Stereo with switching contacts
- Solder or Combo contacts
- Various mounting option

Schematic Chart: Page 115

Panel Cutouts: Page 114









PCB Footprints: Page 116

Specifications: Page 117

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
3.5MM PHONE JACKS					
(Horizontal PCB mount)	(Schematic diagram)	(Dimensions: 3.5mm bore, 16mm height, 6.8mm width, 16.11mm depth)	3.5mm Jack, Horizontal PCB, Plastic housing, Metal entry bore	Mono	ACJM-NH35
				Stereo	ACJS-NH35
(Vertical PCB mount)	(Schematic diagram)	(Dimensions: 30.4mm height, 24mm width, 16mm depth)	3.5mm Jack, Vertical PCB mount, Needle eye contacts, Plastic housing, Metal entry bore	Refer to Schematic Chart on page 115	ACJM-NV35-2
					ACJM-NV35-2S
					ACJS-NV35-3
					ACJS-NV35-3S
					ACJS-NV35-5
(Vertical PCB mount with metal thread)	(Schematic diagram)	(Dimensions: 24mm height, 4mm width, 16mm depth)	3.5mm Jack, Vertical PCB mount, Needle eye contacts, Plastic housing, Metal thread and entry bore	Refer to Schematic Chart on page 115	ACJM-MV35-2
					ACJM-MV35-2S
					ACJS-MV35-3
					ACJS-MV35-3S
					ACJS-MV35-5
(Dual phone jack, horizontal PCB mount)	(Schematic diagram)	(Dimensions: 33.5mm height, 8.8mm width, 16mm depth)	3.5mm / 1/4" (6.35mmØ) Dual Phone Jack, (Piggy-back), Horizontal PCB, Plastic housing, Metal nut and entry bore	Mono	ACJM-MHD985
				Stereo	ACJS-MHD985
(Dual phone jack, vertical PCB mount)	(Schematic diagram)	(Dimensions: 35mm height, 24mm width, 16mm depth)	3.5mm / 1/4" (6.35mmØ) Dual Phone Jack, Vertical PCB mount, Needle eye contacts, Plastic housing, Metal nut and entry bore	Refer to Schematic Chart on page 115	ACJM-MVD985-2
					ACJM-MVD985-2S
					ACJS-MVD985-3
					ACJS-MVD985-3S
					ACJS-MVD985-5
1/4" PHONE JACKS HORIZONTAL					
(Horizontal snap-fit PCB mount)	(Schematic diagram)	(Dimensions: 12.7mm height, 4.50mm width, 16.0mm depth)	1/4" (6.35mmØ) Phone Jack, Horizontal Snap-fit PCB, Plastic housing, Half thread, Metal entry bore. Supplied without mounting hardware.	Mono	ACJM-HHDR
				Stereo	ACJS-HHDR

Plugs & Jacks

Musician / OEM Range 1/4" Phone Jacks

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mmø) Phone Jack, Horizontal Snap-fit PCB, Plastic housing, Metal nut and entry bore	1/4" (6.35mmø) Phone Jack, Horizontal Snap-fit PCB, Plastic housing, Metal nut and entry bore	Mono	ACJM-MHDR
		1/4" (6.35mmø) Phone Jack, Horizontal Snap-fit PCB, Plastic housing, Metal thread, nut, washer and entry bore		Stereo	ACJS-MHDR
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing and entry bore with Half thread. Supplied without mounting hardware.	Refer to Schematic Chart on page 112	ACJM-HHOP	ACJM-HHOP
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing and entry bore with Half thread. Supplied without mounting hardware.		ACJS-HHOP	ACJS-HHOP
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing, thread and entry bore	Refer to Schematic Chart on page 112	Mono - Plastic Nut	ACJM-PHOP
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing, thread and entry bore		Mono - Metal Nut	ACJM-MHOP
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing, thread and entry bore		Stereo - Plastic Nut	ACJS-PHOP
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing, thread and entry bore		Stereo - Metal Nut	ACJS-MHOP
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing, thread and entry bore. Non-switching sleeve contact with separate grounding to panel.	Refer to Schematic Chart on Page 110 PHOP - Denotes Plastic Nut MHOP - Denotes Metal Nut	ACJM-PHOP-1	ACJM-PHOP-1
		1/4" (6.35mmø) Offset Jack, Horizontal PCB mount, Plastic housing, Metal thread and entry bore with Chassis ground connection		Mono - Metal Nut	ACJM-MHOM
		1/4" (6.35mmø) Jack, Horizontal PCB mount, Plastic housing with metal insert		Stereo - Metal Nut	ACJS-MHOM
		1/4" (6.35mmø) Jack, Horizontal PCB mount, Plastic housing with metal insert		Mono - Plastic Nut	ACJM - PH
				Mono - Metal Nut	ACJM - MH

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mmø) Jack, Horizontal PCB mount, Plastic housing with metal insert	Stereo - Plastic Nut	ACJS - PH	
			Stereo - Metal Nut	ACJS - MH	
		1/4" (6.35mmø) Jack, Horizontal Snap-fit PCB mount, Plastic housing with metal insert	Mono - Plastic Nut	ACJM-PHR	
			Mono - Metal Nut	ACJM-MHR	
			Stereo - Plastic Nut	ACJS-PHR	
			Stereo - Metal Nut	ACJS-MHR	
		1/4" (6.35mmø) Jack, Combination Horizontal PCB and Solder lug, Plastic housing with metal insert	Mono - Plastic Nut	ACJM-PC	
			Mono - Metal Nut	ACJM-MC	
			Stereo - Plastic Nut	ACJS-PC	
			Stereo - Metal Nut	ACJS-MC	
		1/4" (6.35mmø) Jack, Solder Lug, Plastic housing with metal insert	Mono - Plastic Nut	ACJM-PHS	
			Mono - Metal Nut	ACJM-MHS	
			Stereo - Plastic Nut	ACJS-PHS	
			Stereo - Metal Nut	ACJS-MHS	
		1/4" (6.35mmø) Jack, Solder Lug, Plastic housing and Bezel with threaded Metal nut.	Mono	ACJM-IHS	
			Stereo	ACJS-IHS	
		1/4" (6.35mmø) Jack, Horizontal PCB mount, Plastic housing and Bezel with threaded Metal nut.	Mono	ACJM-IH	
			Stereo	ACJS-IH	
1/4" PHONE JACKS HORIZONTAL DUAL					
		1/4" (6.35mmø) Dual Phone Jack (Compact Piggyback), Horizontal Snap-fit PCB, Plastic housing, Metal nut and entry bore	Mono	ACJM-MHDC*	
			Stereo	ACJS-MHDC*	
		1/4" (6.35mmø) Dual Phone Jack (Compact Piggyback), Horizontal Snap-fit PCB, Plastic housing, Metal thread, nut and entry bore	Mono	ACJM-MHDCM	
			Stereo	ACJS-MHDCM	


* This product protected by U.S. patent No. 6,116,959

Plugs & Jacks

Musician / OEM Range 1/4" Phone Jacks














PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mmØ) Dual Phone Jack (Piggyback) Horizontal Snap-fit PCB, Plastic housing, Metal nut and entry bore	Mono	ACJM-MHD*	
			Stereo	ACJS-MHD*	
		1/4" (6.35mmØ) Dual Phone Jack (Piggyback) Shielding plate, Horizontal Snap-fit PCB, Plastic housing, Metal nut and entry bore	Mono	ACJM-MHDE*	
			Stereo	ACJS-MHDE*	
		1/4" (6.35mmØ) Dual Phone Jack (Piggyback), Horizontal Snap-fit PCB, Plastic housing, Metal thread, nut, washer and entry bore	Mono	ACJM-MHDM*	
			Stereo	ACJS-MHDM*	
		1/4" (6.35mmØ) Dual Phone Jack (Piggy-back), Shielding plate, Horizontal Snap-fit PCB, Plastic housing, Metal thread, nut and entry bore	Mono	ACJM-MHDEM*	
			Stereo	ACJS-MHDEM*	
1/4" PHONE JACKS VERTICAL					
		1/4" (6.35mmØ) Jack, Vertical PCB mount, Plastic housing, nut and entry bore	Refer to Schematic Chart on page 115	ACJM-PVB-2	
				ACJM-PVB-2S	
				ACJS-PVB-3	
				ACJS-PVB-3S	
				ACJS-PVB-5	
		1/4" (6.35mmØ) Jack, Vertical PCB mount, Needle eye contacts, Plastic thread, Metal nut and insert	Refer to Schematic Chart on page 115	ACJM-MIV-2	
				ACJM-MIV-2S	
				ACJS-MIV-3	
				ACJS-MIV-3S	
				ACJS-MIV-5	
		1/4" (6.35mmØ) Jack, Vertical PCB mount, Needle eye contacts, Star washer, Metal nut and insert	Refer to Schematic Chart on page 115	ACJM-MN-2	
				ACJS-MN-3	
				ACJM-MN-2S	
				ACJS-MN-3S	
				ACJS-MN-5	
		1/4" (6.35mmØ) Jack, Vertical PCB mount, Metal nut and insert	Refer to Schematic Chart on page 115	ACJM-MV-2	
				ACJM-MV-2S	
				ACJS-MV-3	
				ACJS-MV-3S	
				ACJS-MV-5	

* This product protected by U.S. patent No. 6,116,959

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		1/4" (6.35mm) Jack, Solder Lug, Metal nut and insert	Refer to Schematic Chart on Page 110	ACJM-MVS-2 ACJM-MVS-2S ACJS-MVS-3 ACJS-MVS-3S ACJS-MVS-5	ACJM-MVS-2
					ACJM-MVS-2S
					ACJS-MVS-3
					ACJS-MVS-3S
					ACJS-MVS-5

PANEL CUTOUTS
















-FRONT VIEW

 <p>+ Panel cutout CL</p> <p>ACJM-MV ACJS-MV ACJM-MN-2 ACJS-MN-2 ACJM-MN-2S ACJS-MN-3S ACJM-MN-5 ACJS-MN-5 ACJM-MIV ACJS-MIV ACJM-MVS ACJS-MVS</p>	 <p>+ Panel cutout CL</p> <p>ACJM/S-PH ACJM/S-MH ACJM/S-PC ACJM/S-MC ACJM/S-PHR ACJM/S-MHR ACJM/S-PHS ACJM/S-MHS</p>	 <p>+ Panel cutout CL</p> <p>ACJM-MHD ACJS-MHD ACJM-MHDE ACJS-MHDE</p>	 <p>+ Panel cutout CL</p> <p>ACJM-MHDR ACJS-MHDR ACJS-HHDR</p>
 <p>+ Panel cutout CL</p> <p>ACJM-NH35 ACJS-NH35</p>	 <p>+ Panel cutout CL</p> <p>ACJM-NV35-2 ACJM-NV35-2S ACJS-NV-35-3 ACJS-NV-35-3S ACJS-NV-35-5 ACJM-MV35-2 ACJM-MV35-2S ACJS-MV-35-3 ACJS-MV-35-3S ACJS-MV-35-5</p>	 <p>+ Panel cutout CL</p> <p>ACJS-MHDC ACJM-MHDC</p>	 <p>+ Panel cutout CL</p> <p>ACJS-IH ACJM-IH ACJS-IHS ACJM-IHS</p>
 <p>+ Panel cutout CL</p> <p>ACJS-MHD985 ACJM-MHD985</p>	 <p>+ Panel cutout CL</p> <p>ACJS-MHOM ACJM-MHOM</p>	 <p>+ Panel cutout CL</p> <p>ACJS-MHOP ACJS-PHOP ACJM-MHOP ACJM-PHOP ACJS-MHOP-1 ACJS-HHOP-1 ACJS-PHOP-1 ACJM-PHOP-1 ACJM-MHOP-1 ACJM-HHOP-1 ACJS-HHOP ACJS-HHOP</p>	 <p>+ Panel cutout CL</p> <p>ACJS-MVD985 ACJM-MVD985</p>
 <p>+ Panel cutout CL</p> <p>ACJM-PVB-2 ACJM-PVB-2S ACJS-PVB-3 ACJS-PVB-3S ACJS-PVB-5</p>			


Plugs & Jacks

Musician / OEM Range 1/4" Phone Jacks


SCHEMATIC CHART

PART NO.	ACJM-MV35-2 ACJM-MN-2 ACJM-NV35-2 ACJM-PVB-2 ACJM-MV-2 ACJM-MVS-2 ACJM-MIV-2	ACJM-MV35-2S ACJM-MN-2S ACJM-NV35-2S ACJM-PVB-2S ACJM-MV-2S ACJM-MVS-2S ACJM-MIV-2S	ACJS-MV35-3 ACJS-MN-3 ACJS-NV35-3 ACJS-PVB-3 ACJS-MV-3 ACJS-MVS-3 ACJS-MIV-3	ACJS-MV35-3S ACJS-MN-3S ACJS-NV35-3S ACJS-PVB-3S ACJS-MV-3S ACJS-MVS-3S ACJS-MIV-3S	ACJS-MV35-5 ACJS-MN-5 ACJS-NV35-5 ACJS-PVB-5 ACJS-MV-5 ACJS-MVS-5 ACJS-MIV-5
GENERAL SCHEMATIC					
SCHEMATIC	 	 	 		
PART NO.	ACJM-HHOP-1 ACJM-PHOP-1 ACJM-MHOP-1	ACJS-HHOP-1 ACJS-PHOP-1 ACJS-MHOP-1	ACJM-HHOP ACJM-PHOP ACJM-MHOP	ACJS-HHOP ACJS-PHOP ACJS-MHOP	
GENERAL SCHEMATIC	 	 			


PCB FOOTPRINT - CONNECTOR SIDE OF PCB




ACJM-MV
ACJS-MV
ACJM-MN-2
ACJS-MN-3
ACJM-MN-2S
ACJS-MN-3S
ACJS-MN-5
ACJM-NV35-X
ACJM-MV35-X
ACJS-NV35-XX
ACJS-MV35-XX
ACJM-MIV-2
ACJM-MIV-2S
ACJS-MIV-3
ACJS-MIV-3S
ACJS-MIV-5




ACJM-PH
ACJM-MI
ACJS-PH
ACJS-MH
ACJM-PC
ACJM-MO
ACJS-PC
ACJS-MO




ACJM-MHD
ACJS-MHD
ACJM-MHDE
ACJS-MHDE
ACJM-MHDEM
ACJS-MHDEM
ACJM-MHDC
ACJS-MHDC
ACJM-MHDCM
ACJS-MHDCM
ACJM-MHDM
ACJS-MHDM




ACJM-MHDR
ACJS-MHDR
ACJM-PHR
ACJM-MHR
ACJS-PHR
ACJS-MHR
ACJM-HHDR
ACJS-HHDR
ACJM-MHDRV
ACJS-MHDRV




ACJS-IH
ACJM-IH




ACJS-MHD985
AC-JM-MHD985




ACJS-MHOM
ACJM-MHOM




ACJS-MHOP-1
ACJS-PHOP-1
ACJS-HHOP-1
ACJM-MHOP-1
ACJM-PHOP-1
ACJM-HHOP-1




ACJS-MHOP
ACJS-PHOP
ACJM-MHOP
ACJM-PHOP
ACJM-HHOP
ACJS-HHOP



ACJS-MVD985
ACJM-MVD985



ACJS-NH35
ACJM-NH35



ACJM-PVB-2
ACJM-PVB-2S
ACJS-PVB-3
ACJS-PVB-3S
ACJS-PVB-5

Plugs & Jacks

Musician / OEM Range 1/4" Phone Jacks

1/4" PLUGS TECHNICAL DATA

		VALUE
GENERAL CHARACTERISTICS	Number of Contacts	2 Pole (Mono) 3 Pole Tip Ring Sleeve (Stereo)
	Termination	Solder
	Max. Wire Gauge - Stranded Wire	2 Pole (Mono): AWG 16~1.5mm ² 3 Pole (Stereo): AWG 18~1mm ²
	Flammability rating of insulating plastics	UL94V-0
	Solderability, complies with	IEC 68-2-20
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	10A (Depends on Mating Connector and Cable)
	Typical Contact Resistance	Depends on Mating Connector
	Insulation resistance (initial) After Damp Heat Test	>2GΩ ≥1GΩ
	Dielectric Withstand Voltage	2 Pole : 1.5 kV dc 3 Pole : 1 kV dc
CLIMATIC CHARACTERISTICS	Protection Class	IP40
	Operating Temperature	-25°C to +70°C (-13°F to 158°F)
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal Force	≥10N - ≤30N
	Mating Cycles	Min. of 1000 cycles without any physical damage
	Cable O.D. - M Series - M Series II	3mm to 6.5mm (0.118" to 0.256") 6.5mm to 8mm (0.256" to 0.315")
MATERIALS	Connector Shell Material	Diecast Zinc Alloy EZDA No.3
	Connector Shell Finish	Satin Nickel or Black Polyester
	Insulators	UL94 V-0 PBT Resin or Modified PPE Resin and fibreglass laminate
	Cable Bushing	Santoprene
	Contact Plating	Brass / Ni over Cu (Copper)

¹⁾Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

Rev 4 - 06/2014

1/4" JACKS TECHNICAL DATA

		VALUE
GENERAL CHARACTERISTICS	Number of Contacts	2 Pole (Mono) 3 Pole Tip Ring Sleeve (Stereo)
	Termination	Solder, PCB or Combo
	Flammability rating of insulating plastics	UL94V-0
	Solderability, complies with	IEC 68-2-20
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	10A (Depends on Mating Connector and Cable)
	Typical Contact Resistance	$\leq 10\text{m}\Omega$
	Insulation resistance (initial) After Damp Heat Test	$>2\text{G}\Omega$ $\geq 10^3 \text{ Meg }\Omega$
	Rated Voltage Test Voltage AC RMS: Dielectric Strength	34V 500V
CLIMATIC CHARACTERISTICS	Protection Class	IP40
	Operating Temperature	-25°C to +70°C (-13°F to 158°F)
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal Force	$\geq 10\text{N} - \leq 30\text{N}$
	Mating Cycles	Min. of 1000 cycles without any physical damage
	Weight - Straight - Right Angle	18g (0.039lb) 25g (0.055lb)
MATERIALS	Connector Housing	Nylon PA66 30% Glass Filled
	Metal Nut	Brass
	Plastic Nut	Nylon PA66 30% Glass Filled
	Washer	Fiber / Brass / Nylon PA66 30% Glass Filled
	Contact Plating	Tin - 4 μm Min. over 2 μm Min.Cu (Copper) Silver - 0.3 μm Min. over 2 μm Min.Cu (Copper) Nickel - 2 μm Min. over 2 μm Min.Cu (Copper) Gold Flash - 0.05 μm Min. over 2 μm Min.Cu (Copper)
	Contacts	Brass / Sn (Tin) over Cu (Copper)

¹Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

Rev 5 - 09/2017

Plugs & Jacks

Musician / OEM Range 1/4" Phone Jacks



Applications

- Audio Cables and Snakes
- Amplifiers
- Speakers
- Mixing desks
- Rack mount equipment
- Patch panel

Features / Options – RCA Plugs and Jacks

- Red, Black, White, Yellow, Blue or Green shell colours
- Stylish shell design
- Flexible grommet cable protection
- Gold Plated Contacts

Features / Options – Miniature XLR

- 3,4,5, or 6 contacts
- Solder cup
- Printed Circuit Board
- Vertical or Horizontal mounting
- Positive locking latch
- Flexible cable clamp
- Metal cable clamp
- Locking rings
- Chassis front mount
- Chassis middle or rear mount (on request)
- Optional black finish (on request)

Features / Options – 3.5mm Plugs Phone Jack

- Mono / Stereo TRS
- Solder contacts
- Suits cable O.D 2.5mm to 5mm
- Stylised shell design
- Flexible cable grommet
- Metal cable clamp
- Nickel or Gold contact plating
- Satin Nickel or Black finish

Cable Clamp Options



RCA Cable Clamp - M-Series, Cable O.D 3mm to 6.5mm (0.118" to 0.256")



K-Series, Cable O.D 3mm to 5mm (0.118" to 0.196")

PLUGS AND SOCKETS

Amphenol's plugs and sockets range continually expands to meet the needs of our customers. The success of the M-Series phone plugs led to the RCA series being developed. The Miniature XLR range was a natural progression from our standard XLR series as demand for smaller interconnects increased. The latest addition to the range is a professional grade 3.5mm phone plug designed for applications that require a robust interconnect.

Ordering Codes

We have listed the more common ordering codes in each section. Please contact us if you need any further assistance.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use variations column to determine your choice.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.



K-Series (3.5mm)

Features:

- Mono or TRS (Stereo).
- AX Series inspired shell design.
- Suits Cable O.D from 2.5mm to 5mm (0.098" to 0.196")
- Robust diecast shell in Satin nickel or Black finish.
- Nickel or Gold contact plating.
- Flexible grommet cable protection.
- Improved solderability.
- Precision machined contacts.
- Standard or Bulk packaging.

Options: Black Shell, Gold contacts.

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		3.5mm, Mono Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	KM2P	
			Gold Plated Contacts	KM2P-AU	
			Bulk Pack	KM2P BULK	
		3.5mm, Mono Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	KM2PB	
			Gold Plated Contacts	KM2PB-AU	
			Bulk Pack	KM2PB BULK	
		3.5mm, Stereo Phone plug, Diecast Shell, Satin finish, Flexible grommet.	Standard	KS3P	
			Gold Plated Contacts	KS3P-AU	
			Bulk Pack	KS3P BULK	
		3.5mm, Stereo Phone plug, Diecast Shell, Black finish, Flexible grommet.	Standard	KS3PB	
			Gold Plated Contacts	KS3PB-AU	
			Bulk Pack	KS3PB BULK	
		3.5mm, Stereo Phone plug with extended shaft for mobile phones fitted with covers. Diecast Shell, Black Chrome finish, Flexible grommet	Standard	KS3PC	
			Gold Plated Contacts	KS3PC-AU	

Plugs & Jacks

K-Series Plugs (3.5mm) Plugs


PART NUMBER BREAKDOWN

K-SERIES

E. G. **KS3P-AU BULK**
 K (Series Prefix), S3(Stereo), P, Plug,
 - AU (Gold Plated Contacts), Bulk Packaged.

SERIES PREFIX	K	S3	P		-	AU	BULK	PACKAGING
CONTACT TYPE	M2							
SHELL TYPE AND FINISH	P							
PB								
PC								
BACKSHELL TYPE AND CABLE CLAMP	Blank							
CONTACT PLATING	Blank							
AU								
PACKAGING	Blank							
BULK								

ISO VIEW OF KS3P



3.5mm PLUG TECHNICAL DATA

		VALUE
GENERAL CHARACTERISTICS	Number of Contacts	2 Pole (Mono) 3 Pole Tip Ring Sleeve (Stereo)
	Termination	Solder
	Wire Gauge - Stranded Wire	2 Pole (Mono): AWG 16 - 1.5mm ² 3 Pole (Stereo): AWG 18 - 1mm ²
	Flammability rating of insulating plastics	UL94V-0
	Solderability, complies with	IEC 68-2-20
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	>0.5mA (Depends on Mating Connector and Cable)
	Typical Contact Resistance	≤20mΩ (Depends on Mating Connector and Cable)
	Insulation resistance (initial) After Damp Heat Test	>200M Ω >100M Ω
	Test Voltage AC RMS: Dielectric Strength	250VAC
CLIMATIC CHARACTERISTICS	Protection Class	IP40
	Operating Temperature	-20°C to +65°C (-4°F to +149°F)
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal Force	<20N / >3N (depends on mating connector)
	Cable O.D.	3mm to 5mm (0.118" to 0.196")
	Mechanical Operations	1000 mating cycles
	Weight	8g (0.017lb)
MATERIALS	Connector Shell Material (Plugs)	Diecast Zinc Alloy EZDA No.3
	Connector Shell Finish	Satin Nickel or Black Polyester
	Insulators	PA66
	Cable Bushing	Santoprene
	Contacts	Brass
	Plating	Nickel or Gold Flash

¹ Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

Plugs & Jacks

RCA Series




Features:

- Stylish design
- Flexible grommet cable protection
- Robust diecast shell
- Gold plated contacts
- Colour coded
- Good solderability
- Quick and easy assembly
- Panel mount utilises standard 'D' type housing

Part Number Breakdown: Page 121

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			RCA Plug, Diecast Shell, Gold plated contacts, Coloured finish, Flexible coloured grommet	Red Black Yellow White Blue Green	ACPR-RED ACPR-BLK ACPR-YEL ACPR-WHT ACPR-BLU ACPR-GRN
			RCA Plug, Diecast Shell, Gold plated contacts, Satin finish, Flexible coloured grommet	Satin / Red Satin / Black Satin / Yellow Satin / White Satin / Blue Satin / Green	ACPR-SRD ACPR-SBK ACPR-SYL ACPR-SWH ACPR-SBL ACPR-SGR
			RCA Jack, Diecast Shell, Gold plated contacts, Coloured finish, Flexible coloured grommet	Red Black Yellow White Blue Green	ACJR-RED ACJR-BLK ACJR-YEL ACJR-WHT ACJR-BLU ACJR-GRN
			RCA Jack, Diecast Shell, Gold plated contacts, Satin finish, Flexible coloured grommet	Satin / Red Satin / Black Satin / Yellow Satin / White Satin / Blue Satin / Green	ACJR-SRD ACJR-SBK ACJR-SYL ACJR-SWH ACJR-SBL ACJR-SGR
			RCA Plug, Shortened Diecast Shell, Gold plated contacts, Black Chrome finish, Flexible coloured grommet	Red Black Yellow White Blue Green	ACPL-CRD ACPL-CBK ACPL-CYL ACPL-CWH ACPL-CBL ACPL-CGR

NOTE: RCA Series comply with EU RoHS 2 Directive 2011/65/EU

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		RCA Jack, Diecast Shell, Gold plated contacts, Nickel finish shell, coloured insulator.	Red	ACJD-RED	
			Black	ACJD-BLK	
			Yellow	ACJD-YEL	
			White	ACJD-WHT	
			Blue	ACJD-BLU	
			Green	ACJD-GRN	

NOTE: RCA Series comply with EU RoHS 2 Directive 2011/65/EU

PART NUMBER BREAKDOWN

M SERIES RCA

E. G. **ACPR-RED BULK**

AC (Series Prefix), Plug, R(Shell type), RED (Shell and Grommet Colour), Bulk Packaged.

SERIES PREFIX CONTACT TYPE SHELL TYPE SHELL FINISH PACKAGING

AC P R - RED BULK

SERIES PREFIX	AC	≡ Series Prefix
CONTACT TYPE	J	≡ RCA Female Jack
	P	≡ RCA Male Plug
SHELL TYPE	R	≡ Regular Shell Length
	L	≡ Short Shell Length
	D	≡ Chassis Jack 'D' Shell
SHELL AND GROMMET COLOUR	RED	≡ Red, Red Grommet
	BLK	≡ Black, Black Grommet
	YEL	≡ Yellow, Yellow Grommet
	WHT	≡ White, White Grommet
	BLU	≡ Blue, Blue Grommet
	GRN	≡ Green, Green Grommet
	SRD	≡ Satin Nickel, Red Grommet
	CRD	≡ Black Chrome, Red Grommet
	SBK	≡ Satin Nickel, Black Grommet
	CBK	≡ Black Chrome, Black Grommet
	SYL	≡ Satin Nickel, Yellow Grommet
	CYL	≡ Black Chrome, Yellow Grommet
	SWH	≡ Satin Nickel, White Grommet
	CWH	≡ Black Chrome, White Grommet
	SBL	≡ Satin Nickel, Blue Grommet
	CBL	≡ Black Chrome, Blue Grommet
	SGR	≡ Satin Nickel, Green Grommet
	CGR	≡ Black Chrome, Green Grommet
<p>NOTE: Denotes colour of insulator only on shell type D, Chassis Jack 'D' Shell. Shell finish is Nickel.</p>		
PACKAGING	Blank	≡ Individual Bags
	BULK	≡ Bulk Packed

Plugs & Jacks

RCA Series

RCA TECHNICAL DATA

		VALUE
GENERAL CHARACTERISTICS	Number of Contacts	2
	Termination	Solder
	Max. Wire Gauge - Stranded Wire	AWG 14 - 2.5mm ²
	Flammability rating of insulating plastics	UL94V-0
	Solderability, complies with	IEC 68-2-20
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU
ELECTRICAL CHARACTERISTICS	Current Carrying Capacity	10A (Depends on Mating Connector)
	Typical Contact Resistance	$\leq 10\text{m}\Omega$ (Depends on Mating Connector)
	Insulation resistance (initial) After Damp Heat Test	$>2\text{G}\Omega$ $\geq 10^3 \text{ Meg }\Omega$
	Dielectric Strength	1500 V dc
CLIMATIC CHARACTERISTICS	Protection Class	IP40
	Operating Temperature	-25°C to +75°C (-13°F to +167°F)
MECHANICAL CHARACTERISTICS	Insertion and Withdrawal Force	$\geq 10\text{N} - \leq 30\text{N}$ (depends on mating connector)
	Cable O.D.	3mm to 7mm (0.118" to 0.275")
	Mechanical Operations	500 mating cycles
	Weight - Cable Mount - Panel Mount	18g (0.039lb) 30g (0.066lb)
MATERIALS	Connector Shell Material (Plugs)	Diecast Zinc Alloy EZDA No.3
	Connector Shell Finish	Satin Nickel or Coloured Polyester
	Insulators	PA66
	Cable Bushing	Thermoplastic Polyurethane
	Contacts	Brass Alloy
	Plating	Gold Flash

¹⁾Approximate weight only, does not include packaging. Please contact us for exact weight for shipping purposes.

MULTIPIN CONNECTORS



Amphenol has an extensive range of circular and rectangular multi-pin connectors ideally suited to the entertainment industry. Featuring rugged housings and precision made contacts these connectors have proven themselves in the most demanding of applications. The extensive arrangement of different connector sizes and contact numbers ensure we can offer a solution to your multi-pin wiring applications.

Applications

- Audio Cables and Snakes
- Lighting control
- Concert Touring Systems
- Outside Broadcast Systems

Features / Options - MP-41 Series

- 13 to 85 pins with Crimp / Solder bucket contacts
- 150 pins with Crimp contacts only
- 4 to 48 channel
- Gold plated contacts
- Synthetic inserts
- Environmental resistant
- Positive Bayonet locking
- PG cable gland
- 2000 mating cycles
- Bayonet wear pins
- Extended coupling ring
- Metal Housings

Features / Options - MP-62 Series

- 39 or 61 Solder bucket contacts
- Gold plated contacts
- Neoprene inserts
- Environmental resistant
- Positive Bayonet locking
- PG cable gland or NPT thread
- Metal Housings

Ordering Codes

We have listed the more common ordering codes in each section. For further options please contact us.

Simple steps to guide you in using this catalogue

- 1) Identify the product group listed in Contents on page 1 and go directly to that page number.
- 2) Each product group cover page then details information and options available.
- 3) Refer to the product detail pages and identify the product you require pictorially.
- 4) Read the product description column for the products standard features.
- 5) Use pins column to determine number of contacts.
- 6) Identify part number.
- 7) In the event the particular option you require is not listed please refer to the part number breakdown page at the end of each section.
- 8) Please contact us directly if you have any further problems.

Multipin Connectors

MP-41 Series



MP-41 Series

Amphenol's MP-41 series of multipin connectors utilise the same design principals of the rugged Mil-C-5015 military connectors. They can withstand high shock and vibration environments and are ideal for tough on-road applications. Featuring a quick mating bayonet coupling with an audible full mating feature ensures a positive connection every time. Available from 13 to 150 pins with contacts supplied with each connector as standard.

Features:


- 13 to 85 pins with Crimp/Solder bucket contacts
- 150 pins with Crimp contacts only
- 4 to 48 channels
- Gold plated contacts
- Synthetic insert
- Protective dust caps
- Industry standard compatible
- 2000 mating cycles
- Black finish
- Positive bayonet locking
- PG cable glands
- IP67 rated
- Metal housings

Options: NPT threaded backshells.

Crimp Tooling: Page 127

Specifications: Page 128 Part Number Breakdown: Page 127





Wiring Information: Page 141

PRODUCT - FIGURE	Dimensions in mm (inches) DRAWING	Dimensions in mm (inches)			PINS	PART NUMBER	PART NUMBER With Dustcap
		A	B	PG			
	<p>Straight cable plug with socket contacts, Black finish, supplied complete with contacts.</p> 	40.5 (1.60)	160 (6.30)	11	13	MP-4106-13S	MP-4106-13S-C
		44 (1.73)	171 (6.73)	13.5	19	MP-4106-19S	MP-4106-19S-C
		46.6 (1.83)	193 (7.60)	16	25	MP-4106-25S	MP-4106-25S-C
		54.3 (2.14)	210 (8.26)	21	37	MP-4106-37S	MP-4106-37S-C
		60.1 (2.36)	210 (8.26)	21	54	MP-4106-54S	MP-4106-54S-C
		73.3 (2.88)	137 (5.40)	29	85	MP-4106-85S	MP-4106-85S-C
		73.3 (2.88)	145 (5.70)	36	150	MP-4106-150S	MP-4106-150S-C
	<p>Cable connecting receptacle with pin contacts, black finish, supplied complete with contacts.</p> 	37.8 (1.49)	160 (6.30)	11	13	MP-4101-13P	MP-4101-13P-C
		41.1 (1.62)	171 (6.73)	13.5	19	MP-4101-19P	MP-4101-19P-C
		41.5 (1.63)	193 (7.60)	16	25	MP-4101-25P	MP-4101-25P-C
		51 (2.00)	210 (8.26)	21	37	MP-4101-37P	MP-4101-37P-C
		57.1 (2.25)	210 (8.26)	21	54	MP-4101-54P	MP-4101-54P-C
		70 (2.75)	137 (5.40)	29	85	MP-4101-85P	MP-4101-85P-C
		70 (2.75)	145 (5.70)	36	150	MP-4101-150P	MP-4101-150P-C

Note: NPT threaded backshells available on request. Please contact us.

Multipin Connectors

MP-41 Series

PRODUCT - FIGURE	Dimensions in mm (inches) DRAWING	Dimensions in mm (inches)						PINS	PART NUMBER	PART NUMBER With Dustcap
		A	B	C	D	E	F			
	Panel plug with socket contacts, black finish, supplied complete with contacts. 									
		38 (1.49)	29.4 (1.15)	3.2 (0.13)	40.5 (1.60)	38.8 (1.53)	N/A	13	MP-4164-13S	MP-4164-13S-C
		41 (1.61)	31.8 (1.25)	3.2 (0.13)	44 (1.73)	38.8 (1.53)	N/A	19	MP-4164-19S	MP-4164-19S-C
		44.5 (1.75)	34.9 (1.37)	3.73 (0.14)	48.51 (1.91)	40.6 (1.60)	N/A	25	MP-4164-25S	MP-4164-25S-C
		50.8 (1.99)	39.7 (1.56)	3.73 (0.14)	54.3 (2.14)	42 (1.65)	N/A	37	MP-4164-37S	MP-4164-37S-C
		57 (2.24)	44.5 (1.75)	4.39 (0.17)	60.8 (2.40)	45 (1.77)	N/A	54	MP-4164-54S	MP-4164-54S-C
		69.8 (2.74)	55.5 (2.18)	4.39 (0.17)	73.3 (2.88)	45 (1.77)	N/A	85	MP-4164-85S	MP-4164-85S-C
	Panel receptacle with pin contacts, black finish, supplied complete with contacts. 	69.8 (2.74)	55.5 (2.18)	4.39 (0.17)	73.3 (2.88)	45 (1.77)	N/A	150	MP-4164-150S	MP-4164-150S-C
		38 (1.49)	29.4 (1.15)	3.23 (0.13)	34.2 (1.34)	34.5 (1.35)	29 (1.14)	13	MP-4102-13P	MP-4102-13P-C
		41 (1.61)	31.8 (1.25)	3.23 (0.13)	37.4 (1.47)	34.5 (1.35)	32.2 (1.26)	19	MP-4102-19P	MP-4102-19P-C
		44.5 (1.75)	34.9 (1.37)	3.73 (0.14)	40.9 (1.61)	35.7 (1.40)	35.3 (1.38)	25	MP-4102-25P	MP-4102-25P-C
		50.8 (1.99)	39.7 (1.56)	3.73 (0.14)	46.7 (1.83)	36.5 (1.44)	41.4 (1.62)	37	MP-4102-37P	MP-4102-37P-C
		57 (2.24)	44.5 (1.75)	4.30 (0.17)	53.4 (2.10)	38.5 (1.52)	47.8 (1.88)	54	MP-4102-54P	MP-4102-54P-C
		69.8 (2.74)	55.5 (2.18)	4.30 (0.17)	65.5 (2.57)	38.5 (1.52)	59 (2.32)	85	MP-4102-85P	MP-4102-85P-C
	Plug protective dustcap to suit MP-4164 type. 	69.8 (2.74)	55.5 (2.18)	4.30 (0.17)	65.5 (2.57)	38.5 (1.52)	59 (2.32)	150	MP-4102-150P	MP-4102-150P-C
		34.16 (1.35)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	13	MP-25042-13S	-
		37.36 (1.47)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	19	MP-25042-19S	-
		40.87 (1.61)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	25	MP-25042-25S	-
		46.68 (1.84)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	37	MP-25042-37S	-
		53.36 (2.10)	31.5 (1.24)	110 (4.33)	5.5 (0.22)	-	-	54	MP-25042-54S	-
		65.48 (2.58)	31.5 (1.24)	110 (4.33)	5.5 (0.22)	-	-	85	MP-25042-85S	-
	Receptacle protective dustcap to suit MP-4106 types. 	65.48 (2.58)	31.5 (1.24)	110 (4.33)	5.5 (0.22)	-	-	150	MP-25042-150S	-
		38.8 (1.53)	20.7 (0.81)	255 (8.07)	-	-	-	13	MP-25042-13L	-
		41.6 (1.64)	20.7 (0.81)	255 (8.07)	-	-	-	19	MP-25042-19L	-
		45.3 (1.78)	20.7 (0.81)	255 (8.07)	-	-	-	25	MP-25042-25L	-
		52.15 (2.05)	20.7 (0.81)	255 (8.07)	-	-	-	37	MP-25042-37L	-
		58.6 (2.30)	20.7 (0.81)	255 (8.07)	-	-	-	54	MP-25042-54L	-
		70.7 (2.78)	20.7 (0.81)	255 (8.07)	-	-	-	85	MP-25042-85L	-
		70.7 (2.78)	20.7 (0.81)	255 (8.07)	-	-	-	150	MP-25042-150L	-

Multipin Connectors

MP-41 Series

PRODUCT - FIGURE	Dimensions in mm (inches) DRAWING	Dimensions in mm (inches)						PINS	PART NUMBER
		A	B	C	D	E	F		
	Plug protective dustcap to suit MP-4102 types.	34.16 (1.35)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	13	MP-25043-13S
		37.36 (1.47)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	19	MP-25043-19S
		40.87 (1.61)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	25	MP-25043-25S
		46.68 (1.84)	31.5 (1.24)	110 (4.33)	4.7 (0.18)	-	-	37	MP-25043-37S
		53.36 (2.10)	31.5 (1.24)	110 (4.33)	5.5 (0.22)	-	-	54	MP-25043-54S
		65.48 (2.58)	31.5 (1.24)	110 (4.33)	5.5 (0.22)	-	-	85	MP-25043-85S
		65.48 (2.58)	31.5 (1.24)	110 (4.33)	5.5 (0.22)	-	-	150	MP-25043-150S
		38.8 (1.53)	20.7 (0.81)	255 (8.07)	-	-	-	13	MP-25043-13L
	Receptacle protective dustcap to suit MP-4101 types.	41.6 (1.64)	20.7 (0.81)	255 (8.07)	-	-	-	19	MP-25043-19L
		45.3 (1.78)	20.7 (0.81)	255 (8.07)	-	-	-	25	MP-25043-25L
		52.15 (2.05)	20.7 (0.81)	255 (8.07)	-	-	-	37	MP-25043-37L
		58.6 (2.30)	20.7 (0.81)	255 (8.07)	-	-	-	54	MP-25043-54L
		70.7 (2.78)	20.7 (0.81)	255 (8.07)	-	-	-	85	MP-25043-85L
		70.7 (2.78)	20.7 (0.81)	255 (8.07)	-	-	-	150	MP-25043-150L

PRODUCT - FIGURE	DRAWING	DESCRIPTION	NO. OF PINS	PART NUMBER
	N/A	Crimp Tool	All	M22520/1-01
	N/A	Positioner / Turret	All	TH29-1
	N/A	Insertion tool	13-85	MP-INS-16
			150	MP-INS-18
	N/A	Extraction tool	All	MP-EXT-16/18
	N/A	Contact Pilot Pin	13-85	MP-GUIDE-16
			150	MP-GUIDE-18
	N/A	Solder/Crimp Pin Contact	13-85 (Size 16)	MP-108400
		Crimp Pin Contact (Soldering of this contact is not recommended)	150 (Size 18)	MP-108300
	N/A	Solder/Crimp Socket Contact	13-85 (Size 16)	MP-108600
		Crimp Socket Contact (Soldering of this contact is not recommended)	150 (Size 18)	MP-108500

NOTE: Complete instructions for providing reliable crimped wire to contact terminations and inserting proprietary contacts in MP-41 Series connectors are available in publication Pi523 located on our website www.amphenolaudio.com.

PART NUMBER BREAKDOWN MP-41 SERIES

MULTIPIN CIRCULAR CONNECTORS

E. G. **MP-4106-85S**
Multipin, 4106 Cable Plug, 85 Contacts, S Female Socket Contacts,

SERIES PREFIX	MP	=	Series Prefix
HOUSING TYPE	4101	=	Inline cable connecting receptacle
	4102	=	Panel receptacle
	4106	=	Cable plug
	4164	=	Panel plug
	25042S	=	Dustcap for panel plug
	25042L	=	Dustcap for cable plug
	25043S	=	Dustcap for panel receptacle
	25043L	=	Dustcap for cable receptacle
NO. OF CONTACTS	13, 19, 25, 37, 54, 85, 150		
GENDER	P	=	Male pin contacts
*Not required for dustcap part numbers		S	= Female socket contacts
OPTIONS	C	=	Supplied with Dustcap

SERIES PREFIX	HOUSING TYPE	NUMBER OF CONTACTS	*GENDER	OPTIONS
MP	4106	85	S	C

Multipin Connectors

MP-41 Series

STANDARD DATA MP-41 SERIES

		VALUE						
GENERAL CHARACTERISTICS	Number of contacts	13	19	25	37	54	85	150
	Number of channels	4	6	8	12	16	28	48
	Termination	Solder / Crimp "Combo"						Crimp
	Wire Gauge - Stranded Wire	16AWG - 20AWG						18AWG
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU						
ELECTRICAL CHARACTERISTICS	Operating Voltage at Sea level - DC	250V*						250V*
	Operating Voltage at Sea level - AC	200V*						200V*
	Test Voltage AC RMS	1000V						1000V
	Current Carrying Capacity	13A						7.5A
	Typical Contact Resistance	3.46mΩ						11.25mΩ
	Insulation Resistance	5000MΩ						
CLIMATIC CHARACTERISTICS	Protection Class	IP67 (when mated)						
	Operating Temperature	-55°C to +125°C (-67°F to +257°F)						
MECHANICAL CHARACTERISTICS	Cable Retention	PG Gland						
	Mechanical Operations	2000 mating cycles						
MATERIALS	Connector / Shell Finish	Aluminium Alloy / Black						
	Insert	Synthetic Insert to MIL-R-3065						
	Male pin contact / Plating	Brass / Gold plated						
	Female socket contact / Plating	Brass / Gold plated						
CLAMPING CHARACTERISTICS	PG Gland	11	13.5	16	21	29	36	
	Cable Clamping range mm (inches)	4-10 (0.15"- 0.39")	5-12 (0.19"- 0.47")	9-14 (0.35"- 0.55")	13-18 (0.51"- 0.70")	14-25 (0.55"- 0.98")	19-32 (0.74"- 1.25")	

*Not suitable for domestic applications above 50V

Rev 2 - 03/2013







MP-62 / MP-65 Series

Amphenol's Multipin MP-62 series of circular connectors utilise the same design principles as the Mil-C-26482 military connectors. Featuring a three point quick mating bayonet coupling and five key polarisation ensuring a positive connection every time. Available in two contact pin layouts 39 and 61 with gold plated solder contacts fitted as standard.

Features:



- 39 or 61 pins.
- Environmental resistant.
- Gold plated solder contacts.
- Black finish.
- Neoprene insert.
- Positive bayonet locking.
- Protective dust caps
- PG cable glands
- Metal housings





Specifications: Page 131 **Wiring Info: Page 141**

PRODUCT - FIGURE	Dimensions in mm (inches) DRAWING	Dimensions in mm (inches)			PINS	PART NUMBER	PART NUMBER With Dustcap
		A	B	PG			
	<p>Straight cable plug with pin contacts, Black finish, Gold plated solder contacts.</p> 	38.9 (1.53)	181.5 (7.15)	16 39	39	MP-6216-39P	MP-6216-39P-C
		45.5 (1.80)	193 (7.60)	21 61			
	<p>Cable connecting receptacle with socket contacts, Black finish, Gold plated solder contacts.</p> 	36.7 (1.45)	181.5 (7.15)	16 39	39	MP-6211-39S	MP-6211-39S-C
		43.0 (1.70)	193 (7.60)	21 61			
	<p>Straight cable plug with pin contacts, NPT 3/4" threaded backshell, Black finish, Gold plated solder contacts.</p> 	38.9 (1.53)	90 (3.54)	NPT 3/4"	39	MP-6516-39P	MP-6516-39P-C
		45.5 (1.80)	100 (3.94)	NPT 3/4"			
	<p>Cable connecting receptacle with socket contacts, NPT 3/4" threaded backshell, Black finish, Gold plated solder contacts.</p> 	36.7 (1.45)	90 (3.54)	NPT 3/4"	39	MP-6511-39S	MP-6511-39S-C
		43.0 (1.70)	100 (3.94)	NPT 3/4"			

Multipin Connectors

MP-62 / MP-65 Series

PRODUCT - FIGURE	DRAWING Dimensions in mm (inches)	Dimensions in mm (inches)						PINS	PART NUMBER	PART NUMBER With Dustcap
		A	B	C	D	E	F			
	Panel plug with pin contacts, Black finish, Gold plated solder contacts. 	38.86 (1.53)	29.36 (1.16)	6-32 UNC	39.0 (1.54)	32 (1.26)	-	39	MP-6256-39P	MP-6256-39P-C
		43.94 (1.73)	34.93 (1.38)	6-32 UNC	45.5 (1.80)	35 (1.38)	-	61	MP-6256-61P	MP-6256-61P-C
	Panel receptacle plug with socket contacts, Black finish, Gold plated solder contacts. 	36.7 (1.44)	29.36 (1.15)	3.05 (0.12)	31.8 (1.25)	22.3 (0.87)	30.1 (1.18)	39	MP-6212-39S	MP-6212-39S-C
		43.0 (1.69)	34.93 (1.38)	3.74 (0.15)	38.1 (1.50)	22.3 (0.87)	36.4 (1.43)	61	MP-6212-61S	MP-6212-61S-C

PRODUCT - FIGURE	DRAWING Dimensions in mm (inches)	DESCRIPTION	Dimensions in mm (inches)			PINS	PART NUMBER	
			A	B	C			
		Plug protective dustcap to suit MP-6256	31.7 (1.25)	15.9 (0.62)	127 (4.99)	4.40 (0.17)	39	MP-742-39S
			38.05 (1.50)	16.70 (0.66)	127 (4.99)	4.40 (0.17)	61	MP-742-61S
		Receptacle protective dustcap to suit MP-6216	36.9 (1.45)	13.13 (0.52)	127 (4.99)	-	39	MP-742-39L
			43.14 (1.70)	14.15 (0.56)	127 (4.99)	-	61	MP-742-61L
		Plug protective dustcap to suit MP-6212	31.7 (1.25)	15.9 (0.62)	127 (4.99)	4.40 (0.17)	39	MP-738-39S
			38.05 (1.50)	16.70 (0.66)	127 (4.99)	4.40 (0.17)	61	MP-738-61S
		Receptacle protective dustcap to suit MP-6211	36.9 (1.45)	13.13 (0.52)	127 (4.99)	-	39	MP-738-39L
			43.14 (1.70)	14.15 (0.56)	127 (4.99)	-	61	MP-738-61L

STANDARD DATA MP-62 SERIES / MP - 65 SERIES

		VALUE	
GENERAL CHARACTERISTICS	Number of contacts	39	61
	Number of channels	12	20
	Termination	Solder	
	Wire Gauge - Stranded Wire	37 x 24AWG-20AWG 2 x 20AWG-16AWG	24AWG-20AWG
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU	
ELECTRICAL CHARACTERISTICS	Operating Voltage at Sea level - DC	600V*	
	Operating Voltage at Sea level - AC	600V*	
	Test Voltage AC RMS	1500V	
	Current Carrying Capacity	37 x 7.5A 2 x 13A	7.5A
	Insulation Resistance	5000MΩ	
CLIMATIC CHARACTERISTICS	Protection Class	IP67 (when mated)	
	Operating Temperature	-55°C to +125°C (-67°F to +257°F)	
MECHANICAL CHARACTERISTICS	Cable Retention	PG Gland / NPT Thread	
	Mechanical Operations	500 mating cycles (minimum)	
MATERIALS	Connector / Shell Finish	Aluminium Alloy / Black	
	Insert	Neoprene	
	Male pin contact machined - Plating	Brass / Gold plated	
	Female socket contact machined - Plating	Brass / Gold plated	
CLAMPING CHARACTERISTICS	PG Gland	16	21
	Cable Clamping range mm (inches)	9-14 (0.35"-0.55")	13-18 (0.51"-0.70")

*Not suitable for domestic applications above 50V

Rev 3 - 03/2013




146 SERIES RECTANGULAR CONNECTORS

Amphenol Tuchel C146 series rectangular connectors feature modular components ensuring a vast range of different features and benefits for the end user. The zinc diecast aluminum housings are finished in a durable powder coat and available in either top or side entry. Connector coupling is achieved via a positive locking lever ensuring a positive rapid connection. The C146 series is suitable for general-purpose audio and lighting applications and is completely intermateable with all competitor connectors.

FIBRE OPTIC











Amphenol has over 25 years experience in fibre optics dating back to their development of the first industry standard connector, the SMA. Today we can offer a complete range of products including Hybrid Fibre optic connectors for HDTV broadcast cameras SMPTE 304M compliant and ruggedised connectors and cable assemblies for indoor or outdoor applications.



Accessories

- Colour coded boots(backshells) and rings to assist in cable identification.
- In-line adaptors. Pre-wired for convenience.
- Termination tool for fast assembly of cable connectors.
- Mounting hardware.
- Metal boots(backshells) for rugged environments.

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		XLR 3 pole male to 3 pole male adapter, Pre wired, Metal Shell	Nickel Finish	AC3M3MW	
			Black Finish	AC3M3MBW	
		XLR 3 pole female to 3 pole female adapter, Pre wired, Metal Shell	Nickel Finish	AC3F3FW	
			Black Finish	AC3F3FBW	
		XLR 3 pole female to 3 pole male adapter, Pre wired, Metal Shell	Nickel Finish	AC3F3MW	
			Black Finish	AC3F3MBW	
		XLR 3 pole female to 5 pole male adapter, Pre wired, Metal Shell	Nickel Finish	AC3F5MW	
		XLR 3 pole male to 5 pole female adapter, Pre wired, Metal Shell	Nickel Finish	AC3M5FW	
		XLR 5 pole male to 5 pole male adapter, Pre wired, Metal Shell	Nickel Finish	AC5M5MW	
		XLR D shell adapter, 3 pole male to 3 pole male, Pre-wired	Not Applicable	AC3M3MDW	
		XLR D shell adapter, 3 pole female to 3 pole female, Pre-wired	Not Applicable	AC3F3FDW	

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
		Dimensions: 29 (1.14), 75 (2.95), 34 (1.34)	XLR D shell adapter, 5 pole male to 5 pole male, Pre-wired	Not Applicable	AC5M5MDW
		Dimensions: 29 (1.14), 75 (2.95), 34 (1.34)	XLR D shell adapter, 5 pole female to 5 pole female, Pre-wired	Not Applicable	AC5F5FDW
		Dimensions: 29 (1.14), 75 (2.95), 34 (1.34)	SP D shell adapter, SP-2 to SP-2, Pre-wired	Not Applicable	SP2F2FDW
		Dimensions: 29 (1.14), 75 (2.95), 34 (1.34)	SP D shell adapter, SP-4 to SP-4, Pre-wired	Not Applicable	SP4F4FDW
		Dimensions: 29 (1.14), 75 (2.95), 34 (1.34)	BNC D shell adapter, Jack to Jack, Pre-wired	Not Applicable	ACBNCJJDW
		Dimensions: 29 (1.14), 75 (2.95), 19 (0.75), 34 (1.34)	D shell adapter without connectors	Not Applicable	AC-D-ADAPTER
		Dimensions: 18.3 (0.720"), 12.5 (0.492"), 10.2 (0.401"), 7.2 (0.283"), 5.5 (0.216"), 4.4 (0.173"), 3.2 (0.126"), 2.2 (0.087"), 1.2 (0.047"), 0.8 (0.031")	Termination Tool	For AC Series Cable Connectors	T2860
		Dimensions: 22.0 (0.87"), 7.0 (0.276"), 4.4 (0.173"), 2.2 (0.087"), 1.2 (0.047"), 0.8 (0.031"), 0.5 (0.019")	Termination Tool	For AX Series cable connectors	T2890
		Dimensions: Ø5.6 (0.220"), 2.0 (0.077"), 7.8 (0.307")	A Type / C Type Connector Mounting, Self-Tapping Screw	2.9 x 1.06 Tri-rondulear	52500014-734
		Dimensions: Ø4.50 (0.177"), 17 (0.67"), 8.0 (0.317"), M2.5 x 0.45	B Type / XLRnet Connector Mounting, Self-Tapping Screw	M2.5	52500005-732

Accessories

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			AX Series Coloured Boot	Brown Red Orange Yellow Green Blue Violet Grey White Black	AX-BOOT-1 AX-BOOT-2 AX-BOOT-3 AX-BOOT-4 AX-BOOT-5 AX-BOOT-6 AX-BOOT-7 AX-BOOT-8 AX-BOOT-9 AX-BOOT
			AX Series Sleeve for Custom Print Note: Custom printed numbers available (Please contact us)	Black Brown Red Orange Yellow Green Blue Violet Grey White	AX-MARK0 AX-MARK1 AX-MARK2 AX-MARK3 AX-MARK4 AX-MARK5 AX-MARK6 AX-MARK7 AX-MARK8 AX-MARK9
			AC Coloured Boot / Backshell Note: Number Identification optional. (Please contact us.)	Brown Red Orange Yellow Green Blue Violet Grey White	AC-NUT-BRN AC-NUT-RED AC-NUT-ORG AC-NUT-YEL AC-NUT-GRN AC-NUT-BLU AC-NUT-VIO AC-NUT-GRY AC-NUT-WHT
			Coloured Grommets to suit AC Series, T Series and Musician range	Brown Red Orange Yellow Green Blue Violet Grey White	AC-GROMMET-BRN AC-GROMMET-RED AC-GROMMET-ORG AC-GROMMET-YEL AC-GROMMET-GRN AC-GROMMET-BLU AC-GROMMET-VIO AC-GROMMET-GRY AC-GROMMET-WHT


NOTE: All accessories comply with EU RoHS 2 Directive 2011/65/EU

NOTE: Please do not refer to this printed catalogue as a colour reference. For exact colours contact your sales representative.

PRODUCT - FIGURE	DRAWING	Dimensions in mm (inches)	DESCRIPTION	VARIATIONS	PART NUMBER
			AC Coloured Identification Rings – Plain and Numbered Note: Custom number identification optional. (Please contact us.)	Brown Red Orange Yellow Green Blue Violet Grey White Red #1-24 Yellow #1-24 Blue #1-24 Red #1-48 Yellow #1-48 Blue #1-48	AC-RING-BRN AC-RING-RED AC-RING-ORG AC-RING-YEL AC-RING-GRN AC-RING-BLU AC-RING-VIO AC-RING-GRY AC-RING-WHT AC-RING-RED-PK1 AC-RING-YEL-PK1 AC-RING-BLU-PK1 AC-RING-RED-PK2 AC-RING-YEL-PK2 AC-RING-BLU-PK2
			AC Metal Boot / Backshell, Black Finish	Not Applicable	AC-NUT-METAL
			AC Thermoplastic Boot / Backshell. Suitable for use with 8.5mm (0.33") O.D. cable.	Not Applicable	AC-NUT-J-BLK
			M3 threaded metal plate to suit D-type chassis connectors	Nickel Finish	52590060-300
			M3 Screw to suit 52590060-300 M3 x 0.5	Nickel Finish Matt Black	52500016-300 52500016-400

Connector Wiring Information

XLR (Microphone / Patch Cables)




The standard XLR 3 contact pin outs are as shown above for a balanced lead. In such a configuration audio "Hot" (pin 2) is the in-phase connection whilst audio "Cold" (pin 3) is the out-of-phase connection. For an unbalanced lead however, you may connect pin 1 to either pin 2 or pin 3, but not both. In such a configuration the remaining pin is used for the audio signal.


When terminating the cable shielding to pin 1 it is suggested that the shield be only grounded at one end of the cable to avoid inducing "hum". Pin 1 is a leading contact that engages at interconnection, before pin 2 or pin 3.

1/4" Phono (6.35mm) (Standard Applications)


MICROPHONE CABLE - BALANCED




MICROPHONE CABLE - UNBALANCED



INSTRUMENT / LINE CABLE (MONO)



INSTRUMENT / LINE CABLE (STEREO)



Connector Wiring Information

MP Series


MP-41 Series

4 Ch –13 pin

Ch	+	-	G
1	B	C	E
2	F	K	H
3	J	D	A
4	N	M	G

General

Ground




MP-41 Series

6 Ch – 19 pin

Ch	+	-	G
1	L	M	U
2	A	N	B
3	K	J	T
4	V	P	C
5	H	S	G
6	R	D	E

General

Ground




MP-41 Series

8 Ch – 25 pin

Ch	+	-	G
1	A	E	F
2	G	C	B
3	D	H	J
4	M	L	K
5	Q	P	N
6	W	S	R
7	T	X	Y
8	Z	V	U

General

Ground




MP-41 Series

12 Ch – 37 pin

Ch	+	-	G
1	E	F	A
2	B	C	G
3	H	J	D
4	S	T	K
5	L	M	U
6	V	W	N
7	P	R	X
8	a	b	g
9	c	d	j
10	e	f	m
11	n	p	h
12	r	s	k

General

Ground




MP-41 Series

16 Ch – 54 pin

Ch	+	-	G
1	W	f	r
2	J	R	a
3	k	v	AC
4	E	M	V
5	e	q	y
6	B	H	P
7	Z	j	u
8	D	L	U
9	d	p	x
10	A	G	O
11	Y	h	t
12	C	K	T
13	c	n	w
14	F	N	X
15	g	s	AB
16	S	b	m

General

Ground




MP-41 Series

28 Ch – 85 pin

Ch	+	-	G
1	A	B	C
2	E	F	H
3	J	K	L
4	N	P	R
5	S	T	U
6	X	Y	Z
7	a	b	c
8	d	f	g
9	h	i	j
10	k	m	n
11	p	q	r
12	t	u	v
13	w	x	y
14	z	AA	AB
15	AC	AD	AE
16	AF	AH	AJ
17	AK	AL	AM
18	AP	AR	AS
19	AT	AU	AV
20	AW	AX	AY
21	AZ	BA	BB
22	BC	BD	BE
23	BJ	BK	BL
24	BM	BN	BP
25	BS	BT	BU
26	BV	BR	BF
27	BH	AN	s
28	W	M	D

General

Ground



MP-41 Series

48 Ch – 150 pin

Ch	+	-	G
1	1	2	3
2	5	6	7
3	8	9	10
4	11	12	13
5	14	15	16
6	17	18	19
7	21	22	23
8	24	25	26
9	27	28	29
10	20	30	31
11	32	33	34
12	35	36	37
13	38	39	40
14	41	42	43
15	44	45	46
16	47	48	49
17	50	51	52
18	53	54	55
19	57	58	59
20	60	61	62
21	63	64	65
22	66	67	68
23	69	70	71
24	72	73	74
25	75	76	77
26	78	79	80
27	82	83	84
28	85	86	87
29	88	89	90
30	91	92	93
31	94	95	96
32	97	98	99
33	100	101	102
34	103	104	105
35	56	81	106
36	107	108	109
37	110	111	112
38	113	114	115
39	116	117	118
40	119	120	121
41	122	123	124
42	125	126	127
43	139	128	129
44	130	131	132
45	133	134	135
46	136	137	138
47	140	141	142
48	143	144	145
General			
Ground			150


MP-62 Series

MP-62 Series

Ch	+	-	G
1	p	n	q
2	W	A	X
3	N	f	P
4	L	e	M
5	J	d	K
6	G	c	H
7	E	b	F
8	D	a	Z
9	C	B	Y
10	U	j	V
11	i	h	T
12	R	g	S

General


Ground



Ch	+	-	G
1	JJ	HH	NN
2	MM	KK	PP
3	BB	AA	CC
4	s	FF	W
5	r	EE	V
6	e	D	x
7	f	E	y
8	q	DD	U
9	S	p	T
10	P	N	R
11	m	k	n
12	L	K	M
13	J	i	j
14	H	G	h
15	g	F	z
16	d	C	w
17	B	A	c
18	b	a	Z
19	v	u	Y
20	t	GG	X

General

Ground



Index

Symbols	AC3M3MDW	132	AC5F	11	AC7FPZ	20	ACJC9V BULK	43	
	AC3M3MW	132	AC5F5FDW	133	AC7M	12	ACJC9VL BULK	43	
47-10070	87	AC3M5FW	132	AC5FAH-AU-B	27	AC7MB	12	ACJC10AH BULK	40
47-10090	87	AC3MAU-PRE	26	AC5FAV-AU-B	27	AC7MB BULK	12	ACJC10AHL BULK	40
47-10110	87	AC3MAH1-AU-PRE	25	AC5FB	11	AC7MBJ	12	ACJC10AV2 BULK	40
47-10120	87	AC3MAH2-AU-PRE	25	AC5FB-AU	11	AC7M BULK	12	ACJC10AVL BULK	40
47-10150	87	AC3MAH4-SW-B	25	AC5FB BULK	11	AC7MDZ	19	ACJC10AVL BULK	40
112119	86	AC3MAH-AU-PRE	25	AC5FBJ	11	AC7MDZB	19	ACJC10H BULK	43
112133	86	AC3MAV2-AU-PRE	26	AC5F BULK	11	AC7MDZB BULK	19	ACJC10H BULK	43
112507	86	AC3MAV-AU-PRE	25	AC5FDZ	18	AC7MDZ BULK	19	ACJC10H BULK	43
112508	86	AC3MB	10	AC5FDZB	18	AC7MDZV	19	ACJC10S BULK	44
112509	86	AC3MB-AU	10	AC5FDZB-AU	18	AC7MDZVB	19	ACJC10SL BULK	44
112519	86	AC3MB BULK	10	AC5FDZB BULK	18	AC7MJ	12	ACJC10V BULK	43
112521	86	AC3MBH1-AU-B	28	AC5FDZ BULK	18	AC7MP	20	ACJC10VL BULK	43
112565	86	AC3MBH2-AU-B	28	AC5FDZV	18	AC7MPNZ	20	ACJD-BLK	121
112606	86	AC3MBH3-AU-B	28	AC5FDZVB	18	AC-BNC20A	88	ACJD-BLU	121
112950	86	AC3MBH-AU-B	28	AC5FJ	11	AC-BNC20AJ75	88	ACJD-GRN	121
112951	86	AC3MBHL-AU-B	28	AC5FPZ	20	AC-BNC20AP75	88	ACJD-RED	121
112952	86	AC3MBJ	10	AC5M	11	AC-BNC20B	88	ACJD-WHT	121
112953	86	AC3M BULK	10	AC5M5MDW	133	AC-BNC20BJ75	88	ACJD-YEL	121
112955	86	AC3MBV1-AU-B	29	AC5M5MW	132	AC-BNC20BP75	88	ACJM-HHDR	107
112956	86	AC3MBV2-AU-B	29	AC5MAH-AU-B	27	AC-BNC20M	88	ACJM-HHOP	108
112957	86	AC3MBV3-AU-B	29	AC5MAV-AU-B	27	AC-BNC20MJ75	88	ACJM-HHOP-1	108
52500005-732	133	AC3MBV-AU-B	28	AC5MB	11	AC-BNC20MP75	88	ACJM-IH	109
52500014-734	133	AC3MCP	14	AC5MB-AU	11	AC-BNC40A	88	ACJM-IHS	109
52500016-300	135	AC3MCP BULK	14	AC5MB BULK	11	AC-BNC40AJ75	88	ACJM-MC	109
52500016-400	135	AC3MDZ	17	AC5MBJ	11	AC-BNC40AP75	88	ACJM - MH	108
52590060-300	135	AC3MDZB	17	AC5M BULK	11	AC-BNC40B	88	ACJM-MHD	110
	AC3MDZB-AU	17	AC5MDZ	18	AC-BNC40BJ75	88	ACJM-MHD985	107	
A	AC3MDZB BULK	17	AC5MDZB	18	AC-BNC40BP75	88	ACJM-MHDC*	109	
	AC3MDZ BULK	17	AC5MDZB-AU	18	AC-BNC40M	88	ACJM-MHDCM	109	
AC3F	10	AC3MJ	10	AC5MDZB BULK	18	AC-BNC40MJ75	88	ACJM-MHDE	110
AC3F3FBW	132	AC3MM	10	AC5MDZ BULK	18	AC-BNC40MP75	88	ACJM-MHDEM	110
AC3F3FDW	132	AC3MMB	10	AC5MDZV	18	AC-BNC-JJ-75	87	ACJM-MHDM	110
AC3F3FW	132	AC3MMB-AU	10	AC5MDZVB	18	AC-BNC-JJ-75B	87	ACJM-MHDR	108
AC3F3MBW	132	AC3MMB BULK	10	AC5MJ	11	AC-BNC-JJA-75T	87	ACJM-MHDRM	108
AC3F5MW	132	AC3MM BULK	10	AC5MP	20	ACBNJCJDW	133	ACJM-MHOM	108
AC3FAH1-AU-PRE	26	AC3MMCP	14	AC5MPNZ	20	AC-BNC-JS-75	87	ACJM-MHOP	108
AC3FAH2-AU-PRE	26	AC3MMCP BULK	14	AC6AF	12	AC-BNC-JS-75B	87	ACJM-MHOP-1	108
AC3FAH-AU-PRE	26	AC3MMDZ	17	AC6AFB	12	AC-BNC-LABEL	88	ACJM-MHR	109
AC3FAHL1-AU-PRE	26	AC3MMDZB	17	AC6AFB-AU	12	AC-BNC-PJ-75	87	ACJM-MHS	109
AC3FAHL2-AU-PRE	26	AC3MMDZB-AU	17	AC6AFB BULK	12	AC-BNC-PJ-75B	87	ACJM-MIV-2	110
AC3FAHL-AU-PRE	26	AC3MMDZB BULK	17	AC6AFBJ	12	AC-BNC-PJA-75T	87	ACJM-MIV-2S	110
AC3FAV1-AU-PRE	26	AC3MMDZ BULK	17	AC6AF BULK	12	AC-D-ADAPTER	133	ACJM-MN-2	110
AC3FAV2-AU-PRE	27	AC3MMDZV	17	AC6AFDZ	19	AC-GROMMET-BRN	134	ACJM-MN-2S	110
AC3FAV-AU-PRE	26	AC3MMDZVB	17	AC6AFDZB	19	AC-GROMMET-GRN	134	ACJM-MV-2	110
AC3FAVL1-AU-PRE	27	AC3MMP	20	AC6AFDZB-AU	19	AC-GROMMET-GRY	134	ACJM-MV-2S	110
AC3FAVL2-AU-PRE	27	AC3MPNZ	20	AC6AFDZB BULK	19	AC-GROMMET-ORG	134	ACJM-MV35-2	107
AC3FAVL-AU-PRE	27	AC3MP	20	AC6AFDZ BULK	19	AC-GROMMET-RED	134	ACJM-MV35-2S	107
AC3FB	10	AC3MPNZ	20	AC6AFDZV	19	AC-GROMMET-VIO	134	ACJM-MVD985-2	107
AC3FB-AU	10	AC4F	11	AC6AFDZVB	19	AC-GROMMET-WHT	134	ACJM-MVD985-2S	107
AC3FB BULK	10	AC4FB	11	AC6AFJ	12	AC-GROMMET-YEL	134	ACJM-MVS-2	111
AC3FBH1-AU-B	29	AC4FB-AU	11	AC6AFPZ	20	AC-HDMI-RR	84	ACJM-MVS-2S	111
AC3FBH2-AU-B	29	AC4FB BULK	11	AC6AM	12	AC-HDMI-RRB	84	ACJM-NH35	107
AC3FBH3-AU-B	29	AC4FBJ	11	AC6AMB	12	ACJC5H BULK	41	ACJM-NV35-2	107
AC3FBH-AU-B	29	AC4F BULK	11	AC6AMB-AU	12	ACJC5HL BULK	41	ACJM-NV35-2S	107
AC3FBHL1-AU-B	30	AC4FDZ	18	AC6AMB BULK	12	ACJC5S BULK	41	ACJM-PC	109
AC3FBHL2-AU-B	30	AC4FDZB	18	AC6AMBJ	12	ACJC5SL BULK	41	ACJM - PH	108
AC3FBHL3-AU-B	30	AC4FDZB-AU	18	AC6AM BULK	12	ACJC5V BULK	41	ACJM-PHOP	108
AC3FBHL-AU-B	29	AC4FDZB BULK	18	AC6AMDZ	19	ACJC5VL BULK	41	ACJM-PHOP-1	108
AC3FBJ	10	AC4FDZ BULK	18	AC6AMDZB	19	ACJC6AH BULK	39	ACJM-PHR	109
AC3FB BULK	10	AC4FDZV	18	AC6AMDZB-AU	19	ACJC6AHL BULK	39	ACJM-PHS	109
AC3FBV1-AU-B	30	AC4FDZVB	18	AC6AMDZB BULK	19	ACJC6AV2 BULK	39	ACJM-PVB-2	110
AC3FBV2-AU-B	30	AC4FJ	11	AC6AMDZ BULK	19	ACJC6AV2L BULK	39	ACJM-PVB-2S	110
AC3FBV3-AU-B	30	AC4FPZ	20	AC6AMDZV	19	ACJC6AV BULK	39	ACJR-BLK	120
AC3FBV-AU-B	30	AC4M	11	AC6AMDZVB	19	ACJC6AVL BULK	39	ACJR-BLU	120
AC3FBVL1-AU-B	31	AC4MAH-AU-B	27	AC6AMJ	12	ACJC6H BULK	42	ACJR-GRN	120
AC3FBVL2-AU-B	31	AC4MB	11	AC6AMP	20	ACJC6HL BULK	42	ACJR-RED	120
AC3FBVL3-AU-B	31	AC4MB-AU	11	AC6AMPNZ	20	ACJC6S BULK	42	ACJR-SBK	120
AC3FBVL-AU-B	30	AC4MB BULK	11	AC7F	12	ACJC6SL BULK	42	ACJR-SBL	120
AC3FCP	14	AC4MBJ	11	AC7FB	12	ACJC6V BULK	42	ACJR-SGR	120
AC3FCP BULK	14	AC4M BULK	11	AC7FB BULK	12	ACJC6VL BULK	42	ACJR-SRD	120
AC3FDZ	17	AC4MDZ	18	AC7FBJ	12	ACJC9AH BULK	39	ACJR-SWH	120
AC3FDZB	17	AC4MDZB	18	AC7F BULK	12	ACJC9AHL BULK	39	ACJR-SYL	120
AC3FDZB-AU	17	AC4MDZB-AU	18	AC7FDZ	19	ACJC9AV2 BULK	40	ACJR-WHT	120
AC3FDZB BULK	17	AC4MDZB BULK	18	AC7FDZB	19	ACJC9AV2L BULK	40	ACJR-YEL	120
AC3FDZ BULK	17	AC4MDZV	18	AC7FDZB BULK	19	ACJC9AVL BULK	40	ACJS-HHDR	107
AC3FJ	10	AC4MDZVB	18	AC7FDZ BULK	19	ACJC9H BULK	42	ACJS-HHOP	108
AC3FPZ	20	AC4MJ	11	AC7FDZV	19	ACJC9HL BULK	42	ACJS-HHOP-1	108
AC3M	10	AC4MP	20	AC7FDZVB	19	ACJC9S BULK	43	ACJS-IH	109
AC3MBMW	132	AC4MPNZ	20	AC7FJ	12	ACJC9SL BULK	43	ACJS-IHS	109

ACJS-MC	109	ACPM-TB-AU	102	AG6F	47	AX-MARK9	134	KM2P-AU	117
ACJS - MH	109	ACPM-TB BULK	102	AG6FCCH	47			KM2PB	117
ACJS-MHD	110	ACPM-TN	102	AG6FCE	47	B		KM2PB-AU	117
ACJS-MHD985	107	ACPM-TN-AU	102	AG6FCRV	48			KM2PB BULK	117
ACJS-MHDC*	109	ACPM-TN BULK	102	AG6FL	47	B1121A1-ND3G-4CFB-75	86	KM2P BULK	117
ACJS-MHDCM	109	ACPR-BLK	120	AG6M	47	BNC-U-LINK 75*1	87	KS3P	117
ACJS-MHDE	110	ACPR-BLU	120	AG6MCC	47			KS3P-AU	117
ACJS-MHDEM	110	ACPR-GRN	120	AG6MCCH	47			KS3PB	117
ACJS-MHDM	110	ACPR-RED	120	AP-4-11	63	E		KS3PB-AU	117
ACJS-MHDR	108	ACPR-SBK	120	AP-4-12	63			KS3PB BULK	117
ACJS-MHDRM	108	ACPR-SBL	120	AP-4-13	63	EP-3-11P	61	KS3P BULK	117
ACJS-MHOM	108	ACPR-SGR	120	AP-4-14	63	EP-3-11PB	61	KS3PC	117
ACJS-MHOP	108	ACPR-SRD	120	AP-4-21	63	EP-3-12	61	KS3PC-AU	117
ACJS-MHOP-1	108	ACPR-SWH	120	AP-4-22	63	EP-3-12B	61		
ACJS-MHR	109	ACPR-SYL	120	AP-5-11	63	EP-3-13P	62	M	
ACJS-MHS	109	ACPR-WHT	120	AP-5-12	63	EP-3-13PB	62		
ACJS-MIV-3	110	ACPR-YEL	120	AP-5-13	63	EP-3-14	62	M22520/1-01	127
ACJS-MIV-3S	110	ACPS-GB	103	AP-5-14	63	EP-3-14B	62	MP-738-39L	130
ACJS-MIV-5	110	ACPS-GB-AU	103	AP-5-21	63	EP-4-11P	61	MP-738-39S	130
ACJS-MN-3	110	ACPS-GB BULK	103	AP-5-22	63	EP-4-11PB	61	MP-738-61L	130
ACJS-MN-3S	110	ACPS-GN	103	AP-6-11	63	EP-4-12	61	MP-738-61S	130
ACJS-MN-5	110	ACPS-GN-AU	103	AP-6-12	63	EP-4-12B	61	MP-742-39L	130
ACJS-MV-3	110	ACPS-GN BULK	103	AP-6-13	63	EP-4-13P	62	MP-742-39S	130
ACJS-MV-3S	110	ACPS-KB	101	AP-6-14	63	EP-4-13PB	62	MP-742-61L	130
ACJS-MV-5	110	ACPS-KB-AU	101	AP-6-21	63	EP-4-14	62	MP-742-61S	130
ACJS-MV35-3	107	ACPS-KN	101	AP-6-22	63	EP-4-14B	62	MP-4101-13P	124
ACJS-MV35-3S	107	ACPS-KN-AU	101	AP-8-11	63	EP-5-11P	61	MP-4101-13P-C	124
ACJS-MV35-5	107	ACPS-RB	104	AP-8-12	63	EP-5-11PB	61	MP-4101-19P	124
ACJS-MVD985-3	107	ACPS-RB-AU	104	AP-8-13	63	EP-5-12	61	MP-4101-19P-C	124
ACJS-MVD985-3S	107	ACPS-RB BULK	104	AP-8-14	63	EP-5-12B	61	MP-4101-25P	124
ACJS-MVD985-5	107	ACPS-RN	104	AP-8-21	63	EP-5-13P	62	MP-4101-25P-C	124
ACJS-MVS-3	111	ACPS-RN-AU	104	AP-8-22	63	EP-5-13PB	62	MP-4101-37P	124
ACJS-MVS-3S	111	ACPS-RN BULK	104	AX3F	3	EP-5-14	62	MP-4101-37P-C	124
ACJS-MVS-5	111	ACPS-TB	102	AX3FB	3	EP-5-14B	62	MP-4101-54P	124
ACJS-NH35	107	ACPS-TB-AU	102	AX3FB-AU	3	EP-6-11P	61	MP-4101-54P-C	124
ACJS-NV35-3	107	ACPS-TB BULK	102	AX3FB BULK	3	EP-6-11PB	61	MP-4101-85P	124
ACJS-NV35-3S	107	ACPS-TN	102	AX3F BULK	3	EP-6-12	61	MP-4101-85P-C	124
ACJS-NV35-5	107	ACPS-TN-AU	102	AX3M	3	EP-6-12B	61	MP-4101-150P	124
ACJS-PC	109	ACPS-TN BULK	102	AX3MB	3	EP-6-13P	62	MP-4101-150P-C	124
ACJS - PH	109	AC-RING-BLU	135	AX3MB-AU	3	EP-6-13PB	62	MP-4102-13P	125
ACJS-PHOP	108	AC-RING-BLU-PK1	135	AX3MB BULK	3	EP-6-14	62	MP-4102-13P-C	125
ACJS-PHOP-1	108	AC-RING-BLU-PK2	135	AX3M BULK	3	EP-6-14B	62	MP-4102-19P	125
ACJS-PHR	109	AC-RING-BRN	135	AX4F	4	EP-8-11P	61	MP-4102-19P-C	125
ACJS-PHS	109	AC-RING-GRN	135	AX4FB	4	EP-8-11PB	61	MP-4102-25P	125
ACJS-PVB-3	110	AC-RING-GRY	135	AX4FB-AU	4	EP-8-12	61	MP-4102-25P-C	125
ACJS-PVB-3S	110	AC-RING-ORG	135	AX4FB BULK	4	EP-8-12B	61	MP-4102-37P	125
ACJS-PVB-5	110	AC-RING-RED	135	AX4F BULK	4	EP-8-13P	62	MP-4102-37P-C	125
AC-NUT-BLU	134	AC-RING-RED-PK1	135	AX4M	3	EP-8-13PB	62	MP-4102-54P	125
AC-NUT-BRN	134	AC-RING-RED-PK2	135	AX4MB	4	EP-8-14	62	MP-4102-54P-C	125
AC-NUT-GRN	134	AC-RING-VIO	135	AX4MB-AU	4	EP-8-14B	62	MP-4102-85P	125
AC-NUT-GRY	134	AC-RING-WHT	135	AX4MB BULK	4			MP-4102-85P-C	125
AC-NUT-J-BLK	135	AC-RING-YEL	135	AX4M BULK	3	H		MP-4102-150P	125
AC-NUT-METAL	135	AC-RING-YEL-PK1	135	AX5F	4			MP-4102-150P-C	125
AC-NUT-ORG	134	AC-RING-YEL-PK2	135	AX5FB	4	HP-3-F	66	MP-4106-13S	124
AC-NUT-RED	134	AC-USB3-AA	84	AX5FB-AU	4	HP-3-FG	66	MP-4106-13S-C	124
AC-NUT-VIO	134	AC-USB3-AAB	84	AX5FB BULK	4	HP-3-MD	66	MP-4106-19S	124
AC-NUT-WHT	134	AG3F	47	AX5F BULK	4	HP-3-MDG	66	MP-4106-19S-C	124
AC-NUT-YEL	134	AG3FCCH	47	AX5M	4	HP-3-MDW	66	MP-4106-25S	124
ACPL-CBK	120	AG3FCE	47	AX5MB	4	HP-3-CC	68	MP-4106-25S-C	124
ACPL-CBL	120	AG3FCRV	48	AX5MB-AU	4	HP-3-F	68	MP-4106-37S	124
ACPL-CGR	120	AG3FL	47	AX5MB BULK	4	HP-3-FD	68	MP-4106-37S-C	124
ACPL-CRD	120	AG3M	47	AX5M BULK	4	HP-3-FDS	68	MP-4106-54S	124
ACPL-CWH	120	AG3MCC	47	AX-BOOT	134	HP-3-M	68	MP-4106-54S-C	124
ACPL-CYL	120	AG3MCCH	47	AX-BOOT-1	134	HP-3-MD	68	MP-4106-85S	124
ACPM-GB	103	AG4F	47	AX-BOOT-2	134	HP-3-MDW	68	MP-4106-85S-C	124
ACPM-GB-AU	103	AG4FCCH	47	AX-BOOT-3	134			MP-4106-150S	124
ACPM-GB BULK	103	AG4FCE	47	AX-BOOT-4	134	J		MP-4106-150S-C	124
ACPM-GN	103	AG4FCRV	48	AX-BOOT-5	134			MP-4164-13S	125
ACPM-GN-AU	103	AG4FL	47	AX-BOOT-6	134	JM2P	95	MP-4164-13S-C	125
ACPM-GN BULK	103	AG4M	47	AX-BOOT-7	134	JM2P-AU	95	MP-4164-19S	125
ACPM-KB	101	AG4MCC	47	AX-BOOT-8	134	JM2PB	95	MP-4164-19S-C	125
ACPM-KB-AU	101	AG4MCCH	47	AX-BOOT-9	134	JM2PB-AU	95	MP-4164-25S	125
ACPM-KN	101	AG4MPCH	48	AX-MARK0	134	JM2P BULK	95	MP-4164-25S-C	125
ACPM-KN-AU	101	AG5F	47	AX-MARK1	134	JS3P	95	MP-4164-37S	125
ACPM-RB	104	AG5FCCH	47	AX-MARK2	134	JS3P-AU	95	MP-4164-37S-C	125
ACPM-RB-AU	104	AG5FCE	47	AX-MARK3	134	JS3PB	95	MP-4164-54S	125
ACPM-RB BULK	104	AG5FCRV	48	AX-MARK4	134	JS3PB-AU	95	MP-4164-54S-C	125
ACPM-RN	104	AG5FL	47	AX-MARK5	134			MP-4164-85S	125
ACPM-RN-AU	104	AG5M	47	AX-MARK6	134	K		MP-4164-85S-C	125
ACPM-RN BULK	104	AG5MCC	47	AX-MARK7	134			MP-4164-150S	125
ACPM-TB	102	AG5MCCH	47	AX-MARK8	134	KM2P	117	MP-4164-150S-C	125

Index

MP-6211-39S	129	MP-25043-150L	126	RJX8FB5VGYEB	78	RJX8MB BULK	73	SP-4-MDHT-8	55
MP-6211-39S-C	129	MP-25043-150S	126	RJX8FB5VRGB	77	RJX8M BULK	73	SP-4-MDT	54
MP-6211-61S	129	MP-108300	127	RJX8FB5VRGEB	78			SP-4-MDV	55
MP-6211-61S-C	129	MP-108400	127	RJX8FB5VRRB	77	S		SP-4-MDV-2	55
MP-6212-39S	130	MP-108500	127	RJX8FB5VRRB	78			SP-4-MDVT-8	55
MP-6212-39S-C	130	MP-108600	127	RJX8FB5VRYB	77	SP-2-F	52		
MP-6212-61S	130	MP-EXT-16/18	127	RJX8FB5VRYEB	78	SP2F2FDW	133	T	
MP-6212-61S-C	130	MP-GUIDE-16	127	RJX8FB5VUUB	77	SP-2-FB	52		
MP-6216-39P	129	MP-GUIDE-18	127	RJX8FB5VUEB	78	SP-2-FBG	52	T2860	133
MP-6216-39P-C	129	MP-INS-16	127	RJX8FB6HB	76	SP-2-FBL	52	T2890	133
MP-6216-61P	129	MP-INS-18	127	RJX8FB6HEB	76	SP-2-FBS	52	TH29-1	127
MP-6216-61P-C	129			RJX8FB6HGRB	76	SP-2-FBSG	52	TM1P	97
MP-6256-39P	130	Q		RJX8FB6HGREB	77	SP-2-FBSL	52	TM1P-AU	97
MP-6256-39P-C	130			RJX8FB6HGYB	76	SP-2-FG	52	TM1PB	97
MP-6256-61P	130	QM2P	99	RJX8FB6HGYEB	77	SP-2-FL	52	TM1PB-AU	97
MP-6256-61P-C	130	QM2PB-AU	99	RJX8FB6HRGB	76	SP-2-FN	52	TM1PBJ	97
MP-6511-39S	129	QS3P	99	RJX8FB6HRGEB	77	SP-2-FNG	52	TM1PJ	97
MP-6511-39S-C	129	QS3PB-AU	99	RJX8FB6HRRB	76	SP-2-FNL	52	TM1RB	97
MP-6511-61S	129			RJX8FB6HRREB	77	SP-2-FNS	52	TM1RB-AU	97
MP-6511-61S-C	129	R		RJX8FB6HRYB	76	SP-2-FNSG	52	TM1RJ	97
MP-6516-39P	129	RJD1112-0050	70	RJX8FB6HRYEB	77	SP-2-FNSL	52	TM1RJ-AU	97
MP-6516-39P-C	129	RJD1212-0050	70	RJX8FB6HUUUB	76	SP-2-FS	52	TM2P	93
MP-6516-61P	129	RJX8FA3HB	76	RJX8FB6HUUEB	77	SP-2-FSG	52	TM2P-AU	93
MP-6516-61P-C	129	RJX8FA3VB	77	RJX8FB6VB	77	SP-2-FSL	52	TM2PB	93
MP-25042-13L	125	RJX8FA5VB	77	RJX8FB6V6B	77	SP-2-MD	54	TM2PB-AU	93
MP-25042-13S	125	RJX8FA6HB	76	RJX8FB6VGRB	77	SP-2-MDH	54	TM2PB BULK	93
MP-25042-19L	125	RJX8FA6VB	77	RJX8FB6VGREB	78	SP-2-MDV	54	TM2PBJ	93
MP-25042-19S	125	RJX8FB3HB	76	RJX8FB6VGYB	77	SP-4-F	53	TM2P BULK	93
MP-25042-25L	125	RJX8FB3HEB	76	RJX8FB6VGYEB	78	SP4F4FDW	133	TM2PJ	93
MP-25042-25S	125	RJX8FB3VB	77	RJX8FB6VRGB	77	SP-4-FB	53	TM2PN	94
MP-25042-37L	125	RJX8FB3VEB	77	RJX8FB6VRGEB	78	SP-4-FBG	53	TM2PN-AU	94
MP-25042-37S	125	RJX8FB5HB	76	RJX8FB6VRRB	77	SP-4-FBL	53	TM2PN BULK	94
MP-25042-54L	125	RJX8FB5HEB	76	RJX8FB6VREB	78	SP-4-FBS	53	TM2PNJ	94
MP-25042-54S	125	RJX8FB5HGRB	76	RJX8FB6VRYB	77	SP-4-FBSG	53	TM2RBJ	94
MP-25042-85L	125	RJX8FB5HGREB	77	RJX8FB6VRYEB	78	SP-4-FBSL	53	TM2RBJ-AU	94
MP-25042-85S	125	RJX8FB5HGYB	76	RJX8FB6VUUB	77	SP-4-FG	53	TM2RBJ BULK	94
MP-25042-150L	125	RJX8FB5HGYEB	77	RJX8FB6VUEB	78	SP-4-FL	53	TM2RJ	94
MP-25042-150S	125	RJX8FB5HGRB	76	RJX8FD3HB	80	SP-4-FN	53	TM2RJ-AU	94
MP-25043-13L	126	RJX8FB5HGRB	77	RJX8FD3VB	80	SP-4-FNG	53	TS3P	93
MP-25043-13S	126	RJX8FB5HGREB	77	RJX8FD5HB	80	SP-4-FNL	53	TS3P-AU	93
MP-25043-19L	126	RJX8FB5HRRB	76	RJX8FD5I	80	SP-4-FNS	53	TS3PB	93
MP-25043-19S	126	RJX8FB5HRREB	77	RJX8FD5T	80	SP-4-FNSG	53	TS3PB-AU	93
MP-25043-25L	126	RJX8FB5HRYB	76	RJX8FD5VB	80	SP-4-FNSL	53	TS3PB BULK	93
MP-25043-25S	126	RJX8FB5HRYEB	77	RJX8FD6HB	80	SP-4-FS	53	TS3PBJ	93
MP-25043-37L	126	RJX8FB5HUUB	76	RJX8FD6I	80	SP-4-FSG	53	TS3P BULK	93
MP-25043-37S	126	RJX8FB5HUUEB	77	RJX8FD6VB	80	SP-4-FSL	53	TS3PJ	93
MP-25043-54L	126	RJX8FB5V5B	77	RJX8FD6110	80	SP-4-MC	55	TS3RBJ	94
MP-25043-54S	126	RJX8FB5VEB	77	RJX8FD6110	80	SP-4-MD	54	TS3RBJ-AU	94
MP-25043-85L	126	RJX8FB5VGRB	77	RJX8M	73	SP-4-MD-8	54	TS3RJ	94
MP-25043-85S	126	RJX8FB5VGREB	78	RJX8MB	73	SP-4-MDH	54	TS3RJ-AU	94
			77			SP-4-MDHT	55		

PRODUCT SAFETY INFORMATION

This should be read in conjunction with Data Sheet information contained in individual product brochures. Failure to observe the advice in this information sheet and the operating conditions specified in the Data Sheets could result in hazardous situations.

1. Material Content and Physical Form

Electrical connectors do not usually contain hazardous materials. They contain conducting and non-conducting materials. Shells are manufactured in metal and plastic. Insulators can be formed in either natural rubber, synthetic rubber, plastic or glass insulating materials. Contact materials vary with the type of connector and its application. They are usually manufactured from either copper alloys, nickel, alumel, chromel or steel. In special applications, other alloys may be specified.

2. Fire Characteristics and Electric Shock Hazard

There is no fire hazard when the connector is correctly wired and used within the specified parameters. Incorrect wiring or assembly of the connector or careless use of metal tools or conductive fluids, or transit damage to any of the component parts may cause electric shock or burns. Live circuits must not be broken by separating mated connectors as this may cause arcing, ionisation and burning. Heat dissipation is greater at maximum resistance in a circuit. Hot spots may occur when resistance is raised locally by damage, e.g. cracked or deformed contacts, or broken strands of wire. Local overheating may also result from the use of the incorrect application tools or from poor quality soldering.

Overheating may occur if the ratings in the Data Sheets are exceeded and can cause breakdown of insulation and hence electric shock.

If heating is allowed to continue it intensifies by further increasing the local resistance through loss of temper or spring contact, formation of oxide film on contacts and wires, and leakage currents through carbonisation of insulation and tracking points. Fire can then result in the presence of combustible materials and this may release noxious fumes. Overheating may not be visually apparent. Burns may result from touching overheated components.

3. Handling

Care must be taken to avoid damage to any component parts of electrical connectors during installation and use. Although there are normally no sharp edges, care must be taken when handling certain components to avoid injury to fingers. Electrical connectors may be damaged in transit to customers, and damage may result in creation of hazards. Products should therefore be examined prior to installation/use and rejected if found to be damaged.

4. Disposal

Incineration of certain materials may release noxious or even toxic fumes.

5. Application

Connectors with exposed contacts should not be selected for use on the current supply side of an electrical circuit, because an electric shock could result from touching exposed contacts of an unmated connector. Voltages in excess of 30 V.A.C. or 42.5

V.D.C. are potentially hazardous and care should be taken to ensure that such voltages cannot be transmitted in any way to exposed metal parts of the connector body. The connector and wiring should be checked, before making live, to have no damage to metal parts or insulators, no solder blobs, loose strands, conducting lubricants, swarf, or any other undesired conducting particles. Circuit resistance and continuity check should be made to make certain that there are no low resistance joints or spurious conducting paths. Always use the correct application tools as specified in the Data Sheets. Do not permit untrained personnel to wire, assemble or tamper with connectors. For operation voltage please see appropriate national regulations.

Important General Information

A) Air and creepage paths / Operating voltage.

The admissible operating voltages depend on the individual applications and the valid national and other applicable safety regulations. For this reason the air and creepage path data are only reference values. Observe reduction of air and creepage paths due to PC board and/or harnessing.

B) Other important information

Amphenol Australia Pty Ltd continuously endeavours to improve its products. Therefore, products may deviate from the description, technical data and shape as shown in product brochures.

C) Assembly instructions

If applicable, special assembly instructions have been included in or on the connector packaging. See also separate instructions in product brochures.

DISTRIBUTED BY

International Headquarters

Amphenol Australia Pty Ltd

22 Industry Blvd.
Carrum Downs VIC 3201 Australia
Phone: +61 3 8796 8888
Email: info@amphenol.com.au

Europe

Amphenol Audio Representative Office

August-Haeusser – Str. 10
74080 Heilbronn Germany
Phone: +49 71 31 9 29 0
Email: industrial@amphenol.de

North America

Amphenol Audio Representative Office

44724 Morley Drive
Clinton Township, MI, USA 48036
Phone: +1 800 394 7732 or +1 586 913 8650
Email: sales@amphenolaudio.com

Asia Pacific

Amphenol Australia (China Operations)

3rd floor, Building 9 Shan Cheng Industrial Zone,
Zhou Shi Road, Shi Yan Street, Bao An District,
Shen Zhen, China 518108
Phone: (+86) 755 8173 8000
Email: apcd@amphenol.com.au

www.amphenolaudio.com.au

© 2018 Amphenol Australia Pty Ltd

Subject to all applicable laws and regulations Amphenol Australia Pty Ltd reserves the right to change specifications of any product, system or service contained in this brochure without liability.

28/02/2018

Catalogue Part Number: CAT-AUDIO-01