



## **Pressure sensors**

Barometric pressure transmitters for SMT

**Series/Type:** ASB series

**Ordering code:**

Date: 2011-05-02


Version: 2.2

**Preliminary data**
**Description**

- Pressure sensor transmitters based on piezoresistive silicon pressure dies
- On board compensation circuit for non-linearity and temperature error
- Miniaturized SMD hybrid package (4.3mm x 4.3mm x 2.4mm)

**Features**

- Analog ratiometric interface with adjustable output limits (clipping) or digital 14 bit I<sup>2</sup>C interface
- Diagnosis functions like loss of Vdd/Vss, bridge connections and short cuts
- High immunity against electromagnetic influences
- Plastic free surface mount technology for reflow soldering
- Conforming to RoHS Directive


**Options**

- Other output characteristics and / or rated pressure ranges upon request

**Table of Contents**

1. Technical Data .....	3
2. Analog Output (VR/V1) .....	4
3. Digital Output – I <sup>2</sup> C (D5) .....	5
4. Total Error (Temperature Error Multiplier) .....	9
5. Board Layout (Recommendation) .....	9
6. Reliability Testing .....	10
7. Product Key .....	11
8. Ordering Codes .....	11
9. Packaging.....	12
10. Reflow Soldering .....	13
Symbols and terms.....	14
Cautions and warnings .....	15

**Preliminary data**
**1. Technical Data**
**Absolute maximum ratings**




Parameter	Symbol	Conditions	Min.	Max.	Unit
<b>Temperature ranges</b>					
Storage temperature range	$T_{st}$	<sup>1)</sup>	-40	+125	°C
Operating temperature range	$T_{op}$	TN <sup>2)</sup>	-40	+85	°C
		TE <sup>2)</sup>	-40	+125	°C
Compensated temperature range	$T_c$	<sup>3),4)</sup>	0	+70	°C
Soldering temperature	$T_{solder}$			+260	°C
<b>Pressure ranges</b>					
Rated pressure	$p_r$	absolute	0.2 (2.9)	1.2 (17.4)	bar (psi)
Overpressure	$p_{ov}$	<sup>4), 5)</sup>	2		$p_r$
Burst pressure			3		$p_r$
<b>Supply voltage /-current</b>					
Supply voltage	$V_{supply}$	<sup>6)</sup>	2.7	5.5	V
Supply current	$I_{supply}$	$I_{out} = 0$		2.5	mA
Signal output current	$I_{out}$	<sup>7)</sup>		2	mA
Start up time	$t_{STA}$	<sup>8)</sup>		10	ms

## 2. Analog Output (VR/V1)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
<b>Analog output signal (VR/V1) @ <math>T_{op} = 25^\circ\text{C}</math>, <math>V_{\text{supply}} = 5\text{ V}</math>, <math>I_{\text{out}} &lt; 0.1\text{ mA}</math></b>						
Offset (at $p_{r,\text{min}}$ )	$V_{\text{out},0}$	VR: ratiometric <sup>9)</sup>		10		% $V_{\text{CC}}$
		V1: 0 ... 1000 mV <sup>9)</sup>	0	2.5		mV
Signal span (Full Scale)	$V_{\text{FS}}$	VR: ratiometric <sup>10)</sup>		80		% $V_{\text{CC}}$
		V1: 0 ... 1000 mV <sup>10)</sup>		1000		mV
Full scale output at $p_{r,\text{max}}$	$V_{\text{out},0} + V_{\text{FS}}$	VR: ratiometric <sup>9), 10)</sup>		90		% $V_{\text{CC}}$
Diagnostic levels		enabled upon request		disabled		
Non-linearity	$L$	Simple output <sup>10), 11)</sup>		$\pm 0.1$		% FS
Response time	$t_{10-90}$	<sup>12)</sup>		2		ms
Resolution	$r_{\text{OUT}}$	<sup>13)</sup>		12		bit
Basic accuracy		$T_{op}: 0 \dots 70^\circ\text{C}$		$\pm 2$	$\pm 3$	% FS

**Terminal assignment**

Pin	Symbol	Signal
1	-	not connected
2	GND	Ground
3	$V_{\text{out}}$	Output signal
4	$V_{\text{supply}}$	Supply voltage

**Dimensional drawings**

**Output Characteristics**

**Application Circuit**

**Conversion Formula**

$$\text{VR: } p_{\text{meas}} = \frac{(p_{r,\text{max}} - p_{r,\text{min}})}{V_{\text{FS}}} \cdot \left( \frac{V_{\text{meas}}}{V_{\text{Supply}}} - V_{\text{out},\text{min}} \right) + p_{r,\text{min}}$$

$$\text{V1: } p_{\text{meas}} = \frac{(p_{r,\text{max}} - p_{r,\text{min}})}{V_{\text{FS}}} \cdot (V_{\text{meas}} - V_{\text{out},\text{min}}) + p_{r,\text{min}}$$


### 3. Digital Output – I<sup>2</sup>C (D5)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
<b>Digital output pressure signal (D5) @ T<sub>op</sub> = 25 °C, V<sub>supply</sub> = 5 V, I<sub>out</sub> &lt; 0.1 mA</b>						
Offset (at p <sub>r,min</sub> )	D <sup>P</sup> <sub>out,0</sub>	D5: I <sup>2</sup> C - 14bit		1638		digits
Signal span (Full Scale)	D <sup>P</sup> <sub>FS</sub>	D5: I <sup>2</sup> C - 14bit		13107		digits
Full scale output at p <sub>r,max</sub>	D <sup>P</sup> <sub>out,0</sub> + D <sup>P</sup> <sub>FS</sub>	D5: I <sup>2</sup> C - 14bit		14745		digits
Non-linearity	L	Simple output <sup>10), 11)</sup>		±0.1		% FS
Response time	t <sub>10-90</sub>	<sup>12)</sup>		2		ms
Basic accuracy				± 2	± 3	% FS
<b>Digital output temperature signal (D5) @ p<sub>r,min</sub>, V<sub>supply</sub> = 5 V, I<sub>out</sub> &lt; 0.1 mA</b>						
Offset (at 0 °C)	D <sup>T</sup> <sub>out,0</sub>	D5: I <sup>2</sup> C - 11bit		512		digits
Sensitivity	D <sup>T</sup> <sub>S</sub>	D5: I <sup>2</sup> C - 11bit		10.235		digits/K
Basic accuracy		T <sub>op</sub> : 0 ... 70 °C		± 2	± 3	°C

<b>Configuration, digital interface</b>						
System clock frequency				10 <sup>6</sup>		Hz
Update period				1.5		ms
I <sup>2</sup> C address				0x28		hex
Sensor connection check				active		
Sensor short check				active		
Sleep Mode				active		

**Terminal assignment**
**Dimensional drawings**

Pin	Symbol	Signal
1	GND	Ground
2	V <sub>supply</sub>	Supply
3	SDA	Serial Data
4	SCL	Serial Clock



## Pressure sensors


### Barometric pressure transmitters for SMT

**ASB series**


#### Preliminary data

##### Output Characteristics


pressure:



temperature:



##### Application Circuit



##### Conversion Formula



pressure:  $p_{meas} = \frac{(p_{r,max} - p_{r,min})}{D_{FS}^p} \cdot (D_{meas}^p - D_{out,min}^p) + p_{r,min}$

temperature:  $T_{meas} [^{\circ}C] = \frac{D_{meas}^T - 512}{10.235}$

#### Sleep Mode

After the command window, the sensor's signal processor will power down and fall into sleep mode. To wake up the sensor's signal processor the master must send a Read\_MR (measurement request operation) command or a Write\_MR (reduced measurement request operation) command.


After completion of the measurement cycle the data can be transmitted via a data fetch operation and the sensor's signal processor will power down and fall into sleep mode again.



#### Preliminary data


##### I<sup>2</sup>C measurement request operation (Read\_MR)

The Read\_MR command forces the sensor to wake up from sleep mode and to perform a complete measurement and calculation cycle. The Read\_MR command is only containing the slave address and the READ bit (HIGH state) both sent by the master. After the sensor responds with the slave ACK, the master must create a stop condition.




##### I<sup>2</sup>C reduced measurement request operation (Write\_MR)

The Write\_MR command forces the sensor to wake up from sleep mode and to perform only a pressure measurement and calculation cycle. (Please Note: Obsolete, maybe invalid, temperature data is used to calculate the pressure data. For using updated temperature data, please use the I<sup>2</sup>C measurement request operation – Read\_MR) The Write\_MR command is faster then the Read\_MR command, but perhaps results are insufficient. The Write\_MR command is only containing the slave address and the WRITE bit (LOW state) both sent by the master. After the sensor responds with the slave ACK, the master must create a stop condition.



#### I<sup>2</sup>C data fetch operations

For data fetch operations, the I<sup>2</sup>C master must start with the 7bit slave address (0x28h) with the 8<sup>th</sup> bit high (READ request). The sensor (I<sup>2</sup>C slave node) sends an acknowledgement (ACK) indicating success. The sensor sends up to 4 data bytes depending on the master's NACK.




#### Preliminary data

##### I<sup>2</sup>C Status Bits

The sensor offers a full suite of diagnostic features to ensure robust system operation. The diagnostic states are indicated by a transmission of the status of the 2 MSBs of the pressure high byte data.

Status Bits	Definition
00	Normal operation, good (fresh) data packet
01	Reserved
10	Stale data: Data that has already been fetched since the last measurement cycle
11	Internal error occurred

#### I<sup>2</sup>C data fetch example





#### I<sup>2</sup>C protocol limitations

Please note:

- Sending a start-stop condition without any transition on the CLK line (no clock pulses in between) creates a communication error for the next communication, even if the next start condition is correct and the clock pulse is applied. An additional start condition must be sent, which results in restoration of proper communication.
- The restart condition – a falling SDA edge during data transmission when the CLK line is still high – creates the same situation. The next communication fails, and an additional start condition must be sent for correct communication.
- A falling SDA edge is not allowed between the start condition and the first rising SCL edge. If using an I<sup>2</sup>C address with the first bit 0, SDA must be held low from the start condition through the first bit.
- If a data fetch is performed before or during the first measurement after power-on reset (POR), the fetched data is invalid, even though the status bits report it as “valid” or “stale”.

**Preliminary data**
**4. Total Error (Temperature Error Multiplier)**

The output accuracy over the whole temperature range can be calculated by multiplying the basic accuracy with a temperature dependant factor as shown in the following graph.


**5. Board Layout (Recommendation)**


**Preliminary data**
**6. Reliability Testing**
**Performed Tests:**

Test	Standard	Test conditions
Early Life Failure Rate (ELFR)	following to AEC-Q100-008	<ul style="list-style-type: none"> <li>- Storage for 24h at +105 °C</li> </ul>
Preconditioning (PC)	following to AEC-Q100, JEDEC J-STD-020 and JEDEC JESD22-A113	<ul style="list-style-type: none"> <li>- Parts from ELFR test</li> <li>- 5 cycles shipping conditions (-40 °C to +60 °C)</li> <li>- Bake 24h at +125 °C</li> <li>- Soak 192h at +30 °C and 60% r.h.</li> <li>- Apply 3 reflow soldering cycles</li> </ul>
High Temperature Storage Life (HTSL)	following to AEC-Q100 and JEDEC JESD22-A103	<ul style="list-style-type: none"> <li>- Parts from PC test</li> <li>- Storage for 1000h at +125 °C</li> <li>- Unpowered</li> </ul>
High Temperature Operating Life (HTOL)	following to AEC-Q100 and JEDEC JESD22-A108	<ul style="list-style-type: none"> <li>- Parts from ELFR test</li> <li>- Operating for 408h at +105 °C</li> <li>- Powered with <math>V_{\text{supply}}</math> at +5VDC</li> </ul>
Variable Frequency Vibration Test (VFV)	following to AEC-Q100 and JEDEC JESD22-B103	<ul style="list-style-type: none"> <li>- Parts from ELFR test</li> <li>- Logarithmic sweep from 20Hz to 2KHz to 20Hz within 4min</li> <li>- Max. acceleration at 50g</li> <li>- 4 x 4min in each orientation (total 144min)</li> </ul>
Mechanical Shock Test (MS)	following to AEC-Q100 and JEDEC JESD22-B104	<ul style="list-style-type: none"> <li>- Parts from ELFR test</li> <li>- 5 pulses with 1,500g peak acceleration in positive vertical direction</li> <li>- Peak duration 0.5ms</li> </ul>
Pressure Cycle Test	(Internal standard)	<ul style="list-style-type: none"> <li>- Parts from ELFR test</li> <li>- 1,000,000 pressure cycles between minimum rated pressure (<math>p_{r,\min}</math>) and overpressure (<math>p_{ov}</math>)</li> <li>- Test performed at room temperature</li> </ul>

**Test Criterion:**

All sensors have to be within the specified tolerances before and after each test listed below.

**Preliminary data**
**7. Product Key**
**ASB 1.200 VR TN H19 KXXXX**

				Customer Specific Index	Optional, reserved	
				Pressure Feed	Reserved	
				Operating Temperature Range	TN TE	Normal Temperature Range (-40 °C ... +85 °C) Extended Temperature Range (-40 °C ... +125 °C)
				Output signal	VR V1 D5	0.1 ... 0.9 V/V (ratiometrical) 0 ... 1 V I <sup>2</sup> C (pressure 14 bit / temperature 11 bit)
				Rated pressure range	1.200 bar (17.4 psi)	
				Measuring type	B	Barometric (Absolute)
				Sensor type	AS	Advanced Surface Mount Technology

**8. Ordering Codes**

Rated Pressure <b>p<sub>r</sub> [bar] ([psi])</b>	Normal Temperature Range			Extended Temperature Range		
	Ratiometric	0..1000 mV	I <sup>2</sup> C (14 bit)	Ratiometric	0..1000 mV	I <sup>2</sup> C (14 bit)
1.200 (17.4)	n/n (ASB 1.200 VR TN H19)	n/n (ASB 1.200 V1 TN H19)	n/n (ASB 1.200 D5 TN H19)	n/n (ASB 1.200 VR TE H19)	n/n (ASB 1.200 V1 TE H19)	n/n (ASB 1.200 D5 TE H19)

Preliminary data


## **9. Packaging**

Packaging for samples is separated in ESD bags and ESD box.

(Tape and reel packaging acc. to IEC 60286-3 will be defined.)

**Preliminary data**
**10. Reflow soldering**

Recommended temperature characteristic for reflow soldering following JEDEC J-STD-020D



Profile feature		Sn-Pb eutectic assembly	Pb-free assembly
Preheat and soak			
- Temperature min	T <sub>smin</sub>	100 °C	150 °C
- Temperature max	T <sub>smax</sub>	150 °C	200 °C
- Time	t <sub>smin</sub> to t <sub>smax</sub>	60 ... 120 s	60 ... 180 s
Average ramp-up rate	T <sub>smax</sub> to T <sub>p</sub>	3 °C/s max.	3 °C/s max.
Liquidous temperature	T <sub>L</sub>	183 °C	217 °C
Time at liquidous	t <sub>L</sub>	60 ... 150 s	60 ... 150 s
Peak package body temperature	T <sub>p</sub> <sup>A)</sup>	220 °C ... 235 °C <sup>B)</sup>	245 °C ... 260 °C <sup>B)</sup>
Time (t <sub>p</sub> ) <sup>3)</sup> within 5 °C of specified classification temperature (T <sub>c</sub> )		20 s <sup>C)</sup>	30 s <sup>C)</sup>
Average ramp-down rate	T <sub>p</sub> to T <sub>smax</sub>	6 °C/s max.	6 °C/s max.
Time 25 °C to peak temperature		maximum 6 min	maximum 8 min

A) Tolerance for peak profile temperature (T<sub>p</sub>) is defined as a supplier minimum and a user maximum.

B) Depending on package thickness. For details please refer to JEDEC J-STD-020D.

C) Tolerance for time at peak profile temperature (t<sub>p</sub>) is defined as a supplier minimum and a user maximum.

**Preliminary data**
**Symbols and terms**
**1) Storage temperature range  $T_{st}$** 

A storage of the pressure sensor within the temperature range  $T_{st,min}$  up to  $T_{st,max}$  and without applied pressure and supply voltage will not affect the performance of the pressure sensor.

**2) Operating temperature range  $T_{op}$** 

An operation of the pressure sensor within the temperature range  $T_{op,min}$  up to  $T_{op,max}$  will not affect the performance of the pressure sensor.

**3) Compensated temperature range  $T_c$** 

While operating the pressure sensor within the temperature range  $T_{c,min}$  up to  $T_{c,max}$ , the deviation of the output signal from the values at 25 °C will not exceed the temperature coefficients. Out of the compensated temperature range, the deviations may increase.

**4) Rated pressure  $p_r$** 

Within the rated pressure range 0 up to  $p_{r,max}$  the signal output characteristic corresponds to this specification.

**5) Overpressure  $p_{ov}$** 

Pressure cycles within the pressure range 0 up to  $p_{ov}$  will not affect the performance of the pressure sensor.

**6) Supply voltage  $V_{supply}$** 

$V_{supply,max}$  is the maximum permissible supply voltage, which can be applied without damages.

$V_{supply,min}$  is the minimum required supply voltage, which has to be applied for normal operation.

**7) Signal output current  $I_A$** 

$I_{A,max}$  is the maximum permissible sink current of the signal output.

Exceeding (e.g. short circuit) may cause irreparable damages.

**8) Start up time  $t_{STA}$** 

Time between the start up of the normal operation after power on and the first valid output signal.

**9) Offset  $V_{out,0}$** 

The offset  $V_{out,0}$  is the signal output  $V_A(p = 0)$  at zero pressure.

**10) Signal span (Full Scale)**

Simple output:  $V_{FS} = FS = V_{out}(p_{r,max}) - V_{A0}$

**11) Non-linearity L (including pressure hysteresis)**

The non-linearity is the deviation of the real sensor characteristic  $V_A = f(p)$  from the ideal straight line.

It can be approximated by a polynomial of second order, with the maximum at  $p_x = p_r / 2$ .

The equation to calculate the non-linearity is:

$$L = \frac{V_{out}(p_x) - V_{out,0}}{V_{out}(p_r) - V_{out,0}} - \frac{p_x}{p_r}$$

**12) Response time  $t_{10-90}$** 

Delay between a pressure change (10 ... 90%  $p_r$ ) and the corresponding signal output change (10 ... 90% FS).

**13) Resolution  $r_{out}$** 

The resolution of the output DAC (digital/analog converter). For ratiometric output only 80% of DAC range is used.

**Preliminary data****Cautions and warnings****Storage**

The pressure sensors should be stored in their original packaging. They should not be placed in harmful environments such as corrosive gases nor exposed to heat or direct sunlight, which may cause deformations. Similar effects may result from extreme storage temperatures and climatic conditions. Avoid storing the pressure sensors in an environment where condensation may form or in a location exposed to corrosive gases, which will adversely affect their performance.

**Soldering**

The thermal capacity of the pressure sensor is normally low, so steps should be taken to minimize the effects of external heat. High temperatures may lead to damage or changes in characteristics.

A no-clean flux should normally be used. Flux removal processes are not recommended.

Avoid rapid cooling due to dipping in solvent. Note that the output signal may change if pressure is applied to the terminals during soldering.

**Operation**

Media compatibility with the pressure sensors must be ensured to prevent their failure (see page 2).

The use of other media can cause damage and malfunction.

Never use them in atmospheres containing explosive liquids or gases.

Ensure pressure equalization to the environment, if relative pressure sensors are used.

Avoid operating the pressure sensors in an environment where condensation may form or in a location exposed to corrosive gases. These environments adversely affect their performance.

If the operating pressure is not within the rated pressure range, it may change the output characteristics.

Be sure that the applicable pressure does not exceed the overpressure, it may damage the pressure sensor.

Do not exceed the maximum rated supply voltage, it may damage the pressure sensor.

Do not exceed the rated storage temperature range, it may damage the pressure sensor.

Temperature variations in both the ambient conditions and the media (liquid or gas) can affect the accuracy of the output signal from the pressure sensors. Be sure to check the operating temperature range and thermal error specification of the pressure sensors to determine their suitability for the application.

Connections must be wired in accordance with the terminal assignment specified in this publication.

Care should be taken as reversed pin connections can damage the pressure sensors or degrade their performance.

Contact between the pressure sensor terminals and metals or other materials may cause errors in the output characteristics.

This listing does not claim to be complete, but merely reflects the experience of EPCOS AG.

## Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet ([www.epcos.com/material](http://www.epcos.com/material)). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSMP, CSSP, CTVS, DSSP, MiniBlue, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at [www.epcos.com/trademarks](http://www.epcos.com/trademarks).