

BL138 Series

High Intensity Linear Backlights | Product Datasheet



ADVANCED
ILLUMINATION
An Exaktera Company

Ultra-High Power LEDs


Equipped with leading industrial grade LEDs capable of ultra-high output strobe and continuous operation

Uniformity Balancing

Designed with optional uniformity balancing every six inches, useful for linear backlight applications longer than 24" in length

Scalable Extrusion-Based Housing

Built with extrusion-based aluminum construction allowing for linear, one-dimensional scalability, while maintaining structural rigidity and durability



M6 Mounting Channels

Engineered with two M6 mounting channels on each side, allowing for highly adjustable positioning

Passive Thermal Design

Features a passively cooled finned heatsink design for optimal thermal dissipation without the need for active cooling fans

BL138 Series Description

The BL138 Series delivers a high-intensity linear backlight solution for demanding machine vision applications. It excels in high-speed web material imaging with line scan cameras and serves as a powerful general-purpose bar light when highly diffuse front illumination is required.

Equipped with ultra-high power industrial-grade LEDs, the BL138 Series can operate in both exceptionally bright strobe and continuous modes, depending on the control configuration. Its passive finned heatsink design optimizes thermal dissipation without active cooling fans. For applications exceeding 24 inches, optional uniformity balancing every six inches ensures consistent exposure across the entire active area.



High Intensity



Scalable Design



Uniformity Control Optional



RGB Available



Passively Cooled

General Information

General Specifications

Category	Specification	Detail	
Optical	Available Wavelengths	White, 455 nm, 530 nm, 625 nm, 850 nm, RGB	
	Available Lensing	No Lenses	
Electrical	Available Light Conditioning	None	
	Power Consumption Info	See Power Requirements on Page 10	
Mechanical	Cable Info	80"-0/+6" Long (2 m -0/+150 mm), 105 °C Rated, Foil Shield w/ Drain	
	Sizing Info	Length	3.26"(82.8mm) to 96.26"(2445.0mm)
		Standard Width	1.98"(50.2mm)
		Height	3.73"(94.8mm)
Material	Weight Info (Standard)	~ 1.70 lbs (~771 g) per 6" Unit Length	
	Mounting Info	M6 Mounting Nut Channel	
	Material Info	Anodized Aluminum Housing, Acrylic Window, Nickel Plated Brass Strain Relief, PVC Cable Jacket, Steel Black Oxide and Zinc Plated Steel Fasteners, Optional Silicone Sealant	
Thermal	Operating Case Temperatures	25 °C to 60 °C	
	Operating Ambient Temperatures	0 °C to 35 °C	
	Compliance	CE, RoHS, IEC 62471	
Certification	IP Rating	IP50	
	Lumen Maintenance - White Only	L70 (50,000 Hours)	

General Information - Continued

Part Number Key

Model	Emitting Length (in)	-	Peak Wavelength	Connector/Control
BL138	XX	-	XXX	XXX
BL138	06" increments from 06" to 96"		455 (royal blue)	C1
	03" model also available		530 (green)	C5
			625 (red-orange)	IC ²
			850 (IR)	24
			RGB (all colors) ¹	
			WHI (white)	

more information on page

9

5

10

Example Part Numbers:

BL13806-455C1
BL13824-625IC

¹ Not available in IC

² IC option not available with 03" model


In Stock

Lead Times

Unavailable

Build-to-Order custom products ship within one to two weeks (typical).



Configurator



Need a build-to-order custom lighting solution in 2 weeks or less? Advanced Illumination's online configurator helps you tailor our BL138 High Intensity Linear Backlight Series to your specific needs. For a guided configuration, visit our [online configurator](#).



Optical Information

Intensity Distribution




Both intensity distribution images shown above have been taken using a 12-inch white BL138 unit.

FWHM vs Working Distance



Both Full Width Half Maximum (FWHM) vs Working Distance plots shown above have been measured using a 12-inch white BL138 unit.

Intensity vs Working Distance




Linear Backlights, while typically oriented behind the object of interest, can also be used for highly diffuse front illumination at short to medium working distances. The chart to the left shows the BL138's intensity as its distance from the inspection surface changes.

Disclaimer: The measurements provided above are for approximations only and may vary depending on the method of measurement and the specific configuration being measured.


Optical Information - Continued

Continuous vs Pulsed Intensity



Under continuous operation, a 12-inch white BL138 unit will output an **illuminance of 542 klx** and an **irradiance of 1,642 W/m²** at the emitting surface. For applications that require higher output, the BL138 Series has been engineered to be overdrive strobe capable. When configured with a C1 connector, compatible with a DCS-100E or DCS-103E Controller, the BL138 is capable of outputting up-to 7.5X continuous levels when strobed. When configured with a C5 connector, compatible with AI's Pulsar 320, a BL138 can be strobed up-to 10X continuous intensity levels.

White Spectral Profile




White LED illumination is the most commonly used machine vision lighting configuration. It is often the default choice when specific features of interest do not require color-based highlighting. However, **white LEDs can vary in color temperature between different lighting families, which can impact machine vision systems**, specifically when matching white light sources.

The BL138 Series white LEDs have a relatively neutral color correlated temperature (CCT) of **5500k**.

For a more detailed look at the white spectral data, download the [csv file of the raw spectral values](#) and refer to our [Product Spectra Distribution Charts PDF](#).

Visible Spectral Profiles




Visible color illumination consists of using wavelengths between 400-700 nm to either create or eliminate contrast on an inspection subject based on differences in a features color hue. When referring to a color wheel, simply remember the following; like colors reflect and brighten surfaces; conversely, opposing colors absorb and darken surfaces. The BL138 is available in **455nm, 530nm, and 625nm** visible color configurations.

For a more detailed look at the visible color spectral data, download the [csv file of the raw spectral values](#) and refer to our [Product Spectra Distribution Charts PDF](#).

Disclaimer: The measurements provided above are for approximations only and may vary depending on the method of measurement and the specific configuration being measured.

Optical Information - Continued

Non-Visible Spectral Profiles



Near-infrared (NIR) imaging is a machine vision technique using longer wavelengths of 700-1000 nm to penetrate specific materials that are otherwise opaque to under the visible spectrum. When paired with a NIR camera, a NIR light can be ideal for applications such as fill level inspection, circuit board inspection, food safety inspection, and medical imaging.

The BL138 Series is available in an **850nm** configuration.

For a more detailed look at the NIR spectral data, download the [csv file](#) of the raw spectral values and refer to our [Product Spectra Distribution Charts PDF](#).

Photobiological Risk Factors

Group	Description	Affected Wavelengths
Exempt	No Photobiological Hazard	850 nm
Group 1	No Photobiological hazard under normal behavioral limitations	455 nm, 530 nm, 625 nm
Group 2	Does not pose a hazard due to aversion response to bright light or thermal discomfort	White

Advanced Illumination's lighting products have been tested and classified to IEC standards by accredited testing services. For more information on photobiological risk factors, please view the following PDF: <https://www.advancedillumination.com/wp-content/uploads/2019/04/IEC-040119.pdf>

Cleaning Guidelines



To clean our light's optics, it is best to only clean when necessary. Dusting is always the first step in cleaning your optics. Wiping a dusty optic is like cleaning it with sandpaper. So always dust with a canned air duster or compressed and filtered air before wiping any optic. If the dusted optic has no visible stains after you dust it, then remember: "If it's not dirty, don't clean it." Avoid wiping optics when possible.

If dusting did not clean the lens or the lens has stains, use only de-ionized water and mild dish soap with a low lint cloth designed for optics to avoid damage to the optic by any harsh chemicals.

Polarizers, beam splitters and collimated films should never be wiped with any type of cloth or solvent, only use the air dusting method to clean these types of optics.

The aluminum housing can be wiped down when dusting is not a sufficient means to thoroughly clean.

Backlight Comparison Matrix

Not finding the optical specifications you are looking for with the BL138 Series? Refer to the backlight comparison matrix below to compare and contrast Advanced Illumination's comprehensive product offering:

Attributes	Planar Backlights				Linear Backlights / High Diffusion Bar Lights				
	BL2	BX2	BT	BL245	BL313	BL138	BL168	BL128	BL193
Emitting Window Surface Intensity	86 klx	72 klx	48 klx (100 mm x 100 mm unit)	86 klx	231 klx	542 klx	567 klx	51 klx	12 klx
	249 W/m ²	229 W/m ²	137 W/m ² (100 mm x 100 mm unit)	249 W/m ²	735 W/m ²	1,642 W/m ²	1,760 W/m ²	173 W/m ²	41 W/m ²
Emitting Window Surface Edge Effect	0.681 in (17.3 mm)	0 in (0mm) (smaller models)	0 in (0mm)	0.724in (18.4mm)	0.987in (25.1mm)	0.343in (8.7mm)	0.429in (10.9mm)	0.634in (16.1mm)	1.524in (38.7mm)
100 mm Working Distance Intensity	N/A	N/A	N/A	N/A	22 klx	48 klx	50 klx	9 klx	1 klx
100 mm Working Distance FWHM					74 W/m ²	153 W/m ²	164 W/m ²	32 W/m ²	4 W/m ²
Minimum Bezel Thickness	0.465 in (11.8 mm)	1.07 in (27.2 mm)	0.380 in (9.65 mm)	0.215 in (5.46 mm)	0.125 in (3.18 mm)	0.050 in (1.27 mm)	0.050 in (1.27 mm)	0.00 in (0.00 mm)	0.065 in (1.65 mm)
Maximum Light Thickness	0.940 in (23.9 mm)	0.75 in (19.0 mm)	0.420 in (10.7 mm)	0.950 in (24.1 mm)	0.850 in (21.6 mm)	3.570 in (90.7 mm)	3.570 in (90.7 mm)	0.480 in (12.2 mm)	1.180 in (30.0 mm)
Largest Possible Emitting Window Length	46 in (1168 mm)	24 in (610 mm)	8 in (204 mm)	12 in (305 mm)	20 in (508 mm)	96 in (2438 mm)	96 in (2438 mm)	14 in (356 mm)	80 in (2032 mm)
Sizes Available	736	484	3	144	10	17	17	14	80
Visible Wavelengths Available	4	8	4	4	6	4	1	4	4
IR Wavelengths Available	1	3	1	1	2	1	0	1	1
RGB Available	No	No	No	No	No	Yes	No	No	No
Collimation Available	Yes	Yes	Yes	No	No	No	No	No	No
Polarization Available	Yes	Yes	Yes	No	No	No	No	No	No
IP Rating	IP50	IP50	IP50	IP69K Certified	IP50	IP50	IP50	IP50	IP50
Price	\$\$\$	\$\$	\$\$\$	\$\$\$\$	\$\$	\$\$\$	\$\$\$	\$\$\$	\$


To ensure consistent comparisons, all data presented above is based on 12-inch white LED models unless explicitly stated otherwise. This corresponds to 12 inches by 12 inches (300 mm x 300 mm) in length as well as width for planar backlights and 12 inches in length for linear backlights. Additionally, all measurements provided above are derived from "standard" configurations, excluding sealed models if available as optional.

If you are still not finding the optical specifications needed for your application, [inquire](#) about our semi-custom and full-custom capabilities.

Disclaimer: The measurements provided above are for approximations only and may vary depending on the method of measurement and the specific configuration being measured.


Backlight Comparison Matrix - Definitions

For definitions on the terminology used on the previous page, please refer to the table below:



Edge Effect refers to the decrease in light intensity along the outer perimeter of a backlight's emitting surface. It's characterized by the region where the intensity falls below 80% of the peak value. For linear backlights, edge effect is measured along the length of the light. We recommend users avoid this region when sizing a backlight for their application.

FWHM (Full Width Half Maximum) is a measure of the width of a light source's intensity distribution. Specifically, it defines the distance between the points on the intensity profile where the light intensity drops to 50% of its peak value. This FWHM distance is often used to determine the usable FOV (Field of View) when aiming a light at a surface for inspection.




Bezel Thickness refers to the width of the non-illuminated border or frame surrounding the light-emitting surface of a machine vision backlight. Bezel thickness is an important consideration when integrating a backlight into a tight space, as it directly affects how close you can place the light-emitting surface to an object on its side.

Light Thickness refers to the overall depth of a machine vision backlight, measured from the back of the unit to the front of the light-emitting surface. A thinner light thickness is critical in applications with limited space constraints, allowing flexible integration into tight machine vision setups.

Disclaimer: The measurements provided above are for approximations only and may vary depending on the method of measurement and the specific configuration being measured.

Mechanical Information

Installation Drawings



For full installation drawings and complete CAD models of this configuration, please visit the [downloads](#) section of the product webpage.

Sizing Chart

Part Number	Length (Inches)		Length (Millimeters)	
	Unit	Window	Unit	Window
BL13803	3.26	3.04	82.80	77.22
BL13806	6.26	6.00	159.00	152.40
BL13812	12.26	12.00	311.40	304.80
BL13818	18.26	18.00	463.80	457.20
BL13824	24.26	24.00	616.20	609.60
BL13830	30.26	30.00	768.60	762.00
BL13836	36.26	35.95	921.00	913.13
BL13842	42.26	41.95	1073.40	1065.53
BL13848	48.26	47.94	1225.80	1217.68
BL13854	54.26	53.93	1378.20	1369.82
BL13860	60.26	59.92	1530.60	1521.97
BL13866	66.26	65.91	1683.00	1674.11
BL13872	72.26	71.91	1835.40	1826.51
BL13878	78.26	77.90	1987.80	1978.66
BL13884	84.26	83.89	2140.20	2130.81
BL13890	90.26	89.88	2292.60	2282.95
BL13896	96.26	95.87	2445.00	2435.10

Electrical Information

Power Requirements

Current Required for Power Supply Sizing


Wavelengths	Configured w/ Voltage Drive (24)	Configured w/ Other Control Options (IC, C1, C5)
WHL	0.750A per 6 inches	1.000A per 6 inches
455 nm	0.750A per 6 inches	1.000A per 6 inches
530 nm	0.750A per 6 inches	1.000A per 6 inches
625 nm	0.640A per 6 inches	1.000A per 6 inches
850 nm	0.640A per 6 inches	1.000A per 6 inches
RGB	0.640A per 6 inches	1.000A per 6 inches

Note: All Advanced Illumination lights and controllers are nominally powered by 24V DC unless otherwise noted. Strobe overdriving with controller based models may require more current and voltage overhead. The values above do not include background current draw from the controller (~100 mA total)

Control Options

Controller Image	Controller Details	Connector Image
	<p>DCS Single Output Controller - Compatible with C1 Configurations PN: DCS-100E</p> <p>The DCS-100E is a compact, din-rail mounted general-purpose external controller with one C1 output connector, wired with three channels. Capable of providing single channel control or multi-channel control for RGB compatible lights.</p> <p>Output Power: 90 W Max Continuous, 540 W Max Pulsed (Overdrive Strobe) Output Current: 4.5A Max Continuous, 15 A Max Pulsed I/Os: 3 External Trigger Inputs Interface: 10/100 Ethernet with Software and browser-based GUIs. SDKs are also available.</p> <p>For more information about our DCS-100E, please visit the controller product page.</p>	
	<p>DCS Triple Output Controller - Compatible with C1 Configurations PN: DCS-103E</p> <p>The DCS-103E is a din-rail mounted general-purpose multi-light controller with three C1 output connectors. Capable of driving three lights in sync or asynchronously.</p> <p>Output Power: 30 W Max Continuous / Output, 180 W Max Pulsed / Output Output Current: 1.5A Max Continuous / Output, 5 A Max Pulsed / Output I/Os: 3 External Trigger Inputs Interface: 10/100 Ethernet with Software and browser-based GUIs. SDKs are also available.</p> <p>For more information about our DCS-103E, please visit the controller product page.</p>	
	<p>Pulsar 320E High Current Controller - Compatible with C5 Configuration PN: Pulsar 320E</p> <p>The Pulsar 320E is a high-power, dual output, pulse-only controller geared for overdriving driving lights at very short flash durations with very high current.</p> <p>Output Power: 2500 W Max Pulsed / Output Output Current: 50 A Max Pulsed / Output I/Os: 2 External Trigger Inputs Interface: 10/100 Ethernet with Software GUI. SDKs are also available.</p> <p>For more information about our Pulsar 320E, please visit the controller product page.</p>	


Electrical Information - Continued

Controller Image	Controller Details	Connector Image
<p>BL138 Embedded Controller - Continuous Only - IC Configurations PN: N/A</p> <p>The IC on the BL168 and BL138 are embedded controllers which allow for control of light intensity per 6" (152 mm) segment. Each segment is adjusted using a potentiometer located on each 6" segment. See the figure below for illustration:</p> 		

Controlling each 6" (152mm) section independently and making the center of the line less bright and the outside of the immediate camera viewing radius brighter ultimately results in better imaging.

Better imaging occurs because the camera can see very well in its area of focus, but outside that area the camera doesn't focus as well without brighter illumination.

We recommend using this control option for BL138 and BL168 lights over 24" (610mm) in length.

	<p>24V Driver - Continuous Only - 24 Configurations PN: N/A</p> <p>24V option allows lights to operate continuous output with 24V connection and no additional controllers.</p> <p>Modes: Continuous, can be wired to some 3rd party controllers or external relays for gated operation Interface: Direct cable (flying leads or connector options)</p>	
---	---	---

Electrical Information - Continued

24V Option Wiring Information

Flying Lead Functions

Wire Color	24V Functions
BROWN	24V DC
WHITE	0 - 10V Analog Control
BLUE	DC GND
BLACK	N/A
GRAY	N/A

The functions above are only applicable when ordering a 24V power configuration.

Accessories

Advanced Illumination offers a variety of accessories designed to pair with our lighting and control products. Below you will find a table of accessories which are compatible with many configurations of the BL138 series.

Category	Accessory Image	Accessory Detail
Power Supply		<p>24 Volt DC Power Supply PN: PS24-TL</p> <p>This convenient power source is a universal AC input switching power supply with a regulated output DC current. The power supply comes with an LED Power Indicator, tinned leads marked Positive (+) and Negative (-) and 2 WAGO connectors for simplified assembly.</p> <p>For more information about our 24 Volt DC Power Supply, please visit this webpage.</p>
Dimmer		<p>Manual Dimming Accessory for the IC, I3, I3s and I4 PN: DCS-MP</p> <p>The DCS-MP is a 30-position potentiometer, detented for precision level control and provides repeatable dimming with cable inline controllers. Features include DIN-rail mountable, a flip up cover to prevent accidental adjustments, spring clamp wiring terminal for flying leads or an M12 connector for use with the IC, I3/I3S or I4 Inline Controllers.</p> <p>For more information about our Manual Dimming Accessory please visit this webpage.</p>
Dimmer		<p>Manual Dimming Accessory for the IC PN: MP-ICS</p> <p>The MP-ICS is a dimmer which is designed for use on lights with the IC Inline Controller. This unit provides for 0 – 100% intensity control. It is NOT COMPATIBLE with LLI37, BLI38, LLI67, and BLI68 "IC" Lights or lights built with the "24v controller" option.</p> <p>For more information about our Manual Dimming Accessory, please visit this webpage.</p>
Extension Cable		<p>DCS-100E/103E Extension Cable, Single Light Power Cable - C1 Configuration PN: LC-XX-S</p> <p>This extension cable was designed for applications requiring power cables longer than the standard 2 meters provided with Ai lights. This single light cable features a single male and single female 7 pin locking connector (C1) and can be purchased in 3 - 15-meter lengths.</p> <p>For more information about our DCS-100E/103E Extension Cable, Single Output, please visit this webpage.</p>

Electrical Information - Continued

Category	Accessory Image	Accessory Detail
Extension Cable		<p>DCS-100E/103E Extension Cable, Dual Light Power Cable - C1 Configuration PN: LC-XX-Y</p> <p>This extension cable was designed for applications requiring two identical lights to be powered through a single controller. These Y cables feature a single male and dual female 7 pin locking connectors (C1) and can be purchased in 3 - 15-meter lengths. See attached spec sheet for compatible light configuration.</p> <p>For more information about our DCS-100E/103E Extension Cable, Split Output, please visit this webpage.</p>
Extension Cable		<p>Pulsar 320E Extension Cable - C5 Configuration PN: LC-XX-S-C5</p> <p>This extension cable was designed for applications requiring power cables longer than the standard 2 meters provided with Ai lights. This single light cable features a single male and single female Pulsar 320 connector (C5) and can be purchased in 3 - 15 meter lengths.</p> <p>For more information about our Pulsar 320E Extension Cable, please visit this webpage.</p>
Adaptor Cable		<p>Cognex Gen2 Inline Controller Adaptor Cable PN: AD-I3-CGX2</p> <p>This cable adaptor is for connecting I3/I3S configured lights with Cognex Gen2 Cameras, and comes with a male to female M12 connectors.</p> <p>For more information about our Cognex Gen2 Inline Controller Adaptor Cable, please visit this webpage.</p>
Filters		<p>Camera Lens Band Pass Filters PN: BPXXX-YYY</p> <p>Eliminating all but a narrow band of light (+/- 40nm) centered on the specified wavelength, band pass filters are used to enhance colors, or to stop unwanted ambient light from reaching the camera. Filtering can replace existing shrouds, simplifying the physical set up of an inspection site. Ai offers 635nm and 660nm band pass filters to fit several different lens sizes.</p> <p>For more information about our Camera Lens Band Pass Filters, please visit this webpage.</p>

Additional Information

Warranty

Every Advanced illumination, Inc. (Ai) product is thoroughly inspected and tested before leaving the factory. Products are warranted to be free of defects in workmanship and materials for a period of **FIVE YEARS** from the original date of purchase. Should a defect develop during this period, customers may return the complete product, freight prepaid, to one of Ai's distributors or to the Ai factory. All product warranty returns require a Return Merchandise Authorization (RMA) number which is obtained from Customer Service. The RMA number must be clearly marked on the outside of the package. Ai will inspect the unit, and if a defect is found will, at our option, repair or replace the product without charge. Ai disclaims liability for any implied warranties, including implied warranties of "merchantability" and "fitness for a specific purpose." For products under warranty that have since been discontinued, Ai will make an effort to replace with equivalent parts; for circumstances that do not allow for equivalent replacement, Ai reserves the right to repair or replace these products with an updated version. Ai cannot be held responsible for the unauthorized or inappropriate use of its products. Any unauthorized repair or modifications will result in a voided warranty. **No Liability for Consequential Damages:** In no event shall Ai be liable for any consequential, special, incidental, or indirect damages of any kind arising from the sale or use of the products.

Compliance

Our lighting products are designed and tested to meet CE, RoHS, and IEC standards. As a global ISO 9001 certified company, we understand the importance of compliance and perform accelerated testing on every product before shipment. For more information on our compliance standards, please see our compliance documentation here: <https://www.advancedillumination.com/services/compliance-statements/>

Electromagnetic Compatibility

This product was tested and complies with the regulatory requirements and limits for electromagnetic compatibility (EMC) as stated in the product specifications. These requirements and limits are designed to provide reasonable protection against harmful interference only when the product is operated in its intended industrial electromagnetic environment. To minimize the potential for electromagnetic interference or unacceptable performance degradation, install and use this product in strict accordance with the instructions in the product documentation.

Customer Service

For information on existing orders, or to make an order adjustment, contact us Monday through Friday 8:00 am to 5:00 pm ET or send an email to orders@advancedillumination.com.

Company Information

Advanced Illumination
440 State Garage Road, Rochester, VT 05767
Phone: +1 (802) 767 3830
Fax: +1 (802) 767 2636
Email: info@advancedillumination.com
Web: advancedillumination.com
© 2023 Advanced illumination Inc. All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Illumination:](#)

[BL13818-62524](#) [BL13818-53024](#) [BL13812-53024](#) [BL13818-85024](#) [BL13806-85024](#) [BL13812-45524](#) [BL13818-WHI24](#) [BL13806-62524](#) [BL13812-WHI24](#) [BL13806-WHI24](#) [BL13818-45524](#) [BL13812-85024](#) [BL13812-62524](#) [BL13806-45524](#) [BL13806-53024](#)