




SEC. A — A



SEC. 3-3



注意

1. 材質: BRASS, $t=0.25$
2. 処理: Snメッキ
3. 嵌合オスターミナル: 7114-1470

2 NOTE

- | |
|--|
| 1. MATERIAL : BRASS, t=0. 25 |
| 2. TREATMENT : TIN-PLATE |
| 3. MATING MALE TERMINAL PART NO. : 7114-1470 |


3	08. 10. 14	ADDED TOLERANCE ETC.	C08-Z724	C. S	CUSTOMER	CUSTOMER DWG NO.
2	90. 08. 20	ADDED TABLE ETC.	C90-7053	H. Y	CUSTOMER PART NO.	
1	85. 06. 12	注記及重量追加	C85-0765	八島		
	85. 05. 15	NEW	C85-0631	斎藤	OFFICE	TRIAL PART NO.
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR	
		GENERAL TOLERANCE			VENDOR NO.	
	10MAX	50MAX 100MAX 250MAX	2500VR	ANGLE	ECCENT	
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'
C	±0.3	±0.5	±0.8	±1.4	±2	±30'
SPECIFIED					MASS	
					0.3 g	

1



2

3



注意

1. 材質: BRASS, $t=0.25$
2. 処理: Snメッキ
3. 嵌合オスターミナル: 7114-1470

2 NOTE

- | |
|--|
| 1. MATERIAL : BRASS, t=0. 25 |
| 2. TREATMENT : TIN-PLATE |
| 3. MATING MALE TERMINAL PART NO. : 7114-1470 |


3	08. 10. 14	ADDED TOLERANCE ETC.	C08-Z724	C. S	CUSTOMER	CUSTOMER DWG NO.
2	90. 08. 20	ADDED TABLE ETC.	C90-7053	H. Y	CUSTOMER PART NO.	
1	85. 06. 12	注記及重量追加	C85-0765	八島		
	85. 05. 15	NEW	C85-0631	斎藤	OFFICE	TRIAL PART NO.
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR	
		GENERAL TOLERANCE			VENDOR NO.	
	10MAX	50MAX 100MAX 250MAX	2500VR	ANGLE	ECCENT	
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'
C	±0.3	±0.5	±0.8	±1.4	±2	±30'
SPECIFIED					MASS	
					0.3 g	

1



2

3



注意

1. 材質: BRASS, $t=0.25$
2. 処理: Snメッキ
3. 嵌合オスターミナル: 7114-1470

2 NOTE

- | |
|--|
| 1. MATERIAL : BRASS, t=0. 25 |
| 2. TREATMENT : TIN-PLATE |
| 3. MATING MALE TERMINAL PART NO. : 7114-1470 |

3	08. 10. 14	ADDED TOLERANCE ETC.	C08-Z724	C. S	CUSTOMER	CUSTOMER DWG NO.
2	90. 08. 20	ADDED TABLE ETC.	C90-7053	H. Y	CUSTOMER PART NO.	
1	85. 06. 12	注記及重量追加	C85-0765	八島		
	85. 05. 15	NEW	C85-0631	斎藤	OFFICE	TRIAL PART NO.
LET	DATE	REVISION RECORD	NO.	CHKD	VENDOR	
		GENERAL TOLERANCE			VENDOR NO.	
	10MAX	50MAX 100MAX 250MAX	2500VR	ANGLE	ECCENT	
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30'
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30'
C	±0.3	±0.5	±0.8	±1.4	±2	±30'
SPECIFIED					MASS	
					0.3 g	

1



2

3