

PRODUCT DATA

MicroStrain 3DM-CV7 Series

Tactical Grade Embeddable INS, IMU/AHRS, and IMU/VRU

MICROSTRAIN 3DM-CV7 SERIES SPECIFICATIONS

The 3DM-CV7 offers tactical grade inertial performance in the smallest and lightest OEM package yet. Each 3DM-CV7 is individually calibrated and features an Adaptive Extended Kalman Filter for optimal performance over a wide range of operating conditions.

All models in the 3DM-CV7 series feature cutting-edge orientation algorithms, advanced internal time management, and a flexible event triggering system. The INS model adds external position, velocity, and heading inputs as well as NMEA compatibility. With an unparalleled array of advanced features, the 3DM-CV7 sets the benchmark for value and performance in its category.

| Features | AR | AHRS | INS |
|--|----|------|-----|
| 1.5°/h Gyro Bias Instability | • | • | • |
| Low Latency | • | • | • |
| Superior Vibration Rejection | • | • | • |
| Adjustable Sampling Rates Up to 1 KHz | • | • | • |
| External Clock Synchronization | • | • | • |
| Adaptive Extended Kalman Filter | • | • | • |
| Custom Event Trigger System | • | • | • |
| Integrated Magnetometer | | • | • |
| External Position and Velocity Inputs | | | • |
| Industry-Standard NMEA Input Over AUX Port | | | • |
| Defense-Ready: Accepts Encrypted GNSS Receivers | | | • |
| Filter Body Frame Constraints | | | • |
| Body Velocity Inputs and Outputs | | | • |





System Performance

| Attitude and Heading (-AR, -AHRS) | |
|------------------------------------|-------|
| Roll, Pitch (static) | 0.25° |
| Roll, Pitch(dynamic) [1] | 0.5° |
| Heading (static, AHRS only) [2] | 0.5° |
| Heading (dynamic, AHRS only) [1,2] | 2° |

| INS Accuracy [4] | |
|------------------|--------------------------------|
| Position | External GNSS-Dependent |
| Velocity | External GNSS-Dependent |
| Roll, Pitch | TBD |
| Heading | TBD or External GNSS-Dependent |

IMU

| | Accelerometer | Gyroscope | Magnetometer | Barometer |
|-------------------------------------|---------------|---------------------------|--------------|------------------|
| Range | ± 4g, 8g, 16g | ± 250°/s, 500°/s, 1000°/s | ±8 Gauss | 260 to 1260 mbar |
| Random Walk | 30 μg/√Hz | 0.14 °/√h | - | - |
| Bias instability | 18 µg | 1.5 °/h | - | - |
| Noise Density | 30 μg/√Hz | 8.5 °/h/√Hz | - | - |
| Turn-on to Turn-on Bias [3] | 40 μg | 0.004 °/s | - | - |
| Bias Error Over Temperature | 0.75 mg | 0.03 °/s | - | - |
| Scale Factor Error Over Temperature | 600 PPM | 1000 PPM | - | - |

Interface


| Connector | Samtec FTS-105 (2x5) |
|--------------------------------|--|
| Communications Interface | UART (TTL), USB |
| Output Data Rate (IMU and EKF) | 1 to 1000 Hz |
| 1/0 | 4x GPIO |
| GPIO Functions | Event triggering, PPS Input/Output |
| Protocols | MIP, NMEA [4] |
| Aiding Sensors | External Heading, Position [4], Velocity [4], Pressure, Magnetic Field, Body Frame Velocity |


Physical and Electrical

| Weight | 8.3g |
|-----------------------|---|
| Size | 38 mm x 24 mm x 8.6 mm |
| Power Consumption | 230 mW (Typical), 280 mW (Max) |
| Operating Voltage | 3.2 to 5.2 VDC |
| GPIO Voltage | 3V (5V tolerant) |
| Operating Temperature | -40°C to 85°C |
| MTBF | 2,002,026 hours (Telecordia Method, GM/35C) |

Product Variants

| Name | Part Number | Description |
|--------------|-------------|---|
| 3DM-CV7-INS | 6291-9960 | Inertial Navigation System |
| 3DM-CV7-AHRS | 6286-9960 | Attitude and Magnetometer-Aided Heading |
| 3DM-CV7-AR | 6287-9960 | Attitude and Relative Heading |






- [1] Automotive conditions, vehicle dynamics
- dependent


 [2] Magnetic heading, with valid declination, magnetic environment, and hard/soft iron calibration

 [3] Bias repeatability, <24 hours

 [4] INS model only

MICROSTRAIN 3DM-CV7 SERIES ALLAN VARIANCE (AVAR)





MICROSTRAIN 3DM-CV7 SERIES KEY FEATURES

External Clock Synchronization

 Tighter synchronization with external sensors like LiDAR or cameras to improve state estimation

Tactical Grade Gyro

 Improved position accuracy during dead reckoning

Custom Event Trigger System

 Simplifies configuration of context-based events and frees up CPU on vehicle main board

User-Adjustable Gyro & Accel Range

• Range flexibility enables improved noise performance

Low Latency

 Reduces navigation errors from clock drift when combining with external aiding sensors

Adjustable Sampling Rates

• Faster response to vehicle dynamics

Calibrated Over Full Temperature Range

Consistent and reliable performance over entire temperature range

| Auto-Adaptive EKF | |
|---------------------------------------|---|
| Adaptive Extended Kalman Filter (EKF) | More reliable than pre-configured vehicle dynamics model. Rejects the unexpected and auto-adapts its error model to dynamics in real-time |

| EKF for Orientation Estimation (-AR, -AHRS) | |
|---|---|
| Adaptive Extended Kalman Filter (EKF) | Reduces attitude error due to linear acceleration |
| IMU Bias Error Tracking | Improves performance over traditional complementary filters |
| Integrated Magnetometer | Allows for absolute heading tracking (-AHRS and -INS only) |

| EKF for Position, Velocity, Attitude Estimation (-INS) | | |
|---|---|--|
| External Position, Velocity, Heading Inputs | Improves position, velocity, attitude (PVA) estimate of standalone GNSS receiver | |
| Industry-Standard NMEA Input Over AUX Port | Simplifies GNSS input by providing configurable AUX port on any of the 4 GPIO ports | |
| Defense-Ready: Accepts Encrypted GNSS Receivers (SAASM or MCode) | Improves reliability of Position, Navigation, and Timing (PNT) solution during jamming and spoofing events | |
| Filter Body Frame Constraints | Improves position accuracy for known dynamics | |
| Vehicle Frame Velocity I/O | Allows users to input measurements in a non-global frame, enabling sensors like radar and vision as aiding sources (with preprocessing) | |

3 Document 8400-0141 Revision G www.hbkworld.com

Designed for High Volume Production

 Aluminum mounting frame eliminates board stress, thermal shock, and alignment errors seen in surface mount devices for repeatable higher accuracy performance.

Backward Compatibility

 MicroStrain Inertial Packet (MIP) protocol enables simple upgrades from other MicroStrain devices.

SensorConnect*

SensorConnect is PC software for sensor configuration and data collection. Configure inertial parameters, device settings, data channels, and sample rates.

Visualize massive amounts of data instantly using built-in intelligent data collection and graphing algorithms. Create immersive dashboards with rich data visualization.

MSCL™ API and MIP SDK

The MicroStrain Communication Library (MSCL) is our open-sourced API that simplifies writing code to interact with our sensors. MIP SDK is a lightweight C/C++ library for interacting with MicroStrain G and C-series products via baremetal and resource constrained microcontrollers.

Both APIs are readily available and fully-documented on GitHub, featuring valuable tools such as full documentation, example code, and a quick start guide.

:::ROS

MicroStrain offers an open source, license-free (MIT License) series of actively supported drivers specifically designed and tested for Robot Operating System (ROS).

Use ROS for building and simulating robotics applications, unmanned ground vehicles (UGVs) and simultaneous localization and mapping (SLAM).

Actively Maintained Software

 Engineers actively supporting software products ensures features are available, and can assist in integration with your application's nav stack.

Complimentary Support

 Support and Application Engineers provide product integration guidance to provide a smooth test and integration experience.









