



SIMATIC HMI, KTP900 Basic, Basic Panel, Key/touch operation, 9" TFT display, 65536 colors, PROFINET interface, configurable from WinCC Basic V13/ STEP 7 Basic V13, contains open-source software, which is provided free of charge see enclosed CD

| General information | |
|---|--|
| Product type designation | KTP900 Basic color PN |
| Display | |
| Design of display | TFT widescreen display, LED backlighting |
| Screen diagonal | 9 in |
| Display width | 198 mm |
| Display height | 111.7 mm |
| Number of colors | 65 536 |
| Resolution (pixels) | |
| • Horizontal image resolution | 800 pixel |
| • Vertical image resolution | 480 pixel |
| Backlighting | |
| • MTBF backlighting (at 25 °C) | 20 000 h |
| • Backlight dimmable | Yes |
| Control elements | |
| Keyboard | |
| • Function keys | |
| — Number of function keys | 8 |
| — Number of function keys with LEDs | 0 |
| • Keys with LED | No |
| • System keys | No |
| • Numeric keyboard | Yes; Onscreen keyboard |
| • alphanumeric keyboard | Yes; Onscreen keyboard |
| Touch operation | |
| • Design as touch screen | Yes; Analog-resistive |
| Installation type/mounting | |
| Mounting position | vertical |
| Mounting in portrait format possible | Yes |
| Mounting in landscape format possible | Yes |
| maximum permissible angle of inclination without external ventilation | 35° |
| Supply voltage | |
| Type of supply voltage | DC |
| Rated value (DC) | 24 V |
| permissible range, lower limit (DC) | 19.2 V |
| permissible range, upper limit (DC) | 28.8 V |
| Input current | |
| Current consumption (rated value) | 230 mA |
| Starting current inrush I ² t | 0.2 A ² ·s |

| Power | |
|--|---|
| Active power input, typ. | 5.5 W |
| Processor | |
| Processor type | ARM |
| Storage | |
| Flash | Yes |
| RAM | Yes |
| Memory available for user data | 10 Mbyte |
| Type of output | |
| Acoustics | |
| • Buzzer | Yes |
| • Speaker | No |
| Time of day | |
| Clock | |
| • Hardware clock (real-time) | Yes |
| • Software clock | Yes |
| • retentive | Yes; Back-up duration typically 6 weeks |
| • synchronizable | Yes |
| Interfaces | |
| Number of industrial Ethernet interfaces | 1 |
| Number of RS 485 interfaces | 0 |
| Number of RS 422 interfaces | 0 |
| Number of RS 232 interfaces | 0 |
| Number of USB interfaces | 1; Up to 16 GB |
| Number of 20 mA interfaces (TTY) | 0 |
| Number of parallel interfaces | 0 |
| Number of other interfaces | 0 |
| Number of SD card slots | 0 |
| With software interfaces | No |
| Industrial Ethernet | |
| • Industrial Ethernet status LED | 2 |
| Protocols | |
| PROFINET | Yes |
| Supports protocol for PROFINET IO | No |
| IRT | No |
| PROFIBUS | No |
| EtherNet/IP | Yes |
| MPI | No |
| Protocols (Ethernet) | |
| • TCP/IP | Yes |
| • DHCP | Yes |
| • DCP | Yes |
| • LLDP | Yes |
| WEB characteristics | |
| • HTTP | No |
| • HTML | No |
| Redundancy mode | |
| Media redundancy | |
| — MRP | No |
| Further protocols | |
| • CAN | No |
| • MODBUS | Yes; Modicon (MODBUS TCP/IP) |
| Interrupts/diagnostics/status information | |
| Diagnoses | |
| • Diagnostic information readable | No |
| EMC | |
| Emission of radio interference acc. to EN 55 011 | |
| • Limit class A, for use in industrial areas | Yes |

| | |
|--|-----------------------|
| • Limit class B, for use in residential areas | No |
| Degree and class of protection | |
| IP (at the front) | IP65 |
| IP (rear) | IP20 |
| NEMA (front) | |
| • Enclosure Type 4 at the front | Yes |
| • Enclosure Type 4x at the front | Yes |
| Standards, approvals, certificates | |
| CE mark | Yes |
| cULus | Yes |
| RCM (formerly C-TICK) | Yes |
| KC approval | Yes |
| Use in hazardous areas | |
| • ATEX Zone 2 | No |
| • ATEX Zone 22 | No |
| • IECEx Zone 2 | No |
| • IECEx Zone 22 | No |
| • cULus Class I Zone 1 | No |
| • cULus Class I Zone 2, Division 2 | No |
| • FM Class I Division 2 | No |
| Marine approval | |
| • Germanischer Lloyd (GL) | Yes |
| • American Bureau of Shipping (ABS) | Yes |
| • Bureau Veritas (BV) | Yes |
| • Det Norske Veritas (DNV) | Yes |
| • Lloyds Register of Shipping (LRS) | Yes |
| • Nippon Kaiji Kyokai (Class NK) | Yes |
| • Polski Rejestr Statkow (PRS) | No |
| • Chinese Classification Society (CCS) | No |
| Ambient conditions | |
| Ambient temperature during operation | |
| Operation (vertical installation) | |
| — For vertical installation, min. | 0 °C |
| — For vertical installation, max. | 50 °C |
| Operation (max. tilt angle) | |
| — At maximum tilt angle, min. | 0 °C |
| — At maximum tilt angle, max. | 40 °C |
| Operation (vertical installation, portrait format) | |
| — For vertical installation, min. | 0 °C |
| — For vertical installation, max. | 40 °C |
| Operation (max. tilt angle, portrait format) | |
| — At maximum tilt angle, min. | 0 °C |
| — At maximum tilt angle, max. | 35 °C |
| Ambient temperature during storage/transportation | |
| • min. | -20 °C |
| • max. | 60 °C |
| Relative humidity | |
| • Operation, max. | 90 %; no condensation |
| Operating systems | |
| proprietary | Yes |
| pre-installed operating system | |
| • Windows CE | No |
| Configuration | |
| Message indicator | Yes |
| Alarm system (incl. buffer and acknowledgment) | Yes |
| Process value display (output) | Yes |
| Process value default (input) possible | Yes |
| Recipe management | Yes |
| Configuration software | |

| | |
|--|---|
| • STEP 7 Basic (TIA Portal) | Yes; via integrated WinCC Basic (TIA Portal) |
| • STEP 7 Professional (TIA Portal) | Yes; via integrated WinCC Basic (TIA Portal) |
| • WinCC flexible Compact | No |
| • WinCC flexible Standard | No |
| • WinCC flexible Advanced | No |
| • WinCC Basic (TIA Portal) | Yes |
| • WinCC Comfort (TIA Portal) | Yes |
| • WinCC Advanced (TIA Portal) | Yes |
| • WinCC Professional (TIA Portal) | Yes |
| Languages | |
| Online languages | |
| • Number of online/runtime languages | 10 |
| Project languages | |
| • Languages per project | 32 |
| Functionality under WinCC (TIA Portal) | |
| Libraries | Yes |
| Applications/options | |
| • Web browser | Yes |
| • SIMATIC WinCC Sm@rtServer | Yes; Available with WinCC (TIA Portal) V14 or higher |
| Number of Visual Basic Scripts | No |
| Task planner | |
| • time-controlled | No |
| • task-controlled | Yes |
| Help system | |
| • Number of characters per info text | 500 |
| Message system | |
| • Number of alarm classes | 32 |
| • Bit messages | |
| — Number of bit messages | 1 000 |
| • Analog messages | |
| — Number of analog messages | 25 |
| • S7 alarm number procedure | No |
| • System messages HMI | Yes |
| • System event, more (SIMATIC S7, SINUMERIK, SIMOTION, ...) | Yes; System message buffer of the SIMATIC S7-1200 and S7-1500 |
| • Number of characters per message | 80 |
| • Number of process values per message | 8 |
| • Acknowledgment groups | Yes |
| • Message indicator | Yes |
| • Message buffer | |
| — Number of entries | 256 |
| — Circulating buffer | Yes |
| — retentive | Yes |
| — maintenance-free | Yes |
| Recipe management | |
| • Number of recipes | 50 |
| • Data records per recipe | 100 |
| • Entries per data record | 100 |
| • Size of internal recipe memory | 256 kbyte |
| • Recipe memory expandable | No |
| Variables | |
| • Number of variables per device | 800 |
| • Number of variables per screen | 100 |
| • Limit values | Yes |
| • Multiplexing | Yes |
| • Structures | No |
| • Arrays | Yes |
| Images | |
| • Number of configurable images | 250 |

| | |
|--|---|
| • Permanent window/default | Yes |
| • Global image | Yes |
| • Pop-up images | No |
| • Slide-in images | No |
| • Image selection by PLC | Yes |
| • Image number in the PLC | Yes |
| Image objects | |
| • Number of objects per image | 100 |
| • Text fields | Yes |
| • I/O fields | Yes |
| • Graphic I/O fields (graphics list) | Yes |
| • Symbolic I/O fields (text list) | Yes |
| • Date/time fields | Yes |
| • Switches | Yes |
| • Buttons | Yes |
| • Graphic display | Yes |
| • Icons | Yes |
| • Geometric objects | Yes |
| Complex image objects | |
| • Number of complex objects per screen | 10 |
| • Alarm view | Yes |
| • Trend view | Yes |
| • User view | Yes |
| • Status/control | No |
| • Sm@rtClient view | No |
| • Recipe view | Yes |
| • f(x) trend view | No |
| • System diagnostics view | Yes; System message buffer of the SIMATIC S7-1200 and S7-1500 |
| • Media Player | No |
| • HTML browser | Yes |
| • PDF display | No |
| • IP camera display | No |
| • Bar graphs | Yes |
| • Sliders | No |
| • Pointer instruments | No |
| • Analog/digital clock | No |
| Lists | |
| • Number of text lists per project | 300 |
| • Number of entries per text list | 100 |
| • Number of graphics lists per project | 100 |
| • Number of entries per graphics list | 100 |
| Archiving | |
| • Number of archives per device | 2; One message and one process value archive |
| • Number of entries per archive | 10 000 |
| • Message archive | Yes |
| • Process value archive | Yes |
| • Archiving methods | |
| — Sequential archive | Yes |
| — Short-term archive | Yes |
| • Memory location | |
| — Memory card | No |
| — USB memory | Yes |
| — Ethernet | No |
| • Data storage format | |
| — CSV | No |
| — TXT | Yes |
| — RDB | No |
| Security | |
| • Number of user groups | 50 |

| | | | |
|--|----------------------------|----------------|-----------------------|
| • Number of user rights | 32 | | |
| • Number of users | 50 | | |
| • Password export/import | Yes | | |
| • SIMATIC Logon | No | | |
| Character sets | | | |
| • Keyboard fonts | | | |
| — US English | Yes | | |
| Transfer (upload/download) | | | |
| • MPI/PROFIBUS DP | No | | |
| • USB | No | | |
| • Ethernet | Yes | | |
| • using external storage medium | Yes | | |
| Process coupling | | | |
| • S7-1200 | Yes | | |
| • S7-1500 | Yes | | |
| • S7-200 | Yes | | |
| • S7-300/400 | Yes | | |
| • LOGO! | Yes | | |
| • WinAC | Yes | | |
| • SINUMERIK | Yes; No access to NCK data | | |
| • SIMOTION | Yes | | |
| • Allen Bradley (EtherNet/IP) | Yes | | |
| • Allen Bradley (DF1) | No | | |
| • Mitsubishi (MC TCP/IP) | Yes | | |
| • Mitsubishi (FX) | No | | |
| • OMRON (FINS TCP) | No | | |
| • OMRON (Host Link) | No | | |
| • Modicon (Modbus TCP/IP) | Yes | | |
| • Modicon (Modbus RTU) | No | | |
| Service tools/configuration aids | | | |
| • Backup/Restore manually | Yes | | |
| • Backup/Restore automatically | No | | |
| • Simulation | Yes | | |
| • Device switchover | Yes | | |
| Peripherals/Options | | | |
| Printer | No | | |
| SIMATIC HMI MM memory card: Multi Media Card | No | | |
| SIMATIC HMI SD memory card: Secure Digital memory card | No | | |
| SIMATIC HMI CF memory card Compact Flash Card | No | | |
| USB memory | Yes | | |
| SIMATIC IPC USB Flashdrive (USB stick) | Yes | | |
| SIMATIC HMI USB stick | Yes | | |
| Mechanics/material | | | |
| Enclosure material (front) | | | |
| • Plastic | Yes | | |
| • Aluminum | No | | |
| • Stainless steel | No | | |
| Dimensions | | | |
| Width of the housing front | 267 mm | | |
| Height of housing front | 182 mm | | |
| Mounting cutout, width | 251 mm | | |
| Mounting cutout, height | 166 mm | | |
| mounting depth | 39.4 mm | | |
| Weights | | | |
| Weight (without packaging) | 1 130 g | | |
| Weight (with packaging) | 1 393 g | | |
| Classifications | | | |
| | | Version | Classification |

| | | |
|--------|-----|-------------|
| eClass | 14 | 27-33-02-01 |
| eClass | 12 | 27-33-02-01 |
| eClass | 9.1 | 27-33-02-01 |
| eClass | 9 | 27-33-02-01 |
| eClass | 8 | 27-24-23-02 |
| eClass | 7.1 | 27-24-23-02 |
| eClass | 6 | 27-24-23-02 |
| ETIM | 10 | EC001412 |
| ETIM | 9 | EC001412 |
| ETIM | 8 | EC001412 |
| ETIM | 7 | EC001412 |
| IDEA | 4 | 6607 |
| UNSPSC | 15 | 43-21-15-06 |

Approvals / Certificates

General Product Approval



[Manufacturer Declaration](#)

[Miscellaneous](#)



General Product Approval

Maritime application



[China RoHS](#)



Maritime application

[NK / Nippon Kaiji Kyokai](#)

[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

last modified:

7/2/2025