



Image for illustrative purpose only

Summary

[Request a quote](#)

[P series catalog](#)

[Customer Drawing](#)

| | |
|--------------------------------|--|
| Number of contacts Low Voltage | 34 |
| Gender | Standard |
| Socket / Receptacle | Socket / Receptacle - Fixed Panel Rear Mounted |
| Locking system | Push-pull |
| Size | 2P |
| Suggested matching part | CAB.M34.GLA.C72G |
| Series | REDEL P - Push-Pull |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/ckb-m34-glng.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Technical details

Electrical Configuration

| | |
|---------------------------------|-----------------------------|
| Number of contacts Low Voltage | 34 |
| Contact Termination Low voltage | PCB - Straight |
| Insert configuration value | 2P.M34 - 34 Low V. |
| Insulator | L: PEEK for solder contacts |
| Rated current | 1.5 A |
| Test voltage contact-contact | 0.92 (kV DC) |
| Air clearance | 0.3 mm |
| Creepage distance | 0.3 mm |
| Contact Dia. | 0.5 |
| Gender | Standard |

Form & Material

| | |
|------------------------|---|
| Shell style / Model id | CK - Fixed receptacle with two nuts (back panel mounting) |
| Socket / Receptacle | Fixed Panel Rear Mounted |
| Housing material | PSU (Polysulfone), grey |
| Locking system | Push-pull |
| Keying | B: 3 keys (alpha=0, gamma=60, Plug: male contacts, Receptacle: female contacts) |
| Colour | Grey |
| Weight | 7.17 g |

Environment

| | |
|-----------------------------------|--|
| Technical domain | Energy and Industrial, Medical, Test and Measurement, Transportation, Aerospace and UAV |
| Environmental sealing (IP rating) | IP50 |
| Endurance | >5000 mating cycles |
| Temperature range | -50°C / +150°C |
| F ret (max) | 250 N |
| F ret (min) | 150 N |
| Steam sterilization | Compiles with ISO 17665:2024 sterilization standard for autoclave, ISO 11135:2014 for EtO, and ISO 11137-1, -2, -3 standards for gamma, e-beam x-ray. For more details on sterilization methods and cycles, please contact us. |

https://www.lemo.com/int_en/solutions/redel/redel-p-push-pull/ckb-m34-glmg.html

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Documents

| | |
|------------|--------------------------|
| PCB | Download |
| PCB Eagle | Download |
| Kicad | Download |
| PCB Altium | Download |